

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332667-830

Luminaire Tested: **SA4XXDIP-C1020D1205U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332667-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D1205U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8707.1 lumens
Efficiency: N/A
Efficacy: 133.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332667-830
CATALOG NUMBER: SA4XXDIP-C1020D1205U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332667-830

CATALOG NUMBER: SA4XXDIP-C1020D1205U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46	40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38	34
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33	29
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28	25
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25	21
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16	13
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13130	13130	13130
5°	13169	13011	13105
10°	13086	12904	12969
15°	12929	12721	12754
20°	12718	12494	12506
25°	12479	12235	12200
30°	12185	11929	11820
35°	11880	11610	11456
40°	11564	11248	11041
45°	11233	10891	10683
50°	10868	10574	10246
55°	10473	10162	9831
60°	10078	9700	9405
65°	9635	9259	8886
70°	9135	8674	8337
75°	8372	7966	7764
80°	7452	7146	6969
85°	6521	6280	6150



TEST NUMBER: P332667-830

CATALOG NUMBER: SA4XXDIP-C1020D1205U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.2	1.8
10°-20°	431.5	5.0
20°-30°	635.2	7.3
30°-40°	738.4	8.5
40°-50°	738.4	8.5
50°-60°	645.9	7.4
60°-70°	479.7	5.5
70°-80°	272.5	3.1
80°-90°	82.9	1.0
90°-100°	50.1	0.6
100°-110°	319.3	3.7
110°-120°	610.8	7.0
120°-130°	775.4	8.9
130°-140°	829.7	9.5
140°-150°	775.8	8.9
150°-160°	625.7	7.2
160°-170°	403.5	4.6
170°-180°	139.1	1.6
0°-30°	1219.8	14.0
0°-40°	1958.2	22.5
0°-60°	3342.6	38.4
0°-90°	4177.7	48.0
90°-120°	980.2	11.3
90°-150°	3361.2	38.6
90°-180°	4529.0	52.0
0°-180°	8707.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1626	1626	1626	1626	1626	
5°	1625	1619	1606	1619	1617	154
15°	1547	1541	1522	1529	1526	436
25°	1401	1391	1374	1374	1370	644
35°	1205	1196	1178	1169	1162	753
45°	984	974	954	940	936	758
55°	744	739	722	707	698	666
65°	504	497	485	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	78
90°	3	15	24	30	33	7
95°	60	25	24	30	32	77
105°	330	336	342	349	312	345
115°	616	619	618	620	620	605
125°	865	869	867	871	872	772
135°	1073	1072	1077	1079	1081	827
145°	1238	1241	1241	1242	1244	773
155°	1357	1358	1355	1359	1356	625
165°	1431	1426	1426	1434	1425	404
175°	1464	1458	1459	1467	1456	139
180°	1464	1464	1464	1464	1464	



TEST NUMBER: P332667-830

CATALOG NUMBER: SA4XXDIP-C1020D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1630.5	1629.8	1629.1	1628.4	1627.8	1626.1	1623.5	1621.0	1618.4	1615.9	1618.3
5°	1625.0	1623.9	1622.8	1621.6	1620.4	1618.3	1615.0	1611.8	1608.7	1605.5	1608.7
7.5°	1610.0	1608.7	1607.6	1606.5	1605.3	1603.0	1599.4	1595.9	1592.3	1588.8	1591.4
10°	1596.4	1595.3	1594.0	1592.9	1591.8	1589.3	1585.5	1581.8	1578.0	1574.2	1576.5
12.5°	1578.7	1577.5	1576.3	1575.2	1574.0	1571.4	1567.4	1563.5	1559.4	1555.5	1558.0
15°	1546.9	1545.7	1544.5	1543.4	1542.2	1539.5	1535.1	1530.8	1526.4	1522.1	1523.8
17.5°	1508.5	1507.1	1505.6	1504.2	1502.8	1500.0	1495.8	1491.8	1487.6	1483.6	1484.6
20°	1480.4	1478.9	1477.5	1476.0	1474.6	1471.7	1467.4	1463.0	1458.7	1454.3	1455.2
22.5°	1450.2	1448.2	1446.3	1444.4	1442.6	1439.4	1435.0	1430.7	1426.3	1422.0	1423.6
25°	1400.9	1398.9	1396.8	1394.8	1392.8	1389.8	1385.7	1381.7	1377.6	1373.6	1373.9
27.5°	1344.6	1342.6	1340.4	1338.3	1336.2	1333.3	1329.6	1325.8	1322.0	1318.2	1317.6
30°	1307.1	1304.8	1302.4	1300.1	1297.8	1294.8	1291.0	1287.2	1283.5	1279.7	1278.6
32.5°	1267.4	1265.4	1263.3	1261.2	1259.1	1256.0	1252.1	1248.1	1244.1	1240.1	1238.7
35°	1205.4	1203.4	1201.4	1199.4	1197.3	1194.3	1190.2	1186.2	1182.1	1178.1	1176.0
37.5°	1140.0	1138.1	1136.3	1134.4	1132.6	1129.5	1125.1	1120.8	1116.4	1112.1	1109.9
40°	1097.3	1095.0	1092.6	1090.3	1088.0	1084.7	1080.3	1076.0	1071.7	1067.3	1064.4
42.5°	1051.4	1050.0	1048.6	1047.3	1045.8	1042.7	1037.9	1033.1	1028.3	1023.5	1020.1
45°	983.9	981.8	979.9	977.8	975.8	972.4	967.8	963.2	958.6	953.9	950.7
47.5°	913.2	911.9	910.5	909.1	907.7	904.8	900.6	896.3	892.0	887.7	884.1
50°	865.3	864.1	863.0	861.9	860.6	858.1	854.0	850.0	845.9	841.9	837.8
52.5°	818.4	817.0	815.6	814.3	812.8	810.0	805.7	801.4	797.1	792.9	789.3
55°	744.1	743.2	742.3	741.5	740.6	738.2	734.1	730.1	726.0	722.0	718.5
57.5°	673.3	672.2	671.3	670.2	669.3	666.8	662.8	658.8	654.8	650.8	647.5
60°	624.2	622.7	621.3	619.9	618.4	615.9	612.1	608.3	604.5	600.8	598.1
62.5°	576.3	575.0	573.8	572.6	571.4	568.8	564.8	560.8	556.8	552.8	550.4
65°	504.4	502.8	501.4	500.0	498.5	496.3	493.4	490.6	487.7	484.7	481.9
67.5°	431.9	430.6	429.2	427.9	426.5	424.5	421.7	419.0	416.1	413.4	410.6
70°	387.0	385.0	383.0	381.0	378.9	376.7	374.5	372.1	369.9	367.5	365.1
72.5°	339.1	337.1	335.1	333.0	331.0	329.0	327.2	325.4	323.5	321.6	319.8
75°	268.4	267.0	265.5	264.1	262.7	261.2	259.8	258.4	256.8	255.4	254.3
77.5°	201.0	200.3	199.6	199.1	198.4	197.5	196.1	194.9	193.6	192.4	192.0
80°	160.3	159.4	158.5	157.7	156.8	156.1	155.5	155.0	154.4	153.7	153.2
82.5°	120.6	120.3	119.9	119.4	119.0	118.8	118.7	118.6	118.5	118.3	118.0
85°	70.4	70.4	70.4	70.4	70.4	70.1	69.5	68.9	68.3	67.8	67.8
87.5°	27.8	28.1	28.4	28.7	28.9	29.2	29.4	29.5	29.7	29.9	30.2
90°	3.3	5.9	8.7	11.3	13.9	16.3	18.3	20.2	22.1	24.1	25.5
92.5°	13.8	13.9	14.1	14.2	14.4	15.5	17.3	19.3	21.3	23.2	24.7
95°	60.2	51.9	43.6	35.4	27.1	23.1	23.4	23.6	23.8	24.1	25.5
97.5°	127.9	133.1	138.3	143.4	148.5	137.5	110.4	83.2	56.1	28.9	29.0
100°	179.6	184.0	188.4	192.7	197.2	182.6	148.9	115.4	81.8	48.2	44.0
102.5°	237.4	240.6	243.8	247.0	250.2	249.7	245.3	240.9	236.6	232.1	187.6
105°	329.6	331.1	332.5	334.0	335.5	336.9	338.1	339.2	340.4	341.7	343.9
107.5°	415.3	416.0	416.8	417.5	418.2	419.4	421.0	422.7	424.3	426.0	427.1
110°	473.2	473.8	474.6	475.3	476.1	477.1	478.6	480.0	481.5	483.0	483.4



TEST NUMBER: P332667-830

CATALOG NUMBER: SA4XXDIP-C1020D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	529.2	530.6	531.8	533.1	534.4	535.5	536.1	536.8	537.5	538.2	538.1
115°	615.5	616.2	617.0	617.6	618.4	618.7	618.4	618.2	617.9	617.6	618.2
117.5°	693.2	694.2	695.2	696.2	697.1	697.9	698.4	699.0	699.6	700.0	699.9
120°	745.8	746.8	747.8	748.8	749.7	750.1	749.9	749.6	749.3	749.1	749.6
122.5°	794.8	795.5	796.1	796.6	797.2	797.7	798.1	798.3	798.7	799.1	799.4
125°	865.2	866.2	867.1	868.1	869.1	869.3	868.8	868.4	867.9	867.4	868.1
127.5°	931.8	932.0	932.3	932.6	932.7	933.4	934.5	935.7	936.8	937.9	937.7
130°	974.7	975.0	975.2	975.4	975.7	976.2	976.9	977.6	978.4	979.1	979.3
132.5°	1014.2	1014.6	1015.0	1015.5	1015.9	1016.6	1017.5	1018.4	1019.4	1020.3	1020.5
135°	1073.3	1073.1	1072.8	1072.5	1072.3	1072.7	1073.7	1074.6	1075.6	1076.6	1077.0
137.5°	1125.7	1125.8	1125.9	1126.0	1126.1	1126.6	1127.7	1128.8	1129.8	1130.9	1131.4
140°	1159.8	1160.3	1160.7	1161.3	1161.8	1162.2	1162.7	1163.2	1163.7	1164.2	1164.9
142.5°	1190.4	1191.4	1192.2	1193.1	1194.0	1194.6	1194.9	1195.1	1195.4	1195.7	1196.3
145°	1237.6	1238.3	1239.1	1239.7	1240.5	1240.9	1240.9	1240.9	1240.9	1240.9	1241.1
147.5°	1275.0	1276.4	1277.7	1279.1	1280.4	1281.0	1280.8	1280.5	1280.3	1280.1	1280.3
150°	1302.2	1303.2	1304.1	1305.1	1306.1	1306.5	1306.2	1306.0	1305.7	1305.4	1305.4
152.5°	1324.9	1325.8	1326.5	1327.3	1328.0	1328.2	1327.9	1327.4	1326.9	1326.5	1326.9
155°	1357.0	1357.2	1357.4	1357.6	1357.9	1357.6	1357.0	1356.2	1355.5	1354.7	1355.8
157.5°	1383.8	1383.7	1383.6	1383.5	1383.3	1382.8	1382.0	1381.2	1380.4	1379.5	1380.7
160°	1399.7	1398.9	1398.2	1397.5	1396.8	1396.3	1396.0	1395.7	1395.5	1395.2	1396.8
162.5°	1413.6	1412.8	1411.8	1410.9	1409.9	1409.4	1409.1	1408.9	1408.6	1408.4	1409.9
165°	1431.4	1430.2	1429.0	1427.8	1426.5	1426.0	1426.0	1426.0	1426.0	1426.0	1427.9
167.5°	1445.4	1444.2	1442.9	1441.6	1440.4	1439.6	1439.5	1439.4	1439.3	1439.1	1441.2
170°	1453.3	1451.9	1450.4	1449.0	1447.5	1446.9	1447.1	1447.4	1447.6	1447.8	1449.8
172.5°	1458.6	1457.1	1455.7	1454.2	1452.7	1452.1	1452.4	1452.6	1452.8	1453.1	1455.0
175°	1464.2	1462.8	1461.3	1459.9	1458.4	1457.8	1458.0	1458.3	1458.6	1458.8	1460.9
177.5°	1466.9	1465.6	1464.1	1462.8	1461.4	1460.9	1461.3	1461.7	1462.2	1462.5	1464.1
180°	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2



TEST NUMBER: P332667-830

CATALOG NUMBER: SA4XXDIP-C1020D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1620.5	1622.9	1625.2	1626.3	1626.0	1625.8	1625.5	1625.3
5°	1611.8	1615.0	1618.3	1619.6	1619.0	1618.3	1617.8	1617.2
7.5°	1593.9	1596.5	1599.0	1600.2	1599.8	1599.4	1599.0	1598.7
10°	1578.9	1581.2	1583.5	1584.3	1583.8	1583.2	1582.6	1582.1
12.5°	1560.6	1563.1	1565.7	1566.5	1565.8	1564.9	1564.1	1563.3
15°	1525.6	1527.3	1529.1	1529.5	1528.6	1527.8	1526.9	1526.0
17.5°	1485.7	1486.9	1487.9	1488.2	1487.6	1487.0	1486.5	1485.8
20°	1456.0	1457.0	1457.8	1457.9	1457.4	1456.8	1456.2	1455.7
22.5°	1425.1	1426.7	1428.2	1428.5	1427.5	1426.4	1425.4	1424.4
25°	1374.1	1374.4	1374.7	1374.2	1373.1	1372.0	1370.7	1369.6
27.5°	1316.9	1316.2	1315.5	1314.5	1313.0	1311.5	1310.0	1308.6
30°	1277.4	1276.2	1275.1	1273.8	1272.3	1270.8	1269.4	1268.0
32.5°	1237.3	1236.0	1234.5	1233.1	1231.6	1230.2	1228.8	1227.3
35°	1174.0	1172.0	1170.0	1168.2	1166.8	1165.4	1163.9	1162.4
37.5°	1107.7	1105.5	1103.3	1101.3	1099.4	1097.4	1095.5	1093.6
40°	1061.5	1058.6	1055.7	1053.6	1052.1	1050.7	1049.2	1047.7
42.5°	1016.8	1013.4	1010.0	1007.9	1006.9	1005.9	1004.9	1004.0
45°	947.5	944.3	941.1	939.1	938.3	937.5	936.5	935.7
47.5°	880.5	876.9	873.4	870.4	868.3	866.0	863.8	861.7
50°	833.8	829.7	825.7	822.7	821.0	819.3	817.6	815.8
52.5°	785.7	782.0	778.4	775.6	773.4	771.2	769.0	766.8
55°	715.0	711.5	708.0	705.5	703.7	702.0	700.2	698.5
57.5°	644.2	640.9	637.6	635.1	633.4	631.8	630.1	628.4
60°	595.6	593.0	590.3	588.3	586.8	585.4	584.0	582.5
62.5°	548.1	545.6	543.3	541.4	540.0	538.5	537.1	535.6
65°	479.0	476.1	473.2	471.0	469.6	468.2	466.7	465.2
67.5°	407.8	405.0	402.3	400.7	400.2	399.8	399.4	399.1
70°	362.9	360.5	358.3	356.7	355.8	354.9	354.0	353.2
72.5°	317.9	316.0	314.2	312.8	312.0	311.1	310.3	309.3
75°	253.1	251.9	250.8	250.1	249.8	249.5	249.2	248.9
77.5°	191.6	191.3	191.0	190.4	189.6	188.9	188.1	187.4
80°	152.6	152.0	151.5	151.0	150.7	150.4	150.1	149.9
82.5°	117.6	117.3	117.0	116.6	116.3	116.0	115.7	115.5
85°	67.8	67.8	67.8	67.6	67.3	67.0	66.7	66.4
87.5°	30.4	30.7	31.0	31.2	31.3	31.4	31.5	31.6
90°	27.1	28.5	30.0	30.9	31.4	31.9	32.3	32.9
92.5°	26.1	27.6	29.0	29.9	30.0	30.1	30.2	30.3
95°	27.1	28.5	30.0	30.8	31.0	31.3	31.5	31.8
97.5°	29.2	29.3	29.5	29.7	30.0	30.2	30.4	30.6
100°	39.9	35.8	31.7	29.7	30.0	30.2	30.4	30.6
102.5°	142.9	98.3	53.6	31.4	31.4	31.5	31.5	31.6
105°	346.1	348.3	350.4	347.1	338.4	329.6	320.9	312.2
107.5°	428.2	429.2	430.3	431.3	432.3	433.2	434.0	435.0
110°	484.0	484.5	484.9	485.5	486.3	487.0	487.8	488.4



TEST NUMBER: P332667-830

CATALOG NUMBER: SA4XXDIP-C1020D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	538.0	537.9	537.8	538.2	539.1	540.1	541.0	541.9
115°	618.7	619.2	619.6	619.9	619.9	619.9	619.9	619.9
117.5°	699.8	699.7	699.6	699.6	699.5	699.4	699.3	699.2
120°	750.1	750.5	751.0	751.0	750.5	750.1	749.6	749.1
122.5°	799.7	799.9	800.2	800.1	799.7	799.2	798.6	798.1
125°	868.8	869.6	870.3	870.8	871.0	871.3	871.6	871.8
127.5°	937.6	937.5	937.4	937.2	937.0	936.8	936.6	936.4
130°	979.6	979.9	980.1	980.1	980.1	980.1	980.1	980.1
132.5°	1020.8	1021.1	1021.2	1021.2	1021.1	1020.9	1020.7	1020.5
135°	1077.5	1078.0	1078.6	1079.0	1079.5	1080.0	1080.4	1080.9
137.5°	1132.0	1132.5	1133.0	1133.2	1133.1	1132.9	1132.7	1132.7
140°	1165.6	1166.4	1167.2	1167.6	1167.8	1168.1	1168.3	1168.6
142.5°	1196.8	1197.3	1197.9	1198.2	1198.3	1198.3	1198.3	1198.3
145°	1241.3	1241.6	1241.8	1242.2	1242.6	1243.1	1243.7	1244.2
147.5°	1280.4	1280.6	1280.8	1281.0	1281.3	1281.6	1281.8	1282.0
150°	1305.4	1305.4	1305.4	1305.6	1305.8	1306.1	1306.4	1306.6
152.5°	1327.3	1327.7	1328.0	1328.1	1328.0	1327.9	1327.8	1327.6
155°	1356.7	1357.6	1358.7	1358.8	1358.0	1357.3	1356.6	1355.8
157.5°	1382.1	1383.3	1384.6	1384.6	1383.3	1382.1	1380.7	1379.5
160°	1398.2	1399.7	1401.1	1401.1	1399.7	1398.2	1396.8	1395.2
162.5°	1411.4	1412.8	1414.3	1414.2	1412.5	1410.9	1409.2	1407.5
165°	1429.8	1431.8	1433.7	1433.6	1431.4	1429.2	1427.0	1424.8
167.5°	1443.4	1445.5	1447.7	1447.5	1445.1	1442.7	1440.2	1437.8
170°	1451.7	1453.7	1455.7	1455.4	1452.9	1450.5	1448.1	1445.7
172.5°	1457.0	1459.0	1460.8	1460.6	1457.9	1455.3	1452.6	1450.0
175°	1463.2	1465.4	1467.5	1467.2	1464.2	1461.3	1458.4	1455.5
177.5°	1465.7	1467.2	1468.8	1468.4	1466.0	1463.7	1461.3	1459.1
180°	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2

(END OF REPORT)