

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332650-830

Luminaire Tested: **SA4XXDIP-C1020D810U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332650-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1020D810U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6819.7 lumens  
Efficiency: N/A  
Efficacy: 125.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332650-830  
CATALOG NUMBER: SA4XXDIP-C1020D810U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332650-830

CATALOG NUMBER: SA4XXDIP-C1020D810U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66	61
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	51
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	33	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13130	13130	13130
5°	13169	13011	13105
10°	13086	12904	12969
15°	12929	12721	12754
20°	12718	12494	12506
25°	12479	12235	12200
30°	12185	11929	11820
35°	11880	11610	11456
40°	11564	11248	11041
45°	11233	10891	10683
50°	10868	10574	10246
55°	10473	10162	9831
60°	10078	9700	9405
65°	9635	9259	8886
70°	9135	8674	8337
75°	8372	7966	7764
80°	7452	7146	6969
85°	6521	6280	6150



TEST NUMBER: P332650-830

CATALOG NUMBER: SA4XXDIP-C1020D810U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.2	2.2
10°-20°	431.5	6.3
20°-30°	635.2	9.3
30°-40°	738.4	10.8
40°-50°	738.4	10.8
50°-60°	645.9	9.5
60°-70°	479.7	7.0
70°-80°	272.5	4.0
80°-90°	81.5	1.2
90°-100°	62.8	0.9
100°-110°	186.2	2.7
110°-120°	316.0	4.6
120°-130°	416.6	6.1
130°-140°	467.9	6.9
140°-150°	459.8	6.7
150°-160°	386.7	5.7
160°-170°	257.3	3.8
170°-180°	90.1	1.3
0°-30°	1219.8	17.9
0°-40°	1958.2	28.7
0°-60°	3342.6	49.0
0°-90°	4176.3	61.2
90°-120°	565.0	8.3
90°-150°	1909.3	28.0
90°-180°	2643.0	38.8
0°-180°	6819.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1626	1626	1626	1626	1626	
5°	1625	1619	1606	1619	1617	154
15°	1547	1541	1522	1529	1526	436
25°	1401	1391	1374	1374	1370	644
35°	1205	1196	1178	1169	1162	753
45°	984	974	954	940	936	758
55°	744	739	722	707	698	666
65°	504	497	485	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	2	10	16	20	22	7
95°	44	51	56	58	58	49
105°	172	173	175	178	180	182
115°	321	321	320	319	318	317
125°	468	468	467	466	464	417
135°	604	608	608	606	604	467
145°	733	736	737	736	734	459
155°	840	840	839	842	839	386
165°	914	912	911	915	912	258
175°	951	948	947	952	947	90
180°	953	953	953	953	953	



TEST NUMBER: P332650-830

CATALOG NUMBER: SA4XXDIP-C1020D810U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1630.5	1629.8	1629.1	1628.4	1627.8	1626.1	1623.5	1621.0	1618.4	1615.9	1618.3
5°	1625.0	1623.9	1622.8	1621.6	1620.4	1618.3	1615.0	1611.8	1608.7	1605.5	1608.7
7.5°	1610.0	1608.7	1607.6	1606.5	1605.3	1603.0	1599.4	1595.9	1592.3	1588.8	1591.4
10°	1596.4	1595.3	1594.0	1592.9	1591.8	1589.3	1585.5	1581.8	1578.0	1574.2	1576.5
12.5°	1578.7	1577.5	1576.3	1575.2	1574.0	1571.4	1567.4	1563.5	1559.4	1555.5	1558.0
15°	1546.9	1545.7	1544.5	1543.4	1542.2	1539.5	1535.1	1530.8	1526.4	1522.1	1523.8
17.5°	1508.5	1507.1	1505.6	1504.2	1502.8	1500.0	1495.8	1491.8	1487.6	1483.6	1484.6
20°	1480.4	1478.9	1477.5	1476.0	1474.6	1471.7	1467.4	1463.0	1458.7	1454.3	1455.2
22.5°	1450.2	1448.2	1446.3	1444.4	1442.6	1439.4	1435.0	1430.7	1426.3	1422.0	1423.6
25°	1400.9	1398.9	1396.8	1394.8	1392.8	1389.8	1385.7	1381.7	1377.6	1373.6	1373.9
27.5°	1344.6	1342.6	1340.4	1338.3	1336.2	1333.3	1329.6	1325.8	1322.0	1318.2	1317.6
30°	1307.1	1304.8	1302.4	1300.1	1297.8	1294.8	1291.0	1287.2	1283.5	1279.7	1278.6
32.5°	1267.4	1265.4	1263.3	1261.2	1259.1	1256.0	1252.1	1248.1	1244.1	1240.1	1238.7
35°	1205.4	1203.4	1201.4	1199.4	1197.3	1194.3	1190.2	1186.2	1182.1	1178.1	1176.0
37.5°	1140.0	1138.1	1136.3	1134.4	1132.6	1129.5	1125.1	1120.8	1116.4	1112.1	1109.9
40°	1097.3	1095.0	1092.6	1090.3	1088.0	1084.7	1080.3	1076.0	1071.7	1067.3	1064.4
42.5°	1051.4	1050.0	1048.6	1047.3	1045.8	1042.7	1037.9	1033.1	1028.3	1023.5	1020.1
45°	983.9	981.8	979.9	977.8	975.8	972.4	967.8	963.2	958.6	953.9	950.7
47.5°	913.2	911.9	910.5	909.1	907.7	904.8	900.6	896.3	892.0	887.7	884.1
50°	865.3	864.1	863.0	861.9	860.6	858.1	854.0	850.0	845.9	841.9	837.8
52.5°	818.4	817.0	815.6	814.3	812.8	810.0	805.7	801.4	797.1	792.9	789.3
55°	744.1	743.2	742.3	741.5	740.6	738.2	734.1	730.1	726.0	722.0	718.5
57.5°	673.3	672.2	671.3	670.2	669.3	666.8	662.8	658.8	654.8	650.8	647.5
60°	624.2	622.7	621.3	619.9	618.4	615.9	612.1	608.3	604.5	600.8	598.1
62.5°	576.3	575.0	573.8	572.6	571.4	568.8	564.8	560.8	556.8	552.8	550.4
65°	504.4	502.8	501.4	500.0	498.5	496.3	493.4	490.6	487.7	484.7	481.9
67.5°	431.9	430.6	429.2	427.9	426.5	424.5	421.7	419.0	416.1	413.4	410.6
70°	387.0	385.0	383.0	381.0	378.9	376.7	374.5	372.1	369.9	367.5	365.1
72.5°	339.1	337.1	335.1	333.0	331.0	329.0	327.2	325.4	323.5	321.6	319.8
75°	268.4	267.0	265.5	264.1	262.7	261.2	259.8	258.4	256.8	255.4	254.3
77.5°	201.0	200.3	199.6	199.1	198.4	197.5	196.1	194.9	193.6	192.4	192.0
80°	160.3	159.4	158.5	157.7	156.8	156.1	155.5	155.0	154.4	153.7	153.2
82.5°	120.6	120.3	119.9	119.4	119.0	118.8	118.7	118.6	118.5	118.3	118.0
85°	70.4	70.4	70.4	70.4	70.4	70.1	69.5	68.9	68.3	67.8	67.8
87.5°	27.5	27.7	27.8	27.9	28.1	28.2	28.2	28.2	28.3	28.3	28.5
90°	2.2	4.1	5.8	7.6	9.4	10.9	12.3	13.6	14.9	16.2	17.2
92.5°	15.7	17.8	19.9	22.0	24.0	25.5	26.4	27.3	28.3	29.2	29.8
95°	44.2	45.7	47.1	48.6	50.1	51.5	52.6	53.7	54.9	56.0	56.5
97.5°	77.2	78.4	79.6	80.8	81.9	83.2	84.5	85.9	87.2	88.6	89.2
100°	103.2	103.8	104.4	105.1	105.8	106.9	108.3	109.8	111.2	112.7	113.1
102.5°	130.3	130.5	130.8	131.1	131.3	132.1	133.5	134.8	136.2	137.5	138.0
105°	171.7	171.8	172.0	172.2	172.4	172.8	173.4	174.1	174.7	175.4	175.9
107.5°	215.2	215.4	215.6	215.7	215.9	216.1	216.2	216.3	216.4	216.5	217.0
110°	244.7	245.0	245.2	245.6	245.9	246.0	245.9	245.7	245.5	245.3	245.1



TEST NUMBER: P332650-830

CATALOG NUMBER: SA4XXDIP-C1020D810U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.3	275.3	275.4	275.5	275.6	275.4	275.1	274.8	274.6	274.3	274.2
115°	321.3	321.3	321.3	321.3	321.3	321.1	320.7	320.5	320.1	319.8	319.6
117.5°	364.6	364.8	364.9	365.0	365.1	365.0	364.9	364.6	364.4	364.2	363.6
120°	393.5	394.2	394.8	395.5	396.2	396.2	395.7	395.2	394.7	394.3	393.4
122.5°	423.6	423.8	424.0	424.3	424.6	424.6	424.4	424.1	424.0	423.7	423.1
125°	467.9	467.9	467.9	467.9	467.9	467.8	467.7	467.5	467.3	467.2	466.8
127.5°	508.1	508.6	509.2	509.6	510.1	510.2	509.9	509.7	509.4	509.2	508.9
130°	536.4	537.0	537.4	537.9	538.4	538.7	538.7	538.7	538.7	538.7	538.3
132.5°	565.3	565.7	566.1	566.4	566.8	566.8	566.8	566.7	566.5	566.4	566.0
135°	603.5	604.5	605.5	606.4	607.5	607.9	607.9	607.9	607.9	607.9	607.6
137.5°	645.1	645.5	645.9	646.4	646.9	647.2	647.5	647.8	648.0	648.3	647.9
140°	672.8	673.1	673.4	673.7	674.1	674.2	674.2	674.2	674.2	674.2	674.1
142.5°	698.1	698.4	698.8	699.1	699.5	699.6	699.4	699.3	699.1	699.0	699.0
145°	733.2	733.9	734.5	735.2	735.8	736.2	736.4	736.5	736.7	736.9	736.7
147.5°	768.0	768.7	769.5	770.3	771.1	771.5	771.3	771.2	771.0	770.9	770.8
150°	789.2	789.9	790.5	791.2	791.8	792.1	792.1	792.1	792.1	792.1	792.1
152.5°	809.3	809.6	810.0	810.4	810.8	811.1	811.2	811.3	811.4	811.6	812.0
155°	840.0	840.0	840.0	840.0	840.0	839.9	839.8	839.6	839.4	839.3	839.9
157.5°	866.0	865.6	865.3	865.1	864.8	864.6	864.6	864.6	864.5	864.5	865.0
160°	881.3	881.1	881.0	880.8	880.6	880.4	880.3	880.1	880.0	879.9	880.3
162.5°	895.4	895.0	894.6	894.2	893.7	893.4	893.2	893.2	893.0	892.8	893.7
165°	914.5	914.0	913.5	912.9	912.5	912.1	911.7	911.4	911.1	910.8	911.7
167.5°	929.1	928.3	927.7	927.0	926.3	926.0	926.0	926.0	926.0	926.0	927.1
170°	937.3	936.5	935.7	934.8	934.1	933.7	933.9	934.1	934.2	934.3	935.3
172.5°	943.2	942.5	941.8	941.1	940.5	940.1	940.2	940.2	940.2	940.3	941.3
175°	951.3	950.5	949.6	948.9	948.0	947.5	947.3	947.2	947.1	946.9	948.0
177.5°	953.9	953.3	952.6	952.0	951.3	951.0	951.0	951.0	951.0	951.0	951.9
180°	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7



TEST NUMBER: P332650-830

CATALOG NUMBER: SA4XXDIP-C1020D810U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1620.5	1622.9	1625.2	1626.3	1626.0	1625.8	1625.5	1625.3
5°	1611.8	1615.0	1618.3	1619.6	1619.0	1618.3	1617.8	1617.2
7.5°	1593.9	1596.5	1599.0	1600.2	1599.8	1599.4	1599.0	1598.7
10°	1578.9	1581.2	1583.5	1584.3	1583.8	1583.2	1582.6	1582.1
12.5°	1560.6	1563.1	1565.7	1566.5	1565.8	1564.9	1564.1	1563.3
15°	1525.6	1527.3	1529.1	1529.5	1528.6	1527.8	1526.9	1526.0
17.5°	1485.7	1486.9	1487.9	1488.2	1487.6	1487.0	1486.5	1485.8
20°	1456.0	1457.0	1457.8	1457.9	1457.4	1456.8	1456.2	1455.7
22.5°	1425.1	1426.7	1428.2	1428.5	1427.5	1426.4	1425.4	1424.4
25°	1374.1	1374.4	1374.7	1374.2	1373.1	1372.0	1370.7	1369.6
27.5°	1316.9	1316.2	1315.5	1314.5	1313.0	1311.5	1310.0	1308.6
30°	1277.4	1276.2	1275.1	1273.8	1272.3	1270.8	1269.4	1268.0
32.5°	1237.3	1236.0	1234.5	1233.1	1231.6	1230.2	1228.8	1227.3
35°	1174.0	1172.0	1170.0	1168.2	1166.8	1165.4	1163.9	1162.4
37.5°	1107.7	1105.5	1103.3	1101.3	1099.4	1097.4	1095.5	1093.6
40°	1061.5	1058.6	1055.7	1053.6	1052.1	1050.7	1049.2	1047.7
42.5°	1016.8	1013.4	1010.0	1007.9	1006.9	1005.9	1004.9	1004.0
45°	947.5	944.3	941.1	939.1	938.3	937.5	936.5	935.7
47.5°	880.5	876.9	873.4	870.4	868.3	866.0	863.8	861.7
50°	833.8	829.7	825.7	822.7	821.0	819.3	817.6	815.8
52.5°	785.7	782.0	778.4	775.6	773.4	771.2	769.0	766.8
55°	715.0	711.5	708.0	705.5	703.7	702.0	700.2	698.5
57.5°	644.2	640.9	637.6	635.1	633.4	631.8	630.1	628.4
60°	595.6	593.0	590.3	588.3	586.8	585.4	584.0	582.5
62.5°	548.1	545.6	543.3	541.4	540.0	538.5	537.1	535.6
65°	479.0	476.1	473.2	471.0	469.6	468.2	466.7	465.2
67.5°	407.8	405.0	402.3	400.7	400.2	399.8	399.4	399.1
70°	362.9	360.5	358.3	356.7	355.8	354.9	354.0	353.2
72.5°	317.9	316.0	314.2	312.8	312.0	311.1	310.3	309.3
75°	253.1	251.9	250.8	250.1	249.8	249.5	249.2	248.9
77.5°	191.6	191.3	191.0	190.4	189.6	188.9	188.1	187.4
80°	152.6	152.0	151.5	151.0	150.7	150.4	150.1	149.9
82.5°	117.6	117.3	117.0	116.6	116.3	116.0	115.7	115.5
85°	67.8	67.8	67.8	67.6	67.3	67.0	66.7	66.4
87.5°	28.7	28.8	29.0	29.2	29.2	29.3	29.4	29.4
90°	18.2	19.1	20.2	20.8	21.1	21.5	21.8	22.1
92.5°	30.3	30.9	31.6	32.0	32.1	32.3	32.5	32.7
95°	57.0	57.5	58.0	58.2	58.2	58.2	58.2	58.2
97.5°	89.7	90.3	91.0	91.2	91.2	91.2	91.2	91.2
100°	113.4	113.8	114.0	114.2	114.2	114.2	114.2	114.2
102.5°	138.5	138.8	139.3	139.6	139.8	139.9	140.1	140.2
105°	176.3	176.8	177.3	177.9	178.3	178.8	179.3	179.8
107.5°	217.4	217.8	218.3	218.6	218.5	218.5	218.5	218.4
110°	244.7	244.4	244.0	244.1	244.7	245.2	245.6	246.1





TEST NUMBER: P332650-830

CATALOG NUMBER: SA4XXDIP-C1020D810U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	274.1	274.1	274.0	274.0	274.1	274.2	274.3	274.4
115°	319.4	319.3	319.1	319.0	318.9	318.7	318.5	318.3
117.5°	363.1	362.5	361.9	361.5	361.2	360.8	360.5	360.1
120°	392.6	391.7	391.0	390.7	391.1	391.3	391.7	392.0
122.5°	422.5	422.1	421.5	420.9	420.3	419.7	419.1	418.6
125°	466.6	466.2	465.9	465.5	465.2	464.9	464.6	464.2
127.5°	508.5	508.2	507.8	507.6	507.3	507.1	506.8	506.5
130°	538.0	537.6	537.3	536.9	536.2	535.6	534.9	534.2
132.5°	565.7	565.3	565.1	564.8	564.5	564.2	563.9	563.7
135°	607.3	606.9	606.6	606.1	605.7	605.2	604.7	604.3
137.5°	647.4	647.1	646.6	646.4	646.5	646.6	646.7	646.9
140°	673.9	673.7	673.5	673.4	673.3	673.1	672.9	672.8
142.5°	698.9	698.9	698.9	698.8	698.8	698.8	698.7	698.7
145°	736.5	736.4	736.2	735.8	735.4	734.9	734.4	734.0
147.5°	770.6	770.5	770.3	770.2	770.1	769.9	769.8	769.6
150°	792.1	792.1	792.1	792.0	791.9	791.7	791.5	791.4
152.5°	812.4	812.8	813.1	813.1	812.8	812.3	811.9	811.4
155°	840.6	841.2	841.9	841.9	841.2	840.6	839.9	839.3
157.5°	865.4	866.0	866.5	866.4	865.9	865.3	864.8	864.2
160°	880.8	881.3	881.7	881.7	880.8	880.0	879.2	878.4
162.5°	894.6	895.4	896.4	896.4	895.5	894.8	893.9	893.1
165°	912.8	913.7	914.7	914.8	914.2	913.5	912.9	912.3
167.5°	928.0	929.1	930.0	930.0	929.0	927.9	927.0	926.0
170°	936.3	937.3	938.3	938.2	937.1	935.9	934.7	933.6
172.5°	942.4	943.6	944.7	944.7	943.6	942.4	941.2	940.1
175°	949.1	950.3	951.5	951.5	950.3	949.1	948.0	946.9
177.5°	952.8	953.8	954.7	954.6	953.6	952.5	951.5	950.4
180°	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7

(END OF REPORT)