

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332713-830

Luminaire Tested: **SA4XXDIP-C1195D1205U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332713-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1195D1205U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8752.6 lumens  
Efficiency: N/A  
Efficacy: 122.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332713-830  
CATALOG NUMBER: SA4XXDIP-C1195D1205U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332713-830

CATALOG NUMBER: SA4XXDIP-C1195D1205U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	94	91	87	92	88	84	81	76	73	71	64	62	61	54	52	51	46				
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39				
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33				
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28				
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24				
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21				
7	59	46	38	33	54	44	36	31	38	32	28	33	28	25	28	24	22	19				
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15163	15163	15163
5°	15209	15027	15135
10°	15114	14905	14978
15°	14931	14692	14730
20°	14689	14430	14442
25°	14412	14130	14091
30°	14072	13778	13651
35°	13720	13409	13232
40°	13354	12991	12752
45°	12973	12578	12337
50°	12552	12210	11833
55°	12096	11736	11354
60°	11641	11202	10863
65°	11127	10695	10264
70°	10551	10017	9626
75°	9669	9201	8968
80°	8605	8257	8047
85°	7521	7243	7104



TEST NUMBER: P332713-830

CATALOG NUMBER: SA4XXDIP-C1195D1205U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.9	2.0
10°-20°	498.4	5.7
20°-30°	733.6	8.4
30°-40°	852.8	9.7
40°-50°	852.8	9.7
50°-60°	746.0	8.5
60°-70°	554.0	6.3
70°-80°	314.7	3.6
80°-90°	95.1	1.1
90°-100°	93.4	1.1
100°-110°	276.7	3.2
110°-120°	469.6	5.4
120°-130°	619.1	7.1
130°-140°	695.3	7.9
140°-150°	683.3	7.8
150°-160°	574.7	6.6
160°-170°	382.4	4.4
170°-180°	133.9	1.5
0°-30°	1408.8	16.1
0°-40°	2261.6	25.8
0°-60°	3860.5	44.1
0°-90°	4824.3	55.1
90°-120°	839.6	9.6
90°-150°	2837.4	32.4
90°-180°	3928.0	44.9
0°-180°	8752.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1878	1878	1878	1878	1878	
5°	1877	1870	1854	1870	1868	178
15°	1786	1780	1758	1766	1762	503
25°	1618	1607	1586	1587	1582	744
35°	1392	1381	1361	1350	1343	870
45°	1136	1125	1102	1086	1081	876
55°	859	854	834	816	807	769
65°	582	575	560	545	537	577
75°	310	302	295	289	288	329
85°	81	81	78	78	77	90
90°	3	15	24	30	33	9
95°	66	75	83	86	86	73
105°	255	256	261	264	267	271
115°	477	477	475	474	473	471
125°	695	695	694	692	690	620
135°	897	903	903	901	898	694
145°	1090	1094	1095	1094	1091	682
155°	1248	1248	1247	1251	1247	574
165°	1359	1356	1354	1359	1356	383
175°	1414	1408	1407	1414	1407	134
180°	1416	1416	1416	1416	1416	



TEST NUMBER: P332713-830

CATALOG NUMBER: SA4XXDIP-C1195D1205U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1883.1	1882.4	1881.5	1880.7	1879.9	1878.0	1875.1	1872.2	1869.3	1866.3	1869.0
5°	1876.8	1875.5	1874.2	1872.8	1871.5	1869.0	1865.3	1861.6	1857.9	1854.3	1857.9
7.5°	1859.4	1858.0	1856.7	1855.3	1854.0	1851.3	1847.2	1843.1	1839.1	1834.9	1838.0
10°	1843.7	1842.4	1841.1	1839.7	1838.3	1835.5	1831.2	1826.8	1822.5	1818.2	1820.8
12.5°	1823.3	1821.9	1820.5	1819.2	1817.9	1814.9	1810.3	1805.7	1801.1	1796.5	1799.4
15°	1786.5	1785.2	1783.9	1782.5	1781.1	1778.0	1772.9	1767.9	1762.9	1757.9	1759.9
17.5°	1742.3	1740.6	1738.9	1737.3	1735.6	1732.4	1727.6	1722.9	1718.2	1713.4	1714.7
20°	1709.8	1708.1	1706.4	1704.8	1703.1	1699.7	1694.7	1689.7	1684.7	1679.6	1680.6
22.5°	1674.8	1672.6	1670.5	1668.2	1666.0	1662.4	1657.4	1652.4	1647.4	1642.3	1644.2
25°	1618.0	1615.6	1613.3	1610.9	1608.5	1605.1	1600.3	1595.7	1591.0	1586.3	1586.7
27.5°	1552.9	1550.5	1548.1	1545.7	1543.3	1539.9	1535.6	1531.3	1526.9	1522.5	1521.7
30°	1509.6	1506.9	1504.2	1501.6	1498.9	1495.3	1491.0	1486.7	1482.3	1478.0	1476.7
32.5°	1463.9	1461.4	1459.1	1456.6	1454.2	1450.7	1446.0	1441.4	1436.8	1432.2	1430.6
35°	1392.2	1389.9	1387.5	1385.2	1382.8	1379.3	1374.6	1370.0	1365.3	1360.6	1358.2
37.5°	1316.6	1314.5	1312.4	1310.2	1308.1	1304.5	1299.5	1294.5	1289.4	1284.4	1281.9
40°	1267.2	1264.6	1261.9	1259.2	1256.6	1252.7	1247.7	1242.6	1237.7	1232.7	1229.3
42.5°	1214.3	1212.7	1211.1	1209.5	1207.9	1204.3	1198.7	1193.2	1187.6	1182.0	1178.2
45°	1136.3	1134.0	1131.6	1129.3	1127.0	1123.1	1117.8	1112.4	1107.0	1101.7	1098.1
47.5°	1054.7	1053.1	1051.5	1049.9	1048.3	1045.1	1040.1	1035.2	1030.2	1025.3	1021.2
50°	999.4	998.1	996.6	995.3	994.0	991.0	986.3	981.7	976.9	972.2	967.6
52.5°	945.2	943.6	942.0	940.4	938.8	935.5	930.6	925.6	920.7	915.7	911.5
55°	859.4	858.4	857.4	856.4	855.4	852.5	847.8	843.2	838.5	833.8	829.8
57.5°	777.5	776.4	775.2	774.1	773.0	770.1	765.4	760.8	756.2	751.6	747.8
60°	721.0	719.3	717.6	716.0	714.3	711.2	706.9	702.6	698.1	693.8	690.8
62.5°	665.5	664.1	662.7	661.3	660.0	657.0	652.3	647.7	643.1	638.5	635.7
65°	582.5	580.8	579.1	577.4	575.8	573.3	570.0	566.6	563.3	559.9	556.6
67.5°	498.8	497.3	495.7	494.2	492.7	490.2	487.0	483.8	480.6	477.4	474.2
70°	447.0	444.7	442.3	440.0	437.6	435.2	432.4	429.8	427.1	424.4	421.8
72.5°	391.6	389.3	386.9	384.6	382.3	380.0	377.9	375.7	373.6	371.5	369.3
75°	310.0	308.4	306.7	305.0	303.3	301.7	300.0	298.3	296.7	295.0	293.7
77.5°	232.1	231.3	230.6	229.9	229.1	228.0	226.6	225.1	223.7	222.2	221.8
80°	185.1	184.1	183.1	182.1	181.2	180.3	179.6	178.9	178.2	177.6	176.9
82.5°	139.4	138.9	138.5	138.0	137.5	137.2	137.0	137.0	136.8	136.7	136.3
85°	81.2	81.2	81.2	81.2	81.2	81.0	80.3	79.6	78.9	78.2	78.2
87.5°	32.0	32.2	32.5	32.8	33.0	33.3	33.4	33.5	33.6	33.7	34.0
90°	3.3	5.9	8.7	11.3	13.9	16.3	18.3	20.2	22.1	24.1	25.5
92.5°	23.5	26.5	29.6	32.6	35.7	37.9	39.3	40.6	42.0	43.4	44.2
95°	65.7	67.9	70.1	72.3	74.5	76.4	78.1	79.8	81.5	83.2	84.0
97.5°	114.8	116.5	118.3	120.0	121.8	123.7	125.6	127.6	129.6	131.6	132.5
100°	153.4	154.3	155.2	156.2	157.2	158.8	161.0	163.2	165.3	167.6	168.1
102.5°	193.6	194.0	194.4	194.7	195.2	196.3	198.3	200.4	202.4	204.3	205.0
105°	255.1	255.4	255.6	255.9	256.1	256.7	257.7	258.6	259.7	260.6	261.4
107.5°	319.7	320.1	320.4	320.7	320.9	321.1	321.3	321.4	321.6	321.7	322.4
110°	363.5	364.0	364.5	365.0	365.5	365.6	365.4	365.1	364.9	364.7	364.2



TEST NUMBER: P332713-830

CATALOG NUMBER: SA4XXDIP-C1195D1205U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	409.1	409.3	409.3	409.4	409.5	409.3	408.9	408.5	408.0	407.6	407.5
115°	477.4	477.4	477.4	477.4	477.4	477.2	476.7	476.3	475.7	475.2	475.0
117.5°	541.9	542.1	542.2	542.4	542.6	542.5	542.2	541.9	541.5	541.2	540.4
120°	584.8	585.7	586.7	587.7	588.6	588.8	588.1	587.3	586.5	585.9	584.7
122.5°	629.4	629.8	630.2	630.6	631.0	631.0	630.7	630.4	630.0	629.6	628.9
125°	695.3	695.3	695.3	695.3	695.3	695.2	695.0	694.7	694.5	694.3	693.8
127.5°	755.2	755.9	756.6	757.3	758.1	758.3	757.8	757.4	757.1	756.7	756.2
130°	797.2	798.0	798.6	799.4	800.1	800.5	800.5	800.5	800.5	800.5	800.0
132.5°	840.1	840.7	841.2	841.7	842.3	842.4	842.3	842.1	841.9	841.7	841.1
135°	896.8	898.3	899.8	901.3	902.7	903.4	903.4	903.4	903.4	903.4	903.0
137.5°	958.6	959.3	960.0	960.6	961.3	961.9	962.2	962.6	963.0	963.4	962.8
140°	999.8	1000.2	1000.8	1001.3	1001.7	1001.9	1001.9	1001.9	1001.9	1001.9	1001.7
142.5°	1037.5	1037.9	1038.4	1038.9	1039.4	1039.5	1039.3	1039.2	1039.0	1038.8	1038.7
145°	1089.6	1090.5	1091.6	1092.5	1093.4	1094.1	1094.3	1094.6	1094.8	1095.0	1094.8
147.5°	1141.2	1142.5	1143.6	1144.7	1145.9	1146.4	1146.2	1146.0	1145.8	1145.7	1145.5
150°	1172.8	1173.7	1174.8	1175.7	1176.7	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1
152.5°	1202.6	1203.2	1203.7	1204.3	1204.9	1205.3	1205.5	1205.7	1205.9	1206.1	1206.6
155°	1248.3	1248.3	1248.3	1248.3	1248.3	1248.2	1248.0	1247.7	1247.5	1247.3	1248.2
157.5°	1286.9	1286.5	1286.0	1285.6	1285.2	1284.9	1284.9	1284.8	1284.8	1284.7	1285.4
160°	1309.7	1309.5	1309.2	1308.9	1308.7	1308.4	1308.2	1308.0	1307.7	1307.5	1308.2
162.5°	1330.7	1330.0	1329.5	1328.8	1328.1	1327.8	1327.5	1327.3	1327.0	1326.7	1328.0
165°	1359.0	1358.2	1357.4	1356.8	1356.0	1355.4	1354.9	1354.4	1354.0	1353.5	1354.9
167.5°	1380.6	1379.6	1378.6	1377.5	1376.6	1376.0	1376.1	1376.1	1376.2	1376.2	1377.7
170°	1392.9	1391.7	1390.4	1389.2	1388.0	1387.5	1387.8	1388.0	1388.3	1388.6	1390.0
172.5°	1401.7	1400.6	1399.6	1398.5	1397.6	1397.0	1397.1	1397.2	1397.2	1397.3	1398.9
175°	1413.7	1412.5	1411.3	1410.0	1408.8	1408.1	1407.9	1407.6	1407.4	1407.1	1408.8
177.5°	1417.7	1416.6	1415.7	1414.8	1413.7	1413.2	1413.2	1413.2	1413.2	1413.2	1414.7
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332713-830

CATALOG NUMBER: SA4XXDIP-C1195D1205U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1871.6	1874.3	1877.0	1878.2	1877.9	1877.6	1877.4	1877.1
5°	1861.6	1865.3	1869.0	1870.5	1869.8	1869.2	1868.5	1867.7
7.5°	1840.9	1843.8	1846.7	1848.0	1847.7	1847.2	1846.8	1846.4
10°	1823.4	1826.2	1828.8	1829.9	1829.2	1828.5	1827.8	1827.1
12.5°	1802.3	1805.3	1808.3	1809.2	1808.3	1807.3	1806.4	1805.4
15°	1761.9	1764.0	1765.9	1766.4	1765.5	1764.4	1763.4	1762.5
17.5°	1715.9	1717.2	1718.4	1718.7	1718.1	1717.4	1716.7	1716.1
20°	1681.7	1682.6	1683.7	1683.9	1683.2	1682.5	1681.9	1681.1
22.5°	1646.0	1647.8	1649.5	1649.8	1648.7	1647.5	1646.2	1645.0
25°	1587.1	1587.3	1587.7	1587.1	1585.8	1584.5	1583.2	1581.9
27.5°	1520.9	1520.1	1519.3	1518.1	1516.4	1514.8	1513.1	1511.4
30°	1475.3	1473.9	1472.6	1471.1	1469.4	1467.8	1466.1	1464.4
32.5°	1429.0	1427.4	1425.8	1424.2	1422.5	1420.8	1419.2	1417.5
35°	1355.9	1353.6	1351.2	1349.2	1347.6	1345.9	1344.2	1342.6
37.5°	1279.3	1276.8	1274.2	1271.9	1269.7	1267.4	1265.3	1263.0
40°	1226.0	1222.6	1219.3	1216.7	1215.1	1213.4	1211.7	1210.0
42.5°	1174.3	1170.4	1166.6	1164.0	1162.9	1161.8	1160.6	1159.5
45°	1094.4	1090.7	1087.0	1084.7	1083.6	1082.6	1081.7	1080.6
47.5°	1017.0	1012.9	1008.7	1005.3	1002.8	1000.2	997.7	995.1
50°	962.9	958.2	953.6	950.2	948.2	946.2	944.1	942.2
52.5°	907.4	903.2	899.1	895.8	893.2	890.7	888.2	885.6
55°	825.8	821.8	817.7	814.7	812.8	810.8	808.7	806.7
57.5°	744.0	740.2	736.4	733.5	731.6	729.6	727.6	725.8
60°	687.8	684.9	681.8	679.5	677.8	676.1	674.5	672.8
62.5°	632.9	630.2	627.5	625.3	623.6	621.9	620.3	618.6
65°	553.2	549.9	546.5	544.0	542.3	540.6	538.9	537.3
67.5°	471.0	467.8	464.6	462.7	462.2	461.8	461.3	460.8
70°	419.1	416.4	413.7	411.9	410.9	409.9	408.9	407.8
72.5°	367.2	365.0	362.9	361.3	360.3	359.3	358.3	357.3
75°	292.3	291.0	289.6	288.8	288.5	288.1	287.8	287.5
77.5°	221.3	220.9	220.6	219.9	219.0	218.2	217.3	216.4
80°	176.3	175.6	174.9	174.5	174.1	173.7	173.4	173.1
82.5°	135.8	135.4	135.1	134.7	134.3	134.0	133.7	133.4
85°	78.2	78.2	78.2	78.1	77.8	77.4	77.1	76.7
87.5°	34.3	34.6	34.9	35.1	35.2	35.3	35.3	35.4
90°	27.1	28.5	30.0	30.9	31.4	31.9	32.3	32.9
92.5°	45.1	46.0	46.8	47.4	47.8	48.1	48.4	48.6
95°	84.6	85.4	86.1	86.5	86.5	86.5	86.5	86.5
97.5°	133.4	134.2	135.2	135.5	135.5	135.5	135.5	135.5
100°	168.5	169.0	169.5	169.8	169.8	169.8	169.8	169.8
102.5°	205.7	206.4	207.1	207.5	207.7	207.9	208.1	208.3
105°	262.1	262.8	263.5	264.3	265.0	265.7	266.5	267.2
107.5°	323.1	323.8	324.4	324.8	324.7	324.7	324.6	324.6
110°	363.6	363.2	362.7	362.8	363.5	364.3	365.0	365.7





TEST NUMBER: P332713-830

CATALOG NUMBER: SA4XXDIP-C1195D1205U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	407.4	407.3	407.2	407.2	407.4	407.5	407.6	407.8
115°	474.8	474.5	474.3	474.0	473.8	473.5	473.3	473.1
117.5°	539.5	538.7	537.8	537.2	536.7	536.2	535.7	535.3
120°	583.4	582.2	581.0	580.6	581.1	581.5	582.1	582.6
122.5°	628.0	627.2	626.3	625.5	624.6	623.8	622.8	622.0
125°	693.2	692.8	692.3	691.8	691.4	690.9	690.3	689.8
127.5°	755.7	755.3	754.7	754.3	753.9	753.5	753.1	752.7
130°	799.5	799.0	798.5	797.8	796.8	795.9	794.8	793.9
132.5°	840.7	840.2	839.7	839.2	838.9	838.5	838.1	837.7
135°	902.5	901.9	901.4	900.9	900.1	899.4	898.6	898.0
137.5°	962.1	961.5	960.9	960.6	960.8	960.9	961.1	961.2
140°	1001.5	1001.3	1001.0	1000.8	1000.5	1000.2	1000.0	999.8
142.5°	1038.7	1038.6	1038.6	1038.5	1038.5	1038.4	1038.4	1038.3
145°	1094.6	1094.3	1094.1	1093.5	1092.9	1092.1	1091.4	1090.7
147.5°	1145.3	1145.1	1144.8	1144.6	1144.4	1144.2	1143.9	1143.7
150°	1177.1	1177.1	1177.1	1177.0	1176.8	1176.6	1176.3	1176.1
152.5°	1207.2	1207.9	1208.4	1208.4	1207.8	1207.1	1206.5	1205.9
155°	1249.2	1250.2	1251.1	1251.1	1250.2	1249.2	1248.2	1247.3
157.5°	1286.2	1286.9	1287.6	1287.6	1286.8	1285.9	1285.1	1284.3
160°	1308.9	1309.7	1310.4	1310.1	1308.9	1307.7	1306.6	1305.3
162.5°	1329.4	1330.7	1332.0	1332.1	1330.9	1329.6	1328.4	1327.2
165°	1356.4	1357.8	1359.3	1359.5	1358.6	1357.6	1356.6	1355.7
167.5°	1379.1	1380.6	1382.1	1382.1	1380.5	1379.0	1377.5	1376.0
170°	1391.5	1392.9	1394.4	1394.2	1392.5	1390.8	1389.1	1387.4
172.5°	1400.6	1402.2	1403.9	1403.9	1402.1	1400.4	1398.7	1397.0
175°	1410.5	1412.2	1413.9	1413.9	1412.2	1410.5	1408.8	1407.1
177.5°	1416.0	1417.4	1418.7	1418.6	1417.0	1415.5	1413.9	1412.4
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9

(END OF REPORT)