

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331644-840

Luminaire Tested: **SA2XXRDIP-C290D1080U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331644-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C290D1080U840-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5293.1 lumens  
Efficiency: N/A  
Efficacy: 125.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331644-840

CATALOG NUMBER: SA2XXRDIP-C290D1080U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331644-840

CATALOG NUMBER: SA2XXRDIP-C290D1080U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	67	67	67	47	47	47	28	28	28	20				
1	91	87	83	80	80	77	74	71	58	56	55	41	40	39	25	25	24	17				
2	83	76	70	66	73	68	63	59	51	48	45	36	34	33	22	21	21	15				
3	76	67	60	55	67	60	54	49	45	42	38	32	30	28	20	19	18	13				
4	69	59	52	46	61	53	47	42	40	36	33	29	26	24	18	17	15	11				
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	16	15	14	10				
6	58	47	40	34	52	42	36	31	32	28	24	23	20	18	15	13	12	9				
7	54	42	35	30	48	38	32	27	29	25	21	21	18	16	14	12	11	8				
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	12	11	10	7				
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	11	10	9	6				
10	43	32	25	21	38	29	23	19	22	18	15	16	13	11	11	9	8	6				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8186	8186	8186
5°	8217	8083	8126
10°	8153	7950	7883
15°	8058	7714	7492
20°	7930	7378	7009
25°	7798	6996	6538
30°	7612	6604	5936
35°	7433	6177	5409
40°	7253	5735	4795
45°	7040	5236	4242
50°	6822	4735	3697
55°	6598	4197	3178
60°	6339	3630	2638
65°	6044	3049	2399
70°	5698	2511	2209
75°	5265	2289	2059
80°	4649	2046	1878
85°	3649	1612	1612



TEST NUMBER: P331644-840

CATALOG NUMBER: SA2XXRDIP-C290D1080U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.4	0.9
10°-20°	130.3	2.5
20°-30°	183.0	3.5
30°-40°	199.5	3.8
40°-50°	183.4	3.5
50°-60°	144.1	2.7
60°-70°	93.9	1.8
70°-80°	48.4	0.9
80°-90°	18.1	0.3
90°-100°	243.9	4.6
100°-110°	827.7	15.6
110°-120°	879.3	16.6
120°-130°	723.9	13.7
130°-140°	581.3	11.0
140°-150°	439.3	8.3
150°-160°	308.7	5.8
160°-170°	181.7	3.4
170°-180°	59.1	1.1
0°-30°	360.7	6.8
0°-40°	560.2	10.6
0°-60°	887.7	16.8
0°-90°	1048.1	19.8
90°-120°	1951.0	36.9
90°-150°	3695.4	69.8
90°-180°	4245.0	80.2
0°-180°	5293.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	507	504	499	502	501	48
15°	482	476	462	453	448	136
25°	438	422	393	375	367	201
35°	377	353	313	285	274	236
45°	308	277	229	198	186	238
55°	234	198	149	123	113	209
65°	158	121	80	65	63	157
75°	84	53	37	34	33	89
85°	20	11	9	9	9	23
90°	1	16	40	38	39	3
95°	41	101	460	174	134	44
105°	143	216	869	1554	1322	152
115°	252	319	727	1501	1740	250
125°	352	416	699	1216	1411	312
135°	413	493	691	1022	1170	319
145°	472	542	687	854	934	296
155°	536	579	668	755	785	247
165°	584	602	639	678	689	165
175°	609	609	615	622	621	58
180°	610	610	610	610	610	



TEST NUMBER: P331644-840

CATALOG NUMBER: SA2XXRDIP-C290D1080U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	508.8	508.4	508.0	507.6	507.2	506.4	505.5	504.7	503.8	502.9	503.7
5°	507.0	506.4	505.9	505.4	504.9	503.9	502.6	501.3	500.0	498.7	499.6
7.5°	501.7	501.1	500.4	499.8	499.2	498.1	496.6	494.9	493.4	491.9	492.1
10°	497.3	496.6	495.8	495.1	494.4	493.0	491.0	489.0	487.0	484.9	484.6
12.5°	491.8	490.9	490.0	489.2	488.3	486.6	483.9	481.3	478.7	476.1	475.5
15°	482.1	481.0	479.9	478.8	477.7	475.3	471.9	468.5	464.9	461.5	459.6
17.5°	470.3	468.6	466.9	465.1	463.4	460.4	456.0	451.5	447.1	442.6	440.3
20°	461.5	459.5	457.5	455.3	453.3	449.8	444.6	439.6	434.5	429.4	426.9
22.5°	452.0	449.7	447.4	445.1	442.8	438.8	433.0	427.3	421.6	415.9	412.5
25°	437.7	434.3	431.1	427.9	424.6	419.6	412.8	406.2	399.4	392.7	388.5
27.5°	420.4	416.9	413.3	409.8	406.2	400.6	393.0	385.5	377.9	370.3	365.5
30°	408.3	404.5	400.5	396.7	392.8	386.8	378.6	370.5	362.3	354.2	349.0
32.5°	396.6	392.0	387.5	382.9	378.4	372.0	363.8	355.4	347.1	338.7	332.9
35°	377.1	371.9	366.7	361.5	356.3	349.2	340.2	331.2	322.3	313.4	306.9
37.5°	357.7	351.9	346.2	340.5	334.8	327.2	317.6	308.0	298.5	288.9	281.9
40°	344.1	338.0	331.8	325.7	319.6	311.6	301.7	291.9	282.0	272.1	264.8
42.5°	330.1	323.7	317.2	310.8	304.4	296.0	285.8	275.6	265.4	255.2	247.7
45°	308.3	301.4	294.6	287.8	280.9	272.2	261.5	250.7	240.0	229.3	222.2
47.5°	287.0	279.7	272.6	265.3	258.0	248.9	237.8	226.8	215.7	204.7	197.5
50°	271.6	264.4	257.1	249.8	242.7	233.4	222.2	211.0	199.8	188.5	181.5
52.5°	256.5	248.9	241.5	233.9	226.3	217.0	206.0	195.1	184.1	173.1	166.3
55°	234.4	226.5	218.5	210.6	202.6	193.2	182.1	171.1	160.1	149.1	143.0
57.5°	211.8	203.6	195.4	187.3	179.2	169.8	159.2	148.7	138.0	127.4	121.8
60°	196.3	188.2	180.1	171.9	163.7	154.4	143.9	133.4	122.9	112.4	107.1
62.5°	181.3	173.2	165.0	156.8	148.7	139.6	129.6	119.6	109.6	99.6	94.6
65°	158.2	150.0	141.8	133.5	125.2	116.5	107.3	98.2	89.0	79.8	76.3
67.5°	136.0	127.8	119.7	111.5	103.3	95.0	86.7	78.6	70.3	62.0	60.4
70°	120.7	112.7	104.7	96.8	88.9	81.4	74.3	67.3	60.3	53.2	52.2
72.5°	105.9	98.4	90.7	83.1	75.4	68.9	63.2	57.6	51.9	46.3	45.3
75°	84.4	77.3	70.2	63.0	55.8	50.6	47.1	43.6	40.2	36.7	36.0
77.5°	63.2	57.0	50.7	44.4	38.2	34.2	32.5	30.9	29.2	27.6	27.2
80°	50.0	44.8	39.6	34.4	29.2	26.1	25.0	24.0	23.0	22.0	21.6
82.5°	37.9	33.8	29.8	25.8	21.7	19.3	18.6	17.9	17.2	16.6	16.3
85°	19.7	17.6	15.5	13.3	11.2	9.9	9.6	9.3	9.0	8.7	8.7
87.5°	6.1	6.2	6.5	6.3	6.1	6.5	7.7	9.3	10.7	10.9	10.6
90°	1.2	4.6	9.4	11.7	14.0	17.6	23.4	31.7	38.7	39.9	38.7
92.5°	14.3	20.6	29.1	34.2	42.2	53.2	79.8	117.0	150.4	152.5	128.9
95°	41.1	45.7	57.5	68.1	86.8	114.9	169.0	270.9	407.1	459.9	402.4
97.5°	66.9	73.2	85.6	101.6	123.2	155.1	222.9	365.1	591.3	785.1	823.5
100°	90.3	93.8	104.4	123.2	146.6	179.5	241.7	384.8	638.1	926.8	1095.7
102.5°	111.9	114.5	125.0	143.8	168.2	201.1	258.5	385.8	620.4	931.5	1197.1
105°	143.1	147.8	156.0	173.6	199.4	232.3	287.4	391.8	585.4	869.3	1181.3
107.5°	176.9	180.7	188.6	204.8	230.5	263.5	317.0	408.0	568.0	802.6	1078.3
110°	199.4	204.1	211.2	226.4	251.1	285.1	336.7	421.1	564.3	770.7	1013.6



TEST NUMBER: P331644-840

CATALOG NUMBER: SA2XXRDIP-C290D1080U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	220.0	224.8	232.8	247.0	270.7	305.7	355.5	435.3	565.2	750.1	968.6
115°	252.3	258.1	265.1	279.2	302.7	334.4	384.8	456.4	570.2	727.3	912.7
117.5°	285.6	290.2	297.3	309.7	332.2	365.1	411.7	478.9	578.6	716.3	877.5
120°	306.2	310.8	317.9	328.5	351.9	384.8	430.5	493.9	584.2	709.7	858.7
122.5°	325.9	329.6	336.7	348.2	371.6	405.5	448.4	507.1	590.8	706.0	842.7
125°	351.9	355.5	362.5	376.6	400.0	432.9	475.1	528.0	600.7	699.2	820.0
127.5°	372.5	377.3	387.2	402.6	425.2	458.9	500.0	547.3	610.8	695.2	798.9
130°	384.8	389.5	401.2	417.7	441.1	473.9	515.0	559.6	618.2	693.3	784.9
132.5°	396.1	401.7	414.3	431.7	456.2	489.0	528.2	571.8	625.7	692.4	773.6
135°	412.9	417.7	431.7	449.3	476.3	509.2	546.6	587.7	634.7	690.9	757.8
137.5°	428.9	434.5	448.6	467.4	494.1	524.6	561.7	600.0	642.7	690.7	746.8
140°	441.1	445.8	459.9	478.7	504.4	534.9	570.2	606.5	646.4	689.8	740.2
142.5°	453.3	457.1	470.2	489.0	513.8	542.5	576.7	612.2	649.2	689.8	733.7
145°	471.6	476.3	488.1	505.6	529.1	554.9	586.5	619.5	652.3	687.4	725.0
147.5°	491.3	494.8	506.0	522.3	541.8	564.7	594.5	623.4	653.2	683.3	716.1
150°	504.4	508.0	517.4	532.6	550.2	571.3	598.3	625.3	652.3	680.4	708.5
152.5°	517.6	519.3	528.6	542.0	558.7	577.8	602.1	626.2	650.4	675.7	702.0
155°	536.1	537.2	544.3	557.2	570.2	587.7	607.6	627.6	647.5	667.5	689.8
157.5°	551.6	552.8	558.5	569.7	580.0	594.8	611.7	627.6	642.2	659.0	678.3
160°	561.9	563.1	567.7	577.1	586.5	599.5	613.6	627.6	639.3	653.5	669.8
162.5°	572.3	571.6	576.2	583.7	592.2	602.3	614.5	626.7	636.5	648.7	662.4
165°	584.2	583.1	585.4	592.4	598.3	605.3	615.9	624.1	631.2	639.3	649.9
167.5°	594.1	592.7	594.8	599.3	603.5	607.9	615.6	622.5	625.7	631.2	637.7
170°	600.7	598.3	599.5	603.0	605.3	608.8	614.7	620.6	622.9	626.4	631.2
172.5°	604.4	603.0	602.3	605.8	607.2	609.8	613.8	617.7	619.1	620.9	624.6
175°	608.8	607.6	606.5	608.8	608.8	610.1	612.4	614.7	613.6	614.7	615.9
177.5°	611.0	609.0	608.1	610.1	610.1	610.1	611.0	612.9	611.0	610.1	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331644-840

CATALOG NUMBER: SA2XXRDIP-C290D1080U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	504.5	505.3	506.1	506.4	506.3	506.1	505.9	505.8
5°	500.5	501.4	502.3	502.6	502.3	502.0	501.7	501.4
7.5°	492.4	492.7	492.9	492.8	492.3	491.7	491.2	490.7
10°	484.3	484.0	483.7	483.2	482.6	482.0	481.4	480.8
12.5°	475.0	474.4	473.9	473.1	472.1	471.1	470.1	469.1
15°	457.7	455.7	453.7	452.3	451.3	450.2	449.2	448.2
17.5°	438.0	435.7	433.4	431.4	429.6	427.9	426.1	424.3
20°	424.3	421.7	419.2	416.8	414.5	412.3	410.1	407.9
22.5°	409.3	406.0	402.7	400.2	398.5	396.9	395.2	393.5
25°	384.4	380.1	376.0	373.1	371.6	370.0	368.5	367.0
27.5°	360.5	355.7	350.8	347.2	344.8	342.3	339.9	337.5
30°	343.8	338.6	333.4	329.4	326.6	323.9	321.1	318.4
32.5°	326.9	320.9	315.0	310.7	308.2	305.6	303.0	300.4
35°	300.5	294.1	287.6	283.3	281.0	278.8	276.6	274.4
37.5°	274.8	267.7	260.6	255.8	253.3	250.6	248.1	245.5
40°	257.6	250.3	243.1	238.1	235.5	232.9	230.1	227.5
42.5°	240.1	232.7	225.2	220.3	217.6	215.1	212.5	210.0
45°	214.9	207.6	200.5	195.6	193.2	190.7	188.2	185.8
47.5°	190.3	183.1	175.9	171.2	169.0	166.7	164.5	162.3
50°	174.5	167.4	160.4	155.8	153.7	151.6	149.4	147.2
52.5°	159.6	152.8	146.0	141.6	139.7	137.6	135.6	133.7
55°	136.8	130.8	124.6	120.6	118.7	116.7	114.8	112.9
57.5°	116.2	110.6	105.0	101.4	99.8	98.2	96.5	94.8
60°	102.0	96.8	91.6	88.2	86.5	84.9	83.3	81.7
62.5°	89.7	84.7	79.8	76.7	75.7	74.8	73.8	72.8
65°	72.9	69.4	65.9	64.0	63.7	63.4	63.1	62.8
67.5°	58.9	57.3	55.6	54.7	54.3	54.0	53.7	53.4
70°	51.2	50.2	49.2	48.5	48.0	47.6	47.2	46.8
72.5°	44.5	43.6	42.8	42.3	42.0	41.8	41.5	41.3
75°	35.2	34.5	33.8	33.4	33.3	33.2	33.1	33.0
77.5°	26.7	26.3	25.9	25.7	25.4	25.2	25.1	24.9
80°	21.2	20.8	20.4	20.2	20.2	20.2	20.2	20.2
82.5°	16.1	15.8	15.6	15.5	15.5	15.5	15.5	15.5
85°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
87.5°	10.3	9.7	10.1	10.3	10.3	10.3	10.3	10.3
90°	37.6	35.2	37.6	38.7	38.7	38.7	38.7	38.7
92.5°	102.3	87.8	77.9	70.6	69.7	65.9	66.9	65.0
95°	307.4	235.8	186.5	160.7	145.4	136.1	132.6	133.7
97.5°	717.2	586.8	459.9	375.2	319.1	290.2	273.1	263.3
100°	1071.1	925.6	764.9	622.9	525.5	475.1	441.1	420.0
102.5°	1302.9	1270.0	1152.5	1002.1	896.3	810.2	767.7	739.1
105°	1425.3	1557.9	1573.2	1534.5	1461.7	1389.0	1338.6	1322.1
107.5°	1337.2	1536.8	1658.8	1715.6	1724.7	1720.7	1710.6	1688.8
110°	1261.1	1471.1	1621.2	1717.5	1767.9	1790.2	1800.8	1799.6





TEST NUMBER: P331644-840

CATALOG NUMBER: SA2XXRDIP-C290D1080U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1191.6	1393.2	1553.7	1664.0	1734.1	1771.4	1791.4	1797.7
115°	1106.3	1287.0	1440.6	1561.5	1644.8	1698.7	1729.2	1739.8
117.5°	1042.0	1200.6	1340.0	1453.3	1538.2	1595.2	1627.4	1636.3
120°	1010.1	1155.5	1279.9	1386.6	1468.7	1523.9	1557.9	1569.6
122.5°	984.7	1118.0	1235.8	1332.2	1405.8	1460.1	1490.4	1500.2
125°	947.9	1068.7	1171.9	1259.9	1328.0	1372.6	1401.9	1411.3
127.5°	911.5	1020.9	1118.2	1199.4	1258.8	1300.5	1325.9	1333.4
130°	888.1	989.0	1081.7	1159.0	1216.6	1256.5	1279.9	1289.3
132.5°	865.6	959.0	1044.1	1116.8	1173.4	1213.3	1234.9	1243.2
135°	834.0	911.5	989.0	1054.6	1105.1	1143.8	1164.9	1169.6
137.5°	809.0	873.7	935.2	992.5	1038.4	1071.8	1090.4	1097.3
140°	793.0	849.4	903.3	954.9	992.5	1023.0	1040.6	1047.6
142.5°	779.9	827.8	874.2	917.4	953.0	980.8	996.4	997.8
145°	761.3	800.1	836.5	870.5	898.6	918.6	930.3	933.8
147.5°	747.1	777.6	806.0	830.8	854.0	870.0	878.0	880.1
150°	736.7	762.5	787.2	808.3	825.9	840.0	847.0	848.2
152.5°	726.4	750.3	771.2	789.5	803.3	815.6	820.7	820.9
155°	712.1	730.8	748.4	761.3	774.3	782.4	787.2	784.9
157.5°	695.4	711.1	725.9	736.0	745.2	751.9	754.1	754.1
160°	685.1	698.0	710.9	719.1	727.3	733.2	734.4	734.4
162.5°	674.8	685.8	696.8	703.2	711.3	715.4	716.5	715.6
165°	659.3	667.5	675.7	680.4	685.1	689.8	689.8	688.6
167.5°	644.5	650.9	656.5	660.8	662.8	665.4	665.2	663.8
170°	637.0	640.6	645.2	647.5	648.7	652.3	651.1	648.7
172.5°	628.5	631.2	634.9	636.3	637.5	639.1	637.9	636.5
175°	619.5	620.6	621.8	622.9	622.9	624.1	622.9	620.6
177.5°	612.9	612.9	613.8	613.8	613.8	613.8	612.9	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1

(END OF REPORT)