

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332694-830

Luminaire Tested: **SA4XXDIP-C1195D810U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332694-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1195D810U830-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7870.8 lumens  
Efficiency: N/A  
Efficacy: 129.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332694-830

CATALOG NUMBER: SA4XXDIP-C1195D810U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332694-830

CATALOG NUMBER: SA4XXDIP-C1195D810U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66	61
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	37
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	33	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15163	15163	15163
5°	15209	15027	15135
10°	15114	14905	14978
15°	14931	14692	14730
20°	14689	14430	14442
25°	14412	14130	14091
30°	14072	13778	13651
35°	13720	13409	13232
40°	13354	12991	12752
45°	12973	12578	12337
50°	12552	12210	11833
55°	12096	11736	11354
60°	11641	11202	10863
65°	11127	10695	10264
70°	10551	10017	9626
75°	9669	9201	8968
80°	8605	8257	8047
85°	7521	7243	7104



TEST NUMBER: P332694-830

CATALOG NUMBER: SA4XXDIP-C1195D810U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.9	2.2
10°-20°	498.4	6.3
20°-30°	733.6	9.3
30°-40°	852.8	10.8
40°-50°	852.8	10.8
50°-60°	746.0	9.5
60°-70°	554.0	7.0
70°-80°	314.7	4.0
80°-90°	93.7	1.2
90°-100°	33.7	0.4
100°-110°	214.9	2.7
110°-120°	411.0	5.2
120°-130°	521.8	6.6
130°-140°	558.3	7.1
140°-150°	522.1	6.6
150°-160°	421.0	5.3
160°-170°	271.5	3.4
170°-180°	93.6	1.2
0°-30°	1408.8	17.9
0°-40°	2261.6	28.7
0°-60°	3860.5	49.0
0°-90°	4822.9	61.3
90°-120°	659.6	8.4
90°-150°	2261.8	28.7
90°-180°	3048.0	38.7
0°-180°	7870.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1878	1878	1878	1878	1878	
5°	1877	1870	1854	1870	1868	178
15°	1786	1780	1758	1766	1762	503
25°	1618	1607	1586	1587	1582	744
35°	1392	1381	1361	1350	1343	870
45°	1136	1125	1102	1086	1081	876
55°	859	854	834	816	807	769
65°	582	575	560	545	537	577
75°	310	302	295	289	288	329
85°	81	81	78	78	77	89
90°	2	10	16	20	22	6
95°	40	17	16	20	21	52
105°	222	226	230	235	210	232
115°	414	416	416	417	417	407
125°	582	585	584	586	587	520
135°	722	722	724	726	727	556
145°	833	835	835	836	837	520
155°	913	914	912	914	912	421
165°	963	960	960	965	959	272
175°	985	981	982	987	979	94
180°	985	985	985	985	985	



TEST NUMBER: P332694-830

CATALOG NUMBER: SA4XXDIP-C1195D810U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1883.1	1882.4	1881.5	1880.7	1879.9	1878.0	1875.1	1872.2	1869.3	1866.3	1869.0
5°	1876.8	1875.5	1874.2	1872.8	1871.5	1869.0	1865.3	1861.6	1857.9	1854.3	1857.9
7.5°	1859.4	1858.0	1856.7	1855.3	1854.0	1851.3	1847.2	1843.1	1839.1	1834.9	1838.0
10°	1843.7	1842.4	1841.1	1839.7	1838.3	1835.5	1831.2	1826.8	1822.5	1818.2	1820.8
12.5°	1823.3	1821.9	1820.5	1819.2	1817.9	1814.9	1810.3	1805.7	1801.1	1796.5	1799.4
15°	1786.5	1785.2	1783.9	1782.5	1781.1	1778.0	1772.9	1767.9	1762.9	1757.9	1759.9
17.5°	1742.3	1740.6	1738.9	1737.3	1735.6	1732.4	1727.6	1722.9	1718.2	1713.4	1714.7
20°	1709.8	1708.1	1706.4	1704.8	1703.1	1699.7	1694.7	1689.7	1684.7	1679.6	1680.6
22.5°	1674.8	1672.6	1670.5	1668.2	1666.0	1662.4	1657.4	1652.4	1647.4	1642.3	1644.2
25°	1618.0	1615.6	1613.3	1610.9	1608.5	1605.1	1600.3	1595.7	1591.0	1586.3	1586.7
27.5°	1552.9	1550.5	1548.1	1545.7	1543.3	1539.9	1535.6	1531.3	1526.9	1522.5	1521.7
30°	1509.6	1506.9	1504.2	1501.6	1498.9	1495.3	1491.0	1486.7	1482.3	1478.0	1476.7
32.5°	1463.9	1461.4	1459.1	1456.6	1454.2	1450.7	1446.0	1441.4	1436.8	1432.2	1430.6
35°	1392.2	1389.9	1387.5	1385.2	1382.8	1379.3	1374.6	1370.0	1365.3	1360.6	1358.2
37.5°	1316.6	1314.5	1312.4	1310.2	1308.1	1304.5	1299.5	1294.5	1289.4	1284.4	1281.9
40°	1267.2	1264.6	1261.9	1259.2	1256.6	1252.7	1247.7	1242.6	1237.7	1232.7	1229.3
42.5°	1214.3	1212.7	1211.1	1209.5	1207.9	1204.3	1198.7	1193.2	1187.6	1182.0	1178.2
45°	1136.3	1134.0	1131.6	1129.3	1127.0	1123.1	1117.8	1112.4	1107.0	1101.7	1098.1
47.5°	1054.7	1053.1	1051.5	1049.9	1048.3	1045.1	1040.1	1035.2	1030.2	1025.3	1021.2
50°	999.4	998.1	996.6	995.3	994.0	991.0	986.3	981.7	976.9	972.2	967.6
52.5°	945.2	943.6	942.0	940.4	938.8	935.5	930.6	925.6	920.7	915.7	911.5
55°	859.4	858.4	857.4	856.4	855.4	852.5	847.8	843.2	838.5	833.8	829.8
57.5°	777.5	776.4	775.2	774.1	773.0	770.1	765.4	760.8	756.2	751.6	747.8
60°	721.0	719.3	717.6	716.0	714.3	711.2	706.9	702.6	698.1	693.8	690.8
62.5°	665.5	664.1	662.7	661.3	660.0	657.0	652.3	647.7	643.1	638.5	635.7
65°	582.5	580.8	579.1	577.4	575.8	573.3	570.0	566.6	563.3	559.9	556.6
67.5°	498.8	497.3	495.7	494.2	492.7	490.2	487.0	483.8	480.6	477.4	474.2
70°	447.0	444.7	442.3	440.0	437.6	435.2	432.4	429.8	427.1	424.4	421.8
72.5°	391.6	389.3	386.9	384.6	382.3	380.0	377.9	375.7	373.6	371.5	369.3
75°	310.0	308.4	306.7	305.0	303.3	301.7	300.0	298.3	296.7	295.0	293.7
77.5°	232.1	231.3	230.6	229.9	229.1	228.0	226.6	225.1	223.7	222.2	221.8
80°	185.1	184.1	183.1	182.1	181.2	180.3	179.6	178.9	178.2	177.6	176.9
82.5°	139.4	138.9	138.5	138.0	137.5	137.2	137.0	137.0	136.8	136.7	136.3
85°	81.2	81.2	81.2	81.2	81.2	81.0	80.3	79.6	78.9	78.2	78.2
87.5°	31.8	31.9	32.0	32.0	32.1	32.1	32.1	32.1	32.1	32.1	32.3
90°	2.2	4.1	5.8	7.6	9.4	10.9	12.3	13.6	14.9	16.2	17.2
92.5°	9.3	9.4	9.5	9.6	9.7	10.4	11.7	13.0	14.3	15.6	16.6
95°	40.5	35.0	29.4	23.8	18.3	15.6	15.7	15.9	16.0	16.2	17.2
97.5°	86.1	89.5	93.0	96.5	100.0	92.6	74.3	56.0	37.7	19.4	19.5
100°	120.8	123.9	126.8	129.7	132.6	122.8	100.2	77.7	55.0	32.4	29.6
102.5°	159.8	161.9	164.1	166.3	168.4	168.1	165.0	162.1	159.2	156.3	126.2
105°	221.8	222.8	223.8	224.8	225.7	226.7	227.4	228.3	229.1	229.9	231.4
107.5°	279.5	279.9	280.4	281.0	281.4	282.2	283.3	284.5	285.6	286.7	287.4
110°	318.4	318.9	319.3	319.8	320.4	321.0	322.1	323.0	324.0	325.0	325.4



TEST NUMBER: P332694-830

CATALOG NUMBER: SA4XXDIP-C1195D810U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.1	356.9	357.9	358.7	359.7	360.3	360.8	361.2	361.7	362.1	362.1
115°	414.2	414.6	415.2	415.7	416.1	416.3	416.1	415.9	415.8	415.7	415.9
117.5°	466.5	467.1	467.8	468.4	469.1	469.7	470.0	470.3	470.7	471.1	471.0
120°	501.9	502.6	503.2	503.9	504.4	504.7	504.5	504.4	504.3	504.1	504.4
122.5°	534.9	535.3	535.6	536.0	536.5	536.8	537.0	537.2	537.4	537.7	537.9
125°	582.2	582.9	583.5	584.2	584.8	584.9	584.7	584.4	584.0	583.7	584.2
127.5°	627.0	627.2	627.4	627.5	627.6	628.1	628.9	629.6	630.4	631.1	631.0
130°	655.9	656.1	656.2	656.4	656.6	656.9	657.3	657.9	658.4	658.8	659.0
132.5°	682.4	682.7	683.1	683.3	683.6	684.1	684.7	685.3	685.9	686.5	686.7
135°	722.3	722.1	721.9	721.7	721.6	721.8	722.5	723.1	723.8	724.4	724.7
137.5°	757.4	757.5	757.6	757.6	757.7	758.1	758.8	759.6	760.3	761.0	761.4
140°	780.4	780.8	781.1	781.5	781.7	782.1	782.4	782.8	783.1	783.3	783.9
142.5°	801.1	801.6	802.3	802.9	803.4	803.8	804.0	804.3	804.5	804.6	805.0
145°	832.7	833.3	833.8	834.2	834.7	835.0	835.0	835.0	835.0	835.0	835.2
147.5°	858.0	858.9	859.8	860.7	861.7	862.0	861.9	861.7	861.5	861.4	861.5
150°	876.3	876.9	877.6	878.3	878.8	879.1	878.9	878.8	878.6	878.4	878.4
152.5°	891.6	892.1	892.6	893.2	893.7	893.8	893.5	893.2	892.9	892.6	892.9
155°	913.1	913.2	913.4	913.6	913.8	913.6	913.1	912.6	912.1	911.6	912.3
157.5°	931.2	931.1	931.0	930.9	930.9	930.5	929.9	929.4	928.9	928.3	929.2
160°	941.9	941.3	940.8	940.4	939.9	939.5	939.4	939.2	939.1	938.9	939.9
162.5°	951.3	950.6	950.0	949.4	948.8	948.4	948.2	948.1	947.9	947.7	948.8
165°	963.2	962.4	961.6	960.7	960.0	959.5	959.5	959.5	959.5	959.5	960.8
167.5°	972.6	971.8	970.9	970.1	969.2	968.7	968.7	968.6	968.5	968.4	969.8
170°	978.0	976.9	976.0	975.0	974.0	973.6	973.7	973.9	974.1	974.3	975.5
172.5°	981.5	980.5	979.5	978.5	977.6	977.1	977.3	977.5	977.6	977.8	979.1
175°	985.3	984.3	983.4	982.4	981.4	981.0	981.2	981.3	981.5	981.7	983.1
177.5°	987.1	986.2	985.2	984.3	983.4	983.1	983.4	983.6	983.9	984.1	985.1
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3



TEST NUMBER: P332694-830

CATALOG NUMBER: SA4XXDIP-C1195D810U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1871.6	1874.3	1877.0	1878.2	1877.9	1877.6	1877.4	1877.1
5°	1861.6	1865.3	1869.0	1870.5	1869.8	1869.2	1868.5	1867.7
7.5°	1840.9	1843.8	1846.7	1848.0	1847.7	1847.2	1846.8	1846.4
10°	1823.4	1826.2	1828.8	1829.9	1829.2	1828.5	1827.8	1827.1
12.5°	1802.3	1805.3	1808.3	1809.2	1808.3	1807.3	1806.4	1805.4
15°	1761.9	1764.0	1765.9	1766.4	1765.5	1764.4	1763.4	1762.5
17.5°	1715.9	1717.2	1718.4	1718.7	1718.1	1717.4	1716.7	1716.1
20°	1681.7	1682.6	1683.7	1683.9	1683.2	1682.5	1681.9	1681.1
22.5°	1646.0	1647.8	1649.5	1649.8	1648.7	1647.5	1646.2	1645.0
25°	1587.1	1587.3	1587.7	1587.1	1585.8	1584.5	1583.2	1581.9
27.5°	1520.9	1520.1	1519.3	1518.1	1516.4	1514.8	1513.1	1511.4
30°	1475.3	1473.9	1472.6	1471.1	1469.4	1467.8	1466.1	1464.4
32.5°	1429.0	1427.4	1425.8	1424.2	1422.5	1420.8	1419.2	1417.5
35°	1355.9	1353.6	1351.2	1349.2	1347.6	1345.9	1344.2	1342.6
37.5°	1279.3	1276.8	1274.2	1271.9	1269.7	1267.4	1265.3	1263.0
40°	1226.0	1222.6	1219.3	1216.7	1215.1	1213.4	1211.7	1210.0
42.5°	1174.3	1170.4	1166.6	1164.0	1162.9	1161.8	1160.6	1159.5
45°	1094.4	1090.7	1087.0	1084.7	1083.6	1082.6	1081.7	1080.6
47.5°	1017.0	1012.9	1008.7	1005.3	1002.8	1000.2	997.7	995.1
50°	962.9	958.2	953.6	950.2	948.2	946.2	944.1	942.2
52.5°	907.4	903.2	899.1	895.8	893.2	890.7	888.2	885.6
55°	825.8	821.8	817.7	814.7	812.8	810.8	808.7	806.7
57.5°	744.0	740.2	736.4	733.5	731.6	729.6	727.6	725.8
60°	687.8	684.9	681.8	679.5	677.8	676.1	674.5	672.8
62.5°	632.9	630.2	627.5	625.3	623.6	621.9	620.3	618.6
65°	553.2	549.9	546.5	544.0	542.3	540.6	538.9	537.3
67.5°	471.0	467.8	464.6	462.7	462.2	461.8	461.3	460.8
70°	419.1	416.4	413.7	411.9	410.9	409.9	408.9	407.8
72.5°	367.2	365.0	362.9	361.3	360.3	359.3	358.3	357.3
75°	292.3	291.0	289.6	288.8	288.5	288.1	287.8	287.5
77.5°	221.3	220.9	220.6	219.9	219.0	218.2	217.3	216.4
80°	176.3	175.6	174.9	174.5	174.1	173.7	173.4	173.1
82.5°	135.8	135.4	135.1	134.7	134.3	134.0	133.7	133.4
85°	78.2	78.2	78.2	78.1	77.8	77.4	77.1	76.7
87.5°	32.5	32.7	32.9	33.1	33.1	33.2	33.3	33.4
90°	18.2	19.1	20.2	20.8	21.1	21.5	21.8	22.1
92.5°	17.6	18.6	19.5	20.1	20.2	20.2	20.3	20.4
95°	18.2	19.1	20.2	20.7	20.9	21.0	21.2	21.4
97.5°	19.7	19.8	19.9	20.0	20.2	20.3	20.5	20.6
100°	26.9	24.0	21.3	20.0	20.2	20.3	20.5	20.6
102.5°	96.1	66.2	36.1	21.1	21.1	21.1	21.2	21.2
105°	232.9	234.3	235.8	233.7	227.7	221.8	215.9	210.0
107.5°	288.1	288.8	289.5	290.2	290.9	291.4	292.1	292.8
110°	325.6	326.0	326.3	326.7	327.3	327.7	328.2	328.7





TEST NUMBER: P332694-830

CATALOG NUMBER: SA4XXDIP-C1195D810U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	362.0	361.9	361.8	362.1	362.8	363.4	364.0	364.7
115°	416.3	416.6	417.0	417.2	417.2	417.2	417.2	417.2
117.5°	470.9	470.9	470.8	470.7	470.7	470.6	470.5	470.5
120°	504.7	505.1	505.4	505.4	505.1	504.7	504.4	504.1
122.5°	538.1	538.3	538.5	538.4	538.1	537.7	537.4	537.1
125°	584.7	585.1	585.6	586.0	586.2	586.3	586.4	586.6
127.5°	630.9	630.8	630.7	630.7	630.5	630.4	630.3	630.1
130°	659.2	659.3	659.5	659.6	659.6	659.6	659.6	659.6
132.5°	686.9	687.0	687.2	687.2	687.1	686.9	686.8	686.7
135°	725.1	725.4	725.8	726.0	726.4	726.7	727.1	727.4
137.5°	761.7	762.0	762.4	762.5	762.4	762.3	762.2	762.1
140°	784.4	784.9	785.3	785.7	785.9	786.0	786.2	786.4
142.5°	805.3	805.7	806.1	806.3	806.3	806.3	806.3	806.3
145°	835.3	835.5	835.7	835.8	836.2	836.5	836.9	837.2
147.5°	861.7	861.8	861.9	862.0	862.2	862.3	862.5	862.7
150°	878.4	878.4	878.4	878.5	878.7	878.8	879.0	879.2
152.5°	893.2	893.4	893.6	893.7	893.6	893.5	893.4	893.3
155°	912.9	913.6	914.3	914.4	913.8	913.3	912.9	912.4
157.5°	930.0	930.9	931.7	931.7	930.9	930.0	929.2	928.3
160°	940.8	941.9	942.8	942.8	941.9	940.8	939.9	938.9
162.5°	949.7	950.6	951.7	951.6	950.5	949.3	948.3	947.2
165°	962.1	963.5	964.8	964.7	963.2	961.8	960.3	958.8
167.5°	971.3	972.7	974.1	974.0	972.4	970.7	969.1	967.5
170°	976.9	978.2	979.5	979.3	977.7	976.1	974.4	972.8
172.5°	980.4	981.8	983.1	982.8	981.1	979.3	977.5	975.7
175°	984.6	986.1	987.5	987.3	985.3	983.4	981.4	979.4
177.5°	986.3	987.3	988.4	988.1	986.5	985.0	983.4	981.8
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3

(END OF REPORT)