

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332523-830

Luminaire Tested: **SA4XXDIP-C350D1035U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332523-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D1035U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5323.8 lumens
Efficiency: N/A
Efficacy: 142.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332523-830
CATALOG NUMBER: SA4XXDIP-C350D1035U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332523-830

CATALOG NUMBER: SA4XXDIP-C350D1035U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	88	85	81	83	79	76	73	62	59	58	46	44	43	31	30	29	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	47	43	40	35	33	30	24	22	21	16
4	70	60	52	46	62	54	47	42	42	38	34	31	28	26	21	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	47	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14	10
7	55	43	35	30	49	38	32	27	30	26	22	23	20	17	16	14	12	9
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	12	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4495	4495	4495
5°	4508	4454	4486
10°	4480	4418	4440
15°	4425	4355	4367
20°	4354	4277	4281
25°	4272	4188	4177
30°	4172	4084	4047
35°	4066	3975	3921
40°	3958	3851	3780
45°	3846	3729	3658
50°	3720	3620	3508
55°	3586	3478	3365
60°	3450	3321	3219
65°	3299	3171	3043
70°	3127	2969	2854
75°	2866	2729	2658
80°	2552	2450	2385
85°	2232	2149	2103



TEST NUMBER: P332523-830

CATALOG NUMBER: SA4XXDIP-C350D1035U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	1.0
10°-20°	147.7	2.8
20°-30°	217.4	4.1
30°-40°	252.8	4.7
40°-50°	252.8	4.7
50°-60°	221.1	4.2
60°-70°	164.2	3.1
70°-80°	93.3	1.8
80°-90°	30.6	0.6
90°-100°	43.0	0.8
100°-110°	274.3	5.2
110°-120°	524.8	9.9
120°-130°	666.2	12.5
130°-140°	712.8	13.4
140°-150°	666.5	12.5
150°-160°	537.5	10.1
160°-170°	346.7	6.5
170°-180°	119.5	2.2
0°-30°	417.6	7.8
0°-40°	670.4	12.6
0°-60°	1144.3	21.5
0°-90°	1432.4	26.9
90°-120°	842.2	15.8
90°-150°	2887.7	54.2
90°-180°	3891.0	73.1
0°-180°	5323.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	556	554	550	554	554	53
15°	530	528	521	524	522	149
25°	480	476	470	471	469	221
35°	413	409	403	400	398	258
45°	337	333	327	322	320	260
55°	255	253	247	242	239	228
65°	173	170	166	162	159	171
75°	92	90	88	86	85	98
85°	24	24	23	23	23	27
90°	3	13	21	26	28	4
95°	52	22	21	26	27	67
105°	283	289	294	300	268	296
115°	529	531	531	532	532	520
125°	743	747	745	748	749	663
135°	922	921	925	927	929	710
145°	1063	1066	1066	1067	1069	664
155°	1166	1166	1164	1167	1165	537
165°	1230	1225	1225	1232	1224	347
175°	1258	1253	1253	1261	1250	120
180°	1258	1258	1258	1258	1258	



TEST NUMBER: P332523-830

CATALOG NUMBER: SA4XXDIP-C350D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	558.2	558.0	557.7	557.5	557.2	556.7	555.8	555.0	554.1	553.2	554.0
5°	556.3	555.9	555.5	555.2	554.8	554.0	552.9	551.9	550.7	549.6	550.7
7.5°	551.2	550.7	550.4	550.0	549.6	548.7	547.5	546.4	545.2	543.9	544.8
10°	546.5	546.1	545.7	545.4	545.0	544.1	542.8	541.5	540.3	538.9	539.7
12.5°	540.5	540.1	539.7	539.2	538.9	538.0	536.6	535.3	533.9	532.5	533.4
15°	529.5	529.1	528.8	528.4	528.0	527.1	525.6	524.1	522.5	521.1	521.7
17.5°	516.4	515.9	515.5	515.0	514.4	513.5	512.1	510.7	509.3	507.8	508.2
20°	506.8	506.3	505.9	505.3	504.8	503.9	502.4	500.9	499.4	497.9	498.2
22.5°	496.4	495.8	495.1	494.5	493.8	492.8	491.3	489.8	488.3	486.8	487.4
25°	479.6	478.9	478.2	477.5	476.8	475.8	474.4	473.0	471.6	470.2	470.3
27.5°	460.3	459.6	458.9	458.2	457.5	456.5	455.2	453.9	452.6	451.3	451.1
30°	447.5	446.7	445.9	445.1	444.3	443.3	442.0	440.6	439.4	438.1	437.7
32.5°	433.9	433.2	432.4	431.8	431.0	430.0	428.7	427.3	425.9	424.5	424.0
35°	412.6	412.0	411.3	410.6	409.9	408.9	407.5	406.0	404.7	403.3	402.7
37.5°	390.3	389.6	389.0	388.4	387.8	386.7	385.2	383.7	382.2	380.7	379.9
40°	375.6	374.8	374.1	373.2	372.5	371.4	369.9	368.3	366.8	365.4	364.4
42.5°	360.0	359.5	359.0	358.5	358.1	356.9	355.3	353.6	352.0	350.4	349.2
45°	336.9	336.1	335.5	334.8	334.0	332.9	331.3	329.7	328.2	326.6	325.5
47.5°	312.6	312.2	311.7	311.2	310.8	309.8	308.3	306.8	305.4	303.9	302.7
50°	296.2	295.9	295.5	295.0	294.6	293.8	292.4	291.0	289.5	288.2	286.8
52.5°	280.2	279.7	279.2	278.7	278.2	277.3	275.8	274.4	272.9	271.5	270.2
55°	254.8	254.5	254.1	253.8	253.5	252.7	251.3	250.0	248.5	247.1	246.0
57.5°	230.5	230.2	229.8	229.5	229.1	228.3	226.9	225.6	224.1	222.8	221.7
60°	213.7	213.2	212.7	212.2	211.7	210.8	209.5	208.2	207.0	205.7	204.8
62.5°	197.3	196.9	196.4	196.0	195.6	194.7	193.3	192.0	190.6	189.3	188.4
65°	172.7	172.2	171.6	171.2	170.7	169.9	168.9	168.0	166.9	166.0	164.9
67.5°	147.9	147.4	146.9	146.5	146.0	145.3	144.4	143.5	142.5	141.5	140.5
70°	132.5	131.8	131.1	130.4	129.7	128.9	128.2	127.4	126.6	125.8	125.0
72.5°	116.1	115.4	114.7	114.0	113.3	112.6	112.0	111.4	110.7	110.1	109.4
75°	91.9	91.4	91.0	90.4	89.9	89.4	89.0	88.4	87.9	87.5	87.1
77.5°	68.8	68.6	68.3	68.1	68.0	67.6	67.2	66.7	66.3	65.9	65.7
80°	54.9	54.6	54.3	54.0	53.7	53.4	53.3	53.1	52.9	52.7	52.4
82.5°	41.3	41.2	41.0	40.9	40.7	40.6	40.6	40.6	40.5	40.5	40.4
85°	24.1	24.1	24.1	24.1	24.1	24.0	23.8	23.6	23.4	23.2	23.2
87.5°	9.8	10.2	10.7	11.0	11.4	11.7	12.0	12.2	12.4	12.7	12.9
90°	2.8	5.1	7.4	9.7	12.1	14.0	15.6	17.3	19.0	20.7	22.0
92.5°	11.9	12.0	12.1	12.3	12.3	13.3	14.9	16.6	18.3	20.0	21.2
95°	51.7	44.7	37.5	30.4	23.3	19.9	20.1	20.3	20.5	20.7	22.0
97.5°	109.9	114.3	118.8	123.2	127.6	118.2	94.8	71.5	48.2	24.9	25.0
100°	154.3	158.1	161.8	165.6	169.4	156.8	128.0	99.2	70.2	41.4	37.9
102.5°	204.0	206.8	209.5	212.3	215.0	214.5	210.8	207.0	203.2	199.4	161.1
105°	283.2	284.5	285.7	287.0	288.2	289.4	290.4	291.4	292.6	293.6	295.5
107.5°	356.8	357.4	358.1	358.6	359.3	360.3	361.7	363.2	364.6	366.0	366.9
110°	406.5	407.1	407.7	408.3	409.0	409.9	411.1	412.5	413.7	414.9	415.4



TEST NUMBER: P332523-830

CATALOG NUMBER: SA4XXDIP-C350D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	454.7	455.8	456.9	458.1	459.2	460.1	460.6	461.2	461.8	462.3	462.3
115°	528.8	529.4	530.1	530.7	531.3	531.5	531.3	531.1	530.8	530.7	531.1
117.5°	595.6	596.4	597.3	598.1	599.0	599.6	600.0	600.5	601.0	601.4	601.3
120°	640.7	641.6	642.4	643.3	644.1	644.4	644.2	644.0	643.8	643.6	644.0
122.5°	682.9	683.4	683.9	684.4	684.9	685.3	685.6	685.9	686.2	686.5	686.7
125°	743.3	744.1	745.0	745.8	746.7	746.9	746.5	746.0	745.6	745.2	745.8
127.5°	800.5	800.7	801.0	801.2	801.3	801.9	803.0	803.9	804.8	805.8	805.7
130°	837.4	837.6	837.8	838.0	838.2	838.7	839.3	839.9	840.6	841.2	841.4
132.5°	871.3	871.7	872.0	872.4	872.8	873.4	874.2	875.0	875.7	876.6	876.8
135°	922.1	921.9	921.7	921.4	921.2	921.5	922.4	923.2	924.1	924.9	925.3
137.5°	967.0	967.1	967.2	967.3	967.4	967.9	968.8	969.8	970.6	971.6	972.0
140°	996.5	996.8	997.3	997.7	998.1	998.5	998.9	999.4	999.8	1000.2	1000.8
142.5°	1022.8	1023.5	1024.3	1025.0	1025.8	1026.2	1026.5	1026.8	1027.0	1027.3	1027.7
145°	1063.2	1063.8	1064.5	1065.1	1065.7	1066.0	1066.0	1066.0	1066.0	1066.0	1066.3
147.5°	1095.4	1096.6	1097.8	1098.9	1100.1	1100.6	1100.3	1100.1	1099.9	1099.8	1099.9
150°	1118.7	1119.6	1120.4	1121.2	1122.1	1122.4	1122.2	1122.0	1121.8	1121.5	1121.5
152.5°	1138.3	1139.0	1139.6	1140.3	1140.9	1141.1	1140.8	1140.4	1140.0	1139.6	1140.0
155°	1165.8	1166.0	1166.2	1166.4	1166.6	1166.4	1165.8	1165.2	1164.5	1163.9	1164.7
157.5°	1188.9	1188.8	1188.6	1188.5	1188.5	1188.0	1187.3	1186.6	1185.9	1185.2	1186.3
160°	1202.5	1201.8	1201.3	1200.6	1200.0	1199.6	1199.4	1199.1	1198.9	1198.7	1200.0
162.5°	1214.6	1213.7	1213.0	1212.1	1211.4	1210.9	1210.6	1210.4	1210.2	1210.0	1211.3
165°	1229.7	1228.7	1227.7	1226.6	1225.6	1225.0	1225.0	1225.0	1225.0	1225.0	1226.7
167.5°	1241.8	1240.8	1239.6	1238.6	1237.5	1236.9	1236.7	1236.6	1236.5	1236.3	1238.2
170°	1248.6	1247.4	1246.0	1244.8	1243.6	1243.0	1243.2	1243.5	1243.7	1243.9	1245.6
172.5°	1253.1	1251.9	1250.6	1249.3	1248.1	1247.5	1247.7	1248.0	1248.2	1248.4	1250.1
175°	1258.0	1256.8	1255.5	1254.2	1253.0	1252.5	1252.6	1252.9	1253.1	1253.3	1255.2
177.5°	1260.3	1259.0	1257.9	1256.8	1255.6	1255.2	1255.5	1255.8	1256.1	1256.5	1257.8
180°	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0



TEST NUMBER: P332523-830

CATALOG NUMBER: SA4XXDIP-C350D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	554.8	555.6	556.4	556.8	556.7	556.6	556.5	556.4
5°	551.9	552.9	554.0	554.4	554.2	554.0	553.8	553.6
7.5°	545.6	546.6	547.4	547.8	547.7	547.5	547.4	547.3
10°	540.5	541.3	542.2	542.4	542.2	542.0	541.8	541.6
12.5°	534.2	535.1	536.0	536.3	536.0	535.7	535.5	535.2
15°	522.3	522.8	523.5	523.6	523.3	523.0	522.7	522.5
17.5°	508.6	509.0	509.3	509.4	509.3	509.1	508.9	508.7
20°	498.5	498.8	499.1	499.2	498.9	498.7	498.5	498.3
22.5°	487.9	488.4	489.0	489.1	488.7	488.3	488.0	487.7
25°	470.4	470.5	470.6	470.5	470.0	469.7	469.3	468.9
27.5°	450.8	450.6	450.3	450.0	449.5	449.0	448.5	448.0
30°	437.3	437.0	436.5	436.1	435.5	435.1	434.6	434.1
32.5°	423.6	423.1	422.6	422.2	421.7	421.1	420.7	420.2
35°	401.9	401.2	400.5	399.9	399.4	399.0	398.4	397.9
37.5°	379.2	378.4	377.7	377.0	376.4	375.7	375.0	374.4
40°	363.4	362.4	361.5	360.7	360.1	359.7	359.2	358.7
42.5°	348.1	346.9	345.8	345.1	344.7	344.4	344.0	343.7
45°	324.4	323.3	322.3	321.5	321.2	320.9	320.7	320.4
47.5°	301.4	300.2	299.0	298.0	297.3	296.5	295.8	295.0
50°	285.4	284.1	282.7	281.6	281.1	280.5	279.8	279.3
52.5°	269.0	267.8	266.6	265.5	264.8	264.0	263.3	262.5
55°	244.8	243.6	242.4	241.5	240.9	240.3	239.7	239.1
57.5°	220.6	219.4	218.3	217.4	216.9	216.3	215.7	215.1
60°	203.9	203.0	202.1	201.4	201.0	200.4	199.9	199.4
62.5°	187.7	186.8	186.0	185.3	184.8	184.4	183.9	183.3
65°	164.0	163.0	162.0	161.3	160.8	160.2	159.8	159.3
67.5°	139.6	138.6	137.7	137.1	137.0	136.9	136.8	136.6
70°	124.2	123.5	122.6	122.1	121.8	121.5	121.2	120.9
72.5°	108.9	108.2	107.5	107.1	106.8	106.5	106.2	105.9
75°	86.6	86.2	85.9	85.6	85.5	85.4	85.3	85.2
77.5°	65.6	65.5	65.4	65.2	64.9	64.7	64.4	64.2
80°	52.2	52.0	51.8	51.7	51.6	51.5	51.4	51.3
82.5°	40.2	40.2	40.1	40.0	39.9	39.7	39.6	39.5
85°	23.2	23.2	23.2	23.2	23.1	23.0	22.8	22.7
87.5°	13.2	13.5	13.7	13.9	13.9	14.0	14.1	14.2
90°	23.2	24.5	25.7	26.6	27.0	27.4	27.8	28.2
92.5°	22.4	23.8	25.0	25.6	25.7	25.8	25.9	26.0
95°	23.2	24.5	25.7	26.5	26.7	26.9	27.1	27.2
97.5°	25.1	25.3	25.4	25.5	25.7	25.9	26.1	26.4
100°	34.3	30.7	27.1	25.5	25.7	25.9	26.1	26.4
102.5°	122.8	84.5	46.1	27.0	27.0	27.1	27.1	27.1
105°	297.4	299.2	301.0	298.3	290.8	283.2	275.7	268.2
107.5°	367.9	368.8	369.7	370.5	371.4	372.1	373.0	373.7
110°	415.8	416.2	416.6	417.2	417.7	418.4	419.1	419.6



TEST NUMBER: P332523-830

CATALOG NUMBER: SA4XXDIP-C350D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	462.2	462.1	462.0	462.4	463.2	464.0	464.8	465.5
115°	531.5	532.0	532.3	532.5	532.5	532.5	532.5	532.5
117.5°	601.2	601.2	601.1	601.1	601.0	600.9	600.8	600.7
120°	644.4	644.8	645.3	645.3	644.8	644.4	644.0	643.6
122.5°	687.0	687.2	687.5	687.4	687.0	686.5	686.2	685.7
125°	746.5	747.1	747.7	748.1	748.4	748.6	748.8	748.9
127.5°	805.6	805.4	805.3	805.1	805.0	804.8	804.6	804.5
130°	841.6	841.8	842.0	842.2	842.2	842.2	842.2	842.2
132.5°	876.9	877.2	877.4	877.4	877.2	877.0	876.9	876.8
135°	925.8	926.1	926.6	927.0	927.5	927.8	928.2	928.7
137.5°	972.5	973.0	973.5	973.6	973.5	973.4	973.2	973.1
140°	1001.5	1002.1	1002.7	1003.1	1003.3	1003.5	1003.7	1004.0
142.5°	1028.2	1028.7	1029.2	1029.4	1029.4	1029.4	1029.5	1029.5
145°	1066.5	1066.7	1066.9	1067.2	1067.6	1068.0	1068.5	1068.8
147.5°	1100.0	1100.2	1100.4	1100.6	1100.8	1101.0	1101.3	1101.5
150°	1121.5	1121.5	1121.5	1121.6	1121.9	1122.1	1122.3	1122.5
152.5°	1140.3	1140.7	1140.9	1141.0	1140.9	1140.9	1140.7	1140.6
155°	1165.5	1166.4	1167.2	1167.3	1166.8	1166.1	1165.5	1164.9
157.5°	1187.3	1188.5	1189.5	1189.5	1188.5	1187.3	1186.3	1185.2
160°	1201.3	1202.5	1203.7	1203.7	1202.5	1201.3	1200.0	1198.7
162.5°	1212.5	1213.8	1215.0	1214.9	1213.5	1212.1	1210.7	1209.3
165°	1228.4	1230.1	1231.7	1231.6	1229.7	1227.9	1226.0	1224.1
167.5°	1240.0	1241.9	1243.7	1243.6	1241.5	1239.4	1237.3	1235.2
170°	1247.3	1248.9	1250.6	1250.4	1248.3	1246.2	1244.1	1242.0
172.5°	1251.8	1253.4	1255.1	1254.8	1252.5	1250.3	1248.0	1245.8
175°	1257.1	1259.0	1260.8	1260.5	1258.0	1255.5	1253.0	1250.5
177.5°	1259.1	1260.5	1261.9	1261.5	1259.5	1257.5	1255.5	1253.5
180°	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0

(END OF REPORT)