

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332496-830

Luminaire Tested: **SA4XXDIP-C350D365U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332496-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D365U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2807.7 lumens
Efficiency: N/A
Efficacy: 138.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332496-830
CATALOG NUMBER: SA4XXDIP-C350D365U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332496-830

CATALOG NUMBER: SA4XXDIP-C350D365U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	43	43	43	20	20		
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	43	42	41	36	36		
2	89	82	76	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36	35	34	30	30		
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34	30	29	28	24	24		
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30	26	25	24	20	20		
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	32	28	26	23	22	21	18	18		
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	20	19	18	15	15		
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18	17	16	14	14		
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16	15	14	13	13		
9	50	38	31	25	46	36	29	24	31	25	22	26	22	19	22	19	16	14	13	12	11	11		
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13	12	11	10	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4495	4495	4495
5°	4508	4454	4486
10°	4480	4418	4440
15°	4425	4355	4367
20°	4354	4277	4281
25°	4272	4188	4177
30°	4172	4084	4047
35°	4066	3975	3921
40°	3958	3851	3780
45°	3846	3729	3658
50°	3720	3620	3508
55°	3586	3478	3365
60°	3450	3321	3219
65°	3299	3171	3043
70°	3127	2969	2854
75°	2866	2729	2658
80°	2552	2450	2385
85°	2232	2149	2103



TEST NUMBER: P332496-830

CATALOG NUMBER: SA4XXDIP-C350D365U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	1.9
10°-20°	147.7	5.3
20°-30°	217.4	7.7
30°-40°	252.8	9.0
40°-50°	252.8	9.0
50°-60°	221.1	7.9
60°-70°	164.2	5.8
70°-80°	93.3	3.3
80°-90°	28.2	1.0
90°-100°	15.2	0.5
100°-110°	97.1	3.5
110°-120°	185.8	6.6
120°-130°	235.8	8.4
130°-140°	252.3	9.0
140°-150°	236.0	8.4
150°-160°	190.3	6.8
160°-170°	122.7	4.4
170°-180°	42.3	1.5
0°-30°	417.6	14.9
0°-40°	670.4	23.9
0°-60°	1144.3	40.8
0°-90°	1430.1	50.9
90°-120°	298.1	10.6
90°-150°	1022.3	36.4
90°-180°	1378.0	49.1
0°-180°	2807.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	556	554	550	554	554	53
15°	530	528	521	524	522	149
25°	480	476	470	471	469	221
35°	413	409	403	400	398	258
45°	337	333	327	322	320	260
55°	255	253	247	242	239	228
65°	173	170	166	162	159	171
75°	92	90	88	86	85	98
85°	24	24	23	23	23	27
90°	1	5	7	9	10	2
95°	18	8	7	9	10	24
105°	100	102	104	106	95	105
115°	187	188	188	188	188	184
125°	263	264	264	265	265	235
135°	326	326	327	328	329	251
145°	376	377	377	378	378	235
155°	413	413	412	413	412	190
165°	435	434	434	436	433	123
175°	445	444	444	446	443	42
180°	445	445	445	445	445	



TEST NUMBER: P332496-830

CATALOG NUMBER: SA4XXDIP-C350D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	558.2	558.0	557.7	557.5	557.2	556.7	555.8	555.0	554.1	553.2	554.0
5°	556.3	555.9	555.5	555.2	554.8	554.0	552.9	551.9	550.7	549.6	550.7
7.5°	551.2	550.7	550.4	550.0	549.6	548.7	547.5	546.4	545.2	543.9	544.8
10°	546.5	546.1	545.7	545.4	545.0	544.1	542.8	541.5	540.3	538.9	539.7
12.5°	540.5	540.1	539.7	539.2	538.9	538.0	536.6	535.3	533.9	532.5	533.4
15°	529.5	529.1	528.8	528.4	528.0	527.1	525.6	524.1	522.5	521.1	521.7
17.5°	516.4	515.9	515.5	515.0	514.4	513.5	512.1	510.7	509.3	507.8	508.2
20°	506.8	506.3	505.9	505.3	504.8	503.9	502.4	500.9	499.4	497.9	498.2
22.5°	496.4	495.8	495.1	494.5	493.8	492.8	491.3	489.8	488.3	486.8	487.4
25°	479.6	478.9	478.2	477.5	476.8	475.8	474.4	473.0	471.6	470.2	470.3
27.5°	460.3	459.6	458.9	458.2	457.5	456.5	455.2	453.9	452.6	451.3	451.1
30°	447.5	446.7	445.9	445.1	444.3	443.3	442.0	440.6	439.4	438.1	437.7
32.5°	433.9	433.2	432.4	431.8	431.0	430.0	428.7	427.3	425.9	424.5	424.0
35°	412.6	412.0	411.3	410.6	409.9	408.9	407.5	406.0	404.7	403.3	402.7
37.5°	390.3	389.6	389.0	388.4	387.8	386.7	385.2	383.7	382.2	380.7	379.9
40°	375.6	374.8	374.1	373.2	372.5	371.4	369.9	368.3	366.8	365.4	364.4
42.5°	360.0	359.5	359.0	358.5	358.1	356.9	355.3	353.6	352.0	350.4	349.2
45°	336.9	336.1	335.5	334.8	334.0	332.9	331.3	329.7	328.2	326.6	325.5
47.5°	312.6	312.2	311.7	311.2	310.8	309.8	308.3	306.8	305.4	303.9	302.7
50°	296.2	295.9	295.5	295.0	294.6	293.8	292.4	291.0	289.5	288.2	286.8
52.5°	280.2	279.7	279.2	278.7	278.2	277.3	275.8	274.4	272.9	271.5	270.2
55°	254.8	254.5	254.1	253.8	253.5	252.7	251.3	250.0	248.5	247.1	246.0
57.5°	230.5	230.2	229.8	229.5	229.1	228.3	226.9	225.6	224.1	222.8	221.7
60°	213.7	213.2	212.7	212.2	211.7	210.8	209.5	208.2	207.0	205.7	204.8
62.5°	197.3	196.9	196.4	196.0	195.6	194.7	193.3	192.0	190.6	189.3	188.4
65°	172.7	172.2	171.6	171.2	170.7	169.9	168.9	168.0	166.9	166.0	164.9
67.5°	147.9	147.4	146.9	146.5	146.0	145.3	144.4	143.5	142.5	141.5	140.5
70°	132.5	131.8	131.1	130.4	129.7	128.9	128.2	127.4	126.6	125.8	125.0
72.5°	116.1	115.4	114.7	114.0	113.3	112.6	112.0	111.4	110.7	110.1	109.4
75°	91.9	91.4	91.0	90.4	89.9	89.4	89.0	88.4	87.9	87.5	87.1
77.5°	68.8	68.6	68.3	68.1	68.0	67.6	67.2	66.7	66.3	65.9	65.7
80°	54.9	54.6	54.3	54.0	53.7	53.4	53.3	53.1	52.9	52.7	52.4
82.5°	41.3	41.2	41.0	40.9	40.7	40.6	40.6	40.6	40.5	40.5	40.4
85°	24.1	24.1	24.1	24.1	24.1	24.0	23.8	23.6	23.4	23.2	23.2
87.5°	9.5	9.5	9.6	9.7	9.8	9.9	9.9	10.0	10.0	10.0	10.1
90°	1.0	1.8	2.6	3.5	4.2	5.0	5.6	6.1	6.7	7.4	7.7
92.5°	4.2	4.2	4.2	4.3	4.3	4.7	5.3	5.8	6.5	7.1	7.5
95°	18.3	15.8	13.3	10.7	8.3	7.1	7.1	7.2	7.3	7.4	7.7
97.5°	38.9	40.4	42.0	43.6	45.1	41.8	33.6	25.4	17.1	8.8	8.9
100°	54.7	56.0	57.3	58.6	59.9	55.5	45.3	35.1	24.9	14.7	13.4
102.5°	72.2	73.2	74.2	75.1	76.2	76.0	74.6	73.3	71.9	70.6	57.0
105°	100.3	100.7	101.1	101.6	102.1	102.5	102.8	103.2	103.6	104.0	104.6
107.5°	126.3	126.5	126.8	127.0	127.2	127.5	128.1	128.6	129.0	129.6	129.9
110°	143.9	144.1	144.3	144.6	144.8	145.2	145.5	146.0	146.5	146.9	147.0



TEST NUMBER: P332496-830

CATALOG NUMBER: SA4XXDIP-C350D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.0	161.4	161.7	162.1	162.6	162.9	163.1	163.2	163.4	163.7	163.6
115°	187.2	187.5	187.7	187.8	188.1	188.1	188.1	188.0	187.9	187.8	188.0
117.5°	210.8	211.1	211.4	211.8	212.1	212.3	212.4	212.6	212.7	212.9	212.9
120°	226.9	227.2	227.4	227.7	228.0	228.1	228.1	228.0	227.9	227.8	228.0
122.5°	241.8	242.0	242.1	242.3	242.5	242.6	242.7	242.8	242.9	243.1	243.1
125°	263.2	263.4	263.7	264.0	264.4	264.4	264.3	264.1	264.0	263.8	264.0
127.5°	283.4	283.5	283.5	283.6	283.7	283.9	284.3	284.6	284.9	285.3	285.2
130°	296.4	296.5	296.6	296.7	296.8	296.9	297.1	297.4	297.6	297.8	297.8
132.5°	308.5	308.6	308.7	308.9	309.0	309.2	309.4	309.7	310.0	310.3	310.4
135°	326.4	326.4	326.3	326.2	326.1	326.2	326.6	326.9	327.2	327.4	327.6
137.5°	342.3	342.4	342.4	342.4	342.5	342.7	343.0	343.3	343.7	343.9	344.1
140°	352.8	352.9	353.1	353.2	353.4	353.5	353.6	353.8	353.9	354.1	354.3
142.5°	362.1	362.3	362.6	362.9	363.2	363.4	363.4	363.5	363.6	363.7	363.8
145°	376.5	376.6	376.8	377.1	377.3	377.4	377.4	377.4	377.4	377.4	377.5
147.5°	387.8	388.2	388.6	389.1	389.5	389.6	389.6	389.5	389.4	389.4	389.4
150°	396.1	396.3	396.6	397.0	397.3	397.4	397.3	397.2	397.1	397.1	397.1
152.5°	403.0	403.2	403.5	403.7	404.0	404.0	403.9	403.7	403.6	403.5	403.6
155°	412.7	412.8	412.8	412.9	413.0	412.9	412.7	412.5	412.3	412.1	412.4
157.5°	420.9	420.8	420.8	420.8	420.8	420.6	420.4	420.1	419.8	419.6	420.0
160°	425.7	425.5	425.3	425.1	424.8	424.7	424.6	424.5	424.4	424.3	424.8
162.5°	430.0	429.7	429.4	429.1	428.9	428.7	428.6	428.5	428.5	428.4	428.9
165°	435.4	435.0	434.6	434.2	433.9	433.7	433.7	433.7	433.7	433.7	434.3
167.5°	439.6	439.2	438.8	438.5	438.1	437.9	437.8	437.8	437.7	437.7	438.4
170°	442.1	441.6	441.1	440.7	440.3	440.1	440.2	440.3	440.3	440.4	440.9
172.5°	443.7	443.2	442.7	442.3	441.9	441.7	441.8	441.9	441.9	442.0	442.5
175°	445.4	444.9	444.5	444.0	443.6	443.4	443.5	443.6	443.7	443.7	444.4
177.5°	446.2	445.7	445.4	444.9	444.5	444.3	444.5	444.6	444.7	444.8	445.4
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4



TEST NUMBER: P332496-830

CATALOG NUMBER: SA4XXDIP-C350D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	554.8	555.6	556.4	556.8	556.7	556.6	556.5	556.4
5°	551.9	552.9	554.0	554.4	554.2	554.0	553.8	553.6
7.5°	545.6	546.6	547.4	547.8	547.7	547.5	547.4	547.3
10°	540.5	541.3	542.2	542.4	542.2	542.0	541.8	541.6
12.5°	534.2	535.1	536.0	536.3	536.0	535.7	535.5	535.2
15°	522.3	522.8	523.5	523.6	523.3	523.0	522.7	522.5
17.5°	508.6	509.0	509.3	509.4	509.3	509.1	508.9	508.7
20°	498.5	498.8	499.1	499.2	498.9	498.7	498.5	498.3
22.5°	487.9	488.4	489.0	489.1	488.7	488.3	488.0	487.7
25°	470.4	470.5	470.6	470.5	470.0	469.7	469.3	468.9
27.5°	450.8	450.6	450.3	450.0	449.5	449.0	448.5	448.0
30°	437.3	437.0	436.5	436.1	435.5	435.1	434.6	434.1
32.5°	423.6	423.1	422.6	422.2	421.7	421.1	420.7	420.2
35°	401.9	401.2	400.5	399.9	399.4	399.0	398.4	397.9
37.5°	379.2	378.4	377.7	377.0	376.4	375.7	375.0	374.4
40°	363.4	362.4	361.5	360.7	360.1	359.7	359.2	358.7
42.5°	348.1	346.9	345.8	345.1	344.7	344.4	344.0	343.7
45°	324.4	323.3	322.3	321.5	321.2	320.9	320.7	320.4
47.5°	301.4	300.2	299.0	298.0	297.3	296.5	295.8	295.0
50°	285.4	284.1	282.7	281.6	281.1	280.5	279.8	279.3
52.5°	269.0	267.8	266.6	265.5	264.8	264.0	263.3	262.5
55°	244.8	243.6	242.4	241.5	240.9	240.3	239.7	239.1
57.5°	220.6	219.4	218.3	217.4	216.9	216.3	215.7	215.1
60°	203.9	203.0	202.1	201.4	201.0	200.4	199.9	199.4
62.5°	187.7	186.8	186.0	185.3	184.8	184.4	183.9	183.3
65°	164.0	163.0	162.0	161.3	160.8	160.2	159.8	159.3
67.5°	139.6	138.6	137.7	137.1	137.0	136.9	136.8	136.6
70°	124.2	123.5	122.6	122.1	121.8	121.5	121.2	120.9
72.5°	108.9	108.2	107.5	107.1	106.8	106.5	106.2	105.9
75°	86.6	86.2	85.9	85.6	85.5	85.4	85.3	85.2
77.5°	65.6	65.5	65.4	65.2	64.9	64.7	64.4	64.2
80°	52.2	52.0	51.8	51.7	51.6	51.5	51.4	51.3
82.5°	40.2	40.2	40.1	40.0	39.9	39.7	39.6	39.5
85°	23.2	23.2	23.2	23.2	23.1	23.0	22.8	22.7
87.5°	10.2	10.3	10.4	10.5	10.5	10.5	10.6	10.6
90°	8.2	8.7	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	7.9	8.4	8.9	9.0	9.1	9.1	9.1	9.2
95°	8.2	8.7	9.1	9.3	9.4	9.5	9.6	9.6
97.5°	8.9	9.0	9.0	9.0	9.1	9.1	9.2	9.3
100°	12.2	10.8	9.6	9.0	9.1	9.1	9.2	9.3
102.5°	43.5	29.9	16.3	9.5	9.5	9.5	9.6	9.6
105°	105.3	105.9	106.6	105.6	102.9	100.3	97.6	94.9
107.5°	130.3	130.5	130.9	131.2	131.5	131.8	132.1	132.3
110°	147.2	147.3	147.5	147.7	147.9	148.2	148.4	148.5



TEST NUMBER: P332496-830

CATALOG NUMBER: SA4XXDIP-C350D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	163.6	163.6	163.5	163.7	164.0	164.3	164.6	164.9
115°	188.1	188.3	188.5	188.5	188.5	188.5	188.5	188.5
117.5°	212.8	212.8	212.8	212.7	212.7	212.7	212.7	212.6
120°	228.1	228.3	228.5	228.5	228.3	228.1	228.0	227.8
122.5°	243.2	243.3	243.4	243.4	243.2	243.1	242.9	242.8
125°	264.3	264.5	264.7	264.9	264.9	265.0	265.0	265.1
127.5°	285.2	285.1	285.1	285.0	285.0	284.9	284.8	284.8
130°	297.9	298.0	298.1	298.1	298.1	298.1	298.1	298.1
132.5°	310.5	310.6	310.7	310.7	310.6	310.5	310.5	310.4
135°	327.7	327.9	328.0	328.2	328.3	328.5	328.7	328.8
137.5°	344.3	344.5	344.6	344.7	344.6	344.6	344.5	344.5
140°	354.5	354.8	355.0	355.2	355.2	355.2	355.3	355.4
142.5°	364.0	364.2	364.3	364.4	364.5	364.5	364.5	364.5
145°	377.6	377.7	377.7	377.8	378.0	378.1	378.2	378.4
147.5°	389.5	389.6	389.6	389.6	389.7	389.7	389.8	389.9
150°	397.1	397.1	397.1	397.1	397.2	397.3	397.3	397.4
152.5°	403.7	403.8	404.0	404.0	403.9	403.9	403.9	403.8
155°	412.6	412.9	413.2	413.3	413.0	412.8	412.6	412.4
157.5°	420.4	420.8	421.1	421.1	420.8	420.4	420.0	419.6
160°	425.3	425.7	426.1	426.1	425.7	425.3	424.8	424.3
162.5°	429.2	429.7	430.2	430.1	429.6	429.1	428.6	428.1
165°	434.9	435.5	436.1	436.0	435.4	434.7	434.0	433.4
167.5°	439.0	439.7	440.3	440.3	439.5	438.8	438.0	437.3
170°	441.6	442.1	442.7	442.6	442.0	441.2	440.5	439.7
172.5°	443.2	443.7	444.3	444.2	443.5	442.6	441.9	441.0
175°	445.1	445.7	446.4	446.3	445.4	444.5	443.6	442.7
177.5°	445.8	446.3	446.8	446.6	445.9	445.2	444.5	443.7
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4

(END OF REPORT)