

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331634-840

Luminaire Tested: **SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331634-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4485.1 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331634-840
CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	93	89	85	82	82	79	76	74	61	60	58	45	44	43	30	30	29	22
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19
3	77	69	62	57	69	62	56	51	48	44	41	36	33	31	24	23	22	17
4	71	61	54	48	63	55	49	44	43	39	35	32	29	27	22	21	19	15
5	65	54	47	41	58	49	43	38	39	34	31	29	26	24	20	18	17	13
6	60	49	41	36	54	44	38	33	35	30	27	26	23	21	18	17	15	12
7	56	44	37	31	50	40	33	29	32	27	24	24	21	19	17	15	14	11
8	52	40	33	28	46	36	30	26	29	24	21	22	19	17	16	14	12	10
9	48	37	30	25	43	33	27	23	27	22	19	20	17	15	15	13	11	9
10	45	33	27	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10658	10658	10658	10658
5°	11904	10726	9511	10726
10°	13209	10650	8243	10650
15°	13857	10494	6496	10494
20°	12014	10263	5620	10263
25°	7878	9948	5018	9948
30°	5304	9562	4542	9562
35°	4295	9079	4096	9079
40°	3819	8553	3792	8553
45°	3457	7935	3382	7935
50°	3145	7322	3135	7322
55°	2956	6643	2919	6643
60°	2474	6022	2444	6022
65°	2086	5467	2365	5467
70°	1926	4881	2233	4881
75°	1803	4255	2059	4255
80°	1664	3505	1832	3505
85°	1538	2760	1612	2760



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.6	1.4
10°-20°	174.4	3.9
20°-30°	224.7	5.0
30°-40°	213.5	4.8
40°-50°	182.9	4.1
50°-60°	139.3	3.1
60°-70°	88.1	2.0
70°-80°	44.0	1.0
80°-90°	16.2	0.4
90°-100°	75.7	1.7
100°-110°	235.0	5.2
110°-120°	401.8	9.0
120°-130°	528.3	11.8
130°-140°	593.0	13.2
140°-150°	581.4	13.0
150°-160°	487.7	10.9
160°-170°	323.5	7.2
170°-180°	113.0	2.5
0°-30°	461.7	10.3
0°-40°	675.2	15.1
0°-60°	997.5	22.2
0°-90°	1145.7	25.5
90°-120°	712.5	15.9
90°-150°	2415.2	53.8
90°-180°	3339.0	74.4
0°-180°	4485.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	660	660	660	660	660	
5°	734	662	587	662	734	72
15°	829	628	389	628	829	224
25°	442	558	282	558	442	210
35°	218	461	208	461	218	139
45°	151	348	148	348	151	117
55°	105	236	104	236	105	92
65°	55	143	62	143	55	56
75°	29	68	33	68	29	31
85°	8	15	9	15	8	10
90°	34	1	34	1	34	15
95°	62	52	62	52	62	70
105°	224	217	224	217	224	235
115°	403	403	403	403	403	398
125°	588	586	588	586	588	525
135°	768	759	768	759	768	591
145°	931	921	931	921	931	582
155°	1061	1053	1061	1053	1061	488
165°	1147	1146	1147	1146	1147	323
175°	1188	1192	1188	1192	1188	113
180°	1194	1194	1194	1194	1194	



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	687.0	687.5	688.1	686.8	686.8	685.7	683.3	681.5	676.3	675.6	675.6
5°	734.5	734.1	735.0	732.0	727.9	726.9	722.6	716.8	710.8	704.3	702.9
7.5°	781.7	781.0	779.2	778.7	775.6	768.6	761.6	754.2	744.3	734.6	729.7
10°	805.7	813.2	808.6	800.6	802.1	791.4	785.7	775.8	767.5	753.1	749.9
12.5°	829.1	832.1	830.6	826.1	824.0	816.6	808.8	800.2	785.0	772.0	760.7
15°	829.0	833.3	834.6	833.1	834.2	833.8	829.7	822.6	809.3	795.1	782.6
17.5°	767.8	770.8	778.4	783.5	789.9	803.4	810.2	812.7	810.8	802.6	794.0
20°	699.2	694.2	715.3	726.0	735.2	758.1	777.9	785.5	797.6	797.4	795.1
22.5°	601.9	603.1	623.1	635.9	662.7	685.7	708.1	736.6	760.1	775.7	784.8
25°	442.2	451.0	470.9	488.4	518.2	560.9	599.7	644.6	687.0	720.5	752.5
27.5°	332.1	332.9	348.6	364.8	382.4	417.4	466.3	519.9	580.4	630.4	687.7
30°	284.5	283.1	289.7	299.6	314.8	341.8	378.5	431.2	491.6	566.8	633.8
32.5°	250.6	250.7	255.8	263.1	275.6	293.9	319.0	361.9	418.9	492.9	571.4
35°	217.9	217.7	221.4	226.6	231.9	243.6	260.8	283.3	322.6	391.5	471.8
37.5°	194.4	195.4	197.2	200.6	206.3	212.9	223.2	238.3	266.2	307.1	374.6
40°	181.2	181.7	184.2	186.9	190.4	195.4	203.9	216.1	236.5	269.0	318.4
42.5°	169.2	169.6	171.4	173.9	176.6	181.7	188.7	199.2	215.8	241.2	281.9
45°	151.4	151.4	153.0	154.1	157.1	161.7	167.4	176.2	187.6	206.4	233.5
47.5°	134.8	134.8	135.9	137.8	139.8	143.3	149.0	156.1	164.4	178.9	202.1
50°	125.2	125.5	126.1	127.7	129.0	132.1	136.5	142.7	151.4	162.7	181.9
52.5°	117.5	117.4	118.3	119.0	119.8	122.0	125.3	130.8	138.6	148.3	164.3
55°	105.0	104.1	105.5	106.6	107.3	108.3	110.1	113.5	120.2	128.5	140.4
57.5°	89.5	89.1	90.1	91.1	93.3	95.7	97.4	99.5	102.9	108.9	120.7
60°	76.6	76.6	78.7	79.4	81.9	85.1	88.4	90.2	93.6	97.5	106.2
62.5°	65.2	65.4	66.3	67.1	68.5	72.4	77.0	81.0	84.2	88.0	93.7
65°	54.6	55.0	55.0	55.5	56.5	57.4	59.2	62.4	68.2	73.4	77.8
67.5°	46.4	46.5	46.7	47.1	47.3	48.3	49.1	50.5	51.8	56.8	62.2
70°	40.8	41.5	41.3	41.7	42.0	42.4	43.3	44.0	46.2	47.3	50.5
72.5°	35.6	36.2	36.2	36.5	37.1	37.2	37.9	38.6	39.9	40.8	42.6
75°	28.9	28.7	28.9	29.4	29.6	29.8	29.8	30.7	31.4	32.3	33.5
77.5°	22.3	22.5	22.5	22.5	22.6	23.0	22.9	23.3	24.0	24.5	25.0
80°	17.9	18.1	17.9	18.1	18.4	18.6	18.4	18.6	19.3	19.7	19.7
82.5°	13.8	13.9	14.0	14.0	14.1	14.1	14.5	14.5	15.0	14.9	15.1
85°	8.3	8.1	8.1	8.1	8.3	8.5	8.3	8.3	8.5	8.5	8.5
87.5°	9.8	9.9	9.9	9.8	9.8	9.8	9.9	10.2	10.1	10.4	9.2
90°	34.2	34.0	33.8	33.6	33.3	33.5	33.9	34.3	34.8	35.2	30.3
92.5°	32.6	32.6	32.5	32.5	32.5	32.4	32.3	32.2	32.1	32.0	30.9
95°	62.5	62.9	63.4	63.8	64.2	64.5	64.5	64.5	64.5	64.5	64.0
97.5°	108.3	108.3	108.4	108.4	108.5	108.5	108.5	108.5	108.5	108.5	107.6
100°	138.0	138.3	138.6	138.8	139.0	139.1	139.1	139.1	139.1	139.1	138.5
102.5°	172.0	172.2	172.4	172.6	172.8	172.9	172.7	172.5	172.3	172.2	171.3
105°	223.7	223.7	223.7	223.7	223.7	223.5	223.1	222.6	222.2	221.7	221.3
107.5°	272.5	273.6	274.6	275.6	276.6	277.0	276.9	276.7	276.5	276.3	276.3
110°	310.4	311.0	311.7	312.5	313.1	313.5	313.5	313.5	313.5	313.5	313.5



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.7	347.2	347.7	348.2	348.6	349.2	349.7	350.2	350.8	351.3	351.5
115°	403.1	403.7	404.5	405.2	405.8	406.3	406.5	406.7	407.0	407.2	407.6
117.5°	457.0	457.6	458.3	459.0	459.6	460.2	460.8	461.3	461.8	462.4	463.6
120°	494.8	495.5	496.1	496.9	497.6	497.9	497.9	497.9	497.9	497.9	499.7
122.5°	531.9	532.4	532.9	533.4	533.9	534.4	534.9	535.4	536.0	536.5	537.9
125°	588.5	588.8	589.0	589.3	589.5	589.9	590.6	591.3	591.9	592.6	593.3
127.5°	640.2	640.9	641.6	642.3	643.0	643.8	644.6	645.4	646.2	647.0	647.8
130°	677.2	678.1	679.0	679.9	680.9	681.5	682.0	682.4	682.9	683.3	683.8
132.5°	712.8	713.5	714.2	714.9	715.6	716.4	717.4	718.4	719.4	720.3	720.2
135°	767.9	768.6	769.3	769.9	770.6	771.0	771.3	771.5	771.7	771.9	771.5
137.5°	817.9	818.8	819.7	820.6	821.5	822.0	822.2	822.4	822.6	822.7	822.2
140°	852.6	853.5	854.3	855.3	856.2	856.7	856.7	856.7	856.7	856.7	855.6
142.5°	884.0	884.9	885.9	886.8	887.7	888.0	887.8	887.7	887.5	887.3	886.5
145°	931.2	932.1	933.0	933.9	934.8	935.1	934.9	934.6	934.4	934.2	932.9
147.5°	973.3	974.2	975.0	975.9	976.7	976.9	976.4	975.9	975.4	974.9	974.0
150°	1000.8	1001.4	1002.1	1002.8	1003.4	1003.4	1002.8	1002.1	1001.4	1000.8	999.9
152.5°	1026.5	1027.4	1028.2	1029.1	1030.0	1030.0	1029.1	1028.2	1027.4	1026.5	1025.4
155°	1061.2	1061.9	1062.6	1063.2	1063.9	1063.7	1062.6	1061.5	1060.4	1059.1	1058.5
157.5°	1091.1	1092.1	1093.2	1094.3	1095.3	1095.1	1093.6	1092.1	1090.6	1089.0	1088.6
160°	1109.5	1110.4	1111.4	1112.3	1113.2	1113.0	1111.6	1110.2	1108.9	1107.5	1107.3
162.5°	1125.7	1126.8	1127.8	1128.9	1130.0	1129.7	1128.2	1126.7	1125.2	1123.7	1123.5
165°	1146.9	1148.0	1149.1	1150.2	1151.3	1151.1	1149.5	1148.0	1146.4	1144.9	1144.9
167.5°	1164.2	1165.4	1166.5	1167.7	1168.8	1168.6	1167.1	1165.5	1164.0	1162.4	1162.5
170°	1173.1	1174.4	1175.8	1177.1	1178.4	1178.3	1176.8	1175.2	1173.7	1172.0	1172.3
172.5°	1180.3	1181.6	1183.1	1184.4	1185.7	1185.6	1184.1	1182.5	1180.9	1179.3	1179.5
175°	1188.2	1189.5	1190.8	1192.2	1193.6	1193.5	1191.8	1190.3	1188.7	1187.2	1187.6
177.5°	1191.8	1192.9	1194.0	1195.1	1196.1	1196.1	1195.1	1194.0	1192.9	1191.8	1192.1
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	676.0	674.5	673.2	669.9	668.2	664.6	664.1	663.9	659.1	654.5	653.2
5°	699.2	695.5	690.0	683.6	676.9	670.0	665.5	661.8	652.6	643.9	638.8
7.5°	722.6	714.7	705.2	693.1	682.9	671.6	663.1	655.5	642.5	630.0	621.6
10°	740.0	727.2	714.6	697.8	684.7	671.9	659.9	649.6	635.0	618.4	606.7
12.5°	750.8	736.7	719.3	703.0	686.0	669.6	653.7	640.5	623.2	606.1	592.3
15°	765.5	750.3	729.2	705.8	684.1	662.7	644.4	627.8	605.4	584.9	567.9
17.5°	777.5	756.6	734.0	706.9	681.7	654.6	631.0	609.9	584.8	560.2	540.2
20°	781.3	760.6	734.5	707.4	677.6	645.7	620.3	597.3	570.5	543.6	520.7
22.5°	778.9	762.9	733.8	701.4	670.9	637.5	608.7	582.1	552.3	524.9	498.4
25°	762.8	757.2	729.7	694.4	659.5	620.8	587.4	558.4	524.4	495.0	466.2
27.5°	725.0	736.9	719.8	682.2	643.4	601.9	564.4	531.3	496.0	463.0	434.2
30°	688.6	715.9	708.6	673.7	630.4	589.6	547.5	512.9	475.3	441.3	412.9
32.5°	638.9	684.0	691.2	662.0	617.1	572.3	528.3	493.8	454.5	418.8	391.0
35°	559.7	627.1	658.1	639.5	594.6	546.1	500.8	460.6	421.1	385.9	358.3
37.5°	465.2	557.1	608.7	610.1	568.8	518.5	469.0	429.1	388.7	354.1	324.3
40°	403.9	503.5	570.8	585.6	550.8	496.4	446.4	405.8	366.4	332.3	298.2
42.5°	348.9	448.1	530.7	556.6	529.0	474.9	424.7	382.3	344.0	311.8	276.9
45°	282.2	368.9	459.9	506.2	490.9	440.9	387.9	347.5	311.5	283.8	250.2
47.5°	238.0	299.1	387.3	449.9	449.7	404.0	351.8	313.3	279.8	253.8	226.7
50°	212.9	266.1	340.6	411.7	417.7	379.4	329.8	291.5	260.3	233.1	211.3
52.5°	190.3	234.2	301.1	369.4	386.4	353.1	305.1	269.7	239.4	214.3	195.7
55°	160.8	194.8	245.7	309.4	335.2	311.7	269.0	236.0	211.5	190.4	174.3
57.5°	136.0	161.5	202.4	253.7	283.6	268.9	233.7	206.8	185.8	166.7	154.1
60°	120.5	141.3	175.9	218.8	251.9	241.6	211.5	186.5	168.6	152.1	140.2
62.5°	105.7	123.7	153.4	188.2	218.4	214.2	189.7	168.6	153.0	137.9	127.8
65°	85.1	98.2	121.4	148.7	173.0	175.0	157.3	143.1	129.2	117.2	108.3
67.5°	67.8	76.3	92.6	115.6	133.8	140.4	129.6	118.7	107.6	98.4	90.6
70°	57.2	64.0	75.9	94.5	111.3	118.2	111.9	103.4	93.8	86.2	79.6
72.5°	46.3	53.0	61.8	75.4	89.8	97.3	95.0	89.0	81.2	74.8	68.6
75°	34.8	37.0	42.9	52.1	63.3	69.8	71.3	68.2	61.9	57.2	53.4
77.5°	25.8	27.1	29.9	34.6	42.0	47.8	50.1	49.7	45.4	42.7	39.2
80°	20.6	21.3	22.7	24.7	30.3	36.1	37.7	37.7	34.6	33.5	30.1
82.5°	15.7	16.2	17.1	18.2	20.7	25.8	27.6	27.9	26.1	24.5	21.8
85°	9.0	8.7	9.2	9.9	10.3	11.7	14.4	14.9	14.4	12.6	11.9
87.5°	8.2	7.4	6.5	5.5	5.2	4.7	5.2	5.6	5.4	5.4	5.5
90°	25.4	20.5	15.6	11.7	9.1	6.4	3.7	1.0	3.7	6.4	9.1
92.5°	29.7	28.6	27.4	25.9	23.8	21.9	19.9	18.0	19.9	21.9	23.8
95°	63.6	63.1	62.7	61.4	59.1	56.9	54.6	52.4	54.6	56.9	59.1
97.5°	106.7	105.9	105.0	103.6	101.7	99.7	97.8	95.7	97.8	99.7	101.7
100°	137.7	137.0	136.4	135.1	133.4	131.6	129.8	127.9	129.8	131.6	133.4
102.5°	170.5	169.6	168.7	167.5	166.1	164.7	163.3	161.9	163.3	164.7	166.1
105°	220.9	220.4	219.9	219.3	218.7	218.0	217.3	216.7	217.3	218.0	218.7
107.5°	276.3	276.3	276.3	275.9	274.9	273.9	272.9	271.9	272.9	273.9	274.9
110°	313.5	313.5	313.5	312.8	311.4	310.0	308.7	307.4	308.7	310.0	311.4



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	351.6	351.8	352.0	351.4	350.1	348.8	347.4	346.1	347.4	348.8	350.1
115°	408.1	408.5	408.9	408.5	407.2	405.8	404.5	403.1	404.5	405.8	407.2
117.5°	464.8	466.2	467.4	467.2	465.3	463.5	461.7	460.0	461.7	463.5	465.3
120°	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9	499.7	501.4	503.2
122.5°	539.1	540.3	541.6	541.1	539.0	536.8	534.6	532.5	534.6	536.8	539.0
125°	593.9	594.6	595.3	594.6	592.6	590.6	588.5	586.5	588.5	590.6	592.6
127.5°	648.6	649.4	650.3	649.3	646.8	644.3	641.7	639.1	641.7	644.3	646.8
130°	684.2	684.6	685.1	683.9	681.0	678.0	675.1	672.2	675.1	678.0	681.0
132.5°	720.2	720.1	720.0	718.8	716.4	714.1	711.7	709.3	711.7	714.1	716.4
135°	771.0	770.6	770.2	768.7	766.3	763.8	761.3	758.9	761.3	763.8	766.3
137.5°	821.6	821.0	820.4	819.1	817.1	815.1	813.0	811.1	813.0	815.1	817.1
140°	854.3	853.2	852.1	850.6	848.6	846.6	844.6	842.5	844.6	846.6	848.6
142.5°	885.8	884.9	884.2	882.8	880.8	878.8	876.8	874.7	876.8	878.8	880.8
145°	931.5	930.2	928.9	927.4	925.8	924.2	922.7	921.1	922.7	924.2	925.8
147.5°	973.1	972.3	971.4	970.0	968.1	966.2	964.3	962.4	964.3	966.2	968.1
150°	999.0	998.0	997.1	996.0	994.7	993.3	992.0	990.7	992.0	993.3	994.7
152.5°	1024.4	1023.3	1022.3	1021.1	1019.7	1018.3	1017.0	1015.6	1017.0	1018.3	1019.7
155°	1057.8	1057.2	1056.5	1055.8	1055.2	1054.5	1053.8	1053.2	1053.8	1054.5	1055.2
157.5°	1088.2	1087.8	1087.4	1087.0	1086.5	1086.1	1085.6	1085.2	1085.6	1086.1	1086.5
160°	1107.1	1106.9	1106.7	1106.3	1105.9	1105.4	1105.0	1104.6	1105.0	1105.4	1105.9
162.5°	1123.3	1123.1	1122.8	1122.7	1122.6	1122.5	1122.4	1122.3	1122.4	1122.5	1122.6
165°	1144.9	1144.9	1144.9	1145.0	1145.2	1145.4	1145.7	1145.9	1145.7	1145.4	1145.2
167.5°	1162.5	1162.6	1162.6	1163.0	1163.6	1164.3	1165.0	1165.6	1165.0	1164.3	1163.6
170°	1172.6	1172.8	1173.0	1173.4	1174.1	1174.8	1175.4	1176.1	1175.4	1174.8	1174.1
172.5°	1179.7	1180.0	1180.2	1180.6	1181.3	1182.0	1182.7	1183.4	1182.7	1182.0	1181.3
175°	1188.1	1188.5	1189.0	1189.5	1190.2	1190.8	1191.5	1192.2	1191.5	1190.8	1190.2
177.5°	1192.5	1192.9	1193.3	1193.7	1194.3	1194.8	1195.3	1195.9	1195.3	1194.8	1194.3
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	650.9	649.5	647.1	643.5	641.3	637.4	634.9	636.3	636.7	636.3	636.0
5°	633.4	628.5	621.9	615.4	609.5	603.1	599.4	597.8	594.6	592.8	591.8
7.5°	612.2	603.9	594.5	583.3	573.8	563.8	558.8	556.2	549.7	546.1	543.0
10°	596.4	583.3	573.9	559.3	550.3	537.2	528.3	528.6	519.6	514.5	510.9
12.5°	579.0	564.6	549.0	535.7	523.3	512.8	502.0	497.7	488.2	483.3	473.4
15°	550.1	533.3	516.8	499.0	486.4	470.0	454.4	435.4	420.0	406.7	403.0
17.5°	518.6	497.8	481.2	460.2	438.6	411.2	393.1	382.0	372.8	365.8	360.5
20°	496.9	475.7	458.1	426.5	397.3	378.7	365.5	356.9	347.3	339.7	335.6
22.5°	474.1	452.1	428.0	392.6	369.9	355.1	343.3	333.5	326.9	321.0	317.2
25°	441.8	417.7	378.0	353.8	335.4	319.7	311.5	305.6	298.7	290.6	287.0
27.5°	407.7	369.4	340.8	322.8	305.3	295.2	287.7	278.8	272.7	269.0	265.2
30°	382.1	343.9	321.6	301.8	289.5	278.2	269.5	264.5	258.5	252.4	249.8
32.5°	353.8	323.2	301.7	285.4	272.8	263.2	256.3	248.1	243.9	240.0	234.8
35°	318.4	295.2	275.7	262.5	250.4	242.7	234.7	229.8	222.1	218.8	216.8
37.5°	288.5	268.4	253.9	239.8	230.4	221.8	216.8	209.1	205.8	201.3	196.9
40°	271.6	251.9	237.9	226.4	215.8	209.4	203.3	197.0	192.0	190.0	184.7
42.5°	254.4	238.3	224.3	211.8	204.7	197.8	190.1	185.5	180.3	176.9	173.7
45°	230.6	216.3	204.4	194.1	186.2	179.2	174.1	166.5	163.6	156.9	154.1
47.5°	209.6	196.4	185.0	175.2	167.6	163.0	155.6	149.7	144.9	140.8	137.2
50°	194.8	183.7	172.7	164.0	157.1	150.5	142.9	140.0	132.6	130.5	128.5
52.5°	181.2	170.7	160.7	152.1	145.2	138.8	132.1	128.2	123.2	121.2	119.7
55°	162.2	152.1	142.5	134.9	128.1	121.4	117.2	112.4	110.1	108.5	106.6
57.5°	143.1	134.0	126.6	119.0	112.0	106.7	102.0	99.1	96.7	94.6	92.4
60°	131.0	122.3	115.6	108.5	101.4	97.0	93.4	89.9	87.2	83.9	83.0
62.5°	118.2	110.5	104.4	97.5	91.3	87.4	83.8	80.6	77.3	72.6	71.3
65°	100.5	94.5	88.1	82.3	76.9	72.9	67.9	64.2	62.8	62.4	62.2
67.5°	84.5	78.9	73.3	67.5	62.5	58.9	56.2	55.7	54.7	54.5	53.8
70°	73.8	68.6	63.1	57.6	52.7	52.1	51.2	50.2	49.1	48.7	48.2
72.5°	64.3	58.9	53.3	49.0	46.9	46.0	45.1	44.1	43.4	42.9	42.7
75°	49.3	44.2	40.6	39.0	37.9	37.2	35.7	35.1	34.6	33.9	33.7
77.5°	35.5	32.6	31.0	30.0	28.8	28.1	27.3	26.6	26.1	26.0	25.5
80°	27.1	25.7	24.5	23.1	22.7	21.8	21.6	20.9	21.1	20.4	20.4
82.5°	21.0	19.3	18.3	17.7	17.2	16.5	16.3	16.0	16.0	15.5	15.5
85°	10.8	10.3	9.9	9.4	9.4	8.7	9.0	8.7	8.7	8.3	8.1
87.5°	5.9	6.5	7.1	8.0	9.0	9.8	9.7	9.5	9.4	9.3	9.1
90°	11.7	15.6	20.5	25.4	30.3	35.2	34.8	34.3	33.9	33.5	33.3
92.5°	25.9	27.4	28.6	29.7	30.9	32.0	32.1	32.2	32.3	32.4	32.5
95°	61.4	62.7	63.1	63.6	64.0	64.5	64.5	64.5	64.5	64.5	64.2
97.5°	103.6	105.0	105.9	106.7	107.6	108.5	108.5	108.5	108.5	108.5	108.5
100°	135.1	136.4	137.0	137.7	138.5	139.1	139.1	139.1	139.1	139.1	139.0
102.5°	167.5	168.7	169.6	170.5	171.3	172.2	172.3	172.5	172.7	172.9	172.8
105°	219.3	219.9	220.4	220.9	221.3	221.7	222.2	222.6	223.1	223.5	223.7
107.5°	275.9	276.3	276.3	276.3	276.3	276.3	276.5	276.7	276.9	277.0	276.6
110°	312.8	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.1



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	351.4	352.0	351.8	351.6	351.5	351.3	350.8	350.2	349.7	349.2	348.6
115°	408.5	408.9	408.5	408.1	407.6	407.2	407.0	406.7	406.5	406.3	405.8
117.5°	467.2	467.4	466.2	464.8	463.6	462.4	461.8	461.3	460.8	460.2	459.6
120°	505.0	505.0	503.2	501.4	499.7	497.9	497.9	497.9	497.9	497.9	497.6
122.5°	541.1	541.6	540.3	539.1	537.9	536.5	536.0	535.4	534.9	534.4	533.9
125°	594.6	595.3	594.6	593.9	593.3	592.6	591.9	591.3	590.6	589.9	589.5
127.5°	649.3	650.3	649.4	648.6	647.8	647.0	646.2	645.4	644.6	643.8	643.0
130°	683.9	685.1	684.6	684.2	683.8	683.3	682.9	682.4	682.0	681.5	680.9
132.5°	718.8	720.0	720.1	720.2	720.2	720.3	719.4	718.4	717.4	716.4	715.6
135°	768.7	770.2	770.6	771.0	771.5	771.9	771.7	771.5	771.3	771.0	770.6
137.5°	819.1	820.4	821.0	821.6	822.2	822.7	822.6	822.4	822.2	822.0	821.5
140°	850.6	852.1	853.2	854.3	855.6	856.7	856.7	856.7	856.7	856.7	856.2
142.5°	882.8	884.2	884.9	885.8	886.5	887.3	887.5	887.7	887.8	888.0	887.7
145°	927.4	928.9	930.2	931.5	932.9	934.2	934.4	934.6	934.9	935.1	934.8
147.5°	970.0	971.4	972.3	973.1	974.0	974.9	975.4	975.9	976.4	976.9	976.7
150°	996.0	997.1	998.0	999.0	999.9	1000.8	1001.4	1002.1	1002.8	1003.4	1003.4
152.5°	1021.1	1022.3	1023.3	1024.4	1025.4	1026.5	1027.4	1028.2	1029.1	1030.0	1030.0
155°	1055.8	1056.5	1057.2	1057.8	1058.5	1059.1	1060.4	1061.5	1062.6	1063.7	1063.9
157.5°	1087.0	1087.4	1087.8	1088.2	1088.6	1089.0	1090.6	1092.1	1093.6	1095.1	1095.3
160°	1106.3	1106.7	1106.9	1107.1	1107.3	1107.5	1108.9	1110.2	1111.6	1113.0	1113.2
162.5°	1122.7	1122.8	1123.1	1123.3	1123.5	1123.7	1125.2	1126.7	1128.2	1129.7	1130.0
165°	1145.0	1144.9	1144.9	1144.9	1144.9	1144.9	1146.4	1148.0	1149.5	1151.1	1151.3
167.5°	1163.0	1162.6	1162.6	1162.5	1162.5	1162.4	1164.0	1165.5	1167.1	1168.6	1168.8
170°	1173.4	1173.0	1172.8	1172.6	1172.3	1172.0	1173.7	1175.2	1176.8	1178.3	1178.4
172.5°	1180.6	1180.2	1180.0	1179.7	1179.5	1179.3	1180.9	1182.5	1184.1	1185.6	1185.7
175°	1189.5	1189.0	1188.5	1188.1	1187.6	1187.2	1188.7	1190.3	1191.8	1193.5	1193.6
177.5°	1193.7	1193.3	1192.9	1192.5	1192.1	1191.8	1192.9	1194.0	1195.1	1196.1	1196.1
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.0	634.3	633.8	634.1	633.8	634.3	634.0	636.0	636.3	636.7	636.3
5°	590.7	587.9	587.4	586.8	587.4	587.9	590.7	591.8	592.8	594.6	597.8
7.5°	539.1	538.7	537.5	535.8	537.5	538.7	539.1	543.0	546.1	549.7	556.2
10°	505.8	504.6	504.4	502.8	504.4	504.6	505.8	510.9	514.5	519.6	528.6
12.5°	466.9	459.5	458.8	454.7	458.8	459.5	466.9	473.4	483.3	488.2	497.7
15°	397.6	396.2	391.5	388.6	391.5	396.2	397.6	403.0	406.7	420.0	435.4
17.5°	357.9	353.4	351.9	351.3	351.9	353.4	357.9	360.5	365.8	372.8	382.0
20°	332.3	328.3	327.6	327.1	327.6	328.3	332.3	335.6	339.7	347.3	356.9
22.5°	314.8	310.4	308.7	307.3	308.7	310.4	314.8	317.2	321.0	326.9	333.5
25°	284.7	283.1	282.2	281.7	282.2	283.1	284.7	287.0	290.6	298.7	305.6
27.5°	261.2	257.6	256.9	255.7	256.9	257.6	261.2	265.2	269.0	272.7	278.8
30°	247.7	246.6	245.0	243.6	245.0	246.6	247.7	249.8	252.4	258.5	264.5
32.5°	232.0	231.0	229.5	228.9	229.5	231.0	232.0	234.8	240.0	243.9	248.1
35°	214.5	211.3	209.8	207.8	209.8	211.3	214.5	216.8	218.8	222.1	229.8
37.5°	196.0	194.3	192.4	193.1	192.4	194.3	196.0	196.9	201.3	205.8	209.1
40°	181.7	180.6	180.1	179.9	180.1	180.6	181.7	184.7	190.0	192.0	197.0
42.5°	170.3	167.1	165.9	165.9	165.9	167.1	170.3	173.7	176.9	180.3	185.5
45°	153.0	150.1	147.9	148.1	147.9	150.1	153.0	154.1	156.9	163.6	166.5
47.5°	135.3	135.2	133.9	134.3	133.9	135.2	135.3	137.2	140.8	144.9	149.7
50°	126.8	125.5	124.5	124.8	124.5	125.5	126.8	128.5	130.5	132.6	140.0
52.5°	118.8	117.5	116.8	117.9	116.8	117.5	118.8	119.7	121.2	123.2	128.2
55°	105.5	104.1	103.9	103.7	103.9	104.1	105.5	106.6	108.5	110.1	112.4
57.5°	90.7	89.8	88.4	87.9	88.4	89.8	90.7	92.4	94.6	96.7	99.1
60°	80.1	78.3	75.9	75.7	75.9	78.3	80.1	83.0	83.9	87.2	89.9
62.5°	70.3	70.0	69.5	69.5	69.5	70.0	70.3	71.3	72.6	77.3	80.6
65°	61.7	61.5	61.7	61.9	61.7	61.5	61.7	62.2	62.4	62.8	64.2
67.5°	53.7	53.3	52.9	53.1	52.9	53.3	53.7	53.8	54.5	54.7	55.7
70°	47.7	47.5	47.3	47.3	47.3	47.5	47.7	48.2	48.7	49.1	50.2
72.5°	41.8	41.8	41.6	41.4	41.6	41.8	41.8	42.7	42.9	43.4	44.1
75°	33.5	33.0	33.0	33.0	33.0	33.0	33.5	33.7	33.9	34.6	35.1
77.5°	25.5	25.2	25.0	24.8	25.0	25.2	25.5	25.5	26.0	26.1	26.6
80°	20.2	20.0	19.7	19.7	19.7	20.0	20.2	20.4	20.4	21.1	20.9
82.5°	15.5	15.1	15.1	14.9	15.1	15.1	15.5	15.5	15.5	16.0	16.0
85°	8.3	8.5	8.3	8.7	8.3	8.5	8.3	8.1	8.3	8.7	8.7
87.5°	9.1	9.0	9.2	9.1	9.2	9.0	9.1	9.1	9.3	9.4	9.5
90°	33.6	33.8	34.0	34.2	34.0	33.8	33.6	33.3	33.5	33.9	34.3
92.5°	32.5	32.5	32.6	32.6	32.6	32.5	32.5	32.5	32.4	32.3	32.2
95°	63.8	63.4	62.9	62.5	62.9	63.4	63.8	64.2	64.5	64.5	64.5
97.5°	108.4	108.4	108.3	108.3	108.3	108.4	108.4	108.5	108.5	108.5	108.5
100°	138.8	138.6	138.3	138.0	138.3	138.6	138.8	139.0	139.1	139.1	139.1
102.5°	172.6	172.4	172.2	172.0	172.2	172.4	172.6	172.8	172.9	172.7	172.5
105°	223.7	223.7	223.7	223.7	223.7	223.7	223.7	223.7	223.5	223.1	222.6
107.5°	275.6	274.6	273.6	272.5	273.6	274.6	275.6	276.6	277.0	276.9	276.7
110°	312.5	311.7	311.0	310.4	311.0	311.7	312.5	313.1	313.5	313.5	313.5



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	348.2	347.7	347.2	346.7	347.2	347.7	348.2	348.6	349.2	349.7	350.2
115°	405.2	404.5	403.7	403.1	403.7	404.5	405.2	405.8	406.3	406.5	406.7
117.5°	459.0	458.3	457.6	457.0	457.6	458.3	459.0	459.6	460.2	460.8	461.3
120°	496.9	496.1	495.5	494.8	495.5	496.1	496.9	497.6	497.9	497.9	497.9
122.5°	533.4	532.9	532.4	531.9	532.4	532.9	533.4	533.9	534.4	534.9	535.4
125°	589.3	589.0	588.8	588.5	588.8	589.0	589.3	589.5	589.9	590.6	591.3
127.5°	642.3	641.6	640.9	640.2	640.9	641.6	642.3	643.0	643.8	644.6	645.4
130°	679.9	679.0	678.1	677.2	678.1	679.0	679.9	680.9	681.5	682.0	682.4
132.5°	714.9	714.2	713.5	712.8	713.5	714.2	714.9	715.6	716.4	717.4	718.4
135°	769.9	769.3	768.6	767.9	768.6	769.3	769.9	770.6	771.0	771.3	771.5
137.5°	820.6	819.7	818.8	817.9	818.8	819.7	820.6	821.5	822.0	822.2	822.4
140°	855.3	854.3	853.5	852.6	853.5	854.3	855.3	856.2	856.7	856.7	856.7
142.5°	886.8	885.9	884.9	884.0	884.9	885.9	886.8	887.7	888.0	887.8	887.7
145°	933.9	933.0	932.1	931.2	932.1	933.0	933.9	934.8	935.1	934.9	934.6
147.5°	975.9	975.0	974.2	973.3	974.2	975.0	975.9	976.7	976.9	976.4	975.9
150°	1002.8	1002.1	1001.4	1000.8	1001.4	1002.1	1002.8	1003.4	1003.4	1002.8	1002.1
152.5°	1029.1	1028.2	1027.4	1026.5	1027.4	1028.2	1029.1	1030.0	1030.0	1029.1	1028.2
155°	1063.2	1062.6	1061.9	1061.2	1061.9	1062.6	1063.2	1063.9	1063.7	1062.6	1061.5
157.5°	1094.3	1093.2	1092.1	1091.1	1092.1	1093.2	1094.3	1095.3	1095.1	1093.6	1092.1
160°	1112.3	1111.4	1110.4	1109.5	1110.4	1111.4	1112.3	1113.2	1113.0	1111.6	1110.2
162.5°	1128.9	1127.8	1126.8	1125.7	1126.8	1127.8	1128.9	1130.0	1129.7	1128.2	1126.7
165°	1150.2	1149.1	1148.0	1146.9	1148.0	1149.1	1150.2	1151.3	1151.1	1149.5	1148.0
167.5°	1167.7	1166.5	1165.4	1164.2	1165.4	1166.5	1167.7	1168.8	1168.6	1167.1	1165.5
170°	1177.1	1175.8	1174.4	1173.1	1174.4	1175.8	1177.1	1178.4	1178.3	1176.8	1175.2
172.5°	1184.4	1183.1	1181.6	1180.3	1181.6	1183.1	1184.4	1185.7	1185.6	1184.1	1182.5
175°	1192.2	1190.8	1189.5	1188.2	1189.5	1190.8	1192.2	1193.6	1193.5	1191.8	1190.3
177.5°	1195.1	1194.0	1192.9	1191.8	1192.9	1194.0	1195.1	1196.1	1196.1	1195.1	1194.0
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.9	637.4	641.3	643.5	647.1	649.5	650.9	653.2	654.5	659.1	663.9
5°	599.4	603.1	609.5	615.4	621.9	628.5	633.4	638.8	643.9	652.6	661.8
7.5°	558.8	563.8	573.8	583.3	594.5	603.9	612.2	621.6	630.0	642.5	655.5
10°	528.3	537.2	550.3	559.3	573.9	583.3	596.4	606.7	618.4	635.0	649.6
12.5°	502.0	512.8	523.3	535.7	549.0	564.6	579.0	592.3	606.1	623.2	640.5
15°	454.4	470.0	486.4	499.0	516.8	533.3	550.1	567.9	584.9	605.4	627.8
17.5°	393.1	411.2	438.6	460.2	481.2	497.8	518.6	540.2	560.2	584.8	609.9
20°	365.5	378.7	397.3	426.5	458.1	475.7	496.9	520.7	543.6	570.5	597.3
22.5°	343.3	355.1	369.9	392.6	428.0	452.1	474.1	498.4	524.9	552.3	582.1
25°	311.5	319.7	335.4	353.8	378.0	417.7	441.8	466.2	495.0	524.4	558.4
27.5°	287.7	295.2	305.3	322.8	340.8	369.4	407.7	434.2	463.0	496.0	531.3
30°	269.5	278.2	289.5	301.8	321.6	343.9	382.1	412.9	441.3	475.3	512.9
32.5°	256.3	263.2	272.8	285.4	301.7	323.2	353.8	391.0	418.8	454.5	493.8
35°	234.7	242.7	250.4	262.5	275.7	295.2	318.4	358.3	385.9	421.1	460.6
37.5°	216.8	221.8	230.4	239.8	253.9	268.4	288.5	324.3	354.1	388.7	429.1
40°	203.3	209.4	215.8	226.4	237.9	251.9	271.6	298.2	332.3	366.4	405.8
42.5°	190.1	197.8	204.7	211.8	224.3	238.3	254.4	276.9	311.8	344.0	382.3
45°	174.1	179.2	186.2	194.1	204.4	216.3	230.6	250.2	283.8	311.5	347.5
47.5°	155.6	163.0	167.6	175.2	185.0	196.4	209.6	226.7	253.8	279.8	313.3
50°	142.9	150.5	157.1	164.0	172.7	183.7	194.8	211.3	233.1	260.3	291.5
52.5°	132.1	138.8	145.2	152.1	160.7	170.7	181.2	195.7	214.3	239.4	269.7
55°	117.2	121.4	128.1	134.9	142.5	152.1	162.2	174.3	190.4	211.5	236.0
57.5°	102.0	106.7	112.0	119.0	126.6	134.0	143.1	154.1	166.7	185.8	206.8
60°	93.4	97.0	101.4	108.5	115.6	122.3	131.0	140.2	152.1	168.6	186.5
62.5°	83.8	87.4	91.3	97.5	104.4	110.5	118.2	127.8	137.9	153.0	168.6
65°	67.9	72.9	76.9	82.3	88.1	94.5	100.5	108.3	117.2	129.2	143.1
67.5°	56.2	58.9	62.5	67.5	73.3	78.9	84.5	90.6	98.4	107.6	118.7
70°	51.2	52.1	52.7	57.6	63.1	68.6	73.8	79.6	86.2	93.8	103.4
72.5°	45.1	46.0	46.9	49.0	53.3	58.9	64.3	68.6	74.8	81.2	89.0
75°	35.7	37.2	37.9	39.0	40.6	44.2	49.3	53.4	57.2	61.9	68.2
77.5°	27.3	28.1	28.8	30.0	31.0	32.6	35.5	39.2	42.7	45.4	49.7
80°	21.6	21.8	22.7	23.1	24.5	25.7	27.1	30.1	33.5	34.6	37.7
82.5°	16.3	16.5	17.2	17.7	18.3	19.3	21.0	21.8	24.5	26.1	27.9
85°	9.0	8.7	9.4	9.4	9.9	10.3	10.8	11.9	12.6	14.4	14.9
87.5°	9.7	9.8	9.0	8.0	7.1	6.5	5.9	5.5	5.4	5.4	5.6
90°	34.8	35.2	30.3	25.4	20.5	15.6	11.7	9.1	6.4	3.7	1.0
92.5°	32.1	32.0	30.9	29.7	28.6	27.4	25.9	23.8	21.9	19.9	18.0
95°	64.5	64.5	64.0	63.6	63.1	62.7	61.4	59.1	56.9	54.6	52.4
97.5°	108.5	108.5	107.6	106.7	105.9	105.0	103.6	101.7	99.7	97.8	95.7
100°	139.1	139.1	138.5	137.7	137.0	136.4	135.1	133.4	131.6	129.8	127.9
102.5°	172.3	172.2	171.3	170.5	169.6	168.7	167.5	166.1	164.7	163.3	161.9
105°	222.2	221.7	221.3	220.9	220.4	219.9	219.3	218.7	218.0	217.3	216.7
107.5°	276.5	276.3	276.3	276.3	276.3	276.3	275.9	274.9	273.9	272.9	271.9
110°	313.5	313.5	313.5	313.5	313.5	313.5	312.8	311.4	310.0	308.7	307.4



TEST NUMBER: P331634-840
 CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	350.8	351.3	351.5	351.6	351.8	352.0	351.4	350.1	348.8	347.4	346.1
115°	407.0	407.2	407.6	408.1	408.5	408.9	408.5	407.2	405.8	404.5	403.1
117.5°	461.8	462.4	463.6	464.8	466.2	467.4	467.2	465.3	463.5	461.7	460.0
120°	497.9	497.9	499.7	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9
122.5°	536.0	536.5	537.9	539.1	540.3	541.6	541.1	539.0	536.8	534.6	532.5
125°	591.9	592.6	593.3	593.9	594.6	595.3	594.6	592.6	590.6	588.5	586.5
127.5°	646.2	647.0	647.8	648.6	649.4	650.3	649.3	646.8	644.3	641.7	639.1
130°	682.9	683.3	683.8	684.2	684.6	685.1	683.9	681.0	678.0	675.1	672.2
132.5°	719.4	720.3	720.2	720.2	720.1	720.0	718.8	716.4	714.1	711.7	709.3
135°	771.7	771.9	771.5	771.0	770.6	770.2	768.7	766.3	763.8	761.3	758.9
137.5°	822.6	822.7	822.2	821.6	821.0	820.4	819.1	817.1	815.1	813.0	811.1
140°	856.7	856.7	855.6	854.3	853.2	852.1	850.6	848.6	846.6	844.6	842.5
142.5°	887.5	887.3	886.5	885.8	884.9	884.2	882.8	880.8	878.8	876.8	874.7
145°	934.4	934.2	932.9	931.5	930.2	928.9	927.4	925.8	924.2	922.7	921.1
147.5°	975.4	974.9	974.0	973.1	972.3	971.4	970.0	968.1	966.2	964.3	962.4
150°	1001.4	1000.8	999.9	999.0	998.0	997.1	996.0	994.7	993.3	992.0	990.7
152.5°	1027.4	1026.5	1025.4	1024.4	1023.3	1022.3	1021.1	1019.7	1018.3	1017.0	1015.6
155°	1060.4	1059.1	1058.5	1057.8	1057.2	1056.5	1055.8	1055.2	1054.5	1053.8	1053.2
157.5°	1090.6	1089.0	1088.6	1088.2	1087.8	1087.4	1087.0	1086.5	1086.1	1085.6	1085.2
160°	1108.9	1107.5	1107.3	1107.1	1106.9	1106.7	1106.3	1105.9	1105.4	1105.0	1104.6
162.5°	1125.2	1123.7	1123.5	1123.3	1123.1	1122.8	1122.7	1122.6	1122.5	1122.4	1122.3
165°	1146.4	1144.9	1144.9	1144.9	1144.9	1144.9	1145.0	1145.2	1145.4	1145.7	1145.9
167.5°	1164.0	1162.4	1162.5	1162.5	1162.6	1162.6	1163.0	1163.6	1164.3	1165.0	1165.6
170°	1173.7	1172.0	1172.3	1172.6	1172.8	1173.0	1173.4	1174.1	1174.8	1175.4	1176.1
172.5°	1180.9	1179.3	1179.5	1179.7	1180.0	1180.2	1180.6	1181.3	1182.0	1182.7	1183.4
175°	1188.7	1187.2	1187.6	1188.1	1188.5	1189.0	1189.5	1190.2	1190.8	1191.5	1192.2
177.5°	1192.9	1191.8	1192.1	1192.5	1192.9	1193.3	1193.7	1194.3	1194.8	1195.3	1195.9
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	664.1	664.6	668.2	669.9	673.2	674.5	676.0	675.6	675.6	676.3	681.5
5°	665.5	670.0	676.9	683.6	690.0	695.5	699.2	702.9	704.3	710.8	716.8
7.5°	663.1	671.6	682.9	693.1	705.2	714.7	722.6	729.7	734.6	744.3	754.2
10°	659.9	671.9	684.7	697.8	714.6	727.2	740.0	749.9	753.1	767.5	775.8
12.5°	653.7	669.6	686.0	703.0	719.3	736.7	750.8	760.7	772.0	785.0	800.2
15°	644.4	662.7	684.1	705.8	729.2	750.3	765.5	782.6	795.1	809.3	822.6
17.5°	631.0	654.6	681.7	706.9	734.0	756.6	777.5	794.0	802.6	810.8	812.7
20°	620.3	645.7	677.6	707.4	734.5	760.6	781.3	795.1	797.4	797.6	785.5
22.5°	608.7	637.5	670.9	701.4	733.8	762.9	778.9	784.8	775.7	760.1	736.6
25°	587.4	620.8	659.5	694.4	729.7	757.2	762.8	752.5	720.5	687.0	644.6
27.5°	564.4	601.9	643.4	682.2	719.8	736.9	725.0	687.7	630.4	580.4	519.9
30°	547.5	589.6	630.4	673.7	708.6	715.9	688.6	633.8	566.8	491.6	431.2
32.5°	528.3	572.3	617.1	662.0	691.2	684.0	638.9	571.4	492.9	418.9	361.9
35°	500.8	546.1	594.6	639.5	658.1	627.1	559.7	471.8	391.5	322.6	283.3
37.5°	469.0	518.5	568.8	610.1	608.7	557.1	465.2	374.6	307.1	266.2	238.3
40°	446.4	496.4	550.8	585.6	570.8	503.5	403.9	318.4	269.0	236.5	216.1
42.5°	424.7	474.9	529.0	556.6	530.7	448.1	348.9	281.9	241.2	215.8	199.2
45°	387.9	440.9	490.9	506.2	459.9	368.9	282.2	233.5	206.4	187.6	176.2
47.5°	351.8	404.0	449.7	449.9	387.3	299.1	238.0	202.1	178.9	164.4	156.1
50°	329.8	379.4	417.7	411.7	340.6	266.1	212.9	181.9	162.7	151.4	142.7
52.5°	305.1	353.1	386.4	369.4	301.1	234.2	190.3	164.3	148.3	138.6	130.8
55°	269.0	311.7	335.2	309.4	245.7	194.8	160.8	140.4	128.5	120.2	113.5
57.5°	233.7	268.9	283.6	253.7	202.4	161.5	136.0	120.7	108.9	102.9	99.5
60°	211.5	241.6	251.9	218.8	175.9	141.3	120.5	106.2	97.5	93.6	90.2
62.5°	189.7	214.2	218.4	188.2	153.4	123.7	105.7	93.7	88.0	84.2	81.0
65°	157.3	175.0	173.0	148.7	121.4	98.2	85.1	77.8	73.4	68.2	62.4
67.5°	129.6	140.4	133.8	115.6	92.6	76.3	67.8	62.2	56.8	51.8	50.5
70°	111.9	118.2	111.3	94.5	75.9	64.0	57.2	50.5	47.3	46.2	44.0
72.5°	95.0	97.3	89.8	75.4	61.8	53.0	46.3	42.6	40.8	39.9	38.6
75°	71.3	69.8	63.3	52.1	42.9	37.0	34.8	33.5	32.3	31.4	30.7
77.5°	50.1	47.8	42.0	34.6	29.9	27.1	25.8	25.0	24.5	24.0	23.3
80°	37.7	36.1	30.3	24.7	22.7	21.3	20.6	19.7	19.7	19.3	18.6
82.5°	27.6	25.8	20.7	18.2	17.1	16.2	15.7	15.1	14.9	15.0	14.5
85°	14.4	11.7	10.3	9.9	9.2	8.7	9.0	8.5	8.5	8.5	8.3
87.5°	5.2	4.7	5.2	5.5	6.5	7.4	8.2	9.2	10.4	10.1	10.2
90°	3.7	6.4	9.1	11.7	15.6	20.5	25.4	30.3	35.2	34.8	34.3
92.5°	19.9	21.9	23.8	25.9	27.4	28.6	29.7	30.9	32.0	32.1	32.2
95°	54.6	56.9	59.1	61.4	62.7	63.1	63.6	64.0	64.5	64.5	64.5
97.5°	97.8	99.7	101.7	103.6	105.0	105.9	106.7	107.6	108.5	108.5	108.5
100°	129.8	131.6	133.4	135.1	136.4	137.0	137.7	138.5	139.1	139.1	139.1
102.5°	163.3	164.7	166.1	167.5	168.7	169.6	170.5	171.3	172.2	172.3	172.5
105°	217.3	218.0	218.7	219.3	219.9	220.4	220.9	221.3	221.7	222.2	222.6
107.5°	272.9	273.9	274.9	275.9	276.3	276.3	276.3	276.3	276.3	276.5	276.7
110°	308.7	310.0	311.4	312.8	313.5	313.5	313.5	313.5	313.5	313.5	313.5



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	347.4	348.8	350.1	351.4	352.0	351.8	351.6	351.5	351.3	350.8	350.2
115°	404.5	405.8	407.2	408.5	408.9	408.5	408.1	407.6	407.2	407.0	406.7
117.5°	461.7	463.5	465.3	467.2	467.4	466.2	464.8	463.6	462.4	461.8	461.3
120°	499.7	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9	497.9	497.9
122.5°	534.6	536.8	539.0	541.1	541.6	540.3	539.1	537.9	536.5	536.0	535.4
125°	588.5	590.6	592.6	594.6	595.3	594.6	593.9	593.3	592.6	591.9	591.3
127.5°	641.7	644.3	646.8	649.3	650.3	649.4	648.6	647.8	647.0	646.2	645.4
130°	675.1	678.0	681.0	683.9	685.1	684.6	684.2	683.8	683.3	682.9	682.4
132.5°	711.7	714.1	716.4	718.8	720.0	720.1	720.2	720.2	720.3	719.4	718.4
135°	761.3	763.8	766.3	768.7	770.2	770.6	771.0	771.5	771.9	771.7	771.5
137.5°	813.0	815.1	817.1	819.1	820.4	821.0	821.6	822.2	822.7	822.6	822.4
140°	844.6	846.6	848.6	850.6	852.1	853.2	854.3	855.6	856.7	856.7	856.7
142.5°	876.8	878.8	880.8	882.8	884.2	884.9	885.8	886.5	887.3	887.5	887.7
145°	922.7	924.2	925.8	927.4	928.9	930.2	931.5	932.9	934.2	934.4	934.6
147.5°	964.3	966.2	968.1	970.0	971.4	972.3	973.1	974.0	974.9	975.4	975.9
150°	992.0	993.3	994.7	996.0	997.1	998.0	999.0	999.9	1000.8	1001.4	1002.1
152.5°	1017.0	1018.3	1019.7	1021.1	1022.3	1023.3	1024.4	1025.4	1026.5	1027.4	1028.2
155°	1053.8	1054.5	1055.2	1055.8	1056.5	1057.2	1057.8	1058.5	1059.1	1060.4	1061.5
157.5°	1085.6	1086.1	1086.5	1087.0	1087.4	1087.8	1088.2	1088.6	1089.0	1090.6	1092.1
160°	1105.0	1105.4	1105.9	1106.3	1106.7	1106.9	1107.1	1107.3	1107.5	1108.9	1110.2
162.5°	1122.4	1122.5	1122.6	1122.7	1122.8	1123.1	1123.3	1123.5	1123.7	1125.2	1126.7
165°	1145.7	1145.4	1145.2	1145.0	1144.9	1144.9	1144.9	1144.9	1144.9	1146.4	1148.0
167.5°	1165.0	1164.3	1163.6	1163.0	1162.6	1162.6	1162.5	1162.5	1162.4	1164.0	1165.5
170°	1175.4	1174.8	1174.1	1173.4	1173.0	1172.8	1172.6	1172.3	1172.0	1173.7	1175.2
172.5°	1182.7	1182.0	1181.3	1180.6	1180.2	1180.0	1179.7	1179.5	1179.3	1180.9	1182.5
175°	1191.5	1190.8	1190.2	1189.5	1189.0	1188.5	1188.1	1187.6	1187.2	1188.7	1190.3
177.5°	1195.3	1194.8	1194.3	1193.7	1193.3	1192.9	1192.5	1192.1	1191.8	1192.9	1194.0
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	683.3	685.7	686.8	686.8	688.1	687.5	687.0
5°	722.6	726.9	727.9	732.0	735.0	734.1	734.5
7.5°	761.6	768.6	775.6	778.7	779.2	781.0	781.7
10°	785.7	791.4	802.1	800.6	808.6	813.2	805.7
12.5°	808.8	816.6	824.0	826.1	830.6	832.1	829.1
15°	829.7	833.8	834.2	833.1	834.6	833.3	829.0
17.5°	810.2	803.4	789.9	783.5	778.4	770.8	767.8
20°	777.9	758.1	735.2	726.0	715.3	694.2	699.2
22.5°	708.1	685.7	662.7	635.9	623.1	603.1	601.9
25°	599.7	560.9	518.2	488.4	470.9	451.0	442.2
27.5°	466.3	417.4	382.4	364.8	348.6	332.9	332.1
30°	378.5	341.8	314.8	299.6	289.7	283.1	284.5
32.5°	319.0	293.9	275.6	263.1	255.8	250.7	250.6
35°	260.8	243.6	231.9	226.6	221.4	217.7	217.9
37.5°	223.2	212.9	206.3	200.6	197.2	195.4	194.4
40°	203.9	195.4	190.4	186.9	184.2	181.7	181.2
42.5°	188.7	181.7	176.6	173.9	171.4	169.6	169.2
45°	167.4	161.7	157.1	154.1	153.0	151.4	151.4
47.5°	149.0	143.3	139.8	137.8	135.9	134.8	134.8
50°	136.5	132.1	129.0	127.7	126.1	125.5	125.2
52.5°	125.3	122.0	119.8	119.0	118.3	117.4	117.5
55°	110.1	108.3	107.3	106.6	105.5	104.1	105.0
57.5°	97.4	95.7	93.3	91.1	90.1	89.1	89.5
60°	88.4	85.1	81.9	79.4	78.7	76.6	76.6
62.5°	77.0	72.4	68.5	67.1	66.3	65.4	65.2
65°	59.2	57.4	56.5	55.5	55.0	55.0	54.6
67.5°	49.1	48.3	47.3	47.1	46.7	46.5	46.4
70°	43.3	42.4	42.0	41.7	41.3	41.5	40.8
72.5°	37.9	37.2	37.1	36.5	36.2	36.2	35.6
75°	29.8	29.8	29.6	29.4	28.9	28.7	28.9
77.5°	22.9	23.0	22.6	22.5	22.5	22.5	22.3
80°	18.4	18.6	18.4	18.1	17.9	18.1	17.9
82.5°	14.5	14.1	14.1	14.0	14.0	13.9	13.8
85°	8.3	8.5	8.3	8.1	8.1	8.1	8.3
87.5°	9.9	9.8	9.8	9.8	9.9	9.9	9.8
90°	33.9	33.5	33.3	33.6	33.8	34.0	34.2
92.5°	32.3	32.4	32.5	32.5	32.5	32.6	32.6
95°	64.5	64.5	64.2	63.8	63.4	62.9	62.5
97.5°	108.5	108.5	108.5	108.4	108.4	108.3	108.3
100°	139.1	139.1	139.0	138.8	138.6	138.3	138.0
102.5°	172.7	172.9	172.8	172.6	172.4	172.2	172.0
105°	223.1	223.5	223.7	223.7	223.7	223.7	223.7
107.5°	276.9	277.0	276.6	275.6	274.6	273.6	272.5
110°	313.5	313.5	313.1	312.5	311.7	311.0	310.4



TEST NUMBER: P331634-840

CATALOG NUMBER: SA2XXRDIP-C290D925U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	349.7	349.2	348.6	348.2	347.7	347.2	346.7
115°	406.5	406.3	405.8	405.2	404.5	403.7	403.1
117.5°	460.8	460.2	459.6	459.0	458.3	457.6	457.0
120°	497.9	497.9	497.6	496.9	496.1	495.5	494.8
122.5°	534.9	534.4	533.9	533.4	532.9	532.4	531.9
125°	590.6	589.9	589.5	589.3	589.0	588.8	588.5
127.5°	644.6	643.8	643.0	642.3	641.6	640.9	640.2
130°	682.0	681.5	680.9	679.9	679.0	678.1	677.2
132.5°	717.4	716.4	715.6	714.9	714.2	713.5	712.8
135°	771.3	771.0	770.6	769.9	769.3	768.6	767.9
137.5°	822.2	822.0	821.5	820.6	819.7	818.8	817.9
140°	856.7	856.7	856.2	855.3	854.3	853.5	852.6
142.5°	887.8	888.0	887.7	886.8	885.9	884.9	884.0
145°	934.9	935.1	934.8	933.9	933.0	932.1	931.2
147.5°	976.4	976.9	976.7	975.9	975.0	974.2	973.3
150°	1002.8	1003.4	1003.4	1002.8	1002.1	1001.4	1000.8
152.5°	1029.1	1030.0	1030.0	1029.1	1028.2	1027.4	1026.5
155°	1062.6	1063.7	1063.9	1063.2	1062.6	1061.9	1061.2
157.5°	1093.6	1095.1	1095.3	1094.3	1093.2	1092.1	1091.1
160°	1111.6	1113.0	1113.2	1112.3	1111.4	1110.4	1109.5
162.5°	1128.2	1129.7	1130.0	1128.9	1127.8	1126.8	1125.7
165°	1149.5	1151.1	1151.3	1150.2	1149.1	1148.0	1146.9
167.5°	1167.1	1168.6	1168.8	1167.7	1166.5	1165.4	1164.2
170°	1176.8	1178.3	1178.4	1177.1	1175.8	1174.4	1173.1
172.5°	1184.1	1185.6	1185.7	1184.4	1183.1	1181.6	1180.3
175°	1191.8	1193.5	1193.6	1192.2	1190.8	1189.5	1188.2
177.5°	1195.1	1196.1	1196.1	1195.1	1194.0	1192.9	1191.8
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3

(END OF REPORT)