

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332507-830

Luminaire Tested: **SA4XXDIP-C350D590U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332507-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C350D590U830-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3420.7 lumens  
Efficiency: N/A  
Efficacy: 133.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332507-830  
CATALOG NUMBER: SA4XXDIP-C350D590U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332507-830

CATALOG NUMBER: SA4XXDIP-C350D590U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	84	87	84	80	77	69	67	65	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	21
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	19
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4495	4495	4495
5°	4508	4454	4486
10°	4480	4418	4440
15°	4425	4355	4367
20°	4354	4277	4281
25°	4272	4188	4177
30°	4172	4084	4047
35°	4066	3975	3921
40°	3958	3851	3780
45°	3846	3729	3658
50°	3720	3620	3508
55°	3586	3478	3365
60°	3450	3321	3219
65°	3299	3171	3043
70°	3127	2969	2854
75°	2866	2729	2658
80°	2552	2450	2385
85°	2232	2149	2103



TEST NUMBER: P332507-830

CATALOG NUMBER: SA4XXDIP-C350D590U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.4	1.5
10°-20°	147.7	4.3
20°-30°	217.4	6.4
30°-40°	252.8	7.4
40°-50°	252.8	7.4
50°-60°	221.1	6.5
60°-70°	164.2	4.8
70°-80°	93.3	2.7
80°-90°	28.4	0.8
90°-100°	197.7	5.8
100°-110°	411.4	12.0
110°-120°	368.5	10.8
120°-130°	310.0	9.1
130°-140°	258.4	7.6
140°-150°	197.4	5.8
150°-160°	138.8	4.1
160°-170°	81.6	2.4
170°-180°	26.6	0.8
0°-30°	417.6	12.2
0°-40°	670.4	19.6
0°-60°	1144.3	33.5
0°-90°	1430.3	41.8
90°-120°	977.6	28.6
90°-150°	1743.4	51.0
90°-180°	1990.0	58.2
0°-180°	3420.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	556	554	550	554	554	53
15°	530	528	521	524	522	149
25°	480	476	470	471	469	221
35°	413	409	403	400	398	258
45°	337	333	327	322	320	260
55°	255	253	247	242	239	228
65°	173	170	166	162	159	171
75°	92	90	88	86	85	98
85°	24	24	23	23	23	27
90°	1	4	10	11	11	2
95°	18	56	438	217	131	20
105°	63	91	353	760	756	67
115°	111	139	314	604	726	110
125°	154	183	313	514	580	137
135°	183	218	310	456	518	142
145°	211	242	309	385	423	133
155°	240	259	300	340	354	111
165°	262	270	288	305	309	74
175°	273	274	276	280	278	26
180°	274	274	274	274	274	



TEST NUMBER: P332507-830

CATALOG NUMBER: SA4XXDIP-C350D590U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	558.2	558.0	557.7	557.5	557.2	556.7	555.8	555.0	554.1	553.2	554.0
5°	556.3	555.9	555.5	555.2	554.8	554.0	552.9	551.9	550.7	549.6	550.7
7.5°	551.2	550.7	550.4	550.0	549.6	548.7	547.5	546.4	545.2	543.9	544.8
10°	546.5	546.1	545.7	545.4	545.0	544.1	542.8	541.5	540.3	538.9	539.7
12.5°	540.5	540.1	539.7	539.2	538.9	538.0	536.6	535.3	533.9	532.5	533.4
15°	529.5	529.1	528.8	528.4	528.0	527.1	525.6	524.1	522.5	521.1	521.7
17.5°	516.4	515.9	515.5	515.0	514.4	513.5	512.1	510.7	509.3	507.8	508.2
20°	506.8	506.3	505.9	505.3	504.8	503.9	502.4	500.9	499.4	497.9	498.2
22.5°	496.4	495.8	495.1	494.5	493.8	492.8	491.3	489.8	488.3	486.8	487.4
25°	479.6	478.9	478.2	477.5	476.8	475.8	474.4	473.0	471.6	470.2	470.3
27.5°	460.3	459.6	458.9	458.2	457.5	456.5	455.2	453.9	452.6	451.3	451.1
30°	447.5	446.7	445.9	445.1	444.3	443.3	442.0	440.6	439.4	438.1	437.7
32.5°	433.9	433.2	432.4	431.8	431.0	430.0	428.7	427.3	425.9	424.5	424.0
35°	412.6	412.0	411.3	410.6	409.9	408.9	407.5	406.0	404.7	403.3	402.7
37.5°	390.3	389.6	389.0	388.4	387.8	386.7	385.2	383.7	382.2	380.7	379.9
40°	375.6	374.8	374.1	373.2	372.5	371.4	369.9	368.3	366.8	365.4	364.4
42.5°	360.0	359.5	359.0	358.5	358.1	356.9	355.3	353.6	352.0	350.4	349.2
45°	336.9	336.1	335.5	334.8	334.0	332.9	331.3	329.7	328.2	326.6	325.5
47.5°	312.6	312.2	311.7	311.2	310.8	309.8	308.3	306.8	305.4	303.9	302.7
50°	296.2	295.9	295.5	295.0	294.6	293.8	292.4	291.0	289.5	288.2	286.8
52.5°	280.2	279.7	279.2	278.7	278.2	277.3	275.8	274.4	272.9	271.5	270.2
55°	254.8	254.5	254.1	253.8	253.5	252.7	251.3	250.0	248.5	247.1	246.0
57.5°	230.5	230.2	229.8	229.5	229.1	228.3	226.9	225.6	224.1	222.8	221.7
60°	213.7	213.2	212.7	212.2	211.7	210.8	209.5	208.2	207.0	205.7	204.8
62.5°	197.3	196.9	196.4	196.0	195.6	194.7	193.3	192.0	190.6	189.3	188.4
65°	172.7	172.2	171.6	171.2	170.7	169.9	168.9	168.0	166.9	166.0	164.9
67.5°	147.9	147.4	146.9	146.5	146.0	145.3	144.4	143.5	142.5	141.5	140.5
70°	132.5	131.8	131.1	130.4	129.7	128.9	128.2	127.4	126.6	125.8	125.0
72.5°	116.1	115.4	114.7	114.0	113.3	112.6	112.0	111.4	110.7	110.1	109.4
75°	91.9	91.4	91.0	90.4	89.9	89.4	89.0	88.4	87.9	87.5	87.1
77.5°	68.8	68.6	68.3	68.1	68.0	67.6	67.2	66.7	66.3	65.9	65.7
80°	54.9	54.6	54.3	54.0	53.7	53.4	53.3	53.1	52.9	52.7	52.4
82.5°	41.3	41.2	41.0	40.9	40.7	40.6	40.6	40.6	40.5	40.5	40.4
85°	24.1	24.1	24.1	24.1	24.1	24.0	23.8	23.6	23.4	23.2	23.2
87.5°	9.4	9.5	9.8	9.8	9.8	9.7	10.3	10.3	10.4	10.5	10.4
90°	0.6	1.6	3.2	3.8	4.3	4.3	7.5	7.5	8.6	9.7	9.1
92.5°	6.1	9.0	13.9	20.5	28.4	39.6	66.9	108.6	149.3	170.5	142.0
95°	17.7	19.3	24.7	31.8	44.6	67.2	114.0	202.2	330.6	438.2	450.5
97.5°	31.9	31.9	36.5	42.9	54.0	73.0	109.0	181.7	309.5	461.6	566.1
100°	40.9	40.9	44.6	51.1	61.3	78.5	110.2	171.0	280.7	432.3	570.0
102.5°	49.5	50.3	53.6	59.7	69.5	85.8	114.5	168.0	261.3	395.8	537.6
105°	62.9	64.6	67.2	73.7	83.3	99.0	124.7	169.4	244.7	352.7	479.1
107.5°	77.8	78.8	81.5	88.4	97.6	113.0	136.7	177.3	241.7	328.7	431.8
110°	87.7	88.7	91.4	97.8	107.5	122.1	145.7	183.3	242.5	320.5	408.1



TEST NUMBER: P332507-830

CATALOG NUMBER: SA4XXDIP-C350D590U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	97.1	98.2	101.3	107.4	117.0	131.5	154.3	189.8	245.1	316.6	394.7
115°	110.7	112.4	116.1	121.5	131.8	146.3	167.8	200.0	250.1	314.5	382.3
117.5°	125.0	126.5	129.8	135.7	145.2	160.3	180.8	210.5	255.2	314.0	376.7
120°	134.4	135.5	139.2	145.2	154.3	169.4	189.8	217.7	259.2	314.0	373.7
122.5°	143.0	144.1	147.9	153.4	163.3	178.0	198.4	224.6	263.1	313.6	370.2
125°	154.3	156.5	159.7	165.6	175.8	190.9	210.2	235.0	268.8	312.9	364.6
127.5°	164.3	166.1	169.9	176.6	187.3	202.5	221.2	243.9	273.4	311.7	356.9
130°	169.9	172.0	176.3	184.5	194.6	210.2	228.5	249.5	276.9	311.3	352.1
132.5°	175.5	177.2	182.9	190.5	201.5	216.2	234.5	255.1	279.9	310.9	347.9
135°	183.3	185.5	190.9	200.0	211.3	225.3	243.0	262.4	284.5	310.2	341.4
137.5°	191.2	193.2	199.2	207.8	219.6	232.9	249.5	267.6	287.1	310.1	335.8
140°	196.8	198.4	204.3	213.5	224.7	237.6	253.8	271.0	289.3	309.7	332.8
142.5°	202.8	204.4	209.9	218.6	229.5	242.0	257.7	273.5	291.0	309.7	330.3
145°	211.3	212.9	218.3	225.8	236.0	247.9	261.8	276.4	292.0	308.6	325.8
147.5°	220.8	221.4	226.1	233.8	242.4	253.1	266.2	278.8	292.5	306.7	321.9
150°	226.9	227.4	231.8	238.2	246.3	256.5	268.3	280.1	292.5	305.4	318.9
152.5°	232.5	232.6	236.9	242.9	250.2	259.5	270.0	281.0	291.6	303.2	315.4
155°	240.3	240.9	244.1	249.5	255.4	263.4	272.6	281.7	290.3	300.0	310.2
157.5°	248.0	248.0	251.0	255.1	260.3	266.6	274.5	281.7	289.0	296.7	305.0
160°	252.7	252.7	254.9	258.6	262.9	268.8	275.3	281.7	287.7	294.1	301.1
162.5°	257.0	256.6	258.3	261.6	265.5	270.1	276.2	281.7	286.3	291.5	297.7
165°	261.8	261.8	262.9	265.6	268.3	271.5	276.4	280.7	283.9	287.7	292.0
167.5°	266.6	266.2	266.6	268.7	270.2	272.7	276.3	279.4	281.3	283.8	286.8
170°	268.8	268.3	268.8	270.4	271.5	273.1	275.8	278.5	279.6	281.2	283.3
172.5°	271.0	270.4	270.5	271.7	272.4	273.5	275.4	277.7	277.9	278.6	280.3
175°	273.1	272.6	272.6	273.1	273.7	273.7	274.8	276.4	275.8	275.8	276.9
177.5°	274.1	273.7	273.2	273.7	273.7	273.7	274.1	274.9	274.1	274.1	274.6
180°	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7



TEST NUMBER: P332507-830

CATALOG NUMBER: SA4XXDIP-C350D590U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	554.8	555.6	556.4	556.8	556.7	556.6	556.5	556.4
5°	551.9	552.9	554.0	554.4	554.2	554.0	553.8	553.6
7.5°	545.6	546.6	547.4	547.8	547.7	547.5	547.4	547.3
10°	540.5	541.3	542.2	542.4	542.2	542.0	541.8	541.6
12.5°	534.2	535.1	536.0	536.3	536.0	535.7	535.5	535.2
15°	522.3	522.8	523.5	523.6	523.3	523.0	522.7	522.5
17.5°	508.6	509.0	509.3	509.4	509.3	509.1	508.9	508.7
20°	498.5	498.8	499.1	499.2	498.9	498.7	498.5	498.3
22.5°	487.9	488.4	489.0	489.1	488.7	488.3	488.0	487.7
25°	470.4	470.5	470.6	470.5	470.0	469.7	469.3	468.9
27.5°	450.8	450.6	450.3	450.0	449.5	449.0	448.5	448.0
30°	437.3	437.0	436.5	436.1	435.5	435.1	434.6	434.1
32.5°	423.6	423.1	422.6	422.2	421.7	421.1	420.7	420.2
35°	401.9	401.2	400.5	399.9	399.4	399.0	398.4	397.9
37.5°	379.2	378.4	377.7	377.0	376.4	375.7	375.0	374.4
40°	363.4	362.4	361.5	360.7	360.1	359.7	359.2	358.7
42.5°	348.1	346.9	345.8	345.1	344.7	344.4	344.0	343.7
45°	324.4	323.3	322.3	321.5	321.2	320.9	320.7	320.4
47.5°	301.4	300.2	299.0	298.0	297.3	296.5	295.8	295.0
50°	285.4	284.1	282.7	281.6	281.1	280.5	279.8	279.3
52.5°	269.0	267.8	266.6	265.5	264.8	264.0	263.3	262.5
55°	244.8	243.6	242.4	241.5	240.9	240.3	239.7	239.1
57.5°	220.6	219.4	218.3	217.4	216.9	216.3	215.7	215.1
60°	203.9	203.0	202.1	201.4	201.0	200.4	199.9	199.4
62.5°	187.7	186.8	186.0	185.3	184.8	184.4	183.9	183.3
65°	164.0	163.0	162.0	161.3	160.8	160.2	159.8	159.3
67.5°	139.6	138.6	137.7	137.1	137.0	136.9	136.8	136.6
70°	124.2	123.5	122.6	122.1	121.8	121.5	121.2	120.9
72.5°	108.9	108.2	107.5	107.1	106.8	106.5	106.2	105.9
75°	86.6	86.2	85.9	85.6	85.5	85.4	85.3	85.2
77.5°	65.6	65.5	65.4	65.2	64.9	64.7	64.4	64.2
80°	52.2	52.0	51.8	51.7	51.6	51.5	51.4	51.3
82.5°	40.2	40.2	40.1	40.0	39.9	39.7	39.6	39.5
85°	23.2	23.2	23.2	23.2	23.1	23.0	22.8	22.7
87.5°	10.5	10.7	10.7	10.7	10.8	10.9	10.8	10.8
90°	9.7	10.2	10.7	10.7	11.3	11.8	11.3	11.3
92.5°	105.6	79.5	63.2	52.5	46.1	43.3	41.4	41.4
95°	398.4	315.1	243.0	190.9	164.6	147.9	138.2	131.2
97.5°	588.6	557.7	505.1	448.9	410.4	378.0	361.8	350.6
100°	648.5	659.2	632.8	593.0	546.3	513.5	497.4	493.0
102.5°	645.5	698.8	706.4	689.8	661.1	637.3	620.4	616.9
105°	602.2	695.2	748.5	770.5	771.6	767.2	759.7	756.5
107.5°	540.8	639.8	714.8	762.7	789.3	801.5	806.9	808.3
110°	503.8	596.8	674.8	734.0	772.1	794.7	804.4	809.2





TEST NUMBER: P332507-830

CATALOG NUMBER: SA4XXDIP-C350D590U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	476.7	558.9	632.6	691.7	735.1	762.4	776.0	783.8
115°	449.5	515.7	578.5	630.2	672.6	704.9	722.1	726.4
117.5°	436.1	490.9	540.4	584.1	620.4	647.4	664.9	668.3
120°	430.2	480.1	523.1	561.3	592.0	615.7	629.6	635.6
122.5°	425.0	473.3	512.4	545.8	571.7	592.0	603.8	609.7
125°	416.1	462.4	499.5	529.0	550.5	566.2	576.4	579.6
127.5°	405.4	449.6	486.6	514.6	536.3	550.2	558.7	561.9
130°	396.8	439.3	475.8	504.4	526.4	539.8	548.5	551.7
132.5°	387.8	427.6	463.4	491.8	513.5	528.7	536.8	540.1
135°	375.3	410.3	443.0	470.0	491.4	506.5	515.1	518.3
137.5°	364.0	393.6	421.2	445.5	465.6	480.5	487.6	491.4
140°	357.5	382.9	407.0	429.6	448.5	460.2	467.8	472.1
142.5°	351.6	373.8	394.5	414.2	430.7	441.8	448.5	451.4
145°	343.0	361.3	377.5	392.5	406.0	415.1	420.5	423.1
147.5°	336.0	350.5	363.4	375.3	385.2	393.0	397.1	398.1
150°	331.8	344.1	354.9	364.6	373.2	380.1	383.3	383.9
152.5°	327.0	337.6	347.5	355.5	362.8	368.5	370.4	371.0
155°	319.9	328.5	336.6	343.0	348.5	352.7	354.3	354.3
157.5°	312.3	319.5	326.2	331.4	335.5	338.7	339.7	339.7
160°	307.6	313.5	319.3	323.7	326.9	330.2	330.6	330.6
162.5°	302.8	307.8	312.5	316.4	318.8	322.0	322.5	322.1
165°	296.2	299.4	303.2	305.9	308.1	310.2	309.7	309.2
167.5°	289.9	292.4	295.4	297.0	298.1	299.4	299.4	299.0
170°	286.1	287.7	289.8	291.4	292.5	293.0	292.5	292.5
172.5°	282.6	283.8	285.1	286.3	286.9	287.5	286.9	286.1
175°	278.0	278.5	279.6	279.6	279.6	280.7	279.6	278.5
177.5°	274.9	275.4	275.4	275.8	275.4	275.8	274.9	274.1
180°	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7

(END OF REPORT)