

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332579-830

Luminaire Tested: **SA4XXDIP-C575D1205U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332579-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6406.4 lumens  
Efficiency: N/A  
Efficacy: 129.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332579-830  
CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332579-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	83	86	82	79	76	66	64	62	52	51	49	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	51	46	43	41	34	33	31	26
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	61	54	48	65	56	49	44	46	41	37	36	32	30	27	25	23	19
5	66	55	47	41	59	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17	14
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12	10
10	45	33	26	21	41	31	24	20	25	20	17	20	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7389	7389	7389
5°	7412	7323	7376
10°	7365	7263	7299
15°	7276	7160	7178
20°	7158	7032	7039
25°	7023	6886	6866
30°	6858	6715	6652
35°	6686	6535	6447
40°	6509	6330	6215
45°	6322	6130	6012
50°	6116	5951	5766
55°	5895	5719	5533
60°	5672	5459	5293
65°	5421	5213	5001
70°	5141	4881	4692
75°	4713	4482	4370
80°	4193	4021	3924
85°	3668	3538	3464



TEST NUMBER: P332579-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.2	1.3
10°-20°	242.9	3.8
20°-30°	357.5	5.6
30°-40°	415.6	6.5
40°-50°	415.6	6.5
50°-60°	363.5	5.7
60°-70°	270.0	4.2
70°-80°	153.4	2.4
80°-90°	47.3	0.7
90°-100°	402.7	6.3
100°-110°	838.0	13.1
110°-120°	750.6	11.7
120°-130°	631.4	9.9
130°-140°	526.5	8.2
140°-150°	402.2	6.3
150°-160°	282.7	4.4
160°-170°	166.3	2.6
170°-180°	54.1	0.8
0°-30°	686.6	10.7
0°-40°	1102.1	17.2
0°-60°	1881.3	29.4
0°-90°	2352.0	36.7
90°-120°	1991.3	31.1
90°-150°	3551.4	55.4
90°-180°	4054.0	63.3
0°-180°	6406.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	915	915	915	915	915	
5°	915	911	904	911	910	87
15°	871	867	857	861	859	245
25°	788	783	773	774	771	363
35°	678	673	663	658	654	424
45°	554	548	537	529	527	427
55°	419	416	406	398	393	375
65°	284	280	273	266	262	281
75°	151	147	144	141	140	161
85°	40	40	38	38	37	44
90°	1	9	20	22	23	4
95°	36	114	893	442	267	40
105°	128	186	718	1547	1541	137
115°	226	283	641	1231	1480	224
125°	314	374	637	1048	1181	280
135°	373	445	632	930	1056	289
145°	430	493	629	784	862	270
155°	490	528	611	692	722	226
165°	533	550	586	620	630	151
175°	556	558	562	570	567	53
180°	558	558	558	558	558	



TEST NUMBER: P332579-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	917.7	917.3	916.9	916.5	916.2	915.2	913.8	912.4	910.9	909.5	910.8
5°	914.6	914.0	913.3	912.7	912.0	910.8	909.0	907.2	905.4	903.6	905.4
7.5°	906.1	905.4	904.8	904.2	903.5	902.2	900.2	898.2	896.2	894.2	895.7
10°	898.4	897.9	897.2	896.5	895.9	894.5	892.4	890.2	888.2	886.0	887.3
12.5°	888.5	887.9	887.2	886.6	885.9	884.5	882.2	880.0	877.7	875.4	876.8
15°	870.6	870.0	869.3	868.6	868.0	866.5	864.0	861.6	859.1	856.7	857.6
17.5°	849.0	848.2	847.4	846.6	845.7	844.2	841.9	839.6	837.3	835.0	835.6
20°	833.2	832.4	831.6	830.8	829.9	828.3	825.9	823.4	821.0	818.5	819.0
22.5°	816.1	815.1	814.1	812.9	811.9	810.1	807.7	805.2	802.8	800.3	801.3
25°	788.4	787.3	786.2	785.0	783.9	782.2	779.9	777.6	775.3	773.1	773.3
27.5°	756.8	755.6	754.4	753.3	752.1	750.5	748.3	746.2	744.0	742.0	741.6
30°	735.7	734.3	733.0	731.7	730.5	728.7	726.6	724.4	722.4	720.3	719.6
32.5°	713.3	712.2	711.0	709.8	708.7	706.9	704.7	702.5	700.2	698.0	697.2
35°	678.4	677.3	676.2	675.0	673.9	672.1	669.9	667.6	665.3	663.1	661.9
37.5°	641.6	640.6	639.5	638.5	637.4	635.7	633.3	630.8	628.4	625.9	624.7
40°	617.6	616.2	614.9	613.7	612.4	610.5	608.0	605.6	603.1	600.7	599.1
42.5°	591.7	591.0	590.2	589.4	588.6	586.8	584.2	581.5	578.7	576.1	574.2
45°	553.7	552.6	551.5	550.4	549.2	547.3	544.7	542.1	539.5	536.9	535.1
47.5°	514.0	513.2	512.5	511.6	510.9	509.3	506.9	504.4	502.0	499.6	497.6
50°	487.0	486.4	485.7	485.0	484.4	483.0	480.7	478.3	476.1	473.8	471.6
52.5°	460.6	459.9	459.0	458.3	457.5	455.9	453.5	451.1	448.7	446.2	444.2
55°	418.8	418.3	417.8	417.4	416.9	415.5	413.2	410.9	408.6	406.3	404.4
57.5°	378.9	378.3	377.8	377.2	376.6	375.3	373.1	370.8	368.5	366.3	364.4
60°	351.3	350.5	349.7	348.8	348.1	346.6	344.5	342.3	340.3	338.1	336.7
62.5°	324.3	323.7	322.9	322.3	321.6	320.1	317.9	315.7	313.4	311.1	309.8
65°	283.8	283.0	282.2	281.4	280.6	279.4	277.8	276.1	274.5	272.9	271.2
67.5°	243.1	242.3	241.6	240.8	240.1	238.9	237.3	235.8	234.2	232.6	231.1
70°	217.8	216.7	215.6	214.4	213.3	212.1	210.8	209.4	208.1	206.8	205.6
72.5°	190.9	189.7	188.6	187.4	186.2	185.2	184.2	183.1	182.1	181.0	179.9
75°	151.1	150.2	149.5	148.6	147.8	147.0	146.2	145.3	144.6	143.7	143.1
77.5°	113.1	112.7	112.4	112.1	111.7	111.1	110.4	109.7	109.0	108.3	108.0
80°	90.2	89.7	89.3	88.8	88.2	87.8	87.6	87.2	86.9	86.5	86.2
82.5°	68.0	67.7	67.5	67.2	67.0	66.8	66.8	66.7	66.6	66.6	66.4
85°	39.6	39.6	39.6	39.6	39.6	39.4	39.1	38.8	38.5	38.2	38.2
87.5°	15.5	15.7	16.3	16.4	16.5	16.4	17.5	17.4	17.7	18.0	17.8
90°	1.1	3.3	6.6	7.6	8.8	8.8	15.4	15.4	17.5	19.7	18.7
92.5°	12.4	18.2	28.5	41.8	57.9	80.6	136.3	221.2	304.1	347.4	289.4
95°	36.1	39.4	50.4	64.7	90.9	137.0	232.1	411.8	673.5	892.6	917.8
97.5°	64.8	64.8	74.3	87.4	110.0	148.5	221.9	370.2	630.4	940.2	1153.1
100°	83.2	83.2	90.9	104.1	124.9	159.9	224.5	348.3	571.7	880.5	1160.9
102.5°	100.8	102.5	109.3	121.6	141.5	174.8	233.3	342.1	532.3	806.1	1095.2
105°	128.2	131.4	137.0	150.1	169.8	201.5	254.1	345.0	498.3	718.5	975.8
107.5°	158.3	160.5	166.1	180.0	198.9	230.3	278.4	361.2	492.2	669.4	879.5
110°	178.5	180.7	186.2	199.3	219.0	248.6	296.8	373.4	494.0	652.8	831.3



TEST NUMBER: P332579-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	197.8	200.0	206.3	218.6	238.4	267.9	314.3	386.6	499.2	644.9	804.1
115°	225.6	228.9	236.6	247.5	268.3	297.9	341.7	407.5	509.3	640.7	778.7
117.5°	254.5	257.6	264.4	276.4	296.0	326.6	368.3	428.7	520.0	639.6	767.3
120°	273.8	276.0	283.7	295.7	314.3	345.0	386.6	443.6	527.9	639.6	761.2
122.5°	291.3	293.5	301.2	312.4	332.7	362.5	404.2	457.6	535.8	638.8	754.2
125°	314.3	318.7	325.3	337.3	358.2	388.8	428.2	478.6	547.6	637.4	742.5
127.5°	334.7	338.2	346.1	359.9	381.5	412.5	450.5	496.8	557.0	635.0	727.0
130°	346.1	350.4	359.2	375.7	396.4	428.2	465.5	508.2	564.0	634.1	717.4
132.5°	357.5	361.0	372.4	388.0	410.5	440.5	477.8	519.6	570.1	633.3	708.6
135°	373.4	377.9	388.8	407.5	430.5	458.9	495.0	534.5	579.4	632.0	695.5
137.5°	389.5	393.6	405.7	423.4	447.3	474.5	508.2	545.0	584.8	631.7	684.1
140°	400.9	404.2	416.2	434.8	457.8	484.1	517.0	552.0	589.3	630.8	678.0
142.5°	413.1	416.4	427.5	445.4	467.4	492.9	524.8	557.2	592.8	630.8	672.7
145°	430.5	433.8	444.7	460.0	480.8	504.9	533.4	563.0	594.7	628.7	663.7
147.5°	449.9	451.0	460.6	476.5	493.7	515.4	542.2	568.0	595.8	624.7	655.6
150°	462.2	463.3	472.0	485.2	501.6	522.5	546.5	570.6	595.8	622.1	649.5
152.5°	473.5	473.8	482.6	494.8	509.5	528.6	550.1	572.4	594.1	617.7	642.4
155°	489.6	490.7	497.2	508.2	520.3	536.7	555.3	573.9	591.4	611.1	632.0
157.5°	505.1	505.1	511.2	519.8	530.3	543.3	559.0	573.9	588.6	604.4	621.2
160°	514.7	514.7	519.2	526.8	535.6	547.6	560.7	573.9	586.0	599.1	613.3
162.5°	523.5	522.6	526.1	532.9	540.8	550.3	562.5	573.9	583.3	593.8	606.3
165°	533.4	533.4	535.6	541.0	546.5	553.1	563.0	571.7	578.2	586.0	594.7
167.5°	543.3	542.2	543.3	547.4	550.4	555.5	562.7	569.1	573.1	578.1	584.2
170°	547.6	546.5	547.6	550.9	553.1	556.4	561.8	567.3	569.5	572.8	577.2
172.5°	552.0	550.9	551.1	553.6	554.9	557.2	561.0	565.6	566.0	567.5	571.1
175°	556.4	555.3	555.3	556.4	557.5	557.5	559.7	563.0	561.8	561.8	564.0
177.5°	558.4	557.5	556.6	557.5	557.5	557.5	558.4	560.1	558.4	558.4	559.2
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332579-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	912.1	913.4	914.7	915.3	915.1	915.0	914.9	914.7
5°	907.2	909.0	910.8	911.5	911.2	910.9	910.5	910.2
7.5°	897.1	898.5	899.9	900.6	900.4	900.2	900.0	899.8
10°	888.6	889.9	891.3	891.7	891.4	891.1	890.7	890.4
12.5°	878.4	879.8	881.2	881.7	881.2	880.7	880.3	879.9
15°	858.7	859.6	860.5	860.8	860.4	859.9	859.3	858.8
17.5°	836.2	836.8	837.4	837.5	837.3	836.9	836.6	836.3
20°	819.5	820.0	820.5	820.6	820.2	819.9	819.6	819.3
22.5°	802.1	803.0	803.9	804.0	803.4	802.9	802.3	801.6
25°	773.4	773.5	773.7	773.5	772.8	772.1	771.5	770.8
27.5°	741.2	740.7	740.4	739.8	739.0	738.2	737.4	736.5
30°	719.0	718.3	717.7	716.9	716.0	715.3	714.4	713.6
32.5°	696.4	695.6	694.8	694.0	693.2	692.4	691.5	690.8
35°	660.7	659.6	658.5	657.5	656.7	655.8	655.1	654.2
37.5°	623.5	622.2	620.9	619.8	618.8	617.6	616.6	615.5
40°	597.5	595.8	594.2	593.0	592.1	591.4	590.5	589.7
42.5°	572.3	570.3	568.4	567.2	566.8	566.2	565.6	565.1
45°	533.3	531.5	529.7	528.6	528.1	527.6	527.1	526.6
47.5°	495.6	493.5	491.5	489.9	488.7	487.4	486.2	484.9
50°	469.2	466.9	464.7	463.1	462.0	461.1	460.1	459.1
52.5°	442.1	440.2	438.2	436.5	435.3	434.0	432.8	431.6
55°	402.5	400.5	398.5	397.0	396.1	395.1	394.1	393.1
57.5°	362.6	360.7	358.8	357.4	356.5	355.5	354.6	353.6
60°	335.2	333.8	332.2	331.1	330.3	329.5	328.7	327.8
62.5°	308.5	307.1	305.8	304.7	303.9	303.1	302.3	301.4
65°	269.6	268.0	266.4	265.1	264.3	263.4	262.7	261.8
67.5°	229.5	228.0	226.4	225.5	225.3	225.1	224.8	224.6
70°	204.2	202.9	201.6	200.8	200.2	199.7	199.3	198.8
72.5°	178.9	177.9	176.8	176.1	175.6	175.1	174.7	174.1
75°	142.4	141.8	141.2	140.7	140.5	140.4	140.3	140.1
77.5°	107.8	107.6	107.4	107.2	106.7	106.3	105.8	105.5
80°	85.9	85.6	85.2	85.0	84.8	84.6	84.5	84.4
82.5°	66.2	66.0	65.8	65.6	65.5	65.3	65.1	64.9
85°	38.2	38.2	38.2	38.1	37.9	37.7	37.6	37.4
87.5°	18.0	18.3	18.5	18.5	18.7	18.9	18.7	18.7
90°	19.7	20.8	21.9	21.9	23.0	24.1	23.0	23.0
92.5°	215.1	161.8	128.8	106.9	94.0	88.0	84.4	84.4
95°	811.5	641.8	495.0	388.8	335.2	301.2	281.4	267.2
97.5°	1199.1	1136.0	1028.9	914.5	835.8	770.0	737.1	714.4
100°	1320.9	1342.7	1289.1	1208.1	1112.8	1045.9	1013.1	1004.4
102.5°	1314.8	1423.3	1438.9	1405.1	1346.7	1298.3	1263.7	1256.7
105°	1226.6	1416.2	1524.6	1569.4	1571.7	1562.9	1547.6	1541.0
107.5°	1101.5	1303.3	1456.0	1553.7	1607.8	1632.8	1643.7	1646.6
110°	1026.2	1215.7	1374.5	1495.0	1572.7	1618.7	1638.5	1648.3





TEST NUMBER: P332579-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	971.0	1138.6	1288.6	1409.1	1497.4	1553.0	1580.6	1596.7
115°	915.6	1050.4	1178.5	1283.6	1370.2	1435.9	1470.9	1479.7
117.5°	888.4	999.9	1100.7	1189.9	1263.7	1318.9	1354.3	1361.1
120°	876.2	978.1	1065.6	1143.4	1205.9	1254.1	1282.5	1294.6
122.5°	865.6	964.0	1043.8	1111.9	1164.7	1205.9	1229.9	1242.0
125°	847.7	941.9	1017.5	1077.7	1121.5	1153.3	1174.1	1180.6
127.5°	825.8	915.9	991.2	1048.4	1092.4	1120.7	1138.2	1144.7
130°	808.3	894.8	969.3	1027.4	1072.2	1099.6	1117.1	1123.7
132.5°	789.9	871.2	943.9	1001.9	1045.9	1076.9	1093.4	1100.0
135°	764.5	835.7	902.5	957.2	1001.1	1031.7	1049.2	1055.8
137.5°	741.5	801.7	858.0	907.5	948.5	978.7	993.2	1001.1
140°	728.3	779.8	829.1	875.1	913.4	937.5	952.8	961.6
142.5°	716.0	761.4	803.7	843.6	877.5	899.8	913.4	919.5
145°	698.8	736.0	768.8	799.6	826.9	845.6	856.5	862.0
147.5°	684.6	714.1	740.4	764.5	784.7	800.6	809.0	810.9
150°	675.8	701.0	722.8	742.5	760.1	774.3	780.9	782.0
152.5°	666.1	687.8	707.9	724.2	739.0	750.6	754.6	755.7
155°	651.7	669.2	685.6	698.8	709.7	718.5	721.8	721.8
157.5°	636.1	650.8	664.6	675.1	683.4	690.0	692.0	692.0
160°	626.5	638.5	650.5	659.3	665.9	672.5	673.5	673.5
162.5°	616.8	627.2	636.6	644.4	649.2	655.8	657.0	656.0
165°	603.5	610.0	617.7	623.2	627.5	632.0	630.8	629.8
167.5°	590.6	595.6	601.7	605.0	607.2	610.0	609.8	609.0
170°	582.7	586.0	590.3	593.6	595.8	596.9	595.8	595.8
172.5°	575.6	578.1	580.7	583.1	584.4	585.5	584.4	582.7
175°	566.3	567.3	569.5	569.5	569.5	571.7	569.5	567.3
177.5°	560.1	561.0	561.0	561.8	561.0	561.8	560.1	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5

(END OF REPORT)