

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331661-840

Luminaire Tested: **SA2XXRDIP-C485D725U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331661-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C485D725U840-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4333.3 lumens  
Efficiency: N/A  
Efficacy: 112.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331661-840  
CATALOG NUMBER: SA2XXRDIP-C485D725U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331661-840

CATALOG NUMBER: SA2XXRDIP-C485D725U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40				
1	96	92	88	85	87	84	80	78	68	66	64	55	53	52	42	41	40	34				
2	88	80	75	70	79	74	69	64	60	57	54	48	46	44	37	36	34	29				
3	80	71	64	59	73	65	59	54	54	49	46	43	40	37	33	31	30	25				
4	73	63	56	50	67	58	51	46	48	43	39	39	35	32	30	28	26	22				
5	67	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19				
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17				
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15				
8	53	42	34	29	49	38	32	27	32	27	23	26	23	20	21	18	16	14				
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13				
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13454	13454	13454
5°	13506	13287	13361
10°	13404	13070	12959
15°	13249	12682	12318
20°	13036	12129	11519
25°	12818	11501	10750
30°	12515	10856	9758
35°	12220	10153	8889
40°	11921	9428	7885
45°	11574	8611	6976
50°	11215	7784	6081
55°	10849	6899	5222
60°	10424	5968	4334
65°	9941	5012	3947
70°	9361	4131	3635
75°	8659	3762	3387
80°	7643	3366	3087
85°	6002	2649	2649



TEST NUMBER: P331661-840

CATALOG NUMBER: SA2XXRDIP-C485D725U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.0	1.8
10°-20°	214.2	4.9
20°-30°	300.8	6.9
30°-40°	328.0	7.6
40°-50°	301.6	7.0
50°-60°	236.8	5.5
60°-70°	154.4	3.6
70°-80°	79.6	1.8
80°-90°	24.4	0.6
90°-100°	59.3	1.4
100°-110°	184.1	4.2
110°-120°	314.7	7.3
120°-130°	413.8	9.5
130°-140°	464.4	10.7
140°-150°	455.4	10.5
150°-160°	382.0	8.8
160°-170°	253.3	5.8
170°-180°	88.5	2.0
0°-30°	593.0	13.7
0°-40°	921.0	21.3
0°-60°	1459.4	33.7
0°-90°	1717.8	39.6
90°-120°	558.0	12.9
90°-150°	1891.7	43.7
90°-180°	2616.0	60.4
0°-180°	4333.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	833	829	820	826	824	79
15°	793	783	759	745	737	223
25°	720	694	646	616	603	331
35°	620	580	515	469	451	388
45°	507	455	377	326	306	391
55°	385	325	245	202	186	344
65°	260	199	131	107	103	258
75°	139	87	60	55	54	147
85°	32	17	14	14	14	38
90°	1	11	28	26	27	3
95°	41	49	50	50	49	47
105°	170	172	174	175	175	179
115°	316	320	319	318	316	312
125°	459	466	464	462	461	410
135°	594	603	605	604	602	459
145°	721	727	732	732	729	451
155°	825	827	830	833	831	380
165°	898	897	897	902	898	253
175°	934	932	930	935	931	89
180°	935	935	935	935	935	



TEST NUMBER: P331661-840

CATALOG NUMBER: SA2XXRDIP-C485D725U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	836.4	835.8	835.1	834.4	833.7	832.6	831.2	829.7	828.2	826.8	828.1
5°	833.3	832.5	831.7	830.9	830.0	828.5	826.4	824.2	822.0	819.8	821.3
7.5°	824.8	823.7	822.7	821.6	820.6	818.8	816.3	813.7	811.2	808.7	809.1
10°	817.6	816.4	815.2	814.1	812.8	810.6	807.3	803.9	800.5	797.2	796.7
12.5°	808.5	807.1	805.6	804.2	802.7	799.9	795.6	791.3	787.0	782.7	781.8
15°	792.6	790.8	789.0	787.1	785.3	781.5	775.8	770.1	764.5	758.7	755.6
17.5°	773.3	770.4	767.6	764.8	761.9	756.9	749.6	742.3	735.0	727.6	723.9
20°	758.7	755.4	752.0	748.7	745.3	739.4	731.0	722.7	714.3	705.9	701.8
22.5°	743.1	739.3	735.5	731.7	728.0	721.4	712.0	702.5	693.1	683.6	678.2
25°	719.5	714.2	708.8	703.4	698.0	689.8	678.7	667.7	656.6	645.6	638.7
27.5°	691.2	685.3	679.4	673.7	667.8	658.6	646.2	633.7	621.3	608.7	600.8
30°	671.3	664.9	658.5	652.2	645.8	635.9	622.5	609.0	595.6	582.3	573.7
32.5°	652.0	644.5	637.0	629.7	622.2	611.6	597.9	584.2	570.6	556.9	547.1
35°	620.0	611.4	602.9	594.3	585.7	574.1	559.4	544.6	529.9	515.1	504.5
37.5°	587.9	578.6	569.2	559.8	550.5	537.9	522.2	506.4	490.7	475.0	463.3
40°	565.6	555.6	545.5	535.5	525.4	512.3	496.0	479.8	463.5	447.3	435.4
42.5°	542.7	532.1	521.5	511.0	500.4	486.7	469.9	453.0	436.3	419.5	407.2
45°	506.9	495.6	484.3	473.1	461.9	447.5	429.9	412.3	394.7	377.1	365.2
47.5°	471.8	459.9	448.1	436.2	424.2	409.2	391.0	372.8	354.7	336.5	324.7
50°	446.5	434.5	422.7	410.8	398.9	383.7	365.3	346.9	328.4	309.9	298.4
52.5°	421.7	409.3	396.9	384.5	372.0	356.8	338.7	320.7	302.7	284.7	273.5
55°	385.4	372.3	359.2	346.2	333.2	317.5	299.4	281.3	263.2	245.1	235.1
57.5°	348.1	334.8	321.3	307.9	294.5	279.1	261.8	244.3	226.9	209.5	200.3
60°	322.8	309.4	296.0	282.6	269.1	253.9	236.6	219.3	202.1	184.8	176.2
62.5°	298.0	284.7	271.2	257.8	244.4	229.5	213.1	196.6	180.2	163.7	155.5
65°	260.2	246.6	233.1	219.4	205.9	191.6	176.5	161.4	146.3	131.2	125.5
67.5°	223.7	210.3	196.7	183.3	169.8	156.2	142.7	129.2	115.5	102.0	99.4
70°	198.3	185.3	172.2	159.2	146.0	133.7	122.2	110.6	99.1	87.5	85.8
72.5°	174.2	161.7	149.2	136.6	124.1	113.2	103.9	94.6	85.3	76.0	74.6
75°	138.8	127.0	115.3	103.6	91.8	83.1	77.5	71.7	66.0	60.3	59.2
77.5°	103.9	93.6	83.3	73.0	62.8	56.2	53.5	50.8	48.0	45.2	44.5
80°	82.2	73.6	65.1	56.6	48.0	42.9	41.2	39.6	37.9	36.2	35.5
82.5°	62.3	55.6	49.0	42.3	35.6	31.7	30.6	29.4	28.3	27.2	26.8
85°	32.4	28.9	25.3	21.9	18.4	16.4	15.9	15.3	14.8	14.3	14.3
87.5°	9.8	9.2	8.5	7.9	7.2	7.3	8.1	8.8	9.6	10.4	10.1
90°	0.8	2.9	5.0	7.1	9.2	12.2	16.1	19.9	23.7	27.7	27.3
92.5°	14.0	15.6	17.2	18.7	20.2	21.4	22.3	23.2	24.2	25.1	25.1
95°	41.0	42.8	44.5	46.4	48.1	49.1	49.5	49.8	50.2	50.5	50.5
97.5°	75.0	76.5	78.1	79.6	81.2	82.3	82.9	83.6	84.2	84.9	84.9
100°	100.3	101.7	103.0	104.4	105.8	106.8	107.3	107.9	108.4	109.0	109.0
102.5°	126.7	127.8	129.1	130.2	131.3	132.2	132.8	133.5	134.1	134.8	134.9
105°	169.8	170.3	170.8	171.3	171.8	172.3	172.6	173.0	173.3	173.7	174.0
107.5°	213.0	213.8	214.5	215.3	216.0	216.4	216.4	216.4	216.4	216.4	216.6
110°	240.8	241.8	242.9	243.9	245.0	245.5	245.5	245.5	245.5	245.5	245.5



TEST NUMBER: P331661-840  
 CATALOG NUMBER: SA2XXRDIP-C485D725U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.0	272.2	273.2	274.2	275.3	275.7	275.6	275.5	275.3	275.2	274.8
115°	315.8	316.8	317.8	318.9	319.9	320.3	319.9	319.6	319.2	318.9	318.7
117.5°	360.2	361.6	363.0	364.5	365.9	366.1	365.1	364.2	363.1	362.1	361.7
120°	389.9	391.3	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9	389.9
122.5°	417.1	418.8	420.5	422.1	423.8	424.1	423.2	422.2	421.2	420.2	419.8
125°	459.4	461.0	462.5	464.1	465.7	466.3	465.7	465.1	464.6	464.1	463.6
127.5°	500.6	502.6	504.6	506.6	508.6	509.3	508.7	508.1	507.4	506.8	506.1
130°	526.5	528.8	531.1	533.3	535.6	536.5	536.2	535.8	535.5	535.2	534.8
132.5°	555.5	557.4	559.3	561.1	563.0	563.9	564.0	564.1	564.1	564.2	563.5
135°	594.4	596.3	598.2	600.2	602.1	603.2	603.6	603.9	604.3	604.6	604.5
137.5°	635.3	636.8	638.4	640.1	641.6	642.6	643.1	643.5	644.0	644.4	644.3
140°	659.9	661.5	663.1	664.6	666.2	667.4	668.3	669.2	670.0	671.0	671.0
142.5°	685.2	686.7	688.3	689.9	691.5	692.6	693.2	693.8	694.4	695.0	695.1
145°	721.4	722.7	724.0	725.2	726.4	727.5	728.6	729.6	730.6	731.7	732.0
147.5°	753.9	755.3	756.8	758.2	759.7	760.8	761.5	762.2	763.0	763.7	764.0
150°	776.0	777.0	778.0	779.1	780.1	781.0	781.7	782.4	783.2	783.9	784.4
152.5°	795.5	796.6	797.6	798.7	799.7	800.6	801.5	802.3	803.1	804.1	804.7
155°	824.9	825.4	826.0	826.5	827.0	827.5	828.0	828.6	829.1	829.6	830.5
157.5°	850.0	850.3	850.7	851.0	851.4	851.7	852.0	852.3	852.6	852.9	854.1
160°	865.2	865.5	865.9	866.2	866.6	866.8	867.0	867.2	867.4	867.5	868.6
162.5°	879.0	879.1	879.2	879.2	879.3	879.4	879.6	879.8	880.0	880.1	881.3
165°	897.5	897.4	897.2	897.0	896.8	896.7	896.7	896.7	896.7	896.7	898.0
167.5°	912.9	912.4	911.9	911.4	910.9	910.6	910.6	910.5	910.5	910.4	911.7
170°	921.2	920.7	920.1	919.6	919.1	918.7	918.6	918.4	918.2	918.0	919.3
172.5°	926.9	926.3	925.8	925.2	924.7	924.4	924.2	924.0	923.9	923.7	924.9
175°	933.8	933.3	932.7	932.2	931.7	931.3	930.9	930.6	930.2	929.9	931.1
177.5°	936.6	936.2	935.8	935.3	934.9	934.6	934.3	934.0	933.7	933.5	934.3
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331661-840

CATALOG NUMBER: SA2XXRDIP-C485D725U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	829.4	830.8	832.1	832.6	832.4	832.1	831.8	831.6
5°	822.8	824.4	825.9	826.4	825.9	825.4	824.9	824.4
7.5°	809.5	809.9	810.4	810.2	809.3	808.4	807.6	806.7
10°	796.2	795.7	795.2	794.5	793.5	792.4	791.4	790.4
12.5°	780.9	780.0	779.1	777.8	776.1	774.5	772.7	771.1
15°	752.3	749.2	746.0	743.6	741.8	740.2	738.5	736.9
17.5°	720.0	716.3	712.5	709.1	706.3	703.4	700.5	697.6
20°	697.5	693.4	689.1	685.2	681.6	677.8	674.2	670.4
22.5°	672.8	667.4	662.1	657.9	655.2	652.5	649.7	646.9
25°	631.9	625.0	618.1	613.4	610.9	608.3	605.9	603.4
27.5°	592.8	584.7	576.7	570.8	566.7	562.8	558.8	554.8
30°	565.1	556.6	548.1	541.5	536.9	532.5	528.0	523.4
32.5°	537.3	527.7	517.9	510.9	506.6	502.4	498.1	493.8
35°	494.0	483.4	472.9	465.7	462.1	458.4	454.7	451.0
37.5°	451.7	440.1	428.5	420.5	416.4	412.1	407.9	403.6
40°	423.4	411.5	399.6	391.5	387.2	382.8	378.4	374.1
42.5°	394.9	382.5	370.3	362.0	357.8	353.6	349.3	345.1
45°	353.3	341.4	329.5	321.5	317.5	313.5	309.4	305.5
47.5°	312.9	301.0	289.2	281.4	277.8	274.2	270.4	266.8
50°	286.8	275.3	263.7	256.2	252.7	249.1	245.6	242.1
52.5°	262.3	251.2	239.9	232.8	229.5	226.3	223.0	219.7
55°	225.0	214.9	204.9	198.2	195.1	191.9	188.7	185.5
57.5°	191.1	181.9	172.7	166.7	164.0	161.4	158.6	155.9
60°	167.6	159.2	150.6	145.0	142.3	139.6	136.9	134.2
62.5°	147.3	139.3	131.1	126.2	124.6	123.0	121.4	119.8
65°	119.9	114.1	108.5	105.3	104.8	104.3	103.8	103.3
67.5°	96.7	94.1	91.5	90.0	89.4	88.9	88.4	87.8
70°	84.1	82.5	80.8	79.6	79.0	78.3	77.6	77.0
72.5°	73.2	71.8	70.4	69.5	69.1	68.7	68.3	67.9
75°	58.0	56.9	55.6	54.9	54.8	54.6	54.4	54.3
77.5°	43.9	43.2	42.6	42.1	41.8	41.6	41.3	41.0
80°	34.8	34.2	33.5	33.2	33.2	33.2	33.2	33.2
82.5°	26.4	26.0	25.5	25.3	25.3	25.3	25.3	25.3
85°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
87.5°	9.9	9.7	9.5	9.5	9.5	9.5	9.6	9.6
90°	27.0	26.6	26.3	26.2	26.4	26.5	26.7	26.9
92.5°	25.2	25.3	25.3	25.4	25.4	25.5	25.5	25.5
95°	50.5	50.5	50.5	50.4	50.0	49.7	49.3	49.0
97.5°	84.9	84.9	84.9	84.9	84.9	84.8	84.8	84.7
100°	109.0	109.0	109.0	108.9	108.7	108.5	108.4	108.2
102.5°	135.1	135.2	135.4	135.3	135.2	135.0	134.8	134.6
105°	174.4	174.7	175.1	175.2	175.2	175.2	175.2	175.2
107.5°	216.7	216.8	217.0	216.7	215.9	215.1	214.3	213.5
110°	245.5	245.5	245.5	245.2	244.7	244.2	243.7	243.1





TEST NUMBER: P331661-840

CATALOG NUMBER: SA2XXRDIP-C485D725U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	274.3	273.9	273.5	273.1	272.7	272.3	272.0	271.6
115°	318.5	318.4	318.2	317.8	317.3	316.8	316.3	315.8
117.5°	361.3	360.9	360.4	360.0	359.5	358.9	358.4	357.9
120°	389.9	389.9	389.9	389.7	389.1	388.6	388.1	387.6
122.5°	419.4	419.0	418.6	418.2	417.8	417.4	417.0	416.7
125°	463.1	462.5	462.0	461.7	461.5	461.3	461.2	461.0
127.5°	505.5	504.8	504.2	503.6	503.1	502.5	502.0	501.4
130°	534.5	534.1	533.8	533.2	532.5	531.9	531.2	530.5
132.5°	562.7	561.9	561.2	560.5	559.9	559.4	558.8	558.3
135°	604.3	604.1	603.9	603.6	603.1	602.6	602.0	601.5
137.5°	644.2	644.0	643.9	643.5	642.8	642.1	641.4	640.7
140°	671.0	671.0	671.0	670.6	669.9	669.2	668.5	667.8
142.5°	695.2	695.4	695.5	695.2	694.5	693.8	693.2	692.5
145°	732.1	732.3	732.5	732.2	731.4	730.7	730.0	729.3
147.5°	764.4	764.8	765.2	765.1	764.4	763.7	763.1	762.3
150°	784.9	785.4	786.0	786.0	785.4	784.9	784.4	783.9
152.5°	805.4	806.1	806.7	806.7	806.1	805.4	804.7	804.1
155°	831.3	832.2	833.1	833.3	832.7	832.2	831.7	831.2
157.5°	855.4	856.6	857.8	857.9	857.1	856.3	855.4	854.5
160°	869.6	870.7	871.7	871.9	871.2	870.5	869.8	869.1
162.5°	882.5	883.7	884.9	885.0	884.2	883.4	882.5	881.7
165°	899.2	900.4	901.6	901.8	900.9	900.0	899.2	898.3
167.5°	912.9	914.1	915.3	915.5	914.6	913.7	912.8	911.9
170°	920.5	921.7	922.9	923.0	922.0	920.9	919.9	918.8
172.5°	926.1	927.4	928.6	928.7	927.7	926.6	925.5	924.5
175°	932.3	933.5	934.7	934.8	933.8	932.7	931.7	930.7
177.5°	935.1	936.0	936.9	936.9	936.0	935.1	934.3	933.5
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3

(END OF REPORT)