

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332615-830

Luminaire Tested: **SA4XXDIP-C795D1035U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332615-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D1035U830-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6696.7 lumens
Efficiency: N/A
Efficacy: 128.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332615-830
CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332615-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46	40	40	40	40	
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38	34	34	34	34	
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33	29	29	29	29	
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28	25	25	25	25	
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25	21	21	21	21	
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19	19	19	19	
7	58	45	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17	17	17	17	
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15	15	15	15	
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	13	13	13	13	
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12	12	12	12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10101	10101	10101
5°	10131	10009	10083
10°	10067	9928	9977
15°	9947	9787	9812
20°	9784	9613	9620
25°	9600	9413	9386
30°	9374	9177	9093
35°	9140	8932	8814
40°	8896	8652	8495
45°	8643	8379	8218
50°	8361	8133	7882
55°	8058	7817	7562
60°	7753	7463	7237
65°	7412	7125	6837
70°	7027	6675	6413
75°	6441	6129	5973
80°	5732	5500	5360
85°	5011	4826	4733



TEST NUMBER: P332615-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	1.8
10°-20°	332.0	5.0
20°-30°	488.6	7.3
30°-40°	568.1	8.5
40°-50°	568.1	8.5
50°-60°	496.9	7.4
60°-70°	369.0	5.5
70°-80°	209.7	3.1
80°-90°	63.1	0.9
90°-100°	345.9	5.2
100°-110°	720.0	10.8
110°-120°	644.9	9.6
120°-130°	542.4	8.1
130°-140°	452.3	6.8
140°-150°	345.5	5.2
150°-160°	242.9	3.6
160°-170°	142.9	2.1
170°-180°	46.5	0.7
0°-30°	938.5	14.0
0°-40°	1506.5	22.5
0°-60°	2571.5	38.4
0°-90°	3213.4	48.0
90°-120°	1710.8	25.5
90°-150°	3051.1	45.6
90°-180°	3483.0	52.0
0°-180°	6696.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1251	1251	1251	1251	1251	
5°	1250	1246	1235	1245	1244	119
15°	1190	1185	1171	1176	1174	335
25°	1078	1070	1057	1057	1054	496
35°	927	920	906	899	894	580
45°	757	749	734	723	720	583
55°	572	569	555	544	537	513
65°	388	383	373	363	358	384
75°	206	202	196	193	192	219
85°	54	54	52	52	51	60
90°	1	8	17	19	20	5
95°	31	98	767	380	230	35
105°	110	159	617	1329	1324	117
115°	194	243	550	1058	1271	192
125°	270	321	548	900	1014	240
135°	321	382	543	799	907	248
145°	370	423	540	674	741	232
155°	421	454	525	595	620	194
165°	458	472	503	533	541	129
175°	478	479	483	489	487	45
180°	479	479	479	479	479	



TEST NUMBER: P332615-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2
2.5°	1254.4	1253.9	1253.3	1252.8	1252.3	1251.0	1249.1	1247.1	1245.1	1243.2	1244.9
5°	1250.2	1249.3	1248.4	1247.5	1246.6	1244.9	1242.5	1240.0	1237.6	1235.1	1237.6
7.5°	1238.6	1237.7	1236.8	1235.9	1235.0	1233.2	1230.5	1227.8	1225.0	1222.3	1224.3
10°	1228.1	1227.3	1226.3	1225.5	1224.6	1222.7	1219.7	1216.9	1214.0	1211.1	1212.9
12.5°	1214.5	1213.6	1212.7	1211.8	1211.0	1208.9	1205.9	1202.8	1199.8	1196.7	1198.6
15°	1190.1	1189.1	1188.3	1187.3	1186.5	1184.4	1181.0	1177.7	1174.3	1171.0	1172.3
17.5°	1160.6	1159.4	1158.3	1157.3	1156.1	1154.0	1150.8	1147.6	1144.4	1141.3	1142.2
20°	1138.9	1137.7	1136.7	1135.6	1134.4	1132.2	1128.9	1125.5	1122.2	1118.9	1119.6
22.5°	1115.7	1114.2	1112.7	1111.3	1109.7	1107.4	1104.0	1100.7	1097.3	1094.0	1095.2
25°	1077.7	1076.2	1074.6	1073.1	1071.5	1069.1	1066.0	1062.9	1059.8	1056.7	1056.9
27.5°	1034.4	1032.8	1031.2	1029.6	1028.0	1025.8	1022.8	1020.0	1017.1	1014.2	1013.6
30°	1005.6	1003.8	1002.0	1000.2	998.4	996.1	993.2	990.3	987.4	984.5	983.6
32.5°	975.1	973.5	971.9	970.3	968.7	966.3	963.3	960.2	957.2	954.0	953.0
35°	927.4	925.8	924.3	922.7	921.1	918.8	915.7	912.6	909.5	906.3	904.7
37.5°	877.0	875.6	874.2	872.8	871.3	868.9	865.6	862.2	858.9	855.5	853.8
40°	844.1	842.4	840.6	838.8	837.0	834.4	831.1	827.7	824.4	821.0	818.9
42.5°	808.9	807.8	806.7	805.7	804.6	802.2	798.5	794.8	791.1	787.4	784.9
45°	757.0	755.4	753.8	752.2	750.7	748.1	744.6	741.0	737.4	733.9	731.4
47.5°	702.6	701.5	700.5	699.4	698.3	696.2	692.9	689.6	686.3	683.0	680.1
50°	665.7	664.8	663.9	663.0	662.1	660.2	657.0	653.9	650.7	647.6	644.5
52.5°	629.6	628.6	627.5	626.4	625.3	623.1	619.8	616.5	613.2	609.9	607.2
55°	572.5	571.7	571.1	570.4	569.8	567.9	564.8	561.7	558.6	555.4	552.7
57.5°	517.9	517.2	516.4	515.7	514.9	512.9	509.9	506.8	503.8	500.7	498.1
60°	480.2	479.1	478.0	476.9	475.8	473.7	470.9	468.0	465.1	462.2	460.1
62.5°	443.4	442.4	441.5	440.5	439.6	437.6	434.5	431.4	428.4	425.3	423.5
65°	388.0	386.9	385.8	384.7	383.5	381.8	379.7	377.4	375.1	373.0	370.7
67.5°	332.2	331.2	330.2	329.1	328.2	326.6	324.4	322.3	320.2	318.0	315.8
70°	297.7	296.2	294.6	293.0	291.5	289.8	288.0	286.3	284.5	282.8	281.0
72.5°	260.9	259.3	257.8	256.2	254.6	253.2	251.8	250.2	248.8	247.4	246.0
75°	206.5	205.4	204.3	203.2	202.1	201.0	199.8	198.7	197.7	196.5	195.6
77.5°	154.6	154.1	153.6	153.2	152.6	151.9	150.9	150.0	148.9	148.0	147.7
80°	123.3	122.6	122.0	121.3	120.6	120.1	119.6	119.2	118.8	118.3	117.8
82.5°	92.8	92.6	92.2	91.9	91.6	91.4	91.3	91.2	91.1	91.0	90.8
85°	54.1	54.1	54.1	54.1	54.1	53.9	53.4	53.1	52.6	52.1	52.1
87.5°	21.0	21.2	21.6	21.7	21.7	21.5	22.4	22.2	22.4	22.6	22.4
90°	0.9	2.8	5.7	6.6	7.5	7.5	13.2	13.2	15.1	17.0	16.0
92.5°	10.7	15.6	24.5	35.9	49.7	69.3	117.1	190.1	261.2	298.5	248.6
95°	31.0	33.8	43.3	55.5	78.1	117.6	199.4	353.8	578.7	766.9	788.5
97.5°	55.7	55.7	63.8	75.1	94.4	127.6	190.7	318.0	541.6	807.7	990.6
100°	71.5	71.5	78.1	89.4	107.3	137.4	192.9	299.3	491.2	756.5	997.4
102.5°	86.5	88.0	93.9	104.4	121.6	150.1	200.4	294.0	457.3	692.6	940.9
105°	110.1	112.9	117.6	128.9	145.8	173.1	218.3	296.4	428.1	617.3	838.4
107.5°	136.1	138.0	142.6	154.7	170.9	197.7	239.2	310.3	422.8	575.1	755.5
110°	153.4	155.2	159.9	171.3	188.2	213.6	255.0	320.8	424.3	560.8	714.2



TEST NUMBER: P332615-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.9	171.8	177.3	187.8	204.7	230.2	270.0	332.2	428.9	554.0	690.9
115°	193.9	196.6	203.2	212.6	230.5	255.9	293.6	350.1	437.5	550.4	669.0
117.5°	218.7	221.3	227.2	237.5	254.2	280.6	316.3	368.3	446.8	549.5	659.2
120°	235.3	237.1	243.7	254.0	270.0	296.4	332.2	381.1	453.6	549.5	653.9
122.5°	250.3	252.1	258.7	268.3	285.9	311.4	347.2	393.1	460.3	548.7	647.9
125°	270.0	273.8	279.5	289.8	307.6	334.0	367.9	411.2	470.5	547.6	638.0
127.5°	287.6	290.6	297.4	309.2	327.8	354.4	387.1	426.8	478.5	545.5	624.6
130°	297.4	301.1	308.6	322.7	340.6	367.9	399.9	436.6	484.6	544.8	616.3
132.5°	307.1	310.1	319.9	333.3	352.7	378.4	410.5	446.4	489.8	544.0	608.8
135°	320.8	324.6	334.0	350.1	369.8	394.3	425.3	459.2	497.8	542.9	597.5
137.5°	334.6	338.2	348.6	363.7	384.3	407.6	436.6	468.3	502.5	542.7	587.7
140°	344.4	347.2	357.6	373.5	393.3	415.9	444.1	474.2	506.2	542.0	582.5
142.5°	355.0	357.8	367.3	382.6	401.6	423.4	450.9	478.7	509.3	542.0	578.0
145°	369.8	372.6	382.0	395.2	413.1	433.8	458.3	483.6	511.0	540.1	570.2
147.5°	386.5	387.5	395.8	409.3	424.1	442.8	465.8	488.0	511.9	536.7	563.3
150°	397.1	398.0	405.6	416.9	430.9	448.8	469.6	490.2	511.9	534.4	558.0
152.5°	406.9	407.1	414.6	425.1	437.7	454.1	472.6	491.7	510.4	530.7	552.0
155°	420.6	421.5	427.2	436.6	447.0	461.1	477.0	493.0	508.1	525.1	542.9
157.5°	433.9	433.9	439.2	446.6	455.6	466.7	480.2	493.0	505.7	519.2	533.7
160°	442.2	442.2	446.0	452.6	460.1	470.5	481.7	493.0	503.4	514.7	527.0
162.5°	449.8	449.0	452.0	457.9	464.7	472.8	483.2	493.0	501.1	510.2	520.9
165°	458.3	458.3	460.1	464.9	469.6	475.1	483.6	491.2	496.8	503.4	511.0
167.5°	466.7	465.8	466.7	470.3	473.0	477.2	483.4	488.9	492.3	496.6	501.9
170°	470.5	469.6	470.5	473.3	475.1	478.0	482.7	487.4	489.3	492.1	495.9
172.5°	474.2	473.3	473.4	475.5	476.6	478.7	481.9	485.9	486.3	487.6	490.6
175°	478.0	477.0	477.0	478.0	478.9	478.9	480.8	483.6	482.7	482.7	484.6
177.5°	479.7	478.9	478.2	478.9	478.9	478.9	479.7	481.2	479.7	479.7	480.4
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332615-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2
2.5°	1246.7	1248.5	1250.3	1251.1	1250.9	1250.8	1250.6	1250.4
5°	1240.0	1242.5	1244.9	1245.9	1245.5	1245.1	1244.6	1244.2
7.5°	1226.2	1228.2	1230.1	1231.0	1230.8	1230.5	1230.2	1229.9
10°	1214.7	1216.4	1218.2	1218.9	1218.4	1218.0	1217.6	1217.1
12.5°	1200.6	1202.5	1204.5	1205.1	1204.6	1203.9	1203.2	1202.7
15°	1173.7	1175.0	1176.3	1176.7	1176.0	1175.4	1174.7	1174.0
17.5°	1143.0	1143.9	1144.7	1144.9	1144.4	1144.0	1143.6	1143.1
20°	1120.2	1120.9	1121.5	1121.6	1121.2	1120.8	1120.3	1119.8
22.5°	1096.4	1097.6	1098.8	1099.0	1098.2	1097.4	1096.6	1095.8
25°	1057.2	1057.3	1057.6	1057.2	1056.4	1055.5	1054.6	1053.7
27.5°	1013.1	1012.6	1012.0	1011.3	1010.1	1009.0	1007.9	1006.7
30°	982.7	981.8	980.9	980.0	978.8	977.7	976.6	975.5
32.5°	951.9	950.8	949.8	948.7	947.5	946.4	945.3	944.2
35°	903.2	901.6	900.0	898.7	897.6	896.5	895.4	894.3
37.5°	852.2	850.5	848.9	847.3	845.7	844.3	842.8	841.3
40°	816.6	814.5	812.2	810.5	809.4	808.3	807.2	806.1
42.5°	782.2	779.7	777.0	775.4	774.7	773.9	773.2	772.4
45°	729.0	726.5	724.1	722.6	721.8	721.1	720.5	719.8
47.5°	677.4	674.7	671.8	669.7	668.0	666.3	664.6	662.9
50°	641.4	638.3	635.2	632.9	631.6	630.3	629.0	627.6
52.5°	604.5	601.6	598.9	596.7	595.0	593.3	591.6	589.9
55°	550.1	547.4	544.7	542.7	541.4	540.1	538.7	537.3
57.5°	495.6	493.0	490.5	488.6	487.3	486.0	484.7	483.4
60°	458.2	456.2	454.1	452.6	451.5	450.3	449.2	448.2
62.5°	421.6	419.8	418.0	416.5	415.4	414.2	413.2	412.1
65°	368.5	366.3	364.0	362.4	361.3	360.1	359.0	357.9
67.5°	313.8	311.6	309.4	308.2	307.9	307.6	307.3	307.0
70°	279.2	277.4	275.6	274.4	273.7	273.1	272.4	271.7
72.5°	244.6	243.2	241.8	240.7	240.0	239.3	238.7	238.0
75°	194.7	193.8	192.9	192.4	192.2	191.9	191.7	191.5
77.5°	147.4	147.1	146.9	146.5	145.9	145.3	144.8	144.2
80°	117.4	117.0	116.5	116.2	115.9	115.7	115.6	115.3
82.5°	90.5	90.2	89.9	89.7	89.5	89.3	89.1	88.8
85°	52.1	52.1	52.1	52.0	51.8	51.6	51.4	51.1
87.5°	22.6	22.8	23.0	23.0	23.2	23.4	23.2	23.2
90°	17.0	17.9	18.9	18.9	19.8	20.7	19.8	19.8
92.5°	184.8	139.1	110.7	91.8	80.8	75.7	72.5	72.5
95°	697.2	551.4	425.3	334.0	287.9	258.7	241.9	229.6
97.5°	1030.2	975.9	883.9	785.7	718.1	661.5	633.3	613.7
100°	1134.8	1153.6	1107.5	1037.8	956.0	898.6	870.3	862.9
102.5°	1129.5	1222.9	1236.2	1207.2	1157.0	1115.4	1085.7	1079.7
105°	1053.9	1216.6	1309.8	1348.4	1350.3	1342.7	1329.6	1323.9
107.5°	946.4	1119.7	1250.9	1334.8	1381.3	1402.8	1412.2	1414.7
110°	881.7	1044.4	1180.9	1284.4	1351.2	1390.7	1407.7	1416.2



TEST NUMBER: P332615-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	834.2	978.2	1107.1	1210.6	1286.5	1334.3	1358.0	1371.7
115°	786.6	902.4	1012.5	1102.8	1177.1	1233.6	1263.7	1271.2
117.5°	763.3	859.1	945.7	1022.3	1085.7	1133.1	1163.6	1169.4
120°	752.7	840.3	915.6	982.3	1035.9	1077.4	1101.8	1112.2
122.5°	743.8	828.2	896.7	955.3	1000.6	1035.9	1056.7	1067.1
125°	728.3	809.2	874.1	925.9	963.6	990.8	1008.7	1014.4
127.5°	709.5	786.8	851.6	900.7	938.5	962.8	977.8	983.4
130°	694.5	768.7	832.7	882.6	921.1	944.7	959.8	965.4
132.5°	678.6	748.5	810.9	860.8	898.6	925.1	939.4	945.1
135°	656.8	717.9	775.3	822.4	860.1	886.4	901.4	907.1
137.5°	637.1	688.8	737.2	779.7	814.8	840.8	853.3	860.1
140°	625.8	670.0	712.3	751.8	784.8	805.5	818.6	826.1
142.5°	615.2	654.1	690.5	724.7	753.8	773.1	784.8	790.0
145°	600.3	632.4	660.5	686.9	710.4	726.4	735.8	740.6
147.5°	588.1	613.5	636.1	656.8	674.1	687.9	695.0	696.6
150°	580.6	602.2	621.0	638.0	653.0	665.2	670.9	671.8
152.5°	572.3	590.9	608.2	622.2	635.0	644.9	648.3	649.2
155°	559.9	575.0	589.0	600.3	609.7	617.3	620.1	620.1
157.5°	546.5	559.1	571.0	580.0	587.1	592.8	594.5	594.5
160°	538.2	548.6	558.9	566.5	572.1	577.8	578.7	578.7
162.5°	529.9	538.8	546.9	553.6	557.8	563.5	564.4	563.6
165°	518.5	524.1	530.7	535.4	539.1	542.9	542.0	541.0
167.5°	507.4	511.7	517.0	519.8	521.7	524.1	524.0	523.2
170°	500.6	503.4	507.2	510.0	511.9	512.8	511.9	511.9
172.5°	494.6	496.6	498.9	501.0	502.1	503.0	502.1	500.6
175°	486.4	487.4	489.3	489.3	489.3	491.2	489.3	487.4
177.5°	481.2	481.9	481.9	482.7	481.9	482.7	481.2	479.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9

(END OF REPORT)