

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331665-840

Luminaire Tested: **SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331665-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5527.5 lumens
Efficiency: N/A
Efficacy: 124.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	37	37	36	30
2	87	80	74	69	78	72	68	63	58	55	52	45	43	41	34	32	31	26
3	79	71	64	58	72	64	58	54	52	48	45	41	38	36	30	29	27	22
4	73	63	55	50	66	57	51	46	47	42	38	37	34	31	27	25	24	20
5	67	56	49	43	60	51	45	40	42	37	33	33	30	27	25	23	21	18
6	62	51	43	38	56	46	40	35	38	33	29	30	27	24	23	21	19	16
7	57	46	38	33	52	42	35	31	35	30	26	28	24	22	21	19	17	14
8	53	42	34	29	48	38	32	27	32	27	23	25	22	19	20	17	16	13
9	50	38	31	26	45	35	29	24	29	24	21	23	20	18	18	16	14	12
10	46	35	28	24	42	32	26	22	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17525	17525	17525	17525
5°	19571	17634	15635	17634
10°	21713	17510	13554	17510
15°	22781	17254	10678	17254
20°	19749	16873	9241	16873
25°	12953	16352	8250	16352
30°	8720	15720	7467	15720
35°	7062	14927	6733	14927
40°	6279	14060	6232	14060
45°	5683	13047	5562	13047
50°	5172	12039	5152	12039
55°	4861	10925	4799	10925
60°	4066	9901	4017	9901
65°	3431	8989	3889	8989
70°	3172	8030	3668	8030
75°	2969	6987	3387	6987
80°	2734	5746	3013	5746
85°	2501	4539	2649	4539



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.9	1.9
10°-20°	286.7	5.2
20°-30°	369.4	6.7
30°-40°	351.1	6.4
40°-50°	300.7	5.4
50°-60°	229.0	4.1
60°-70°	144.8	2.6
70°-80°	72.3	1.3
80°-90°	23.5	0.4
90°-100°	209.6	3.8
100°-110°	711.1	12.9
110°-120°	755.5	13.7
120°-130°	621.9	11.3
130°-140°	499.4	9.0
140°-150°	377.4	6.8
150°-160°	265.2	4.8
160°-170°	156.1	2.8
170°-180°	50.8	0.9
0°-30°	759.0	13.7
0°-40°	1110.1	20.1
0°-60°	1639.8	29.7
0°-90°	1880.5	34.0
90°-120°	1676.1	30.3
90°-150°	3174.8	57.4
90°-180°	3647.0	66.0
0°-180°	5527.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1085	1085	1085	1085	1085	
5°	1208	1088	965	1088	1208	119
15°	1363	1032	639	1032	1363	368
25°	727	918	463	918	727	345
35°	358	757	342	757	358	229
45°	249	571	244	571	249	193
55°	173	388	170	388	173	152
65°	90	235	102	235	90	91
75°	48	112	54	112	48	50
85°	14	24	14	24	14	15
90°	33	1	33	1	33	18
95°	115	35	115	35	115	149
105°	1136	123	1136	123	1136	1099
115°	1495	217	1495	217	1495	1464
125°	1212	302	1212	302	1212	1096
135°	1005	355	1005	355	1005	781
145°	802	405	802	405	802	510
155°	674	461	674	461	674	315
165°	592	502	592	502	592	169
175°	533	523	533	523	533	52
180°	524	524	524	524	524	



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1129.4	1130.3	1131.3	1129.1	1129.1	1127.3	1123.4	1120.3	1111.9	1110.6	1110.6
5°	1207.5	1206.8	1208.3	1203.4	1196.6	1195.1	1187.9	1178.5	1168.7	1157.7	1155.5
7.5°	1285.3	1284.1	1281.1	1280.2	1275.1	1263.6	1252.1	1239.8	1223.6	1207.6	1199.6
10°	1324.4	1336.9	1329.4	1316.2	1318.8	1301.1	1291.6	1275.5	1261.8	1238.1	1232.8
12.5°	1363.0	1368.0	1365.5	1358.1	1354.7	1342.4	1329.7	1315.6	1290.5	1269.2	1250.6
15°	1362.9	1370.1	1372.0	1369.7	1371.6	1370.8	1364.0	1352.3	1330.5	1307.1	1286.8
17.5°	1262.3	1267.3	1279.6	1288.0	1298.6	1320.9	1331.9	1336.3	1332.9	1319.6	1305.3
20°	1149.4	1141.1	1175.9	1193.6	1208.7	1246.4	1278.8	1291.2	1311.2	1310.9	1307.1
22.5°	989.6	991.5	1024.4	1045.4	1089.5	1127.2	1164.2	1211.0	1249.7	1275.3	1290.2
25°	727.1	741.4	774.3	802.8	851.9	922.1	985.8	1059.8	1129.4	1184.6	1237.0
27.5°	546.0	547.1	573.1	599.7	628.7	686.2	766.5	854.7	954.2	1036.2	1130.6
30°	467.7	465.3	476.4	492.5	517.5	561.9	622.3	709.0	808.2	931.9	1042.0
32.5°	412.1	412.2	420.5	432.5	453.1	483.1	524.5	594.9	688.7	810.3	939.4
35°	358.3	357.9	364.0	372.6	381.2	400.5	428.8	465.7	530.3	643.8	775.8
37.5°	319.6	321.3	324.3	329.7	339.2	349.9	367.0	391.7	437.7	504.8	615.7
40°	297.9	298.7	302.9	307.4	313.1	321.3	335.3	355.3	388.8	442.3	523.4
42.5°	278.0	278.7	281.8	285.9	290.3	298.7	310.2	327.5	354.8	396.5	463.4
45°	248.9	248.9	251.6	253.4	258.3	265.9	275.3	289.6	308.5	339.4	384.0
47.5°	221.6	221.7	223.4	226.6	229.7	235.6	244.9	256.6	270.3	294.3	332.2
50°	205.9	206.3	207.4	210.1	212.0	217.2	224.4	234.6	248.9	267.4	299.0
52.5°	193.2	193.0	194.4	195.6	196.8	200.7	206.0	215.0	227.8	243.9	270.1
55°	172.7	171.2	173.5	175.3	176.5	178.0	181.0	186.7	197.6	211.2	230.8
57.5°	147.0	146.4	148.0	149.8	153.3	157.4	160.0	163.6	169.3	178.9	198.4
60°	125.9	125.9	129.4	130.5	134.6	139.9	145.2	148.2	153.9	160.3	174.6
62.5°	107.2	107.6	109.2	110.3	112.6	119.1	126.5	133.1	138.5	144.6	154.1
65°	89.8	90.5	90.5	91.3	92.8	94.3	97.3	102.6	112.0	120.7	127.8
67.5°	76.1	76.4	76.6	77.4	77.8	79.4	80.6	83.0	85.1	93.4	102.3
70°	67.2	68.3	67.9	68.7	69.0	69.8	71.3	72.4	75.8	77.7	83.0
72.5°	58.7	59.5	59.5	59.9	60.9	61.0	62.2	63.3	65.5	67.2	70.0
75°	47.6	47.2	47.6	48.3	48.7	49.0	49.0	50.5	51.7	53.2	55.0
77.5°	36.7	37.1	37.0	37.1	37.1	37.8	37.7	38.4	39.5	40.3	41.2
80°	29.4	29.8	29.4	29.8	30.2	30.5	30.2	30.5	31.7	32.4	32.4
82.5°	22.8	22.8	23.1	23.1	23.2	23.3	23.8	23.9	24.7	24.5	24.8
85°	13.5	13.2	13.2	13.2	13.5	13.9	13.5	13.5	13.9	13.9	13.9
87.5°	11.5	11.8	11.8	11.8	11.8	11.6	11.2	11.9	11.8	12.3	11.8
90°	33.2	33.2	33.2	33.2	33.2	32.2	30.2	32.2	33.2	34.2	33.2
92.5°	55.8	57.5	56.7	59.9	60.7	67.0	75.4	87.9	110.7	131.0	129.2
95°	114.9	113.9	116.9	125.0	138.0	160.3	202.6	264.1	345.7	395.1	349.7
97.5°	226.2	234.6	249.3	274.2	322.3	395.1	504.1	616.2	707.5	674.5	508.0
100°	360.8	379.0	408.2	451.5	535.2	657.1	795.2	920.2	941.4	796.2	548.3
102.5°	635.0	659.5	696.0	770.0	860.9	990.2	1091.2	1119.3	1028.4	800.2	533.0
105°	1135.9	1149.9	1193.4	1255.8	1318.3	1351.6	1338.5	1224.6	1014.9	746.8	502.9
107.5°	1451.0	1469.7	1478.3	1481.8	1473.9	1425.1	1320.3	1148.8	926.5	689.6	488.0
110°	1546.1	1547.1	1538.0	1518.8	1475.5	1392.9	1263.8	1083.5	870.8	662.2	484.8



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1544.5	1539.0	1521.9	1489.9	1429.6	1334.8	1197.0	1023.8	832.1	644.4	485.5
115°	1494.7	1485.6	1459.4	1413.0	1341.5	1237.7	1105.6	950.4	784.2	624.9	489.8
117.5°	1405.7	1398.2	1370.5	1321.5	1248.6	1151.1	1031.5	895.1	753.9	615.4	497.1
120°	1348.6	1338.5	1309.2	1261.8	1191.3	1099.5	992.8	867.8	737.8	609.8	501.9
122.5°	1288.9	1280.4	1254.4	1207.8	1144.6	1061.7	960.5	846.0	724.1	606.5	507.6
125°	1212.4	1204.4	1179.2	1140.9	1082.5	1006.8	918.2	814.4	704.5	600.7	516.0
127.5°	1145.6	1139.1	1117.3	1081.5	1030.5	960.7	877.1	783.2	686.4	597.2	524.7
130°	1107.6	1099.5	1079.4	1045.2	995.8	929.3	849.6	763.0	674.3	595.6	531.2
132.5°	1068.1	1060.9	1042.4	1008.0	959.5	897.0	823.8	743.6	664.6	594.8	537.6
135°	1004.8	1000.8	982.7	949.4	906.1	849.6	783.2	716.6	651.1	593.6	545.2
137.5°	942.8	936.8	920.8	892.2	852.6	803.4	750.6	695.0	641.6	593.4	552.1
140°	900.0	894.0	878.9	852.6	820.4	776.1	729.7	681.4	636.0	592.6	555.3
142.5°	857.3	856.1	842.6	818.8	788.2	751.0	711.1	670.0	630.4	592.6	557.7
145°	802.2	799.2	789.2	772.0	747.8	718.6	687.4	654.1	622.9	590.6	560.4
147.5°	756.1	754.3	747.4	733.8	713.8	692.4	668.0	641.8	615.2	587.0	561.2
150°	728.7	727.7	721.6	709.5	694.4	676.3	655.1	633.0	608.7	584.6	560.4
152.5°	705.3	705.1	700.6	690.1	678.3	662.6	644.6	624.1	603.1	580.6	558.8
155°	674.3	676.3	672.3	665.2	654.1	643.0	627.9	611.8	592.6	573.5	556.3
157.5°	647.8	647.8	646.0	640.2	632.4	623.7	611.0	597.4	582.8	566.2	551.7
160°	631.0	631.0	630.0	624.9	617.8	610.8	599.7	588.5	575.5	561.4	549.3
162.5°	614.8	615.6	614.6	611.2	604.1	598.6	589.2	579.8	569.1	557.3	546.8
165°	591.6	592.6	592.6	588.5	584.6	580.6	573.5	566.4	558.4	549.3	542.2
167.5°	570.3	571.5	571.7	569.5	567.6	564.0	559.2	553.7	547.9	542.2	537.6
170°	557.3	559.4	560.4	557.3	556.3	554.3	550.3	547.2	542.2	538.2	535.2
172.5°	546.8	548.1	549.1	547.6	546.6	545.4	542.2	540.0	536.6	533.4	532.0
175°	533.2	535.2	536.2	535.2	535.2	534.2	533.2	532.2	529.2	528.2	527.1
177.5°	524.9	526.5	527.4	527.4	527.4	527.4	526.5	526.5	524.9	524.1	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1111.3	1108.9	1106.8	1101.4	1098.6	1092.6	1091.7	1091.4	1083.6	1076.0	1073.9
5°	1149.4	1143.5	1134.4	1123.8	1112.9	1101.6	1094.0	1088.0	1072.9	1058.5	1050.3
7.5°	1187.9	1175.0	1159.3	1139.3	1122.7	1104.0	1090.1	1077.6	1056.2	1035.7	1021.9
10°	1216.6	1195.5	1174.8	1147.2	1125.7	1104.6	1085.0	1068.0	1043.9	1016.7	997.4
12.5°	1234.4	1211.1	1182.6	1155.7	1127.8	1101.0	1074.7	1052.9	1024.6	996.5	973.6
15°	1258.5	1233.6	1198.9	1160.4	1124.6	1089.5	1059.3	1032.2	995.2	961.7	933.7
17.5°	1278.2	1243.9	1206.6	1162.2	1120.6	1076.1	1037.2	1002.5	961.4	920.9	888.1
20°	1284.4	1250.5	1207.5	1163.1	1114.0	1061.6	1019.8	982.0	937.9	893.7	856.1
22.5°	1280.5	1254.2	1206.3	1153.1	1102.9	1048.0	1000.8	956.9	908.1	863.0	819.3
25°	1253.9	1244.9	1199.6	1141.6	1084.2	1020.5	965.8	917.9	862.1	813.9	766.3
27.5°	1191.8	1211.4	1183.4	1121.5	1057.7	989.4	928.0	873.4	815.5	761.1	713.8
30°	1132.2	1177.0	1164.9	1107.6	1036.3	969.2	900.2	843.2	781.4	725.6	678.8
32.5°	1050.4	1124.5	1136.3	1088.3	1014.6	940.8	868.5	811.8	747.3	688.4	642.9
35°	920.2	1031.1	1082.0	1051.4	977.4	898.0	823.2	757.3	692.4	634.3	589.1
37.5°	764.9	915.8	1000.8	1002.9	935.0	852.3	771.0	705.5	639.0	582.1	533.1
40°	664.1	827.8	938.3	962.8	905.4	816.1	733.9	667.1	602.3	546.4	490.3
42.5°	573.6	736.7	872.5	915.1	869.6	780.8	698.3	628.5	565.4	512.6	455.2
45°	463.8	606.4	756.1	832.3	807.1	724.8	637.7	571.4	512.1	466.5	411.4
47.5°	391.3	491.8	636.6	739.7	739.2	664.2	578.6	514.9	460.0	417.3	372.6
50°	349.9	437.5	560.1	676.9	686.7	623.8	542.3	479.3	428.1	383.1	347.3
52.5°	312.9	385.0	495.1	607.2	635.1	580.6	501.6	443.4	393.6	352.3	321.6
55°	264.4	320.1	403.9	508.8	551.0	512.5	442.3	388.1	347.7	313.1	286.6
57.5°	223.6	265.5	332.6	417.1	466.3	442.0	384.3	340.1	305.6	274.2	253.4
60°	198.0	232.3	289.2	359.8	414.0	397.1	347.7	306.6	277.2	250.0	230.5
62.5°	173.9	203.4	252.2	309.4	359.2	352.1	311.8	277.3	251.6	226.8	210.3
65°	139.9	161.4	199.4	244.4	284.4	287.7	258.7	235.3	212.3	192.7	178.0
67.5°	111.4	125.4	152.3	190.1	220.0	230.8	213.0	195.1	176.8	161.7	149.0
70°	93.9	105.2	124.8	155.4	182.9	194.2	184.0	170.1	154.2	141.8	130.9
72.5°	76.1	87.2	101.6	124.0	147.6	159.9	156.3	146.2	133.4	123.1	112.8
75°	57.4	60.7	70.5	85.6	104.1	114.6	117.2	112.0	101.8	93.9	87.9
77.5°	42.4	44.4	49.1	57.1	69.1	78.5	82.4	81.8	74.7	70.2	64.5
80°	33.9	35.0	37.4	40.7	49.8	59.2	61.8	61.8	57.0	55.0	49.4
82.5°	25.8	26.7	28.0	29.9	34.1	42.3	45.2	45.8	42.7	40.3	35.9
85°	14.7	14.3	15.0	16.3	17.0	19.2	23.7	24.5	23.7	20.7	19.6
87.5°	10.6	9.5	8.5	7.6	7.5	7.4	8.1	9.0	8.4	8.3	8.1
90°	27.2	20.2	15.1	12.1	10.1	8.1	4.0	1.0	4.0	8.1	10.1
92.5°	100.6	68.6	45.7	36.3	29.4	25.0	17.8	12.3	17.8	25.0	29.4
95°	232.8	145.1	98.8	74.6	58.5	49.4	39.3	35.2	39.3	49.4	58.5
97.5°	313.7	191.5	133.2	105.8	87.3	73.6	62.9	57.5	62.9	73.6	87.3
100°	330.6	207.6	154.2	126.0	105.8	89.7	80.6	77.6	80.6	89.7	105.8
102.5°	331.4	222.2	172.8	144.5	123.6	107.4	98.4	96.1	98.4	107.4	123.6
105°	336.6	246.9	199.5	171.4	149.2	134.0	127.0	123.0	127.0	134.0	149.2
107.5°	350.5	272.4	226.4	197.9	176.0	162.1	155.2	152.0	155.2	162.1	176.0
110°	361.8	289.2	244.9	215.7	194.5	181.4	175.4	171.4	175.4	181.4	194.5



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	374.0	305.4	262.7	232.6	212.3	200.0	193.1	189.0	193.1	200.0	212.3
115°	392.0	330.6	287.2	260.0	239.8	227.8	221.8	216.7	221.8	227.8	239.8
117.5°	411.4	353.8	313.7	285.4	266.1	255.4	249.3	245.3	249.3	255.4	266.1
120°	424.3	369.9	330.6	302.4	282.2	273.2	267.1	263.1	267.1	273.2	282.2
122.5°	435.6	385.2	348.3	319.3	299.1	289.2	283.2	280.0	283.2	289.2	299.1
125°	453.5	408.2	371.9	343.7	323.6	311.4	305.4	302.4	305.4	311.4	323.6
127.5°	470.3	429.6	394.3	365.3	345.9	332.5	324.2	320.1	324.2	332.5	345.9
130°	480.8	442.4	407.2	379.0	358.8	344.7	334.6	330.6	334.6	344.7	358.8
132.5°	491.2	453.7	420.1	391.8	370.9	356.0	345.1	340.2	345.1	356.0	370.9
135°	504.9	469.7	437.4	409.2	386.0	370.9	358.8	354.8	358.8	370.9	386.0
137.5°	515.4	482.6	450.7	424.5	401.5	385.4	373.3	368.5	373.3	385.4	401.5
140°	521.1	489.8	459.6	433.4	411.2	395.1	383.0	379.0	383.0	395.1	411.2
142.5°	525.9	495.4	466.1	441.4	420.1	403.9	392.6	389.4	392.6	403.9	420.1
145°	532.2	503.9	476.8	454.5	434.4	419.3	409.2	405.2	409.2	419.3	434.4
147.5°	535.6	510.8	485.2	465.4	448.7	434.7	425.2	422.1	425.2	434.7	448.7
150°	537.1	514.0	490.8	472.7	457.6	444.4	436.4	433.4	436.4	444.4	457.6
152.5°	538.0	517.3	496.4	480.0	465.6	454.1	446.1	444.6	446.1	454.1	465.6
155°	539.2	522.1	504.9	489.8	478.8	467.7	461.6	460.6	461.6	467.7	478.8
157.5°	539.2	525.5	511.0	498.3	489.4	479.8	474.9	473.9	474.9	479.8	489.4
160°	539.2	527.1	515.0	503.9	495.8	487.8	483.8	482.8	483.8	487.8	495.8
162.5°	538.4	528.0	517.5	508.8	501.5	495.0	491.0	491.6	491.0	495.0	501.5
165°	536.2	529.2	520.1	514.0	509.0	502.9	500.9	501.9	500.9	502.9	509.0
167.5°	534.8	529.0	522.3	518.5	514.8	511.0	509.2	510.4	509.2	511.0	514.8
170°	533.2	528.2	523.1	520.1	518.1	515.0	514.0	516.0	514.0	515.0	518.1
172.5°	530.8	527.4	523.9	521.7	520.5	517.5	518.1	519.3	518.1	517.5	520.5
175°	528.2	526.1	524.1	523.1	523.1	521.1	522.1	523.1	522.1	521.1	523.1
177.5°	526.5	524.9	524.1	524.1	524.1	522.5	523.3	524.9	523.3	522.5	524.1
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1070.0	1067.8	1063.9	1057.9	1054.3	1047.9	1043.7	1046.1	1046.7	1046.1	1045.5
5°	1041.3	1033.3	1022.4	1011.8	1002.0	991.5	985.4	982.8	977.4	974.5	973.0
7.5°	1006.4	992.8	977.3	959.0	943.3	927.0	918.6	914.4	903.6	897.8	892.6
10°	980.5	959.0	943.5	919.4	904.7	883.2	868.5	868.9	854.1	845.9	839.8
12.5°	951.9	928.3	902.5	880.8	860.4	843.1	825.4	818.2	802.5	794.6	778.3
15°	904.3	876.8	849.7	820.2	799.5	772.7	747.1	715.8	690.5	668.6	662.6
17.5°	852.4	818.4	791.1	756.6	721.0	676.0	646.3	628.1	612.9	601.4	592.8
20°	816.9	782.1	753.2	701.0	653.2	622.6	600.8	586.8	571.0	558.6	551.7
22.5°	779.4	743.3	703.7	645.5	608.2	583.7	564.2	548.2	537.5	527.8	521.6
25°	726.3	686.7	621.5	581.5	551.4	525.7	512.1	502.3	491.0	477.8	471.8
27.5°	670.2	607.2	560.4	530.7	501.9	485.2	473.0	458.4	448.3	442.3	436.1
30°	628.2	565.3	528.8	496.2	475.9	457.5	443.1	434.8	425.1	414.9	410.7
32.5°	581.5	531.2	496.1	469.2	448.5	432.7	421.4	408.0	400.9	394.7	386.0
35°	523.4	485.3	453.3	431.4	411.8	399.0	385.8	377.9	365.1	359.8	356.4
37.5°	474.2	441.2	417.3	394.3	378.7	364.6	356.5	343.9	338.3	330.9	323.8
40°	446.5	414.0	391.1	372.2	354.9	344.3	334.2	324.0	315.7	312.3	303.6
42.5°	418.2	391.7	368.7	348.1	336.5	325.3	312.5	305.0	296.3	290.8	285.5
45°	379.0	355.7	336.0	319.0	306.2	294.6	286.2	273.8	268.9	257.9	253.4
47.5°	344.6	322.9	304.2	288.0	275.5	267.9	255.8	246.0	238.2	231.5	225.7
50°	320.1	302.1	284.0	269.6	258.3	247.4	235.0	230.0	217.9	214.6	211.2
52.5°	297.8	280.6	264.1	250.0	238.7	228.1	217.1	210.8	202.6	199.1	196.7
55°	266.6	250.0	234.2	221.8	210.5	199.4	192.7	184.8	181.0	178.3	175.3
57.5°	235.2	220.4	208.1	195.6	184.2	175.5	167.6	162.9	159.0	155.5	151.9
60°	215.3	201.0	190.1	178.3	166.7	159.6	153.5	147.8	143.3	138.0	136.5
62.5°	194.2	181.7	171.7	160.3	150.1	143.5	137.8	132.5	127.0	119.4	117.2
65°	165.2	155.4	144.8	135.4	126.3	120.0	111.6	105.6	103.3	102.6	102.2
67.5°	139.0	129.7	120.6	111.0	102.7	96.7	92.5	91.6	90.1	89.6	88.6
70°	121.4	112.8	103.7	94.6	86.7	85.6	84.1	82.6	80.7	80.0	79.2
72.5°	105.7	96.7	87.8	80.5	77.1	75.6	74.1	72.6	71.4	70.6	70.2
75°	81.1	72.8	66.8	64.1	62.2	61.1	58.9	57.7	57.0	55.8	55.4
77.5°	58.4	53.7	50.9	49.3	47.3	46.0	44.8	43.6	42.8	42.6	42.0
80°	44.5	42.2	40.4	38.1	37.4	35.9	35.4	34.3	34.7	33.5	33.5
82.5°	34.5	31.7	30.1	29.1	28.3	27.1	26.7	26.2	26.3	25.4	25.4
85°	17.8	17.0	16.3	15.5	15.5	14.3	14.7	14.3	14.3	13.5	13.2
87.5°	8.2	8.5	8.9	10.3	11.5	11.4	11.2	10.7	10.3	10.7	10.6
90°	12.1	15.1	20.2	27.2	33.2	34.2	33.2	32.2	30.2	32.2	33.2
92.5°	36.3	45.7	68.6	100.6	129.2	131.0	110.7	87.9	75.4	67.0	60.7
95°	74.6	98.8	145.1	232.8	349.7	395.1	345.7	264.1	202.6	160.3	138.0
97.5°	105.8	133.2	191.5	313.7	508.0	674.5	707.5	616.2	504.1	395.1	322.3
100°	126.0	154.2	207.6	330.6	548.3	796.2	941.4	920.2	795.2	657.1	535.2
102.5°	144.5	172.8	222.2	331.4	533.0	800.2	1028.4	1119.3	1091.2	990.2	860.9
105°	171.4	199.5	246.9	336.6	502.9	746.8	1014.9	1224.6	1338.5	1351.6	1318.3
107.5°	197.9	226.4	272.4	350.5	488.0	689.6	926.5	1148.8	1320.3	1425.1	1473.9
110°	215.7	244.9	289.2	361.8	484.8	662.2	870.8	1083.5	1263.8	1392.9	1475.5



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	232.6	262.7	305.4	374.0	485.5	644.4	832.1	1023.8	1197.0	1334.8	1429.6
115°	260.0	287.2	330.6	392.0	489.8	624.9	784.2	950.4	1105.6	1237.7	1341.5
117.5°	285.4	313.7	353.8	411.4	497.1	615.4	753.9	895.1	1031.5	1151.1	1248.6
120°	302.4	330.6	369.9	424.3	501.9	609.8	737.8	867.8	992.8	1099.5	1191.3
122.5°	319.3	348.3	385.2	435.6	507.6	606.5	724.1	846.0	960.5	1061.7	1144.6
125°	343.7	371.9	408.2	453.5	516.0	600.7	704.5	814.4	918.2	1006.8	1082.5
127.5°	365.3	394.3	429.6	470.3	524.7	597.2	686.4	783.2	877.1	960.7	1030.5
130°	379.0	407.2	442.4	480.8	531.2	595.6	674.3	763.0	849.6	929.3	995.8
132.5°	391.8	420.1	453.7	491.2	537.6	594.8	664.6	743.6	823.8	897.0	959.5
135°	409.2	437.4	469.7	504.9	545.2	593.6	651.1	716.6	783.2	849.6	906.1
137.5°	424.5	450.7	482.6	515.4	552.1	593.4	641.6	695.0	750.6	803.4	852.6
140°	433.4	459.6	489.8	521.1	555.3	592.6	636.0	681.4	729.7	776.1	820.4
142.5°	441.4	466.1	495.4	525.9	557.7	592.6	630.4	670.0	711.1	751.0	788.2
145°	454.5	476.8	503.9	532.2	560.4	590.6	622.9	654.1	687.4	718.6	747.8
147.5°	465.4	485.2	510.8	535.6	561.2	587.0	615.2	641.8	668.0	692.4	713.8
150°	472.7	490.8	514.0	537.1	560.4	584.6	608.7	633.0	655.1	676.3	694.4
152.5°	480.0	496.4	517.3	538.0	558.8	580.6	603.1	624.1	644.6	662.6	678.3
155°	489.8	504.9	522.1	539.2	556.3	573.5	592.6	611.8	627.9	643.0	654.1
157.5°	498.3	511.0	525.5	539.2	551.7	566.2	582.8	597.4	611.0	623.7	632.4
160°	503.9	515.0	527.1	539.2	549.3	561.4	575.5	588.5	599.7	610.8	617.8
162.5°	508.8	517.5	528.0	538.4	546.8	557.3	569.1	579.8	589.2	598.6	604.1
165°	514.0	520.1	529.2	536.2	542.2	549.3	558.4	566.4	573.5	580.6	584.6
167.5°	518.5	522.3	529.0	534.8	537.6	542.2	547.9	553.7	559.2	564.0	567.6
170°	520.1	523.1	528.2	533.2	535.2	538.2	542.2	547.2	550.3	554.3	556.3
172.5°	521.7	523.9	527.4	530.8	532.0	533.4	536.6	540.0	542.2	545.4	546.6
175°	523.1	524.1	526.1	528.2	527.1	528.2	529.2	532.2	533.2	534.2	535.2
177.5°	524.1	524.1	524.9	526.5	524.9	524.1	524.9	526.5	526.5	527.4	527.4
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1042.2	1042.8	1041.9	1042.5	1041.9	1042.8	1042.2	1045.5	1046.1	1046.7	1046.1
5°	971.1	966.5	965.8	964.7	965.8	966.5	971.1	973.0	974.5	977.4	982.8
7.5°	886.2	885.4	883.6	880.9	883.6	885.4	886.2	892.6	897.8	903.6	914.4
10°	831.5	829.7	829.3	826.7	829.3	829.7	831.5	839.8	845.9	854.1	868.9
12.5°	767.6	755.5	754.2	747.6	754.2	755.5	767.6	778.3	794.6	802.5	818.2
15°	653.6	651.3	643.8	638.8	643.8	651.3	653.6	662.6	668.6	690.5	715.8
17.5°	588.3	581.0	578.7	577.6	578.7	581.0	588.3	592.8	601.4	612.9	628.1
20°	546.4	539.7	538.6	537.8	538.6	539.7	546.4	551.7	558.6	571.0	586.8
22.5°	517.5	510.4	507.5	505.2	507.5	510.4	517.5	521.6	527.8	537.5	548.2
25°	468.0	465.3	463.8	463.1	463.8	465.3	468.0	471.8	477.8	491.0	502.3
27.5°	429.3	423.5	422.3	420.4	422.3	423.5	429.3	436.1	442.3	448.3	458.4
30°	407.3	405.4	402.7	400.5	402.7	405.4	407.3	410.7	414.9	425.1	434.8
32.5°	381.3	379.8	377.4	376.4	377.4	379.8	381.3	386.0	394.7	400.9	408.0
35°	352.6	347.3	345.1	341.6	345.1	347.3	352.6	356.4	359.8	365.1	377.9
37.5°	322.2	319.4	316.3	317.4	316.3	319.4	322.2	323.8	330.9	338.3	343.9
40°	298.7	296.8	296.0	295.7	296.0	296.8	298.7	303.6	312.3	315.7	324.0
42.5°	279.9	274.8	272.8	272.8	272.8	274.8	279.9	285.5	290.8	296.3	305.0
45°	251.6	246.6	243.3	243.6	243.3	246.6	251.6	253.4	257.9	268.9	273.8
47.5°	222.5	222.3	220.2	220.9	220.2	222.3	222.5	225.7	231.5	238.2	246.0
50°	208.5	206.3	204.8	205.1	204.8	206.3	208.5	211.2	214.6	217.9	230.0
52.5°	195.3	193.3	192.1	193.7	192.1	193.3	195.3	196.7	199.1	202.6	210.8
55°	173.5	171.2	170.9	170.5	170.9	171.2	173.5	175.3	178.3	181.0	184.8
57.5°	149.2	147.6	145.3	144.4	145.3	147.6	149.2	151.9	155.5	159.0	162.9
60°	131.6	128.6	124.8	124.4	124.8	128.6	131.6	136.5	138.0	143.3	147.8
62.5°	115.6	115.0	114.3	114.2	114.3	115.0	115.6	117.2	119.4	127.0	132.5
65°	101.5	101.1	101.5	101.8	101.5	101.1	101.5	102.2	102.6	103.3	105.6
67.5°	88.4	87.8	87.1	87.4	87.1	87.8	88.4	88.6	89.6	90.1	91.6
70°	78.5	78.1	77.7	77.7	77.7	78.1	78.5	79.2	80.0	80.7	82.6
72.5°	68.8	68.7	68.4	68.1	68.4	68.7	68.8	70.2	70.6	71.4	72.6
75°	55.0	54.3	54.3	54.3	54.3	54.3	55.0	55.4	55.8	57.0	57.7
77.5°	41.9	41.6	41.2	40.9	41.2	41.6	41.9	42.0	42.6	42.8	43.6
80°	33.2	32.8	32.4	32.4	32.4	32.8	33.2	33.5	33.5	34.7	34.3
82.5°	25.3	24.9	24.8	24.5	24.8	24.9	25.3	25.4	25.4	26.3	26.2
85°	13.5	13.9	13.5	14.3	13.5	13.9	13.5	13.2	13.5	14.3	14.3
87.5°	10.6	10.3	10.6	10.3	10.6	10.3	10.6	10.6	10.7	10.3	10.7
90°	33.2	33.2	33.2	33.2	33.2	33.2	33.2	33.2	32.2	30.2	32.2
92.5°	59.9	56.7	57.5	55.8	57.5	56.7	59.9	60.7	67.0	75.4	87.9
95°	125.0	116.9	113.9	114.9	113.9	116.9	125.0	138.0	160.3	202.6	264.1
97.5°	274.2	249.3	234.6	226.2	234.6	249.3	274.2	322.3	395.1	504.1	616.2
100°	451.5	408.2	379.0	360.8	379.0	408.2	451.5	535.2	657.1	795.2	920.2
102.5°	770.0	696.0	659.5	635.0	659.5	696.0	770.0	860.9	990.2	1091.2	1119.3
105°	1255.8	1193.4	1149.9	1135.9	1149.9	1193.4	1255.8	1318.3	1351.6	1338.5	1224.6
107.5°	1481.8	1478.3	1469.7	1451.0	1469.7	1478.3	1481.8	1473.9	1425.1	1320.3	1148.8
110°	1518.8	1538.0	1547.1	1546.1	1547.1	1538.0	1518.8	1475.5	1392.9	1263.8	1083.5



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1489.9	1521.9	1539.0	1544.5	1539.0	1521.9	1489.9	1429.6	1334.8	1197.0	1023.8
115°	1413.0	1459.4	1485.6	1494.7	1485.6	1459.4	1413.0	1341.5	1237.7	1105.6	950.4
117.5°	1321.5	1370.5	1398.2	1405.7	1398.2	1370.5	1321.5	1248.6	1151.1	1031.5	895.1
120°	1261.8	1309.2	1338.5	1348.6	1338.5	1309.2	1261.8	1191.3	1099.5	992.8	867.8
122.5°	1207.8	1254.4	1280.4	1288.9	1280.4	1254.4	1207.8	1144.6	1061.7	960.5	846.0
125°	1140.9	1179.2	1204.4	1212.4	1204.4	1179.2	1140.9	1082.5	1006.8	918.2	814.4
127.5°	1081.5	1117.3	1139.1	1145.6	1139.1	1117.3	1081.5	1030.5	960.7	877.1	783.2
130°	1045.2	1079.4	1099.5	1107.6	1099.5	1079.4	1045.2	995.8	929.3	849.6	763.0
132.5°	1008.0	1042.4	1060.9	1068.1	1060.9	1042.4	1008.0	959.5	897.0	823.8	743.6
135°	949.4	982.7	1000.8	1004.8	1000.8	982.7	949.4	906.1	849.6	783.2	716.6
137.5°	892.2	920.8	936.8	942.8	936.8	920.8	892.2	852.6	803.4	750.6	695.0
140°	852.6	878.9	894.0	900.0	894.0	878.9	852.6	820.4	776.1	729.7	681.4
142.5°	818.8	842.6	856.1	857.3	856.1	842.6	818.8	788.2	751.0	711.1	670.0
145°	772.0	789.2	799.2	802.2	799.2	789.2	772.0	747.8	718.6	687.4	654.1
147.5°	733.8	747.4	754.3	756.1	754.3	747.4	733.8	713.8	692.4	668.0	641.8
150°	709.5	721.6	727.7	728.7	727.7	721.6	709.5	694.4	676.3	655.1	633.0
152.5°	690.1	700.6	705.1	705.3	705.1	700.6	690.1	678.3	662.6	644.6	624.1
155°	665.2	672.3	676.3	674.3	676.3	672.3	665.2	654.1	643.0	627.9	611.8
157.5°	640.2	646.0	647.8	647.8	647.8	646.0	640.2	632.4	623.7	611.0	597.4
160°	624.9	630.0	631.0	631.0	631.0	630.0	624.9	617.8	610.8	599.7	588.5
162.5°	611.2	614.6	615.6	614.8	615.6	614.6	611.2	604.1	598.6	589.2	579.8
165°	588.5	592.6	592.6	591.6	592.6	592.6	588.5	584.6	580.6	573.5	566.4
167.5°	569.5	571.7	571.5	570.3	571.5	571.7	569.5	567.6	564.0	559.2	553.7
170°	557.3	560.4	559.4	557.3	559.4	560.4	557.3	556.3	554.3	550.3	547.2
172.5°	547.6	549.1	548.1	546.8	548.1	549.1	547.6	546.6	545.4	542.2	540.0
175°	535.2	536.2	535.2	533.2	535.2	536.2	535.2	535.2	534.2	533.2	532.2
177.5°	527.4	527.4	526.5	524.9	526.5	527.4	527.4	527.4	527.4	526.5	526.5
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1043.7	1047.9	1054.3	1057.9	1063.9	1067.8	1070.0	1073.9	1076.0	1083.6	1091.4
5°	985.4	991.5	1002.0	1011.8	1022.4	1033.3	1041.3	1050.3	1058.5	1072.9	1088.0
7.5°	918.6	927.0	943.3	959.0	977.3	992.8	1006.4	1021.9	1035.7	1056.2	1077.6
10°	868.5	883.2	904.7	919.4	943.5	959.0	980.5	997.4	1016.7	1043.9	1068.0
12.5°	825.4	843.1	860.4	880.8	902.5	928.3	951.9	973.6	996.5	1024.6	1052.9
15°	747.1	772.7	799.5	820.2	849.7	876.8	904.3	933.7	961.7	995.2	1032.2
17.5°	646.3	676.0	721.0	756.6	791.1	818.4	852.4	888.1	920.9	961.4	1002.5
20°	600.8	622.6	653.2	701.0	753.2	782.1	816.9	856.1	893.7	937.9	982.0
22.5°	564.2	583.7	608.2	645.5	703.7	743.3	779.4	819.3	863.0	908.1	956.9
25°	512.1	525.7	551.4	581.5	621.5	686.7	726.3	766.3	813.9	862.1	917.9
27.5°	473.0	485.2	501.9	530.7	560.4	607.2	670.2	713.8	761.1	815.5	873.4
30°	443.1	457.5	475.9	496.2	528.8	565.3	628.2	678.8	725.6	781.4	843.2
32.5°	421.4	432.7	448.5	469.2	496.1	531.2	581.5	642.9	688.4	747.3	811.8
35°	385.8	399.0	411.8	431.4	453.3	485.3	523.4	589.1	634.3	692.4	757.3
37.5°	356.5	364.6	378.7	394.3	417.3	441.2	474.2	533.1	582.1	639.0	705.5
40°	334.2	344.3	354.9	372.2	391.1	414.0	446.5	490.3	546.4	602.3	667.1
42.5°	312.5	325.3	336.5	348.1	368.7	391.7	418.2	455.2	512.6	565.4	628.5
45°	286.2	294.6	306.2	319.0	336.0	355.7	379.0	411.4	466.5	512.1	571.4
47.5°	255.8	267.9	275.5	288.0	304.2	322.9	344.6	372.6	417.3	460.0	514.9
50°	235.0	247.4	258.3	269.6	284.0	302.1	320.1	347.3	383.1	428.1	479.3
52.5°	217.1	228.1	238.7	250.0	264.1	280.6	297.8	321.6	352.3	393.6	443.4
55°	192.7	199.4	210.5	221.8	234.2	250.0	266.6	286.6	313.1	347.7	388.1
57.5°	167.6	175.5	184.2	195.6	208.1	220.4	235.2	253.4	274.2	305.6	340.1
60°	153.5	159.6	166.7	178.3	190.1	201.0	215.3	230.5	250.0	277.2	306.6
62.5°	137.8	143.5	150.1	160.3	171.7	181.7	194.2	210.3	226.8	251.6	277.3
65°	111.6	120.0	126.3	135.4	144.8	155.4	165.2	178.0	192.7	212.3	235.3
67.5°	92.5	96.7	102.7	111.0	120.6	129.7	139.0	149.0	161.7	176.8	195.1
70°	84.1	85.6	86.7	94.6	103.7	112.8	121.4	130.9	141.8	154.2	170.1
72.5°	74.1	75.6	77.1	80.5	87.8	96.7	105.7	112.8	123.1	133.4	146.2
75°	58.9	61.1	62.2	64.1	66.8	72.8	81.1	87.9	93.9	101.8	112.0
77.5°	44.8	46.0	47.3	49.3	50.9	53.7	58.4	64.5	70.2	74.7	81.8
80°	35.4	35.9	37.4	38.1	40.4	42.2	44.5	49.4	55.0	57.0	61.8
82.5°	26.7	27.1	28.3	29.1	30.1	31.7	34.5	35.9	40.3	42.7	45.8
85°	14.7	14.3	15.5	15.5	16.3	17.0	17.8	19.6	20.7	23.7	24.5
87.5°	11.2	11.4	11.5	10.3	8.9	8.5	8.2	8.1	8.3	8.4	9.0
90°	33.2	34.2	33.2	27.2	20.2	15.1	12.1	10.1	8.1	4.0	1.0
92.5°	110.7	131.0	129.2	100.6	68.6	45.7	36.3	29.4	25.0	17.8	12.3
95°	345.7	395.1	349.7	232.8	145.1	98.8	74.6	58.5	49.4	39.3	35.2
97.5°	707.5	674.5	508.0	313.7	191.5	133.2	105.8	87.3	73.6	62.9	57.5
100°	941.4	796.2	548.3	330.6	207.6	154.2	126.0	105.8	89.7	80.6	77.6
102.5°	1028.4	800.2	533.0	331.4	222.2	172.8	144.5	123.6	107.4	98.4	96.1
105°	1014.9	746.8	502.9	336.6	246.9	199.5	171.4	149.2	134.0	127.0	123.0
107.5°	926.5	689.6	488.0	350.5	272.4	226.4	197.9	176.0	162.1	155.2	152.0
110°	870.8	662.2	484.8	361.8	289.2	244.9	215.7	194.5	181.4	175.4	171.4



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	832.1	644.4	485.5	374.0	305.4	262.7	232.6	212.3	200.0	193.1	189.0
115°	784.2	624.9	489.8	392.0	330.6	287.2	260.0	239.8	227.8	221.8	216.7
117.5°	753.9	615.4	497.1	411.4	353.8	313.7	285.4	266.1	255.4	249.3	245.3
120°	737.8	609.8	501.9	424.3	369.9	330.6	302.4	282.2	273.2	267.1	263.1
122.5°	724.1	606.5	507.6	435.6	385.2	348.3	319.3	299.1	289.2	283.2	280.0
125°	704.5	600.7	516.0	453.5	408.2	371.9	343.7	323.6	311.4	305.4	302.4
127.5°	686.4	597.2	524.7	470.3	429.6	394.3	365.3	345.9	332.5	324.2	320.1
130°	674.3	595.6	531.2	480.8	442.4	407.2	379.0	358.8	344.7	334.6	330.6
132.5°	664.6	594.8	537.6	491.2	453.7	420.1	391.8	370.9	356.0	345.1	340.2
135°	651.1	593.6	545.2	504.9	469.7	437.4	409.2	386.0	370.9	358.8	354.8
137.5°	641.6	593.4	552.1	515.4	482.6	450.7	424.5	401.5	385.4	373.3	368.5
140°	636.0	592.6	555.3	521.1	489.8	459.6	433.4	411.2	395.1	383.0	379.0
142.5°	630.4	592.6	557.7	525.9	495.4	466.1	441.4	420.1	403.9	392.6	389.4
145°	622.9	590.6	560.4	532.2	503.9	476.8	454.5	434.4	419.3	409.2	405.2
147.5°	615.2	587.0	561.2	535.6	510.8	485.2	465.4	448.7	434.7	425.2	422.1
150°	608.7	584.6	560.4	537.1	514.0	490.8	472.7	457.6	444.4	436.4	433.4
152.5°	603.1	580.6	558.8	538.0	517.3	496.4	480.0	465.6	454.1	446.1	444.6
155°	592.6	573.5	556.3	539.2	522.1	504.9	489.8	478.8	467.7	461.6	460.6
157.5°	582.8	566.2	551.7	539.2	525.5	511.0	498.3	489.4	479.8	474.9	473.9
160°	575.5	561.4	549.3	539.2	527.1	515.0	503.9	495.8	487.8	483.8	482.8
162.5°	569.1	557.3	546.8	538.4	528.0	517.5	508.8	501.5	495.0	491.0	491.6
165°	558.4	549.3	542.2	536.2	529.2	520.1	514.0	509.0	502.9	500.9	501.9
167.5°	547.9	542.2	537.6	534.8	529.0	522.3	518.5	514.8	511.0	509.2	510.4
170°	542.2	538.2	535.2	533.2	528.2	523.1	520.1	518.1	515.0	514.0	516.0
172.5°	536.6	533.4	532.0	530.8	527.4	523.9	521.7	520.5	517.5	518.1	519.3
175°	529.2	528.2	527.1	528.2	526.1	524.1	523.1	523.1	521.1	522.1	523.1
177.5°	524.9	524.1	524.9	526.5	524.9	524.1	524.1	524.1	522.5	523.3	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331665-840
 CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1091.7	1092.6	1098.6	1101.4	1106.8	1108.9	1111.3	1110.6	1110.6	1111.9	1120.3
5°	1094.0	1101.6	1112.9	1123.8	1134.4	1143.5	1149.4	1155.5	1157.7	1168.7	1178.5
7.5°	1090.1	1104.0	1122.7	1139.3	1159.3	1175.0	1187.9	1199.6	1207.6	1223.6	1239.8
10°	1085.0	1104.6	1125.7	1147.2	1174.8	1195.5	1216.6	1232.8	1238.1	1261.8	1275.5
12.5°	1074.7	1101.0	1127.8	1155.7	1182.6	1211.1	1234.4	1250.6	1269.2	1290.5	1315.6
15°	1059.3	1089.5	1124.6	1160.4	1198.9	1233.6	1258.5	1286.8	1307.1	1330.5	1352.3
17.5°	1037.2	1076.1	1120.6	1162.2	1206.6	1243.9	1278.2	1305.3	1319.6	1332.9	1336.3
20°	1019.8	1061.6	1114.0	1163.1	1207.5	1250.5	1284.4	1307.1	1310.9	1311.2	1291.2
22.5°	1000.8	1048.0	1102.9	1153.1	1206.3	1254.2	1280.5	1290.2	1275.3	1249.7	1211.0
25°	965.8	1020.5	1084.2	1141.6	1199.6	1244.9	1253.9	1237.0	1184.6	1129.4	1059.8
27.5°	928.0	989.4	1057.7	1121.5	1183.4	1211.4	1191.8	1130.6	1036.2	954.2	854.7
30°	900.2	969.2	1036.3	1107.6	1164.9	1177.0	1132.2	1042.0	931.9	808.2	709.0
32.5°	868.5	940.8	1014.6	1088.3	1136.3	1124.5	1050.4	939.4	810.3	688.7	594.9
35°	823.2	898.0	977.4	1051.4	1082.0	1031.1	920.2	775.8	643.8	530.3	465.7
37.5°	771.0	852.3	935.0	1002.9	1000.8	915.8	764.9	615.7	504.8	437.7	391.7
40°	733.9	816.1	905.4	962.8	938.3	827.8	664.1	523.4	442.3	388.8	355.3
42.5°	698.3	780.8	869.6	915.1	872.5	736.7	573.6	463.4	396.5	354.8	327.5
45°	637.7	724.8	807.1	832.3	756.1	606.4	463.8	384.0	339.4	308.5	289.6
47.5°	578.6	664.2	739.2	739.7	636.6	491.8	391.3	332.2	294.3	270.3	256.6
50°	542.3	623.8	686.7	676.9	560.1	437.5	349.9	299.0	267.4	248.9	234.6
52.5°	501.6	580.6	635.1	607.2	495.1	385.0	312.9	270.1	243.9	227.8	215.0
55°	442.3	512.5	551.0	508.8	403.9	320.1	264.4	230.8	211.2	197.6	186.7
57.5°	384.3	442.0	466.3	417.1	332.6	265.5	223.6	198.4	178.9	169.3	163.6
60°	347.7	397.1	414.0	359.8	289.2	232.3	198.0	174.6	160.3	153.9	148.2
62.5°	311.8	352.1	359.2	309.4	252.2	203.4	173.9	154.1	144.6	138.5	133.1
65°	258.7	287.7	284.4	244.4	199.4	161.4	139.9	127.8	120.7	112.0	102.6
67.5°	213.0	230.8	220.0	190.1	152.3	125.4	111.4	102.3	93.4	85.1	83.0
70°	184.0	194.2	182.9	155.4	124.8	105.2	93.9	83.0	77.7	75.8	72.4
72.5°	156.3	159.9	147.6	124.0	101.6	87.2	76.1	70.0	67.2	65.5	63.3
75°	117.2	114.6	104.1	85.6	70.5	60.7	57.4	55.0	53.2	51.7	50.5
77.5°	82.4	78.5	69.1	57.1	49.1	44.4	42.4	41.2	40.3	39.5	38.4
80°	61.8	59.2	49.8	40.7	37.4	35.0	33.9	32.4	32.4	31.7	30.5
82.5°	45.2	42.3	34.1	29.9	28.0	26.7	25.8	24.8	24.5	24.7	23.9
85°	23.7	19.2	17.0	16.3	15.0	14.3	14.7	13.9	13.9	13.9	13.5
87.5°	8.1	7.4	7.5	7.6	8.5	9.5	10.6	11.8	12.3	11.8	11.9
90°	4.0	8.1	10.1	12.1	15.1	20.2	27.2	33.2	34.2	33.2	32.2
92.5°	17.8	25.0	29.4	36.3	45.7	68.6	100.6	129.2	131.0	110.7	87.9
95°	39.3	49.4	58.5	74.6	98.8	145.1	232.8	349.7	395.1	345.7	264.1
97.5°	62.9	73.6	87.3	105.8	133.2	191.5	313.7	508.0	674.5	707.5	616.2
100°	80.6	89.7	105.8	126.0	154.2	207.6	330.6	548.3	796.2	941.4	920.2
102.5°	98.4	107.4	123.6	144.5	172.8	222.2	331.4	533.0	800.2	1028.4	1119.3
105°	127.0	134.0	149.2	171.4	199.5	246.9	336.6	502.9	746.8	1014.9	1224.6
107.5°	155.2	162.1	176.0	197.9	226.4	272.4	350.5	488.0	689.6	926.5	1148.8
110°	175.4	181.4	194.5	215.7	244.9	289.2	361.8	484.8	662.2	870.8	1083.5



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	193.1	200.0	212.3	232.6	262.7	305.4	374.0	485.5	644.4	832.1	1023.8
115°	221.8	227.8	239.8	260.0	287.2	330.6	392.0	489.8	624.9	784.2	950.4
117.5°	249.3	255.4	266.1	285.4	313.7	353.8	411.4	497.1	615.4	753.9	895.1
120°	267.1	273.2	282.2	302.4	330.6	369.9	424.3	501.9	609.8	737.8	867.8
122.5°	283.2	289.2	299.1	319.3	348.3	385.2	435.6	507.6	606.5	724.1	846.0
125°	305.4	311.4	323.6	343.7	371.9	408.2	453.5	516.0	600.7	704.5	814.4
127.5°	324.2	332.5	345.9	365.3	394.3	429.6	470.3	524.7	597.2	686.4	783.2
130°	334.6	344.7	358.8	379.0	407.2	442.4	480.8	531.2	595.6	674.3	763.0
132.5°	345.1	356.0	370.9	391.8	420.1	453.7	491.2	537.6	594.8	664.6	743.6
135°	358.8	370.9	386.0	409.2	437.4	469.7	504.9	545.2	593.6	651.1	716.6
137.5°	373.3	385.4	401.5	424.5	450.7	482.6	515.4	552.1	593.4	641.6	695.0
140°	383.0	395.1	411.2	433.4	459.6	489.8	521.1	555.3	592.6	636.0	681.4
142.5°	392.6	403.9	420.1	441.4	466.1	495.4	525.9	557.7	592.6	630.4	670.0
145°	409.2	419.3	434.4	454.5	476.8	503.9	532.2	560.4	590.6	622.9	654.1
147.5°	425.2	434.7	448.7	465.4	485.2	510.8	535.6	561.2	587.0	615.2	641.8
150°	436.4	444.4	457.6	472.7	490.8	514.0	537.1	560.4	584.6	608.7	633.0
152.5°	446.1	454.1	465.6	480.0	496.4	517.3	538.0	558.8	580.6	603.1	624.1
155°	461.6	467.7	478.8	489.8	504.9	522.1	539.2	556.3	573.5	592.6	611.8
157.5°	474.9	479.8	489.4	498.3	511.0	525.5	539.2	551.7	566.2	582.8	597.4
160°	483.8	487.8	495.8	503.9	515.0	527.1	539.2	549.3	561.4	575.5	588.5
162.5°	491.0	495.0	501.5	508.8	517.5	528.0	538.4	546.8	557.3	569.1	579.8
165°	500.9	502.9	509.0	514.0	520.1	529.2	536.2	542.2	549.3	558.4	566.4
167.5°	509.2	511.0	514.8	518.5	522.3	529.0	534.8	537.6	542.2	547.9	553.7
170°	514.0	515.0	518.1	520.1	523.1	528.2	533.2	535.2	538.2	542.2	547.2
172.5°	518.1	517.5	520.5	521.7	523.9	527.4	530.8	532.0	533.4	536.6	540.0
175°	522.1	521.1	523.1	523.1	524.1	526.1	528.2	527.1	528.2	529.2	532.2
177.5°	523.3	522.5	524.1	524.1	524.1	524.9	526.5	524.9	524.1	524.9	526.5
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331665-840
 CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1123.4	1127.3	1129.1	1129.1	1131.3	1130.3	1129.4
5°	1187.9	1195.1	1196.6	1203.4	1208.3	1206.8	1207.5
7.5°	1252.1	1263.6	1275.1	1280.2	1281.1	1284.1	1285.3
10°	1291.6	1301.1	1318.8	1316.2	1329.4	1336.9	1324.4
12.5°	1329.7	1342.4	1354.7	1358.1	1365.5	1368.0	1363.0
15°	1364.0	1370.8	1371.6	1369.7	1372.0	1370.1	1362.9
17.5°	1331.9	1320.9	1298.6	1288.0	1279.6	1267.3	1262.3
20°	1278.8	1246.4	1208.7	1193.6	1175.9	1141.1	1149.4
22.5°	1164.2	1127.2	1089.5	1045.4	1024.4	991.5	989.6
25°	985.8	922.1	851.9	802.8	774.3	741.4	727.1
27.5°	766.5	686.2	628.7	599.7	573.1	547.1	546.0
30°	622.3	561.9	517.5	492.5	476.4	465.3	467.7
32.5°	524.5	483.1	453.1	432.5	420.5	412.2	412.1
35°	428.8	400.5	381.2	372.6	364.0	357.9	358.3
37.5°	367.0	349.9	339.2	329.7	324.3	321.3	319.6
40°	335.3	321.3	313.1	307.4	302.9	298.7	297.9
42.5°	310.2	298.7	290.3	285.9	281.8	278.7	278.0
45°	275.3	265.9	258.3	253.4	251.6	248.9	248.9
47.5°	244.9	235.6	229.7	226.6	223.4	221.7	221.6
50°	224.4	217.2	212.0	210.1	207.4	206.3	205.9
52.5°	206.0	200.7	196.8	195.6	194.4	193.0	193.2
55°	181.0	178.0	176.5	175.3	173.5	171.2	172.7
57.5°	160.0	157.4	153.3	149.8	148.0	146.4	147.0
60°	145.2	139.9	134.6	130.5	129.4	125.9	125.9
62.5°	126.5	119.1	112.6	110.3	109.2	107.6	107.2
65°	97.3	94.3	92.8	91.3	90.5	90.5	89.8
67.5°	80.6	79.4	77.8	77.4	76.6	76.4	76.1
70°	71.3	69.8	69.0	68.7	67.9	68.3	67.2
72.5°	62.2	61.0	60.9	59.9	59.5	59.5	58.7
75°	49.0	49.0	48.7	48.3	47.6	47.2	47.6
77.5°	37.7	37.8	37.1	37.1	37.0	37.1	36.7
80°	30.2	30.5	30.2	29.8	29.4	29.8	29.4
82.5°	23.8	23.3	23.2	23.1	23.1	22.8	22.8
85°	13.5	13.9	13.5	13.2	13.2	13.2	13.5
87.5°	11.2	11.6	11.8	11.8	11.8	11.8	11.5
90°	30.2	32.2	33.2	33.2	33.2	33.2	33.2
92.5°	75.4	67.0	60.7	59.9	56.7	57.5	55.8
95°	202.6	160.3	138.0	125.0	116.9	113.9	114.9
97.5°	504.1	395.1	322.3	274.2	249.3	234.6	226.2
100°	795.2	657.1	535.2	451.5	408.2	379.0	360.8
102.5°	1091.2	990.2	860.9	770.0	696.0	659.5	635.0
105°	1338.5	1351.6	1318.3	1255.8	1193.4	1149.9	1135.9
107.5°	1320.3	1425.1	1473.9	1481.8	1478.3	1469.7	1451.0
110°	1263.8	1392.9	1475.5	1518.8	1538.0	1547.1	1546.1



TEST NUMBER: P331665-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1197.0	1334.8	1429.6	1489.9	1521.9	1539.0	1544.5
115°	1105.6	1237.7	1341.5	1413.0	1459.4	1485.6	1494.7
117.5°	1031.5	1151.1	1248.6	1321.5	1370.5	1398.2	1405.7
120°	992.8	1099.5	1191.3	1261.8	1309.2	1338.5	1348.6
122.5°	960.5	1061.7	1144.6	1207.8	1254.4	1280.4	1288.9
125°	918.2	1006.8	1082.5	1140.9	1179.2	1204.4	1212.4
127.5°	877.1	960.7	1030.5	1081.5	1117.3	1139.1	1145.6
130°	849.6	929.3	995.8	1045.2	1079.4	1099.5	1107.6
132.5°	823.8	897.0	959.5	1008.0	1042.4	1060.9	1068.1
135°	783.2	849.6	906.1	949.4	982.7	1000.8	1004.8
137.5°	750.6	803.4	852.6	892.2	920.8	936.8	942.8
140°	729.7	776.1	820.4	852.6	878.9	894.0	900.0
142.5°	711.1	751.0	788.2	818.8	842.6	856.1	857.3
145°	687.4	718.6	747.8	772.0	789.2	799.2	802.2
147.5°	668.0	692.4	713.8	733.8	747.4	754.3	756.1
150°	655.1	676.3	694.4	709.5	721.6	727.7	728.7
152.5°	644.6	662.6	678.3	690.1	700.6	705.1	705.3
155°	627.9	643.0	654.1	665.2	672.3	676.3	674.3
157.5°	611.0	623.7	632.4	640.2	646.0	647.8	647.8
160°	599.7	610.8	617.8	624.9	630.0	631.0	631.0
162.5°	589.2	598.6	604.1	611.2	614.6	615.6	614.8
165°	573.5	580.6	584.6	588.5	592.6	592.6	591.6
167.5°	559.2	564.0	567.6	569.5	571.7	571.5	570.3
170°	550.3	554.3	556.3	557.3	560.4	559.4	557.3
172.5°	542.2	545.4	546.6	547.6	549.1	548.1	546.8
175°	533.2	534.2	535.2	535.2	536.2	535.2	533.2
177.5°	526.5	527.4	527.4	527.4	527.4	526.5	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1

(END OF REPORT)