

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331667-840

Luminaire Tested: **SA2XXRDIP-C485D925U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331667-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C485D925U840-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5058.2 lumens  
Efficiency: N/A  
Efficacy: 113.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331667-840  
CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331667-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	94	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	36	29				
2	86	79	73	69	78	72	67	63	58	54	51	45	43	41	33	32	30	25				
3	79	70	63	57	71	63	58	53	51	47	44	40	37	35	29	28	26	22				
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19				
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	17				
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18	15				
7	57	45	37	32	51	41	34	30	34	29	25	27	23	20	20	18	16	13				
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	19	16	14	12				
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11				
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13454	13454	13454
5°	13506	13287	13361
10°	13404	13070	12959
15°	13249	12682	12318
20°	13036	12129	11519
25°	12818	11501	10750
30°	12515	10856	9758
35°	12220	10153	8889
40°	11921	9428	7885
45°	11574	8611	6976
50°	11215	7784	6081
55°	10849	6899	5222
60°	10424	5968	4334
65°	9941	5012	3947
70°	9361	4131	3635
75°	8659	3762	3387
80°	7643	3366	3087
85°	6002	2649	2649



TEST NUMBER: P331667-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.0	1.5
10°-20°	214.2	4.2
20°-30°	300.8	5.9
30°-40°	328.0	6.5
40°-50°	301.6	6.0
50°-60°	236.8	4.7
60°-70°	154.4	3.1
70°-80°	79.6	1.6
80°-90°	25.4	0.5
90°-100°	75.7	1.5
100°-110°	235.0	4.6
110°-120°	401.8	7.9
120°-130°	528.3	10.4
130°-140°	593.0	11.7
140°-150°	581.4	11.5
150°-160°	487.7	9.6
160°-170°	323.5	6.4
170°-180°	113.0	2.2
0°-30°	593.0	11.7
0°-40°	921.0	18.2
0°-60°	1459.4	28.9
0°-90°	1718.8	34.0
90°-120°	712.5	14.1
90°-150°	2415.2	47.7
90°-180°	3339.0	66.0
0°-180°	5058.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	833	829	820	826	824	79
15°	793	783	759	745	737	223
25°	720	694	646	616	603	331
35°	620	580	515	469	451	388
45°	507	455	377	326	306	391
55°	385	325	245	202	186	344
65°	260	199	131	107	103	258
75°	139	87	60	55	54	147
85°	32	17	14	14	14	38
90°	1	14	35	33	34	4
95°	52	62	64	64	62	60
105°	217	220	222	224	224	229
115°	403	409	407	406	403	399
125°	586	595	593	590	588	524
135°	759	769	772	771	768	586
145°	921	928	934	935	931	575
155°	1053	1056	1059	1064	1061	485
165°	1146	1145	1145	1151	1147	323
175°	1192	1189	1187	1194	1188	113
180°	1194	1194	1194	1194	1194	



TEST NUMBER: P331667-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	836.4	835.8	835.1	834.4	833.7	832.6	831.2	829.7	828.2	826.8	828.1
5°	833.3	832.5	831.7	830.9	830.0	828.5	826.4	824.2	822.0	819.8	821.3
7.5°	824.8	823.7	822.7	821.6	820.6	818.8	816.3	813.7	811.2	808.7	809.1
10°	817.6	816.4	815.2	814.1	812.8	810.6	807.3	803.9	800.5	797.2	796.7
12.5°	808.5	807.1	805.6	804.2	802.7	799.9	795.6	791.3	787.0	782.7	781.8
15°	792.6	790.8	789.0	787.1	785.3	781.5	775.8	770.1	764.5	758.7	755.6
17.5°	773.3	770.4	767.6	764.8	761.9	756.9	749.6	742.3	735.0	727.6	723.9
20°	758.7	755.4	752.0	748.7	745.3	739.4	731.0	722.7	714.3	705.9	701.8
22.5°	743.1	739.3	735.5	731.7	728.0	721.4	712.0	702.5	693.1	683.6	678.2
25°	719.5	714.2	708.8	703.4	698.0	689.8	678.7	667.7	656.6	645.6	638.7
27.5°	691.2	685.3	679.4	673.7	667.8	658.6	646.2	633.7	621.3	608.7	600.8
30°	671.3	664.9	658.5	652.2	645.8	635.9	622.5	609.0	595.6	582.3	573.7
32.5°	652.0	644.5	637.0	629.7	622.2	611.6	597.9	584.2	570.6	556.9	547.1
35°	620.0	611.4	602.9	594.3	585.7	574.1	559.4	544.6	529.9	515.1	504.5
37.5°	587.9	578.6	569.2	559.8	550.5	537.9	522.2	506.4	490.7	475.0	463.3
40°	565.6	555.6	545.5	535.5	525.4	512.3	496.0	479.8	463.5	447.3	435.4
42.5°	542.7	532.1	521.5	511.0	500.4	486.7	469.9	453.0	436.3	419.5	407.2
45°	506.9	495.6	484.3	473.1	461.9	447.5	429.9	412.3	394.7	377.1	365.2
47.5°	471.8	459.9	448.1	436.2	424.2	409.2	391.0	372.8	354.7	336.5	324.7
50°	446.5	434.5	422.7	410.8	398.9	383.7	365.3	346.9	328.4	309.9	298.4
52.5°	421.7	409.3	396.9	384.5	372.0	356.8	338.7	320.7	302.7	284.7	273.5
55°	385.4	372.3	359.2	346.2	333.2	317.5	299.4	281.3	263.2	245.1	235.1
57.5°	348.1	334.8	321.3	307.9	294.5	279.1	261.8	244.3	226.9	209.5	200.3
60°	322.8	309.4	296.0	282.6	269.1	253.9	236.6	219.3	202.1	184.8	176.2
62.5°	298.0	284.7	271.2	257.8	244.4	229.5	213.1	196.6	180.2	163.7	155.5
65°	260.2	246.6	233.1	219.4	205.9	191.6	176.5	161.4	146.3	131.2	125.5
67.5°	223.7	210.3	196.7	183.3	169.8	156.2	142.7	129.2	115.5	102.0	99.4
70°	198.3	185.3	172.2	159.2	146.0	133.7	122.2	110.6	99.1	87.5	85.8
72.5°	174.2	161.7	149.2	136.6	124.1	113.2	103.9	94.6	85.3	76.0	74.6
75°	138.8	127.0	115.3	103.6	91.8	83.1	77.5	71.7	66.0	60.3	59.2
77.5°	103.9	93.6	83.3	73.0	62.8	56.2	53.5	50.8	48.0	45.2	44.5
80°	82.2	73.6	65.1	56.6	48.0	42.9	41.2	39.6	37.9	36.2	35.5
82.5°	62.3	55.6	49.0	42.3	35.6	31.7	30.6	29.4	28.3	27.2	26.8
85°	32.4	28.9	25.3	21.9	18.4	16.4	15.9	15.3	14.8	14.3	14.3
87.5°	9.9	9.3	8.8	8.3	7.7	8.0	8.9	9.9	10.9	11.9	11.6
90°	1.0	3.7	6.4	9.1	11.7	15.6	20.5	25.4	30.3	35.2	34.8
92.5°	18.0	19.9	21.9	23.8	25.9	27.4	28.6	29.7	30.9	32.0	32.1
95°	52.4	54.6	56.9	59.1	61.4	62.7	63.1	63.6	64.0	64.5	64.5
97.5°	95.7	97.8	99.7	101.7	103.6	105.0	105.9	106.7	107.6	108.5	108.5
100°	127.9	129.8	131.6	133.4	135.1	136.4	137.0	137.7	138.5	139.1	139.1
102.5°	161.9	163.3	164.7	166.1	167.5	168.7	169.6	170.5	171.3	172.2	172.3
105°	216.7	217.3	218.0	218.7	219.3	219.9	220.4	220.9	221.3	221.7	222.2
107.5°	271.9	272.9	273.9	274.9	275.9	276.3	276.3	276.3	276.3	276.3	276.5
110°	307.4	308.7	310.0	311.4	312.8	313.5	313.5	313.5	313.5	313.5	313.5



TEST NUMBER: P331667-840

CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.1	347.4	348.8	350.1	351.4	352.0	351.8	351.6	351.5	351.3	350.8
115°	403.1	404.5	405.8	407.2	408.5	408.9	408.5	408.1	407.6	407.2	407.0
117.5°	460.0	461.7	463.5	465.3	467.2	467.4	466.2	464.8	463.6	462.4	461.8
120°	497.9	499.7	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9	497.9
122.5°	532.5	534.6	536.8	539.0	541.1	541.6	540.3	539.1	537.9	536.5	536.0
125°	586.5	588.5	590.6	592.6	594.6	595.3	594.6	593.9	593.3	592.6	591.9
127.5°	639.1	641.7	644.3	646.8	649.3	650.3	649.4	648.6	647.8	647.0	646.2
130°	672.2	675.1	678.0	681.0	683.9	685.1	684.6	684.2	683.8	683.3	682.9
132.5°	709.3	711.7	714.1	716.4	718.8	720.0	720.1	720.2	720.2	720.3	719.4
135°	758.9	761.3	763.8	766.3	768.7	770.2	770.6	771.0	771.5	771.9	771.7
137.5°	811.1	813.0	815.1	817.1	819.1	820.4	821.0	821.6	822.2	822.7	822.6
140°	842.5	844.6	846.6	848.6	850.6	852.1	853.2	854.3	855.6	856.7	856.7
142.5°	874.7	876.8	878.8	880.8	882.8	884.2	884.9	885.8	886.5	887.3	887.5
145°	921.1	922.7	924.2	925.8	927.4	928.9	930.2	931.5	932.9	934.2	934.4
147.5°	962.4	964.3	966.2	968.1	970.0	971.4	972.3	973.1	974.0	974.9	975.4
150°	990.7	992.0	993.3	994.7	996.0	997.1	998.0	999.0	999.9	1000.8	1001.4
152.5°	1015.6	1017.0	1018.3	1019.7	1021.1	1022.3	1023.3	1024.4	1025.4	1026.5	1027.4
155°	1053.2	1053.8	1054.5	1055.2	1055.8	1056.5	1057.2	1057.8	1058.5	1059.1	1060.4
157.5°	1085.2	1085.6	1086.1	1086.5	1087.0	1087.4	1087.8	1088.2	1088.6	1089.0	1090.6
160°	1104.6	1105.0	1105.4	1105.9	1106.3	1106.7	1106.9	1107.1	1107.3	1107.5	1108.9
162.5°	1122.3	1122.4	1122.5	1122.6	1122.7	1122.8	1123.1	1123.3	1123.5	1123.7	1125.2
165°	1145.9	1145.7	1145.4	1145.2	1145.0	1144.9	1144.9	1144.9	1144.9	1144.9	1146.4
167.5°	1165.6	1165.0	1164.3	1163.6	1163.0	1162.6	1162.6	1162.5	1162.5	1162.4	1164.0
170°	1176.1	1175.4	1174.8	1174.1	1173.4	1173.0	1172.8	1172.6	1172.3	1172.0	1173.7
172.5°	1183.4	1182.7	1182.0	1181.3	1180.6	1180.2	1180.0	1179.7	1179.5	1179.3	1180.9
175°	1192.2	1191.5	1190.8	1190.2	1189.5	1189.0	1188.5	1188.1	1187.6	1187.2	1188.7
177.5°	1195.9	1195.3	1194.8	1194.3	1193.7	1193.3	1192.9	1192.5	1192.1	1191.8	1192.9
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331667-840  
 CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	829.4	830.8	832.1	832.6	832.4	832.1	831.8	831.6
5°	822.8	824.4	825.9	826.4	825.9	825.4	824.9	824.4
7.5°	809.5	809.9	810.4	810.2	809.3	808.4	807.6	806.7
10°	796.2	795.7	795.2	794.5	793.5	792.4	791.4	790.4
12.5°	780.9	780.0	779.1	777.8	776.1	774.5	772.7	771.1
15°	752.3	749.2	746.0	743.6	741.8	740.2	738.5	736.9
17.5°	720.0	716.3	712.5	709.1	706.3	703.4	700.5	697.6
20°	697.5	693.4	689.1	685.2	681.6	677.8	674.2	670.4
22.5°	672.8	667.4	662.1	657.9	655.2	652.5	649.7	646.9
25°	631.9	625.0	618.1	613.4	610.9	608.3	605.9	603.4
27.5°	592.8	584.7	576.7	570.8	566.7	562.8	558.8	554.8
30°	565.1	556.6	548.1	541.5	536.9	532.5	528.0	523.4
32.5°	537.3	527.7	517.9	510.9	506.6	502.4	498.1	493.8
35°	494.0	483.4	472.9	465.7	462.1	458.4	454.7	451.0
37.5°	451.7	440.1	428.5	420.5	416.4	412.1	407.9	403.6
40°	423.4	411.5	399.6	391.5	387.2	382.8	378.4	374.1
42.5°	394.9	382.5	370.3	362.0	357.8	353.6	349.3	345.1
45°	353.3	341.4	329.5	321.5	317.5	313.5	309.4	305.5
47.5°	312.9	301.0	289.2	281.4	277.8	274.2	270.4	266.8
50°	286.8	275.3	263.7	256.2	252.7	249.1	245.6	242.1
52.5°	262.3	251.2	239.9	232.8	229.5	226.3	223.0	219.7
55°	225.0	214.9	204.9	198.2	195.1	191.9	188.7	185.5
57.5°	191.1	181.9	172.7	166.7	164.0	161.4	158.6	155.9
60°	167.6	159.2	150.6	145.0	142.3	139.6	136.9	134.2
62.5°	147.3	139.3	131.1	126.2	124.6	123.0	121.4	119.8
65°	119.9	114.1	108.5	105.3	104.8	104.3	103.8	103.3
67.5°	96.7	94.1	91.5	90.0	89.4	88.9	88.4	87.8
70°	84.1	82.5	80.8	79.6	79.0	78.3	77.6	77.0
72.5°	73.2	71.8	70.4	69.5	69.1	68.7	68.3	67.9
75°	58.0	56.9	55.6	54.9	54.8	54.6	54.4	54.3
77.5°	43.9	43.2	42.6	42.1	41.8	41.6	41.3	41.0
80°	34.8	34.2	33.5	33.2	33.2	33.2	33.2	33.2
82.5°	26.4	26.0	25.5	25.3	25.3	25.3	25.3	25.3
85°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
87.5°	11.4	11.2	11.0	10.9	10.9	11.0	11.0	11.1
90°	34.3	33.9	33.5	33.3	33.6	33.8	34.0	34.2
92.5°	32.2	32.3	32.4	32.5	32.5	32.5	32.6	32.6
95°	64.5	64.5	64.5	64.2	63.8	63.4	62.9	62.5
97.5°	108.5	108.5	108.5	108.5	108.4	108.4	108.3	108.3
100°	139.1	139.1	139.1	139.0	138.8	138.6	138.3	138.0
102.5°	172.5	172.7	172.9	172.8	172.6	172.4	172.2	172.0
105°	222.6	223.1	223.5	223.7	223.7	223.7	223.7	223.7
107.5°	276.7	276.9	277.0	276.6	275.6	274.6	273.6	272.5
110°	313.5	313.5	313.5	313.1	312.5	311.7	311.0	310.4





TEST NUMBER: P331667-840  
 CATALOG NUMBER: SA2XXRDIP-C485D925U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	350.2	349.7	349.2	348.6	348.2	347.7	347.2	346.7
115°	406.7	406.5	406.3	405.8	405.2	404.5	403.7	403.1
117.5°	461.3	460.8	460.2	459.6	459.0	458.3	457.6	457.0
120°	497.9	497.9	497.9	497.6	496.9	496.1	495.5	494.8
122.5°	535.4	534.9	534.4	533.9	533.4	532.9	532.4	531.9
125°	591.3	590.6	589.9	589.5	589.3	589.0	588.8	588.5
127.5°	645.4	644.6	643.8	643.0	642.3	641.6	640.9	640.2
130°	682.4	682.0	681.5	680.9	679.9	679.0	678.1	677.2
132.5°	718.4	717.4	716.4	715.6	714.9	714.2	713.5	712.8
135°	771.5	771.3	771.0	770.6	769.9	769.3	768.6	767.9
137.5°	822.4	822.2	822.0	821.5	820.6	819.7	818.8	817.9
140°	856.7	856.7	856.7	856.2	855.3	854.3	853.5	852.6
142.5°	887.7	887.8	888.0	887.7	886.8	885.9	884.9	884.0
145°	934.6	934.9	935.1	934.8	933.9	933.0	932.1	931.2
147.5°	975.9	976.4	976.9	976.7	975.9	975.0	974.2	973.3
150°	1002.1	1002.8	1003.4	1003.4	1002.8	1002.1	1001.4	1000.8
152.5°	1028.2	1029.1	1030.0	1030.0	1029.1	1028.2	1027.4	1026.5
155°	1061.5	1062.6	1063.7	1063.9	1063.2	1062.6	1061.9	1061.2
157.5°	1092.1	1093.6	1095.1	1095.3	1094.3	1093.2	1092.1	1091.1
160°	1110.2	1111.6	1113.0	1113.2	1112.3	1111.4	1110.4	1109.5
162.5°	1126.7	1128.2	1129.7	1130.0	1128.9	1127.8	1126.8	1125.7
165°	1148.0	1149.5	1151.1	1151.3	1150.2	1149.1	1148.0	1146.9
167.5°	1165.5	1167.1	1168.6	1168.8	1167.7	1166.5	1165.4	1164.2
170°	1175.2	1176.8	1178.3	1178.4	1177.1	1175.8	1174.4	1173.1
172.5°	1182.5	1184.1	1185.6	1185.7	1184.4	1183.1	1181.6	1180.3
175°	1190.3	1191.8	1193.5	1193.6	1192.2	1190.8	1189.5	1188.2
177.5°	1194.0	1195.1	1196.1	1196.1	1195.1	1194.0	1192.9	1191.8
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3

(END OF REPORT)