

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331675-840

Luminaire Tested: **SA2XXRDIP-C675D330U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331675-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3887.5 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66				
1	102	98	95	91	96	93	90	87	82	80	78	73	71	70	64	63	62	58				
2	94	87	81	77	88	82	77	73	74	70	66	65	62	60	58	56	54	50				
3	87	78	71	65	81	74	67	62	66	61	57	59	55	52	52	49	47	44				
4	80	70	62	56	75	66	59	54	59	54	50	53	49	46	48	44	42	39				
5	74	63	55	49	70	60	53	47	54	48	44	49	44	40	43	40	37	34				
6	69	57	49	44	65	54	47	42	49	43	39	44	40	36	40	36	33	31				
7	64	52	44	39	60	50	43	38	45	39	35	41	36	33	37	33	30	28				
8	60	48	40	35	56	46	39	34	42	36	32	38	33	30	34	30	28	25				
9	56	44	37	32	53	42	35	31	38	33	29	35	30	27	32	28	25	23				
10	52	41	34	29	50	39	32	28	36	30	26	33	28	25	30	26	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23954	23954	23954	23954
5°	26752	24104	21371	24104
10°	29681	23935	18525	23935
15°	31141	23584	14596	23584
20°	26996	23063	12631	23063
25°	17706	22352	11277	22352
30°	11917	21490	10206	21490
35°	9652	20402	9207	20402
40°	8585	19220	8517	19220
45°	7768	17831	7606	17831
50°	7068	16458	7043	16458
55°	6646	14933	6559	14933
60°	5561	13533	5493	13533
65°	4688	12287	5318	12287
70°	4334	10976	5013	10976
75°	4049	9551	4629	9551
80°	3738	7857	4119	7857
85°	3446	6206	3631	6206



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.6	3.6
10°-20°	391.9	10.1
20°-30°	505.0	13.0
30°-40°	479.9	12.3
40°-50°	411.1	10.6
50°-60°	313.0	8.1
60°-70°	197.9	5.1
70°-80°	98.8	2.5
80°-90°	26.8	0.7
90°-100°	15.1	0.4
100°-110°	55.2	1.4
110°-120°	147.6	3.8
120°-130°	243.6	6.3
130°-140°	259.0	6.7
140°-150°	240.8	6.2
150°-160°	193.6	5.0
160°-170°	124.7	3.2
170°-180°	42.9	1.1
0°-30°	1037.5	26.7
0°-40°	1517.4	39.0
0°-60°	2241.5	57.7
0°-90°	2565.1	66.0
90°-120°	217.8	5.6
90°-150°	961.2	24.7
90°-180°	1322.0	34.0
0°-180°	3887.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1484	1484	1484	1484	1484	
5°	1651	1487	1319	1487	1651	163
15°	1863	1411	873	1411	1863	503
25°	994	1255	633	1255	994	472
35°	490	1035	467	1035	490	313
45°	340	781	333	781	340	263
55°	236	530	233	530	236	207
65°	123	322	139	322	123	125
75°	65	153	74	153	65	69
85°	19	34	20	34	19	20
90°	9	0	9	0	9	5
95°	14	21	14	21	14	13
105°	25	99	25	99	25	26
115°	27	188	27	188	27	67
125°	279	266	279	266	279	242
135°	339	328	339	328	339	261
145°	387	381	387	381	387	242
155°	420	420	420	420	420	194
165°	441	442	441	442	441	125
175°	450	452	450	452	450	43
180°	451	451	451	451	451	



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1543.8	1545.0	1546.3	1543.4	1543.4	1540.9	1535.5	1531.5	1519.8	1518.2	1518.2
5°	1650.6	1649.5	1651.6	1645.0	1635.7	1633.6	1623.8	1610.9	1597.5	1582.6	1579.4
7.5°	1756.8	1755.2	1751.1	1750.0	1742.8	1727.3	1711.5	1694.8	1672.4	1650.7	1639.8
10°	1810.4	1827.5	1817.1	1799.1	1802.7	1778.5	1765.5	1743.4	1724.8	1692.3	1685.2
12.5°	1863.2	1869.9	1866.6	1856.3	1851.7	1834.9	1817.6	1798.3	1764.0	1734.8	1709.5
15°	1863.0	1872.8	1875.3	1872.3	1874.8	1873.8	1864.5	1848.6	1818.7	1786.7	1758.9
17.5°	1725.5	1732.2	1749.2	1760.6	1775.0	1805.5	1820.6	1826.4	1822.0	1803.8	1784.2
20°	1571.2	1559.8	1607.3	1631.5	1652.1	1703.6	1748.0	1765.0	1792.3	1791.8	1786.7
22.5°	1352.6	1355.3	1400.3	1429.1	1489.2	1540.8	1591.3	1655.4	1708.2	1743.1	1763.6
25°	993.9	1013.5	1058.3	1097.5	1164.5	1260.4	1347.5	1448.6	1543.9	1619.1	1690.8
27.5°	746.4	747.9	783.5	819.6	859.4	938.0	1047.6	1168.3	1304.2	1416.4	1545.5
30°	639.2	636.1	651.1	673.3	707.2	768.1	850.5	969.2	1104.7	1273.7	1424.3
32.5°	563.3	563.5	574.8	591.2	619.5	660.5	716.9	813.2	941.4	1107.6	1284.0
35°	489.7	489.2	497.5	509.3	521.2	547.4	586.1	636.6	724.8	879.9	1060.4
37.5°	437.0	439.2	443.2	450.6	463.7	478.4	501.6	535.5	598.2	690.0	841.7
40°	407.3	408.3	413.9	420.1	427.9	439.2	458.3	485.5	531.5	604.7	715.5
42.5°	380.0	381.0	385.1	390.8	396.9	408.3	424.0	447.7	484.8	542.0	633.4
45°	340.2	340.2	343.9	346.4	353.1	363.5	376.3	395.9	421.7	463.9	524.7
47.5°	302.9	303.0	305.4	309.8	314.1	322.0	334.8	350.7	369.5	402.2	454.1
50°	281.4	282.0	283.5	287.1	289.7	296.9	306.7	320.6	340.2	365.5	408.8
52.5°	264.2	263.8	265.8	267.3	269.1	274.3	281.6	293.9	311.3	333.4	369.2
55°	236.1	234.0	237.1	239.7	241.3	243.3	247.4	255.2	270.1	288.7	315.5
57.5°	201.1	200.3	202.4	204.8	209.6	215.2	218.6	223.6	231.4	244.7	271.2
60°	172.2	172.2	176.8	178.3	184.0	191.3	198.4	202.6	210.4	219.0	238.6
62.5°	146.6	147.0	149.2	150.8	153.9	162.8	172.9	182.0	189.2	197.6	210.7
65°	122.7	123.7	123.7	124.7	126.8	128.9	133.0	140.2	153.1	164.9	174.7
67.5°	104.1	104.4	104.7	105.7	106.3	108.6	110.2	113.4	116.4	127.6	139.8
70°	91.8	93.3	92.8	93.8	94.3	95.3	97.5	99.0	103.6	106.2	113.4
72.5°	80.2	81.3	81.2	81.9	83.2	83.4	85.0	86.6	89.6	91.8	95.6
75°	64.9	64.4	64.9	65.9	66.4	67.1	67.1	69.1	70.6	72.7	75.2
77.5°	50.1	50.6	50.5	50.6	50.7	51.6	51.5	52.5	54.0	55.0	56.2
80°	40.2	40.7	40.2	40.7	41.2	41.7	41.2	41.7	43.3	44.3	44.3
82.5°	31.1	31.2	31.5	31.6	31.7	31.8	32.6	32.7	33.8	33.6	34.0
85°	18.6	18.1	18.1	18.1	18.6	19.1	18.6	18.6	19.1	19.1	19.1
87.5°	8.4	8.8	8.7	8.7	8.7	8.6	8.6	8.9	8.4	8.7	8.2
90°	8.8	8.7	8.5	8.4	8.3	8.0	7.6	7.3	6.9	6.6	6.0
92.5°	8.8	8.7	8.7	8.6	8.5	8.3	8.2	8.0	7.8	7.6	7.3
95°	14.0	14.1	14.1	14.2	14.3	14.1	13.8	13.4	13.1	12.7	12.2
97.5°	18.8	18.7	18.6	18.5	18.4	18.2	17.9	17.7	17.4	17.1	15.9
100°	21.9	21.7	21.6	21.4	21.3	20.9	20.4	19.8	19.2	18.6	17.4
102.5°	23.4	23.2	23.0	22.8	22.6	22.1	21.4	20.6	19.9	19.1	29.5
105°	24.8	24.5	24.2	23.9	23.6	23.1	22.3	21.5	20.7	19.9	39.7
107.5°	25.5	25.2	24.9	24.6	24.3	24.6	25.4	26.3	27.1	27.9	51.6
110°	25.8	25.5	25.2	24.9	24.6	28.1	35.3	42.6	49.9	57.2	78.1



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	26.1	25.9	25.5	25.3	25.1	38.3	64.7	91.2	117.6	144.1	149.3
115°	26.8	32.0	37.3	42.4	47.7	67.1	100.7	134.3	167.8	201.5	199.7
117.5°	109.4	126.5	143.7	160.9	178.0	190.7	198.7	206.9	215.0	223.2	221.9
120°	199.1	208.9	218.7	228.5	238.3	242.8	242.0	241.1	240.2	239.3	238.0
122.5°	248.5	250.4	252.4	254.3	256.1	256.8	256.3	255.8	255.3	254.8	253.4
125°	279.1	278.9	278.7	278.5	278.3	277.9	277.4	276.9	276.4	275.9	274.5
127.5°	298.5	298.4	298.4	298.4	298.3	297.9	297.2	296.5	295.7	295.0	294.0
130°	310.5	310.6	310.6	310.7	310.8	310.4	309.6	308.8	308.0	307.3	306.5
132.5°	322.2	322.3	322.4	322.4	322.6	322.2	321.5	320.9	320.2	319.5	318.7
135°	339.2	339.4	339.5	339.7	339.8	339.5	338.8	338.1	337.4	336.7	336.0
137.5°	354.8	355.0	355.3	355.5	355.7	355.5	354.8	354.1	353.4	352.6	351.9
140°	364.4	364.8	365.2	365.5	365.9	365.7	365.1	364.4	363.8	363.0	362.3
142.5°	373.8	374.2	374.6	374.9	375.3	375.2	374.6	374.0	373.3	372.7	371.8
145°	386.9	387.3	387.7	388.0	388.4	388.3	387.8	387.3	386.8	386.3	385.1
147.5°	398.5	398.8	399.1	399.4	399.7	399.7	399.3	398.9	398.5	398.2	397.0
150°	405.6	405.9	406.3	406.7	407.0	407.0	406.5	406.1	405.7	405.3	404.0
152.5°	411.5	412.0	412.5	412.9	413.4	413.4	413.0	412.6	412.1	411.7	410.6
155°	419.9	420.5	421.1	421.6	422.2	422.3	421.8	421.4	421.0	420.5	419.7
157.5°	427.6	428.1	428.7	429.2	429.8	429.8	429.4	428.9	428.4	427.9	427.3
160°	432.0	432.5	433.0	433.5	434.0	434.0	433.6	433.2	432.7	432.3	431.9
162.5°	435.7	436.3	436.9	437.5	438.2	438.2	437.7	437.2	436.8	436.3	435.9
165°	441.1	441.6	442.1	442.6	443.1	443.1	442.6	442.1	441.6	441.1	440.9
167.5°	444.5	445.2	445.9	446.6	447.2	447.3	446.8	446.3	445.8	445.2	445.0
170°	446.7	447.4	448.0	448.7	449.3	449.4	448.9	448.4	447.9	447.4	447.2
172.5°	448.3	448.9	449.6	450.2	450.9	450.9	450.4	449.9	449.4	448.9	448.8
175°	449.6	450.3	451.1	451.8	452.5	452.6	452.1	451.6	451.1	450.6	450.5
177.5°	450.5	451.0	451.5	452.0	452.5	452.6	452.2	451.8	451.4	451.0	450.9
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1519.0	1515.7	1512.9	1505.4	1501.8	1493.5	1492.3	1491.9	1481.1	1470.8	1467.9
5°	1571.2	1563.0	1550.5	1536.1	1521.2	1505.7	1495.4	1487.2	1466.5	1446.9	1435.6
7.5°	1623.8	1606.1	1584.7	1557.4	1534.6	1509.0	1490.1	1473.1	1443.8	1415.7	1396.8
10°	1662.9	1634.1	1605.8	1568.1	1538.7	1509.8	1483.1	1459.9	1426.8	1389.8	1363.4
12.5°	1687.3	1655.6	1616.5	1579.6	1541.7	1504.9	1469.1	1439.3	1400.5	1362.1	1330.9
15°	1720.2	1686.2	1638.7	1586.2	1537.2	1489.2	1448.0	1410.9	1360.4	1314.5	1276.4
17.5°	1747.1	1700.3	1649.3	1588.5	1531.9	1470.9	1417.7	1370.4	1314.1	1258.8	1213.9
20°	1755.8	1709.4	1650.6	1589.7	1522.8	1451.1	1393.9	1342.3	1282.0	1221.7	1170.1
22.5°	1750.4	1714.3	1648.9	1576.2	1507.5	1432.5	1367.9	1308.1	1241.2	1179.6	1119.8
25°	1714.0	1701.6	1639.8	1560.3	1482.1	1394.9	1320.2	1254.7	1178.4	1112.5	1047.4
27.5°	1629.1	1655.9	1617.5	1533.0	1445.8	1352.4	1268.4	1193.9	1114.7	1040.5	975.7
30°	1547.5	1608.8	1592.4	1514.0	1416.5	1324.8	1230.5	1152.7	1068.1	991.8	927.9
32.5°	1435.7	1537.1	1553.2	1487.6	1386.8	1286.1	1187.2	1109.7	1021.5	941.1	878.8
35°	1257.8	1409.4	1478.9	1437.1	1336.2	1227.4	1125.3	1035.1	946.4	867.1	805.2
37.5°	1045.5	1251.9	1367.9	1370.9	1278.1	1165.0	1053.9	964.3	873.5	795.6	728.7
40°	907.8	1131.5	1282.5	1316.1	1237.7	1115.5	1003.1	911.9	823.2	746.9	670.1
42.5°	784.1	1006.9	1192.7	1250.9	1188.6	1067.2	954.5	859.1	773.0	700.7	622.3
45°	634.1	828.9	1033.6	1137.7	1103.2	990.8	871.7	780.9	700.0	637.6	562.4
47.5°	534.8	672.2	870.2	1011.1	1010.5	907.9	790.7	703.9	628.8	570.4	509.4
50°	478.4	597.9	765.5	925.3	938.7	852.6	741.2	655.2	585.1	523.7	474.7
52.5°	427.7	526.2	676.8	830.0	868.2	793.7	685.6	606.1	538.1	481.7	439.7
55°	361.3	437.7	552.1	695.4	753.2	700.5	604.7	530.5	475.2	427.9	391.7
57.5°	305.7	362.9	454.7	570.2	637.3	604.3	525.1	464.8	417.7	374.8	346.3
60°	270.6	317.5	395.4	491.8	566.0	542.8	475.2	419.1	378.9	341.7	315.0
62.5°	237.6	277.9	344.7	422.9	491.0	481.4	426.2	379.1	343.9	310.0	287.3
65°	191.3	220.7	272.7	334.1	388.7	393.3	353.7	321.6	290.2	263.4	243.3
67.5°	152.3	171.5	208.1	259.8	300.7	315.4	291.1	266.7	241.8	221.1	203.6
70°	128.4	143.8	170.7	212.4	250.0	265.5	251.6	232.5	210.9	193.8	178.8
72.5°	104.0	119.1	138.9	169.5	201.8	218.4	213.6	200.0	182.4	168.2	154.1
75°	78.4	83.0	96.4	117.0	142.3	156.7	160.4	153.1	139.2	128.4	120.1
77.5°	58.0	60.7	67.2	78.0	94.4	107.3	112.6	111.8	102.2	95.8	88.2
80°	46.4	48.0	51.0	55.6	68.1	80.9	84.5	84.5	77.9	75.2	67.6
82.5°	35.2	36.4	38.3	40.8	46.6	57.9	61.9	62.7	58.5	55.0	49.0
85°	20.1	19.6	20.6	22.1	23.2	26.3	32.5	33.5	32.5	28.4	26.8
87.5°	8.1	8.4	8.3	7.7	8.0	8.2	10.1	12.0	10.5	9.5	8.8
90°	5.4	4.7	4.2	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	7.0	6.7	6.5	6.3	6.4	6.5	6.6	6.6	6.6	6.5	6.4
95°	11.7	11.2	10.7	11.6	14.0	16.5	18.8	21.2	18.8	16.5	14.0
97.5°	14.6	13.5	12.3	15.1	21.9	28.6	35.3	42.1	35.3	28.6	21.9
100°	16.2	14.9	13.6	18.1	28.0	37.9	47.9	57.8	47.9	37.9	28.0
102.5°	39.8	50.1	60.4	66.7	68.8	70.8	72.9	75.0	72.9	70.8	68.8
105°	59.6	79.4	99.2	108.0	105.8	103.6	101.4	99.3	101.4	103.6	105.8
107.5°	75.4	99.2	122.9	133.9	132.2	130.4	128.7	126.8	128.7	130.4	132.2
110°	99.1	120.1	141.0	150.8	149.3	147.7	146.1	144.6	146.1	147.7	149.3



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	154.5	159.7	164.8	166.7	165.4	164.1	162.7	161.4	162.7	164.1	165.4
115°	197.8	196.0	194.2	192.7	191.5	190.3	188.9	187.7	188.9	190.3	191.5
117.5°	220.7	219.4	218.1	216.8	215.5	214.1	212.7	211.4	212.7	214.1	215.5
120°	236.7	235.4	234.1	232.9	231.9	230.8	229.6	228.5	229.6	230.8	231.9
122.5°	251.9	250.4	249.0	247.8	246.6	245.5	244.4	243.2	244.4	245.5	246.6
125°	273.2	271.8	270.4	269.2	268.3	267.3	266.4	265.5	266.4	267.3	268.3
127.5°	293.0	291.9	290.8	289.8	288.8	287.7	286.7	285.6	286.7	287.7	288.8
130°	305.7	304.9	304.1	303.1	301.9	300.7	299.6	298.4	299.6	300.7	301.9
132.5°	317.9	317.1	316.3	315.5	314.5	313.5	312.5	311.5	312.5	313.5	314.5
135°	335.4	334.7	334.1	333.2	331.9	330.8	329.6	328.5	329.6	330.8	331.9
137.5°	351.1	350.4	349.7	348.9	348.1	347.3	346.5	345.7	346.5	347.3	348.1
140°	361.5	360.7	359.9	359.2	358.6	358.0	357.5	356.9	357.5	358.0	358.6
142.5°	370.9	370.0	369.1	368.4	367.9	367.3	366.8	366.3	366.8	367.3	367.9
145°	383.8	382.5	381.3	380.7	380.8	380.9	381.0	381.0	381.0	380.9	380.8
147.5°	395.8	394.5	393.2	392.8	393.0	393.3	393.6	393.9	393.6	393.3	393.0
150°	402.9	401.7	400.6	400.2	400.7	401.2	401.7	402.2	401.7	401.2	400.7
152.5°	409.5	408.4	407.3	407.1	407.6	408.2	408.8	409.3	408.8	408.2	407.6
155°	418.8	418.0	417.1	417.0	417.6	418.3	418.9	419.6	418.9	418.3	417.6
157.5°	426.7	426.1	425.5	425.4	426.0	426.5	427.1	427.6	427.1	426.5	426.0
160°	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3	431.9	431.4	431.0
162.5°	435.5	435.0	434.7	434.7	435.2	435.7	436.1	436.5	436.1	435.7	435.2
165°	440.7	440.5	440.3	440.4	440.8	441.2	441.7	442.1	441.7	441.2	440.8
167.5°	444.8	444.6	444.4	444.5	444.9	445.5	445.9	446.3	445.9	445.5	444.9
170°	447.1	446.9	446.8	446.9	447.4	447.8	448.2	448.7	448.2	447.8	447.4
172.5°	448.6	448.5	448.3	448.5	448.9	449.3	449.8	450.2	449.8	449.3	448.9
175°	450.3	450.2	450.0	450.2	450.7	451.2	451.7	452.2	451.7	451.2	450.7
177.5°	450.9	450.8	450.8	450.9	451.3	451.7	452.1	452.5	452.1	451.7	451.3
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1462.6	1459.7	1454.3	1446.0	1441.1	1432.4	1426.6	1430.0	1430.8	1430.0	1429.2
5°	1423.3	1412.4	1397.5	1383.0	1369.7	1355.2	1347.0	1343.3	1336.2	1332.0	1330.0
7.5°	1375.7	1357.1	1336.0	1310.8	1289.4	1267.1	1255.7	1249.9	1235.2	1227.2	1220.1
10°	1340.3	1310.9	1289.8	1256.8	1236.7	1207.3	1187.2	1187.7	1167.6	1156.2	1148.0
12.5°	1301.1	1268.8	1233.7	1204.0	1176.0	1152.5	1128.2	1118.4	1097.0	1086.1	1063.9
15°	1236.2	1198.5	1161.4	1121.2	1092.9	1056.2	1021.2	978.4	943.8	913.9	905.7
17.5°	1165.2	1118.6	1081.4	1034.2	985.6	924.0	883.4	858.6	837.8	822.0	810.2
20°	1116.5	1069.1	1029.5	958.3	892.8	851.1	821.2	802.1	780.4	763.5	754.2
22.5°	1065.4	1015.9	961.8	882.4	831.4	797.9	771.2	749.3	734.7	721.3	713.0
25°	992.8	938.7	849.5	794.9	753.7	718.6	700.0	686.6	671.2	653.1	644.9
27.5°	916.1	830.0	766.0	725.4	686.0	663.2	646.5	626.5	612.7	604.6	596.0
30°	858.8	772.7	722.8	678.4	650.6	625.3	605.7	594.4	581.0	567.0	561.4
32.5°	794.9	726.1	678.2	641.3	613.0	591.5	576.0	557.6	548.0	539.4	527.6
35°	715.5	663.5	619.7	589.8	562.9	545.4	527.4	516.5	499.0	491.8	487.2
37.5°	648.2	603.1	570.5	538.9	517.7	498.3	487.3	470.0	462.4	452.4	442.6
40°	610.4	566.0	534.5	508.8	485.0	470.6	456.8	442.8	431.4	426.9	415.0
42.5°	571.6	535.5	504.0	475.7	459.9	444.6	427.1	416.9	405.1	397.6	390.2
45°	518.1	486.1	459.3	436.1	418.6	402.6	391.2	374.3	367.6	352.5	346.4
47.5°	471.1	441.3	415.8	393.7	376.6	366.2	349.6	336.3	325.6	316.4	308.5
50°	437.7	412.9	388.2	368.6	353.1	338.2	321.1	314.5	297.9	293.3	288.7
52.5°	407.2	383.6	360.9	341.7	326.3	311.7	296.8	288.0	276.9	272.3	268.9
55°	364.5	341.7	320.1	303.1	287.6	272.7	263.4	252.6	247.4	243.8	239.7
57.5°	321.5	301.1	284.6	267.3	251.8	239.9	229.1	222.7	217.3	212.6	207.6
60°	294.4	274.8	259.8	243.8	227.8	218.0	209.8	202.1	195.9	188.6	186.6
62.5°	265.5	248.3	234.7	219.0	205.2	196.2	188.3	181.1	173.6	163.1	160.2
65°	225.8	212.4	197.9	185.1	172.7	163.9	152.6	144.3	141.3	140.2	139.7
67.5°	190.0	177.2	164.8	151.7	140.4	132.3	126.5	125.2	123.1	122.5	121.1
70°	166.0	154.1	141.8	129.4	118.6	117.0	114.9	112.9	110.3	109.3	108.3
72.5°	144.5	132.3	119.9	110.0	105.3	103.4	101.4	99.3	97.6	96.5	95.8
75°	110.8	99.5	91.3	87.7	85.0	83.5	80.4	78.9	77.9	76.2	75.7
77.5°	79.8	73.4	69.6	67.4	64.6	63.0	61.2	59.7	58.6	58.3	57.5
80°	60.8	57.8	55.1	52.1	51.0	49.0	48.5	47.0	47.5	45.8	45.8
82.5°	47.3	43.3	41.1	39.7	38.7	37.1	36.5	35.7	35.9	34.7	34.7
85°	24.2	23.2	22.1	21.1	21.1	19.6	20.1	19.6	19.6	18.6	18.1
87.5°	8.6	8.3	7.6	7.7	7.8	7.5	7.6	7.3	7.3	7.4	7.0
90°	3.5	4.2	4.7	5.4	6.0	6.6	6.9	7.3	7.6	8.0	8.3
92.5°	6.3	6.5	6.7	7.0	7.3	7.6	7.8	8.0	8.2	8.3	8.5
95°	11.6	10.7	11.2	11.7	12.2	12.7	13.1	13.4	13.8	14.1	14.3
97.5°	15.1	12.3	13.5	14.6	15.9	17.1	17.4	17.7	17.9	18.2	18.4
100°	18.1	13.6	14.9	16.2	17.4	18.6	19.2	19.8	20.4	20.9	21.3
102.5°	66.7	60.4	50.1	39.8	29.5	19.1	19.9	20.6	21.4	22.1	22.6
105°	108.0	99.2	79.4	59.6	39.7	19.9	20.7	21.5	22.3	23.1	23.6
107.5°	133.9	122.9	99.2	75.4	51.6	27.9	27.1	26.3	25.4	24.6	24.3
110°	150.8	141.0	120.1	99.1	78.1	57.2	49.9	42.6	35.3	28.1	24.6



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	166.7	164.8	159.7	154.5	149.3	144.1	117.6	91.2	64.7	38.3	25.1
115°	192.7	194.2	196.0	197.8	199.7	201.5	167.8	134.3	100.7	67.1	47.7
117.5°	216.8	218.1	219.4	220.7	221.9	223.2	215.0	206.9	198.7	190.7	178.0
120°	232.9	234.1	235.4	236.7	238.0	239.3	240.2	241.1	242.0	242.8	238.3
122.5°	247.8	249.0	250.4	251.9	253.4	254.8	255.3	255.8	256.3	256.8	256.1
125°	269.2	270.4	271.8	273.2	274.5	275.9	276.4	276.9	277.4	277.9	278.3
127.5°	289.8	290.8	291.9	293.0	294.0	295.0	295.7	296.5	297.2	297.9	298.3
130°	303.1	304.1	304.9	305.7	306.5	307.3	308.0	308.8	309.6	310.4	310.8
132.5°	315.5	316.3	317.1	317.9	318.7	319.5	320.2	320.9	321.5	322.2	322.6
135°	333.2	334.1	334.7	335.4	336.0	336.7	337.4	338.1	338.8	339.5	339.8
137.5°	348.9	349.7	350.4	351.1	351.9	352.6	353.4	354.1	354.8	355.5	355.7
140°	359.2	359.9	360.7	361.5	362.3	363.0	363.8	364.4	365.1	365.7	365.9
142.5°	368.4	369.1	370.0	370.9	371.8	372.7	373.3	374.0	374.6	375.2	375.3
145°	380.7	381.3	382.5	383.8	385.1	386.3	386.8	387.3	387.8	388.3	388.4
147.5°	392.8	393.2	394.5	395.8	397.0	398.2	398.5	398.9	399.3	399.7	399.7
150°	400.2	400.6	401.7	402.9	404.0	405.3	405.7	406.1	406.5	407.0	407.0
152.5°	407.1	407.3	408.4	409.5	410.6	411.7	412.1	412.6	413.0	413.4	413.4
155°	417.0	417.1	418.0	418.8	419.7	420.5	421.0	421.4	421.8	422.3	422.2
157.5°	425.4	425.5	426.1	426.7	427.3	427.9	428.4	428.9	429.4	429.8	429.8
160°	430.6	430.6	431.0	431.4	431.9	432.3	432.7	433.2	433.6	434.0	434.0
162.5°	434.7	434.7	435.0	435.5	435.9	436.3	436.8	437.2	437.7	438.2	438.2
165°	440.4	440.3	440.5	440.7	440.9	441.1	441.6	442.1	442.6	443.1	443.1
167.5°	444.5	444.4	444.6	444.8	445.0	445.2	445.8	446.3	446.8	447.3	447.2
170°	446.9	446.8	446.9	447.1	447.2	447.4	447.9	448.4	448.9	449.4	449.3
172.5°	448.5	448.3	448.5	448.6	448.8	448.9	449.4	449.9	450.4	450.9	450.9
175°	450.2	450.0	450.2	450.3	450.5	450.6	451.1	451.6	452.1	452.6	452.5
177.5°	450.9	450.8	450.8	450.9	450.9	451.0	451.4	451.8	452.2	452.6	452.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1424.6	1425.4	1424.2	1425.0	1424.2	1425.4	1424.6	1429.2	1430.0	1430.8	1430.0
5°	1327.4	1321.2	1320.2	1318.6	1320.2	1321.2	1327.4	1330.0	1332.0	1336.2	1343.3
7.5°	1211.3	1210.3	1207.8	1204.2	1207.8	1210.3	1211.3	1220.1	1227.2	1235.2	1249.9
10°	1136.6	1134.1	1133.6	1129.9	1133.6	1134.1	1136.6	1148.0	1156.2	1167.6	1187.7
12.5°	1049.2	1032.6	1030.9	1021.9	1030.9	1032.6	1049.2	1063.9	1086.1	1097.0	1118.4
15°	893.3	890.3	879.9	873.2	879.9	890.3	893.3	905.7	913.9	943.8	978.4
17.5°	804.3	794.2	790.9	789.5	790.9	794.2	804.3	810.2	822.0	837.8	858.6
20°	746.9	737.7	736.1	735.1	736.1	737.7	746.9	754.2	763.5	780.4	802.1
22.5°	707.3	697.6	693.7	690.5	693.7	697.6	707.3	713.0	721.3	734.7	749.3
25°	639.7	636.1	634.1	633.0	634.1	636.1	639.7	644.9	653.1	671.2	686.6
27.5°	586.8	578.9	577.3	574.7	577.3	578.9	586.8	596.0	604.6	612.7	626.5
30°	556.7	554.1	550.6	547.4	550.6	554.1	556.7	561.4	567.0	581.0	594.4
32.5°	521.3	519.1	515.9	514.4	515.9	519.1	521.3	527.6	539.4	548.0	557.6
35°	482.0	474.7	471.7	467.1	471.7	474.7	482.0	487.2	491.8	499.0	516.5
37.5°	440.4	436.7	432.3	433.8	432.3	436.7	440.4	442.6	452.4	462.4	470.0
40°	408.3	405.7	404.7	404.1	404.7	405.7	408.3	415.0	426.9	431.4	442.8
42.5°	382.7	375.6	372.9	372.8	372.9	375.6	382.7	390.2	397.6	405.1	416.9
45°	343.9	337.1	332.4	333.1	332.4	337.1	343.9	346.4	352.5	367.6	374.3
47.5°	304.1	303.9	300.9	301.8	300.9	303.9	304.1	308.5	316.4	325.6	336.3
50°	285.1	282.0	279.9	280.4	279.9	282.0	285.1	288.7	293.3	297.9	314.5
52.5°	266.9	264.3	262.6	264.8	262.6	264.3	266.9	268.9	272.3	276.9	288.0
55°	237.1	234.0	233.5	233.0	233.5	234.0	237.1	239.7	243.8	247.4	252.6
57.5°	203.8	201.8	198.6	197.3	198.6	201.8	203.8	207.6	212.6	217.3	222.7
60°	179.9	175.8	170.7	170.1	170.7	175.8	179.9	186.6	188.6	195.9	202.1
62.5°	158.0	157.2	156.2	156.1	156.2	157.2	158.0	160.2	163.1	173.6	181.1
65°	138.7	138.1	138.7	139.2	138.7	138.1	138.7	139.7	140.2	141.3	144.3
67.5°	120.9	119.9	119.0	119.4	119.0	119.9	120.9	121.1	122.5	123.1	125.2
70°	107.2	106.7	106.2	106.2	106.2	106.7	107.2	108.3	109.3	110.3	112.9
72.5°	94.0	93.9	93.4	93.0	93.4	93.9	94.0	95.8	96.5	97.6	99.3
75°	75.2	74.2	74.2	74.2	74.2	74.2	75.2	75.7	76.2	77.9	78.9
77.5°	57.4	56.9	56.2	55.8	56.2	56.9	57.4	57.5	58.3	58.6	59.7
80°	45.3	44.8	44.3	44.3	44.3	44.8	45.3	45.8	45.8	47.5	47.0
82.5°	34.6	34.1	34.0	33.6	34.0	34.1	34.6	34.7	34.7	35.9	35.7
85°	18.6	19.1	18.6	19.6	18.6	19.1	18.6	18.1	18.6	19.6	19.6
87.5°	7.1	6.7	7.1	6.7	7.1	6.7	7.1	7.0	7.4	7.3	7.3
90°	8.4	8.5	8.7	8.8	8.7	8.5	8.4	8.3	8.0	7.6	7.3
92.5°	8.6	8.7	8.7	8.8	8.7	8.7	8.6	8.5	8.3	8.2	8.0
95°	14.2	14.1	14.1	14.0	14.1	14.1	14.2	14.3	14.1	13.8	13.4
97.5°	18.5	18.6	18.7	18.8	18.7	18.6	18.5	18.4	18.2	17.9	17.7
100°	21.4	21.6	21.7	21.9	21.7	21.6	21.4	21.3	20.9	20.4	19.8
102.5°	22.8	23.0	23.2	23.4	23.2	23.0	22.8	22.6	22.1	21.4	20.6
105°	23.9	24.2	24.5	24.8	24.5	24.2	23.9	23.6	23.1	22.3	21.5
107.5°	24.6	24.9	25.2	25.5	25.2	24.9	24.6	24.3	24.6	25.4	26.3
110°	24.9	25.2	25.5	25.8	25.5	25.2	24.9	24.6	28.1	35.3	42.6



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	25.3	25.5	25.9	26.1	25.9	25.5	25.3	25.1	38.3	64.7	91.2
115°	42.4	37.3	32.0	26.8	32.0	37.3	42.4	47.7	67.1	100.7	134.3
117.5°	160.9	143.7	126.5	109.4	126.5	143.7	160.9	178.0	190.7	198.7	206.9
120°	228.5	218.7	208.9	199.1	208.9	218.7	228.5	238.3	242.8	242.0	241.1
122.5°	254.3	252.4	250.4	248.5	250.4	252.4	254.3	256.1	256.8	256.3	255.8
125°	278.5	278.7	278.9	279.1	278.9	278.7	278.5	278.3	277.9	277.4	276.9
127.5°	298.4	298.4	298.4	298.5	298.4	298.4	298.4	298.3	297.9	297.2	296.5
130°	310.7	310.6	310.6	310.5	310.6	310.6	310.7	310.8	310.4	309.6	308.8
132.5°	322.4	322.4	322.3	322.2	322.3	322.4	322.4	322.6	322.2	321.5	320.9
135°	339.7	339.5	339.4	339.2	339.4	339.5	339.7	339.8	339.5	338.8	338.1
137.5°	355.5	355.3	355.0	354.8	355.0	355.3	355.5	355.7	355.5	354.8	354.1
140°	365.5	365.2	364.8	364.4	364.8	365.2	365.5	365.9	365.7	365.1	364.4
142.5°	374.9	374.6	374.2	373.8	374.2	374.6	374.9	375.3	375.2	374.6	374.0
145°	388.0	387.7	387.3	386.9	387.3	387.7	388.0	388.4	388.3	387.8	387.3
147.5°	399.4	399.1	398.8	398.5	398.8	399.1	399.4	399.7	399.7	399.3	398.9
150°	406.7	406.3	405.9	405.6	405.9	406.3	406.7	407.0	407.0	406.5	406.1
152.5°	412.9	412.5	412.0	411.5	412.0	412.5	412.9	413.4	413.4	413.0	412.6
155°	421.6	421.1	420.5	419.9	420.5	421.1	421.6	422.2	422.3	421.8	421.4
157.5°	429.2	428.7	428.1	427.6	428.1	428.7	429.2	429.8	429.8	429.4	428.9
160°	433.5	433.0	432.5	432.0	432.5	433.0	433.5	434.0	434.0	433.6	433.2
162.5°	437.5	436.9	436.3	435.7	436.3	436.9	437.5	438.2	438.2	437.7	437.2
165°	442.6	442.1	441.6	441.1	441.6	442.1	442.6	443.1	443.1	442.6	442.1
167.5°	446.6	445.9	445.2	444.5	445.2	445.9	446.6	447.2	447.3	446.8	446.3
170°	448.7	448.0	447.4	446.7	447.4	448.0	448.7	449.3	449.4	448.9	448.4
172.5°	450.2	449.6	448.9	448.3	448.9	449.6	450.2	450.9	450.9	450.4	449.9
175°	451.8	451.1	450.3	449.6	450.3	451.1	451.8	452.5	452.6	452.1	451.6
177.5°	452.0	451.5	451.0	450.5	451.0	451.5	452.0	452.5	452.6	452.2	451.8
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331675-840
 CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1426.6	1432.4	1441.1	1446.0	1454.3	1459.7	1462.6	1467.9	1470.8	1481.1	1491.9
5°	1347.0	1355.2	1369.7	1383.0	1397.5	1412.4	1423.3	1435.6	1446.9	1466.5	1487.2
7.5°	1255.7	1267.1	1289.4	1310.8	1336.0	1357.1	1375.7	1396.8	1415.7	1443.8	1473.1
10°	1187.2	1207.3	1236.7	1256.8	1289.8	1310.9	1340.3	1363.4	1389.8	1426.8	1459.9
12.5°	1128.2	1152.5	1176.0	1204.0	1233.7	1268.8	1301.1	1330.9	1362.1	1400.5	1439.3
15°	1021.2	1056.2	1092.9	1121.2	1161.4	1198.5	1236.2	1276.4	1314.5	1360.4	1410.9
17.5°	883.4	924.0	985.6	1034.2	1081.4	1118.6	1165.2	1213.9	1258.8	1314.1	1370.4
20°	821.2	851.1	892.8	958.3	1029.5	1069.1	1116.5	1170.1	1221.7	1282.0	1342.3
22.5°	771.2	797.9	831.4	882.4	961.8	1015.9	1065.4	1119.8	1179.6	1241.2	1308.1
25°	700.0	718.6	753.7	794.9	849.5	938.7	992.8	1047.4	1112.5	1178.4	1254.7
27.5°	646.5	663.2	686.0	725.4	766.0	830.0	916.1	975.7	1040.5	1114.7	1193.9
30°	605.7	625.3	650.6	678.4	722.8	772.7	858.8	927.9	991.8	1068.1	1152.7
32.5°	576.0	591.5	613.0	641.3	678.2	726.1	794.9	878.8	941.1	1021.5	1109.7
35°	527.4	545.4	562.9	589.8	619.7	663.5	715.5	805.2	867.1	946.4	1035.1
37.5°	487.3	498.3	517.7	538.9	570.5	603.1	648.2	728.7	795.6	873.5	964.3
40°	456.8	470.6	485.0	508.8	534.5	566.0	610.4	670.1	746.9	823.2	911.9
42.5°	427.1	444.6	459.9	475.7	504.0	535.5	571.6	622.3	700.7	773.0	859.1
45°	391.2	402.6	418.6	436.1	459.3	486.1	518.1	562.4	637.6	700.0	780.9
47.5°	349.6	366.2	376.6	393.7	415.8	441.3	471.1	509.4	570.4	628.8	703.9
50°	321.1	338.2	353.1	368.6	388.2	412.9	437.7	474.7	523.7	585.1	655.2
52.5°	296.8	311.7	326.3	341.7	360.9	383.6	407.2	439.7	481.7	538.1	606.1
55°	263.4	272.7	287.6	303.1	320.1	341.7	364.5	391.7	427.9	475.2	530.5
57.5°	229.1	239.9	251.8	267.3	284.6	301.1	321.5	346.3	374.8	417.7	464.8
60°	209.8	218.0	227.8	243.8	259.8	274.8	294.4	315.0	341.7	378.9	419.1
62.5°	188.3	196.2	205.2	219.0	234.7	248.3	265.5	287.3	310.0	343.9	379.1
65°	152.6	163.9	172.7	185.1	197.9	212.4	225.8	243.3	263.4	290.2	321.6
67.5°	126.5	132.3	140.4	151.7	164.8	177.2	190.0	203.6	221.1	241.8	266.7
70°	114.9	117.0	118.6	129.4	141.8	154.1	166.0	178.8	193.8	210.9	232.5
72.5°	101.4	103.4	105.3	110.0	119.9	132.3	144.5	154.1	168.2	182.4	200.0
75°	80.4	83.5	85.0	87.7	91.3	99.5	110.8	120.1	128.4	139.2	153.1
77.5°	61.2	63.0	64.6	67.4	69.6	73.4	79.8	88.2	95.8	102.2	111.8
80°	48.5	49.0	51.0	52.1	55.1	57.8	60.8	67.6	75.2	77.9	84.5
82.5°	36.5	37.1	38.7	39.7	41.1	43.3	47.3	49.0	55.0	58.5	62.7
85°	20.1	19.6	21.1	21.1	22.1	23.2	24.2	26.8	28.4	32.5	33.5
87.5°	7.6	7.5	7.8	7.7	7.6	8.3	8.6	8.8	9.5	10.5	12.0
90°	6.9	6.6	6.0	5.4	4.7	4.2	3.5	2.7	1.9	1.1	0.3
92.5°	7.8	7.6	7.3	7.0	6.7	6.5	6.3	6.4	6.5	6.6	6.6
95°	13.1	12.7	12.2	11.7	11.2	10.7	11.6	14.0	16.5	18.8	21.2
97.5°	17.4	17.1	15.9	14.6	13.5	12.3	15.1	21.9	28.6	35.3	42.1
100°	19.2	18.6	17.4	16.2	14.9	13.6	18.1	28.0	37.9	47.9	57.8
102.5°	19.9	19.1	29.5	39.8	50.1	60.4	66.7	68.8	70.8	72.9	75.0
105°	20.7	19.9	39.7	59.6	79.4	99.2	108.0	105.8	103.6	101.4	99.3
107.5°	27.1	27.9	51.6	75.4	99.2	122.9	133.9	132.2	130.4	128.7	126.8
110°	49.9	57.2	78.1	99.1	120.1	141.0	150.8	149.3	147.7	146.1	144.6



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	117.6	144.1	149.3	154.5	159.7	164.8	166.7	165.4	164.1	162.7	161.4
115°	167.8	201.5	199.7	197.8	196.0	194.2	192.7	191.5	190.3	188.9	187.7
117.5°	215.0	223.2	221.9	220.7	219.4	218.1	216.8	215.5	214.1	212.7	211.4
120°	240.2	239.3	238.0	236.7	235.4	234.1	232.9	231.9	230.8	229.6	228.5
122.5°	255.3	254.8	253.4	251.9	250.4	249.0	247.8	246.6	245.5	244.4	243.2
125°	276.4	275.9	274.5	273.2	271.8	270.4	269.2	268.3	267.3	266.4	265.5
127.5°	295.7	295.0	294.0	293.0	291.9	290.8	289.8	288.8	287.7	286.7	285.6
130°	308.0	307.3	306.5	305.7	304.9	304.1	303.1	301.9	300.7	299.6	298.4
132.5°	320.2	319.5	318.7	317.9	317.1	316.3	315.5	314.5	313.5	312.5	311.5
135°	337.4	336.7	336.0	335.4	334.7	334.1	333.2	331.9	330.8	329.6	328.5
137.5°	353.4	352.6	351.9	351.1	350.4	349.7	348.9	348.1	347.3	346.5	345.7
140°	363.8	363.0	362.3	361.5	360.7	359.9	359.2	358.6	358.0	357.5	356.9
142.5°	373.3	372.7	371.8	370.9	370.0	369.1	368.4	367.9	367.3	366.8	366.3
145°	386.8	386.3	385.1	383.8	382.5	381.3	380.7	380.8	380.9	381.0	381.0
147.5°	398.5	398.2	397.0	395.8	394.5	393.2	392.8	393.0	393.3	393.6	393.9
150°	405.7	405.3	404.0	402.9	401.7	400.6	400.2	400.7	401.2	401.7	402.2
152.5°	412.1	411.7	410.6	409.5	408.4	407.3	407.1	407.6	408.2	408.8	409.3
155°	421.0	420.5	419.7	418.8	418.0	417.1	417.0	417.6	418.3	418.9	419.6
157.5°	428.4	427.9	427.3	426.7	426.1	425.5	425.4	426.0	426.5	427.1	427.6
160°	432.7	432.3	431.9	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3
162.5°	436.8	436.3	435.9	435.5	435.0	434.7	434.7	435.2	435.7	436.1	436.5
165°	441.6	441.1	440.9	440.7	440.5	440.3	440.4	440.8	441.2	441.7	442.1
167.5°	445.8	445.2	445.0	444.8	444.6	444.4	444.5	444.9	445.5	445.9	446.3
170°	447.9	447.4	447.2	447.1	446.9	446.8	446.9	447.4	447.8	448.2	448.7
172.5°	449.4	448.9	448.8	448.6	448.5	448.3	448.5	448.9	449.3	449.8	450.2
175°	451.1	450.6	450.5	450.3	450.2	450.0	450.2	450.7	451.2	451.7	452.2
177.5°	451.4	451.0	450.9	450.9	450.8	450.8	450.9	451.3	451.7	452.1	452.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1492.3	1493.5	1501.8	1505.4	1512.9	1515.7	1519.0	1518.2	1518.2	1519.8	1531.5
5°	1495.4	1505.7	1521.2	1536.1	1550.5	1563.0	1571.2	1579.4	1582.6	1597.5	1610.9
7.5°	1490.1	1509.0	1534.6	1557.4	1584.7	1606.1	1623.8	1639.8	1650.7	1672.4	1694.8
10°	1483.1	1509.8	1538.7	1568.1	1605.8	1634.1	1662.9	1685.2	1692.3	1724.8	1743.4
12.5°	1469.1	1504.9	1541.7	1579.6	1616.5	1655.6	1687.3	1709.5	1734.8	1764.0	1798.3
15°	1448.0	1489.2	1537.2	1586.2	1638.7	1686.2	1720.2	1758.9	1786.7	1818.7	1848.6
17.5°	1417.7	1470.9	1531.9	1588.5	1649.3	1700.3	1747.1	1784.2	1803.8	1822.0	1826.4
20°	1393.9	1451.1	1522.8	1589.7	1650.6	1709.4	1755.8	1786.7	1791.8	1792.3	1765.0
22.5°	1367.9	1432.5	1507.5	1576.2	1648.9	1714.3	1750.4	1763.6	1743.1	1708.2	1655.4
25°	1320.2	1394.9	1482.1	1560.3	1639.8	1701.6	1714.0	1690.8	1619.1	1543.9	1448.6
27.5°	1268.4	1352.4	1445.8	1533.0	1617.5	1655.9	1629.1	1545.5	1416.4	1304.2	1168.3
30°	1230.5	1324.8	1416.5	1514.0	1592.4	1608.8	1547.5	1424.3	1273.7	1104.7	969.2
32.5°	1187.2	1286.1	1386.8	1487.6	1553.2	1537.1	1435.7	1284.0	1107.6	941.4	813.2
35°	1125.3	1227.4	1336.2	1437.1	1478.9	1409.4	1257.8	1060.4	879.9	724.8	636.6
37.5°	1053.9	1165.0	1278.1	1370.9	1367.9	1251.9	1045.5	841.7	690.0	598.2	535.5
40°	1003.1	1115.5	1237.7	1316.1	1282.5	1131.5	907.8	715.5	604.7	531.5	485.5
42.5°	954.5	1067.2	1188.6	1250.9	1192.7	1006.9	784.1	633.4	542.0	484.8	447.7
45°	871.7	990.8	1103.2	1137.7	1033.6	828.9	634.1	524.7	463.9	421.7	395.9
47.5°	790.7	907.9	1010.5	1011.1	870.2	672.2	534.8	454.1	402.2	369.5	350.7
50°	741.2	852.6	938.7	925.3	765.5	597.9	478.4	408.8	365.5	340.2	320.6
52.5°	685.6	793.7	868.2	830.0	676.8	526.2	427.7	369.2	333.4	311.3	293.9
55°	604.7	700.5	753.2	695.4	552.1	437.7	361.3	315.5	288.7	270.1	255.2
57.5°	525.1	604.3	637.3	570.2	454.7	362.9	305.7	271.2	244.7	231.4	223.6
60°	475.2	542.8	566.0	491.8	395.4	317.5	270.6	238.6	219.0	210.4	202.6
62.5°	426.2	481.4	491.0	422.9	344.7	277.9	237.6	210.7	197.6	189.2	182.0
65°	353.7	393.3	388.7	334.1	272.7	220.7	191.3	174.7	164.9	153.1	140.2
67.5°	291.1	315.4	300.7	259.8	208.1	171.5	152.3	139.8	127.6	116.4	113.4
70°	251.6	265.5	250.0	212.4	170.7	143.8	128.4	113.4	106.2	103.6	99.0
72.5°	213.6	218.4	201.8	169.5	138.9	119.1	104.0	95.6	91.8	89.6	86.6
75°	160.4	156.7	142.3	117.0	96.4	83.0	78.4	75.2	72.7	70.6	69.1
77.5°	112.6	107.3	94.4	78.0	67.2	60.7	58.0	56.2	55.0	54.0	52.5
80°	84.5	80.9	68.1	55.6	51.0	48.0	46.4	44.3	44.3	43.3	41.7
82.5°	61.9	57.9	46.6	40.8	38.3	36.4	35.2	34.0	33.6	33.8	32.7
85°	32.5	26.3	23.2	22.1	20.6	19.6	20.1	19.1	19.1	19.1	18.6
87.5°	10.1	8.2	8.0	7.7	8.3	8.4	8.1	8.2	8.7	8.4	8.9
90°	1.1	1.9	2.7	3.5	4.2	4.7	5.4	6.0	6.6	6.9	7.3
92.5°	6.6	6.5	6.4	6.3	6.5	6.7	7.0	7.3	7.6	7.8	8.0
95°	18.8	16.5	14.0	11.6	10.7	11.2	11.7	12.2	12.7	13.1	13.4
97.5°	35.3	28.6	21.9	15.1	12.3	13.5	14.6	15.9	17.1	17.4	17.7
100°	47.9	37.9	28.0	18.1	13.6	14.9	16.2	17.4	18.6	19.2	19.8
102.5°	72.9	70.8	68.8	66.7	60.4	50.1	39.8	29.5	19.1	19.9	20.6
105°	101.4	103.6	105.8	108.0	99.2	79.4	59.6	39.7	19.9	20.7	21.5
107.5°	128.7	130.4	132.2	133.9	122.9	99.2	75.4	51.6	27.9	27.1	26.3
110°	146.1	147.7	149.3	150.8	141.0	120.1	99.1	78.1	57.2	49.9	42.6



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	162.7	164.1	165.4	166.7	164.8	159.7	154.5	149.3	144.1	117.6	91.2
115°	188.9	190.3	191.5	192.7	194.2	196.0	197.8	199.7	201.5	167.8	134.3
117.5°	212.7	214.1	215.5	216.8	218.1	219.4	220.7	221.9	223.2	215.0	206.9
120°	229.6	230.8	231.9	232.9	234.1	235.4	236.7	238.0	239.3	240.2	241.1
122.5°	244.4	245.5	246.6	247.8	249.0	250.4	251.9	253.4	254.8	255.3	255.8
125°	266.4	267.3	268.3	269.2	270.4	271.8	273.2	274.5	275.9	276.4	276.9
127.5°	286.7	287.7	288.8	289.8	290.8	291.9	293.0	294.0	295.0	295.7	296.5
130°	299.6	300.7	301.9	303.1	304.1	304.9	305.7	306.5	307.3	308.0	308.8
132.5°	312.5	313.5	314.5	315.5	316.3	317.1	317.9	318.7	319.5	320.2	320.9
135°	329.6	330.8	331.9	333.2	334.1	334.7	335.4	336.0	336.7	337.4	338.1
137.5°	346.5	347.3	348.1	348.9	349.7	350.4	351.1	351.9	352.6	353.4	354.1
140°	357.5	358.0	358.6	359.2	359.9	360.7	361.5	362.3	363.0	363.8	364.4
142.5°	366.8	367.3	367.9	368.4	369.1	370.0	370.9	371.8	372.7	373.3	374.0
145°	381.0	380.9	380.8	380.7	381.3	382.5	383.8	385.1	386.3	386.8	387.3
147.5°	393.6	393.3	393.0	392.8	393.2	394.5	395.8	397.0	398.2	398.5	398.9
150°	401.7	401.2	400.7	400.2	400.6	401.7	402.9	404.0	405.3	405.7	406.1
152.5°	408.8	408.2	407.6	407.1	407.3	408.4	409.5	410.6	411.7	412.1	412.6
155°	418.9	418.3	417.6	417.0	417.1	418.0	418.8	419.7	420.5	421.0	421.4
157.5°	427.1	426.5	426.0	425.4	425.5	426.1	426.7	427.3	427.9	428.4	428.9
160°	431.9	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3	432.7	433.2
162.5°	436.1	435.7	435.2	434.7	434.7	435.0	435.5	435.9	436.3	436.8	437.2
165°	441.7	441.2	440.8	440.4	440.3	440.5	440.7	440.9	441.1	441.6	442.1
167.5°	445.9	445.5	444.9	444.5	444.4	444.6	444.8	445.0	445.2	445.8	446.3
170°	448.2	447.8	447.4	446.9	446.8	446.9	447.1	447.2	447.4	447.9	448.4
172.5°	449.8	449.3	448.9	448.5	448.3	448.5	448.6	448.8	448.9	449.4	449.9
175°	451.7	451.2	450.7	450.2	450.0	450.2	450.3	450.5	450.6	451.1	451.6
177.5°	452.1	451.7	451.3	450.9	450.8	450.8	450.9	450.9	451.0	451.4	451.8
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1535.5	1540.9	1543.4	1543.4	1546.3	1545.0	1543.8
5°	1623.8	1633.6	1635.7	1645.0	1651.6	1649.5	1650.6
7.5°	1711.5	1727.3	1742.8	1750.0	1751.1	1755.2	1756.8
10°	1765.5	1778.5	1802.7	1799.1	1817.1	1827.5	1810.4
12.5°	1817.6	1834.9	1851.7	1856.3	1866.6	1869.9	1863.2
15°	1864.5	1873.8	1874.8	1872.3	1875.3	1872.8	1863.0
17.5°	1820.6	1805.5	1775.0	1760.6	1749.2	1732.2	1725.5
20°	1748.0	1703.6	1652.1	1631.5	1607.3	1559.8	1571.2
22.5°	1591.3	1540.8	1489.2	1429.1	1400.3	1355.3	1352.6
25°	1347.5	1260.4	1164.5	1097.5	1058.3	1013.5	993.9
27.5°	1047.6	938.0	859.4	819.6	783.5	747.9	746.4
30°	850.5	768.1	707.2	673.3	651.1	636.1	639.2
32.5°	716.9	660.5	619.5	591.2	574.8	563.5	563.3
35°	586.1	547.4	521.2	509.3	497.5	489.2	489.7
37.5°	501.6	478.4	463.7	450.6	443.2	439.2	437.0
40°	458.3	439.2	427.9	420.1	413.9	408.3	407.3
42.5°	424.0	408.3	396.9	390.8	385.1	381.0	380.0
45°	376.3	363.5	353.1	346.4	343.9	340.2	340.2
47.5°	334.8	322.0	314.1	309.8	305.4	303.0	302.9
50°	306.7	296.9	289.7	287.1	283.5	282.0	281.4
52.5°	281.6	274.3	269.1	267.3	265.8	263.8	264.2
55°	247.4	243.3	241.3	239.7	237.1	234.0	236.1
57.5°	218.6	215.2	209.6	204.8	202.4	200.3	201.1
60°	198.4	191.3	184.0	178.3	176.8	172.2	172.2
62.5°	172.9	162.8	153.9	150.8	149.2	147.0	146.6
65°	133.0	128.9	126.8	124.7	123.7	123.7	122.7
67.5°	110.2	108.6	106.3	105.7	104.7	104.4	104.1
70°	97.5	95.3	94.3	93.8	92.8	93.3	91.8
72.5°	85.0	83.4	83.2	81.9	81.2	81.3	80.2
75°	67.1	67.1	66.4	65.9	64.9	64.4	64.9
77.5°	51.5	51.6	50.7	50.6	50.5	50.6	50.1
80°	41.2	41.7	41.2	40.7	40.2	40.7	40.2
82.5°	32.6	31.8	31.7	31.6	31.5	31.2	31.1
85°	18.6	19.1	18.6	18.1	18.1	18.1	18.6
87.5°	8.6	8.6	8.7	8.7	8.7	8.8	8.4
90°	7.6	8.0	8.3	8.4	8.5	8.7	8.8
92.5°	8.2	8.3	8.5	8.6	8.7	8.7	8.8
95°	13.8	14.1	14.3	14.2	14.1	14.1	14.0
97.5°	17.9	18.2	18.4	18.5	18.6	18.7	18.8
100°	20.4	20.9	21.3	21.4	21.6	21.7	21.9
102.5°	21.4	22.1	22.6	22.8	23.0	23.2	23.4
105°	22.3	23.1	23.6	23.9	24.2	24.5	24.8
107.5°	25.4	24.6	24.3	24.6	24.9	25.2	25.5
110°	35.3	28.1	24.6	24.9	25.2	25.5	25.8



TEST NUMBER: P331675-840

CATALOG NUMBER: SA2XXRDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	64.7	38.3	25.1	25.3	25.5	25.9	26.1
115°	100.7	67.1	47.7	42.4	37.3	32.0	26.8
117.5°	198.7	190.7	178.0	160.9	143.7	126.5	109.4
120°	242.0	242.8	238.3	228.5	218.7	208.9	199.1
122.5°	256.3	256.8	256.1	254.3	252.4	250.4	248.5
125°	277.4	277.9	278.3	278.5	278.7	278.9	279.1
127.5°	297.2	297.9	298.3	298.4	298.4	298.4	298.5
130°	309.6	310.4	310.8	310.7	310.6	310.6	310.5
132.5°	321.5	322.2	322.6	322.4	322.4	322.3	322.2
135°	338.8	339.5	339.8	339.7	339.5	339.4	339.2
137.5°	354.8	355.5	355.7	355.5	355.3	355.0	354.8
140°	365.1	365.7	365.9	365.5	365.2	364.8	364.4
142.5°	374.6	375.2	375.3	374.9	374.6	374.2	373.8
145°	387.8	388.3	388.4	388.0	387.7	387.3	386.9
147.5°	399.3	399.7	399.7	399.4	399.1	398.8	398.5
150°	406.5	407.0	407.0	406.7	406.3	405.9	405.6
152.5°	413.0	413.4	413.4	412.9	412.5	412.0	411.5
155°	421.8	422.3	422.2	421.6	421.1	420.5	419.9
157.5°	429.4	429.8	429.8	429.2	428.7	428.1	427.6
160°	433.6	434.0	434.0	433.5	433.0	432.5	432.0
162.5°	437.7	438.2	438.2	437.5	436.9	436.3	435.7
165°	442.6	443.1	443.1	442.6	442.1	441.6	441.1
167.5°	446.8	447.3	447.2	446.6	445.9	445.2	444.5
170°	448.9	449.4	449.3	448.7	448.0	447.4	446.7
172.5°	450.4	450.9	450.9	450.2	449.6	448.9	448.3
175°	452.1	452.6	452.5	451.8	451.1	450.3	449.6
177.5°	452.2	452.6	452.5	452.0	451.5	451.0	450.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2

(END OF REPORT)