

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332604-830

Luminaire Tested: **SA4XXDIP-C795D810U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332604-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D810U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6261.5 lumens
Efficiency: N/A
Efficacy: 136.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332604-830
CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332604-830

CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43	43	43	43	
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	42	41	36	36	36	36	
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31	31	31	31	
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26	26	26	26	
5	68	57	49	43	63	53	45	40	45	40	35	38	34	31	32	29	26	23	23	23	23	
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20	20	20	20	
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18	18	18	18	
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16	16	16	16	
9	50	38	31	25	46	36	29	24	31	25	22	27	22	19	22	19	16	14	14	14	14	
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13	13	13	13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10101	10101	10101
5°	10131	10009	10083
10°	10067	9928	9977
15°	9947	9787	9812
20°	9784	9613	9620
25°	9600	9413	9386
30°	9374	9177	9093
35°	9140	8932	8814
40°	8896	8652	8495
45°	8643	8379	8218
50°	8361	8133	7882
55°	8058	7817	7562
60°	7753	7463	7237
65°	7412	7125	6837
70°	7027	6675	6413
75°	6441	6129	5973
80°	5732	5500	5360
85°	5011	4826	4733



TEST NUMBER: P332604-830

CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	1.9
10°-20°	332.0	5.3
20°-30°	488.6	7.8
30°-40°	568.1	9.1
40°-50°	568.1	9.1
50°-60°	496.9	7.9
60°-70°	369.0	5.9
70°-80°	209.7	3.3
80°-90°	63.4	1.0
90°-100°	33.7	0.5
100°-110°	214.9	3.4
110°-120°	411.0	6.6
120°-130°	521.8	8.3
130°-140°	558.3	8.9
140°-150°	522.1	8.3
150°-160°	421.0	6.7
160°-170°	271.5	4.3
170°-180°	93.6	1.5
0°-30°	938.5	15.0
0°-40°	1506.5	24.1
0°-60°	2571.5	41.1
0°-90°	3213.6	51.3
90°-120°	659.6	10.5
90°-150°	2261.8	36.1
90°-180°	3048.0	48.7
0°-180°	6261.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1251	1251	1251	1251	1251	
5°	1250	1246	1235	1245	1244	119
15°	1190	1185	1171	1176	1174	335
25°	1078	1070	1057	1057	1054	496
35°	927	920	906	899	894	580
45°	757	749	734	723	720	583
55°	572	569	555	544	537	513
65°	388	383	373	363	358	384
75°	206	202	196	193	192	219
85°	54	54	52	52	51	60
90°	2	10	16	20	22	5
95°	40	17	16	20	21	52
105°	222	226	230	235	210	232
115°	414	416	416	417	417	407
125°	582	585	584	586	587	520
135°	722	722	724	726	727	556
145°	833	835	835	836	837	520
155°	913	914	912	914	912	421
165°	963	960	960	965	959	272
175°	985	981	982	987	979	94
180°	985	985	985	985	985	



TEST NUMBER: P332604-830

CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2
2.5°	1254.4	1253.9	1253.3	1252.8	1252.3	1251.0	1249.1	1247.1	1245.1	1243.2	1244.9
5°	1250.2	1249.3	1248.4	1247.5	1246.6	1244.9	1242.5	1240.0	1237.6	1235.1	1237.6
7.5°	1238.6	1237.7	1236.8	1235.9	1235.0	1233.2	1230.5	1227.8	1225.0	1222.3	1224.3
10°	1228.1	1227.3	1226.3	1225.5	1224.6	1222.7	1219.7	1216.9	1214.0	1211.1	1212.9
12.5°	1214.5	1213.6	1212.7	1211.8	1211.0	1208.9	1205.9	1202.8	1199.8	1196.7	1198.6
15°	1190.1	1189.1	1188.3	1187.3	1186.5	1184.4	1181.0	1177.7	1174.3	1171.0	1172.3
17.5°	1160.6	1159.4	1158.3	1157.3	1156.1	1154.0	1150.8	1147.6	1144.4	1141.3	1142.2
20°	1138.9	1137.7	1136.7	1135.6	1134.4	1132.2	1128.9	1125.5	1122.2	1118.9	1119.6
22.5°	1115.7	1114.2	1112.7	1111.3	1109.7	1107.4	1104.0	1100.7	1097.3	1094.0	1095.2
25°	1077.7	1076.2	1074.6	1073.1	1071.5	1069.1	1066.0	1062.9	1059.8	1056.7	1056.9
27.5°	1034.4	1032.8	1031.2	1029.6	1028.0	1025.8	1022.8	1020.0	1017.1	1014.2	1013.6
30°	1005.6	1003.8	1002.0	1000.2	998.4	996.1	993.2	990.3	987.4	984.5	983.6
32.5°	975.1	973.5	971.9	970.3	968.7	966.3	963.3	960.2	957.2	954.0	953.0
35°	927.4	925.8	924.3	922.7	921.1	918.8	915.7	912.6	909.5	906.3	904.7
37.5°	877.0	875.6	874.2	872.8	871.3	868.9	865.6	862.2	858.9	855.5	853.8
40°	844.1	842.4	840.6	838.8	837.0	834.4	831.1	827.7	824.4	821.0	818.9
42.5°	808.9	807.8	806.7	805.7	804.6	802.2	798.5	794.8	791.1	787.4	784.9
45°	757.0	755.4	753.8	752.2	750.7	748.1	744.6	741.0	737.4	733.9	731.4
47.5°	702.6	701.5	700.5	699.4	698.3	696.2	692.9	689.6	686.3	683.0	680.1
50°	665.7	664.8	663.9	663.0	662.1	660.2	657.0	653.9	650.7	647.6	644.5
52.5°	629.6	628.6	627.5	626.4	625.3	623.1	619.8	616.5	613.2	609.9	607.2
55°	572.5	571.7	571.1	570.4	569.8	567.9	564.8	561.7	558.6	555.4	552.7
57.5°	517.9	517.2	516.4	515.7	514.9	512.9	509.9	506.8	503.8	500.7	498.1
60°	480.2	479.1	478.0	476.9	475.8	473.7	470.9	468.0	465.1	462.2	460.1
62.5°	443.4	442.4	441.5	440.5	439.6	437.6	434.5	431.4	428.4	425.3	423.5
65°	388.0	386.9	385.8	384.7	383.5	381.8	379.7	377.4	375.1	373.0	370.7
67.5°	332.2	331.2	330.2	329.1	328.2	326.6	324.4	322.3	320.2	318.0	315.8
70°	297.7	296.2	294.6	293.0	291.5	289.8	288.0	286.3	284.5	282.8	281.0
72.5°	260.9	259.3	257.8	256.2	254.6	253.2	251.8	250.2	248.8	247.4	246.0
75°	206.5	205.4	204.3	203.2	202.1	201.0	199.8	198.7	197.7	196.5	195.6
77.5°	154.6	154.1	153.6	153.2	152.6	151.9	150.9	150.0	148.9	148.0	147.7
80°	123.3	122.6	122.0	121.3	120.6	120.1	119.6	119.2	118.8	118.3	117.8
82.5°	92.8	92.6	92.2	91.9	91.6	91.4	91.3	91.2	91.1	91.0	90.8
85°	54.1	54.1	54.1	54.1	54.1	53.9	53.4	53.1	52.6	52.1	52.1
87.5°	21.3	21.5	21.7	21.9	22.1	22.1	22.2	22.3	22.4	22.5	22.7
90°	2.2	4.1	5.8	7.6	9.4	10.9	12.3	13.6	14.9	16.2	17.2
92.5°	9.3	9.4	9.5	9.6	9.7	10.4	11.7	13.0	14.3	15.6	16.6
95°	40.5	35.0	29.4	23.8	18.3	15.6	15.7	15.9	16.0	16.2	17.2
97.5°	86.1	89.5	93.0	96.5	100.0	92.6	74.3	56.0	37.7	19.4	19.5
100°	120.8	123.9	126.8	129.7	132.6	122.8	100.2	77.7	55.0	32.4	29.6
102.5°	159.8	161.9	164.1	166.3	168.4	168.1	165.0	162.1	159.2	156.3	126.2
105°	221.8	222.8	223.8	224.8	225.7	226.7	227.4	228.3	229.1	229.9	231.4
107.5°	279.5	279.9	280.4	281.0	281.4	282.2	283.3	284.5	285.6	286.7	287.4
110°	318.4	318.9	319.3	319.8	320.4	321.0	322.1	323.0	324.0	325.0	325.4



TEST NUMBER: P332604-830

CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.1	356.9	357.9	358.7	359.7	360.3	360.8	361.2	361.7	362.1	362.1
115°	414.2	414.6	415.2	415.7	416.1	416.3	416.1	415.9	415.8	415.7	415.9
117.5°	466.5	467.1	467.8	468.4	469.1	469.7	470.0	470.3	470.7	471.1	471.0
120°	501.9	502.6	503.2	503.9	504.4	504.7	504.5	504.4	504.3	504.1	504.4
122.5°	534.9	535.3	535.6	536.0	536.5	536.8	537.0	537.2	537.4	537.7	537.9
125°	582.2	582.9	583.5	584.2	584.8	584.9	584.7	584.4	584.0	583.7	584.2
127.5°	627.0	627.2	627.4	627.5	627.6	628.1	628.9	629.6	630.4	631.1	631.0
130°	655.9	656.1	656.2	656.4	656.6	656.9	657.3	657.9	658.4	658.8	659.0
132.5°	682.4	682.7	683.1	683.3	683.6	684.1	684.7	685.3	685.9	686.5	686.7
135°	722.3	722.1	721.9	721.7	721.6	721.8	722.5	723.1	723.8	724.4	724.7
137.5°	757.4	757.5	757.6	757.6	757.7	758.1	758.8	759.6	760.3	761.0	761.4
140°	780.4	780.8	781.1	781.5	781.7	782.1	782.4	782.8	783.1	783.3	783.9
142.5°	801.1	801.6	802.3	802.9	803.4	803.8	804.0	804.3	804.5	804.6	805.0
145°	832.7	833.3	833.8	834.2	834.7	835.0	835.0	835.0	835.0	835.0	835.2
147.5°	858.0	858.9	859.8	860.7	861.7	862.0	861.9	861.7	861.5	861.4	861.5
150°	876.3	876.9	877.6	878.3	878.8	879.1	878.9	878.8	878.6	878.4	878.4
152.5°	891.6	892.1	892.6	893.2	893.7	893.8	893.5	893.2	892.9	892.6	892.9
155°	913.1	913.2	913.4	913.6	913.8	913.6	913.1	912.6	912.1	911.6	912.3
157.5°	931.2	931.1	931.0	930.9	930.9	930.5	929.9	929.4	928.9	928.3	929.2
160°	941.9	941.3	940.8	940.4	939.9	939.5	939.4	939.2	939.1	938.9	939.9
162.5°	951.3	950.6	950.0	949.4	948.8	948.4	948.2	948.1	947.9	947.7	948.8
165°	963.2	962.4	961.6	960.7	960.0	959.5	959.5	959.5	959.5	959.5	960.8
167.5°	972.6	971.8	970.9	970.1	969.2	968.7	968.7	968.6	968.5	968.4	969.8
170°	978.0	976.9	976.0	975.0	974.0	973.6	973.7	973.9	974.1	974.3	975.5
172.5°	981.5	980.5	979.5	978.5	977.6	977.1	977.3	977.5	977.6	977.8	979.1
175°	985.3	984.3	983.4	982.4	981.4	981.0	981.2	981.3	981.5	981.7	983.1
177.5°	987.1	986.2	985.2	984.3	983.4	983.1	983.4	983.6	983.9	984.1	985.1
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3



TEST NUMBER: P332604-830

CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2
2.5°	1246.7	1248.5	1250.3	1251.1	1250.9	1250.8	1250.6	1250.4
5°	1240.0	1242.5	1244.9	1245.9	1245.5	1245.1	1244.6	1244.2
7.5°	1226.2	1228.2	1230.1	1231.0	1230.8	1230.5	1230.2	1229.9
10°	1214.7	1216.4	1218.2	1218.9	1218.4	1218.0	1217.6	1217.1
12.5°	1200.6	1202.5	1204.5	1205.1	1204.6	1203.9	1203.2	1202.7
15°	1173.7	1175.0	1176.3	1176.7	1176.0	1175.4	1174.7	1174.0
17.5°	1143.0	1143.9	1144.7	1144.9	1144.4	1144.0	1143.6	1143.1
20°	1120.2	1120.9	1121.5	1121.6	1121.2	1120.8	1120.3	1119.8
22.5°	1096.4	1097.6	1098.8	1099.0	1098.2	1097.4	1096.6	1095.8
25°	1057.2	1057.3	1057.6	1057.2	1056.4	1055.5	1054.6	1053.7
27.5°	1013.1	1012.6	1012.0	1011.3	1010.1	1009.0	1007.9	1006.7
30°	982.7	981.8	980.9	980.0	978.8	977.7	976.6	975.5
32.5°	951.9	950.8	949.8	948.7	947.5	946.4	945.3	944.2
35°	903.2	901.6	900.0	898.7	897.6	896.5	895.4	894.3
37.5°	852.2	850.5	848.9	847.3	845.7	844.3	842.8	841.3
40°	816.6	814.5	812.2	810.5	809.4	808.3	807.2	806.1
42.5°	782.2	779.7	777.0	775.4	774.7	773.9	773.2	772.4
45°	729.0	726.5	724.1	722.6	721.8	721.1	720.5	719.8
47.5°	677.4	674.7	671.8	669.7	668.0	666.3	664.6	662.9
50°	641.4	638.3	635.2	632.9	631.6	630.3	629.0	627.6
52.5°	604.5	601.6	598.9	596.7	595.0	593.3	591.6	589.9
55°	550.1	547.4	544.7	542.7	541.4	540.1	538.7	537.3
57.5°	495.6	493.0	490.5	488.6	487.3	486.0	484.7	483.4
60°	458.2	456.2	454.1	452.6	451.5	450.3	449.2	448.2
62.5°	421.6	419.8	418.0	416.5	415.4	414.2	413.2	412.1
65°	368.5	366.3	364.0	362.4	361.3	360.1	359.0	357.9
67.5°	313.8	311.6	309.4	308.2	307.9	307.6	307.3	307.0
70°	279.2	277.4	275.6	274.4	273.7	273.1	272.4	271.7
72.5°	244.6	243.2	241.8	240.7	240.0	239.3	238.7	238.0
75°	194.7	193.8	192.9	192.4	192.2	191.9	191.7	191.5
77.5°	147.4	147.1	146.9	146.5	145.9	145.3	144.8	144.2
80°	117.4	117.0	116.5	116.2	115.9	115.7	115.6	115.3
82.5°	90.5	90.2	89.9	89.7	89.5	89.3	89.1	88.8
85°	52.1	52.1	52.1	52.0	51.8	51.6	51.4	51.1
87.5°	22.9	23.1	23.3	23.4	23.5	23.6	23.6	23.7
90°	18.2	19.1	20.2	20.8	21.1	21.5	21.8	22.1
92.5°	17.6	18.6	19.5	20.1	20.2	20.2	20.3	20.4
95°	18.2	19.1	20.2	20.7	20.9	21.0	21.2	21.4
97.5°	19.7	19.8	19.9	20.0	20.2	20.3	20.5	20.6
100°	26.9	24.0	21.3	20.0	20.2	20.3	20.5	20.6
102.5°	96.1	66.2	36.1	21.1	21.1	21.1	21.2	21.2
105°	232.9	234.3	235.8	233.7	227.7	221.8	215.9	210.0
107.5°	288.1	288.8	289.5	290.2	290.9	291.4	292.1	292.8
110°	325.6	326.0	326.3	326.7	327.3	327.7	328.2	328.7



TEST NUMBER: P332604-830

CATALOG NUMBER: SA4XXDIP-C795D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	362.0	361.9	361.8	362.1	362.8	363.4	364.0	364.7
115°	416.3	416.6	417.0	417.2	417.2	417.2	417.2	417.2
117.5°	470.9	470.9	470.8	470.7	470.7	470.6	470.5	470.5
120°	504.7	505.1	505.4	505.4	505.1	504.7	504.4	504.1
122.5°	538.1	538.3	538.5	538.4	538.1	537.7	537.4	537.1
125°	584.7	585.1	585.6	586.0	586.2	586.3	586.4	586.6
127.5°	630.9	630.8	630.7	630.7	630.5	630.4	630.3	630.1
130°	659.2	659.3	659.5	659.6	659.6	659.6	659.6	659.6
132.5°	686.9	687.0	687.2	687.2	687.1	686.9	686.8	686.7
135°	725.1	725.4	725.8	726.0	726.4	726.7	727.1	727.4
137.5°	761.7	762.0	762.4	762.5	762.4	762.3	762.2	762.1
140°	784.4	784.9	785.3	785.7	785.9	786.0	786.2	786.4
142.5°	805.3	805.7	806.1	806.3	806.3	806.3	806.3	806.3
145°	835.3	835.5	835.7	835.8	836.2	836.5	836.9	837.2
147.5°	861.7	861.8	861.9	862.0	862.2	862.3	862.5	862.7
150°	878.4	878.4	878.4	878.5	878.7	878.8	879.0	879.2
152.5°	893.2	893.4	893.6	893.7	893.6	893.5	893.4	893.3
155°	912.9	913.6	914.3	914.4	913.8	913.3	912.9	912.4
157.5°	930.0	930.9	931.7	931.7	930.9	930.0	929.2	928.3
160°	940.8	941.9	942.8	942.8	941.9	940.8	939.9	938.9
162.5°	949.7	950.6	951.7	951.6	950.5	949.3	948.3	947.2
165°	962.1	963.5	964.8	964.7	963.2	961.8	960.3	958.8
167.5°	971.3	972.7	974.1	974.0	972.4	970.7	969.1	967.5
170°	976.9	978.2	979.5	979.3	977.7	976.1	974.4	972.8
172.5°	980.4	981.8	983.1	982.8	981.1	979.3	977.5	975.7
175°	984.6	986.1	987.5	987.3	985.3	983.4	981.4	979.4
177.5°	986.3	987.3	988.4	988.1	986.5	985.0	983.4	981.8
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3

(END OF REPORT)