

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331688-840

Luminaire Tested: **SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331688-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5183.2 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	91	88	91	87	84	81	74	72	70	62	60	59	50	49	48	43				
2	90	83	78	73	83	77	72	68	66	62	59	55	53	50	45	44	42	37				
3	83	74	67	62	76	69	63	58	59	54	51	50	46	44	41	39	37	33				
4	76	66	59	53	70	62	55	50	53	48	44	45	41	38	37	35	32	29				
5	70	59	52	46	65	55	49	43	48	43	39	41	37	34	34	31	29	26				
6	65	54	46	40	60	50	43	38	43	38	34	37	33	30	31	28	26	23				
7	60	49	41	36	56	46	39	34	40	34	30	34	30	27	29	26	23	21				
8	56	45	37	32	52	42	35	31	36	31	27	31	27	24	27	24	21	19				
9	53	41	34	29	49	38	32	28	34	28	25	29	25	22	25	22	20	17				
10	49	38	31	26	46	35	29	25	31	26	23	27	23	20	23	20	18	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23954	23954	23954	23954
5°	26752	24104	21371	24104
10°	29681	23935	18525	23935
15°	31141	23584	14596	23584
20°	26996	23063	12631	23063
25°	17706	22352	11277	22352
30°	11917	21490	10206	21490
35°	9652	20402	9207	20402
40°	8585	19220	8517	19220
45°	7768	17831	7606	17831
50°	7068	16458	7043	16458
55°	6646	14933	6559	14933
60°	5561	13533	5493	13533
65°	4688	12287	5318	12287
70°	4334	10976	5013	10976
75°	4049	9551	4629	9551
80°	3738	7857	4119	7857
85°	3446	6206	3631	6206



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.6	2.7
10°-20°	391.9	7.6
20°-30°	505.0	9.7
30°-40°	479.9	9.3
40°-50°	411.1	7.9
50°-60°	313.0	6.0
60°-70°	197.9	3.8
70°-80°	98.8	1.9
80°-90°	29.5	0.6
90°-100°	59.3	1.1
100°-110°	184.1	3.6
110°-120°	314.7	6.1
120°-130°	413.8	8.0
130°-140°	464.4	9.0
140°-150°	455.4	8.8
150°-160°	382.0	7.4
160°-170°	253.3	4.9
170°-180°	88.5	1.7
0°-30°	1037.5	20.0
0°-40°	1517.4	29.3
0°-60°	2241.5	43.2
0°-90°	2567.7	49.5
90°-120°	558.0	10.8
90°-150°	1891.7	36.5
90°-180°	2616.0	50.5
0°-180°	5183.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1484	1484	1484	1484	1484	
5°	1651	1487	1319	1487	1651	163
15°	1863	1411	873	1411	1863	503
25°	994	1255	633	1255	994	472
35°	490	1035	467	1035	490	313
45°	340	781	333	781	340	263
55°	236	530	233	530	236	207
65°	123	322	139	322	123	125
75°	65	153	74	153	65	69
85°	19	34	20	34	19	21
90°	27	1	27	1	27	12
95°	49	41	49	41	49	55
105°	175	170	175	170	175	184
115°	316	316	316	316	316	312
125°	461	459	461	459	461	411
135°	602	594	602	594	602	463
145°	729	721	729	721	729	455
155°	831	825	831	825	831	383
165°	898	898	898	898	898	253
175°	931	934	931	934	931	88
180°	935	935	935	935	935	



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1543.8	1545.0	1546.3	1543.4	1543.4	1540.9	1535.5	1531.5	1519.8	1518.2	1518.2
5°	1650.6	1649.5	1651.6	1645.0	1635.7	1633.6	1623.8	1610.9	1597.5	1582.6	1579.4
7.5°	1756.8	1755.2	1751.1	1750.0	1742.8	1727.3	1711.5	1694.8	1672.4	1650.7	1639.8
10°	1810.4	1827.5	1817.1	1799.1	1802.7	1778.5	1765.5	1743.4	1724.8	1692.3	1685.2
12.5°	1863.2	1869.9	1866.6	1856.3	1851.7	1834.9	1817.6	1798.3	1764.0	1734.8	1709.5
15°	1863.0	1872.8	1875.3	1872.3	1874.8	1873.8	1864.5	1848.6	1818.7	1786.7	1758.9
17.5°	1725.5	1732.2	1749.2	1760.6	1775.0	1805.5	1820.6	1826.4	1822.0	1803.8	1784.2
20°	1571.2	1559.8	1607.3	1631.5	1652.1	1703.6	1748.0	1765.0	1792.3	1791.8	1786.7
22.5°	1352.6	1355.3	1400.3	1429.1	1489.2	1540.8	1591.3	1655.4	1708.2	1743.1	1763.6
25°	993.9	1013.5	1058.3	1097.5	1164.5	1260.4	1347.5	1448.6	1543.9	1619.1	1690.8
27.5°	746.4	747.9	783.5	819.6	859.4	938.0	1047.6	1168.3	1304.2	1416.4	1545.5
30°	639.2	636.1	651.1	673.3	707.2	768.1	850.5	969.2	1104.7	1273.7	1424.3
32.5°	563.3	563.5	574.8	591.2	619.5	660.5	716.9	813.2	941.4	1107.6	1284.0
35°	489.7	489.2	497.5	509.3	521.2	547.4	586.1	636.6	724.8	879.9	1060.4
37.5°	437.0	439.2	443.2	450.6	463.7	478.4	501.6	535.5	598.2	690.0	841.7
40°	407.3	408.3	413.9	420.1	427.9	439.2	458.3	485.5	531.5	604.7	715.5
42.5°	380.0	381.0	385.1	390.8	396.9	408.3	424.0	447.7	484.8	542.0	633.4
45°	340.2	340.2	343.9	346.4	353.1	363.5	376.3	395.9	421.7	463.9	524.7
47.5°	302.9	303.0	305.4	309.8	314.1	322.0	334.8	350.7	369.5	402.2	454.1
50°	281.4	282.0	283.5	287.1	289.7	296.9	306.7	320.6	340.2	365.5	408.8
52.5°	264.2	263.8	265.8	267.3	269.1	274.3	281.6	293.9	311.3	333.4	369.2
55°	236.1	234.0	237.1	239.7	241.3	243.3	247.4	255.2	270.1	288.7	315.5
57.5°	201.1	200.3	202.4	204.8	209.6	215.2	218.6	223.6	231.4	244.7	271.2
60°	172.2	172.2	176.8	178.3	184.0	191.3	198.4	202.6	210.4	219.0	238.6
62.5°	146.6	147.0	149.2	150.8	153.9	162.8	172.9	182.0	189.2	197.6	210.7
65°	122.7	123.7	123.7	124.7	126.8	128.9	133.0	140.2	153.1	164.9	174.7
67.5°	104.1	104.4	104.7	105.7	106.3	108.6	110.2	113.4	116.4	127.6	139.8
70°	91.8	93.3	92.8	93.8	94.3	95.3	97.5	99.0	103.6	106.2	113.4
72.5°	80.2	81.3	81.2	81.9	83.2	83.4	85.0	86.6	89.6	91.8	95.6
75°	64.9	64.4	64.9	65.9	66.4	67.1	67.1	69.1	70.6	72.7	75.2
77.5°	50.1	50.6	50.5	50.6	50.7	51.6	51.5	52.5	54.0	55.0	56.2
80°	40.2	40.7	40.2	40.7	41.2	41.7	41.2	41.7	43.3	44.3	44.3
82.5°	31.1	31.2	31.5	31.6	31.7	31.8	32.6	32.7	33.8	33.6	34.0
85°	18.6	18.1	18.1	18.1	18.6	19.1	18.6	18.6	19.1	19.1	19.1
87.5°	11.9	12.3	12.3	12.3	12.2	12.2	12.3	12.8	12.4	12.9	11.7
90°	26.9	26.7	26.5	26.4	26.2	26.3	26.6	27.0	27.3	27.7	23.7
92.5°	25.5	25.5	25.5	25.4	25.4	25.3	25.3	25.2	25.1	25.1	24.2
95°	49.0	49.3	49.7	50.0	50.4	50.5	50.5	50.5	50.5	50.5	50.2
97.5°	84.7	84.8	84.8	84.9	84.9	84.9	84.9	84.9	84.9	84.9	84.2
100°	108.2	108.4	108.5	108.7	108.9	109.0	109.0	109.0	109.0	109.0	108.4
102.5°	134.6	134.8	135.0	135.2	135.3	135.4	135.2	135.1	134.9	134.8	134.1
105°	175.2	175.2	175.2	175.2	175.2	175.1	174.7	174.4	174.0	173.7	173.3
107.5°	213.5	214.3	215.1	215.9	216.7	217.0	216.8	216.7	216.6	216.4	216.4
110°	243.1	243.7	244.2	244.7	245.2	245.5	245.5	245.5	245.5	245.5	245.5



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.6	272.0	272.3	272.7	273.1	273.5	273.9	274.3	274.8	275.2	275.3
115°	315.8	316.3	316.8	317.3	317.8	318.2	318.4	318.5	318.7	318.9	319.2
117.5°	357.9	358.4	358.9	359.5	360.0	360.4	360.9	361.3	361.7	362.1	363.1
120°	387.6	388.1	388.6	389.1	389.7	389.9	389.9	389.9	389.9	389.9	391.3
122.5°	416.7	417.0	417.4	417.8	418.2	418.6	419.0	419.4	419.8	420.2	421.2
125°	461.0	461.2	461.3	461.5	461.7	462.0	462.5	463.1	463.6	464.1	464.6
127.5°	501.4	502.0	502.5	503.1	503.6	504.2	504.8	505.5	506.1	506.8	507.4
130°	530.5	531.2	531.9	532.5	533.2	533.8	534.1	534.5	534.8	535.2	535.5
132.5°	558.3	558.8	559.4	559.9	560.5	561.2	561.9	562.7	563.5	564.2	564.1
135°	601.5	602.0	602.6	603.1	603.6	603.9	604.1	604.3	604.5	604.6	604.3
137.5°	640.7	641.4	642.1	642.8	643.5	643.9	644.0	644.2	644.3	644.4	644.0
140°	667.8	668.5	669.2	669.9	670.6	671.0	671.0	671.0	671.0	671.0	670.0
142.5°	692.5	693.2	693.8	694.5	695.2	695.5	695.4	695.2	695.1	695.0	694.4
145°	729.3	730.0	730.7	731.4	732.2	732.5	732.3	732.1	732.0	731.7	730.6
147.5°	762.3	763.1	763.7	764.4	765.1	765.2	764.8	764.4	764.0	763.7	763.0
150°	783.9	784.4	784.9	785.4	786.0	786.0	785.4	784.9	784.4	783.9	783.2
152.5°	804.1	804.7	805.4	806.1	806.7	806.7	806.1	805.4	804.7	804.1	803.1
155°	831.2	831.7	832.2	832.7	833.3	833.1	832.2	831.3	830.5	829.6	829.1
157.5°	854.5	855.4	856.3	857.1	857.9	857.8	856.6	855.4	854.1	852.9	852.6
160°	869.1	869.8	870.5	871.2	871.9	871.7	870.7	869.6	868.6	867.5	867.4
162.5°	881.7	882.5	883.4	884.2	885.0	884.9	883.7	882.5	881.3	880.1	880.0
165°	898.3	899.2	900.0	900.9	901.8	901.6	900.4	899.2	898.0	896.7	896.7
167.5°	911.9	912.8	913.7	914.6	915.5	915.3	914.1	912.9	911.7	910.4	910.5
170°	918.8	919.9	920.9	922.0	923.0	922.9	921.7	920.5	919.3	918.0	918.2
172.5°	924.5	925.5	926.6	927.7	928.7	928.6	927.4	926.1	924.9	923.7	923.9
175°	930.7	931.7	932.7	933.8	934.8	934.7	933.5	932.3	931.1	929.9	930.2
177.5°	933.5	934.3	935.1	936.0	936.9	936.9	936.0	935.1	934.3	933.5	933.7
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1519.0	1515.7	1512.9	1505.4	1501.8	1493.5	1492.3	1491.9	1481.1	1470.8	1467.9
5°	1571.2	1563.0	1550.5	1536.1	1521.2	1505.7	1495.4	1487.2	1466.5	1446.9	1435.6
7.5°	1623.8	1606.1	1584.7	1557.4	1534.6	1509.0	1490.1	1473.1	1443.8	1415.7	1396.8
10°	1662.9	1634.1	1605.8	1568.1	1538.7	1509.8	1483.1	1459.9	1426.8	1389.8	1363.4
12.5°	1687.3	1655.6	1616.5	1579.6	1541.7	1504.9	1469.1	1439.3	1400.5	1362.1	1330.9
15°	1720.2	1686.2	1638.7	1586.2	1537.2	1489.2	1448.0	1410.9	1360.4	1314.5	1276.4
17.5°	1747.1	1700.3	1649.3	1588.5	1531.9	1470.9	1417.7	1370.4	1314.1	1258.8	1213.9
20°	1755.8	1709.4	1650.6	1589.7	1522.8	1451.1	1393.9	1342.3	1282.0	1221.7	1170.1
22.5°	1750.4	1714.3	1648.9	1576.2	1507.5	1432.5	1367.9	1308.1	1241.2	1179.6	1119.8
25°	1714.0	1701.6	1639.8	1560.3	1482.1	1394.9	1320.2	1254.7	1178.4	1112.5	1047.4
27.5°	1629.1	1655.9	1617.5	1533.0	1445.8	1352.4	1268.4	1193.9	1114.7	1040.5	975.7
30°	1547.5	1608.8	1592.4	1514.0	1416.5	1324.8	1230.5	1152.7	1068.1	991.8	927.9
32.5°	1435.7	1537.1	1553.2	1487.6	1386.8	1286.1	1187.2	1109.7	1021.5	941.1	878.8
35°	1257.8	1409.4	1478.9	1437.1	1336.2	1227.4	1125.3	1035.1	946.4	867.1	805.2
37.5°	1045.5	1251.9	1367.9	1370.9	1278.1	1165.0	1053.9	964.3	873.5	795.6	728.7
40°	907.8	1131.5	1282.5	1316.1	1237.7	1115.5	1003.1	911.9	823.2	746.9	670.1
42.5°	784.1	1006.9	1192.7	1250.9	1188.6	1067.2	954.5	859.1	773.0	700.7	622.3
45°	634.1	828.9	1033.6	1137.7	1103.2	990.8	871.7	780.9	700.0	637.6	562.4
47.5°	534.8	672.2	870.2	1011.1	1010.5	907.9	790.7	703.9	628.8	570.4	509.4
50°	478.4	597.9	765.5	925.3	938.7	852.6	741.2	655.2	585.1	523.7	474.7
52.5°	427.7	526.2	676.8	830.0	868.2	793.7	685.6	606.1	538.1	481.7	439.7
55°	361.3	437.7	552.1	695.4	753.2	700.5	604.7	530.5	475.2	427.9	391.7
57.5°	305.7	362.9	454.7	570.2	637.3	604.3	525.1	464.8	417.7	374.8	346.3
60°	270.6	317.5	395.4	491.8	566.0	542.8	475.2	419.1	378.9	341.7	315.0
62.5°	237.6	277.9	344.7	422.9	491.0	481.4	426.2	379.1	343.9	310.0	287.3
65°	191.3	220.7	272.7	334.1	388.7	393.3	353.7	321.6	290.2	263.4	243.3
67.5°	152.3	171.5	208.1	259.8	300.7	315.4	291.1	266.7	241.8	221.1	203.6
70°	128.4	143.8	170.7	212.4	250.0	265.5	251.6	232.5	210.9	193.8	178.8
72.5°	104.0	119.1	138.9	169.5	201.8	218.4	213.6	200.0	182.4	168.2	154.1
75°	78.4	83.0	96.4	117.0	142.3	156.7	160.4	153.1	139.2	128.4	120.1
77.5°	58.0	60.7	67.2	78.0	94.4	107.3	112.6	111.8	102.2	95.8	88.2
80°	46.4	48.0	51.0	55.6	68.1	80.9	84.5	84.5	77.9	75.2	67.6
82.5°	35.2	36.4	38.3	40.8	46.6	57.9	61.9	62.7	58.5	55.0	49.0
85°	20.1	19.6	20.6	22.1	23.2	26.3	32.5	33.5	32.5	28.4	26.8
87.5°	11.0	10.6	9.9	8.9	8.9	8.8	10.5	12.1	10.9	10.1	9.7
90°	19.9	16.1	12.2	9.2	7.1	5.0	2.9	0.8	2.9	5.0	7.1
92.5°	23.2	22.3	21.4	20.2	18.7	17.2	15.6	14.0	15.6	17.2	18.7
95°	49.8	49.5	49.1	48.1	46.4	44.5	42.8	41.0	42.8	44.5	46.4
97.5°	83.6	82.9	82.3	81.2	79.6	78.1	76.5	75.0	76.5	78.1	79.6
100°	107.9	107.3	106.8	105.8	104.4	103.0	101.7	100.3	101.7	103.0	104.4
102.5°	133.5	132.8	132.2	131.3	130.2	129.1	127.8	126.7	127.8	129.1	130.2
105°	173.0	172.6	172.3	171.8	171.3	170.8	170.3	169.8	170.3	170.8	171.3
107.5°	216.4	216.4	216.4	216.0	215.3	214.5	213.8	213.0	213.8	214.5	215.3
110°	245.5	245.5	245.5	245.0	243.9	242.9	241.8	240.8	241.8	242.9	243.9



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.5	275.6	275.7	275.3	274.2	273.2	272.2	271.0	272.2	273.2	274.2
115°	319.6	319.9	320.3	319.9	318.9	317.8	316.8	315.8	316.8	317.8	318.9
117.5°	364.2	365.1	366.1	365.9	364.5	363.0	361.6	360.2	361.6	363.0	364.5
120°	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9	391.3	392.7	394.2
122.5°	422.2	423.2	424.1	423.8	422.1	420.5	418.8	417.1	418.8	420.5	422.1
125°	465.1	465.7	466.3	465.7	464.1	462.5	461.0	459.4	461.0	462.5	464.1
127.5°	508.1	508.7	509.3	508.6	506.6	504.6	502.6	500.6	502.6	504.6	506.6
130°	535.8	536.2	536.5	535.6	533.3	531.1	528.8	526.5	528.8	531.1	533.3
132.5°	564.1	564.0	563.9	563.0	561.1	559.3	557.4	555.5	557.4	559.3	561.1
135°	603.9	603.6	603.2	602.1	600.2	598.2	596.3	594.4	596.3	598.2	600.2
137.5°	643.5	643.1	642.6	641.6	640.1	638.4	636.8	635.3	636.8	638.4	640.1
140°	669.2	668.3	667.4	666.2	664.6	663.1	661.5	659.9	661.5	663.1	664.6
142.5°	693.8	693.2	692.6	691.5	689.9	688.3	686.7	685.2	686.7	688.3	689.9
145°	729.6	728.6	727.5	726.4	725.2	724.0	722.7	721.4	722.7	724.0	725.2
147.5°	762.2	761.5	760.8	759.7	758.2	756.8	755.3	753.9	755.3	756.8	758.2
150°	782.4	781.7	781.0	780.1	779.1	778.0	777.0	776.0	777.0	778.0	779.1
152.5°	802.3	801.5	800.6	799.7	798.7	797.6	796.6	795.5	796.6	797.6	798.7
155°	828.6	828.0	827.5	827.0	826.5	826.0	825.4	824.9	825.4	826.0	826.5
157.5°	852.3	852.0	851.7	851.4	851.0	850.7	850.3	850.0	850.3	850.7	851.0
160°	867.2	867.0	866.8	866.6	866.2	865.9	865.5	865.2	865.5	865.9	866.2
162.5°	879.8	879.6	879.4	879.3	879.2	879.2	879.1	879.0	879.1	879.2	879.2
165°	896.7	896.7	896.7	896.8	897.0	897.2	897.4	897.5	897.4	897.2	897.0
167.5°	910.5	910.6	910.6	910.9	911.4	911.9	912.4	912.9	912.4	911.9	911.4
170°	918.4	918.6	918.7	919.1	919.6	920.1	920.7	921.2	920.7	920.1	919.6
172.5°	924.0	924.2	924.4	924.7	925.2	925.8	926.3	926.9	926.3	925.8	925.2
175°	930.6	930.9	931.3	931.7	932.2	932.7	933.3	933.8	933.3	932.7	932.2
177.5°	934.0	934.3	934.6	934.9	935.3	935.8	936.2	936.6	936.2	935.8	935.3
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331688-840
 CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1462.6	1459.7	1454.3	1446.0	1441.1	1432.4	1426.6	1430.0	1430.8	1430.0	1429.2
5°	1423.3	1412.4	1397.5	1383.0	1369.7	1355.2	1347.0	1343.3	1336.2	1332.0	1330.0
7.5°	1375.7	1357.1	1336.0	1310.8	1289.4	1267.1	1255.7	1249.9	1235.2	1227.2	1220.1
10°	1340.3	1310.9	1289.8	1256.8	1236.7	1207.3	1187.2	1187.7	1167.6	1156.2	1148.0
12.5°	1301.1	1268.8	1233.7	1204.0	1176.0	1152.5	1128.2	1118.4	1097.0	1086.1	1063.9
15°	1236.2	1198.5	1161.4	1121.2	1092.9	1056.2	1021.2	978.4	943.8	913.9	905.7
17.5°	1165.2	1118.6	1081.4	1034.2	985.6	924.0	883.4	858.6	837.8	822.0	810.2
20°	1116.5	1069.1	1029.5	958.3	892.8	851.1	821.2	802.1	780.4	763.5	754.2
22.5°	1065.4	1015.9	961.8	882.4	831.4	797.9	771.2	749.3	734.7	721.3	713.0
25°	992.8	938.7	849.5	794.9	753.7	718.6	700.0	686.6	671.2	653.1	644.9
27.5°	916.1	830.0	766.0	725.4	686.0	663.2	646.5	626.5	612.7	604.6	596.0
30°	858.8	772.7	722.8	678.4	650.6	625.3	605.7	594.4	581.0	567.0	561.4
32.5°	794.9	726.1	678.2	641.3	613.0	591.5	576.0	557.6	548.0	539.4	527.6
35°	715.5	663.5	619.7	589.8	562.9	545.4	527.4	516.5	499.0	491.8	487.2
37.5°	648.2	603.1	570.5	538.9	517.7	498.3	487.3	470.0	462.4	452.4	442.6
40°	610.4	566.0	534.5	508.8	485.0	470.6	456.8	442.8	431.4	426.9	415.0
42.5°	571.6	535.5	504.0	475.7	459.9	444.6	427.1	416.9	405.1	397.6	390.2
45°	518.1	486.1	459.3	436.1	418.6	402.6	391.2	374.3	367.6	352.5	346.4
47.5°	471.1	441.3	415.8	393.7	376.6	366.2	349.6	336.3	325.6	316.4	308.5
50°	437.7	412.9	388.2	368.6	353.1	338.2	321.1	314.5	297.9	293.3	288.7
52.5°	407.2	383.6	360.9	341.7	326.3	311.7	296.8	288.0	276.9	272.3	268.9
55°	364.5	341.7	320.1	303.1	287.6	272.7	263.4	252.6	247.4	243.8	239.7
57.5°	321.5	301.1	284.6	267.3	251.8	239.9	229.1	222.7	217.3	212.6	207.6
60°	294.4	274.8	259.8	243.8	227.8	218.0	209.8	202.1	195.9	188.6	186.6
62.5°	265.5	248.3	234.7	219.0	205.2	196.2	188.3	181.1	173.6	163.1	160.2
65°	225.8	212.4	197.9	185.1	172.7	163.9	152.6	144.3	141.3	140.2	139.7
67.5°	190.0	177.2	164.8	151.7	140.4	132.3	126.5	125.2	123.1	122.5	121.1
70°	166.0	154.1	141.8	129.4	118.6	117.0	114.9	112.9	110.3	109.3	108.3
72.5°	144.5	132.3	119.9	110.0	105.3	103.4	101.4	99.3	97.6	96.5	95.8
75°	110.8	99.5	91.3	87.7	85.0	83.5	80.4	78.9	77.9	76.2	75.7
77.5°	79.8	73.4	69.6	67.4	64.6	63.0	61.2	59.7	58.6	58.3	57.5
80°	60.8	57.8	55.1	52.1	51.0	49.0	48.5	47.0	47.5	45.8	45.8
82.5°	47.3	43.3	41.1	39.7	38.7	37.1	36.5	35.7	35.9	34.7	34.7
85°	24.2	23.2	22.1	21.1	21.1	19.6	20.1	19.6	19.6	18.6	18.1
87.5°	9.7	9.9	9.8	10.6	11.3	11.7	11.6	11.1	11.1	11.0	10.6
90°	9.2	12.2	16.1	19.9	23.7	27.7	27.3	27.0	26.6	26.3	26.2
92.5°	20.2	21.4	22.3	23.2	24.2	25.1	25.1	25.2	25.3	25.3	25.4
95°	48.1	49.1	49.5	49.8	50.2	50.5	50.5	50.5	50.5	50.5	50.4
97.5°	81.2	82.3	82.9	83.6	84.2	84.9	84.9	84.9	84.9	84.9	84.9
100°	105.8	106.8	107.3	107.9	108.4	109.0	109.0	109.0	109.0	109.0	108.9
102.5°	131.3	132.2	132.8	133.5	134.1	134.8	134.9	135.1	135.2	135.4	135.3
105°	171.8	172.3	172.6	173.0	173.3	173.7	174.0	174.4	174.7	175.1	175.2
107.5°	216.0	216.4	216.4	216.4	216.4	216.4	216.6	216.7	216.8	217.0	216.7
110°	245.0	245.5	245.5	245.5	245.5	245.5	245.5	245.5	245.5	245.5	245.2



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	275.3	275.7	275.6	275.5	275.3	275.2	274.8	274.3	273.9	273.5	273.1
115°	319.9	320.3	319.9	319.6	319.2	318.9	318.7	318.5	318.4	318.2	317.8
117.5°	365.9	366.1	365.1	364.2	363.1	362.1	361.7	361.3	360.9	360.4	360.0
120°	395.6	395.6	394.2	392.7	391.3	389.9	389.9	389.9	389.9	389.9	389.7
122.5°	423.8	424.1	423.2	422.2	421.2	420.2	419.8	419.4	419.0	418.6	418.2
125°	465.7	466.3	465.7	465.1	464.6	464.1	463.6	463.1	462.5	462.0	461.7
127.5°	508.6	509.3	508.7	508.1	507.4	506.8	506.1	505.5	504.8	504.2	503.6
130°	535.6	536.5	536.2	535.8	535.5	535.2	534.8	534.5	534.1	533.8	533.2
132.5°	563.0	563.9	564.0	564.1	564.1	564.2	563.5	562.7	561.9	561.2	560.5
135°	602.1	603.2	603.6	603.9	604.3	604.6	604.5	604.3	604.1	603.9	603.6
137.5°	641.6	642.6	643.1	643.5	644.0	644.4	644.3	644.2	644.0	643.9	643.5
140°	666.2	667.4	668.3	669.2	670.0	671.0	671.0	671.0	671.0	671.0	670.6
142.5°	691.5	692.6	693.2	693.8	694.4	695.0	695.1	695.2	695.4	695.5	695.2
145°	726.4	727.5	728.6	729.6	730.6	731.7	732.0	732.1	732.3	732.5	732.2
147.5°	759.7	760.8	761.5	762.2	763.0	763.7	764.0	764.4	764.8	765.2	765.1
150°	780.1	781.0	781.7	782.4	783.2	783.9	784.4	784.9	785.4	786.0	786.0
152.5°	799.7	800.6	801.5	802.3	803.1	804.1	804.7	805.4	806.1	806.7	806.7
155°	827.0	827.5	828.0	828.6	829.1	829.6	830.5	831.3	832.2	833.1	833.3
157.5°	851.4	851.7	852.0	852.3	852.6	852.9	854.1	855.4	856.6	857.8	857.9
160°	866.6	866.8	867.0	867.2	867.4	867.5	868.6	869.6	870.7	871.7	871.9
162.5°	879.3	879.4	879.6	879.8	880.0	880.1	881.3	882.5	883.7	884.9	885.0
165°	896.8	896.7	896.7	896.7	896.7	896.7	898.0	899.2	900.4	901.6	901.8
167.5°	910.9	910.6	910.6	910.5	910.5	910.4	911.7	912.9	914.1	915.3	915.5
170°	919.1	918.7	918.6	918.4	918.2	918.0	919.3	920.5	921.7	922.9	923.0
172.5°	924.7	924.4	924.2	924.0	923.9	923.7	924.9	926.1	927.4	928.6	928.7
175°	931.7	931.3	930.9	930.6	930.2	929.9	931.1	932.3	933.5	934.7	934.8
177.5°	934.9	934.6	934.3	934.0	933.7	933.5	934.3	935.1	936.0	936.9	936.9
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1424.6	1425.4	1424.2	1425.0	1424.2	1425.4	1424.6	1429.2	1430.0	1430.8	1430.0
5°	1327.4	1321.2	1320.2	1318.6	1320.2	1321.2	1327.4	1330.0	1332.0	1336.2	1343.3
7.5°	1211.3	1210.3	1207.8	1204.2	1207.8	1210.3	1211.3	1220.1	1227.2	1235.2	1249.9
10°	1136.6	1134.1	1133.6	1129.9	1133.6	1134.1	1136.6	1148.0	1156.2	1167.6	1187.7
12.5°	1049.2	1032.6	1030.9	1021.9	1030.9	1032.6	1049.2	1063.9	1086.1	1097.0	1118.4
15°	893.3	890.3	879.9	873.2	879.9	890.3	893.3	905.7	913.9	943.8	978.4
17.5°	804.3	794.2	790.9	789.5	790.9	794.2	804.3	810.2	822.0	837.8	858.6
20°	746.9	737.7	736.1	735.1	736.1	737.7	746.9	754.2	763.5	780.4	802.1
22.5°	707.3	697.6	693.7	690.5	693.7	697.6	707.3	713.0	721.3	734.7	749.3
25°	639.7	636.1	634.1	633.0	634.1	636.1	639.7	644.9	653.1	671.2	686.6
27.5°	586.8	578.9	577.3	574.7	577.3	578.9	586.8	596.0	604.6	612.7	626.5
30°	556.7	554.1	550.6	547.4	550.6	554.1	556.7	561.4	567.0	581.0	594.4
32.5°	521.3	519.1	515.9	514.4	515.9	519.1	521.3	527.6	539.4	548.0	557.6
35°	482.0	474.7	471.7	467.1	471.7	474.7	482.0	487.2	491.8	499.0	516.5
37.5°	440.4	436.7	432.3	433.8	432.3	436.7	440.4	442.6	452.4	462.4	470.0
40°	408.3	405.7	404.7	404.1	404.7	405.7	408.3	415.0	426.9	431.4	442.8
42.5°	382.7	375.6	372.9	372.8	372.9	375.6	382.7	390.2	397.6	405.1	416.9
45°	343.9	337.1	332.4	333.1	332.4	337.1	343.9	346.4	352.5	367.6	374.3
47.5°	304.1	303.9	300.9	301.8	300.9	303.9	304.1	308.5	316.4	325.6	336.3
50°	285.1	282.0	279.9	280.4	279.9	282.0	285.1	288.7	293.3	297.9	314.5
52.5°	266.9	264.3	262.6	264.8	262.6	264.3	266.9	268.9	272.3	276.9	288.0
55°	237.1	234.0	233.5	233.0	233.5	234.0	237.1	239.7	243.8	247.4	252.6
57.5°	203.8	201.8	198.6	197.3	198.6	201.8	203.8	207.6	212.6	217.3	222.7
60°	179.9	175.8	170.7	170.1	170.7	175.8	179.9	186.6	188.6	195.9	202.1
62.5°	158.0	157.2	156.2	156.1	156.2	157.2	158.0	160.2	163.1	173.6	181.1
65°	138.7	138.1	138.7	139.2	138.7	138.1	138.7	139.7	140.2	141.3	144.3
67.5°	120.9	119.9	119.0	119.4	119.0	119.9	120.9	121.1	122.5	123.1	125.2
70°	107.2	106.7	106.2	106.2	106.2	106.7	107.2	108.3	109.3	110.3	112.9
72.5°	94.0	93.9	93.4	93.0	93.4	93.9	94.0	95.8	96.5	97.6	99.3
75°	75.2	74.2	74.2	74.2	74.2	74.2	75.2	75.7	76.2	77.9	78.9
77.5°	57.4	56.9	56.2	55.8	56.2	56.9	57.4	57.5	58.3	58.6	59.7
80°	45.3	44.8	44.3	44.3	44.3	44.8	45.3	45.8	45.8	47.5	47.0
82.5°	34.6	34.1	34.0	33.6	34.0	34.1	34.6	34.7	34.7	35.9	35.7
85°	18.6	19.1	18.6	19.6	18.6	19.1	18.6	18.1	18.6	19.6	19.6
87.5°	10.6	10.2	10.7	10.3	10.7	10.2	10.6	10.6	11.0	11.1	11.1
90°	26.4	26.5	26.7	26.9	26.7	26.5	26.4	26.2	26.3	26.6	27.0
92.5°	25.4	25.5	25.5	25.5	25.5	25.5	25.4	25.4	25.3	25.3	25.2
95°	50.0	49.7	49.3	49.0	49.3	49.7	50.0	50.4	50.5	50.5	50.5
97.5°	84.9	84.8	84.8	84.7	84.8	84.8	84.9	84.9	84.9	84.9	84.9
100°	108.7	108.5	108.4	108.2	108.4	108.5	108.7	108.9	109.0	109.0	109.0
102.5°	135.2	135.0	134.8	134.6	134.8	135.0	135.2	135.3	135.4	135.2	135.1
105°	175.2	175.2	175.2	175.2	175.2	175.2	175.2	175.2	175.1	174.7	174.4
107.5°	215.9	215.1	214.3	213.5	214.3	215.1	215.9	216.7	217.0	216.8	216.7
110°	244.7	244.2	243.7	243.1	243.7	244.2	244.7	245.2	245.5	245.5	245.5



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	272.7	272.3	272.0	271.6	272.0	272.3	272.7	273.1	273.5	273.9	274.3
115°	317.3	316.8	316.3	315.8	316.3	316.8	317.3	317.8	318.2	318.4	318.5
117.5°	359.5	358.9	358.4	357.9	358.4	358.9	359.5	360.0	360.4	360.9	361.3
120°	389.1	388.6	388.1	387.6	388.1	388.6	389.1	389.7	389.9	389.9	389.9
122.5°	417.8	417.4	417.0	416.7	417.0	417.4	417.8	418.2	418.6	419.0	419.4
125°	461.5	461.3	461.2	461.0	461.2	461.3	461.5	461.7	462.0	462.5	463.1
127.5°	503.1	502.5	502.0	501.4	502.0	502.5	503.1	503.6	504.2	504.8	505.5
130°	532.5	531.9	531.2	530.5	531.2	531.9	532.5	533.2	533.8	534.1	534.5
132.5°	559.9	559.4	558.8	558.3	558.8	559.4	559.9	560.5	561.2	561.9	562.7
135°	603.1	602.6	602.0	601.5	602.0	602.6	603.1	603.6	603.9	604.1	604.3
137.5°	642.8	642.1	641.4	640.7	641.4	642.1	642.8	643.5	643.9	644.0	644.2
140°	669.9	669.2	668.5	667.8	668.5	669.2	669.9	670.6	671.0	671.0	671.0
142.5°	694.5	693.8	693.2	692.5	693.2	693.8	694.5	695.2	695.5	695.4	695.2
145°	731.4	730.7	730.0	729.3	730.0	730.7	731.4	732.2	732.5	732.3	732.1
147.5°	764.4	763.7	763.1	762.3	763.1	763.7	764.4	765.1	765.2	764.8	764.4
150°	785.4	784.9	784.4	783.9	784.4	784.9	785.4	786.0	786.0	785.4	784.9
152.5°	806.1	805.4	804.7	804.1	804.7	805.4	806.1	806.7	806.7	806.1	805.4
155°	832.7	832.2	831.7	831.2	831.7	832.2	832.7	833.3	833.1	832.2	831.3
157.5°	857.1	856.3	855.4	854.5	855.4	856.3	857.1	857.9	857.8	856.6	855.4
160°	871.2	870.5	869.8	869.1	869.8	870.5	871.2	871.9	871.7	870.7	869.6
162.5°	884.2	883.4	882.5	881.7	882.5	883.4	884.2	885.0	884.9	883.7	882.5
165°	900.9	900.0	899.2	898.3	899.2	900.0	900.9	901.8	901.6	900.4	899.2
167.5°	914.6	913.7	912.8	911.9	912.8	913.7	914.6	915.5	915.3	914.1	912.9
170°	922.0	920.9	919.9	918.8	919.9	920.9	922.0	923.0	922.9	921.7	920.5
172.5°	927.7	926.6	925.5	924.5	925.5	926.6	927.7	928.7	928.6	927.4	926.1
175°	933.8	932.7	931.7	930.7	931.7	932.7	933.8	934.8	934.7	933.5	932.3
177.5°	936.0	935.1	934.3	933.5	934.3	935.1	936.0	936.9	936.9	936.0	935.1
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1426.6	1432.4	1441.1	1446.0	1454.3	1459.7	1462.6	1467.9	1470.8	1481.1	1491.9
5°	1347.0	1355.2	1369.7	1383.0	1397.5	1412.4	1423.3	1435.6	1446.9	1466.5	1487.2
7.5°	1255.7	1267.1	1289.4	1310.8	1336.0	1357.1	1375.7	1396.8	1415.7	1443.8	1473.1
10°	1187.2	1207.3	1236.7	1256.8	1289.8	1310.9	1340.3	1363.4	1389.8	1426.8	1459.9
12.5°	1128.2	1152.5	1176.0	1204.0	1233.7	1268.8	1301.1	1330.9	1362.1	1400.5	1439.3
15°	1021.2	1056.2	1092.9	1121.2	1161.4	1198.5	1236.2	1276.4	1314.5	1360.4	1410.9
17.5°	883.4	924.0	985.6	1034.2	1081.4	1118.6	1165.2	1213.9	1258.8	1314.1	1370.4
20°	821.2	851.1	892.8	958.3	1029.5	1069.1	1116.5	1170.1	1221.7	1282.0	1342.3
22.5°	771.2	797.9	831.4	882.4	961.8	1015.9	1065.4	1119.8	1179.6	1241.2	1308.1
25°	700.0	718.6	753.7	794.9	849.5	938.7	992.8	1047.4	1112.5	1178.4	1254.7
27.5°	646.5	663.2	686.0	725.4	766.0	830.0	916.1	975.7	1040.5	1114.7	1193.9
30°	605.7	625.3	650.6	678.4	722.8	772.7	858.8	927.9	991.8	1068.1	1152.7
32.5°	576.0	591.5	613.0	641.3	678.2	726.1	794.9	878.8	941.1	1021.5	1109.7
35°	527.4	545.4	562.9	589.8	619.7	663.5	715.5	805.2	867.1	946.4	1035.1
37.5°	487.3	498.3	517.7	538.9	570.5	603.1	648.2	728.7	795.6	873.5	964.3
40°	456.8	470.6	485.0	508.8	534.5	566.0	610.4	670.1	746.9	823.2	911.9
42.5°	427.1	444.6	459.9	475.7	504.0	535.5	571.6	622.3	700.7	773.0	859.1
45°	391.2	402.6	418.6	436.1	459.3	486.1	518.1	562.4	637.6	700.0	780.9
47.5°	349.6	366.2	376.6	393.7	415.8	441.3	471.1	509.4	570.4	628.8	703.9
50°	321.1	338.2	353.1	368.6	388.2	412.9	437.7	474.7	523.7	585.1	655.2
52.5°	296.8	311.7	326.3	341.7	360.9	383.6	407.2	439.7	481.7	538.1	606.1
55°	263.4	272.7	287.6	303.1	320.1	341.7	364.5	391.7	427.9	475.2	530.5
57.5°	229.1	239.9	251.8	267.3	284.6	301.1	321.5	346.3	374.8	417.7	464.8
60°	209.8	218.0	227.8	243.8	259.8	274.8	294.4	315.0	341.7	378.9	419.1
62.5°	188.3	196.2	205.2	219.0	234.7	248.3	265.5	287.3	310.0	343.9	379.1
65°	152.6	163.9	172.7	185.1	197.9	212.4	225.8	243.3	263.4	290.2	321.6
67.5°	126.5	132.3	140.4	151.7	164.8	177.2	190.0	203.6	221.1	241.8	266.7
70°	114.9	117.0	118.6	129.4	141.8	154.1	166.0	178.8	193.8	210.9	232.5
72.5°	101.4	103.4	105.3	110.0	119.9	132.3	144.5	154.1	168.2	182.4	200.0
75°	80.4	83.5	85.0	87.7	91.3	99.5	110.8	120.1	128.4	139.2	153.1
77.5°	61.2	63.0	64.6	67.4	69.6	73.4	79.8	88.2	95.8	102.2	111.8
80°	48.5	49.0	51.0	52.1	55.1	57.8	60.8	67.6	75.2	77.9	84.5
82.5°	36.5	37.1	38.7	39.7	41.1	43.3	47.3	49.0	55.0	58.5	62.7
85°	20.1	19.6	21.1	21.1	22.1	23.2	24.2	26.8	28.4	32.5	33.5
87.5°	11.6	11.7	11.3	10.6	9.8	9.9	9.7	9.7	10.1	10.9	12.1
90°	27.3	27.7	23.7	19.9	16.1	12.2	9.2	7.1	5.0	2.9	0.8
92.5°	25.1	25.1	24.2	23.2	22.3	21.4	20.2	18.7	17.2	15.6	14.0
95°	50.5	50.5	50.2	49.8	49.5	49.1	48.1	46.4	44.5	42.8	41.0
97.5°	84.9	84.9	84.2	83.6	82.9	82.3	81.2	79.6	78.1	76.5	75.0
100°	109.0	109.0	108.4	107.9	107.3	106.8	105.8	104.4	103.0	101.7	100.3
102.5°	134.9	134.8	134.1	133.5	132.8	132.2	131.3	130.2	129.1	127.8	126.7
105°	174.0	173.7	173.3	173.0	172.6	172.3	171.8	171.3	170.8	170.3	169.8
107.5°	216.6	216.4	216.4	216.4	216.4	216.4	216.0	215.3	214.5	213.8	213.0
110°	245.5	245.5	245.5	245.5	245.5	245.5	245.0	243.9	242.9	241.8	240.8



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	274.8	275.2	275.3	275.5	275.6	275.7	275.3	274.2	273.2	272.2	271.0
115°	318.7	318.9	319.2	319.6	319.9	320.3	319.9	318.9	317.8	316.8	315.8
117.5°	361.7	362.1	363.1	364.2	365.1	366.1	365.9	364.5	363.0	361.6	360.2
120°	389.9	389.9	391.3	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9
122.5°	419.8	420.2	421.2	422.2	423.2	424.1	423.8	422.1	420.5	418.8	417.1
125°	463.6	464.1	464.6	465.1	465.7	466.3	465.7	464.1	462.5	461.0	459.4
127.5°	506.1	506.8	507.4	508.1	508.7	509.3	508.6	506.6	504.6	502.6	500.6
130°	534.8	535.2	535.5	535.8	536.2	536.5	535.6	533.3	531.1	528.8	526.5
132.5°	563.5	564.2	564.1	564.1	564.0	563.9	563.0	561.1	559.3	557.4	555.5
135°	604.5	604.6	604.3	603.9	603.6	603.2	602.1	600.2	598.2	596.3	594.4
137.5°	644.3	644.4	644.0	643.5	643.1	642.6	641.6	640.1	638.4	636.8	635.3
140°	671.0	671.0	670.0	669.2	668.3	667.4	666.2	664.6	663.1	661.5	659.9
142.5°	695.1	695.0	694.4	693.8	693.2	692.6	691.5	689.9	688.3	686.7	685.2
145°	732.0	731.7	730.6	729.6	728.6	727.5	726.4	725.2	724.0	722.7	721.4
147.5°	764.0	763.7	763.0	762.2	761.5	760.8	759.7	758.2	756.8	755.3	753.9
150°	784.4	783.9	783.2	782.4	781.7	781.0	780.1	779.1	778.0	777.0	776.0
152.5°	804.7	804.1	803.1	802.3	801.5	800.6	799.7	798.7	797.6	796.6	795.5
155°	830.5	829.6	829.1	828.6	828.0	827.5	827.0	826.5	826.0	825.4	824.9
157.5°	854.1	852.9	852.6	852.3	852.0	851.7	851.4	851.0	850.7	850.3	850.0
160°	868.6	867.5	867.4	867.2	867.0	866.8	866.6	866.2	865.9	865.5	865.2
162.5°	881.3	880.1	880.0	879.8	879.6	879.4	879.3	879.2	879.2	879.1	879.0
165°	898.0	896.7	896.7	896.7	896.7	896.7	896.8	897.0	897.2	897.4	897.5
167.5°	911.7	910.4	910.5	910.5	910.6	910.6	910.9	911.4	911.9	912.4	912.9
170°	919.3	918.0	918.2	918.4	918.6	918.7	919.1	919.6	920.1	920.7	921.2
172.5°	924.9	923.7	923.9	924.0	924.2	924.4	924.7	925.2	925.8	926.3	926.9
175°	931.1	929.9	930.2	930.6	930.9	931.3	931.7	932.2	932.7	933.3	933.8
177.5°	934.3	933.5	933.7	934.0	934.3	934.6	934.9	935.3	935.8	936.2	936.6
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331688-840
 CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1492.3	1493.5	1501.8	1505.4	1512.9	1515.7	1519.0	1518.2	1518.2	1519.8	1531.5
5°	1495.4	1505.7	1521.2	1536.1	1550.5	1563.0	1571.2	1579.4	1582.6	1597.5	1610.9
7.5°	1490.1	1509.0	1534.6	1557.4	1584.7	1606.1	1623.8	1639.8	1650.7	1672.4	1694.8
10°	1483.1	1509.8	1538.7	1568.1	1605.8	1634.1	1662.9	1685.2	1692.3	1724.8	1743.4
12.5°	1469.1	1504.9	1541.7	1579.6	1616.5	1655.6	1687.3	1709.5	1734.8	1764.0	1798.3
15°	1448.0	1489.2	1537.2	1586.2	1638.7	1686.2	1720.2	1758.9	1786.7	1818.7	1848.6
17.5°	1417.7	1470.9	1531.9	1588.5	1649.3	1700.3	1747.1	1784.2	1803.8	1822.0	1826.4
20°	1393.9	1451.1	1522.8	1589.7	1650.6	1709.4	1755.8	1786.7	1791.8	1792.3	1765.0
22.5°	1367.9	1432.5	1507.5	1576.2	1648.9	1714.3	1750.4	1763.6	1743.1	1708.2	1655.4
25°	1320.2	1394.9	1482.1	1560.3	1639.8	1701.6	1714.0	1690.8	1619.1	1543.9	1448.6
27.5°	1268.4	1352.4	1445.8	1533.0	1617.5	1655.9	1629.1	1545.5	1416.4	1304.2	1168.3
30°	1230.5	1324.8	1416.5	1514.0	1592.4	1608.8	1547.5	1424.3	1273.7	1104.7	969.2
32.5°	1187.2	1286.1	1386.8	1487.6	1553.2	1537.1	1435.7	1284.0	1107.6	941.4	813.2
35°	1125.3	1227.4	1336.2	1437.1	1478.9	1409.4	1257.8	1060.4	879.9	724.8	636.6
37.5°	1053.9	1165.0	1278.1	1370.9	1367.9	1251.9	1045.5	841.7	690.0	598.2	535.5
40°	1003.1	1115.5	1237.7	1316.1	1282.5	1131.5	907.8	715.5	604.7	531.5	485.5
42.5°	954.5	1067.2	1188.6	1250.9	1192.7	1006.9	784.1	633.4	542.0	484.8	447.7
45°	871.7	990.8	1103.2	1137.7	1033.6	828.9	634.1	524.7	463.9	421.7	395.9
47.5°	790.7	907.9	1010.5	1011.1	870.2	672.2	534.8	454.1	402.2	369.5	350.7
50°	741.2	852.6	938.7	925.3	765.5	597.9	478.4	408.8	365.5	340.2	320.6
52.5°	685.6	793.7	868.2	830.0	676.8	526.2	427.7	369.2	333.4	311.3	293.9
55°	604.7	700.5	753.2	695.4	552.1	437.7	361.3	315.5	288.7	270.1	255.2
57.5°	525.1	604.3	637.3	570.2	454.7	362.9	305.7	271.2	244.7	231.4	223.6
60°	475.2	542.8	566.0	491.8	395.4	317.5	270.6	238.6	219.0	210.4	202.6
62.5°	426.2	481.4	491.0	422.9	344.7	277.9	237.6	210.7	197.6	189.2	182.0
65°	353.7	393.3	388.7	334.1	272.7	220.7	191.3	174.7	164.9	153.1	140.2
67.5°	291.1	315.4	300.7	259.8	208.1	171.5	152.3	139.8	127.6	116.4	113.4
70°	251.6	265.5	250.0	212.4	170.7	143.8	128.4	113.4	106.2	103.6	99.0
72.5°	213.6	218.4	201.8	169.5	138.9	119.1	104.0	95.6	91.8	89.6	86.6
75°	160.4	156.7	142.3	117.0	96.4	83.0	78.4	75.2	72.7	70.6	69.1
77.5°	112.6	107.3	94.4	78.0	67.2	60.7	58.0	56.2	55.0	54.0	52.5
80°	84.5	80.9	68.1	55.6	51.0	48.0	46.4	44.3	44.3	43.3	41.7
82.5°	61.9	57.9	46.6	40.8	38.3	36.4	35.2	34.0	33.6	33.8	32.7
85°	32.5	26.3	23.2	22.1	20.6	19.6	20.1	19.1	19.1	19.1	18.6
87.5°	10.5	8.8	8.9	8.9	9.9	10.6	11.0	11.7	12.9	12.4	12.8
90°	2.9	5.0	7.1	9.2	12.2	16.1	19.9	23.7	27.7	27.3	27.0
92.5°	15.6	17.2	18.7	20.2	21.4	22.3	23.2	24.2	25.1	25.1	25.2
95°	42.8	44.5	46.4	48.1	49.1	49.5	49.8	50.2	50.5	50.5	50.5
97.5°	76.5	78.1	79.6	81.2	82.3	82.9	83.6	84.2	84.9	84.9	84.9
100°	101.7	103.0	104.4	105.8	106.8	107.3	107.9	108.4	109.0	109.0	109.0
102.5°	127.8	129.1	130.2	131.3	132.2	132.8	133.5	134.1	134.8	134.9	135.1
105°	170.3	170.8	171.3	171.8	172.3	172.6	173.0	173.3	173.7	174.0	174.4
107.5°	213.8	214.5	215.3	216.0	216.4	216.4	216.4	216.4	216.4	216.6	216.7
110°	241.8	242.9	243.9	245.0	245.5	245.5	245.5	245.5	245.5	245.5	245.5



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.2	273.2	274.2	275.3	275.7	275.6	275.5	275.3	275.2	274.8	274.3
115°	316.8	317.8	318.9	319.9	320.3	319.9	319.6	319.2	318.9	318.7	318.5
117.5°	361.6	363.0	364.5	365.9	366.1	365.1	364.2	363.1	362.1	361.7	361.3
120°	391.3	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9	389.9	389.9
122.5°	418.8	420.5	422.1	423.8	424.1	423.2	422.2	421.2	420.2	419.8	419.4
125°	461.0	462.5	464.1	465.7	466.3	465.7	465.1	464.6	464.1	463.6	463.1
127.5°	502.6	504.6	506.6	508.6	509.3	508.7	508.1	507.4	506.8	506.1	505.5
130°	528.8	531.1	533.3	535.6	536.5	536.2	535.8	535.5	535.2	534.8	534.5
132.5°	557.4	559.3	561.1	563.0	563.9	564.0	564.1	564.1	564.2	563.5	562.7
135°	596.3	598.2	600.2	602.1	603.2	603.6	603.9	604.3	604.6	604.5	604.3
137.5°	636.8	638.4	640.1	641.6	642.6	643.1	643.5	644.0	644.4	644.3	644.2
140°	661.5	663.1	664.6	666.2	667.4	668.3	669.2	670.0	671.0	671.0	671.0
142.5°	686.7	688.3	689.9	691.5	692.6	693.2	693.8	694.4	695.0	695.1	695.2
145°	722.7	724.0	725.2	726.4	727.5	728.6	729.6	730.6	731.7	732.0	732.1
147.5°	755.3	756.8	758.2	759.7	760.8	761.5	762.2	763.0	763.7	764.0	764.4
150°	777.0	778.0	779.1	780.1	781.0	781.7	782.4	783.2	783.9	784.4	784.9
152.5°	796.6	797.6	798.7	799.7	800.6	801.5	802.3	803.1	804.1	804.7	805.4
155°	825.4	826.0	826.5	827.0	827.5	828.0	828.6	829.1	829.6	830.5	831.3
157.5°	850.3	850.7	851.0	851.4	851.7	852.0	852.3	852.6	852.9	854.1	855.4
160°	865.5	865.9	866.2	866.6	866.8	867.0	867.2	867.4	867.5	868.6	869.6
162.5°	879.1	879.2	879.2	879.3	879.4	879.6	879.8	880.0	880.1	881.3	882.5
165°	897.4	897.2	897.0	896.8	896.7	896.7	896.7	896.7	896.7	898.0	899.2
167.5°	912.4	911.9	911.4	910.9	910.6	910.6	910.5	910.5	910.4	911.7	912.9
170°	920.7	920.1	919.6	919.1	918.7	918.6	918.4	918.2	918.0	919.3	920.5
172.5°	926.3	925.8	925.2	924.7	924.4	924.2	924.0	923.9	923.7	924.9	926.1
175°	933.3	932.7	932.2	931.7	931.3	930.9	930.6	930.2	929.9	931.1	932.3
177.5°	936.2	935.8	935.3	934.9	934.6	934.3	934.0	933.7	933.5	934.3	935.1
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1535.5	1540.9	1543.4	1543.4	1546.3	1545.0	1543.8
5°	1623.8	1633.6	1635.7	1645.0	1651.6	1649.5	1650.6
7.5°	1711.5	1727.3	1742.8	1750.0	1751.1	1755.2	1756.8
10°	1765.5	1778.5	1802.7	1799.1	1817.1	1827.5	1810.4
12.5°	1817.6	1834.9	1851.7	1856.3	1866.6	1869.9	1863.2
15°	1864.5	1873.8	1874.8	1872.3	1875.3	1872.8	1863.0
17.5°	1820.6	1805.5	1775.0	1760.6	1749.2	1732.2	1725.5
20°	1748.0	1703.6	1652.1	1631.5	1607.3	1559.8	1571.2
22.5°	1591.3	1540.8	1489.2	1429.1	1400.3	1355.3	1352.6
25°	1347.5	1260.4	1164.5	1097.5	1058.3	1013.5	993.9
27.5°	1047.6	938.0	859.4	819.6	783.5	747.9	746.4
30°	850.5	768.1	707.2	673.3	651.1	636.1	639.2
32.5°	716.9	660.5	619.5	591.2	574.8	563.5	563.3
35°	586.1	547.4	521.2	509.3	497.5	489.2	489.7
37.5°	501.6	478.4	463.7	450.6	443.2	439.2	437.0
40°	458.3	439.2	427.9	420.1	413.9	408.3	407.3
42.5°	424.0	408.3	396.9	390.8	385.1	381.0	380.0
45°	376.3	363.5	353.1	346.4	343.9	340.2	340.2
47.5°	334.8	322.0	314.1	309.8	305.4	303.0	302.9
50°	306.7	296.9	289.7	287.1	283.5	282.0	281.4
52.5°	281.6	274.3	269.1	267.3	265.8	263.8	264.2
55°	247.4	243.3	241.3	239.7	237.1	234.0	236.1
57.5°	218.6	215.2	209.6	204.8	202.4	200.3	201.1
60°	198.4	191.3	184.0	178.3	176.8	172.2	172.2
62.5°	172.9	162.8	153.9	150.8	149.2	147.0	146.6
65°	133.0	128.9	126.8	124.7	123.7	123.7	122.7
67.5°	110.2	108.6	106.3	105.7	104.7	104.4	104.1
70°	97.5	95.3	94.3	93.8	92.8	93.3	91.8
72.5°	85.0	83.4	83.2	81.9	81.2	81.3	80.2
75°	67.1	67.1	66.4	65.9	64.9	64.4	64.9
77.5°	51.5	51.6	50.7	50.6	50.5	50.6	50.1
80°	41.2	41.7	41.2	40.7	40.2	40.7	40.2
82.5°	32.6	31.8	31.7	31.6	31.5	31.2	31.1
85°	18.6	19.1	18.6	18.1	18.1	18.1	18.6
87.5°	12.3	12.2	12.2	12.3	12.3	12.3	11.9
90°	26.6	26.3	26.2	26.4	26.5	26.7	26.9
92.5°	25.3	25.3	25.4	25.4	25.5	25.5	25.5
95°	50.5	50.5	50.4	50.0	49.7	49.3	49.0
97.5°	84.9	84.9	84.9	84.9	84.8	84.8	84.7
100°	109.0	109.0	108.9	108.7	108.5	108.4	108.2
102.5°	135.2	135.4	135.3	135.2	135.0	134.8	134.6
105°	174.7	175.1	175.2	175.2	175.2	175.2	175.2
107.5°	216.8	217.0	216.7	215.9	215.1	214.3	213.5
110°	245.5	245.5	245.2	244.7	244.2	243.7	243.1



TEST NUMBER: P331688-840

CATALOG NUMBER: SA2XXRDIP-C675D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	273.9	273.5	273.1	272.7	272.3	272.0	271.6
115°	318.4	318.2	317.8	317.3	316.8	316.3	315.8
117.5°	360.9	360.4	360.0	359.5	358.9	358.4	357.9
120°	389.9	389.9	389.7	389.1	388.6	388.1	387.6
122.5°	419.0	418.6	418.2	417.8	417.4	417.0	416.7
125°	462.5	462.0	461.7	461.5	461.3	461.2	461.0
127.5°	504.8	504.2	503.6	503.1	502.5	502.0	501.4
130°	534.1	533.8	533.2	532.5	531.9	531.2	530.5
132.5°	561.9	561.2	560.5	559.9	559.4	558.8	558.3
135°	604.1	603.9	603.6	603.1	602.6	602.0	601.5
137.5°	644.0	643.9	643.5	642.8	642.1	641.4	640.7
140°	671.0	671.0	670.6	669.9	669.2	668.5	667.8
142.5°	695.4	695.5	695.2	694.5	693.8	693.2	692.5
145°	732.3	732.5	732.2	731.4	730.7	730.0	729.3
147.5°	764.8	765.2	765.1	764.4	763.7	763.1	762.3
150°	785.4	786.0	786.0	785.4	784.9	784.4	783.9
152.5°	806.1	806.7	806.7	806.1	805.4	804.7	804.1
155°	832.2	833.1	833.3	832.7	832.2	831.7	831.2
157.5°	856.6	857.8	857.9	857.1	856.3	855.4	854.5
160°	870.7	871.7	871.9	871.2	870.5	869.8	869.1
162.5°	883.7	884.9	885.0	884.2	883.4	882.5	881.7
165°	900.4	901.6	901.8	900.9	900.0	899.2	898.3
167.5°	914.1	915.3	915.5	914.6	913.7	912.8	911.9
170°	921.7	922.9	923.0	922.0	920.9	919.9	918.8
172.5°	927.4	928.6	928.7	927.7	926.6	925.5	924.5
175°	933.5	934.7	934.8	933.8	932.7	931.7	930.7
177.5°	936.0	936.9	936.9	936.0	935.1	934.3	933.5
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3

(END OF REPORT)