

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332976-830

Luminaire Tested: **SA4XXRDIP-C1020D1035U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332976-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D1035U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7827.2 lumens
Efficiency: N/A
Efficacy: 129.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332976-830

CATALOG NUMBER: SA4XXRDIP-C1020D1035U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332976-830

CATALOG NUMBER: SA4XXRDIP-C1020D1035U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43				
2	90	82	76	71	82	76	71	67	65	61	58	54	52	49	45	43	41	36				
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31				
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	30	27				
5	69	57	49	44	63	53	46	41	46	40	36	39	35	31	32	29	27	23				
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21				
7	59	47	39	33	54	44	36	31	38	32	28	32	28	24	27	24	21	18				
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17				
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15				
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13739	13739	13739
5°	13771	13602	13686
10°	13684	13439	13439
15°	13527	13157	13059
20°	13311	12785	12550
25°	13036	12351	12038
30°	12767	11893	11395
35°	12471	11417	10749
40°	12113	10877	10053
45°	11783	10340	9344
50°	11408	9722	8593
55°	11005	9080	7776
60°	10563	8375	6944
65°	10157	7494	6124
70°	9567	6522	5200
75°	8821	5405	4226
80°	7694	4119	3877
85°	6521	3742	3501



TEST NUMBER: P332976-830

CATALOG NUMBER: SA4XXRDIP-C1020D1035U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.9	2.0
10°-20°	445.8	5.7
20°-30°	643.8	8.2
30°-40°	729.7	9.3
40°-50°	704.7	9.0
50°-60°	586.0	7.5
60°-70°	404.6	5.2
70°-80°	205.1	2.6
80°-90°	56.3	0.7
90°-100°	43.0	0.5
100°-110°	274.3	3.5
110°-120°	524.8	6.7
120°-130°	666.2	8.5
130°-140°	712.8	9.1
140°-150°	666.5	8.5
150°-160°	537.5	6.9
160°-170°	346.7	4.4
170°-180°	119.5	1.5
0°-30°	1249.5	16.0
0°-40°	1979.2	25.3
0°-60°	3269.8	41.8
0°-90°	3935.8	50.3
90°-120°	842.2	10.8
90°-150°	2887.7	36.9
90°-180°	3891.0	49.7
0°-180°	7827.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1702	1702	1702	1702	1702	
5°	1699	1694	1678	1691	1689	161
15°	1618	1606	1574	1571	1562	456
25°	1464	1438	1387	1365	1351	674
35°	1265	1222	1158	1115	1091	790
45°	1032	982	906	844	818	795
55°	782	728	645	580	552	699
65°	532	474	392	338	321	525
75°	283	234	173	145	136	299
85°	70	46	40	38	38	79
90°	3	13	21	26	28	6
95°	52	22	21	26	27	67
105°	283	289	294	300	268	296
115°	529	531	531	532	532	520
125°	743	747	745	748	749	663
135°	922	921	925	927	929	710
145°	1063	1066	1066	1067	1069	664
155°	1166	1166	1164	1167	1165	537
165°	1230	1225	1225	1232	1224	347
175°	1258	1253	1253	1261	1250	120
180°	1258	1258	1258	1258	1258	



TEST NUMBER: P332976-830

CATALOG NUMBER: SA4XXRDIP-C1020D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1706.1	1705.2	1704.2	1703.4	1702.4	1700.6	1698.1	1695.5	1693.0	1690.5	1693.0
5°	1699.3	1698.2	1697.0	1695.8	1694.7	1692.3	1688.9	1685.5	1682.0	1678.5	1681.4
7.5°	1683.9	1682.7	1681.5	1680.3	1679.0	1676.2	1671.7	1667.2	1662.6	1658.1	1660.0
10°	1669.3	1667.9	1666.4	1665.0	1663.6	1660.2	1655.0	1649.8	1644.5	1639.4	1640.5
12.5°	1650.6	1648.9	1647.2	1645.6	1643.9	1639.9	1633.8	1627.7	1621.6	1615.4	1616.1
15°	1618.5	1615.9	1613.4	1610.7	1608.1	1603.2	1595.9	1588.7	1581.5	1574.2	1573.7
17.5°	1579.7	1575.9	1572.2	1568.4	1564.6	1558.4	1549.7	1541.1	1532.4	1523.6	1522.0
20°	1549.4	1545.7	1541.9	1538.1	1534.4	1527.6	1517.8	1507.9	1498.1	1488.2	1485.9
22.5°	1516.1	1511.8	1507.6	1503.4	1499.2	1491.8	1481.3	1470.7	1460.2	1449.6	1446.1
25°	1463.5	1458.2	1453.0	1447.8	1442.6	1434.1	1422.2	1410.3	1398.5	1386.6	1381.7
27.5°	1408.2	1401.7	1395.2	1388.6	1382.1	1372.4	1359.7	1347.1	1334.4	1321.6	1315.6
30°	1369.6	1362.4	1355.2	1347.9	1340.7	1330.2	1316.6	1303.0	1289.4	1275.8	1268.6
32.5°	1329.0	1320.8	1312.6	1304.5	1296.3	1285.2	1271.1	1257.1	1242.9	1228.9	1220.5
35°	1265.4	1256.1	1246.8	1237.6	1228.3	1216.4	1201.9	1187.5	1173.0	1158.5	1148.7
37.5°	1197.3	1187.8	1178.3	1168.7	1159.1	1146.3	1130.3	1114.3	1098.2	1082.1	1071.1
40°	1149.4	1139.8	1130.3	1120.7	1111.2	1098.2	1081.7	1065.1	1048.6	1032.1	1019.9
42.5°	1103.5	1093.5	1083.5	1073.5	1063.5	1049.8	1032.6	1015.4	998.2	981.0	968.7
45°	1032.1	1021.4	1010.7	999.9	989.2	975.2	957.8	940.5	923.0	905.7	891.6
47.5°	958.4	947.3	936.2	925.2	914.1	899.6	881.5	863.4	845.3	827.3	812.6
50°	908.3	897.0	885.7	874.4	863.1	848.2	829.7	811.2	792.6	774.1	759.6
52.5°	857.2	846.1	835.1	824.1	812.9	798.0	778.9	760.0	740.9	722.0	707.3
55°	781.9	770.3	758.7	747.2	735.6	720.4	701.5	682.7	663.9	645.1	630.0
57.5°	707.4	695.3	683.2	671.2	659.2	643.9	625.4	606.8	588.2	569.8	554.5
60°	654.2	642.6	631.0	619.4	607.8	592.8	574.3	555.7	537.2	518.7	503.6
62.5°	606.2	594.2	582.1	570.0	558.1	542.5	523.5	504.5	485.5	466.6	452.6
65°	531.7	519.2	506.8	494.4	481.9	466.4	447.9	429.3	410.8	392.3	379.8
67.5°	454.3	442.3	430.5	418.5	406.5	392.0	374.8	357.6	340.4	323.2	312.5
70°	405.3	393.1	381.0	368.8	356.7	342.3	325.8	309.2	292.8	276.3	266.7
72.5°	353.2	342.1	331.1	320.2	309.2	295.9	280.3	264.7	249.1	233.6	225.4
75°	282.8	272.1	261.4	250.6	240.0	227.7	214.1	200.6	186.9	173.3	166.6
77.5°	211.4	202.3	193.2	184.1	175.0	164.9	153.9	143.0	132.0	120.9	117.1
80°	165.5	157.1	148.7	140.3	132.0	123.4	114.7	106.0	97.3	88.6	87.8
82.5°	125.9	118.2	110.5	102.7	95.1	88.7	83.8	78.8	73.8	68.8	68.1
85°	70.4	64.6	58.8	53.0	47.2	43.8	43.0	42.1	41.3	40.4	39.8
87.5°	24.5	23.2	21.8	20.4	18.9	18.3	18.5	18.6	18.7	18.8	18.8
90°	2.8	5.1	7.4	9.7	12.1	14.0	15.6	17.3	19.0	20.7	22.0
92.5°	11.9	12.0	12.1	12.3	12.3	13.3	14.9	16.6	18.3	20.0	21.2
95°	51.7	44.7	37.5	30.4	23.3	19.9	20.1	20.3	20.5	20.7	22.0
97.5°	109.9	114.3	118.8	123.2	127.6	118.2	94.8	71.5	48.2	24.9	25.0
100°	154.3	158.1	161.8	165.6	169.4	156.8	128.0	99.2	70.2	41.4	37.9
102.5°	204.0	206.8	209.5	212.3	215.0	214.5	210.8	207.0	203.2	199.4	161.1
105°	283.2	284.5	285.7	287.0	288.2	289.4	290.4	291.4	292.6	293.6	295.5
107.5°	356.8	357.4	358.1	358.6	359.3	360.3	361.7	363.2	364.6	366.0	366.9
110°	406.5	407.1	407.7	408.3	409.0	409.9	411.1	412.5	413.7	414.9	415.4



TEST NUMBER: P332976-830

CATALOG NUMBER: SA4XXRDIP-C1020D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	454.7	455.8	456.9	458.1	459.2	460.1	460.6	461.2	461.8	462.3	462.3
115°	528.8	529.4	530.1	530.7	531.3	531.5	531.3	531.1	530.8	530.7	531.1
117.5°	595.6	596.4	597.3	598.1	599.0	599.6	600.0	600.5	601.0	601.4	601.3
120°	640.7	641.6	642.4	643.3	644.1	644.4	644.2	644.0	643.8	643.6	644.0
122.5°	682.9	683.4	683.9	684.4	684.9	685.3	685.6	685.9	686.2	686.5	686.7
125°	743.3	744.1	745.0	745.8	746.7	746.9	746.5	746.0	745.6	745.2	745.8
127.5°	800.5	800.7	801.0	801.2	801.3	801.9	803.0	803.9	804.8	805.8	805.7
130°	837.4	837.6	837.8	838.0	838.2	838.7	839.3	839.9	840.6	841.2	841.4
132.5°	871.3	871.7	872.0	872.4	872.8	873.4	874.2	875.0	875.7	876.6	876.8
135°	922.1	921.9	921.7	921.4	921.2	921.5	922.4	923.2	924.1	924.9	925.3
137.5°	967.0	967.1	967.2	967.3	967.4	967.9	968.8	969.8	970.6	971.6	972.0
140°	996.5	996.8	997.3	997.7	998.1	998.5	998.9	999.4	999.8	1000.2	1000.8
142.5°	1022.8	1023.5	1024.3	1025.0	1025.8	1026.2	1026.5	1026.8	1027.0	1027.3	1027.7
145°	1063.2	1063.8	1064.5	1065.1	1065.7	1066.0	1066.0	1066.0	1066.0	1066.0	1066.3
147.5°	1095.4	1096.6	1097.8	1098.9	1100.1	1100.6	1100.3	1100.1	1099.9	1099.8	1099.9
150°	1118.7	1119.6	1120.4	1121.2	1122.1	1122.4	1122.2	1122.0	1121.8	1121.5	1121.5
152.5°	1138.3	1139.0	1139.6	1140.3	1140.9	1141.1	1140.8	1140.4	1140.0	1139.6	1140.0
155°	1165.8	1166.0	1166.2	1166.4	1166.6	1166.4	1165.8	1165.2	1164.5	1163.9	1164.7
157.5°	1188.9	1188.8	1188.6	1188.5	1188.5	1188.0	1187.3	1186.6	1185.9	1185.2	1186.3
160°	1202.5	1201.8	1201.3	1200.6	1200.0	1199.6	1199.4	1199.1	1198.9	1198.7	1200.0
162.5°	1214.6	1213.7	1213.0	1212.1	1211.4	1210.9	1210.6	1210.4	1210.2	1210.0	1211.3
165°	1229.7	1228.7	1227.7	1226.6	1225.6	1225.0	1225.0	1225.0	1225.0	1225.0	1226.7
167.5°	1241.8	1240.8	1239.6	1238.6	1237.5	1236.9	1236.7	1236.6	1236.5	1236.3	1238.2
170°	1248.6	1247.4	1246.0	1244.8	1243.6	1243.0	1243.2	1243.5	1243.7	1243.9	1245.6
172.5°	1253.1	1251.9	1250.6	1249.3	1248.1	1247.5	1247.7	1248.0	1248.2	1248.4	1250.1
175°	1258.0	1256.8	1255.5	1254.2	1253.0	1252.5	1252.6	1252.9	1253.1	1253.3	1255.2
177.5°	1260.3	1259.0	1257.9	1256.8	1255.6	1255.2	1255.5	1255.8	1256.1	1256.5	1257.8
180°	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0



TEST NUMBER: P332976-830

CATALOG NUMBER: SA4XXRDIP-C1020D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1695.5	1698.1	1700.6	1701.9	1701.6	1701.4	1701.1	1700.9
5°	1684.2	1687.2	1690.1	1691.2	1690.6	1690.1	1689.5	1688.9
7.5°	1661.9	1663.7	1665.6	1666.0	1665.1	1664.2	1663.2	1662.3
10°	1641.7	1642.9	1644.0	1644.0	1642.9	1641.7	1640.5	1639.4
12.5°	1616.7	1617.5	1618.2	1617.7	1616.1	1614.5	1612.9	1611.3
15°	1573.1	1572.4	1571.9	1570.6	1568.6	1566.5	1564.5	1562.5
17.5°	1520.4	1518.8	1517.2	1514.9	1511.7	1508.7	1505.6	1502.5
20°	1483.6	1481.3	1478.9	1475.9	1472.2	1468.4	1464.6	1460.8
22.5°	1442.7	1439.2	1435.8	1432.5	1429.4	1426.3	1423.2	1420.2
25°	1376.7	1371.8	1366.9	1362.9	1360.1	1357.2	1354.2	1351.4
27.5°	1309.5	1303.4	1297.3	1292.2	1288.1	1283.8	1279.7	1275.5
30°	1261.3	1254.1	1246.8	1240.9	1236.2	1231.6	1227.0	1222.4
32.5°	1212.1	1203.7	1195.3	1188.9	1184.5	1180.1	1175.7	1171.3
35°	1138.8	1129.0	1119.1	1111.6	1106.4	1101.2	1096.0	1090.7
37.5°	1060.2	1049.1	1038.1	1030.0	1024.8	1019.5	1014.4	1009.2
40°	1007.8	995.6	983.4	974.8	969.6	964.3	959.1	953.9
42.5°	956.2	943.9	931.4	922.6	917.1	911.6	906.2	900.8
45°	877.3	863.1	848.9	839.2	834.1	828.8	823.6	818.4
47.5°	797.9	783.2	768.4	758.2	752.4	746.7	740.9	735.3
50°	745.1	730.7	716.1	706.2	700.7	695.1	689.7	684.2
52.5°	692.5	677.8	663.1	652.9	647.1	641.4	635.7	630.0
55°	614.9	599.9	584.8	574.6	569.0	563.5	558.1	552.5
57.5°	539.1	523.9	508.6	498.9	494.6	490.5	486.4	482.2
60°	488.5	473.4	458.5	448.6	443.9	439.3	434.7	430.1
62.5°	438.8	424.8	410.9	402.1	398.4	394.7	391.0	387.3
65°	367.3	354.9	342.4	334.5	331.0	327.5	324.0	320.6
67.5°	301.7	291.1	280.3	273.1	269.2	265.4	261.6	257.8
70°	257.1	247.6	238.1	231.8	228.9	226.0	223.1	220.3
72.5°	217.2	209.1	200.9	195.5	192.7	190.1	187.5	184.8
75°	160.0	153.4	146.7	142.5	140.7	139.0	137.2	135.5
77.5°	113.2	109.3	105.4	103.2	102.6	102.2	101.6	101.1
80°	86.9	86.1	85.1	84.5	84.3	84.0	83.7	83.4
82.5°	67.5	66.9	66.3	65.8	65.5	65.2	64.9	64.7
85°	39.2	38.6	38.1	37.8	37.8	37.8	37.8	37.8
87.5°	18.8	18.8	18.9	18.9	19.3	19.6	19.9	20.3
90°	23.2	24.5	25.7	26.6	27.0	27.4	27.8	28.2
92.5°	22.4	23.8	25.0	25.6	25.7	25.8	25.9	26.0
95°	23.2	24.5	25.7	26.5	26.7	26.9	27.1	27.2
97.5°	25.1	25.3	25.4	25.5	25.7	25.9	26.1	26.4
100°	34.3	30.7	27.1	25.5	25.7	25.9	26.1	26.4
102.5°	122.8	84.5	46.1	27.0	27.0	27.1	27.1	27.1
105°	297.4	299.2	301.0	298.3	290.8	283.2	275.7	268.2
107.5°	367.9	368.8	369.7	370.5	371.4	372.1	373.0	373.7
110°	415.8	416.2	416.6	417.2	417.7	418.4	419.1	419.6



TEST NUMBER: P332976-830

CATALOG NUMBER: SA4XXRDIP-C1020D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	462.2	462.1	462.0	462.4	463.2	464.0	464.8	465.5
115°	531.5	532.0	532.3	532.5	532.5	532.5	532.5	532.5
117.5°	601.2	601.2	601.1	601.1	601.0	600.9	600.8	600.7
120°	644.4	644.8	645.3	645.3	644.8	644.4	644.0	643.6
122.5°	687.0	687.2	687.5	687.4	687.0	686.5	686.2	685.7
125°	746.5	747.1	747.7	748.1	748.4	748.6	748.8	748.9
127.5°	805.6	805.4	805.3	805.1	805.0	804.8	804.6	804.5
130°	841.6	841.8	842.0	842.2	842.2	842.2	842.2	842.2
132.5°	876.9	877.2	877.4	877.4	877.2	877.0	876.9	876.8
135°	925.8	926.1	926.6	927.0	927.5	927.8	928.2	928.7
137.5°	972.5	973.0	973.5	973.6	973.5	973.4	973.2	973.1
140°	1001.5	1002.1	1002.7	1003.1	1003.3	1003.5	1003.7	1004.0
142.5°	1028.2	1028.7	1029.2	1029.4	1029.4	1029.4	1029.5	1029.5
145°	1066.5	1066.7	1066.9	1067.2	1067.6	1068.0	1068.5	1068.8
147.5°	1100.0	1100.2	1100.4	1100.6	1100.8	1101.0	1101.3	1101.5
150°	1121.5	1121.5	1121.5	1121.6	1121.9	1122.1	1122.3	1122.5
152.5°	1140.3	1140.7	1140.9	1141.0	1140.9	1140.9	1140.7	1140.6
155°	1165.5	1166.4	1167.2	1167.3	1166.8	1166.1	1165.5	1164.9
157.5°	1187.3	1188.5	1189.5	1189.5	1188.5	1187.3	1186.3	1185.2
160°	1201.3	1202.5	1203.7	1203.7	1202.5	1201.3	1200.0	1198.7
162.5°	1212.5	1213.8	1215.0	1214.9	1213.5	1212.1	1210.7	1209.3
165°	1228.4	1230.1	1231.7	1231.6	1229.7	1227.9	1226.0	1224.1
167.5°	1240.0	1241.9	1243.7	1243.6	1241.5	1239.4	1237.3	1235.2
170°	1247.3	1248.9	1250.6	1250.4	1248.3	1246.2	1244.1	1242.0
172.5°	1251.8	1253.4	1255.1	1254.8	1252.5	1250.3	1248.0	1245.8
175°	1257.1	1259.0	1260.8	1260.5	1258.0	1255.5	1253.0	1250.5
177.5°	1259.1	1260.5	1261.9	1261.5	1259.5	1257.5	1255.5	1253.5
180°	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0

(END OF REPORT)