

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333007-830

Luminaire Tested: **SA4XXRDIP-C1195D1035U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P333007-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D1035U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7919.9 lumens
Efficiency: N/A
Efficacy: 118.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333007-830
CATALOG NUMBER: SA4XXRDIP-C1195D1035U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333007-830

CATALOG NUMBER: SA4XXRDIP-C1195D1035U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	95	92	88	93	89	86	83	77	75	73	66	64	63	56	55	54	49
2	91	84	78	73	85	78	73	68	68	64	61	59	56	53	50	48	46	41
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	42	39	35
4	76	66	58	52	71	61	54	49	54	48	44	46	42	39	40	37	34	31
5	70	59	51	45	65	55	48	42	48	42	38	42	37	34	36	33	30	27
6	65	53	45	39	60	50	42	37	44	38	33	38	33	30	33	29	26	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	40	32	27	48	38	31	26	33	28	24	29	25	21	26	22	19	17
10	49	37	29	24	45	35	28	23	31	25	21	27	23	19	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15868	15868	15868
5°	15904	15709	15807
10°	15805	15521	15521
15°	15623	15195	15082
20°	15374	14766	14495
25°	15055	14264	13903
30°	14746	13736	13160
35°	14402	13186	12415
40°	13990	12562	11610
45°	13609	11942	10791
50°	13175	11228	9923
55°	12711	10486	8981
60°	12198	9671	8018
65°	11731	8653	7072
70°	11049	7532	6005
75°	10187	6245	4885
80°	8884	4761	4477
85°	7521	4326	4039



TEST NUMBER: P333007-830

CATALOG NUMBER: SA4XXRDIP-C1195D1035U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.6	2.3
10°-20°	514.9	6.5
20°-30°	743.5	9.4
30°-40°	842.8	10.6
40°-50°	813.8	10.3
50°-60°	676.7	8.5
60°-70°	467.3	5.9
70°-80°	236.9	3.0
80°-90°	64.4	0.8
90°-100°	80.2	1.0
100°-110°	237.7	3.0
110°-120°	403.4	5.1
120°-130°	531.9	6.7
130°-140°	597.4	7.5
140°-150°	587.0	7.4
150°-160°	493.7	6.2
160°-170°	328.5	4.1
170°-180°	115.0	1.5
0°-30°	1443.1	18.2
0°-40°	2285.8	28.9
0°-60°	3776.4	47.7
0°-90°	4545.0	57.4
90°-120°	721.3	9.1
90°-150°	2437.7	30.8
90°-180°	3375.0	42.6
0°-180°	7919.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1966	1966	1966	1966	1966	
5°	1963	1956	1938	1953	1951	186
15°	1869	1854	1818	1815	1805	526
25°	1690	1661	1601	1576	1561	778
35°	1461	1412	1338	1288	1260	913
45°	1192	1134	1046	975	945	919
55°	903	841	745	669	638	807
65°	614	548	453	391	370	606
75°	327	270	200	167	157	345
85°	81	53	47	44	44	91
90°	3	13	21	26	28	7
95°	56	65	72	74	74	63
105°	219	220	224	227	230	233
115°	410	410	408	407	406	404
125°	597	597	596	595	593	532
135°	770	776	776	774	772	596
145°	936	940	941	940	937	586
155°	1072	1072	1072	1075	1072	493
165°	1168	1165	1163	1168	1165	329
175°	1215	1210	1209	1215	1209	115
180°	1216	1216	1216	1216	1216	



TEST NUMBER: P333007-830

CATALOG NUMBER: SA4XXRDIP-C1195D1035U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1970.4	1969.3	1968.3	1967.2	1966.1	1964.2	1961.2	1958.2	1955.3	1952.4	1955.3
5°	1962.6	1961.2	1959.9	1958.6	1957.3	1954.6	1950.6	1946.5	1942.6	1938.5	1941.8
7.5°	1944.8	1943.4	1942.0	1940.6	1939.2	1935.9	1930.7	1925.5	1920.2	1915.1	1917.2
10°	1928.0	1926.3	1924.7	1923.0	1921.3	1917.4	1911.5	1905.4	1899.4	1893.4	1894.7
12.5°	1906.3	1904.4	1902.4	1900.4	1898.6	1894.0	1887.0	1879.9	1872.7	1865.7	1866.5
15°	1869.3	1866.2	1863.3	1860.3	1857.3	1851.5	1843.2	1834.8	1826.5	1818.1	1817.4
17.5°	1824.5	1820.0	1815.7	1811.4	1807.0	1799.9	1789.8	1779.8	1769.7	1759.7	1757.8
20°	1789.5	1785.2	1780.8	1776.5	1772.2	1764.3	1752.9	1741.5	1730.1	1718.8	1716.1
22.5°	1751.0	1746.2	1741.3	1736.4	1731.5	1723.0	1710.7	1698.6	1686.4	1674.2	1670.2
25°	1690.2	1684.1	1678.1	1672.2	1666.1	1656.2	1642.6	1628.8	1615.1	1601.4	1595.7
27.5°	1626.4	1618.8	1611.3	1603.7	1596.1	1585.1	1570.4	1555.8	1541.1	1526.4	1519.4
30°	1581.9	1573.5	1565.1	1556.7	1548.4	1536.3	1520.6	1504.9	1489.2	1473.5	1465.1
32.5°	1534.8	1525.4	1516.0	1506.6	1497.1	1484.3	1468.0	1451.8	1435.5	1419.3	1409.6
35°	1461.4	1450.7	1440.0	1429.3	1418.6	1404.9	1388.2	1371.5	1354.7	1338.0	1326.6
37.5°	1382.9	1371.8	1360.7	1349.7	1338.7	1323.9	1305.4	1286.9	1268.4	1249.8	1237.1
40°	1327.5	1316.4	1305.4	1294.4	1283.3	1268.3	1249.2	1230.1	1211.1	1192.0	1178.0
42.5°	1274.5	1262.9	1251.3	1239.7	1228.2	1212.5	1192.6	1172.7	1152.9	1133.0	1118.7
45°	1192.0	1179.6	1167.2	1154.9	1142.6	1126.2	1106.3	1086.2	1066.1	1046.0	1029.6
47.5°	1106.8	1094.0	1081.3	1068.5	1055.7	1038.9	1018.0	997.1	976.3	955.5	938.4
50°	1049.0	1035.9	1022.9	1009.9	996.8	979.6	958.2	936.8	915.4	894.0	877.3
52.5°	990.0	977.2	964.5	951.7	939.0	921.5	899.7	877.7	855.7	833.8	816.8
55°	903.1	889.7	876.3	862.9	849.5	832.0	810.2	788.5	766.8	745.0	727.6
57.5°	816.9	803.0	789.1	775.2	761.3	743.7	722.3	700.8	679.4	658.0	640.4
60°	755.5	742.2	728.8	715.4	702.0	684.7	663.3	641.9	620.4	599.0	581.6
62.5°	700.1	686.3	672.3	658.5	644.5	626.6	604.6	582.7	560.7	538.9	522.7
65°	614.1	599.6	585.3	570.9	556.6	538.7	517.3	495.9	474.5	453.0	438.7
67.5°	524.6	510.9	497.1	483.3	469.6	452.7	432.8	413.0	393.1	373.2	360.9
70°	468.1	454.0	440.0	425.9	411.9	395.3	376.3	357.2	338.2	319.1	308.0
72.5°	407.8	395.2	382.5	369.8	357.0	341.7	323.7	305.7	287.7	269.7	260.2
75°	326.6	314.2	301.8	289.5	277.1	263.1	247.3	231.6	215.9	200.2	192.5
77.5°	244.1	233.7	223.1	212.6	202.1	190.5	177.8	165.1	152.4	139.7	135.2
80°	191.1	181.4	171.7	162.0	152.3	142.5	132.4	122.4	112.4	102.4	101.3
82.5°	145.4	136.5	127.6	118.7	109.8	102.5	96.7	91.0	85.2	79.5	78.7
85°	81.2	74.6	67.9	61.2	54.5	50.7	49.7	48.6	47.7	46.7	46.0
87.5°	28.3	26.6	24.9	23.2	21.5	20.7	20.8	20.8	20.9	21.0	21.0
90°	2.8	5.1	7.4	9.7	12.1	14.0	15.6	17.3	19.0	20.7	22.0
92.5°	20.2	22.8	25.4	28.0	30.6	32.6	33.7	34.9	36.1	37.2	38.0
95°	56.5	58.3	60.2	62.1	64.0	65.6	67.1	68.6	70.0	71.5	72.1
97.5°	98.6	100.1	101.6	103.1	104.6	106.2	107.9	109.6	111.4	113.1	113.9
100°	131.7	132.5	133.4	134.2	135.1	136.4	138.3	140.2	142.0	143.9	144.4
102.5°	166.4	166.6	167.0	167.3	167.7	168.7	170.4	172.1	173.8	175.6	176.2
105°	219.2	219.4	219.6	219.8	220.1	220.6	221.4	222.3	223.1	223.9	224.5
107.5°	274.8	274.9	275.2	275.5	275.7	275.9	276.1	276.2	276.3	276.4	277.0
110°	312.4	312.7	313.2	313.6	314.1	314.1	313.9	313.7	313.5	313.3	312.8



TEST NUMBER: P333007-830

CATALOG NUMBER: SA4XXRDIP-C1195D1035U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	351.5	351.6	351.7	351.8	351.9	351.7	351.3	350.9	350.5	350.2	350.1
115°	410.2	410.2	410.2	410.2	410.2	410.0	409.5	409.2	408.7	408.3	408.1
117.5°	465.5	465.7	465.8	466.0	466.2	466.1	465.8	465.5	465.2	465.0	464.2
120°	502.4	503.2	504.1	504.9	505.8	505.9	505.2	504.5	504.0	503.3	502.3
122.5°	540.7	541.1	541.4	541.8	542.1	542.2	541.9	541.5	541.2	540.9	540.3
125°	597.4	597.4	597.4	597.4	597.4	597.3	597.1	596.9	596.6	596.4	596.1
127.5°	648.8	649.4	650.0	650.6	651.3	651.4	651.1	650.7	650.4	650.1	649.7
130°	684.9	685.5	686.2	686.7	687.4	687.7	687.7	687.7	687.7	687.7	687.3
132.5°	721.8	722.3	722.6	723.1	723.6	723.8	723.6	723.4	723.2	723.1	722.6
135°	770.5	771.8	773.0	774.3	775.5	776.2	776.2	776.2	776.2	776.2	775.7
137.5°	823.6	824.2	824.7	825.3	826.0	826.3	826.7	827.1	827.4	827.7	827.2
140°	858.9	859.3	859.8	860.2	860.6	860.8	860.8	860.8	860.8	860.8	860.6
142.5°	891.3	891.7	892.1	892.6	893.0	893.1	893.0	892.8	892.6	892.4	892.4
145°	936.0	936.9	937.7	938.6	939.4	939.9	940.2	940.4	940.6	940.8	940.6
147.5°	980.5	981.5	982.5	983.5	984.5	985.0	984.8	984.6	984.4	984.3	984.1
150°	1007.6	1008.4	1009.3	1010.1	1011.0	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3
152.5°	1033.2	1033.7	1034.2	1034.7	1035.2	1035.5	1035.7	1035.9	1036.0	1036.1	1036.7
155°	1072.5	1072.5	1072.5	1072.5	1072.5	1072.4	1072.1	1072.0	1071.8	1071.6	1072.4
157.5°	1105.6	1105.2	1104.8	1104.5	1104.1	1103.9	1103.8	1103.8	1103.8	1103.7	1104.4
160°	1125.2	1124.9	1124.7	1124.5	1124.4	1124.2	1123.9	1123.7	1123.5	1123.3	1123.9
162.5°	1143.2	1142.7	1142.2	1141.6	1141.0	1140.7	1140.5	1140.3	1140.1	1139.8	1140.9
165°	1167.5	1166.9	1166.3	1165.6	1165.0	1164.5	1164.0	1163.7	1163.2	1162.8	1164.0
167.5°	1186.2	1185.2	1184.4	1183.6	1182.6	1182.2	1182.2	1182.3	1182.3	1182.4	1183.6
170°	1196.7	1195.6	1194.6	1193.5	1192.5	1192.0	1192.3	1192.5	1192.7	1192.9	1194.2
172.5°	1204.2	1203.3	1202.5	1201.6	1200.7	1200.2	1200.3	1200.3	1200.4	1200.4	1201.8
175°	1214.6	1213.5	1212.5	1211.4	1210.4	1209.8	1209.6	1209.3	1209.1	1208.9	1210.4
177.5°	1218.0	1217.1	1216.3	1215.4	1214.6	1214.2	1214.2	1214.2	1214.2	1214.2	1215.3
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4



TEST NUMBER: P333007-830

CATALOG NUMBER: SA4XXRDIP-C1195D1035U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1958.2	1961.2	1964.2	1965.5	1965.2	1964.9	1964.6	1964.4
5°	1945.2	1948.5	1951.9	1953.2	1952.6	1951.9	1951.3	1950.6
7.5°	1919.3	1921.5	1923.6	1924.1	1923.1	1922.0	1920.9	1919.9
10°	1896.0	1897.3	1898.8	1898.8	1897.3	1896.0	1894.7	1893.4
12.5°	1867.3	1868.1	1868.9	1868.3	1866.5	1864.6	1862.7	1860.9
15°	1816.8	1816.1	1815.4	1813.9	1811.6	1809.2	1806.9	1804.6
17.5°	1756.0	1754.1	1752.2	1749.5	1746.0	1742.4	1738.9	1735.3
20°	1713.4	1710.7	1708.1	1704.6	1700.3	1695.9	1691.5	1687.2
22.5°	1666.2	1662.2	1658.2	1654.4	1650.9	1647.3	1643.8	1640.2
25°	1590.0	1584.3	1578.7	1574.1	1570.7	1567.4	1564.1	1560.8
27.5°	1512.4	1505.3	1498.4	1492.4	1487.6	1482.8	1478.0	1473.2
30°	1456.7	1448.4	1440.0	1433.1	1427.8	1422.5	1417.1	1411.7
32.5°	1399.9	1390.2	1380.4	1373.1	1368.0	1362.9	1357.8	1352.7
35°	1315.2	1303.9	1292.5	1283.8	1277.8	1271.8	1265.7	1259.7
37.5°	1224.4	1211.6	1199.0	1189.6	1183.6	1177.5	1171.6	1165.5
40°	1163.9	1149.9	1135.9	1125.8	1119.7	1113.7	1107.8	1101.7
42.5°	1104.4	1090.1	1075.7	1065.5	1059.1	1052.9	1046.6	1040.3
45°	1013.2	996.8	980.4	969.2	963.3	957.2	951.2	945.2
47.5°	921.4	904.5	887.5	875.6	869.0	862.4	855.7	849.1
50°	860.5	843.9	827.1	815.6	809.3	802.9	796.5	790.1
52.5°	799.8	782.9	765.8	754.0	747.4	740.8	734.1	727.5
55°	710.2	692.9	675.4	663.5	657.2	650.8	644.5	638.1
57.5°	622.7	605.0	587.4	576.2	571.4	566.5	561.7	556.9
60°	564.2	546.9	529.4	518.1	512.7	507.4	502.0	496.6
62.5°	506.7	490.7	474.6	464.4	460.1	455.9	451.6	447.3
65°	424.2	409.9	395.5	386.3	382.3	378.2	374.3	370.2
67.5°	348.6	336.1	323.8	315.4	310.9	306.5	302.1	297.7
70°	297.0	286.0	274.9	267.8	264.4	261.1	257.7	254.4
72.5°	250.8	241.4	232.0	225.7	222.6	219.6	216.5	213.4
75°	184.8	177.1	169.4	164.6	162.6	160.5	158.5	156.6
77.5°	130.7	126.2	121.8	119.2	118.6	118.0	117.4	116.8
80°	100.4	99.3	98.3	97.6	97.4	97.0	96.7	96.3
82.5°	78.0	77.3	76.5	76.0	75.7	75.3	75.0	74.6
85°	45.3	44.7	44.0	43.6	43.6	43.6	43.6	43.6
87.5°	20.9	20.9	20.9	21.1	21.5	21.8	22.1	22.5
90°	23.2	24.5	25.7	26.6	27.0	27.4	27.8	28.2
92.5°	38.7	39.5	40.2	40.8	41.0	41.3	41.6	41.8
95°	72.8	73.4	74.0	74.4	74.4	74.4	74.4	74.4
97.5°	114.6	115.4	116.1	116.5	116.5	116.5	116.5	116.5
100°	144.8	145.2	145.6	145.8	145.8	145.8	145.8	145.8
102.5°	176.7	177.3	177.9	178.2	178.4	178.6	178.8	178.9
105°	225.2	225.8	226.4	227.1	227.6	228.3	228.9	229.5
107.5°	277.6	278.1	278.7	279.0	279.0	278.9	278.9	278.8
110°	312.5	312.0	311.6	311.7	312.4	312.9	313.6	314.2



TEST NUMBER: P333007-830

CATALOG NUMBER: SA4XXRDIP-C1195D1035U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	350.0	349.9	349.9	349.9	350.0	350.1	350.2	350.3
115°	407.8	407.6	407.5	407.3	407.1	406.8	406.6	406.4
117.5°	463.5	462.8	462.1	461.6	461.1	460.7	460.2	459.9
120°	501.2	500.2	499.2	498.8	499.3	499.6	500.1	500.5
122.5°	539.5	538.9	538.1	537.3	536.6	535.8	535.1	534.3
125°	595.6	595.2	594.7	594.4	594.0	593.5	593.1	592.7
127.5°	649.2	648.8	648.4	648.0	647.7	647.3	647.1	646.7
130°	686.9	686.5	686.1	685.4	684.6	683.7	682.9	682.0
132.5°	722.3	721.8	721.4	721.0	720.7	720.4	720.0	719.7
135°	775.3	774.9	774.5	773.9	773.4	772.7	772.0	771.5
137.5°	826.6	826.0	825.6	825.3	825.5	825.6	825.7	825.9
140°	860.4	860.2	860.0	859.8	859.6	859.3	859.1	858.9
142.5°	892.3	892.3	892.3	892.2	892.2	892.1	892.1	892.0
145°	940.4	940.2	939.9	939.5	938.9	938.3	937.6	937.0
147.5°	983.9	983.7	983.5	983.4	983.2	983.0	982.8	982.6
150°	1011.3	1011.3	1011.3	1011.3	1011.1	1010.8	1010.6	1010.4
152.5°	1037.2	1037.6	1038.2	1038.2	1037.6	1037.1	1036.5	1035.9
155°	1073.3	1074.0	1074.9	1074.9	1074.0	1073.3	1072.4	1071.6
157.5°	1104.9	1105.6	1106.3	1106.2	1105.5	1104.8	1104.1	1103.3
160°	1124.5	1125.2	1125.8	1125.6	1124.5	1123.5	1122.5	1121.4
162.5°	1142.1	1143.2	1144.3	1144.4	1143.4	1142.4	1141.3	1140.2
165°	1165.4	1166.6	1167.8	1168.0	1167.2	1166.4	1165.5	1164.7
167.5°	1184.9	1186.2	1187.4	1187.4	1186.1	1184.8	1183.5	1182.2
170°	1195.4	1196.7	1198.0	1197.8	1196.4	1194.9	1193.4	1191.9
172.5°	1203.2	1204.7	1206.2	1206.1	1204.7	1203.2	1201.7	1200.2
175°	1211.8	1213.3	1214.7	1214.7	1213.3	1211.8	1210.4	1208.9
177.5°	1216.5	1217.7	1218.9	1218.8	1217.5	1216.1	1214.7	1213.4
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4

(END OF REPORT)