

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331717-840

Luminaire Tested: **SA2XXRDIP-C865D725U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331717-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6260.9 lumens  
Efficiency: N/A  
Efficacy: 115.1 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331717-840  
CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				
1	99	95	92	88	92	89	85	83	76	74	72	64	63	61	54	52	52	46				
2	91	84	78	74	84	78	73	69	68	64	61	57	55	53	48	46	45	40				
3	84	75	68	62	78	70	64	59	60	56	52	52	48	46	44	41	39	35				
4	77	67	59	54	71	63	56	51	54	49	45	47	43	40	40	37	35	31				
5	71	60	52	47	66	56	50	44	49	44	40	42	38	35	36	33	31	28				
6	66	54	47	41	61	51	44	39	45	39	35	39	35	31	33	30	28	25				
7	61	50	42	37	57	47	40	35	41	35	32	36	31	28	31	27	25	23				
8	57	45	38	33	53	43	36	31	38	32	28	33	29	26	28	25	23	20				
9	53	42	34	30	50	39	33	28	35	29	26	30	26	23	26	23	21	19				
10	50	38	31	27	47	36	30	26	32	27	23	28	24	21	25	21	19	17				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	31136	31136	31136	31136
5°	34775	31331	27780	31331
10°	38581	31111	24079	31111
15°	40478	30654	18974	30654
20°	35093	29979	16417	29979
25°	23013	29054	14658	29054
30°	15491	27932	13267	27932
35°	12546	26518	11964	26518
40°	11158	24982	11072	24982
45°	10097	23178	9882	23178
50°	9191	21391	9156	21391
55°	8639	19409	8526	19409
60°	7227	17589	7143	17589
65°	6094	15973	6911	15973
70°	5632	14266	6515	14266
75°	5265	12414	6014	12414
80°	4863	10219	5365	10219
85°	4465	8058	4705	8058



TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.8	2.9
10°-20°	509.4	8.1
20°-30°	656.4	10.5
30°-40°	623.8	10.0
40°-50°	534.4	8.5
50°-60°	406.9	6.5
60°-70°	257.2	4.1
70°-80°	128.5	2.1
80°-90°	35.9	0.6
90°-100°	33.3	0.5
100°-110°	122.1	2.0
110°-120°	326.4	5.2
120°-130°	538.9	8.6
130°-140°	573.1	9.2
140°-150°	532.7	8.5
150°-160°	428.3	6.8
160°-170°	276.0	4.4
170°-180°	95.0	1.5
0°-30°	1348.5	21.5
0°-40°	1972.3	31.5
0°-60°	2913.6	46.5
0°-90°	3335.2	53.3
90°-120°	481.9	7.7
90°-150°	2126.5	34.0
90°-180°	2926.0	46.7
0°-180°	6260.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1928	1928	1928	1928	1928	
5°	2146	1933	1714	1933	2146	212
15°	2422	1834	1135	1834	2422	653
25°	1292	1631	823	1631	1292	613
35°	636	1345	607	1345	636	407
45°	442	1015	433	1015	442	342
55°	307	690	303	690	307	269
65°	160	418	181	418	160	162
75°	84	199	96	199	84	90
85°	24	44	25	44	24	26
90°	20	1	20	1	20	10
95°	31	47	31	47	31	29
105°	55	220	55	220	55	57
115°	59	415	59	415	59	148
125°	618	587	618	587	618	534
135°	750	727	750	727	750	578
145°	856	843	856	843	856	535
155°	929	928	929	928	929	429
165°	976	978	976	978	976	276
175°	995	1000	995	1000	995	95
180°	998	998	998	998	998	



TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	2006.7	2008.3	2009.9	2006.1	2006.1	2003.0	1996.0	1990.6	1975.6	1973.5	1973.5
5°	2145.6	2144.1	2146.9	2138.2	2126.1	2123.4	2110.7	2094.0	2076.5	2057.1	2053.1
7.5°	2283.5	2281.5	2276.1	2274.7	2265.4	2245.2	2224.7	2202.9	2173.9	2145.7	2131.4
10°	2353.2	2375.3	2362.0	2338.4	2343.2	2311.7	2294.9	2266.1	2242.0	2199.8	2190.4
12.5°	2421.9	2430.5	2426.3	2413.0	2407.0	2385.1	2362.5	2337.4	2292.9	2255.0	2222.0
15°	2421.6	2434.3	2437.6	2433.7	2437.0	2435.7	2423.6	2402.8	2364.0	2322.4	2286.2
17.5°	2242.8	2251.7	2273.6	2288.5	2307.2	2346.9	2366.5	2374.1	2368.3	2344.6	2319.2
20°	2042.4	2027.6	2089.2	2120.7	2147.5	2214.5	2272.2	2294.3	2329.8	2329.2	2322.4
22.5°	1758.2	1761.7	1820.2	1857.5	1935.8	2002.8	2068.5	2151.7	2220.4	2265.8	2292.4
25°	1291.8	1317.4	1375.6	1426.5	1513.7	1638.3	1751.5	1882.9	2006.8	2104.7	2197.8
27.5°	970.3	972.1	1018.3	1065.4	1117.1	1219.2	1361.8	1518.6	1695.4	1841.2	2008.9
30°	830.9	826.9	846.3	875.0	919.3	998.4	1105.6	1259.7	1435.9	1655.7	1851.4
32.5°	732.3	732.5	747.1	768.4	805.2	858.5	931.9	1057.1	1223.7	1439.7	1669.1
35°	636.5	635.9	646.6	662.0	677.4	711.6	761.8	827.5	942.1	1143.8	1378.3
37.5°	567.9	570.9	576.1	585.7	602.8	621.8	652.0	696.1	777.7	897.0	1094.1
40°	529.4	530.7	538.1	546.1	556.1	570.9	595.7	631.2	690.8	786.0	930.0
42.5°	493.9	495.3	500.5	508.1	515.9	530.7	551.2	581.9	630.3	704.5	823.3
45°	442.2	442.2	447.0	450.3	459.0	472.4	489.2	514.6	548.1	603.1	682.2
47.5°	393.7	393.8	397.0	402.7	408.2	418.7	435.2	456.0	480.3	522.8	590.4
50°	365.9	366.5	368.5	373.2	376.6	386.0	398.7	416.8	442.2	475.0	531.4
52.5°	343.4	343.0	345.5	347.5	349.8	356.5	366.0	381.9	404.8	433.2	479.9
55°	306.9	304.2	308.2	311.5	313.6	316.3	321.6	331.6	351.1	375.3	410.1
57.5°	261.4	260.2	263.1	266.1	272.5	279.6	284.3	290.6	300.7	318.0	352.5
60°	223.8	223.8	229.8	231.9	239.2	248.6	258.0	263.4	273.4	284.8	310.2
62.5°	190.6	191.1	193.9	195.9	200.1	211.6	224.7	236.5	246.0	256.9	273.8
65°	159.5	160.8	160.8	162.2	164.8	167.5	172.9	182.3	199.0	214.4	227.1
67.5°	135.3	135.7	136.1	137.5	138.1	141.1	143.3	147.4	151.3	165.9	181.7
70°	119.3	121.3	120.6	122.0	122.6	123.9	126.6	128.7	134.7	138.0	147.4
72.5°	104.2	105.7	105.6	106.4	108.2	108.5	110.6	112.6	116.4	119.3	124.3
75°	84.4	83.7	84.4	85.7	86.4	87.2	87.2	89.8	91.8	94.5	97.9
77.5°	65.1	65.8	65.6	65.8	65.9	67.2	67.1	68.2	70.2	71.6	73.2
80°	52.3	52.9	52.3	52.9	53.6	54.2	53.6	54.2	56.2	57.7	57.7
82.5°	40.5	40.6	41.0	41.1	41.3	41.4	42.3	42.5	43.9	43.7	44.2
85°	24.1	23.4	23.4	23.4	24.1	24.7	24.1	24.1	24.7	24.7	24.7
87.5°	12.5	12.9	12.9	12.8	12.7	12.6	12.5	12.8	12.1	12.5	11.7
90°	19.5	19.2	18.9	18.6	18.2	17.7	16.9	16.1	15.2	14.4	13.1
92.5°	19.5	19.3	19.1	18.9	18.8	18.4	18.0	17.6	17.2	16.8	16.2
95°	31.1	31.2	31.4	31.5	31.7	31.4	30.6	29.8	29.0	28.2	27.1
97.5°	41.5	41.3	41.1	40.9	40.7	40.3	39.6	39.0	38.4	37.7	35.1
100°	48.4	48.1	47.8	47.5	47.2	46.4	45.0	43.7	42.4	41.2	38.5
102.5°	51.9	51.4	51.0	50.5	50.1	49.0	47.4	45.6	44.0	42.3	65.1
105°	54.9	54.2	53.6	53.0	52.3	51.1	49.4	47.6	45.8	44.0	87.9
107.5°	56.5	55.8	55.2	54.5	53.9	54.5	56.2	58.1	59.9	61.7	114.2
110°	57.1	56.5	55.7	55.1	54.5	62.2	78.3	94.3	110.4	126.4	172.8



TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.7	57.2	56.7	56.1	55.5	84.6	143.2	201.8	260.3	318.8	330.3
115°	59.3	70.8	82.3	93.9	105.4	148.5	222.8	297.1	371.4	445.8	441.7
117.5°	241.9	279.8	317.8	355.8	393.7	421.7	439.7	457.8	475.7	493.7	490.9
120°	440.7	462.3	484.0	505.6	527.4	537.2	535.3	533.4	531.4	529.5	526.6
122.5°	549.9	554.1	558.3	562.5	566.7	568.3	567.0	565.9	564.7	563.6	560.5
125°	617.6	617.1	616.7	616.2	615.7	614.9	613.8	612.7	611.6	610.5	607.3
127.5°	660.5	660.4	660.2	660.1	660.0	659.1	657.5	655.9	654.3	652.6	650.4
130°	687.0	687.1	687.3	687.5	687.6	686.8	685.1	683.3	681.6	679.7	678.0
132.5°	713.0	713.2	713.4	713.5	713.7	713.0	711.4	709.9	708.4	706.9	705.2
135°	750.5	750.8	751.2	751.5	751.8	751.2	749.6	748.0	746.4	744.8	743.4
137.5°	784.8	785.4	785.9	786.5	787.0	786.5	784.9	783.4	781.7	780.2	778.5
140°	806.2	807.0	807.8	808.6	809.4	809.1	807.6	806.2	804.8	803.3	801.5
142.5°	827.0	827.8	828.6	829.4	830.2	829.9	828.6	827.3	826.0	824.7	822.6
145°	856.1	856.9	857.7	858.5	859.2	859.1	858.0	856.9	855.8	854.5	851.8
147.5°	881.6	882.3	882.9	883.6	884.3	884.2	883.4	882.5	881.7	880.9	878.2
150°	897.2	898.0	898.8	899.6	900.4	900.3	899.4	898.4	897.5	896.5	893.9
152.5°	910.5	911.6	912.6	913.7	914.7	914.8	913.8	912.8	911.9	910.9	908.5
155°	929.0	930.3	931.6	932.8	934.1	934.3	933.3	932.4	931.4	930.4	928.5
157.5°	945.9	947.2	948.4	949.7	950.9	951.0	949.9	948.8	947.8	946.6	945.2
160°	955.7	956.8	958.0	959.1	960.2	960.3	959.4	958.4	957.5	956.4	955.4
162.5°	963.8	965.2	966.5	968.0	969.4	969.5	968.4	967.2	966.2	965.1	964.3
165°	975.9	977.0	978.2	979.4	980.5	980.5	979.4	978.2	977.0	975.9	975.4
167.5°	983.6	985.0	986.5	988.0	989.4	989.6	988.5	987.3	986.1	985.0	984.6
170°	988.3	989.7	991.1	992.6	994.0	994.2	993.0	991.9	990.8	989.7	989.4
172.5°	991.7	993.1	994.6	996.0	997.4	997.6	996.5	995.4	994.3	993.1	992.8
175°	994.7	996.3	997.9	999.6	1001.2	1001.4	1000.3	999.2	998.0	996.9	996.5
177.5°	996.6	997.7	999.0	1000.1	1001.3	1001.4	1000.5	999.6	998.7	997.7	997.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1974.5	1970.2	1966.5	1956.8	1952.0	1941.3	1939.6	1939.1	1925.2	1911.8	1908.0
5°	2042.4	2031.6	2015.5	1996.8	1977.3	1957.2	1943.8	1933.1	1906.3	1880.9	1866.1
7.5°	2110.7	2087.6	2059.9	2024.4	1994.8	1961.6	1936.8	1914.7	1876.7	1840.3	1815.7
10°	2161.6	2124.0	2087.2	2038.3	2000.1	1962.6	1927.7	1897.6	1854.7	1806.4	1772.3
12.5°	2193.2	2151.9	2101.1	2053.4	2003.9	1956.1	1909.6	1870.8	1820.4	1770.6	1729.9
15°	2235.9	2191.7	2130.1	2061.7	1998.1	1935.8	1882.2	1833.9	1768.3	1708.6	1659.0
17.5°	2271.0	2210.1	2143.9	2064.9	1991.2	1912.0	1842.9	1781.3	1708.2	1636.3	1577.8
20°	2282.2	2221.9	2145.6	2066.5	1979.3	1886.2	1811.8	1744.8	1666.4	1588.0	1521.1
22.5°	2275.2	2228.4	2143.3	2048.7	1959.5	1862.1	1778.1	1700.3	1613.4	1533.4	1455.6
25°	2228.0	2211.8	2131.4	2028.2	1926.4	1813.2	1716.0	1630.9	1531.8	1446.0	1361.5
27.5°	2117.7	2152.3	2102.5	1992.6	1879.4	1758.0	1648.7	1551.9	1449.0	1352.4	1268.3
30°	2011.6	2091.2	2069.8	1967.9	1841.3	1722.0	1599.4	1498.2	1388.4	1289.2	1206.1
32.5°	1866.2	1997.9	2018.9	1933.7	1802.7	1671.6	1543.2	1442.5	1327.8	1223.2	1142.3
35°	1635.0	1831.9	1922.4	1868.1	1736.8	1595.4	1462.7	1345.4	1230.2	1127.0	1046.6
37.5°	1359.0	1627.3	1778.1	1781.9	1661.3	1514.3	1369.9	1253.4	1135.5	1034.2	947.2
40°	1179.9	1470.8	1667.1	1710.6	1608.8	1450.0	1303.9	1185.3	1070.1	970.9	871.1
42.5°	1019.2	1308.9	1550.2	1626.0	1545.0	1387.3	1240.7	1116.7	1004.7	910.9	808.9
45°	824.2	1077.4	1343.4	1478.8	1433.9	1287.9	1133.1	1015.1	909.9	828.9	731.0
47.5°	695.3	873.7	1131.1	1314.2	1313.4	1180.1	1027.8	914.9	817.3	741.3	662.2
50°	621.8	777.3	995.0	1202.7	1220.1	1108.2	963.5	851.6	760.5	680.8	617.1
52.5°	555.8	684.0	879.8	1078.9	1128.5	1031.6	891.2	787.9	699.4	626.1	571.6
55°	469.7	568.9	717.6	903.9	979.0	910.6	786.0	689.5	617.8	556.1	509.3
57.5°	397.4	471.7	591.1	741.0	828.5	785.5	682.7	604.3	542.9	487.2	450.1
60°	351.7	412.7	513.9	639.2	735.7	705.6	617.8	544.7	492.5	444.2	409.4
62.5°	308.9	361.3	448.0	549.7	638.1	625.7	554.0	492.7	447.0	402.9	373.4
65°	248.6	286.8	354.5	434.2	505.2	511.3	459.7	418.1	377.3	342.4	316.3
67.5°	197.9	222.9	270.5	337.7	390.9	409.9	378.4	346.7	314.3	287.3	264.7
70°	166.8	186.9	221.8	276.1	325.0	345.1	327.0	302.2	274.1	252.0	232.5
72.5°	135.2	154.8	180.5	220.4	262.3	284.0	277.7	259.8	237.0	218.7	200.4
75°	101.9	107.9	125.3	152.1	184.9	203.7	208.4	199.0	180.9	166.8	156.1
77.5°	75.3	79.0	87.3	101.3	122.8	139.5	146.3	145.2	132.8	124.6	114.6
80°	60.3	62.3	66.3	72.4	88.5	105.2	109.9	109.9	101.2	97.9	87.8
82.5°	45.8	47.3	49.7	53.0	60.6	75.1	80.4	81.5	75.9	71.6	63.6
85°	26.2	25.4	26.8	28.8	30.2	34.1	42.2	43.5	42.2	36.9	34.8
87.5°	11.5	11.8	11.5	10.7	10.8	11.0	13.3	15.7	13.9	12.6	11.9
90°	11.9	10.6	9.3	7.8	6.1	4.2	2.5	0.7	2.5	4.2	6.1
92.5°	15.5	14.8	14.2	13.9	14.1	14.2	14.4	14.5	14.4	14.2	14.1
95°	26.0	24.8	23.6	25.8	31.1	36.4	41.7	47.0	41.7	36.4	31.1
97.5°	32.5	29.9	27.3	33.4	48.4	63.3	78.3	93.2	78.3	63.3	48.4
100°	35.7	33.0	30.3	39.9	61.9	83.9	105.8	127.8	105.8	83.9	61.9
102.5°	88.0	110.8	133.6	147.3	152.1	156.7	161.4	166.0	161.4	156.7	152.1
105°	131.7	175.5	219.3	238.8	234.1	229.2	224.4	219.6	224.4	229.2	234.1
107.5°	166.8	219.3	272.0	296.3	292.4	288.5	284.6	280.7	284.6	288.5	292.4
110°	219.2	265.6	311.9	333.5	330.1	326.8	323.4	320.0	323.4	326.8	330.1





TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	341.7	353.3	364.7	368.9	366.0	362.9	360.0	357.0	360.0	362.9	366.0
115°	437.7	433.6	429.7	426.3	423.5	420.8	418.1	415.4	418.1	420.8	423.5
117.5°	488.2	485.4	482.6	479.7	476.7	473.6	470.6	467.6	470.6	473.6	476.7
120°	523.7	520.9	518.0	515.3	512.9	510.5	508.1	505.6	508.1	510.5	512.9
122.5°	557.3	554.2	551.0	548.2	545.6	543.1	540.6	538.1	540.6	543.1	545.6
125°	604.3	601.3	598.2	595.6	593.6	591.5	589.4	587.3	589.4	591.5	593.6
127.5°	648.0	645.8	643.5	641.2	638.8	636.6	634.3	632.0	634.3	636.6	638.8
130°	676.2	674.5	672.7	670.6	667.9	665.4	662.9	660.2	662.9	665.4	667.9
132.5°	703.4	701.7	699.8	697.9	695.7	693.6	691.4	689.1	691.4	693.6	695.7
135°	741.8	740.4	739.0	737.0	734.5	731.8	729.3	726.7	729.3	731.8	734.5
137.5°	776.9	775.3	773.7	771.9	770.1	768.3	766.5	764.8	766.5	768.3	770.1
140°	799.8	798.0	796.3	794.7	793.5	792.1	790.8	789.6	790.8	792.1	793.5
142.5°	820.6	818.6	816.6	815.0	813.9	812.7	811.5	810.4	811.5	812.7	813.9
145°	849.1	846.4	843.6	842.4	842.5	842.7	842.8	843.0	842.8	842.7	842.5
147.5°	875.5	872.8	870.1	869.1	869.7	870.3	870.9	871.5	870.9	870.3	869.7
150°	891.3	888.8	886.3	885.4	886.7	887.8	888.9	890.0	888.9	887.8	886.7
152.5°	906.1	903.6	901.2	900.6	901.8	903.1	904.3	905.5	904.3	903.1	901.8
155°	926.6	924.6	922.7	922.5	923.9	925.3	926.9	928.3	926.9	925.3	923.9
157.5°	943.9	942.6	941.2	941.2	942.4	943.6	944.8	946.0	944.8	943.6	942.4
160°	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4	955.4	954.5	953.5
162.5°	963.4	962.6	961.8	961.8	962.8	963.8	964.7	965.7	964.7	963.8	962.8
165°	975.0	974.5	974.0	974.2	975.2	976.2	977.1	978.2	977.1	976.2	975.2
167.5°	984.1	983.7	983.2	983.5	984.5	985.4	986.4	987.3	986.4	985.4	984.5
170°	989.1	988.8	988.4	988.8	989.7	990.7	991.6	992.6	991.6	990.7	989.7
172.5°	992.5	992.2	991.9	992.2	993.1	994.1	995.0	996.0	995.0	994.1	993.1
175°	996.2	995.9	995.6	996.0	997.1	998.3	999.4	1000.5	999.4	998.3	997.1
177.5°	997.5	997.3	997.2	997.6	998.6	999.5	1000.4	1001.3	1000.4	999.5	998.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1901.1	1897.3	1890.4	1879.7	1873.2	1862.0	1854.4	1858.8	1859.8	1858.8	1857.6
5°	1850.0	1835.9	1816.5	1797.8	1780.3	1761.6	1750.8	1746.2	1736.8	1731.4	1728.8
7.5°	1788.3	1764.0	1736.5	1703.8	1676.1	1647.0	1632.1	1624.8	1605.6	1595.1	1586.0
10°	1742.1	1703.9	1676.5	1633.6	1607.5	1569.2	1543.2	1543.8	1517.6	1502.9	1492.2
12.5°	1691.2	1649.3	1603.6	1565.0	1528.6	1497.9	1466.5	1453.7	1426.0	1411.8	1382.8
15°	1606.8	1557.9	1509.6	1457.3	1420.5	1372.9	1327.4	1271.7	1226.9	1188.0	1177.3
17.5°	1514.6	1454.0	1405.6	1344.2	1281.1	1201.1	1148.3	1116.0	1088.9	1068.4	1053.2
20°	1451.4	1389.7	1338.1	1245.7	1160.5	1106.3	1067.4	1042.6	1014.5	992.4	980.3
22.5°	1384.8	1320.5	1250.2	1147.0	1080.7	1037.1	1002.5	974.0	954.9	937.7	926.7
25°	1290.5	1220.1	1104.3	1033.2	979.6	934.0	909.9	892.5	872.4	849.0	838.2
27.5°	1190.8	1078.9	995.7	942.9	891.7	862.1	840.4	814.4	796.4	785.9	774.7
30°	1116.3	1004.4	939.4	881.8	845.6	812.7	787.3	772.5	755.2	737.1	729.7
32.5°	1033.2	943.8	881.5	833.5	796.8	768.8	748.7	724.9	712.3	701.1	685.7
35°	930.0	862.3	805.4	766.6	731.7	708.9	685.5	671.4	648.6	639.2	633.2
37.5°	842.6	784.0	741.4	700.4	672.9	647.6	633.3	611.0	601.1	588.0	575.3
40°	793.3	735.7	694.9	661.4	630.6	611.8	593.7	575.6	560.9	554.8	539.4
42.5°	743.0	696.1	655.2	618.4	597.8	577.9	555.1	541.8	526.5	516.7	507.3
45°	673.4	631.9	597.0	566.8	544.1	523.3	508.6	486.5	477.8	458.3	450.3
47.5°	612.3	573.7	540.5	511.8	489.6	476.1	454.4	437.2	423.2	411.3	400.9
50°	568.9	536.7	504.5	479.1	459.0	439.6	417.5	408.7	387.3	381.2	375.3
52.5°	529.2	498.7	469.2	444.2	424.1	405.3	385.8	374.5	359.9	354.0	349.5
55°	473.7	444.2	416.1	393.9	373.9	354.5	342.4	328.3	321.6	316.9	311.5
57.5°	418.0	391.4	369.9	347.5	327.3	311.8	297.9	289.4	282.5	276.3	269.9
60°	382.6	357.1	337.7	316.9	296.2	283.5	272.7	262.7	254.6	245.2	242.6
62.5°	345.1	322.9	305.0	284.8	266.7	255.0	244.8	235.3	225.7	212.0	208.2
65°	293.5	276.1	257.3	240.5	224.5	213.1	198.3	187.6	183.6	182.3	181.6
67.5°	246.8	230.4	214.3	197.1	182.5	172.0	164.4	162.8	160.0	159.2	157.3
70°	215.7	200.4	184.3	168.1	154.1	152.1	149.5	146.7	143.4	142.1	140.7
72.5°	187.8	172.0	155.8	143.0	136.9	134.4	131.7	129.1	126.7	125.4	124.6
75°	144.1	129.4	118.6	113.9	110.6	108.6	104.5	102.5	101.2	99.2	98.5
77.5°	103.7	95.4	90.5	87.6	84.0	81.9	79.6	77.6	76.1	75.7	74.6
80°	79.1	75.0	71.7	67.7	66.3	63.6	63.0	61.0	61.6	59.7	59.7
82.5°	61.4	56.2	53.4	51.6	50.3	48.1	47.5	46.5	46.7	45.1	45.1
85°	31.5	30.2	28.8	27.5	27.5	25.4	26.2	25.4	25.4	24.1	23.4
87.5°	11.7	11.5	10.7	10.9	11.2	10.9	11.1	10.7	10.9	11.0	10.6
90°	7.8	9.3	10.6	11.9	13.1	14.4	15.2	16.1	16.9	17.7	18.2
92.5°	13.9	14.2	14.8	15.5	16.2	16.8	17.2	17.6	18.0	18.4	18.8
95°	25.8	23.6	24.8	26.0	27.1	28.2	29.0	29.8	30.6	31.4	31.7
97.5°	33.4	27.3	29.9	32.5	35.1	37.7	38.4	39.0	39.6	40.3	40.7
100°	39.9	30.3	33.0	35.7	38.5	41.2	42.4	43.7	45.0	46.4	47.2
102.5°	147.3	133.6	110.8	88.0	65.1	42.3	44.0	45.6	47.4	49.0	50.1
105°	238.8	219.3	175.5	131.7	87.9	44.0	45.8	47.6	49.4	51.1	52.3
107.5°	296.3	272.0	219.3	166.8	114.2	61.7	59.9	58.1	56.2	54.5	53.9
110°	333.5	311.9	265.6	219.2	172.8	126.4	110.4	94.3	78.3	62.2	54.5



TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	368.9	364.7	353.3	341.7	330.3	318.8	260.3	201.8	143.2	84.6	55.5
115°	426.3	429.7	433.6	437.7	441.7	445.8	371.4	297.1	222.8	148.5	105.4
117.5°	479.7	482.6	485.4	488.2	490.9	493.7	475.7	457.8	439.7	421.7	393.7
120°	515.3	518.0	520.9	523.7	526.6	529.5	531.4	533.4	535.3	537.2	527.4
122.5°	548.2	551.0	554.2	557.3	560.5	563.6	564.7	565.9	567.0	568.3	566.7
125°	595.6	598.2	601.3	604.3	607.3	610.5	611.6	612.7	613.8	614.9	615.7
127.5°	641.2	643.5	645.8	648.0	650.4	652.6	654.3	655.9	657.5	659.1	660.0
130°	670.6	672.7	674.5	676.2	678.0	679.7	681.6	683.3	685.1	686.8	687.6
132.5°	697.9	699.8	701.7	703.4	705.2	706.9	708.4	709.9	711.4	713.0	713.7
135°	737.0	739.0	740.4	741.8	743.4	744.8	746.4	748.0	749.6	751.2	751.8
137.5°	771.9	773.7	775.3	776.9	778.5	780.2	781.7	783.4	784.9	786.5	787.0
140°	794.7	796.3	798.0	799.8	801.5	803.3	804.8	806.2	807.6	809.1	809.4
142.5°	815.0	816.6	818.6	820.6	822.6	824.7	826.0	827.3	828.6	829.9	830.2
145°	842.4	843.6	846.4	849.1	851.8	854.5	855.8	856.9	858.0	859.1	859.2
147.5°	869.1	870.1	872.8	875.5	878.2	880.9	881.7	882.5	883.4	884.2	884.3
150°	885.4	886.3	888.8	891.3	893.9	896.5	897.5	898.4	899.4	900.3	900.4
152.5°	900.6	901.2	903.6	906.1	908.5	910.9	911.9	912.8	913.8	914.8	914.7
155°	922.5	922.7	924.6	926.6	928.5	930.4	931.4	932.4	933.3	934.3	934.1
157.5°	941.2	941.2	942.6	943.9	945.2	946.6	947.8	948.8	949.9	951.0	950.9
160°	952.6	952.6	953.5	954.5	955.4	956.4	957.5	958.4	959.4	960.3	960.2
162.5°	961.8	961.8	962.6	963.4	964.3	965.1	966.2	967.2	968.4	969.5	969.4
165°	974.2	974.0	974.5	975.0	975.4	975.9	977.0	978.2	979.4	980.5	980.5
167.5°	983.5	983.2	983.7	984.1	984.6	985.0	986.1	987.3	988.5	989.6	989.4
170°	988.8	988.4	988.8	989.1	989.4	989.7	990.8	991.9	993.0	994.2	994.0
172.5°	992.2	991.9	992.2	992.5	992.8	993.1	994.3	995.4	996.5	997.6	997.4
175°	996.0	995.6	995.9	996.2	996.5	996.9	998.0	999.2	1000.3	1001.4	1001.2
177.5°	997.6	997.2	997.3	997.5	997.6	997.7	998.7	999.6	1000.5	1001.4	1001.3
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331717-840  
 CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1851.8	1852.8	1851.2	1852.3	1851.2	1852.8	1851.8	1857.6	1858.8	1859.8	1858.8
5°	1725.4	1717.4	1716.0	1714.0	1716.0	1717.4	1725.4	1728.8	1731.4	1736.8	1746.2
7.5°	1574.5	1573.3	1569.9	1565.3	1569.9	1573.3	1574.5	1586.0	1595.1	1605.6	1624.8
10°	1477.4	1474.1	1473.5	1468.7	1473.5	1474.1	1477.4	1492.2	1502.9	1517.6	1543.8
12.5°	1363.8	1342.2	1340.0	1328.3	1340.0	1342.2	1363.8	1382.8	1411.8	1426.0	1453.7
15°	1161.2	1157.2	1143.8	1135.1	1143.8	1157.2	1161.2	1177.3	1188.0	1226.9	1271.7
17.5°	1045.4	1032.3	1028.1	1026.2	1028.1	1032.3	1045.4	1053.2	1068.4	1088.9	1116.0
20°	970.9	958.9	956.8	955.5	956.8	958.9	970.9	980.3	992.4	1014.5	1042.6
22.5°	919.5	906.9	901.6	897.6	901.6	906.9	919.5	926.7	937.7	954.9	974.0
25°	831.5	826.9	824.2	822.8	824.2	826.9	831.5	838.2	849.0	872.4	892.5
27.5°	762.8	752.5	750.4	747.0	750.4	752.5	762.8	774.7	785.9	796.4	814.4
30°	723.7	720.3	715.6	711.6	715.6	720.3	723.7	729.7	737.1	755.2	772.5
32.5°	677.5	674.8	670.6	668.7	670.6	674.8	677.5	685.7	701.1	712.3	724.9
35°	626.5	617.1	613.1	607.0	613.1	617.1	626.5	633.2	639.2	648.6	671.4
37.5°	572.5	567.5	561.9	563.9	561.9	567.5	572.5	575.3	588.0	601.1	611.0
40°	530.7	527.4	526.0	525.3	526.0	527.4	530.7	539.4	554.8	560.9	575.6
42.5°	497.5	488.2	484.7	484.5	484.7	488.2	497.5	507.3	516.7	526.5	541.8
45°	447.0	438.2	432.2	432.8	432.2	438.2	447.0	450.3	458.3	477.8	486.5
47.5°	395.2	395.0	391.2	392.4	391.2	395.0	395.2	400.9	411.3	423.2	437.2
50°	370.5	366.5	363.9	364.5	363.9	366.5	370.5	375.3	381.2	387.3	408.7
52.5°	347.0	343.5	341.3	344.2	341.3	343.5	347.0	349.5	354.0	359.9	374.5
55°	308.2	304.2	303.6	302.9	303.6	304.2	308.2	311.5	316.9	321.6	328.3
57.5°	265.0	262.3	258.2	256.5	258.2	262.3	265.0	269.9	276.3	282.5	289.4
60°	233.9	228.5	221.8	221.2	221.8	228.5	233.9	242.6	245.2	254.6	262.7
62.5°	205.4	204.4	203.0	202.9	203.0	204.4	205.4	208.2	212.0	225.7	235.3
65°	180.3	179.6	180.3	180.9	180.3	179.6	180.3	181.6	182.3	183.6	187.6
67.5°	157.0	155.8	154.6	155.2	154.6	155.8	157.0	157.3	159.2	160.0	162.8
70°	139.4	138.7	138.0	138.0	138.0	138.7	139.4	140.7	142.1	143.4	146.7
72.5°	122.2	122.1	121.4	120.9	121.4	122.1	122.2	124.6	125.4	126.7	129.1
75°	97.9	96.4	96.4	96.4	96.4	96.4	97.9	98.5	99.2	101.2	102.5
77.5°	74.5	73.8	73.2	72.6	73.2	73.8	74.5	74.6	75.7	76.1	77.6
80°	59.0	58.3	57.7	57.7	57.7	58.3	59.0	59.7	59.7	61.6	61.0
82.5°	45.0	44.3	44.2	43.7	44.2	44.3	45.0	45.1	45.1	46.7	46.5
85°	24.1	24.7	24.1	25.4	24.1	24.7	24.1	23.4	24.1	25.4	25.4
87.5°	10.7	10.2	10.8	10.3	10.8	10.2	10.7	10.6	11.0	10.9	10.7
90°	18.6	18.9	19.2	19.5	19.2	18.9	18.6	18.2	17.7	16.9	16.1
92.5°	18.9	19.1	19.3	19.5	19.3	19.1	18.9	18.8	18.4	18.0	17.6
95°	31.5	31.4	31.2	31.1	31.2	31.4	31.5	31.7	31.4	30.6	29.8
97.5°	40.9	41.1	41.3	41.5	41.3	41.1	40.9	40.7	40.3	39.6	39.0
100°	47.5	47.8	48.1	48.4	48.1	47.8	47.5	47.2	46.4	45.0	43.7
102.5°	50.5	51.0	51.4	51.9	51.4	51.0	50.5	50.1	49.0	47.4	45.6
105°	53.0	53.6	54.2	54.9	54.2	53.6	53.0	52.3	51.1	49.4	47.6
107.5°	54.5	55.2	55.8	56.5	55.8	55.2	54.5	53.9	54.5	56.2	58.1
110°	55.1	55.7	56.5	57.1	56.5	55.7	55.1	54.5	62.2	78.3	94.3



TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	56.1	56.7	57.2	57.7	57.2	56.7	56.1	55.5	84.6	143.2	201.8
115°	93.9	82.3	70.8	59.3	70.8	82.3	93.9	105.4	148.5	222.8	297.1
117.5°	355.8	317.8	279.8	241.9	279.8	317.8	355.8	393.7	421.7	439.7	457.8
120°	505.6	484.0	462.3	440.7	462.3	484.0	505.6	527.4	537.2	535.3	533.4
122.5°	562.5	558.3	554.1	549.9	554.1	558.3	562.5	566.7	568.3	567.0	565.9
125°	616.2	616.7	617.1	617.6	617.1	616.7	616.2	615.7	614.9	613.8	612.7
127.5°	660.1	660.2	660.4	660.5	660.4	660.2	660.1	660.0	659.1	657.5	655.9
130°	687.5	687.3	687.1	687.0	687.1	687.3	687.5	687.6	686.8	685.1	683.3
132.5°	713.5	713.4	713.2	713.0	713.2	713.4	713.5	713.7	713.0	711.4	709.9
135°	751.5	751.2	750.8	750.5	750.8	751.2	751.5	751.8	751.2	749.6	748.0
137.5°	786.5	785.9	785.4	784.8	785.4	785.9	786.5	787.0	786.5	784.9	783.4
140°	808.6	807.8	807.0	806.2	807.0	807.8	808.6	809.4	809.1	807.6	806.2
142.5°	829.4	828.6	827.8	827.0	827.8	828.6	829.4	830.2	829.9	828.6	827.3
145°	858.5	857.7	856.9	856.1	856.9	857.7	858.5	859.2	859.1	858.0	856.9
147.5°	883.6	882.9	882.3	881.6	882.3	882.9	883.6	884.3	884.2	883.4	882.5
150°	899.6	898.8	898.0	897.2	898.0	898.8	899.6	900.4	900.3	899.4	898.4
152.5°	913.7	912.6	911.6	910.5	911.6	912.6	913.7	914.7	914.8	913.8	912.8
155°	932.8	931.6	930.3	929.0	930.3	931.6	932.8	934.1	934.3	933.3	932.4
157.5°	949.7	948.4	947.2	945.9	947.2	948.4	949.7	950.9	951.0	949.9	948.8
160°	959.1	958.0	956.8	955.7	956.8	958.0	959.1	960.2	960.3	959.4	958.4
162.5°	968.0	966.5	965.2	963.8	965.2	966.5	968.0	969.4	969.5	968.4	967.2
165°	979.4	978.2	977.0	975.9	977.0	978.2	979.4	980.5	980.5	979.4	978.2
167.5°	988.0	986.5	985.0	983.6	985.0	986.5	988.0	989.4	989.6	988.5	987.3
170°	992.6	991.1	989.7	988.3	989.7	991.1	992.6	994.0	994.2	993.0	991.9
172.5°	996.0	994.6	993.1	991.7	993.1	994.6	996.0	997.4	997.6	996.5	995.4
175°	999.6	997.9	996.3	994.7	996.3	997.9	999.6	1001.2	1001.4	1000.3	999.2
177.5°	1000.1	999.0	997.7	996.6	997.7	999.0	1000.1	1001.3	1001.4	1000.5	999.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1854.4	1862.0	1873.2	1879.7	1890.4	1897.3	1901.1	1908.0	1911.8	1925.2	1939.1
5°	1750.8	1761.6	1780.3	1797.8	1816.5	1835.9	1850.0	1866.1	1880.9	1906.3	1933.1
7.5°	1632.1	1647.0	1676.1	1703.8	1736.5	1764.0	1788.3	1815.7	1840.3	1876.7	1914.7
10°	1543.2	1569.2	1607.5	1633.6	1676.5	1703.9	1742.1	1772.3	1806.4	1854.7	1897.6
12.5°	1466.5	1497.9	1528.6	1565.0	1603.6	1649.3	1691.2	1729.9	1770.6	1820.4	1870.8
15°	1327.4	1372.9	1420.5	1457.3	1509.6	1557.9	1606.8	1659.0	1708.6	1768.3	1833.9
17.5°	1148.3	1201.1	1281.1	1344.2	1405.6	1454.0	1514.6	1577.8	1636.3	1708.2	1781.3
20°	1067.4	1106.3	1160.5	1245.7	1338.1	1389.7	1451.4	1521.1	1588.0	1666.4	1744.8
22.5°	1002.5	1037.1	1080.7	1147.0	1250.2	1320.5	1384.8	1455.6	1533.4	1613.4	1700.3
25°	909.9	934.0	979.6	1033.2	1104.3	1220.1	1290.5	1361.5	1446.0	1531.8	1630.9
27.5°	840.4	862.1	891.7	942.9	995.7	1078.9	1190.8	1268.3	1352.4	1449.0	1551.9
30°	787.3	812.7	845.6	881.8	939.4	1004.4	1116.3	1206.1	1289.2	1388.4	1498.2
32.5°	748.7	768.8	796.8	833.5	881.5	943.8	1033.2	1142.3	1223.2	1327.8	1442.5
35°	685.5	708.9	731.7	766.6	805.4	862.3	930.0	1046.6	1127.0	1230.2	1345.4
37.5°	633.3	647.6	672.9	700.4	741.4	784.0	842.6	947.2	1034.2	1135.5	1253.4
40°	593.7	611.8	630.6	661.4	694.9	735.7	793.3	871.1	970.9	1070.1	1185.3
42.5°	555.1	577.9	597.8	618.4	655.2	696.1	743.0	808.9	910.9	1004.7	1116.7
45°	508.6	523.3	544.1	566.8	597.0	631.9	673.4	731.0	828.9	909.9	1015.1
47.5°	454.4	476.1	489.6	511.8	540.5	573.7	612.3	662.2	741.3	817.3	914.9
50°	417.5	439.6	459.0	479.1	504.5	536.7	568.9	617.1	680.8	760.5	851.6
52.5°	385.8	405.3	424.1	444.2	469.2	498.7	529.2	571.6	626.1	699.4	787.9
55°	342.4	354.5	373.9	393.9	416.1	444.2	473.7	509.3	556.1	617.8	689.5
57.5°	297.9	311.8	327.3	347.5	369.9	391.4	418.0	450.1	487.2	542.9	604.3
60°	272.7	283.5	296.2	316.9	337.7	357.1	382.6	409.4	444.2	492.5	544.7
62.5°	244.8	255.0	266.7	284.8	305.0	322.9	345.1	373.4	402.9	447.0	492.7
65°	198.3	213.1	224.5	240.5	257.3	276.1	293.5	316.3	342.4	377.3	418.1
67.5°	164.4	172.0	182.5	197.1	214.3	230.4	246.8	264.7	287.3	314.3	346.7
70°	149.5	152.1	154.1	168.1	184.3	200.4	215.7	232.5	252.0	274.1	302.2
72.5°	131.7	134.4	136.9	143.0	155.8	172.0	187.8	200.4	218.7	237.0	259.8
75°	104.5	108.6	110.6	113.9	118.6	129.4	144.1	156.1	166.8	180.9	199.0
77.5°	79.6	81.9	84.0	87.6	90.5	95.4	103.7	114.6	124.6	132.8	145.2
80°	63.0	63.6	66.3	67.7	71.7	75.0	79.1	87.8	97.9	101.2	109.9
82.5°	47.5	48.1	50.3	51.6	53.4	56.2	61.4	63.6	71.6	75.9	81.5
85°	26.2	25.4	27.5	27.5	28.8	30.2	31.5	34.8	36.9	42.2	43.5
87.5°	11.1	10.9	11.2	10.9	10.7	11.5	11.7	11.9	12.6	13.9	15.7
90°	15.2	14.4	13.1	11.9	10.6	9.3	7.8	6.1	4.2	2.5	0.7
92.5°	17.2	16.8	16.2	15.5	14.8	14.2	13.9	14.1	14.2	14.4	14.5
95°	29.0	28.2	27.1	26.0	24.8	23.6	25.8	31.1	36.4	41.7	47.0
97.5°	38.4	37.7	35.1	32.5	29.9	27.3	33.4	48.4	63.3	78.3	93.2
100°	42.4	41.2	38.5	35.7	33.0	30.3	39.9	61.9	83.9	105.8	127.8
102.5°	44.0	42.3	65.1	88.0	110.8	133.6	147.3	152.1	156.7	161.4	166.0
105°	45.8	44.0	87.9	131.7	175.5	219.3	238.8	234.1	229.2	224.4	219.6
107.5°	59.9	61.7	114.2	166.8	219.3	272.0	296.3	292.4	288.5	284.6	280.7
110°	110.4	126.4	172.8	219.2	265.6	311.9	333.5	330.1	326.8	323.4	320.0



TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.3	318.8	330.3	341.7	353.3	364.7	368.9	366.0	362.9	360.0	357.0
115°	371.4	445.8	441.7	437.7	433.6	429.7	426.3	423.5	420.8	418.1	415.4
117.5°	475.7	493.7	490.9	488.2	485.4	482.6	479.7	476.7	473.6	470.6	467.6
120°	531.4	529.5	526.6	523.7	520.9	518.0	515.3	512.9	510.5	508.1	505.6
122.5°	564.7	563.6	560.5	557.3	554.2	551.0	548.2	545.6	543.1	540.6	538.1
125°	611.6	610.5	607.3	604.3	601.3	598.2	595.6	593.6	591.5	589.4	587.3
127.5°	654.3	652.6	650.4	648.0	645.8	643.5	641.2	638.8	636.6	634.3	632.0
130°	681.6	679.7	678.0	676.2	674.5	672.7	670.6	667.9	665.4	662.9	660.2
132.5°	708.4	706.9	705.2	703.4	701.7	699.8	697.9	695.7	693.6	691.4	689.1
135°	746.4	744.8	743.4	741.8	740.4	739.0	737.0	734.5	731.8	729.3	726.7
137.5°	781.7	780.2	778.5	776.9	775.3	773.7	771.9	770.1	768.3	766.5	764.8
140°	804.8	803.3	801.5	799.8	798.0	796.3	794.7	793.5	792.1	790.8	789.6
142.5°	826.0	824.7	822.6	820.6	818.6	816.6	815.0	813.9	812.7	811.5	810.4
145°	855.8	854.5	851.8	849.1	846.4	843.6	842.4	842.5	842.7	842.8	843.0
147.5°	881.7	880.9	878.2	875.5	872.8	870.1	869.1	869.7	870.3	870.9	871.5
150°	897.5	896.5	893.9	891.3	888.8	886.3	885.4	886.7	887.8	888.9	890.0
152.5°	911.9	910.9	908.5	906.1	903.6	901.2	900.6	901.8	903.1	904.3	905.5
155°	931.4	930.4	928.5	926.6	924.6	922.7	922.5	923.9	925.3	926.9	928.3
157.5°	947.8	946.6	945.2	943.9	942.6	941.2	941.2	942.4	943.6	944.8	946.0
160°	957.5	956.4	955.4	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4
162.5°	966.2	965.1	964.3	963.4	962.6	961.8	961.8	962.8	963.8	964.7	965.7
165°	977.0	975.9	975.4	975.0	974.5	974.0	974.2	975.2	976.2	977.1	978.2
167.5°	986.1	985.0	984.6	984.1	983.7	983.2	983.5	984.5	985.4	986.4	987.3
170°	990.8	989.7	989.4	989.1	988.8	988.4	988.8	989.7	990.7	991.6	992.6
172.5°	994.3	993.1	992.8	992.5	992.2	991.9	992.2	993.1	994.1	995.0	996.0
175°	998.0	996.9	996.5	996.2	995.9	995.6	996.0	997.1	998.3	999.4	1000.5
177.5°	998.7	997.7	997.6	997.5	997.3	997.2	997.6	998.6	999.5	1000.4	1001.3
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1939.6	1941.3	1952.0	1956.8	1966.5	1970.2	1974.5	1973.5	1973.5	1975.6	1990.6
5°	1943.8	1957.2	1977.3	1996.8	2015.5	2031.6	2042.4	2053.1	2057.1	2076.5	2094.0
7.5°	1936.8	1961.6	1994.8	2024.4	2059.9	2087.6	2110.7	2131.4	2145.7	2173.9	2202.9
10°	1927.7	1962.6	2000.1	2038.3	2087.2	2124.0	2161.6	2190.4	2199.8	2242.0	2266.1
12.5°	1909.6	1956.1	2003.9	2053.4	2101.1	2151.9	2193.2	2222.0	2255.0	2292.9	2337.4
15°	1882.2	1935.8	1998.1	2061.7	2130.1	2191.7	2235.9	2286.2	2322.4	2364.0	2402.8
17.5°	1842.9	1912.0	1991.2	2064.9	2143.9	2210.1	2271.0	2319.2	2344.6	2368.3	2374.1
20°	1811.8	1886.2	1979.3	2066.5	2145.6	2221.9	2282.2	2322.4	2329.2	2329.8	2294.3
22.5°	1778.1	1862.1	1959.5	2048.7	2143.3	2228.4	2275.2	2292.4	2265.8	2220.4	2151.7
25°	1716.0	1813.2	1926.4	2028.2	2131.4	2211.8	2228.0	2197.8	2104.7	2006.8	1882.9
27.5°	1648.7	1758.0	1879.4	1992.6	2102.5	2152.3	2117.7	2008.9	1841.2	1695.4	1518.6
30°	1599.4	1722.0	1841.3	1967.9	2069.8	2091.2	2011.6	1851.4	1655.7	1435.9	1259.7
32.5°	1543.2	1671.6	1802.7	1933.7	2018.9	1997.9	1866.2	1669.1	1439.7	1223.7	1057.1
35°	1462.7	1595.4	1736.8	1868.1	1922.4	1831.9	1635.0	1378.3	1143.8	942.1	827.5
37.5°	1369.9	1514.3	1661.3	1781.9	1778.1	1627.3	1359.0	1094.1	897.0	777.7	696.1
40°	1303.9	1450.0	1608.8	1710.6	1667.1	1470.8	1179.9	930.0	786.0	690.8	631.2
42.5°	1240.7	1387.3	1545.0	1626.0	1550.2	1308.9	1019.2	823.3	704.5	630.3	581.9
45°	1133.1	1287.9	1433.9	1478.8	1343.4	1077.4	824.2	682.2	603.1	548.1	514.6
47.5°	1027.8	1180.1	1313.4	1314.2	1131.1	873.7	695.3	590.4	522.8	480.3	456.0
50°	963.5	1108.2	1220.1	1202.7	995.0	777.3	621.8	531.4	475.0	442.2	416.8
52.5°	891.2	1031.6	1128.5	1078.9	879.8	684.0	555.8	479.9	433.2	404.8	381.9
55°	786.0	910.6	979.0	903.9	717.6	568.9	469.7	410.1	375.3	351.1	331.6
57.5°	682.7	785.5	828.5	741.0	591.1	471.7	397.4	352.5	318.0	300.7	290.6
60°	617.8	705.6	735.7	639.2	513.9	412.7	351.7	310.2	284.8	273.4	263.4
62.5°	554.0	625.7	638.1	549.7	448.0	361.3	308.9	273.8	256.9	246.0	236.5
65°	459.7	511.3	505.2	434.2	354.5	286.8	248.6	227.1	214.4	199.0	182.3
67.5°	378.4	409.9	390.9	337.7	270.5	222.9	197.9	181.7	165.9	151.3	147.4
70°	327.0	345.1	325.0	276.1	221.8	186.9	166.8	147.4	138.0	134.7	128.7
72.5°	277.7	284.0	262.3	220.4	180.5	154.8	135.2	124.3	119.3	116.4	112.6
75°	208.4	203.7	184.9	152.1	125.3	107.9	101.9	97.9	94.5	91.8	89.8
77.5°	146.3	139.5	122.8	101.3	87.3	79.0	75.3	73.2	71.6	70.2	68.2
80°	109.9	105.2	88.5	72.4	66.3	62.3	60.3	57.7	57.7	56.2	54.2
82.5°	80.4	75.1	60.6	53.0	49.7	47.3	45.8	44.2	43.7	43.9	42.5
85°	42.2	34.1	30.2	28.8	26.8	25.4	26.2	24.7	24.7	24.7	24.1
87.5°	13.3	11.0	10.8	10.7	11.5	11.8	11.5	11.7	12.5	12.1	12.8
90°	2.5	4.2	6.1	7.8	9.3	10.6	11.9	13.1	14.4	15.2	16.1
92.5°	14.4	14.2	14.1	13.9	14.2	14.8	15.5	16.2	16.8	17.2	17.6
95°	41.7	36.4	31.1	25.8	23.6	24.8	26.0	27.1	28.2	29.0	29.8
97.5°	78.3	63.3	48.4	33.4	27.3	29.9	32.5	35.1	37.7	38.4	39.0
100°	105.8	83.9	61.9	39.9	30.3	33.0	35.7	38.5	41.2	42.4	43.7
102.5°	161.4	156.7	152.1	147.3	133.6	110.8	88.0	65.1	42.3	44.0	45.6
105°	224.4	229.2	234.1	238.8	219.3	175.5	131.7	87.9	44.0	45.8	47.6
107.5°	284.6	288.5	292.4	296.3	272.0	219.3	166.8	114.2	61.7	59.9	58.1
110°	323.4	326.8	330.1	333.5	311.9	265.6	219.2	172.8	126.4	110.4	94.3





TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	360.0	362.9	366.0	368.9	364.7	353.3	341.7	330.3	318.8	260.3	201.8
115°	418.1	420.8	423.5	426.3	429.7	433.6	437.7	441.7	445.8	371.4	297.1
117.5°	470.6	473.6	476.7	479.7	482.6	485.4	488.2	490.9	493.7	475.7	457.8
120°	508.1	510.5	512.9	515.3	518.0	520.9	523.7	526.6	529.5	531.4	533.4
122.5°	540.6	543.1	545.6	548.2	551.0	554.2	557.3	560.5	563.6	564.7	565.9
125°	589.4	591.5	593.6	595.6	598.2	601.3	604.3	607.3	610.5	611.6	612.7
127.5°	634.3	636.6	638.8	641.2	643.5	645.8	648.0	650.4	652.6	654.3	655.9
130°	662.9	665.4	667.9	670.6	672.7	674.5	676.2	678.0	679.7	681.6	683.3
132.5°	691.4	693.6	695.7	697.9	699.8	701.7	703.4	705.2	706.9	708.4	709.9
135°	729.3	731.8	734.5	737.0	739.0	740.4	741.8	743.4	744.8	746.4	748.0
137.5°	766.5	768.3	770.1	771.9	773.7	775.3	776.9	778.5	780.2	781.7	783.4
140°	790.8	792.1	793.5	794.7	796.3	798.0	799.8	801.5	803.3	804.8	806.2
142.5°	811.5	812.7	813.9	815.0	816.6	818.6	820.6	822.6	824.7	826.0	827.3
145°	842.8	842.7	842.5	842.4	843.6	846.4	849.1	851.8	854.5	855.8	856.9
147.5°	870.9	870.3	869.7	869.1	870.1	872.8	875.5	878.2	880.9	881.7	882.5
150°	888.9	887.8	886.7	885.4	886.3	888.8	891.3	893.9	896.5	897.5	898.4
152.5°	904.3	903.1	901.8	900.6	901.2	903.6	906.1	908.5	910.9	911.9	912.8
155°	926.9	925.3	923.9	922.5	922.7	924.6	926.6	928.5	930.4	931.4	932.4
157.5°	944.8	943.6	942.4	941.2	941.2	942.6	943.9	945.2	946.6	947.8	948.8
160°	955.4	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4	957.5	958.4
162.5°	964.7	963.8	962.8	961.8	961.8	962.6	963.4	964.3	965.1	966.2	967.2
165°	977.1	976.2	975.2	974.2	974.0	974.5	975.0	975.4	975.9	977.0	978.2
167.5°	986.4	985.4	984.5	983.5	983.2	983.7	984.1	984.6	985.0	986.1	987.3
170°	991.6	990.7	989.7	988.8	988.4	988.8	989.1	989.4	989.7	990.8	991.9
172.5°	995.0	994.1	993.1	992.2	991.9	992.2	992.5	992.8	993.1	994.3	995.4
175°	999.4	998.3	997.1	996.0	995.6	995.9	996.2	996.5	996.9	998.0	999.2
177.5°	1000.4	999.5	998.6	997.6	997.2	997.3	997.5	997.6	997.7	998.7	999.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1996.0	2003.0	2006.1	2006.1	2009.9	2008.3	2006.7
5°	2110.7	2123.4	2126.1	2138.2	2146.9	2144.1	2145.6
7.5°	2224.7	2245.2	2265.4	2274.7	2276.1	2281.5	2283.5
10°	2294.9	2311.7	2343.2	2338.4	2362.0	2375.3	2353.2
12.5°	2362.5	2385.1	2407.0	2413.0	2426.3	2430.5	2421.9
15°	2423.6	2435.7	2437.0	2433.7	2437.6	2434.3	2421.6
17.5°	2366.5	2346.9	2307.2	2288.5	2273.6	2251.7	2242.8
20°	2272.2	2214.5	2147.5	2120.7	2089.2	2027.6	2042.4
22.5°	2068.5	2002.8	1935.8	1857.5	1820.2	1761.7	1758.2
25°	1751.5	1638.3	1513.7	1426.5	1375.6	1317.4	1291.8
27.5°	1361.8	1219.2	1117.1	1065.4	1018.3	972.1	970.3
30°	1105.6	998.4	919.3	875.0	846.3	826.9	830.9
32.5°	931.9	858.5	805.2	768.4	747.1	732.5	732.3
35°	761.8	711.6	677.4	662.0	646.6	635.9	636.5
37.5°	652.0	621.8	602.8	585.7	576.1	570.9	567.9
40°	595.7	570.9	556.1	546.1	538.1	530.7	529.4
42.5°	551.2	530.7	515.9	508.1	500.5	495.3	493.9
45°	489.2	472.4	459.0	450.3	447.0	442.2	442.2
47.5°	435.2	418.7	408.2	402.7	397.0	393.8	393.7
50°	398.7	386.0	376.6	373.2	368.5	366.5	365.9
52.5°	366.0	356.5	349.8	347.5	345.5	343.0	343.4
55°	321.6	316.3	313.6	311.5	308.2	304.2	306.9
57.5°	284.3	279.6	272.5	266.1	263.1	260.2	261.4
60°	258.0	248.6	239.2	231.9	229.8	223.8	223.8
62.5°	224.7	211.6	200.1	195.9	193.9	191.1	190.6
65°	172.9	167.5	164.8	162.2	160.8	160.8	159.5
67.5°	143.3	141.1	138.1	137.5	136.1	135.7	135.3
70°	126.6	123.9	122.6	122.0	120.6	121.3	119.3
72.5°	110.6	108.5	108.2	106.4	105.6	105.7	104.2
75°	87.2	87.2	86.4	85.7	84.4	83.7	84.4
77.5°	67.1	67.2	65.9	65.8	65.6	65.8	65.1
80°	53.6	54.2	53.6	52.9	52.3	52.9	52.3
82.5°	42.3	41.4	41.3	41.1	41.0	40.6	40.5
85°	24.1	24.7	24.1	23.4	23.4	23.4	24.1
87.5°	12.5	12.6	12.7	12.8	12.9	12.9	12.5
90°	16.9	17.7	18.2	18.6	18.9	19.2	19.5
92.5°	18.0	18.4	18.8	18.9	19.1	19.3	19.5
95°	30.6	31.4	31.7	31.5	31.4	31.2	31.1
97.5°	39.6	40.3	40.7	40.9	41.1	41.3	41.5
100°	45.0	46.4	47.2	47.5	47.8	48.1	48.4
102.5°	47.4	49.0	50.1	50.5	51.0	51.4	51.9
105°	49.4	51.1	52.3	53.0	53.6	54.2	54.9
107.5°	56.2	54.5	53.9	54.5	55.2	55.8	56.5
110°	78.3	62.2	54.5	55.1	55.7	56.5	57.1



TEST NUMBER: P331717-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	143.2	84.6	55.5	56.1	56.7	57.2	57.7
115°	222.8	148.5	105.4	93.9	82.3	70.8	59.3
117.5°	439.7	421.7	393.7	355.8	317.8	279.8	241.9
120°	535.3	537.2	527.4	505.6	484.0	462.3	440.7
122.5°	567.0	568.3	566.7	562.5	558.3	554.1	549.9
125°	613.8	614.9	615.7	616.2	616.7	617.1	617.6
127.5°	657.5	659.1	660.0	660.1	660.2	660.4	660.5
130°	685.1	686.8	687.6	687.5	687.3	687.1	687.0
132.5°	711.4	713.0	713.7	713.5	713.4	713.2	713.0
135°	749.6	751.2	751.8	751.5	751.2	750.8	750.5
137.5°	784.9	786.5	787.0	786.5	785.9	785.4	784.8
140°	807.6	809.1	809.4	808.6	807.8	807.0	806.2
142.5°	828.6	829.9	830.2	829.4	828.6	827.8	827.0
145°	858.0	859.1	859.2	858.5	857.7	856.9	856.1
147.5°	883.4	884.2	884.3	883.6	882.9	882.3	881.6
150°	899.4	900.3	900.4	899.6	898.8	898.0	897.2
152.5°	913.8	914.8	914.7	913.7	912.6	911.6	910.5
155°	933.3	934.3	934.1	932.8	931.6	930.3	929.0
157.5°	949.9	951.0	950.9	949.7	948.4	947.2	945.9
160°	959.4	960.3	960.2	959.1	958.0	956.8	955.7
162.5°	968.4	969.5	969.4	968.0	966.5	965.2	963.8
165°	979.4	980.5	980.5	979.4	978.2	977.0	975.9
167.5°	988.5	989.6	989.4	988.0	986.5	985.0	983.6
170°	993.0	994.2	994.0	992.6	991.1	989.7	988.3
172.5°	996.5	997.6	997.4	996.0	994.6	993.1	991.7
175°	1000.3	1001.4	1001.2	999.6	997.9	996.3	994.7
177.5°	1000.5	1001.4	1001.3	1000.1	999.0	997.7	996.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4

(END OF REPORT)