

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331721-840

Luminaire Tested: **SA2XXRDIP-C865D725U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331721-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C865D725U840-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5664.7 lumens  
Efficiency: N/A  
Efficacy: 104.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331721-840  
CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331721-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	63	58	60	55	51	51	47	44	43	40	38	34
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	39	36	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26	23
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	23909	23909	23909
5°	24000	23608	23738
10°	23815	23222	23023
15°	23542	22534	21884
20°	23163	21551	20469
25°	22775	20436	19099
30°	22236	19287	17339
35°	21711	18039	15794
40°	21182	16750	14010
45°	20562	15299	12392
50°	19926	13835	10803
55°	19277	12262	9278
60°	18519	10601	7702
65°	17662	8909	7014
70°	16636	7336	6449
75°	15384	6687	6014
80°	13575	5979	5486
85°	10689	4705	4705



TEST NUMBER: P331721-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.6	2.4
10°-20°	380.6	6.7
20°-30°	534.4	9.4
30°-40°	582.7	10.3
40°-50°	535.8	9.5
50°-60°	420.8	7.4
60°-70°	274.4	4.8
70°-80°	141.5	2.5
80°-90°	40.4	0.7
90°-100°	59.3	1.0
100°-110°	184.1	3.2
110°-120°	314.7	5.6
120°-130°	413.8	7.3
130°-140°	464.4	8.2
140°-150°	455.4	8.0
150°-160°	382.0	6.7
160°-170°	253.3	4.5
170°-180°	88.5	1.6
0°-30°	1053.6	18.6
0°-40°	1636.3	28.9
0°-60°	2593.0	45.8
0°-90°	3049.2	53.8
90°-120°	558.0	9.9
90°-150°	1891.7	33.4
90°-180°	2616.0	46.2
0°-180°	5664.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1481	1481	1481	1481	1481	
5°	1481	1473	1457	1468	1465	140
15°	1408	1392	1348	1323	1309	397
25°	1278	1233	1147	1094	1072	588
35°	1102	1030	915	834	801	689
45°	900	808	670	578	543	695
55°	685	578	436	358	330	612
65°	462	353	233	190	184	458
75°	247	155	107	98	96	261
85°	58	31	25	25	25	68
90°	1	11	28	26	27	5
95°	41	49	50	50	49	47
105°	170	172	174	175	175	179
115°	316	320	319	318	316	312
125°	459	466	464	462	461	410
135°	594	603	605	604	602	459
145°	721	727	732	732	729	451
155°	825	827	830	833	831	380
165°	898	897	897	902	898	253
175°	934	932	930	935	931	89
180°	935	935	935	935	935	



TEST NUMBER: P331721-840  
 CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8
2.5°	1486.1	1484.9	1483.7	1482.5	1481.4	1479.5	1476.8	1474.2	1471.6	1468.9	1471.4
5°	1480.8	1479.3	1477.7	1476.2	1474.8	1472.1	1468.2	1464.4	1460.5	1456.6	1459.3
7.5°	1465.4	1463.6	1461.8	1460.0	1458.0	1454.9	1450.4	1445.8	1441.3	1436.7	1437.5
10°	1452.6	1450.5	1448.4	1446.3	1444.2	1440.3	1434.3	1428.4	1422.4	1416.4	1415.5
12.5°	1436.5	1433.9	1431.4	1428.9	1426.2	1421.2	1413.5	1405.9	1398.3	1390.7	1389.1
15°	1408.4	1405.1	1401.8	1398.6	1395.2	1388.6	1378.5	1368.4	1358.2	1348.1	1342.4
17.5°	1373.8	1368.8	1363.8	1358.8	1353.8	1344.8	1331.8	1318.8	1305.9	1292.8	1286.2
20°	1348.1	1342.1	1336.2	1330.2	1324.2	1313.8	1298.9	1284.0	1269.2	1254.3	1246.8
22.5°	1320.2	1313.5	1306.9	1300.2	1293.5	1281.8	1265.0	1248.2	1231.4	1214.6	1205.0
25°	1278.4	1268.9	1259.3	1249.8	1240.3	1225.7	1206.0	1186.4	1166.7	1147.1	1134.9
27.5°	1228.0	1217.6	1207.3	1196.9	1186.6	1170.3	1148.1	1126.0	1103.8	1081.7	1067.4
30°	1192.7	1181.3	1170.0	1158.7	1147.4	1129.8	1106.0	1082.2	1058.3	1034.5	1019.4
32.5°	1158.3	1145.1	1131.9	1118.6	1105.4	1086.7	1062.4	1038.0	1013.8	989.5	972.2
35°	1101.5	1086.3	1071.2	1055.9	1040.8	1020.1	993.8	967.7	941.5	915.2	896.5
37.5°	1044.7	1028.0	1011.4	994.6	978.0	955.6	927.8	899.8	871.9	843.9	823.2
40°	1005.0	987.1	969.3	951.4	933.5	910.2	881.3	852.4	823.5	794.7	773.5
42.5°	964.3	945.4	926.7	907.9	889.0	864.6	834.9	805.0	775.2	745.3	723.5
45°	900.5	880.5	860.6	840.6	820.7	795.1	763.9	732.6	701.3	670.0	648.8
47.5°	838.3	817.2	796.1	774.9	753.8	727.0	694.8	662.5	630.2	597.9	576.9
50°	793.3	772.1	751.0	729.8	708.7	681.8	649.0	616.2	583.5	550.8	530.2
52.5°	749.3	727.2	705.2	683.1	661.0	633.9	601.9	569.8	537.8	505.7	485.8
55°	684.8	661.6	638.3	615.1	591.9	564.1	532.0	499.8	467.7	435.6	417.7
57.5°	618.5	594.7	570.9	547.0	523.3	495.9	464.9	434.0	403.1	372.2	355.9
60°	573.5	549.7	525.9	502.1	478.3	451.0	420.3	389.6	359.0	328.3	313.2
62.5°	529.6	505.7	481.9	458.1	434.2	407.8	378.5	349.3	320.0	290.7	276.3
65°	462.3	438.2	414.0	389.9	365.9	340.3	313.6	286.8	259.9	233.2	223.1
67.5°	397.5	373.5	349.6	325.6	301.6	277.6	253.6	229.4	205.3	181.2	176.5
70°	352.4	329.2	306.0	282.8	259.5	237.6	217.1	196.5	176.0	155.4	152.5
72.5°	309.5	287.3	265.0	242.8	220.5	201.1	184.6	168.0	151.6	135.1	132.6
75°	246.6	225.7	204.9	184.0	163.2	147.7	137.5	127.4	117.3	107.2	105.1
77.5°	184.7	166.3	148.0	129.8	111.5	100.0	95.0	90.2	85.3	80.4	79.2
80°	146.0	130.9	115.7	100.5	85.3	76.2	73.2	70.3	67.3	64.3	63.1
82.5°	110.7	98.9	86.9	75.1	63.3	56.4	54.3	52.3	50.3	48.3	47.6
85°	57.7	51.4	45.1	38.9	32.6	29.1	28.2	27.3	26.4	25.4	25.4
87.5°	17.3	15.9	14.3	12.8	11.4	11.0	11.8	12.5	13.3	14.1	13.8
90°	0.8	2.9	5.0	7.1	9.2	12.2	16.1	19.9	23.7	27.7	27.3
92.5°	14.0	15.6	17.2	18.7	20.2	21.4	22.3	23.2	24.2	25.1	25.1
95°	41.0	42.8	44.5	46.4	48.1	49.1	49.5	49.8	50.2	50.5	50.5
97.5°	75.0	76.5	78.1	79.6	81.2	82.3	82.9	83.6	84.2	84.9	84.9
100°	100.3	101.7	103.0	104.4	105.8	106.8	107.3	107.9	108.4	109.0	109.0
102.5°	126.7	127.8	129.1	130.2	131.3	132.2	132.8	133.5	134.1	134.8	134.9
105°	169.8	170.3	170.8	171.3	171.8	172.3	172.6	173.0	173.3	173.7	174.0
107.5°	213.0	213.8	214.5	215.3	216.0	216.4	216.4	216.4	216.4	216.4	216.6
110°	240.8	241.8	242.9	243.9	245.0	245.5	245.5	245.5	245.5	245.5	245.5



TEST NUMBER: P331721-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.0	272.2	273.2	274.2	275.3	275.7	275.6	275.5	275.3	275.2	274.8
115°	315.8	316.8	317.8	318.9	319.9	320.3	319.9	319.6	319.2	318.9	318.7
117.5°	360.2	361.6	363.0	364.5	365.9	366.1	365.1	364.2	363.1	362.1	361.7
120°	389.9	391.3	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9	389.9
122.5°	417.1	418.8	420.5	422.1	423.8	424.1	423.2	422.2	421.2	420.2	419.8
125°	459.4	461.0	462.5	464.1	465.7	466.3	465.7	465.1	464.6	464.1	463.6
127.5°	500.6	502.6	504.6	506.6	508.6	509.3	508.7	508.1	507.4	506.8	506.1
130°	526.5	528.8	531.1	533.3	535.6	536.5	536.2	535.8	535.5	535.2	534.8
132.5°	555.5	557.4	559.3	561.1	563.0	563.9	564.0	564.1	564.1	564.2	563.5
135°	594.4	596.3	598.2	600.2	602.1	603.2	603.6	603.9	604.3	604.6	604.5
137.5°	635.3	636.8	638.4	640.1	641.6	642.6	643.1	643.5	644.0	644.4	644.3
140°	659.9	661.5	663.1	664.6	666.2	667.4	668.3	669.2	670.0	671.0	671.0
142.5°	685.2	686.7	688.3	689.9	691.5	692.6	693.2	693.8	694.4	695.0	695.1
145°	721.4	722.7	724.0	725.2	726.4	727.5	728.6	729.6	730.6	731.7	732.0
147.5°	753.9	755.3	756.8	758.2	759.7	760.8	761.5	762.2	763.0	763.7	764.0
150°	776.0	777.0	778.0	779.1	780.1	781.0	781.7	782.4	783.2	783.9	784.4
152.5°	795.5	796.6	797.6	798.7	799.7	800.6	801.5	802.3	803.1	804.1	804.7
155°	824.9	825.4	826.0	826.5	827.0	827.5	828.0	828.6	829.1	829.6	830.5
157.5°	850.0	850.3	850.7	851.0	851.4	851.7	852.0	852.3	852.6	852.9	854.1
160°	865.2	865.5	865.9	866.2	866.6	866.8	867.0	867.2	867.4	867.5	868.6
162.5°	879.0	879.1	879.2	879.2	879.3	879.4	879.6	879.8	880.0	880.1	881.3
165°	897.5	897.4	897.2	897.0	896.8	896.7	896.7	896.7	896.7	896.7	898.0
167.5°	912.9	912.4	911.9	911.4	910.9	910.6	910.6	910.5	910.5	910.4	911.7
170°	921.2	920.7	920.1	919.6	919.1	918.7	918.6	918.4	918.2	918.0	919.3
172.5°	926.9	926.3	925.8	925.2	924.7	924.4	924.2	924.0	923.9	923.7	924.9
175°	933.8	933.3	932.7	932.2	931.7	931.3	930.9	930.6	930.2	929.9	931.1
177.5°	936.6	936.2	935.8	935.3	934.9	934.6	934.3	934.0	933.7	933.5	934.3
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331721-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8
2.5°	1473.7	1476.1	1478.4	1479.5	1478.9	1478.4	1478.0	1477.5
5°	1462.0	1464.6	1467.3	1468.2	1467.3	1466.4	1465.5	1464.6
7.5°	1438.4	1439.1	1439.9	1439.5	1437.9	1436.4	1434.8	1433.3
10°	1414.6	1413.7	1412.8	1411.5	1409.7	1408.0	1406.1	1404.3
12.5°	1387.5	1385.8	1384.2	1382.0	1379.0	1376.0	1373.0	1370.1
15°	1336.8	1331.1	1325.4	1321.1	1318.2	1315.1	1312.2	1309.2
17.5°	1279.4	1272.6	1266.0	1260.0	1254.9	1249.8	1244.7	1239.5
20°	1239.4	1231.9	1224.5	1217.5	1210.9	1204.4	1197.8	1191.3
22.5°	1195.5	1185.9	1176.3	1169.0	1164.2	1159.2	1154.4	1149.5
25°	1122.7	1110.4	1098.2	1089.8	1085.4	1081.0	1076.5	1072.1
27.5°	1053.2	1038.9	1024.7	1014.1	1007.0	999.9	992.8	985.7
30°	1004.1	989.0	973.7	962.1	954.1	946.0	938.1	930.0
32.5°	954.8	937.5	920.2	907.7	900.2	892.6	885.0	877.5
35°	877.7	859.0	840.2	827.6	821.0	814.5	807.9	801.3
37.5°	802.6	781.9	761.3	747.2	739.7	732.2	724.7	717.2
40°	752.3	731.2	710.0	695.6	687.9	680.1	672.4	664.7
42.5°	701.7	679.7	657.9	643.2	635.7	628.2	620.7	613.2
45°	627.7	606.6	585.4	571.3	564.1	557.0	549.9	542.7
47.5°	555.8	534.8	513.8	500.1	493.6	487.1	480.6	474.1
50°	509.7	489.1	468.6	455.1	448.9	442.6	436.4	430.1
52.5°	466.1	446.3	426.4	413.6	407.8	402.0	396.3	390.5
55°	399.8	381.9	364.1	352.2	346.6	340.9	335.3	329.6
57.5°	339.5	323.2	306.8	296.2	291.4	286.6	281.9	277.1
60°	297.9	282.8	267.5	257.6	252.8	248.0	243.3	238.5
62.5°	261.9	247.4	232.9	224.2	221.4	218.5	215.6	212.8
65°	212.9	202.8	192.7	187.1	186.2	185.4	184.5	183.6
67.5°	171.9	167.2	162.6	159.8	158.9	157.8	156.9	156.0
70°	149.5	146.5	143.5	141.5	140.3	139.1	137.8	136.6
72.5°	130.1	127.5	125.0	123.5	122.7	122.0	121.3	120.6
75°	103.0	101.0	98.9	97.7	97.4	97.0	96.7	96.4
77.5°	78.1	76.9	75.6	74.8	74.3	73.8	73.4	72.9
80°	61.9	60.8	59.6	59.0	59.0	59.0	59.0	59.0
82.5°	46.9	46.0	45.3	45.0	45.0	45.0	45.0	45.0
85°	25.4	25.4	25.4	25.4	25.4	25.4	25.4	25.4
87.5°	13.5	13.1	12.8	12.7	12.7	12.8	12.8	12.8
90°	27.0	26.6	26.3	26.2	26.4	26.5	26.7	26.9
92.5°	25.2	25.3	25.3	25.4	25.4	25.5	25.5	25.5
95°	50.5	50.5	50.5	50.4	50.0	49.7	49.3	49.0
97.5°	84.9	84.9	84.9	84.9	84.9	84.8	84.8	84.7
100°	109.0	109.0	109.0	108.9	108.7	108.5	108.4	108.2
102.5°	135.1	135.2	135.4	135.3	135.2	135.0	134.8	134.6
105°	174.4	174.7	175.1	175.2	175.2	175.2	175.2	175.2
107.5°	216.7	216.8	217.0	216.7	215.9	215.1	214.3	213.5
110°	245.5	245.5	245.5	245.2	244.7	244.2	243.7	243.1





TEST NUMBER: P331721-840

CATALOG NUMBER: SA2XXRDIP-C865D725U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	274.3	273.9	273.5	273.1	272.7	272.3	272.0	271.6
115°	318.5	318.4	318.2	317.8	317.3	316.8	316.3	315.8
117.5°	361.3	360.9	360.4	360.0	359.5	358.9	358.4	357.9
120°	389.9	389.9	389.9	389.7	389.1	388.6	388.1	387.6
122.5°	419.4	419.0	418.6	418.2	417.8	417.4	417.0	416.7
125°	463.1	462.5	462.0	461.7	461.5	461.3	461.2	461.0
127.5°	505.5	504.8	504.2	503.6	503.1	502.5	502.0	501.4
130°	534.5	534.1	533.8	533.2	532.5	531.9	531.2	530.5
132.5°	562.7	561.9	561.2	560.5	559.9	559.4	558.8	558.3
135°	604.3	604.1	603.9	603.6	603.1	602.6	602.0	601.5
137.5°	644.2	644.0	643.9	643.5	642.8	642.1	641.4	640.7
140°	671.0	671.0	671.0	670.6	669.9	669.2	668.5	667.8
142.5°	695.2	695.4	695.5	695.2	694.5	693.8	693.2	692.5
145°	732.1	732.3	732.5	732.2	731.4	730.7	730.0	729.3
147.5°	764.4	764.8	765.2	765.1	764.4	763.7	763.1	762.3
150°	784.9	785.4	786.0	786.0	785.4	784.9	784.4	783.9
152.5°	805.4	806.1	806.7	806.7	806.1	805.4	804.7	804.1
155°	831.3	832.2	833.1	833.3	832.7	832.2	831.7	831.2
157.5°	855.4	856.6	857.8	857.9	857.1	856.3	855.4	854.5
160°	869.6	870.7	871.7	871.9	871.2	870.5	869.8	869.1
162.5°	882.5	883.7	884.9	885.0	884.2	883.4	882.5	881.7
165°	899.2	900.4	901.6	901.8	900.9	900.0	899.2	898.3
167.5°	912.9	914.1	915.3	915.5	914.6	913.7	912.8	911.9
170°	920.5	921.7	922.9	923.0	922.0	920.9	919.9	918.8
172.5°	926.1	927.4	928.6	928.7	927.7	926.6	925.5	924.5
175°	932.3	933.5	934.7	934.8	933.8	932.7	931.7	930.7
177.5°	935.1	936.0	936.9	936.9	936.0	935.1	934.3	933.5
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3

(END OF REPORT)