

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332995-830

Luminaire Tested: **SA4XXRDIP-C1195D590U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332995-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D590U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6471.9 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332995-830

CATALOG NUMBER: SA4XXRDIP-C1195D590U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332995-830

CATALOG NUMBER: SA4XXRDIP-C1195D590U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70				
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60				
2	94	86	80	75	89	82	77	72	74	69	66	66	63	60	59	57	54	51				
3	86	76	69	63	81	73	66	61	65	60	56	59	55	51	53	49	47	43				
4	79	68	60	54	74	65	57	52	58	53	48	53	48	44	47	44	41	38				
5	73	61	52	46	68	58	50	45	52	46	42	47	42	39	43	39	36	33				
6	67	55	46	41	63	52	45	39	48	41	37	43	38	34	39	35	31	29				
7	62	50	42	36	59	47	40	35	43	37	32	39	34	30	36	31	28	26				
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25	23				
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	30	26	23	21				
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15868	15868	15868
5°	15904	15709	15807
10°	15805	15521	15521
15°	15623	15195	15082
20°	15374	14766	14495
25°	15055	14264	13903
30°	14746	13736	13160
35°	14402	13186	12415
40°	13990	12562	11610
45°	13609	11942	10791
50°	13175	11228	9923
55°	12711	10486	8981
60°	12198	9671	8018
65°	11731	8653	7072
70°	11049	7532	6005
75°	10187	6245	4885
80°	8884	4761	4477
85°	7521	4326	4039



TEST NUMBER: P332995-830

CATALOG NUMBER: SA4XXRDIP-C1195D590U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.6	2.9
10°-20°	514.9	8.0
20°-30°	743.5	11.5
30°-40°	842.8	13.0
40°-50°	813.8	12.6
50°-60°	676.7	10.5
60°-70°	467.3	7.2
70°-80°	236.9	3.7
80°-90°	62.8	1.0
90°-100°	45.8	0.7
100°-110°	135.8	2.1
110°-120°	230.5	3.6
120°-130°	304.0	4.7
130°-140°	341.4	5.3
140°-150°	335.4	5.2
150°-160°	282.1	4.4
160°-170°	187.7	2.9
170°-180°	65.7	1.0
0°-30°	1443.1	22.3
0°-40°	2285.8	35.3
0°-60°	3776.4	58.4
0°-90°	4543.5	70.2
90°-120°	412.2	6.4
90°-150°	1392.9	21.5
90°-180°	1928.0	29.8
0°-180°	6471.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1966	1966	1966	1966	1966	
5°	1963	1956	1938	1953	1951	186
15°	1869	1854	1818	1815	1805	526
25°	1690	1661	1601	1576	1561	778
35°	1461	1412	1338	1288	1260	913
45°	1192	1134	1046	975	945	919
55°	903	841	745	669	638	807
65°	614	548	453	391	370	606
75°	327	270	200	167	157	345
85°	81	53	47	44	44	91
90°	2	7	12	15	16	6
95°	32	37	41	42	42	36
105°	125	126	128	130	131	133
115°	234	234	233	233	232	231
125°	341	341	341	340	339	304
135°	440	443	444	442	441	340
145°	535	537	538	537	536	335
155°	613	613	612	614	612	282
165°	667	666	664	667	666	188
175°	694	691	691	694	691	66
180°	695	695	695	695	695	



TEST NUMBER: P332995-830

CATALOG NUMBER: SA4XXRDIP-C1195D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1970.4	1969.3	1968.3	1967.2	1966.1	1964.2	1961.2	1958.2	1955.3	1952.4	1955.3
5°	1962.6	1961.2	1959.9	1958.6	1957.3	1954.6	1950.6	1946.5	1942.6	1938.5	1941.8
7.5°	1944.8	1943.4	1942.0	1940.6	1939.2	1935.9	1930.7	1925.5	1920.2	1915.1	1917.2
10°	1928.0	1926.3	1924.7	1923.0	1921.3	1917.4	1911.5	1905.4	1899.4	1893.4	1894.7
12.5°	1906.3	1904.4	1902.4	1900.4	1898.6	1894.0	1887.0	1879.9	1872.7	1865.7	1866.5
15°	1869.3	1866.2	1863.3	1860.3	1857.3	1851.5	1843.2	1834.8	1826.5	1818.1	1817.4
17.5°	1824.5	1820.0	1815.7	1811.4	1807.0	1799.9	1789.8	1779.8	1769.7	1759.7	1757.8
20°	1789.5	1785.2	1780.8	1776.5	1772.2	1764.3	1752.9	1741.5	1730.1	1718.8	1716.1
22.5°	1751.0	1746.2	1741.3	1736.4	1731.5	1723.0	1710.7	1698.6	1686.4	1674.2	1670.2
25°	1690.2	1684.1	1678.1	1672.2	1666.1	1656.2	1642.6	1628.8	1615.1	1601.4	1595.7
27.5°	1626.4	1618.8	1611.3	1603.7	1596.1	1585.1	1570.4	1555.8	1541.1	1526.4	1519.4
30°	1581.9	1573.5	1565.1	1556.7	1548.4	1536.3	1520.6	1504.9	1489.2	1473.5	1465.1
32.5°	1534.8	1525.4	1516.0	1506.6	1497.1	1484.3	1468.0	1451.8	1435.5	1419.3	1409.6
35°	1461.4	1450.7	1440.0	1429.3	1418.6	1404.9	1388.2	1371.5	1354.7	1338.0	1326.6
37.5°	1382.9	1371.8	1360.7	1349.7	1338.7	1323.9	1305.4	1286.9	1268.4	1249.8	1237.1
40°	1327.5	1316.4	1305.4	1294.4	1283.3	1268.3	1249.2	1230.1	1211.1	1192.0	1178.0
42.5°	1274.5	1262.9	1251.3	1239.7	1228.2	1212.5	1192.6	1172.7	1152.9	1133.0	1118.7
45°	1192.0	1179.6	1167.2	1154.9	1142.6	1126.2	1106.3	1086.2	1066.1	1046.0	1029.6
47.5°	1106.8	1094.0	1081.3	1068.5	1055.7	1038.9	1018.0	997.1	976.3	955.5	938.4
50°	1049.0	1035.9	1022.9	1009.9	996.8	979.6	958.2	936.8	915.4	894.0	877.3
52.5°	990.0	977.2	964.5	951.7	939.0	921.5	899.7	877.7	855.7	833.8	816.8
55°	903.1	889.7	876.3	862.9	849.5	832.0	810.2	788.5	766.8	745.0	727.6
57.5°	816.9	803.0	789.1	775.2	761.3	743.7	722.3	700.8	679.4	658.0	640.4
60°	755.5	742.2	728.8	715.4	702.0	684.7	663.3	641.9	620.4	599.0	581.6
62.5°	700.1	686.3	672.3	658.5	644.5	626.6	604.6	582.7	560.7	538.9	522.7
65°	614.1	599.6	585.3	570.9	556.6	538.7	517.3	495.9	474.5	453.0	438.7
67.5°	524.6	510.9	497.1	483.3	469.6	452.7	432.8	413.0	393.1	373.2	360.9
70°	468.1	454.0	440.0	425.9	411.9	395.3	376.3	357.2	338.2	319.1	308.0
72.5°	407.8	395.2	382.5	369.8	357.0	341.7	323.7	305.7	287.7	269.7	260.2
75°	326.6	314.2	301.8	289.5	277.1	263.1	247.3	231.6	215.9	200.2	192.5
77.5°	244.1	233.7	223.1	212.6	202.1	190.5	177.8	165.1	152.4	139.7	135.2
80°	191.1	181.4	171.7	162.0	152.3	142.5	132.4	122.4	112.4	102.4	101.3
82.5°	145.4	136.5	127.6	118.7	109.8	102.5	96.7	91.0	85.2	79.5	78.7
85°	81.2	74.6	67.9	61.2	54.5	50.7	49.7	48.6	47.7	46.7	46.0
87.5°	28.0	26.1	24.2	22.3	20.5	19.5	19.4	19.4	19.3	19.2	19.1
90°	1.6	2.9	4.2	5.6	6.9	8.0	9.0	9.9	10.8	11.8	12.5
92.5°	11.5	13.0	14.5	16.0	17.5	18.6	19.3	20.0	20.6	21.3	21.7
95°	32.2	33.4	34.4	35.4	36.6	37.5	38.4	39.2	40.1	40.8	41.2
97.5°	56.4	57.2	58.1	58.9	59.8	60.7	61.6	62.7	63.6	64.7	65.0
100°	75.2	75.8	76.3	76.7	77.2	77.9	79.0	80.1	81.2	82.3	82.5
102.5°	95.0	95.2	95.4	95.6	95.8	96.4	97.4	98.3	99.3	100.3	100.7
105°	125.3	125.4	125.5	125.6	125.7	126.0	126.5	127.0	127.4	127.9	128.3
107.5°	156.9	157.1	157.2	157.4	157.6	157.7	157.7	157.8	157.9	158.0	158.3
110°	178.5	178.7	179.0	179.2	179.5	179.5	179.4	179.3	179.2	179.0	178.8



TEST NUMBER: P332995-830

CATALOG NUMBER: SA4XXRDIP-C1195D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	200.9	200.9	201.0	201.0	201.0	201.0	200.8	200.5	200.3	200.1	200.0
115°	234.4	234.4	234.4	234.4	234.4	234.2	234.0	233.8	233.6	233.3	233.2
117.5°	266.0	266.1	266.2	266.3	266.4	266.4	266.2	266.0	265.8	265.7	265.2
120°	287.1	287.6	288.0	288.5	289.0	289.1	288.7	288.3	287.9	287.6	287.0
122.5°	309.0	309.2	309.3	309.5	309.7	309.8	309.6	309.4	309.2	309.2	308.7
125°	341.4	341.4	341.4	341.4	341.4	341.3	341.2	341.1	340.9	340.8	340.5
127.5°	370.7	371.1	371.5	371.8	372.1	372.2	372.0	371.8	371.6	371.5	371.3
130°	391.3	391.7	392.1	392.5	392.8	392.9	392.9	392.9	392.9	392.9	392.8
132.5°	412.5	412.7	412.9	413.2	413.5	413.6	413.5	413.4	413.3	413.2	412.9
135°	440.3	441.0	441.7	442.4	443.2	443.5	443.5	443.5	443.5	443.5	443.3
137.5°	470.6	470.9	471.3	471.6	471.9	472.2	472.4	472.6	472.8	473.0	472.7
140°	490.8	491.1	491.3	491.5	491.7	491.9	491.9	491.9	491.9	491.9	491.7
142.5°	509.3	509.5	509.8	510.0	510.3	510.3	510.2	510.1	510.0	509.9	509.9
145°	534.9	535.4	535.8	536.3	536.8	537.1	537.2	537.3	537.4	537.5	537.4
147.5°	560.2	560.8	561.4	561.9	562.6	562.8	562.7	562.6	562.5	562.4	562.3
150°	575.7	576.3	576.7	577.2	577.7	577.9	577.9	577.9	577.9	577.9	577.9
152.5°	590.4	590.7	591.0	591.3	591.5	591.7	591.8	591.9	592.0	592.1	592.4
155°	612.8	612.8	612.8	612.8	612.8	612.7	612.7	612.6	612.5	612.3	612.7
157.5°	631.8	631.5	631.3	631.1	630.9	630.7	630.7	630.7	630.7	630.7	631.0
160°	642.9	642.8	642.7	642.6	642.4	642.3	642.2	642.2	642.0	641.9	642.2
162.5°	653.3	653.0	652.6	652.3	652.1	651.8	651.7	651.6	651.5	651.3	652.0
165°	667.1	666.8	666.4	666.1	665.7	665.4	665.2	665.0	664.7	664.5	665.2
167.5°	677.8	677.3	676.7	676.3	675.8	675.5	675.5	675.6	675.6	675.6	676.4
170°	683.8	683.2	682.6	682.0	681.4	681.2	681.3	681.4	681.6	681.6	682.4
172.5°	688.1	687.6	687.1	686.6	686.1	685.9	685.9	685.9	685.9	686.0	686.7
175°	694.0	693.4	692.9	692.2	691.6	691.3	691.2	691.1	690.9	690.8	691.6
177.5°	696.0	695.5	695.0	694.6	694.0	693.8	693.8	693.8	693.8	693.8	694.5
180°	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1



TEST NUMBER: P332995-830

CATALOG NUMBER: SA4XXRDIP-C1195D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1958.2	1961.2	1964.2	1965.5	1965.2	1964.9	1964.6	1964.4
5°	1945.2	1948.5	1951.9	1953.2	1952.6	1951.9	1951.3	1950.6
7.5°	1919.3	1921.5	1923.6	1924.1	1923.1	1922.0	1920.9	1919.9
10°	1896.0	1897.3	1898.8	1898.8	1897.3	1896.0	1894.7	1893.4
12.5°	1867.3	1868.1	1868.9	1868.3	1866.5	1864.6	1862.7	1860.9
15°	1816.8	1816.1	1815.4	1813.9	1811.6	1809.2	1806.9	1804.6
17.5°	1756.0	1754.1	1752.2	1749.5	1746.0	1742.4	1738.9	1735.3
20°	1713.4	1710.7	1708.1	1704.6	1700.3	1695.9	1691.5	1687.2
22.5°	1666.2	1662.2	1658.2	1654.4	1650.9	1647.3	1643.8	1640.2
25°	1590.0	1584.3	1578.7	1574.1	1570.7	1567.4	1564.1	1560.8
27.5°	1512.4	1505.3	1498.4	1492.4	1487.6	1482.8	1478.0	1473.2
30°	1456.7	1448.4	1440.0	1433.1	1427.8	1422.5	1417.1	1411.7
32.5°	1399.9	1390.2	1380.4	1373.1	1368.0	1362.9	1357.8	1352.7
35°	1315.2	1303.9	1292.5	1283.8	1277.8	1271.8	1265.7	1259.7
37.5°	1224.4	1211.6	1199.0	1189.6	1183.6	1177.5	1171.6	1165.5
40°	1163.9	1149.9	1135.9	1125.8	1119.7	1113.7	1107.8	1101.7
42.5°	1104.4	1090.1	1075.7	1065.5	1059.1	1052.9	1046.6	1040.3
45°	1013.2	996.8	980.4	969.2	963.3	957.2	951.2	945.2
47.5°	921.4	904.5	887.5	875.6	869.0	862.4	855.7	849.1
50°	860.5	843.9	827.1	815.6	809.3	802.9	796.5	790.1
52.5°	799.8	782.9	765.8	754.0	747.4	740.8	734.1	727.5
55°	710.2	692.9	675.4	663.5	657.2	650.8	644.5	638.1
57.5°	622.7	605.0	587.4	576.2	571.4	566.5	561.7	556.9
60°	564.2	546.9	529.4	518.1	512.7	507.4	502.0	496.6
62.5°	506.7	490.7	474.6	464.4	460.1	455.9	451.6	447.3
65°	424.2	409.9	395.5	386.3	382.3	378.2	374.3	370.2
67.5°	348.6	336.1	323.8	315.4	310.9	306.5	302.1	297.7
70°	297.0	286.0	274.9	267.8	264.4	261.1	257.7	254.4
72.5°	250.8	241.4	232.0	225.7	222.6	219.6	216.5	213.4
75°	184.8	177.1	169.4	164.6	162.6	160.5	158.5	156.6
77.5°	130.7	126.2	121.8	119.2	118.6	118.0	117.4	116.8
80°	100.4	99.3	98.3	97.6	97.4	97.0	96.7	96.3
82.5°	78.0	77.3	76.5	76.0	75.7	75.3	75.0	74.6
85°	45.3	44.7	44.0	43.6	43.6	43.6	43.6	43.6
87.5°	18.9	18.9	18.8	18.9	19.1	19.4	19.8	20.1
90°	13.3	13.9	14.7	15.2	15.5	15.6	15.9	16.1
92.5°	22.1	22.6	23.0	23.3	23.5	23.6	23.8	23.8
95°	41.6	41.9	42.3	42.5	42.5	42.5	42.5	42.5
97.5°	65.5	65.9	66.4	66.5	66.5	66.5	66.5	66.5
100°	82.8	82.9	83.2	83.3	83.3	83.3	83.3	83.3
102.5°	100.9	101.3	101.6	101.9	102.0	102.1	102.2	102.3
105°	128.7	129.0	129.4	129.7	130.1	130.4	130.8	131.2
107.5°	158.6	158.9	159.3	159.5	159.4	159.4	159.4	159.4
110°	178.5	178.3	178.0	178.1	178.5	178.8	179.2	179.6



TEST NUMBER: P332995-830

CATALOG NUMBER: SA4XXRDIP-C1195D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	200.0	199.9	199.9	199.9	200.0	200.0	200.1	200.2
115°	233.1	233.0	232.8	232.7	232.6	232.4	232.3	232.2
117.5°	264.9	264.5	264.0	263.7	263.4	263.3	263.0	262.8
120°	286.4	285.8	285.2	285.0	285.3	285.5	285.8	286.0
122.5°	308.3	307.9	307.5	307.1	306.6	306.2	305.8	305.4
125°	340.4	340.1	339.9	339.6	339.4	339.1	338.9	338.7
127.5°	371.0	370.8	370.5	370.3	370.1	369.9	369.8	369.6
130°	392.5	392.3	392.0	391.6	391.2	390.7	390.2	389.7
132.5°	412.7	412.5	412.3	412.0	411.8	411.6	411.4	411.2
135°	443.0	442.8	442.5	442.2	441.9	441.5	441.2	440.8
137.5°	472.3	472.0	471.7	471.6	471.6	471.7	471.8	471.9
140°	491.6	491.5	491.4	491.3	491.2	491.1	491.0	490.8
142.5°	509.9	509.9	509.8	509.8	509.8	509.8	509.7	509.7
145°	537.3	537.2	537.1	536.9	536.5	536.1	535.7	535.5
147.5°	562.2	562.1	562.0	561.9	561.8	561.7	561.6	561.5
150°	577.9	577.9	577.9	577.9	577.7	577.6	577.5	577.4
152.5°	592.7	593.0	593.2	593.2	593.0	592.6	592.3	592.0
155°	613.2	613.7	614.3	614.3	613.7	613.2	612.7	612.3
157.5°	631.4	631.8	632.2	632.1	631.7	631.3	630.8	630.5
160°	642.6	642.9	643.3	643.2	642.6	642.0	641.4	640.8
162.5°	652.6	653.3	653.9	653.9	653.4	652.7	652.1	651.6
165°	665.9	666.6	667.3	667.4	666.9	666.5	666.0	665.5
167.5°	677.0	677.8	678.5	678.4	677.8	677.0	676.3	675.5
170°	683.1	683.8	684.5	684.5	683.6	682.8	681.9	681.1
172.5°	687.6	688.4	689.2	689.2	688.3	687.5	686.6	685.9
175°	692.5	693.3	694.1	694.1	693.3	692.5	691.6	690.8
177.5°	695.1	695.8	696.4	696.4	695.7	694.9	694.1	693.3
180°	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1

(END OF REPORT)