

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331463-940

Luminaire Tested: **SA2XXDIP-C1005D1080U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331463-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D1080U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7052.8 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331463-940
CATALOG NUMBER: SA2XXDIP-C1005D1080U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331463-940

CATALOG NUMBER: SA2XXDIP-C1005D1080U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43	43	43	43	
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36	36	36	36	
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31	31	31	31	
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26	26	26	26	
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23	23	23	23	
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20	20	20	20	
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18	18	18	18	
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16	16	16	16	
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	17	14	14	14	14	
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	17	15	13	13	13	13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22946	22946	22946
5°	23034	22702	22835
10°	22897	22471	22584
15°	22614	22181	22158
20°	22213	21742	21720
25°	21814	21205	21205
30°	21300	20713	20534
35°	20820	20120	19825
40°	20219	19530	19153
45°	19628	18941	18472
50°	18982	18331	17678
55°	18311	17619	16963
60°	17563	16769	16152
65°	16756	15924	15194
70°	15739	14903	14195
75°	14323	13724	13381
80°	12710	12329	11688
85°	10374	9874	8855



TEST NUMBER: P331463-940

CATALOG NUMBER: SA2XXDIP-C1005D1080U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.6	1.9
10°-20°	376.0	5.3
20°-30°	552.7	7.8
30°-40°	642.0	9.1
40°-50°	641.3	9.1
50°-60°	559.3	7.9
60°-70°	413.6	5.9
70°-80°	234.2	3.3
80°-90°	67.9	1.0
90°-100°	77.8	1.1
100°-110°	241.6	3.4
110°-120°	412.9	5.9
120°-130°	543.0	7.7
130°-140°	609.4	8.6
140°-150°	597.6	8.5
150°-160°	501.2	7.1
160°-170°	332.4	4.7
170°-180°	116.2	1.6
0°-30°	1062.4	15.1
0°-40°	1704.4	24.2
0°-60°	2905.1	41.2
0°-90°	3620.7	51.3
90°-120°	732.3	10.4
90°-150°	2482.3	35.2
90°-180°	3432.0	48.7
0°-180°	7052.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1421	1421	1421	1421	1421	
5°	1421	1415	1401	1411	1409	135
15°	1353	1344	1327	1332	1326	381
25°	1224	1213	1190	1193	1190	563
35°	1056	1042	1021	1013	1006	659
45°	860	849	830	815	809	663
55°	650	642	626	610	603	581
65°	439	430	417	405	398	434
75°	230	227	220	212	214	245
85°	56	55	53	49	48	64
90°	1	14	36	34	35	6
95°	54	64	66	66	64	62
105°	223	226	228	230	230	235
115°	414	420	418	417	414	410
125°	603	611	609	606	605	538
135°	780	791	793	792	789	602
145°	947	954	960	961	957	591
155°	1082	1086	1089	1093	1091	498
165°	1178	1177	1177	1183	1179	332
175°	1225	1222	1220	1227	1221	116
180°	1227	1227	1227	1227	1227	



TEST NUMBER: P331463-940

CATALOG NUMBER: SA2XXDIP-C1005D1080U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1427.8	1426.6	1425.4	1424.2	1422.9	1421.0	1418.4	1415.7	1413.0	1410.3	1412.7
5°	1421.2	1420.0	1418.8	1417.6	1416.4	1414.1	1410.8	1407.4	1404.1	1400.7	1403.2
7.5°	1408.6	1406.8	1404.9	1403.0	1401.1	1398.5	1395.1	1391.7	1388.3	1384.9	1387.3
10°	1396.6	1394.5	1392.4	1390.3	1388.1	1385.3	1381.6	1378.0	1374.3	1370.6	1373.1
12.5°	1380.3	1378.3	1376.4	1374.6	1372.7	1369.9	1366.3	1362.6	1359.1	1355.4	1357.1
15°	1352.9	1351.1	1349.2	1347.5	1345.6	1342.7	1338.8	1334.8	1330.9	1327.0	1328.2
17.5°	1317.9	1316.1	1314.3	1312.4	1310.6	1307.7	1303.7	1299.7	1295.7	1291.7	1293.1
20°	1292.8	1290.9	1289.1	1287.3	1285.5	1282.5	1278.2	1274.0	1269.7	1265.4	1266.3
22.5°	1267.7	1265.1	1262.6	1260.0	1257.4	1254.2	1250.2	1246.2	1242.2	1238.1	1238.3
25°	1224.5	1222.0	1219.6	1217.2	1214.8	1210.9	1205.8	1200.6	1195.4	1190.3	1190.9
27.5°	1175.3	1173.0	1170.9	1168.7	1166.5	1163.4	1159.3	1155.2	1151.2	1147.1	1146.2
30°	1142.5	1140.1	1137.6	1135.1	1132.7	1129.3	1124.7	1120.2	1115.6	1111.0	1110.1
32.5°	1107.5	1105.5	1103.6	1101.6	1099.7	1096.4	1091.5	1086.7	1081.9	1077.1	1075.5
35°	1056.3	1053.3	1050.3	1047.2	1044.2	1040.3	1035.4	1030.6	1025.7	1020.8	1019.0
37.5°	998.7	996.0	993.4	990.7	988.0	984.3	979.4	974.6	969.6	964.8	962.5
40°	959.3	956.9	954.5	952.1	949.6	946.0	941.1	936.3	931.4	926.6	923.8
42.5°	921.0	918.6	916.2	913.8	911.3	907.7	902.9	898.0	893.1	888.2	885.3
45°	859.6	857.5	855.3	853.2	851.0	847.7	843.2	838.7	834.1	829.5	826.2
47.5°	798.3	796.4	794.3	792.4	790.3	786.9	782.2	777.5	772.8	768.0	764.5
50°	755.7	754.2	752.7	751.2	749.7	746.7	742.5	738.2	734.0	729.8	725.5
52.5°	714.2	712.2	710.2	708.2	706.1	703.1	699.1	695.1	691.2	687.2	683.6
55°	650.5	648.6	646.8	645.1	643.2	640.4	636.9	633.2	629.5	625.9	622.2
57.5°	586.6	585.1	583.6	582.2	580.7	578.0	574.0	570.0	566.0	562.0	558.4
60°	543.9	542.7	541.4	540.3	539.0	536.3	532.1	527.8	523.5	519.3	515.9
62.5°	502.4	500.4	498.5	496.5	494.5	492.0	488.7	485.4	482.1	478.8	475.7
65°	438.6	436.8	435.1	433.2	431.4	428.9	425.9	422.8	419.8	416.8	414.1
67.5°	373.9	372.5	371.0	369.5	368.1	366.0	363.2	360.5	357.8	355.1	352.9
70°	333.4	332.3	331.0	329.8	328.6	326.6	323.9	321.1	318.4	315.7	313.5
72.5°	291.9	290.7	289.4	288.3	287.0	285.5	283.8	282.0	280.3	278.5	276.3
75°	229.6	229.0	228.4	227.7	227.1	226.0	224.5	223.0	221.5	220.0	218.2
77.5°	173.8	172.8	171.7	170.8	169.7	168.9	168.3	167.6	167.0	166.5	165.5
80°	136.7	136.3	136.1	135.7	135.5	135.0	134.4	133.8	133.1	132.6	131.6
82.5°	101.7	101.7	101.6	101.5	101.4	101.2	100.9	100.5	100.1	99.8	98.6
85°	56.0	55.7	55.5	55.1	54.8	54.5	54.2	53.9	53.6	53.3	52.3
87.5°	19.9	20.0	20.1	20.1	20.2	20.4	21.0	21.5	22.0	22.6	21.8
90°	1.1	3.8	6.6	9.4	12.1	16.0	21.0	26.1	31.2	36.3	35.8
92.5°	18.5	20.4	22.5	24.5	26.6	28.2	29.3	30.6	31.7	32.9	33.0
95°	53.9	56.2	58.5	60.7	63.0	64.5	64.9	65.4	65.8	66.3	66.3
97.5°	98.4	100.4	102.5	104.5	106.5	108.0	108.8	109.7	110.6	111.5	111.5
100°	131.5	133.4	135.3	137.1	138.9	140.2	140.9	141.5	142.2	142.9	142.9
102.5°	166.4	167.8	169.3	170.8	172.3	173.4	174.3	175.1	176.0	176.9	177.1
105°	222.7	223.4	224.1	224.8	225.4	226.0	226.5	226.9	227.4	227.8	228.4
107.5°	279.5	280.4	281.5	282.5	283.5	284.0	284.0	284.0	284.0	284.0	284.2
110°	315.9	317.3	318.7	320.0	321.5	322.2	322.2	322.2	322.2	322.2	322.2



TEST NUMBER: P331463-940

CATALOG NUMBER: SA2XXDIP-C1005D1080U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	355.7	357.0	358.5	359.8	361.2	361.9	361.6	361.4	361.2	361.1	360.5
115°	414.3	415.7	417.1	418.5	419.8	420.3	419.8	419.4	418.9	418.5	418.2
117.5°	472.7	474.6	476.4	478.2	480.1	480.4	479.1	477.8	476.5	475.2	474.7
120°	511.7	513.5	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7	511.7
122.5°	547.3	549.6	551.7	553.9	556.2	556.6	555.4	554.0	552.8	551.4	550.9
125°	602.8	604.9	607.0	609.0	611.1	611.8	611.1	610.5	609.8	609.0	608.3
127.5°	656.9	659.5	662.2	664.8	667.4	668.3	667.4	666.6	665.8	664.9	664.1
130°	690.9	693.8	696.9	699.8	702.8	704.1	703.6	703.2	702.8	702.3	701.8
132.5°	729.0	731.5	733.9	736.3	738.8	740.0	740.1	740.2	740.3	740.4	739.4
135°	780.0	782.5	785.1	787.6	790.1	791.6	792.0	792.5	793.0	793.4	793.2
137.5°	833.6	835.7	837.8	839.8	841.9	843.2	843.8	844.5	845.0	845.6	845.4
140°	865.9	868.0	870.0	872.2	874.2	875.8	877.0	878.2	879.3	880.4	880.4
142.5°	899.1	901.2	903.2	905.3	907.3	908.7	909.5	910.3	911.2	912.0	912.1
145°	946.7	948.3	949.9	951.5	953.1	954.7	956.0	957.4	958.8	960.2	960.4
147.5°	989.2	991.1	993.0	995.0	996.9	998.4	999.3	1000.2	1001.1	1002.0	1002.6
150°	1018.2	1019.6	1020.9	1022.3	1023.7	1024.8	1025.8	1026.7	1027.6	1028.6	1029.2
152.5°	1043.8	1045.3	1046.6	1048.0	1049.4	1050.6	1051.8	1052.8	1054.0	1055.1	1056.0
155°	1082.4	1083.1	1083.8	1084.5	1085.2	1085.8	1086.5	1087.3	1088.0	1088.6	1089.8
157.5°	1115.4	1115.8	1116.2	1116.7	1117.2	1117.6	1118.0	1118.5	1118.8	1119.3	1120.9
160°	1135.2	1135.7	1136.1	1136.6	1137.1	1137.4	1137.6	1137.9	1138.1	1138.4	1139.7
162.5°	1153.4	1153.5	1153.6	1153.7	1153.9	1154.0	1154.2	1154.4	1154.7	1154.9	1156.5
165°	1177.7	1177.5	1177.2	1177.0	1176.8	1176.7	1176.7	1176.7	1176.7	1176.7	1178.3
167.5°	1198.0	1197.3	1196.6	1196.0	1195.2	1194.9	1194.8	1194.8	1194.7	1194.7	1196.3
170°	1208.8	1208.1	1207.4	1206.7	1206.0	1205.6	1205.3	1205.1	1204.9	1204.6	1206.2
172.5°	1216.2	1215.6	1214.9	1214.2	1213.4	1213.0	1212.8	1212.5	1212.3	1212.1	1213.7
175°	1225.4	1224.7	1224.0	1223.2	1222.6	1222.0	1221.6	1221.1	1220.7	1220.1	1221.8
177.5°	1229.0	1228.5	1228.0	1227.4	1226.9	1226.4	1226.0	1225.7	1225.3	1224.9	1226.0
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331463-940

CATALOG NUMBER: SA2XXDIP-C1005D1080U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1415.1	1417.6	1420.0	1421.0	1420.5	1420.0	1419.5	1419.1
5°	1405.6	1408.0	1410.4	1411.4	1410.8	1410.2	1409.5	1408.9
7.5°	1389.7	1392.1	1394.6	1395.5	1394.8	1394.2	1393.5	1392.9
10°	1375.6	1378.0	1380.4	1381.2	1380.3	1379.3	1378.4	1377.5
12.5°	1358.8	1360.5	1362.2	1362.7	1362.0	1361.4	1360.7	1360.0
15°	1329.4	1330.6	1331.8	1331.7	1330.2	1328.6	1327.1	1325.6
17.5°	1294.5	1295.9	1297.3	1297.3	1295.7	1294.3	1292.9	1291.4
20°	1267.3	1268.2	1269.1	1268.9	1267.7	1266.5	1265.3	1264.1
22.5°	1238.5	1238.7	1238.9	1238.6	1237.9	1237.2	1236.4	1235.6
25°	1191.5	1192.1	1192.8	1192.8	1192.1	1191.5	1190.9	1190.3
27.5°	1145.3	1144.3	1143.4	1142.3	1140.9	1139.3	1137.9	1136.5
30°	1109.2	1108.3	1107.4	1106.3	1105.1	1103.8	1102.7	1101.4
32.5°	1073.9	1072.2	1070.6	1069.2	1067.9	1066.8	1065.5	1064.3
35°	1017.2	1015.4	1013.5	1011.9	1010.4	1008.9	1007.3	1005.8
37.5°	960.3	958.1	955.8	954.0	952.5	951.0	949.6	948.2
40°	921.0	918.4	915.6	913.6	912.4	911.2	910.0	908.7
42.5°	882.3	879.3	876.4	874.1	872.4	870.7	869.0	867.2
45°	822.9	819.5	816.2	813.9	812.6	811.5	810.2	809.0
47.5°	761.0	757.4	753.9	751.3	749.5	747.8	746.0	744.2
50°	721.2	717.0	712.7	709.9	708.4	706.9	705.3	703.8
52.5°	680.1	676.5	673.1	670.3	668.2	666.3	664.2	662.3
55°	618.6	614.9	611.4	608.8	607.3	605.7	604.2	602.6
57.5°	554.7	551.2	547.6	545.2	544.1	543.0	541.8	540.6
60°	512.6	509.3	506.0	503.8	502.9	502.0	501.1	500.2
62.5°	472.7	469.6	466.5	464.3	463.2	462.0	460.8	459.7
65°	411.3	408.6	405.9	403.8	402.3	400.7	399.2	397.7
67.5°	350.8	348.7	346.5	344.8	343.7	342.4	341.3	340.0
70°	311.4	309.3	307.2	305.5	304.3	303.1	301.8	300.7
72.5°	274.3	272.2	270.0	268.5	267.5	266.5	265.6	264.6
75°	216.4	214.5	212.8	212.1	212.8	213.3	213.9	214.5
77.5°	164.6	163.7	162.8	161.9	161.0	160.2	159.3	158.5
80°	130.7	129.8	128.9	128.1	127.5	127.0	126.4	125.7
82.5°	97.5	96.3	95.1	94.5	94.3	94.3	94.2	94.0
85°	51.5	50.6	49.7	49.0	48.8	48.4	48.2	47.8
87.5°	21.0	20.1	19.3	18.7	18.5	18.4	18.2	18.0
90°	35.3	34.9	34.4	34.3	34.5	34.8	35.0	35.2
92.5°	33.1	33.2	33.3	33.3	33.4	33.4	33.5	33.5
95°	66.3	66.3	66.3	66.1	65.6	65.2	64.6	64.2
97.5°	111.5	111.5	111.5	111.5	111.4	111.4	111.3	111.3
100°	142.9	142.9	142.9	142.9	142.6	142.4	142.1	141.9
102.5°	177.3	177.5	177.6	177.6	177.4	177.2	176.9	176.7
105°	228.8	229.3	229.7	230.0	230.0	230.0	230.0	230.0
107.5°	284.4	284.5	284.7	284.3	283.3	282.2	281.2	280.1
110°	322.2	322.2	322.2	321.8	321.1	320.4	319.7	319.1



TEST NUMBER: P331463-940

CATALOG NUMBER: SA2XXDIP-C1005D1080U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	360.0	359.4	358.9	358.4	357.8	357.3	356.9	356.3
115°	418.0	417.8	417.5	417.1	416.4	415.7	415.0	414.3
117.5°	474.1	473.6	473.1	472.4	471.7	471.0	470.3	469.7
120°	511.7	511.7	511.7	511.3	510.7	510.0	509.3	508.5
122.5°	550.4	549.8	549.2	548.8	548.2	547.7	547.2	546.7
125°	607.7	607.0	606.3	605.8	605.6	605.4	605.1	604.9
127.5°	663.3	662.5	661.6	660.8	660.1	659.4	658.7	657.9
130°	701.3	700.9	700.4	699.7	698.8	697.9	697.0	696.1
132.5°	738.3	737.4	736.4	735.5	734.8	734.0	733.3	732.5
135°	793.0	792.7	792.5	792.0	791.3	790.7	790.0	789.3
137.5°	845.3	845.1	844.9	844.4	843.4	842.5	841.6	840.6
140°	880.4	880.4	880.4	879.9	879.0	878.2	877.2	876.3
142.5°	912.3	912.5	912.7	912.3	911.3	910.4	909.5	908.6
145°	960.6	960.9	961.1	960.7	959.8	958.9	958.0	957.1
147.5°	1003.1	1003.5	1004.1	1003.9	1003.0	1002.1	1001.2	1000.4
150°	1029.9	1030.6	1031.4	1031.4	1030.6	1029.9	1029.2	1028.6
152.5°	1056.9	1057.7	1058.5	1058.5	1057.7	1056.9	1056.0	1055.1
155°	1090.9	1092.1	1093.2	1093.4	1092.8	1092.1	1091.4	1090.7
157.5°	1122.4	1124.0	1125.5	1125.8	1124.6	1123.6	1122.5	1121.3
160°	1141.1	1142.5	1143.9	1144.1	1143.2	1142.3	1141.3	1140.4
162.5°	1158.1	1159.6	1161.2	1161.4	1160.3	1159.2	1158.1	1157.0
165°	1179.9	1181.5	1183.1	1183.3	1182.2	1181.1	1179.9	1178.8
167.5°	1197.9	1199.5	1201.1	1201.3	1200.2	1198.9	1197.7	1196.6
170°	1207.8	1209.4	1211.0	1211.2	1209.8	1208.4	1207.0	1205.7
172.5°	1215.3	1216.9	1218.5	1218.6	1217.3	1215.8	1214.5	1213.1
175°	1223.4	1225.0	1226.6	1226.7	1225.4	1224.0	1222.6	1221.2
177.5°	1227.2	1228.2	1229.3	1229.3	1228.2	1227.2	1226.0	1224.9
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4

(END OF REPORT)