

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331420-940

Luminaire Tested: **SA2XXDIP-C1005D330U940-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331420-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5091.5 lumens  
Efficiency: N/A  
Efficacy: 102.2 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331420-940  
CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	105	100	97	93	100	96	93	90	88	85	83	80	78	76	73	71	70	66
2	96	89	83	77	91	85	79	75	78	73	70	71	68	65	65	62	60	57
3	88	79	71	65	84	75	69	63	69	64	59	64	59	56	58	55	52	49
4	81	70	62	56	77	67	60	55	62	56	51	57	52	48	53	49	45	43
5	75	63	55	49	71	61	53	48	56	50	45	52	47	43	48	44	40	38
6	69	57	49	43	66	55	47	42	51	45	40	47	42	38	44	39	36	33
7	64	52	44	38	61	50	43	37	47	40	36	43	38	34	40	36	32	30
8	60	48	40	34	57	46	39	34	43	37	32	40	34	31	37	32	29	27
9	56	44	36	31	54	42	35	30	39	33	29	37	32	28	34	30	26	25
10	53	40	33	28	50	39	32	28	37	31	26	34	29	25	32	27	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	28709	28709	28709	28709
5°	32185	28896	25606	28896
10°	36882	28658	22161	28658
15°	40802	28134	19579	28134
20°	40180	27569	17849	27569
25°	36230	26820	16751	26820
30°	29940	25620	15951	25620
35°	21821	24366	15382	24366
40°	17428	22885	15066	22885
45°	15230	21174	14636	21174
50°	14315	19515	14350	19515
55°	13196	17833	13965	17833
60°	12093	16043	13372	16043
65°	11018	14437	12791	14437
70°	10003	12873	11939	12873
75°	8865	11123	10574	11123
80°	7624	9214	8517	9214
85°	6836	6836	5076	6836



TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	169.3	3.3
10°-20°	492.3	9.7
20°-30°	714.5	14.0
30°-40°	754.0	14.8
40°-50°	667.6	13.1
50°-60°	532.7	10.5
60°-70°	362.1	7.1
70°-80°	185.6	3.6
80°-90°	45.7	0.9
90°-100°	13.3	0.3
100°-110°	48.7	1.0
110°-120°	130.3	2.6
120°-130°	215.1	4.2
130°-140°	228.7	4.5
140°-150°	212.6	4.2
150°-160°	170.9	3.4
160°-170°	110.1	2.2
170°-180°	37.9	0.7
0°-30°	1376.1	27.0
0°-40°	2130.1	41.8
0°-60°	3330.4	65.4
0°-90°	3923.9	77.1
90°-120°	192.3	3.8
90°-150°	848.7	16.7
90°-180°	1168.0	22.9
0°-180°	5091.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1778	1778	1778	1778	1778	
5°	1986	1783	1580	1783	1986	198
15°	2441	1683	1171	1683	2441	674
25°	2034	1506	940	1506	2034	919
35°	1107	1236	780	1236	1107	720
45°	667	927	641	927	667	524
55°	469	634	496	634	469	420
65°	288	378	335	378	288	287
75°	142	178	170	178	142	152
85°	37	37	27	37	37	41
90°	8	0	8	0	8	5
95°	12	19	12	19	12	12
105°	22	88	22	88	22	23
115°	24	166	24	166	24	59
125°	246	234	246	234	246	213
135°	300	290	300	290	300	231
145°	342	336	342	336	342	214
155°	371	370	371	370	371	171
165°	390	390	390	390	390	110
175°	397	399	397	399	397	38
180°	398	398	398	398	398	



TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1860.1	1860.6	1861.7	1853.0	1851.9	1851.9	1844.2	1837.7	1830.1	1819.6	1820.8
5°	1985.8	1993.3	1996.1	1987.9	1975.6	1974.2	1962.7	1943.5	1925.7	1911.4	1901.1
7.5°	2135.9	2138.9	2132.3	2121.5	2112.3	2095.9	2074.3	2053.1	2023.5	1996.3	1976.0
10°	2249.6	2253.7	2242.1	2226.4	2213.4	2194.3	2162.8	2130.7	2091.8	2054.2	2024.1
12.5°	2336.0	2346.1	2331.2	2329.1	2306.9	2280.6	2243.2	2227.0	2172.1	2119.8	2087.6
15°	2441.0	2440.3	2441.7	2428.7	2412.3	2408.2	2368.6	2325.5	2248.3	2217.5	2164.2
17.5°	2410.7	2421.0	2425.8	2425.6	2425.3	2422.7	2409.9	2382.7	2344.0	2294.2	2232.7
20°	2338.5	2352.2	2354.2	2369.9	2378.8	2390.4	2395.2	2387.6	2363.7	2322.1	2268.8
22.5°	2227.0	2230.8	2237.2	2261.6	2280.9	2310.1	2325.2	2350.5	2341.4	2320.9	2276.4
25°	2033.7	2026.9	2050.8	2063.1	2107.5	2153.9	2187.5	2224.4	2257.2	2277.0	2264.0
27.5°	1801.6	1791.4	1827.2	1859.8	1896.0	1946.2	1998.4	2060.0	2111.3	2175.4	2197.4
30°	1605.9	1612.0	1646.2	1681.1	1735.7	1806.8	1865.5	1933.2	2006.3	2078.1	2128.0
32.5°	1394.9	1418.5	1440.1	1493.5	1541.7	1621.0	1707.0	1791.6	1882.8	1964.4	2041.7
35°	1107.1	1134.3	1164.5	1203.4	1271.0	1349.6	1433.7	1547.8	1672.2	1783.6	1875.2
37.5°	931.8	927.5	944.7	972.9	1027.6	1091.1	1187.8	1300.6	1447.0	1577.9	1707.0
40°	826.9	824.1	836.4	862.4	904.1	950.6	1035.3	1134.3	1270.3	1430.3	1584.0
42.5°	754.7	756.3	763.2	781.5	810.0	848.3	911.8	996.0	1120.6	1271.2	1436.5
45°	667.0	671.7	679.3	688.1	704.5	736.0	771.5	831.7	930.1	1055.8	1218.4
47.5°	603.8	604.0	611.6	619.4	629.1	646.8	675.8	713.5	783.0	885.4	1025.2
50°	569.9	565.2	570.6	576.8	587.0	599.3	618.4	654.0	700.4	783.1	900.0
52.5°	528.3	528.5	533.4	535.7	544.9	557.2	574.7	599.3	641.4	706.1	802.1
55°	468.8	472.2	474.9	479.0	487.2	496.1	509.8	526.2	559.0	607.5	678.6
57.5°	412.8	413.8	416.6	424.4	429.5	437.7	450.8	465.7	487.0	522.9	576.3
60°	374.5	374.5	380.0	383.3	390.2	398.4	408.7	423.0	442.1	471.5	514.6
62.5°	339.5	338.9	341.2	346.7	352.0	359.6	369.8	382.0	400.0	426.1	461.5
65°	288.4	287.0	291.1	292.5	297.9	305.5	313.7	326.6	341.0	360.2	391.6
67.5°	239.2	240.9	243.0	245.6	248.6	256.5	262.0	271.2	283.3	299.2	320.5
70°	211.9	211.9	211.9	213.9	218.0	222.1	227.6	235.1	246.7	260.4	279.5
72.5°	181.2	183.4	185.6	184.4	189.6	192.0	198.6	202.9	213.9	222.7	239.6
75°	142.1	142.1	142.1	145.5	147.6	149.6	153.7	157.8	163.4	174.2	183.2
77.5°	106.0	105.8	106.5	107.3	109.5	111.9	113.2	116.8	121.9	127.0	134.5
80°	82.0	83.4	84.1	85.4	85.4	86.8	87.5	92.3	95.7	99.1	103.9
82.5°	63.4	63.7	63.8	64.1	64.6	65.5	67.2	68.8	70.0	72.9	76.5
85°	36.9	36.2	36.2	37.5	36.9	36.9	38.3	39.6	39.6	40.3	42.4
87.5°	15.8	15.8	16.2	15.7	15.7	16.1	16.1	15.5	16.0	16.5	16.9
90°	7.8	7.7	7.5	7.4	7.3	7.0	6.7	6.4	6.1	5.8	5.3
92.5°	7.8	7.7	7.7	7.6	7.5	7.3	7.2	7.0	6.9	6.7	6.4
95°	12.4	12.5	12.5	12.6	12.7	12.5	12.2	11.9	11.6	11.2	10.8
97.5°	16.6	16.5	16.4	16.3	16.2	16.1	15.8	15.6	15.3	15.1	14.0
100°	19.4	19.2	19.1	18.9	18.8	18.5	18.0	17.5	16.9	16.4	15.3
102.5°	20.7	20.5	20.3	20.2	20.0	19.5	18.9	18.2	17.6	16.9	26.0
105°	21.9	21.7	21.4	21.1	20.9	20.4	19.7	19.0	18.3	17.6	35.0
107.5°	22.6	22.3	22.0	21.8	21.5	21.8	22.5	23.2	23.9	24.6	45.6
110°	22.7	22.6	22.3	22.0	21.8	24.8	31.2	37.6	44.1	50.5	68.9



TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	23.0	22.8	22.6	22.4	22.2	33.8	57.2	80.5	103.9	127.2	131.8
115°	23.6	28.3	32.9	37.5	42.1	59.2	88.9	118.6	148.2	177.9	176.3
117.5°	96.6	111.7	126.9	142.0	157.2	168.4	175.5	182.7	189.8	197.1	195.9
120°	175.8	184.5	193.1	201.8	210.4	214.4	213.7	212.9	212.1	211.3	210.2
122.5°	219.5	221.1	222.8	224.5	226.1	226.8	226.3	225.9	225.4	225.0	223.7
125°	246.5	246.3	246.1	245.9	245.8	245.4	245.0	244.5	244.1	243.6	242.4
127.5°	263.6	263.5	263.5	263.5	263.4	263.1	262.4	261.8	261.1	260.5	259.6
130°	274.2	274.3	274.3	274.4	274.5	274.1	273.4	272.7	272.0	271.3	270.6
132.5°	284.5	284.6	284.7	284.7	284.8	284.5	283.9	283.4	282.8	282.1	281.4
135°	299.5	299.7	299.8	300.0	300.1	299.8	299.2	298.5	297.9	297.3	296.7
137.5°	313.3	313.4	313.7	313.9	314.1	313.9	313.3	312.6	312.0	311.4	310.8
140°	321.7	322.1	322.4	322.7	323.1	322.9	322.4	321.7	321.2	320.6	319.9
142.5°	330.0	330.4	330.7	331.0	331.4	331.3	330.7	330.2	329.7	329.1	328.3
145°	341.6	342.0	342.3	342.6	343.0	342.9	342.4	342.0	341.5	341.1	340.0
147.5°	351.9	352.1	352.4	352.7	352.9	352.9	352.6	352.2	351.9	351.6	350.5
150°	358.1	358.4	358.7	359.1	359.4	359.4	358.9	358.6	358.2	357.8	356.8
152.5°	363.4	363.8	364.3	364.6	365.1	365.1	364.7	364.4	363.9	363.6	362.6
155°	370.8	371.3	371.8	372.3	372.8	372.9	372.5	372.1	371.8	371.3	370.6
157.5°	377.6	378.0	378.5	379.0	379.5	379.5	379.2	378.7	378.3	377.8	377.3
160°	381.5	381.9	382.4	382.8	383.3	383.3	382.9	382.5	382.1	381.7	381.4
162.5°	384.7	385.2	385.8	386.3	386.9	386.9	386.5	386.0	385.7	385.2	384.9
165°	389.5	389.9	390.4	390.8	391.3	391.3	390.8	390.4	389.9	389.5	389.3
167.5°	392.5	393.2	393.7	394.3	394.8	394.9	394.5	394.0	393.6	393.2	393.0
170°	394.4	395.0	395.6	396.2	396.7	396.8	396.4	395.9	395.5	395.0	394.8
172.5°	395.8	396.4	397.0	397.5	398.1	398.1	397.7	397.3	396.8	396.4	396.3
175°	397.0	397.6	398.3	399.0	399.6	399.7	399.2	398.8	398.3	397.9	397.8
177.5°	397.8	398.2	398.7	399.1	399.6	399.7	399.3	399.0	398.6	398.2	398.1
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1824.6	1820.2	1817.5	1807.7	1798.8	1790.1	1787.4	1788.5	1776.5	1765.0	1760.1
5°	1895.7	1882.0	1869.0	1850.6	1828.7	1804.7	1792.4	1782.9	1759.0	1733.0	1718.0
7.5°	1959.4	1939.8	1914.8	1880.1	1848.2	1810.6	1786.7	1765.5	1730.5	1693.9	1671.5
10°	1998.1	1971.5	1939.4	1897.0	1858.1	1812.3	1780.1	1748.0	1707.0	1663.3	1635.9
12.5°	2031.5	1995.6	1964.0	1909.6	1863.5	1806.2	1768.2	1722.9	1679.7	1627.7	1601.0
15°	2110.9	2044.6	1984.5	1923.0	1866.3	1786.3	1743.9	1683.1	1626.4	1562.2	1531.4
17.5°	2172.3	2097.7	2003.0	1924.9	1858.8	1770.2	1708.0	1635.1	1568.1	1494.7	1452.9
20°	2207.3	2121.8	2020.0	1927.1	1847.8	1746.7	1679.0	1604.5	1526.0	1443.2	1398.2
22.5°	2228.0	2138.2	2037.6	1918.9	1826.0	1727.5	1642.4	1560.8	1481.1	1391.9	1344.6
25°	2234.6	2152.6	2046.0	1912.1	1798.6	1687.2	1584.7	1505.5	1409.1	1325.7	1256.7
27.5°	2202.1	2143.3	2040.8	1899.2	1767.0	1636.8	1522.5	1432.7	1331.1	1240.5	1171.2
30°	2162.1	2128.0	2028.2	1886.1	1741.9	1601.8	1476.0	1374.2	1273.1	1181.5	1110.4
32.5°	2100.4	2093.0	2005.3	1867.5	1715.1	1557.6	1427.5	1324.5	1212.5	1122.5	1054.7
35°	1979.1	2011.8	1956.5	1826.0	1664.6	1494.5	1353.7	1236.2	1120.1	1033.9	970.4
37.5°	1816.4	1897.8	1883.4	1765.1	1596.6	1425.9	1270.5	1147.6	1037.0	950.0	887.7
40°	1704.3	1808.2	1823.2	1718.7	1548.5	1372.9	1208.2	1085.8	977.9	898.7	835.7
42.5°	1584.0	1705.4	1746.7	1662.9	1496.0	1317.1	1152.4	1025.7	918.8	841.8	786.0
45°	1382.4	1543.0	1617.6	1569.7	1408.5	1225.3	1055.8	927.3	830.3	757.9	714.8
47.5°	1194.0	1369.5	1469.6	1452.7	1311.0	1129.6	962.1	838.7	744.3	686.5	648.0
50°	1060.6	1241.0	1361.9	1367.4	1241.0	1061.2	893.1	776.9	690.2	636.2	604.8
52.5°	944.7	1116.9	1248.8	1277.7	1162.8	990.2	831.3	715.8	639.4	589.8	561.6
55°	793.4	939.0	1085.2	1138.4	1046.2	882.3	735.3	633.5	561.7	527.5	502.9
57.5°	659.6	781.0	916.0	974.9	918.0	777.7	639.9	551.4	493.3	463.3	444.4
60°	589.1	684.7	805.0	875.4	826.2	701.2	580.9	496.8	449.0	422.3	404.6
62.5°	523.4	608.2	709.9	774.3	747.4	629.5	521.8	447.6	406.4	381.3	368.5
65°	431.9	498.8	577.5	636.9	619.1	529.6	441.5	377.9	345.1	325.3	315.0
67.5°	355.6	404.0	458.5	510.6	496.2	432.8	362.0	312.5	288.1	271.0	264.8
70°	307.6	344.4	393.0	434.6	423.0	371.0	315.0	272.7	251.5	237.1	231.0
72.5°	261.6	291.9	329.0	363.0	355.2	312.0	265.3	233.3	217.0	203.8	198.8
75°	197.5	220.7	243.3	265.8	263.8	230.3	203.0	178.3	165.4	155.2	153.1
77.5°	145.8	158.8	174.2	187.5	183.8	164.7	143.2	129.1	119.6	112.7	111.6
80°	111.4	118.9	129.8	139.4	134.6	126.4	109.3	99.1	92.3	85.4	82.7
82.5°	80.8	88.3	94.9	100.0	96.4	88.7	78.2	71.2	67.1	62.4	61.3
85°	42.4	46.5	49.2	50.6	49.2	44.4	39.6	36.9	33.5	31.5	30.8
87.5°	17.4	17.2	17.1	18.1	16.3	16.2	13.8	12.1	11.7	11.2	10.3
90°	4.7	4.2	3.7	3.1	2.4	1.7	1.0	0.3	1.0	1.7	2.4
92.5°	6.2	5.9	5.7	5.5	5.6	5.7	5.8	5.8	5.8	5.7	5.6
95°	10.3	9.9	9.5	10.3	12.4	14.5	16.6	18.7	16.6	14.5	12.4
97.5°	12.9	11.9	10.9	13.4	19.4	25.2	31.2	37.2	31.2	25.2	19.4
100°	14.3	13.2	12.0	16.0	24.7	33.4	42.3	51.0	42.3	33.4	24.7
102.5°	35.1	44.2	53.3	58.9	60.7	62.5	64.4	66.3	64.4	62.5	60.7
105°	52.6	70.1	87.6	95.3	93.5	91.5	89.5	87.7	89.5	91.5	93.5
107.5°	66.6	87.6	108.5	118.2	116.7	115.1	113.6	112.0	113.6	115.1	116.7
110°	87.5	106.0	124.5	133.1	131.8	130.5	129.0	127.7	129.0	130.5	131.8





TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	136.4	141.0	145.5	147.2	146.1	144.9	143.7	142.5	143.7	144.9	146.1
115°	174.7	173.1	171.5	170.1	169.1	168.0	166.8	165.8	166.8	168.0	169.1
117.5°	194.8	193.8	192.6	191.5	190.3	189.0	187.8	186.6	187.8	189.0	190.3
120°	209.0	207.9	206.7	205.6	204.7	203.8	202.8	201.8	202.8	203.8	204.7
122.5°	222.4	221.1	219.9	218.8	217.8	216.8	215.8	214.7	215.8	216.8	217.8
125°	241.2	240.0	238.8	237.7	236.9	236.0	235.2	234.4	235.2	236.0	236.9
127.5°	258.7	257.7	256.8	255.9	255.0	254.0	253.2	252.2	253.2	254.0	255.0
130°	269.9	269.2	268.5	267.6	266.6	265.6	264.6	263.5	264.6	265.6	266.6
132.5°	280.7	280.0	279.3	278.6	277.7	276.8	275.9	275.1	275.9	276.8	277.7
135°	296.1	295.5	295.0	294.2	293.1	292.1	291.1	290.1	291.1	292.1	293.1
137.5°	310.0	309.4	308.8	308.1	307.4	306.7	305.9	305.2	305.9	306.7	307.4
140°	319.2	318.5	317.8	317.2	316.6	316.1	315.7	315.1	315.7	316.1	316.6
142.5°	327.5	326.7	325.9	325.3	324.9	324.3	323.9	323.4	323.9	324.3	324.9
145°	338.9	337.8	336.7	336.2	336.3	336.4	336.4	336.4	336.4	336.4	336.3
147.5°	349.5	348.3	347.2	346.9	347.1	347.3	347.6	347.9	347.6	347.3	347.1
150°	355.8	354.7	353.7	353.4	353.8	354.3	354.7	355.2	354.7	354.3	353.8
152.5°	361.6	360.6	359.6	359.4	359.9	360.4	361.0	361.4	361.0	360.4	359.9
155°	369.8	369.1	368.3	368.2	368.7	369.3	369.9	370.5	369.9	369.3	368.7
157.5°	376.7	376.2	375.7	375.6	376.1	376.6	377.1	377.6	377.1	376.6	376.1
160°	380.9	380.6	380.2	380.2	380.6	380.9	381.4	381.7	381.4	380.9	380.6
162.5°	384.5	384.1	383.9	383.9	384.2	384.7	385.0	385.4	385.0	384.7	384.2
165°	389.1	389.0	388.8	388.9	389.2	389.6	390.0	390.4	390.0	389.6	389.2
167.5°	392.8	392.6	392.4	392.5	392.9	393.3	393.7	394.0	393.7	393.3	392.9
170°	394.8	394.6	394.5	394.6	395.0	395.4	395.7	396.2	395.7	395.4	395.0
172.5°	396.1	396.0	395.8	396.0	396.4	396.7	397.2	397.5	397.2	396.7	396.4
175°	397.6	397.5	397.3	397.5	398.0	398.4	398.9	399.3	398.9	398.4	398.0
177.5°	398.1	398.1	398.1	398.1	398.5	398.9	399.2	399.6	399.2	398.9	398.5
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1754.6	1751.3	1739.8	1733.8	1724.0	1714.7	1708.7	1711.5	1713.6	1712.5	1710.8
5°	1704.3	1691.3	1671.5	1654.4	1642.1	1619.6	1610.0	1605.3	1601.2	1596.3	1591.5
7.5°	1644.4	1624.0	1595.5	1571.2	1548.2	1520.2	1504.2	1494.7	1484.8	1474.0	1464.5
10°	1601.8	1573.1	1543.0	1508.9	1481.6	1456.3	1433.7	1418.6	1405.0	1392.0	1382.4
12.5°	1557.0	1523.9	1486.7	1440.0	1409.9	1373.7	1370.3	1343.8	1322.4	1314.4	1303.1
15°	1485.6	1439.1	1392.0	1336.7	1312.8	1280.0	1259.5	1238.9	1220.5	1207.5	1204.1
17.5°	1404.6	1344.4	1297.5	1257.8	1218.6	1185.0	1166.1	1149.7	1134.5	1117.1	1114.8
20°	1342.8	1290.8	1239.7	1204.8	1164.5	1130.2	1107.1	1090.7	1077.6	1067.4	1058.5
22.5°	1284.3	1227.4	1180.5	1142.5	1102.7	1075.0	1056.8	1040.9	1030.1	1018.8	1010.4
25°	1190.4	1146.0	1094.8	1051.7	1018.9	1001.1	986.1	972.4	965.6	958.1	948.5
27.5°	1108.3	1058.9	1010.9	977.6	948.8	933.1	922.4	913.1	906.7	902.3	896.9
30°	1050.3	1000.4	962.9	930.1	906.2	890.5	883.6	878.2	870.6	867.9	865.1
32.5°	994.5	949.6	917.5	889.0	866.2	856.0	849.7	844.8	838.9	836.2	830.7
35°	915.7	878.2	846.7	831.0	812.5	803.6	798.9	792.0	786.6	783.8	783.1
37.5°	841.5	808.9	788.2	767.9	760.2	754.7	748.1	743.5	741.9	741.5	740.7
40°	793.4	766.7	748.3	731.9	728.4	720.2	714.8	710.7	710.7	711.4	710.7
42.5°	749.7	725.8	709.4	695.3	691.3	686.3	680.9	680.6	681.7	684.0	681.7
45°	683.4	666.3	654.7	647.8	640.3	635.5	634.8	636.9	637.6	638.3	640.3
47.5°	622.4	611.1	600.6	593.0	589.8	588.9	588.1	591.7	594.9	596.2	599.3
50°	586.3	573.4	564.5	559.6	557.0	555.5	557.0	561.1	563.7	567.2	569.3
52.5°	545.9	536.7	530.6	526.9	525.8	526.6	526.9	531.5	535.9	537.2	538.1
55°	490.0	483.1	481.8	475.6	478.3	477.7	481.1	483.8	487.9	492.0	492.7
57.5°	434.2	428.7	425.1	425.6	426.4	429.4	432.3	437.1	441.5	445.9	446.2
60°	397.1	394.3	392.3	392.3	393.6	397.7	401.1	405.9	408.7	411.3	413.4
62.5°	363.1	360.4	358.4	359.4	363.0	365.4	369.4	372.0	374.8	377.5	378.4
65°	309.6	308.2	310.2	311.7	312.3	315.8	320.5	322.5	325.3	326.6	331.4
67.5°	260.2	260.5	260.2	262.2	266.1	266.9	271.4	276.3	276.8	279.4	282.5
70°	226.9	228.3	229.6	231.0	234.4	235.8	239.2	241.2	244.0	246.0	248.1
72.5°	196.3	196.5	197.9	197.6	200.5	203.5	206.3	208.4	211.2	213.7	215.8
75°	151.1	151.1	152.4	153.1	156.5	159.9	159.3	160.6	163.4	166.0	167.5
77.5°	110.3	108.8	110.3	111.0	112.1	114.9	115.5	117.4	120.6	119.6	121.1
80°	84.1	82.0	84.1	84.7	84.7	88.2	88.2	89.5	91.6	89.5	91.6
82.5°	60.0	59.0	60.5	60.7	61.8	61.9	63.0	63.3	65.4	64.4	65.4
85°	30.1	29.4	30.1	29.4	30.1	30.8	30.8	30.1	30.1	31.5	29.4
87.5°	9.9	9.5	9.0	9.2	8.7	8.3	7.8	7.8	7.9	6.9	7.0
90°	3.1	3.7	4.2	4.7	5.3	5.8	6.1	6.4	6.7	7.0	7.3
92.5°	5.5	5.7	5.9	6.2	6.4	6.7	6.9	7.0	7.2	7.3	7.5
95°	10.3	9.5	9.9	10.3	10.8	11.2	11.6	11.9	12.2	12.5	12.7
97.5°	13.4	10.9	11.9	12.9	14.0	15.1	15.3	15.6	15.8	16.1	16.2
100°	16.0	12.0	13.2	14.3	15.3	16.4	16.9	17.5	18.0	18.5	18.8
102.5°	58.9	53.3	44.2	35.1	26.0	16.9	17.6	18.2	18.9	19.5	20.0
105°	95.3	87.6	70.1	52.6	35.0	17.6	18.3	19.0	19.7	20.4	20.9
107.5°	118.2	108.5	87.6	66.6	45.6	24.6	23.9	23.2	22.5	21.8	21.5
110°	133.1	124.5	106.0	87.5	68.9	50.5	44.1	37.6	31.2	24.8	21.8



TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	147.2	145.5	141.0	136.4	131.8	127.2	103.9	80.5	57.2	33.8	22.2
115°	170.1	171.5	173.1	174.7	176.3	177.9	148.2	118.6	88.9	59.2	42.1
117.5°	191.5	192.6	193.8	194.8	195.9	197.1	189.8	182.7	175.5	168.4	157.2
120°	205.6	206.7	207.9	209.0	210.2	211.3	212.1	212.9	213.7	214.4	210.4
122.5°	218.8	219.9	221.1	222.4	223.7	225.0	225.4	225.9	226.3	226.8	226.1
125°	237.7	238.8	240.0	241.2	242.4	243.6	244.1	244.5	245.0	245.4	245.8
127.5°	255.9	256.8	257.7	258.7	259.6	260.5	261.1	261.8	262.4	263.1	263.4
130°	267.6	268.5	269.2	269.9	270.6	271.3	272.0	272.7	273.4	274.1	274.5
132.5°	278.6	279.3	280.0	280.7	281.4	282.1	282.8	283.4	283.9	284.5	284.8
135°	294.2	295.0	295.5	296.1	296.7	297.3	297.9	298.5	299.2	299.8	300.1
137.5°	308.1	308.8	309.4	310.0	310.8	311.4	312.0	312.6	313.3	313.9	314.1
140°	317.2	317.8	318.5	319.2	319.9	320.6	321.2	321.7	322.4	322.9	323.1
142.5°	325.3	325.9	326.7	327.5	328.3	329.1	329.7	330.2	330.7	331.3	331.4
145°	336.2	336.7	337.8	338.9	340.0	341.1	341.5	342.0	342.4	342.9	343.0
147.5°	346.9	347.2	348.3	349.5	350.5	351.6	351.9	352.2	352.6	352.9	352.9
150°	353.4	353.7	354.7	355.8	356.8	357.8	358.2	358.6	358.9	359.4	359.4
152.5°	359.4	359.6	360.6	361.6	362.6	363.6	363.9	364.4	364.7	365.1	365.1
155°	368.2	368.3	369.1	369.8	370.6	371.3	371.8	372.1	372.5	372.9	372.8
157.5°	375.6	375.7	376.2	376.7	377.3	377.8	378.3	378.7	379.2	379.5	379.5
160°	380.2	380.2	380.6	380.9	381.4	381.7	382.1	382.5	382.9	383.3	383.3
162.5°	383.9	383.9	384.1	384.5	384.9	385.2	385.7	386.0	386.5	386.9	386.9
165°	388.9	388.8	389.0	389.1	389.3	389.5	389.9	390.4	390.8	391.3	391.3
167.5°	392.5	392.4	392.6	392.8	393.0	393.2	393.6	394.0	394.5	394.9	394.8
170°	394.6	394.5	394.6	394.8	394.8	395.0	395.5	395.9	396.4	396.8	396.7
172.5°	396.0	395.8	396.0	396.1	396.3	396.4	396.8	397.3	397.7	398.1	398.1
175°	397.5	397.3	397.5	397.6	397.8	397.9	398.3	398.8	399.2	399.7	399.6
177.5°	398.1	398.1	398.1	398.1	398.1	398.2	398.6	399.0	399.3	399.7	399.6
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1705.4	1704.3	1704.3	1699.4	1704.3	1704.3	1705.4	1710.8	1712.5	1713.6	1711.5
5°	1582.0	1579.9	1576.5	1579.9	1576.5	1579.9	1582.0	1591.5	1596.3	1601.2	1605.3
7.5°	1459.9	1451.7	1450.5	1442.4	1450.5	1451.7	1459.9	1464.5	1474.0	1484.8	1494.7
10°	1370.8	1365.4	1364.7	1351.7	1364.7	1365.4	1370.8	1382.4	1392.0	1405.0	1418.6
12.5°	1303.1	1289.9	1292.5	1285.0	1292.5	1289.9	1303.1	1303.1	1314.4	1322.4	1343.8
15°	1185.6	1185.6	1182.9	1171.3	1182.9	1185.6	1185.6	1204.1	1207.5	1220.5	1238.9
17.5°	1101.4	1099.9	1093.4	1096.6	1093.4	1099.9	1101.4	1114.8	1117.1	1134.5	1149.7
20°	1051.0	1047.0	1038.8	1038.8	1038.8	1047.0	1051.0	1058.5	1067.4	1077.6	1090.7
22.5°	1003.4	1003.2	994.4	997.2	994.4	1003.2	1003.4	1010.4	1018.8	1030.1	1040.9
25°	947.8	942.4	938.3	940.3	938.3	942.4	947.8	948.5	958.1	965.6	972.4
27.5°	895.1	892.1	891.8	886.2	891.8	892.1	895.1	896.9	902.3	906.7	913.1
30°	864.4	857.6	859.0	855.6	859.0	857.6	864.4	865.1	867.9	870.6	878.2
32.5°	829.5	827.0	825.6	822.8	825.6	827.0	829.5	830.7	836.2	838.9	844.8
35°	781.8	782.5	779.0	780.4	779.0	782.5	781.8	783.1	783.8	786.6	792.0
37.5°	740.1	742.3	740.7	741.0	740.7	742.3	740.1	740.7	741.5	741.9	743.5
40°	712.7	712.7	712.7	714.8	712.7	712.7	712.7	710.7	711.4	710.7	710.7
42.5°	686.5	685.5	684.3	684.2	684.3	685.5	686.5	681.7	684.0	681.7	680.6
45°	641.7	643.7	644.4	641.0	644.4	643.7	641.7	640.3	638.3	637.6	636.9
47.5°	601.1	601.4	601.1	604.1	601.1	601.4	601.1	599.3	596.2	594.9	591.7
50°	572.7	571.3	572.7	571.3	572.7	571.3	572.7	569.3	567.2	563.7	561.1
52.5°	542.6	542.9	542.1	541.8	542.1	542.9	542.6	538.1	537.2	535.9	531.5
55°	495.4	496.8	496.1	496.1	496.1	496.8	495.4	492.7	492.0	487.9	483.8
57.5°	446.7	447.9	448.8	445.9	448.8	447.9	446.7	446.2	445.9	441.5	437.1
60°	412.8	416.2	415.4	414.1	415.4	416.2	412.8	413.4	411.3	408.7	405.9
62.5°	381.6	382.8	382.7	382.5	382.7	382.8	381.6	378.4	377.5	374.8	372.0
65°	333.5	334.8	332.8	334.8	332.8	334.8	333.5	331.4	326.6	325.3	322.5
67.5°	281.7	282.1	283.6	284.5	283.6	282.1	281.7	282.5	279.4	276.8	276.3
70°	249.4	248.8	250.8	252.9	250.8	248.8	249.4	248.1	246.0	244.0	241.2
72.5°	215.5	217.0	216.3	217.8	216.3	217.0	215.5	215.8	213.7	211.2	208.4
75°	166.0	168.1	167.5	169.5	167.5	168.1	166.0	167.5	166.0	163.4	160.6
77.5°	120.0	120.3	120.0	121.1	120.0	120.3	120.0	121.1	119.6	120.6	117.4
80°	91.6	90.2	88.8	91.6	88.8	90.2	91.6	91.6	89.5	91.6	89.5
82.5°	63.7	64.5	63.1	63.1	63.1	64.5	63.7	65.4	64.4	65.4	63.3
85°	29.4	28.7	27.4	27.4	27.4	28.7	29.4	29.4	31.5	30.1	30.1
87.5°	7.0	6.4	6.4	6.0	6.4	6.4	7.0	7.0	6.9	7.9	7.8
90°	7.4	7.5	7.7	7.8	7.7	7.5	7.4	7.3	7.0	6.7	6.4
92.5°	7.6	7.7	7.7	7.8	7.7	7.7	7.6	7.5	7.3	7.2	7.0
95°	12.6	12.5	12.5	12.4	12.5	12.5	12.6	12.7	12.5	12.2	11.9
97.5°	16.3	16.4	16.5	16.6	16.5	16.4	16.3	16.2	16.1	15.8	15.6
100°	18.9	19.1	19.2	19.4	19.2	19.1	18.9	18.8	18.5	18.0	17.5
102.5°	20.2	20.3	20.5	20.7	20.5	20.3	20.2	20.0	19.5	18.9	18.2
105°	21.1	21.4	21.7	21.9	21.7	21.4	21.1	20.9	20.4	19.7	19.0
107.5°	21.8	22.0	22.3	22.6	22.3	22.0	21.8	21.5	21.8	22.5	23.2
110°	22.0	22.3	22.6	22.7	22.6	22.3	22.0	21.8	24.8	31.2	37.6



TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	22.4	22.6	22.8	23.0	22.8	22.6	22.4	22.2	33.8	57.2	80.5
115°	37.5	32.9	28.3	23.6	28.3	32.9	37.5	42.1	59.2	88.9	118.6
117.5°	142.0	126.9	111.7	96.6	111.7	126.9	142.0	157.2	168.4	175.5	182.7
120°	201.8	193.1	184.5	175.8	184.5	193.1	201.8	210.4	214.4	213.7	212.9
122.5°	224.5	222.8	221.1	219.5	221.1	222.8	224.5	226.1	226.8	226.3	225.9
125°	245.9	246.1	246.3	246.5	246.3	246.1	245.9	245.8	245.4	245.0	244.5
127.5°	263.5	263.5	263.5	263.6	263.5	263.5	263.5	263.4	263.1	262.4	261.8
130°	274.4	274.3	274.3	274.2	274.3	274.3	274.4	274.5	274.1	273.4	272.7
132.5°	284.7	284.7	284.6	284.5	284.6	284.7	284.7	284.8	284.5	283.9	283.4
135°	300.0	299.8	299.7	299.5	299.7	299.8	300.0	300.1	299.8	299.2	298.5
137.5°	313.9	313.7	313.4	313.3	313.4	313.7	313.9	314.1	313.9	313.3	312.6
140°	322.7	322.4	322.1	321.7	322.1	322.4	322.7	323.1	322.9	322.4	321.7
142.5°	331.0	330.7	330.4	330.0	330.4	330.7	331.0	331.4	331.3	330.7	330.2
145°	342.6	342.3	342.0	341.6	342.0	342.3	342.6	343.0	342.9	342.4	342.0
147.5°	352.7	352.4	352.1	351.9	352.1	352.4	352.7	352.9	352.9	352.6	352.2
150°	359.1	358.7	358.4	358.1	358.4	358.7	359.1	359.4	359.4	358.9	358.6
152.5°	364.6	364.3	363.8	363.4	363.8	364.3	364.6	365.1	365.1	364.7	364.4
155°	372.3	371.8	371.3	370.8	371.3	371.8	372.3	372.8	372.9	372.5	372.1
157.5°	379.0	378.5	378.0	377.6	378.0	378.5	379.0	379.5	379.5	379.2	378.7
160°	382.8	382.4	381.9	381.5	381.9	382.4	382.8	383.3	383.3	382.9	382.5
162.5°	386.3	385.8	385.2	384.7	385.2	385.8	386.3	386.9	386.9	386.5	386.0
165°	390.8	390.4	389.9	389.5	389.9	390.4	390.8	391.3	391.3	390.8	390.4
167.5°	394.3	393.7	393.2	392.5	393.2	393.7	394.3	394.8	394.9	394.5	394.0
170°	396.2	395.6	395.0	394.4	395.0	395.6	396.2	396.7	396.8	396.4	395.9
172.5°	397.5	397.0	396.4	395.8	396.4	397.0	397.5	398.1	398.1	397.7	397.3
175°	399.0	398.3	397.6	397.0	397.6	398.3	399.0	399.6	399.7	399.2	398.8
177.5°	399.1	398.7	398.2	397.8	398.2	398.7	399.1	399.6	399.7	399.3	399.0
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331420-940  
 CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1708.7	1714.7	1724.0	1733.8	1739.8	1751.3	1754.6	1760.1	1765.0	1776.5	1788.5
5°	1610.0	1619.6	1642.1	1654.4	1671.5	1691.3	1704.3	1718.0	1733.0	1759.0	1782.9
7.5°	1504.2	1520.2	1548.2	1571.2	1595.5	1624.0	1644.4	1671.5	1693.9	1730.5	1765.5
10°	1433.7	1456.3	1481.6	1508.9	1543.0	1573.1	1601.8	1635.9	1663.3	1707.0	1748.0
12.5°	1370.3	1373.7	1409.9	1440.0	1486.7	1523.9	1557.0	1601.0	1627.7	1679.7	1722.9
15°	1259.5	1280.0	1312.8	1336.7	1392.0	1439.1	1485.6	1531.4	1562.2	1626.4	1683.1
17.5°	1166.1	1185.0	1218.6	1257.8	1297.5	1344.4	1404.6	1452.9	1494.7	1568.1	1635.1
20°	1107.1	1130.2	1164.5	1204.8	1239.7	1290.8	1342.8	1398.2	1443.2	1526.0	1604.5
22.5°	1056.8	1075.0	1102.7	1142.5	1180.5	1227.4	1284.3	1344.6	1391.9	1481.1	1560.8
25°	986.1	1001.1	1018.9	1051.7	1094.8	1146.0	1190.4	1256.7	1325.7	1409.1	1505.5
27.5°	922.4	933.1	948.8	977.6	1010.9	1058.9	1108.3	1171.2	1240.5	1331.1	1432.7
30°	883.6	890.5	906.2	930.1	962.9	1000.4	1050.3	1110.4	1181.5	1273.1	1374.2
32.5°	849.7	856.0	866.2	889.0	917.5	949.6	994.5	1054.7	1122.5	1212.5	1324.5
35°	798.9	803.6	812.5	831.0	846.7	878.2	915.7	970.4	1033.9	1120.1	1236.2
37.5°	748.1	754.7	760.2	767.9	788.2	808.9	841.5	887.7	950.0	1037.0	1147.6
40°	714.8	720.2	728.4	731.9	748.3	766.7	793.4	835.7	898.7	977.9	1085.8
42.5°	680.9	686.3	691.3	695.3	709.4	725.8	749.7	786.0	841.8	918.8	1025.7
45°	634.8	635.5	640.3	647.8	654.7	666.3	683.4	714.8	757.9	830.3	927.3
47.5°	588.1	588.9	589.8	593.0	600.6	611.1	622.4	648.0	686.5	744.3	838.7
50°	557.0	555.5	557.0	559.6	564.5	573.4	586.3	604.8	636.2	690.2	776.9
52.5°	526.9	526.6	525.8	526.9	530.6	536.7	545.9	561.6	589.8	639.4	715.8
55°	481.1	477.7	478.3	475.6	481.8	483.1	490.0	502.9	527.5	561.7	633.5
57.5°	432.3	429.4	426.4	425.6	425.1	428.7	434.2	444.4	463.3	493.3	551.4
60°	401.1	397.7	393.6	392.3	392.3	394.3	397.1	404.6	422.3	449.0	496.8
62.5°	369.4	365.4	363.0	359.4	358.4	360.4	363.1	368.5	381.3	406.4	447.6
65°	320.5	315.8	312.3	311.7	310.2	308.2	309.6	315.0	325.3	345.1	377.9
67.5°	271.4	266.9	266.1	262.2	260.2	260.5	260.2	264.8	271.0	288.1	312.5
70°	239.2	235.8	234.4	231.0	229.6	228.3	226.9	231.0	237.1	251.5	272.7
72.5°	206.3	203.5	200.5	197.6	197.9	196.5	196.3	198.8	203.8	217.0	233.3
75°	159.3	159.9	156.5	153.1	152.4	151.1	151.1	153.1	155.2	165.4	178.3
77.5°	115.5	114.9	112.1	111.0	110.3	108.8	110.3	111.6	112.7	119.6	129.1
80°	88.2	88.2	84.7	84.7	84.1	82.0	84.1	82.7	85.4	92.3	99.1
82.5°	63.0	61.9	61.8	60.7	60.5	59.0	60.0	61.3	62.4	67.1	71.2
85°	30.8	30.8	30.1	29.4	30.1	29.4	30.1	30.8	31.5	33.5	36.9
87.5°	7.8	8.3	8.7	9.2	9.0	9.5	9.9	10.3	11.2	11.7	12.1
90°	6.1	5.8	5.3	4.7	4.2	3.7	3.1	2.4	1.7	1.0	0.3
92.5°	6.9	6.7	6.4	6.2	5.9	5.7	5.5	5.6	5.7	5.8	5.8
95°	11.6	11.2	10.8	10.3	9.9	9.5	10.3	12.4	14.5	16.6	18.7
97.5°	15.3	15.1	14.0	12.9	11.9	10.9	13.4	19.4	25.2	31.2	37.2
100°	16.9	16.4	15.3	14.3	13.2	12.0	16.0	24.7	33.4	42.3	51.0
102.5°	17.6	16.9	26.0	35.1	44.2	53.3	58.9	60.7	62.5	64.4	66.3
105°	18.3	17.6	35.0	52.6	70.1	87.6	95.3	93.5	91.5	89.5	87.7
107.5°	23.9	24.6	45.6	66.6	87.6	108.5	118.2	116.7	115.1	113.6	112.0
110°	44.1	50.5	68.9	87.5	106.0	124.5	133.1	131.8	130.5	129.0	127.7



TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	103.9	127.2	131.8	136.4	141.0	145.5	147.2	146.1	144.9	143.7	142.5
115°	148.2	177.9	176.3	174.7	173.1	171.5	170.1	169.1	168.0	166.8	165.8
117.5°	189.8	197.1	195.9	194.8	193.8	192.6	191.5	190.3	189.0	187.8	186.6
120°	212.1	211.3	210.2	209.0	207.9	206.7	205.6	204.7	203.8	202.8	201.8
122.5°	225.4	225.0	223.7	222.4	221.1	219.9	218.8	217.8	216.8	215.8	214.7
125°	244.1	243.6	242.4	241.2	240.0	238.8	237.7	236.9	236.0	235.2	234.4
127.5°	261.1	260.5	259.6	258.7	257.7	256.8	255.9	255.0	254.0	253.2	252.2
130°	272.0	271.3	270.6	269.9	269.2	268.5	267.6	266.6	265.6	264.6	263.5
132.5°	282.8	282.1	281.4	280.7	280.0	279.3	278.6	277.7	276.8	275.9	275.1
135°	297.9	297.3	296.7	296.1	295.5	295.0	294.2	293.1	292.1	291.1	290.1
137.5°	312.0	311.4	310.8	310.0	309.4	308.8	308.1	307.4	306.7	305.9	305.2
140°	321.2	320.6	319.9	319.2	318.5	317.8	317.2	316.6	316.1	315.7	315.1
142.5°	329.7	329.1	328.3	327.5	326.7	325.9	325.3	324.9	324.3	323.9	323.4
145°	341.5	341.1	340.0	338.9	337.8	336.7	336.2	336.3	336.4	336.4	336.4
147.5°	351.9	351.6	350.5	349.5	348.3	347.2	346.9	347.1	347.3	347.6	347.9
150°	358.2	357.8	356.8	355.8	354.7	353.7	353.4	353.8	354.3	354.7	355.2
152.5°	363.9	363.6	362.6	361.6	360.6	359.6	359.4	359.9	360.4	361.0	361.4
155°	371.8	371.3	370.6	369.8	369.1	368.3	368.2	368.7	369.3	369.9	370.5
157.5°	378.3	377.8	377.3	376.7	376.2	375.7	375.6	376.1	376.6	377.1	377.6
160°	382.1	381.7	381.4	380.9	380.6	380.2	380.2	380.6	380.9	381.4	381.7
162.5°	385.7	385.2	384.9	384.5	384.1	383.9	383.9	384.2	384.7	385.0	385.4
165°	389.9	389.5	389.3	389.1	389.0	388.8	388.9	389.2	389.6	390.0	390.4
167.5°	393.6	393.2	393.0	392.8	392.6	392.4	392.5	392.9	393.3	393.7	394.0
170°	395.5	395.0	394.8	394.8	394.6	394.5	394.6	395.0	395.4	395.7	396.2
172.5°	396.8	396.4	396.3	396.1	396.0	395.8	396.0	396.4	396.7	397.2	397.5
175°	398.3	397.9	397.8	397.6	397.5	397.3	397.5	398.0	398.4	398.9	399.3
177.5°	398.6	398.2	398.1	398.1	398.1	398.1	398.1	398.5	398.9	399.2	399.6
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1787.4	1790.1	1798.8	1807.7	1817.5	1820.2	1824.6	1820.8	1819.6	1830.1	1837.7
5°	1792.4	1804.7	1828.7	1850.6	1869.0	1882.0	1895.7	1901.1	1911.4	1925.7	1943.5
7.5°	1786.7	1810.6	1848.2	1880.1	1914.8	1939.8	1959.4	1976.0	1996.3	2023.5	2053.1
10°	1780.1	1812.3	1858.1	1897.0	1939.4	1971.5	1998.1	2024.1	2054.2	2091.8	2130.7
12.5°	1768.2	1806.2	1863.5	1909.6	1964.0	1995.6	2031.5	2087.6	2119.8	2172.1	2227.0
15°	1743.9	1786.3	1866.3	1923.0	1984.5	2044.6	2110.9	2164.2	2217.5	2248.3	2325.5
17.5°	1708.0	1770.2	1858.8	1924.9	2003.0	2097.7	2172.3	2232.7	2294.2	2344.0	2382.7
20°	1679.0	1746.7	1847.8	1927.1	2020.0	2121.8	2207.3	2268.8	2322.1	2363.7	2387.6
22.5°	1642.4	1727.5	1826.0	1918.9	2037.6	2138.2	2228.0	2276.4	2320.9	2341.4	2350.5
25°	1584.7	1687.2	1798.6	1912.1	2046.0	2152.6	2234.6	2264.0	2277.0	2257.2	2224.4
27.5°	1522.5	1636.8	1767.0	1899.2	2040.8	2143.3	2202.1	2197.4	2175.4	2111.3	2060.0
30°	1476.0	1601.8	1741.9	1886.1	2028.2	2128.0	2162.1	2128.0	2078.1	2006.3	1933.2
32.5°	1427.5	1557.6	1715.1	1867.5	2005.3	2093.0	2100.4	2041.7	1964.4	1882.8	1791.6
35°	1353.7	1494.5	1664.6	1826.0	1956.5	2011.8	1979.1	1875.2	1783.6	1672.2	1547.8
37.5°	1270.5	1425.9	1596.6	1765.1	1883.4	1897.8	1816.4	1707.0	1577.9	1447.0	1300.6
40°	1208.2	1372.9	1548.5	1718.7	1823.2	1808.2	1704.3	1584.0	1430.3	1270.3	1134.3
42.5°	1152.4	1317.1	1496.0	1662.9	1746.7	1705.4	1584.0	1436.5	1271.2	1120.6	996.0
45°	1055.8	1225.3	1408.5	1569.7	1617.6	1543.0	1382.4	1218.4	1055.8	930.1	831.7
47.5°	962.1	1129.6	1311.0	1452.7	1469.6	1369.5	1194.0	1025.2	885.4	783.0	713.5
50°	893.1	1061.2	1241.0	1367.4	1361.9	1241.0	1060.6	900.0	783.1	700.4	654.0
52.5°	831.3	990.2	1162.8	1277.7	1248.8	1116.9	944.7	802.1	706.1	641.4	599.3
55°	735.3	882.3	1046.2	1138.4	1085.2	939.0	793.4	678.6	607.5	559.0	526.2
57.5°	639.9	777.7	918.0	974.9	916.0	781.0	659.6	576.3	522.9	487.0	465.7
60°	580.9	701.2	826.2	875.4	805.0	684.7	589.1	514.6	471.5	442.1	423.0
62.5°	521.8	629.5	747.4	774.3	709.9	608.2	523.4	461.5	426.1	400.0	382.0
65°	441.5	529.6	619.1	636.9	577.5	498.8	431.9	391.6	360.2	341.0	326.6
67.5°	362.0	432.8	496.2	510.6	458.5	404.0	355.6	320.5	299.2	283.3	271.2
70°	315.0	371.0	423.0	434.6	393.0	344.4	307.6	279.5	260.4	246.7	235.1
72.5°	265.3	312.0	355.2	363.0	329.0	291.9	261.6	239.6	222.7	213.9	202.9
75°	203.0	230.3	263.8	265.8	243.3	220.7	197.5	183.2	174.2	163.4	157.8
77.5°	143.2	164.7	183.8	187.5	174.2	158.8	145.8	134.5	127.0	121.9	116.8
80°	109.3	126.4	134.6	139.4	129.8	118.9	111.4	103.9	99.1	95.7	92.3
82.5°	78.2	88.7	96.4	100.0	94.9	88.3	80.8	76.5	72.9	70.0	68.8
85°	39.6	44.4	49.2	50.6	49.2	46.5	42.4	42.4	40.3	39.6	39.6
87.5°	13.8	16.2	16.3	18.1	17.1	17.2	17.4	16.9	16.5	16.0	15.5
90°	1.0	1.7	2.4	3.1	3.7	4.2	4.7	5.3	5.8	6.1	6.4
92.5°	5.8	5.7	5.6	5.5	5.7	5.9	6.2	6.4	6.7	6.9	7.0
95°	16.6	14.5	12.4	10.3	9.5	9.9	10.3	10.8	11.2	11.6	11.9
97.5°	31.2	25.2	19.4	13.4	10.9	11.9	12.9	14.0	15.1	15.3	15.6
100°	42.3	33.4	24.7	16.0	12.0	13.2	14.3	15.3	16.4	16.9	17.5
102.5°	64.4	62.5	60.7	58.9	53.3	44.2	35.1	26.0	16.9	17.6	18.2
105°	89.5	91.5	93.5	95.3	87.6	70.1	52.6	35.0	17.6	18.3	19.0
107.5°	113.6	115.1	116.7	118.2	108.5	87.6	66.6	45.6	24.6	23.9	23.2
110°	129.0	130.5	131.8	133.1	124.5	106.0	87.5	68.9	50.5	44.1	37.6





TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	143.7	144.9	146.1	147.2	145.5	141.0	136.4	131.8	127.2	103.9	80.5
115°	166.8	168.0	169.1	170.1	171.5	173.1	174.7	176.3	177.9	148.2	118.6
117.5°	187.8	189.0	190.3	191.5	192.6	193.8	194.8	195.9	197.1	189.8	182.7
120°	202.8	203.8	204.7	205.6	206.7	207.9	209.0	210.2	211.3	212.1	212.9
122.5°	215.8	216.8	217.8	218.8	219.9	221.1	222.4	223.7	225.0	225.4	225.9
125°	235.2	236.0	236.9	237.7	238.8	240.0	241.2	242.4	243.6	244.1	244.5
127.5°	253.2	254.0	255.0	255.9	256.8	257.7	258.7	259.6	260.5	261.1	261.8
130°	264.6	265.6	266.6	267.6	268.5	269.2	269.9	270.6	271.3	272.0	272.7
132.5°	275.9	276.8	277.7	278.6	279.3	280.0	280.7	281.4	282.1	282.8	283.4
135°	291.1	292.1	293.1	294.2	295.0	295.5	296.1	296.7	297.3	297.9	298.5
137.5°	305.9	306.7	307.4	308.1	308.8	309.4	310.0	310.8	311.4	312.0	312.6
140°	315.7	316.1	316.6	317.2	317.8	318.5	319.2	319.9	320.6	321.2	321.7
142.5°	323.9	324.3	324.9	325.3	325.9	326.7	327.5	328.3	329.1	329.7	330.2
145°	336.4	336.4	336.3	336.2	336.7	337.8	338.9	340.0	341.1	341.5	342.0
147.5°	347.6	347.3	347.1	346.9	347.2	348.3	349.5	350.5	351.6	351.9	352.2
150°	354.7	354.3	353.8	353.4	353.7	354.7	355.8	356.8	357.8	358.2	358.6
152.5°	361.0	360.4	359.9	359.4	359.6	360.6	361.6	362.6	363.6	363.9	364.4
155°	369.9	369.3	368.7	368.2	368.3	369.1	369.8	370.6	371.3	371.8	372.1
157.5°	377.1	376.6	376.1	375.6	375.7	376.2	376.7	377.3	377.8	378.3	378.7
160°	381.4	380.9	380.6	380.2	380.2	380.6	380.9	381.4	381.7	382.1	382.5
162.5°	385.0	384.7	384.2	383.9	383.9	384.1	384.5	384.9	385.2	385.7	386.0
165°	390.0	389.6	389.2	388.9	388.8	389.0	389.1	389.3	389.5	389.9	390.4
167.5°	393.7	393.3	392.9	392.5	392.4	392.6	392.8	393.0	393.2	393.6	394.0
170°	395.7	395.4	395.0	394.6	394.5	394.6	394.8	394.8	395.0	395.5	395.9
172.5°	397.2	396.7	396.4	396.0	395.8	396.0	396.1	396.3	396.4	396.8	397.3
175°	398.9	398.4	398.0	397.5	397.3	397.5	397.6	397.8	397.9	398.3	398.8
177.5°	399.2	398.9	398.5	398.1	398.1	398.1	398.1	398.1	398.2	398.6	399.0
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1844.2	1851.9	1851.9	1853.0	1861.7	1860.6	1860.1
5°	1962.7	1974.2	1975.6	1987.9	1996.1	1993.3	1985.8
7.5°	2074.3	2095.9	2112.3	2121.5	2132.3	2138.9	2135.9
10°	2162.8	2194.3	2213.4	2226.4	2242.1	2253.7	2249.6
12.5°	2243.2	2280.6	2306.9	2329.1	2331.2	2346.1	2336.0
15°	2368.6	2408.2	2412.3	2428.7	2441.7	2440.3	2441.0
17.5°	2409.9	2422.7	2425.3	2425.6	2425.8	2421.0	2410.7
20°	2395.2	2390.4	2378.8	2369.9	2354.2	2352.2	2338.5
22.5°	2325.2	2310.1	2280.9	2261.6	2237.2	2230.8	2227.0
25°	2187.5	2153.9	2107.5	2063.1	2050.8	2026.9	2033.7
27.5°	1998.4	1946.2	1896.0	1859.8	1827.2	1791.4	1801.6
30°	1865.5	1806.8	1735.7	1681.1	1646.2	1612.0	1605.9
32.5°	1707.0	1621.0	1541.7	1493.5	1440.1	1418.5	1394.9
35°	1433.7	1349.6	1271.0	1203.4	1164.5	1134.3	1107.1
37.5°	1187.8	1091.1	1027.6	972.9	944.7	927.5	931.8
40°	1035.3	950.6	904.1	862.4	836.4	824.1	826.9
42.5°	911.8	848.3	810.0	781.5	763.2	756.3	754.7
45°	771.5	736.0	704.5	688.1	679.3	671.7	667.0
47.5°	675.8	646.8	629.1	619.4	611.6	604.0	603.8
50°	618.4	599.3	587.0	576.8	570.6	565.2	569.9
52.5°	574.7	557.2	544.9	535.7	533.4	528.5	528.3
55°	509.8	496.1	487.2	479.0	474.9	472.2	468.8
57.5°	450.8	437.7	429.5	424.4	416.6	413.8	412.8
60°	408.7	398.4	390.2	383.3	380.0	374.5	374.5
62.5°	369.8	359.6	352.0	346.7	341.2	338.9	339.5
65°	313.7	305.5	297.9	292.5	291.1	287.0	288.4
67.5°	262.0	256.5	248.6	245.6	243.0	240.9	239.2
70°	227.6	222.1	218.0	213.9	211.9	211.9	211.9
72.5°	198.6	192.0	189.6	184.4	185.6	183.4	181.2
75°	153.7	149.6	147.6	145.5	142.1	142.1	142.1
77.5°	113.2	111.9	109.5	107.3	106.5	105.8	106.0
80°	87.5	86.8	85.4	85.4	84.1	83.4	82.0
82.5°	67.2	65.5	64.6	64.1	63.8	63.7	63.4
85°	38.3	36.9	36.9	37.5	36.2	36.2	36.9
87.5°	16.1	16.1	15.7	15.7	16.2	15.8	15.8
90°	6.7	7.0	7.3	7.4	7.5	7.7	7.8
92.5°	7.2	7.3	7.5	7.6	7.7	7.7	7.8
95°	12.2	12.5	12.7	12.6	12.5	12.5	12.4
97.5°	15.8	16.1	16.2	16.3	16.4	16.5	16.6
100°	18.0	18.5	18.8	18.9	19.1	19.2	19.4
102.5°	18.9	19.5	20.0	20.2	20.3	20.5	20.7
105°	19.7	20.4	20.9	21.1	21.4	21.7	21.9
107.5°	22.5	21.8	21.5	21.8	22.0	22.3	22.6
110°	31.2	24.8	21.8	22.0	22.3	22.6	22.7



TEST NUMBER: P331420-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	57.2	33.8	22.2	22.4	22.6	22.8	23.0
115°	88.9	59.2	42.1	37.5	32.9	28.3	23.6
117.5°	175.5	168.4	157.2	142.0	126.9	111.7	96.6
120°	213.7	214.4	210.4	201.8	193.1	184.5	175.8
122.5°	226.3	226.8	226.1	224.5	222.8	221.1	219.5
125°	245.0	245.4	245.8	245.9	246.1	246.3	246.5
127.5°	262.4	263.1	263.4	263.5	263.5	263.5	263.6
130°	273.4	274.1	274.5	274.4	274.3	274.3	274.2
132.5°	283.9	284.5	284.8	284.7	284.7	284.6	284.5
135°	299.2	299.8	300.1	300.0	299.8	299.7	299.5
137.5°	313.3	313.9	314.1	313.9	313.7	313.4	313.3
140°	322.4	322.9	323.1	322.7	322.4	322.1	321.7
142.5°	330.7	331.3	331.4	331.0	330.7	330.4	330.0
145°	342.4	342.9	343.0	342.6	342.3	342.0	341.6
147.5°	352.6	352.9	352.9	352.7	352.4	352.1	351.9
150°	358.9	359.4	359.4	359.1	358.7	358.4	358.1
152.5°	364.7	365.1	365.1	364.6	364.3	363.8	363.4
155°	372.5	372.9	372.8	372.3	371.8	371.3	370.8
157.5°	379.2	379.5	379.5	379.0	378.5	378.0	377.6
160°	382.9	383.3	383.3	382.8	382.4	381.9	381.5
162.5°	386.5	386.9	386.9	386.3	385.8	385.2	384.7
165°	390.8	391.3	391.3	390.8	390.4	389.9	389.5
167.5°	394.5	394.9	394.8	394.3	393.7	393.2	392.5
170°	396.4	396.8	396.7	396.2	395.6	395.0	394.4
172.5°	397.7	398.1	398.1	397.5	397.0	396.4	395.8
175°	399.2	399.7	399.6	399.0	398.3	397.6	397.0
177.5°	399.3	399.7	399.6	399.1	398.7	398.2	397.8
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4

(END OF REPORT)