

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331428-940

Luminaire Tested: **SA2XXDIP-C1005D330U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331428-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D330U940-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4757.4 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331428-940
CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331428-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	80	80	80	76
1	104	99	95	91	98	95	91	88	86	83	81	78	76	74	71	69	68	64
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	62	60	57	54
3	86	76	69	62	82	73	66	60	67	61	56	61	56	52	55	52	49	45
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	39
5	73	60	52	46	69	58	50	44	53	47	42	49	43	39	45	40	37	34
6	67	54	46	40	64	52	44	39	48	41	36	44	39	34	40	36	32	30
7	62	49	41	35	59	47	40	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	29	25	31	27	23	21
10	50	38	30	25	48	37	29	25	34	28	24	32	26	22	29	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22946	22946	22946
5°	23034	22702	22835
10°	22897	22471	22584
15°	22614	22181	22158
20°	22213	21742	21720
25°	21814	21205	21205
30°	21300	20713	20534
35°	20820	20120	19825
40°	20219	19530	19153
45°	19628	18941	18472
50°	18982	18331	17678
55°	18311	17619	16963
60°	17563	16769	16152
65°	16756	15924	15194
70°	15739	14903	14195
75°	14323	13724	13381
80°	12710	12329	11688
85°	10374	9874	8855



TEST NUMBER: P331428-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.6	2.8
10°-20°	376.0	7.9
20°-30°	552.7	11.6
30°-40°	642.0	13.5
40°-50°	641.3	13.5
50°-60°	559.3	11.8
60°-70°	413.6	8.7
70°-80°	234.2	4.9
80°-90°	64.5	1.4
90°-100°	65.5	1.4
100°-110°	222.3	4.7
110°-120°	236.2	5.0
120°-130°	194.4	4.1
130°-140°	156.1	3.3
140°-150°	118.0	2.5
150°-160°	82.9	1.7
160°-170°	48.8	1.0
170°-180°	15.9	0.3
0°-30°	1062.4	22.3
0°-40°	1704.4	35.8
0°-60°	2905.1	61.1
0°-90°	3617.3	76.0
90°-120°	524.0	11.0
90°-150°	992.5	20.9
90°-180°	1140.0	24.0
0°-180°	4757.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1421	1421	1421	1421	1421	
5°	1421	1415	1401	1411	1409	135
15°	1353	1344	1327	1332	1326	381
25°	1224	1213	1190	1193	1190	563
35°	1056	1042	1021	1013	1006	659
45°	860	849	830	815	809	663
55°	650	642	626	610	603	581
65°	439	430	417	405	398	434
75°	230	227	220	212	214	245
85°	56	55	53	49	48	64
90°	0	4	11	10	10	3
95°	11	27	124	47	36	12
105°	38	58	233	417	355	41
115°	68	86	195	403	467	67
125°	94	112	188	327	379	84
135°	111	132	186	274	314	86
145°	127	146	185	229	251	79
155°	144	155	179	203	211	66
165°	157	162	172	182	185	44
175°	164	164	165	167	167	16
180°	164	164	164	164	164	



TEST NUMBER: P331428-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1427.8	1426.6	1425.4	1424.2	1422.9	1421.0	1418.4	1415.7	1413.0	1410.3	1412.7
5°	1421.2	1420.0	1418.8	1417.6	1416.4	1414.1	1410.8	1407.4	1404.1	1400.7	1403.2
7.5°	1408.6	1406.8	1404.9	1403.0	1401.1	1398.5	1395.1	1391.7	1388.3	1384.9	1387.3
10°	1396.6	1394.5	1392.4	1390.3	1388.1	1385.3	1381.6	1378.0	1374.3	1370.6	1373.1
12.5°	1380.3	1378.3	1376.4	1374.6	1372.7	1369.9	1366.3	1362.6	1359.1	1355.4	1357.1
15°	1352.9	1351.1	1349.2	1347.5	1345.6	1342.7	1338.8	1334.8	1330.9	1327.0	1328.2
17.5°	1317.9	1316.1	1314.3	1312.4	1310.6	1307.7	1303.7	1299.7	1295.7	1291.7	1293.1
20°	1292.8	1290.9	1289.1	1287.3	1285.5	1282.5	1278.2	1274.0	1269.7	1265.4	1266.3
22.5°	1267.7	1265.1	1262.6	1260.0	1257.4	1254.2	1250.2	1246.2	1242.2	1238.1	1238.3
25°	1224.5	1222.0	1219.6	1217.2	1214.8	1210.9	1205.8	1200.6	1195.4	1190.3	1190.9
27.5°	1175.3	1173.0	1170.9	1168.7	1166.5	1163.4	1159.3	1155.2	1151.2	1147.1	1146.2
30°	1142.5	1140.1	1137.6	1135.1	1132.7	1129.3	1124.7	1120.2	1115.6	1111.0	1110.1
32.5°	1107.5	1105.5	1103.6	1101.6	1099.7	1096.4	1091.5	1086.7	1081.9	1077.1	1075.5
35°	1056.3	1053.3	1050.3	1047.2	1044.2	1040.3	1035.4	1030.6	1025.7	1020.8	1019.0
37.5°	998.7	996.0	993.4	990.7	988.0	984.3	979.4	974.6	969.6	964.8	962.5
40°	959.3	956.9	954.5	952.1	949.6	946.0	941.1	936.3	931.4	926.6	923.8
42.5°	921.0	918.6	916.2	913.8	911.3	907.7	902.9	898.0	893.1	888.2	885.3
45°	859.6	857.5	855.3	853.2	851.0	847.7	843.2	838.7	834.1	829.5	826.2
47.5°	798.3	796.4	794.3	792.4	790.3	786.9	782.2	777.5	772.8	768.0	764.5
50°	755.7	754.2	752.7	751.2	749.7	746.7	742.5	738.2	734.0	729.8	725.5
52.5°	714.2	712.2	710.2	708.2	706.1	703.1	699.1	695.1	691.2	687.2	683.6
55°	650.5	648.6	646.8	645.1	643.2	640.4	636.9	633.2	629.5	625.9	622.2
57.5°	586.6	585.1	583.6	582.2	580.7	578.0	574.0	570.0	566.0	562.0	558.4
60°	543.9	542.7	541.4	540.3	539.0	536.3	532.1	527.8	523.5	519.3	515.9
62.5°	502.4	500.4	498.5	496.5	494.5	492.0	488.7	485.4	482.1	478.8	475.7
65°	438.6	436.8	435.1	433.2	431.4	428.9	425.9	422.8	419.8	416.8	414.1
67.5°	373.9	372.5	371.0	369.5	368.1	366.0	363.2	360.5	357.8	355.1	352.9
70°	333.4	332.3	331.0	329.8	328.6	326.6	323.9	321.1	318.4	315.7	313.5
72.5°	291.9	290.7	289.4	288.3	287.0	285.5	283.8	282.0	280.3	278.5	276.3
75°	229.6	229.0	228.4	227.7	227.1	226.0	224.5	223.0	221.5	220.0	218.2
77.5°	173.8	172.8	171.7	170.8	169.7	168.9	168.3	167.6	167.0	166.5	165.5
80°	136.7	136.3	136.1	135.7	135.5	135.0	134.4	133.8	133.1	132.6	131.6
82.5°	101.7	101.7	101.6	101.5	101.4	101.2	100.9	100.5	100.1	99.8	98.6
85°	56.0	55.7	55.5	55.1	54.8	54.5	54.2	53.9	53.6	53.3	52.3
87.5°	19.7	19.4	19.2	18.8	18.5	18.2	18.0	18.0	17.8	17.5	16.7
90°	0.4	1.2	2.5	3.1	3.7	4.7	6.3	8.5	10.4	10.7	10.4
92.5°	3.8	5.5	7.8	9.2	11.3	14.3	21.4	31.5	40.4	40.9	34.6
95°	11.1	12.3	15.4	18.3	23.3	30.9	45.4	72.8	109.3	123.5	108.1
97.5°	17.9	19.6	23.0	27.3	33.1	41.6	59.8	98.1	158.8	210.8	221.1
100°	24.3	25.2	28.0	33.1	39.4	48.2	64.9	103.3	171.4	248.9	294.3
102.5°	30.1	30.8	33.6	38.6	45.2	54.0	69.5	103.6	166.6	250.1	321.5
105°	38.4	39.7	41.9	46.6	53.6	62.4	77.2	105.2	157.2	233.4	317.3
107.5°	47.5	48.5	50.6	55.0	61.9	70.8	85.2	109.6	152.6	215.5	289.6
110°	53.6	54.8	56.7	60.8	67.4	76.6	90.4	113.1	151.6	207.0	272.2



TEST NUMBER: P331428-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	59.1	60.4	62.5	66.3	72.7	82.1	95.5	116.9	151.8	201.4	260.1
115°	67.8	69.3	71.2	75.0	81.3	89.8	103.3	122.5	153.1	195.4	245.1
117.5°	76.7	77.9	79.8	83.2	89.3	98.1	110.6	128.6	155.4	192.3	235.7
120°	82.2	83.5	85.4	88.2	94.5	103.3	115.7	132.7	156.9	190.6	230.6
122.5°	87.6	88.5	90.4	93.5	99.8	108.9	120.4	136.2	158.6	189.6	226.3
125°	94.5	95.5	97.4	101.1	107.5	116.3	127.6	141.8	161.3	187.8	220.3
127.5°	100.0	101.3	104.0	108.2	114.1	123.2	134.3	147.0	164.0	186.7	214.5
130°	103.3	104.6	107.7	112.2	118.5	127.2	138.3	150.3	166.0	186.2	210.8
132.5°	106.4	107.9	111.3	115.9	122.5	131.3	141.9	153.6	168.1	185.9	207.8
135°	110.9	112.2	115.9	120.6	128.0	136.7	146.9	157.8	170.5	185.6	203.5
137.5°	115.2	116.7	120.5	125.6	132.7	140.9	150.9	161.1	172.6	185.5	200.5
140°	118.5	119.8	123.5	128.6	135.5	143.7	153.1	162.9	173.6	185.3	198.8
142.5°	121.7	122.8	126.3	131.3	138.0	145.7	154.9	164.4	174.3	185.3	197.1
145°	126.6	128.0	131.1	135.8	142.1	149.0	157.6	166.4	175.1	184.6	194.7
147.5°	132.0	132.9	135.9	140.3	145.5	151.7	159.7	167.5	175.4	183.5	192.3
150°	135.5	136.4	138.9	143.0	147.8	153.5	160.7	167.9	175.1	182.7	190.3
152.5°	139.0	139.5	142.0	145.5	150.1	155.2	161.7	168.2	174.7	181.5	188.5
155°	144.0	144.3	146.2	149.6	153.1	157.8	163.2	168.5	173.9	179.2	185.3
157.5°	148.1	148.5	150.0	153.0	155.8	159.7	164.3	168.5	172.5	177.0	182.2
160°	150.9	151.2	152.5	155.0	157.6	161.0	164.8	168.5	171.7	175.5	179.9
162.5°	153.7	153.5	154.8	156.8	159.1	161.8	165.1	168.3	170.9	174.2	177.9
165°	156.9	156.6	157.2	159.1	160.7	162.6	165.4	167.6	169.5	171.7	174.5
167.5°	159.5	159.2	159.7	161.0	162.1	163.3	165.3	167.2	168.1	169.5	171.3
170°	161.3	160.7	161.0	161.9	162.6	163.5	165.1	166.7	167.3	168.3	169.5
172.5°	162.3	161.9	161.8	162.7	163.1	163.8	164.9	165.9	166.3	166.7	167.7
175°	163.5	163.2	162.9	163.5	163.5	163.8	164.4	165.1	164.8	165.1	165.4
177.5°	164.1	163.5	163.4	163.8	163.8	163.8	164.1	164.6	164.1	163.8	164.1
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8



TEST NUMBER: P331428-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1415.1	1417.6	1420.0	1421.0	1420.5	1420.0	1419.5	1419.1
5°	1405.6	1408.0	1410.4	1411.4	1410.8	1410.2	1409.5	1408.9
7.5°	1389.7	1392.1	1394.6	1395.5	1394.8	1394.2	1393.5	1392.9
10°	1375.6	1378.0	1380.4	1381.2	1380.3	1379.3	1378.4	1377.5
12.5°	1358.8	1360.5	1362.2	1362.7	1362.0	1361.4	1360.7	1360.0
15°	1329.4	1330.6	1331.8	1331.7	1330.2	1328.6	1327.1	1325.6
17.5°	1294.5	1295.9	1297.3	1297.3	1295.7	1294.3	1292.9	1291.4
20°	1267.3	1268.2	1269.1	1268.9	1267.7	1266.5	1265.3	1264.1
22.5°	1238.5	1238.7	1238.9	1238.6	1237.9	1237.2	1236.4	1235.6
25°	1191.5	1192.1	1192.8	1192.8	1192.1	1191.5	1190.9	1190.3
27.5°	1145.3	1144.3	1143.4	1142.3	1140.9	1139.3	1137.9	1136.5
30°	1109.2	1108.3	1107.4	1106.3	1105.1	1103.8	1102.7	1101.4
32.5°	1073.9	1072.2	1070.6	1069.2	1067.9	1066.8	1065.5	1064.3
35°	1017.2	1015.4	1013.5	1011.9	1010.4	1008.9	1007.3	1005.8
37.5°	960.3	958.1	955.8	954.0	952.5	951.0	949.6	948.2
40°	921.0	918.4	915.6	913.6	912.4	911.2	910.0	908.7
42.5°	882.3	879.3	876.4	874.1	872.4	870.7	869.0	867.2
45°	822.9	819.5	816.2	813.9	812.6	811.5	810.2	809.0
47.5°	761.0	757.4	753.9	751.3	749.5	747.8	746.0	744.2
50°	721.2	717.0	712.7	709.9	708.4	706.9	705.3	703.8
52.5°	680.1	676.5	673.1	670.3	668.2	666.3	664.2	662.3
55°	618.6	614.9	611.4	608.8	607.3	605.7	604.2	602.6
57.5°	554.7	551.2	547.6	545.2	544.1	543.0	541.8	540.6
60°	512.6	509.3	506.0	503.8	502.9	502.0	501.1	500.2
62.5°	472.7	469.6	466.5	464.3	463.2	462.0	460.8	459.7
65°	411.3	408.6	405.9	403.8	402.3	400.7	399.2	397.7
67.5°	350.8	348.7	346.5	344.8	343.7	342.4	341.3	340.0
70°	311.4	309.3	307.2	305.5	304.3	303.1	301.8	300.7
72.5°	274.3	272.2	270.0	268.5	267.5	266.5	265.6	264.6
75°	216.4	214.5	212.8	212.1	212.8	213.3	213.9	214.5
77.5°	164.6	163.7	162.8	161.9	161.0	160.2	159.3	158.5
80°	130.7	129.8	128.9	128.1	127.5	127.0	126.4	125.7
82.5°	97.5	96.3	95.1	94.5	94.3	94.3	94.2	94.0
85°	51.5	50.6	49.7	49.0	48.8	48.4	48.2	47.8
87.5°	15.9	15.0	14.4	14.0	13.7	13.5	13.3	13.0
90°	10.1	9.5	10.1	10.4	10.4	10.4	10.4	10.4
92.5°	27.5	23.5	21.0	19.0	18.7	17.7	17.9	17.5
95°	82.6	63.3	50.1	43.2	39.1	36.6	35.6	35.9
97.5°	192.6	157.6	123.5	100.8	85.7	77.9	73.4	70.7
100°	287.7	248.6	205.5	167.3	141.2	127.6	118.5	112.8
102.5°	349.9	341.1	309.5	269.1	240.7	217.6	206.2	198.5
105°	382.8	418.4	422.5	412.1	392.5	373.0	359.4	355.1
107.5°	359.1	412.8	445.5	460.7	463.2	462.2	459.4	453.6
110°	338.7	395.1	435.4	461.3	474.8	480.8	483.7	483.3



TEST NUMBER: P331428-940

CATALOG NUMBER: SA2XXDIP-C1005D330U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	320.0	374.2	417.2	446.9	465.7	475.7	481.1	482.8
115°	297.1	345.6	386.9	419.4	441.8	456.2	464.4	467.3
117.5°	279.8	322.4	359.9	390.3	413.1	428.5	437.0	439.4
120°	271.3	310.3	343.8	372.4	394.5	409.3	418.4	421.6
122.5°	264.5	300.2	331.9	357.8	377.6	392.2	400.3	402.9
125°	254.6	287.0	314.8	338.4	356.7	368.6	376.5	379.1
127.5°	244.8	274.2	300.3	322.1	338.0	349.3	356.1	358.1
130°	238.5	265.6	290.5	311.3	326.7	337.4	343.8	346.3
132.5°	232.5	257.5	280.4	300.0	315.1	325.8	331.6	333.9
135°	224.0	244.8	265.6	283.2	296.8	307.2	312.9	314.1
137.5°	217.3	234.7	251.2	266.5	278.9	287.8	292.8	294.7
140°	212.9	228.1	242.6	256.5	266.5	274.7	279.5	281.3
142.5°	209.5	222.3	234.8	246.4	255.9	263.4	267.6	268.0
145°	204.5	214.9	224.6	233.8	241.3	246.7	249.9	250.7
147.5°	200.6	208.8	216.4	223.1	229.3	233.6	235.8	236.4
150°	197.9	204.8	211.4	217.0	221.8	225.6	227.5	227.8
152.5°	195.1	201.5	207.1	212.0	215.8	219.0	220.4	220.5
155°	191.3	196.3	201.0	204.5	207.9	210.2	211.4	210.8
157.5°	186.8	191.0	194.9	197.7	200.1	202.0	202.5	202.5
160°	184.0	187.4	190.9	193.1	195.4	196.9	197.2	197.2
162.5°	181.2	184.2	187.2	188.9	191.1	192.2	192.4	192.2
165°	177.1	179.2	181.5	182.7	184.0	185.3	185.3	184.9
167.5°	173.1	174.8	176.3	177.5	178.0	178.7	178.6	178.3
170°	171.1	172.0	173.3	173.9	174.2	175.1	174.9	174.2
172.5°	168.8	169.5	170.5	170.9	171.2	171.7	171.3	170.9
175°	166.4	166.7	167.0	167.3	167.3	167.6	167.3	166.7
177.5°	164.6	164.6	164.9	164.9	164.9	164.9	164.6	164.1
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8

(END OF REPORT)