

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332917-830

Luminaire Tested: **SA4XXRDIP-C575D1035U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332917-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C575D1035U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5591.7 lumens  
Efficiency: N/A  
Efficacy: 125.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332917-830

CATALOG NUMBER: SA4XXRDIP-C575D1035U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332917-830

CATALOG NUMBER: SA4XXRDIP-C575D1035U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40				40
1	96	91	88	84	87	83	80	77	68	66	64	54	53	52	41	41	40	34				34
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34	29				29
3	80	71	63	58	72	64	58	53	53	49	45	43	39	37	33	31	29	24				24
4	73	62	55	49	66	57	51	45	47	42	38	38	34	32	29	27	25	21				21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	27	24	22	18				18
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16				16
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17	15				15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13				13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	17	15	13	11				11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7733	7733	7733
5°	7750	7656	7703
10°	7702	7564	7564
15°	7614	7405	7350
20°	7491	7196	7064
25°	7337	6951	6774
30°	7185	6693	6413
35°	7019	6427	6050
40°	6817	6122	5658
45°	6632	5819	5259
50°	6420	5471	4835
55°	6194	5111	4376
60°	5945	4713	3907
65°	5717	4216	3446
70°	5384	3670	2924
75°	4966	3044	2380
80°	4328	2320	2180
85°	3668	2103	1973



TEST NUMBER: P332917-830

CATALOG NUMBER: SA4XXRDIP-C575D1035U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.0	1.6
10°-20°	250.9	4.5
20°-30°	362.3	6.5
30°-40°	410.7	7.3
40°-50°	396.6	7.1
50°-60°	329.8	5.9
60°-70°	227.7	4.1
70°-80°	115.4	2.1
80°-90°	33.3	0.6
90°-100°	80.2	1.4
100°-110°	237.7	4.3
110°-120°	403.4	7.2
120°-130°	531.9	9.5
130°-140°	597.4	10.7
140°-150°	587.0	10.5
150°-160°	493.7	8.8
160°-170°	328.5	5.9
170°-180°	115.0	2.1
0°-30°	703.2	12.6
0°-40°	1113.9	19.9
0°-60°	1840.3	32.9
0°-90°	2216.7	39.6
90°-120°	721.3	12.9
90°-150°	2437.7	43.6
90°-180°	3375.0	60.4
0°-180°	5591.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	958	958	958	958	958	
5°	956	953	945	952	951	91
15°	911	904	886	884	879	257
25°	824	810	780	768	760	379
35°	712	688	652	628	614	445
45°	581	553	510	475	461	448
55°	440	410	363	326	311	394
65°	299	267	221	190	180	295
75°	159	132	98	81	76	168
85°	40	26	23	21	21	45
90°	3	13	21	26	28	5
95°	56	65	72	74	74	63
105°	219	220	224	227	230	233
115°	410	410	408	407	406	404
125°	597	597	596	595	593	532
135°	770	776	776	774	772	596
145°	936	940	941	940	937	586
155°	1072	1072	1072	1075	1072	493
165°	1168	1165	1163	1168	1165	329
175°	1215	1210	1209	1215	1209	115
180°	1216	1216	1216	1216	1216	



TEST NUMBER: P332917-830

CATALOG NUMBER: SA4XXRDIP-C575D1035U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	960.3	959.7	959.2	958.7	958.2	957.2	955.7	954.3	952.8	951.4	952.8
5°	956.4	955.7	955.1	954.4	953.9	952.5	950.6	948.6	946.6	944.7	946.3
7.5°	947.7	947.1	946.4	945.7	945.0	943.4	940.8	938.3	935.8	933.2	934.2
10°	939.5	938.8	937.9	937.1	936.3	934.4	931.5	928.5	925.6	922.7	923.3
12.5°	929.0	928.0	927.1	926.1	925.2	923.0	919.5	916.1	912.7	909.2	909.6
15°	911.0	909.5	908.0	906.5	905.0	902.3	898.2	894.2	890.0	886.0	885.7
17.5°	889.1	886.9	884.9	882.7	880.6	877.1	872.2	867.3	862.4	857.5	856.7
20°	872.0	870.0	867.8	865.7	863.6	859.8	854.2	848.7	843.1	837.6	836.3
22.5°	853.3	850.9	848.6	846.1	843.8	839.6	833.7	827.7	821.8	815.9	813.9
25°	823.7	820.8	817.7	814.8	811.9	807.1	800.4	793.7	787.0	780.4	777.6
27.5°	792.6	788.9	785.2	781.6	777.8	772.4	765.3	758.2	751.0	743.9	740.5
30°	770.8	766.8	762.7	758.7	754.6	748.7	741.0	733.4	725.7	718.0	714.0
32.5°	748.0	743.4	738.8	734.1	729.6	723.3	715.4	707.5	699.6	691.6	686.9
35°	712.2	707.0	701.7	696.5	691.4	684.7	676.5	668.4	660.2	652.1	646.5
37.5°	673.9	668.5	663.2	657.8	652.3	645.2	636.1	627.1	618.1	609.1	602.9
40°	646.9	641.5	636.1	630.7	625.4	618.0	608.8	599.5	590.2	580.9	574.0
42.5°	621.0	615.5	609.8	604.2	598.5	590.9	581.2	571.5	561.8	552.1	545.2
45°	580.9	574.9	568.8	562.8	556.8	548.8	539.0	529.3	519.5	509.7	501.7
47.5°	539.4	533.2	526.9	520.7	514.4	506.2	496.1	486.0	475.8	465.6	457.3
50°	511.2	504.8	498.5	492.1	485.8	477.4	466.9	456.6	446.1	435.6	427.5
52.5°	482.5	476.3	470.0	463.8	457.5	449.1	438.4	427.7	417.0	406.3	398.0
55°	440.1	433.6	427.1	420.5	414.0	405.4	394.8	384.3	373.6	363.1	354.6
57.5°	398.1	391.3	384.6	377.8	371.0	362.4	351.9	341.5	331.1	320.7	312.1
60°	368.2	361.7	355.2	348.6	342.1	333.7	323.2	312.7	302.4	291.9	283.4
62.5°	341.2	334.4	327.6	320.8	314.1	305.4	294.6	284.0	273.2	262.6	254.8
65°	299.3	292.3	285.2	278.2	271.2	262.5	252.0	241.7	231.2	220.7	213.8
67.5°	255.7	248.9	242.2	235.5	228.8	220.6	210.9	201.2	191.6	181.9	175.9
70°	228.1	221.2	214.4	207.5	200.8	192.7	183.3	174.1	164.8	155.5	150.1
72.5°	198.8	192.6	186.3	180.2	174.0	166.5	157.8	149.0	140.2	131.4	126.9
75°	159.2	153.2	147.1	141.1	135.1	128.2	120.6	112.8	105.2	97.6	93.8
77.5°	118.9	113.9	108.8	103.6	98.5	92.8	86.6	80.5	74.3	68.1	65.9
80°	93.1	88.4	83.7	79.0	74.3	69.5	64.6	59.7	54.8	49.9	49.4
82.5°	70.9	66.5	62.2	57.9	53.5	50.0	47.1	44.3	41.6	38.7	38.4
85°	39.6	36.4	33.1	29.8	26.6	24.7	24.2	23.8	23.2	22.7	22.4
87.5°	14.0	13.5	12.9	12.3	11.7	11.5	11.8	12.0	12.2	12.3	12.4
90°	2.8	5.1	7.4	9.7	12.1	14.0	15.6	17.3	19.0	20.7	22.0
92.5°	20.2	22.8	25.4	28.0	30.6	32.6	33.7	34.9	36.1	37.2	38.0
95°	56.5	58.3	60.2	62.1	64.0	65.6	67.1	68.6	70.0	71.5	72.1
97.5°	98.6	100.1	101.6	103.1	104.6	106.2	107.9	109.6	111.4	113.1	113.9
100°	131.7	132.5	133.4	134.2	135.1	136.4	138.3	140.2	142.0	143.9	144.4
102.5°	166.4	166.6	167.0	167.3	167.7	168.7	170.4	172.1	173.8	175.6	176.2
105°	219.2	219.4	219.6	219.8	220.1	220.6	221.4	222.3	223.1	223.9	224.5
107.5°	274.8	274.9	275.2	275.5	275.7	275.9	276.1	276.2	276.3	276.4	277.0
110°	312.4	312.7	313.2	313.6	314.1	314.1	313.9	313.7	313.5	313.3	312.8



TEST NUMBER: P332917-830

CATALOG NUMBER: SA4XXRDIP-C575D1035U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	351.5	351.6	351.7	351.8	351.9	351.7	351.3	350.9	350.5	350.2	350.1
115°	410.2	410.2	410.2	410.2	410.2	410.0	409.5	409.2	408.7	408.3	408.1
117.5°	465.5	465.7	465.8	466.0	466.2	466.1	465.8	465.5	465.2	465.0	464.2
120°	502.4	503.2	504.1	504.9	505.8	505.9	505.2	504.5	504.0	503.3	502.3
122.5°	540.7	541.1	541.4	541.8	542.1	542.2	541.9	541.5	541.2	540.9	540.3
125°	597.4	597.4	597.4	597.4	597.4	597.3	597.1	596.9	596.6	596.4	596.1
127.5°	648.8	649.4	650.0	650.6	651.3	651.4	651.1	650.7	650.4	650.1	649.7
130°	684.9	685.5	686.2	686.7	687.4	687.7	687.7	687.7	687.7	687.7	687.3
132.5°	721.8	722.3	722.6	723.1	723.6	723.8	723.6	723.4	723.2	723.1	722.6
135°	770.5	771.8	773.0	774.3	775.5	776.2	776.2	776.2	776.2	776.2	775.7
137.5°	823.6	824.2	824.7	825.3	826.0	826.3	826.7	827.1	827.4	827.7	827.2
140°	858.9	859.3	859.8	860.2	860.6	860.8	860.8	860.8	860.8	860.8	860.6
142.5°	891.3	891.7	892.1	892.6	893.0	893.1	893.0	892.8	892.6	892.4	892.4
145°	936.0	936.9	937.7	938.6	939.4	939.9	940.2	940.4	940.6	940.8	940.6
147.5°	980.5	981.5	982.5	983.5	984.5	985.0	984.8	984.6	984.4	984.3	984.1
150°	1007.6	1008.4	1009.3	1010.1	1011.0	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3
152.5°	1033.2	1033.7	1034.2	1034.7	1035.2	1035.5	1035.7	1035.9	1036.0	1036.1	1036.7
155°	1072.5	1072.5	1072.5	1072.5	1072.5	1072.4	1072.1	1072.0	1071.8	1071.6	1072.4
157.5°	1105.6	1105.2	1104.8	1104.5	1104.1	1103.9	1103.8	1103.8	1103.8	1103.7	1104.4
160°	1125.2	1124.9	1124.7	1124.5	1124.4	1124.2	1123.9	1123.7	1123.5	1123.3	1123.9
162.5°	1143.2	1142.7	1142.2	1141.6	1141.0	1140.7	1140.5	1140.3	1140.1	1139.8	1140.9
165°	1167.5	1166.9	1166.3	1165.6	1165.0	1164.5	1164.0	1163.7	1163.2	1162.8	1164.0
167.5°	1186.2	1185.2	1184.4	1183.6	1182.6	1182.2	1182.2	1182.3	1182.3	1182.4	1183.6
170°	1196.7	1195.6	1194.6	1193.5	1192.5	1192.0	1192.3	1192.5	1192.7	1192.9	1194.2
172.5°	1204.2	1203.3	1202.5	1201.6	1200.7	1200.2	1200.3	1200.3	1200.4	1200.4	1201.8
175°	1214.6	1213.5	1212.5	1211.4	1210.4	1209.8	1209.6	1209.3	1209.1	1208.9	1210.4
177.5°	1218.0	1217.1	1216.3	1215.4	1214.6	1214.2	1214.2	1214.2	1214.2	1214.2	1215.3
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4



TEST NUMBER: P332917-830

CATALOG NUMBER: SA4XXRDIP-C575D1035U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	954.3	955.7	957.2	957.8	957.7	957.5	957.4	957.3
5°	947.9	949.6	951.2	951.9	951.5	951.2	950.8	950.6
7.5°	935.3	936.3	937.5	937.6	937.2	936.6	936.1	935.6
10°	924.0	924.6	925.3	925.3	924.6	924.0	923.3	922.7
12.5°	909.9	910.3	910.8	910.5	909.6	908.7	907.8	906.8
15°	885.3	885.0	884.7	884.0	882.8	881.7	880.5	879.4
17.5°	855.7	854.8	853.8	852.5	850.8	849.1	847.3	845.6
20°	835.0	833.7	832.4	830.7	828.6	826.4	824.3	822.2
22.5°	812.0	810.0	808.0	806.3	804.5	802.8	801.1	799.3
25°	774.9	772.0	769.3	767.1	765.4	763.8	762.2	760.5
27.5°	737.0	733.6	730.2	727.3	724.9	722.6	720.3	717.9
30°	709.9	705.8	701.7	698.4	695.8	693.1	690.6	688.0
32.5°	682.2	677.5	672.7	669.1	666.7	664.2	661.7	659.2
35°	640.9	635.4	629.9	625.7	622.7	619.7	616.8	613.9
37.5°	596.6	590.5	584.3	579.8	576.7	573.8	570.9	568.0
40°	567.2	560.3	553.5	548.7	545.6	542.7	539.8	536.9
42.5°	538.2	531.2	524.2	519.2	516.1	513.1	510.0	507.0
45°	493.8	485.8	477.8	472.3	469.4	466.5	463.5	460.6
47.5°	449.0	440.7	432.4	426.7	423.5	420.3	417.1	413.8
50°	419.3	411.2	403.0	397.5	394.4	391.2	388.1	385.0
52.5°	389.7	381.4	373.2	367.5	364.2	361.0	357.8	354.6
55°	346.1	337.6	329.1	323.4	320.3	317.2	314.1	310.9
57.5°	303.4	294.8	286.3	280.8	278.4	276.1	273.7	271.4
60°	274.9	266.5	258.0	252.5	249.9	247.2	244.7	242.0
62.5°	246.9	239.1	231.3	226.3	224.2	222.2	220.1	218.0
65°	206.8	199.7	192.7	188.2	186.3	184.4	182.4	180.4
67.5°	169.8	163.8	157.8	153.7	151.6	149.4	147.2	145.1
70°	144.8	139.4	133.9	130.4	128.8	127.2	125.5	123.9
72.5°	122.2	117.6	113.0	110.0	108.5	107.0	105.5	104.0
75°	90.0	86.3	82.6	80.2	79.2	78.2	77.3	76.3
77.5°	63.7	61.5	59.3	58.1	57.8	57.5	57.2	56.9
80°	48.9	48.4	47.9	47.6	47.4	47.2	47.1	46.9
82.5°	38.0	37.6	37.3	37.0	36.9	36.7	36.6	36.4
85°	22.1	21.8	21.4	21.3	21.3	21.3	21.3	21.3
87.5°	12.6	12.7	12.8	13.0	13.2	13.5	13.7	13.9
90°	23.2	24.5	25.7	26.6	27.0	27.4	27.8	28.2
92.5°	38.7	39.5	40.2	40.8	41.0	41.3	41.6	41.8
95°	72.8	73.4	74.0	74.4	74.4	74.4	74.4	74.4
97.5°	114.6	115.4	116.1	116.5	116.5	116.5	116.5	116.5
100°	144.8	145.2	145.6	145.8	145.8	145.8	145.8	145.8
102.5°	176.7	177.3	177.9	178.2	178.4	178.6	178.8	178.9
105°	225.2	225.8	226.4	227.1	227.6	228.3	228.9	229.5
107.5°	277.6	278.1	278.7	279.0	279.0	278.9	278.9	278.8
110°	312.5	312.0	311.6	311.7	312.4	312.9	313.6	314.2





TEST NUMBER: P332917-830

CATALOG NUMBER: SA4XXRDIP-C575D1035U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	350.0	349.9	349.9	349.9	350.0	350.1	350.2	350.3
115°	407.8	407.6	407.5	407.3	407.1	406.8	406.6	406.4
117.5°	463.5	462.8	462.1	461.6	461.1	460.7	460.2	459.9
120°	501.2	500.2	499.2	498.8	499.3	499.6	500.1	500.5
122.5°	539.5	538.9	538.1	537.3	536.6	535.8	535.1	534.3
125°	595.6	595.2	594.7	594.4	594.0	593.5	593.1	592.7
127.5°	649.2	648.8	648.4	648.0	647.7	647.3	647.1	646.7
130°	686.9	686.5	686.1	685.4	684.6	683.7	682.9	682.0
132.5°	722.3	721.8	721.4	721.0	720.7	720.4	720.0	719.7
135°	775.3	774.9	774.5	773.9	773.4	772.7	772.0	771.5
137.5°	826.6	826.0	825.6	825.3	825.5	825.6	825.7	825.9
140°	860.4	860.2	860.0	859.8	859.6	859.3	859.1	858.9
142.5°	892.3	892.3	892.3	892.2	892.2	892.1	892.1	892.0
145°	940.4	940.2	939.9	939.5	938.9	938.3	937.6	937.0
147.5°	983.9	983.7	983.5	983.4	983.2	983.0	982.8	982.6
150°	1011.3	1011.3	1011.3	1011.3	1011.1	1010.8	1010.6	1010.4
152.5°	1037.2	1037.6	1038.2	1038.2	1037.6	1037.1	1036.5	1035.9
155°	1073.3	1074.0	1074.9	1074.9	1074.0	1073.3	1072.4	1071.6
157.5°	1104.9	1105.6	1106.3	1106.2	1105.5	1104.8	1104.1	1103.3
160°	1124.5	1125.2	1125.8	1125.6	1124.5	1123.5	1122.5	1121.4
162.5°	1142.1	1143.2	1144.3	1144.4	1143.4	1142.4	1141.3	1140.2
165°	1165.4	1166.6	1167.8	1168.0	1167.2	1166.4	1165.5	1164.7
167.5°	1184.9	1186.2	1187.4	1187.4	1186.1	1184.8	1183.5	1182.2
170°	1195.4	1196.7	1198.0	1197.8	1196.4	1194.9	1193.4	1191.9
172.5°	1203.2	1204.7	1206.2	1206.1	1204.7	1203.2	1201.7	1200.2
175°	1211.8	1213.3	1214.7	1214.7	1213.3	1211.8	1210.4	1208.9
177.5°	1216.5	1217.7	1218.9	1218.8	1217.5	1216.1	1214.7	1213.4
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4

(END OF REPORT)