

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331431-940

Luminaire Tested: **SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331431-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5765.4 lumens  
Efficiency: N/A  
Efficacy: 104.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331431-940  
CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68
1	102	98	95	91	97	93	90	87	83	80	78	74	72	70	65	64	63	59
2	94	87	81	76	88	82	77	72	73	69	66	66	62	60	58	56	54	50
3	86	77	70	64	81	73	66	61	65	60	56	59	55	51	52	49	47	43
4	79	68	61	55	75	65	58	53	59	53	49	53	48	45	47	44	41	38
5	73	61	53	47	69	59	51	46	53	47	42	48	43	39	43	39	36	33
6	68	56	47	42	64	53	46	40	48	42	37	43	38	35	39	35	32	30
7	63	50	43	37	59	48	41	36	44	38	33	40	35	31	36	32	29	26
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	33	29	26	24
9	55	42	35	30	52	41	34	29	37	31	27	34	29	25	31	27	24	22
10	51	39	32	27	48	37	31	26	34	29	25	31	27	23	29	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	28709	28709	28709	28709
5°	32185	28896	25606	28896
10°	36882	28658	22161	28658
15°	40802	28134	19579	28134
20°	40180	27569	17849	27569
25°	36230	26820	16751	26820
30°	29940	25620	15951	25620
35°	21821	24366	15382	24366
40°	17428	22885	15066	22885
45°	15230	21174	14636	21174
50°	14315	19515	14350	19515
55°	13196	17833	13965	17833
60°	12093	16043	13372	16043
65°	11018	14437	12791	14437
70°	10003	12873	11939	12873
75°	8865	11123	10574	11123
80°	7624	9214	8517	9214
85°	6836	6836	5076	6836



TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	169.3	2.9
10°-20°	492.3	8.5
20°-30°	714.5	12.4
30°-40°	754.0	13.1
40°-50°	667.6	11.6
50°-60°	532.7	9.2
60°-70°	362.1	6.3
70°-80°	185.6	3.2
80°-90°	47.1	0.8
90°-100°	105.7	1.8
100°-110°	358.8	6.2
110°-120°	381.2	6.6
120°-130°	313.8	5.4
130°-140°	252.0	4.4
140°-150°	190.4	3.3
150°-160°	133.8	2.3
160°-170°	78.8	1.4
170°-180°	25.6	0.4
0°-30°	1376.1	23.9
0°-40°	2130.1	36.9
0°-60°	3330.4	57.8
0°-90°	3925.3	68.1
90°-120°	845.7	14.7
90°-150°	1601.9	27.8
90°-180°	1840.0	31.9
0°-180°	5765.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1778	1778	1778	1778	1778	
5°	1986	1783	1580	1783	1986	198
15°	2441	1683	1171	1683	2441	674
25°	2034	1506	940	1506	2034	919
35°	1107	1236	780	1236	1107	720
45°	667	927	641	927	667	524
55°	469	634	496	634	469	420
65°	288	378	335	378	288	287
75°	142	178	170	178	142	152
85°	37	37	27	37	37	41
90°	17	0	17	0	17	11
95°	58	18	58	18	58	75
105°	573	62	573	62	573	555
115°	754	109	754	109	754	738
125°	612	153	612	153	612	553
135°	507	179	507	179	507	394
145°	405	204	405	204	405	257
155°	340	232	340	232	340	159
165°	298	253	298	253	298	85
175°	269	264	269	264	269	26
180°	264	264	264	264	264	



TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1860.1	1860.6	1861.7	1853.0	1851.9	1851.9	1844.2	1837.7	1830.1	1819.6	1820.8
5°	1985.8	1993.3	1996.1	1987.9	1975.6	1974.2	1962.7	1943.5	1925.7	1911.4	1901.1
7.5°	2135.9	2138.9	2132.3	2121.5	2112.3	2095.9	2074.3	2053.1	2023.5	1996.3	1976.0
10°	2249.6	2253.7	2242.1	2226.4	2213.4	2194.3	2162.8	2130.7	2091.8	2054.2	2024.1
12.5°	2336.0	2346.1	2331.2	2329.1	2306.9	2280.6	2243.2	2227.0	2172.1	2119.8	2087.6
15°	2441.0	2440.3	2441.7	2428.7	2412.3	2408.2	2368.6	2325.5	2248.3	2217.5	2164.2
17.5°	2410.7	2421.0	2425.8	2425.6	2425.3	2422.7	2409.9	2382.7	2344.0	2294.2	2232.7
20°	2338.5	2352.2	2354.2	2369.9	2378.8	2390.4	2395.2	2387.6	2363.7	2322.1	2268.8
22.5°	2227.0	2230.8	2237.2	2261.6	2280.9	2310.1	2325.2	2350.5	2341.4	2320.9	2276.4
25°	2033.7	2026.9	2050.8	2063.1	2107.5	2153.9	2187.5	2224.4	2257.2	2277.0	2264.0
27.5°	1801.6	1791.4	1827.2	1859.8	1896.0	1946.2	1998.4	2060.0	2111.3	2175.4	2197.4
30°	1605.9	1612.0	1646.2	1681.1	1735.7	1806.8	1865.5	1933.2	2006.3	2078.1	2128.0
32.5°	1394.9	1418.5	1440.1	1493.5	1541.7	1621.0	1707.0	1791.6	1882.8	1964.4	2041.7
35°	1107.1	1134.3	1164.5	1203.4	1271.0	1349.6	1433.7	1547.8	1672.2	1783.6	1875.2
37.5°	931.8	927.5	944.7	972.9	1027.6	1091.1	1187.8	1300.6	1447.0	1577.9	1707.0
40°	826.9	824.1	836.4	862.4	904.1	950.6	1035.3	1134.3	1270.3	1430.3	1584.0
42.5°	754.7	756.3	763.2	781.5	810.0	848.3	911.8	996.0	1120.6	1271.2	1436.5
45°	667.0	671.7	679.3	688.1	704.5	736.0	771.5	831.7	930.1	1055.8	1218.4
47.5°	603.8	604.0	611.6	619.4	629.1	646.8	675.8	713.5	783.0	885.4	1025.2
50°	569.9	565.2	570.6	576.8	587.0	599.3	618.4	654.0	700.4	783.1	900.0
52.5°	528.3	528.5	533.4	535.7	544.9	557.2	574.7	599.3	641.4	706.1	802.1
55°	468.8	472.2	474.9	479.0	487.2	496.1	509.8	526.2	559.0	607.5	678.6
57.5°	412.8	413.8	416.6	424.4	429.5	437.7	450.8	465.7	487.0	522.9	576.3
60°	374.5	374.5	380.0	383.3	390.2	398.4	408.7	423.0	442.1	471.5	514.6
62.5°	339.5	338.9	341.2	346.7	352.0	359.6	369.8	382.0	400.0	426.1	461.5
65°	288.4	287.0	291.1	292.5	297.9	305.5	313.7	326.6	341.0	360.2	391.6
67.5°	239.2	240.9	243.0	245.6	248.6	256.5	262.0	271.2	283.3	299.2	320.5
70°	211.9	211.9	211.9	213.9	218.0	222.1	227.6	235.1	246.7	260.4	279.5
72.5°	181.2	183.4	185.6	184.4	189.6	192.0	198.6	202.9	213.9	222.7	239.6
75°	142.1	142.1	142.1	145.5	147.6	149.6	153.7	157.8	163.4	174.2	183.2
77.5°	106.0	105.8	106.5	107.3	109.5	111.9	113.2	116.8	121.9	127.0	134.5
80°	82.0	83.4	84.1	85.4	85.4	86.8	87.5	92.3	95.7	99.1	103.9
82.5°	63.4	63.7	63.8	64.1	64.6	65.5	67.2	68.8	70.0	72.9	76.5
85°	36.9	36.2	36.2	37.5	36.9	36.9	38.3	39.6	39.6	40.3	42.4
87.5°	17.6	17.6	18.1	17.6	17.6	18.0	17.8	17.5	18.1	18.7	19.2
90°	16.8	16.8	16.8	16.8	16.8	16.2	15.2	16.2	16.8	17.3	16.8
92.5°	28.2	29.0	28.6	30.2	30.6	33.8	38.1	44.3	55.8	66.1	65.2
95°	58.0	57.4	59.0	63.0	69.6	80.9	102.2	133.2	174.4	199.4	176.5
97.5°	114.1	118.4	125.8	138.3	162.6	199.4	254.4	310.9	357.0	340.3	256.3
100°	182.1	191.2	206.0	227.8	270.0	331.5	401.3	464.3	474.9	401.7	276.6
102.5°	320.4	332.8	351.2	388.5	434.4	499.6	550.5	564.8	518.9	403.8	268.9
105°	573.1	580.2	602.1	633.6	665.1	682.0	675.3	617.9	512.1	376.8	253.8
107.5°	732.1	741.5	745.9	747.6	743.7	719.1	666.2	579.6	467.4	347.9	246.2
110°	780.1	780.6	776.1	766.3	744.5	702.8	637.7	546.7	439.3	334.1	244.6



TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	779.3	776.5	767.9	751.7	721.3	673.5	604.0	516.6	419.8	325.1	245.0
115°	754.1	749.6	736.4	712.9	676.9	624.5	557.9	479.6	395.7	315.3	247.2
117.5°	709.3	705.4	691.5	666.8	630.0	580.9	520.4	451.7	380.4	310.5	250.8
120°	680.4	675.3	660.6	636.7	601.1	554.8	500.9	437.8	372.3	307.6	253.2
122.5°	650.3	646.0	632.9	609.4	577.5	535.7	484.6	426.9	365.3	306.0	256.1
125°	611.8	607.7	594.9	575.7	546.2	508.0	463.2	410.9	355.4	303.1	260.4
127.5°	578.0	574.7	563.7	545.6	520.0	484.7	442.6	395.1	346.3	301.4	264.7
130°	558.8	554.8	544.7	527.4	502.4	468.9	428.7	385.0	340.2	300.5	268.0
132.5°	539.0	535.3	525.9	508.6	484.1	452.6	415.7	375.2	335.3	300.1	271.3
135°	507.0	505.0	495.8	479.0	457.2	428.7	395.1	361.6	328.5	299.5	275.1
137.5°	475.6	472.6	464.6	450.1	430.3	405.4	378.8	350.7	323.7	299.4	278.6
140°	454.1	451.0	443.4	430.3	413.9	391.6	368.2	343.8	320.9	299.0	280.2
142.5°	432.6	431.9	425.2	413.1	397.7	379.0	358.8	338.0	318.1	299.0	281.4
145°	404.7	403.2	398.1	389.5	377.4	362.6	346.8	330.0	314.2	298.0	282.8
147.5°	381.5	380.6	377.1	370.2	360.2	349.4	337.1	323.9	310.4	296.1	283.1
150°	367.7	367.1	364.1	358.0	350.4	341.3	330.6	319.3	307.2	295.0	282.8
152.5°	355.9	355.8	353.6	348.2	342.2	334.3	325.3	314.9	304.3	292.9	282.0
155°	340.2	341.3	339.2	335.6	330.0	324.4	316.8	308.7	299.0	289.4	280.7
157.5°	326.9	326.9	326.0	323.0	319.1	314.7	308.3	301.5	294.0	285.7	278.4
160°	318.3	318.3	317.8	315.3	311.7	308.2	302.6	296.9	290.3	283.3	277.1
162.5°	310.2	310.6	310.1	308.4	304.8	302.1	297.3	292.5	287.1	281.2	275.9
165°	298.5	299.0	299.0	296.9	295.0	292.9	289.4	285.8	281.7	277.1	273.6
167.5°	287.8	288.4	288.5	287.3	286.4	284.5	282.1	279.4	276.4	273.6	271.3
170°	281.2	282.2	282.8	281.2	280.7	279.7	277.7	276.2	273.6	271.5	270.0
172.5°	275.9	276.5	277.1	276.3	275.8	275.2	273.6	272.5	270.7	269.1	268.4
175°	269.0	270.0	270.5	270.0	270.0	269.6	269.0	268.5	267.0	266.4	266.0
177.5°	264.8	265.6	266.1	266.1	266.1	266.1	265.6	265.6	264.8	264.4	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1824.6	1820.2	1817.5	1807.7	1798.8	1790.1	1787.4	1788.5	1776.5	1765.0	1760.1
5°	1895.7	1882.0	1869.0	1850.6	1828.7	1804.7	1792.4	1782.9	1759.0	1733.0	1718.0
7.5°	1959.4	1939.8	1914.8	1880.1	1848.2	1810.6	1786.7	1765.5	1730.5	1693.9	1671.5
10°	1998.1	1971.5	1939.4	1897.0	1858.1	1812.3	1780.1	1748.0	1707.0	1663.3	1635.9
12.5°	2031.5	1995.6	1964.0	1909.6	1863.5	1806.2	1768.2	1722.9	1679.7	1627.7	1601.0
15°	2110.9	2044.6	1984.5	1923.0	1866.3	1786.3	1743.9	1683.1	1626.4	1562.2	1531.4
17.5°	2172.3	2097.7	2003.0	1924.9	1858.8	1770.2	1708.0	1635.1	1568.1	1494.7	1452.9
20°	2207.3	2121.8	2020.0	1927.1	1847.8	1746.7	1679.0	1604.5	1526.0	1443.2	1398.2
22.5°	2228.0	2138.2	2037.6	1918.9	1826.0	1727.5	1642.4	1560.8	1481.1	1391.9	1344.6
25°	2234.6	2152.6	2046.0	1912.1	1798.6	1687.2	1584.7	1505.5	1409.1	1325.7	1256.7
27.5°	2202.1	2143.3	2040.8	1899.2	1767.0	1636.8	1522.5	1432.7	1331.1	1240.5	1171.2
30°	2162.1	2128.0	2028.2	1886.1	1741.9	1601.8	1476.0	1374.2	1273.1	1181.5	1110.4
32.5°	2100.4	2093.0	2005.3	1867.5	1715.1	1557.6	1427.5	1324.5	1212.5	1122.5	1054.7
35°	1979.1	2011.8	1956.5	1826.0	1664.6	1494.5	1353.7	1236.2	1120.1	1033.9	970.4
37.5°	1816.4	1897.8	1883.4	1765.1	1596.6	1425.9	1270.5	1147.6	1037.0	950.0	887.7
40°	1704.3	1808.2	1823.2	1718.7	1548.5	1372.9	1208.2	1085.8	977.9	898.7	835.7
42.5°	1584.0	1705.4	1746.7	1662.9	1496.0	1317.1	1152.4	1025.7	918.8	841.8	786.0
45°	1382.4	1543.0	1617.6	1569.7	1408.5	1225.3	1055.8	927.3	830.3	757.9	714.8
47.5°	1194.0	1369.5	1469.6	1452.7	1311.0	1129.6	962.1	838.7	744.3	686.5	648.0
50°	1060.6	1241.0	1361.9	1367.4	1241.0	1061.2	893.1	776.9	690.2	636.2	604.8
52.5°	944.7	1116.9	1248.8	1277.7	1162.8	990.2	831.3	715.8	639.4	589.8	561.6
55°	793.4	939.0	1085.2	1138.4	1046.2	882.3	735.3	633.5	561.7	527.5	502.9
57.5°	659.6	781.0	916.0	974.9	918.0	777.7	639.9	551.4	493.3	463.3	444.4
60°	589.1	684.7	805.0	875.4	826.2	701.2	580.9	496.8	449.0	422.3	404.6
62.5°	523.4	608.2	709.9	774.3	747.4	629.5	521.8	447.6	406.4	381.3	368.5
65°	431.9	498.8	577.5	636.9	619.1	529.6	441.5	377.9	345.1	325.3	315.0
67.5°	355.6	404.0	458.5	510.6	496.2	432.8	362.0	312.5	288.1	271.0	264.8
70°	307.6	344.4	393.0	434.6	423.0	371.0	315.0	272.7	251.5	237.1	231.0
72.5°	261.6	291.9	329.0	363.0	355.2	312.0	265.3	233.3	217.0	203.8	198.8
75°	197.5	220.7	243.3	265.8	263.8	230.3	203.0	178.3	165.4	155.2	153.1
77.5°	145.8	158.8	174.2	187.5	183.8	164.7	143.2	129.1	119.6	112.7	111.6
80°	111.4	118.9	129.8	139.4	134.6	126.4	109.3	99.1	92.3	85.4	82.7
82.5°	80.8	88.3	94.9	100.0	96.4	88.7	78.2	71.2	67.1	62.4	61.3
85°	42.4	46.5	49.2	50.6	49.2	44.4	39.6	36.9	33.5	31.5	30.8
87.5°	19.2	18.5	17.9	18.7	16.9	16.7	14.1	12.1	11.9	11.8	10.9
90°	13.7	10.2	7.7	6.1	5.1	4.1	2.1	0.5	2.1	4.1	5.1
92.5°	50.7	34.6	23.1	18.3	14.9	12.6	8.9	6.2	8.9	12.6	14.9
95°	117.4	73.2	49.8	37.6	29.5	24.9	19.8	17.8	19.8	24.9	29.5
97.5°	158.3	96.7	67.2	53.4	44.1	37.1	31.7	29.0	31.7	37.1	44.1
100°	166.8	104.8	77.8	63.6	53.4	45.3	40.7	39.1	40.7	45.3	53.4
102.5°	167.2	112.1	87.1	72.9	62.3	54.2	49.7	48.5	49.7	54.2	62.3
105°	169.9	124.6	100.7	86.4	75.3	67.6	64.1	62.1	64.1	67.6	75.3
107.5°	176.8	137.4	114.2	99.9	88.8	81.8	78.3	76.7	78.3	81.8	88.8
110°	182.5	146.0	123.6	108.8	98.2	91.6	88.5	86.4	88.5	91.6	98.2





TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	188.7	154.1	132.5	117.3	107.1	100.9	97.5	95.4	97.5	100.9	107.1
115°	197.8	166.8	144.9	131.2	121.0	114.9	111.9	109.3	111.9	114.9	121.0
117.5°	207.6	178.5	158.3	144.0	134.3	128.9	125.8	123.8	125.8	128.9	134.3
120°	214.1	186.6	166.8	152.6	142.4	137.8	134.7	132.7	134.7	137.8	142.4
122.5°	219.8	194.4	175.8	161.1	151.0	146.0	142.9	141.2	142.9	146.0	151.0
125°	228.8	206.0	187.6	173.4	163.3	157.1	154.1	152.6	154.1	157.1	163.3
127.5°	237.3	216.8	198.9	184.3	174.5	167.8	163.5	161.5	163.5	167.8	174.5
130°	242.5	223.3	205.5	191.2	181.0	173.9	168.8	166.8	168.8	173.9	181.0
132.5°	247.9	228.9	212.0	197.7	187.2	179.6	174.2	171.7	174.2	179.6	187.2
135°	254.8	237.0	220.7	206.4	194.7	187.2	181.0	179.0	181.0	187.2	194.7
137.5°	260.0	243.5	227.4	214.2	202.6	194.5	188.3	185.9	188.3	194.5	202.6
140°	262.9	247.2	231.9	218.6	207.5	199.4	193.2	191.2	193.2	199.4	207.5
142.5°	265.4	250.0	235.1	222.7	212.0	203.8	198.1	196.5	198.1	203.8	212.0
145°	268.5	254.2	240.5	229.3	219.2	211.5	206.4	204.5	206.4	211.5	219.2
147.5°	270.3	257.7	244.8	234.9	226.4	219.4	214.5	212.9	214.5	219.4	226.4
150°	271.1	259.3	247.6	238.5	230.9	224.3	220.2	218.6	220.2	224.3	230.9
152.5°	271.4	261.0	250.5	242.2	235.0	229.2	225.1	224.4	225.1	229.2	235.0
155°	272.1	263.4	254.8	247.2	241.6	235.9	232.9	232.4	232.9	235.9	241.6
157.5°	272.1	265.1	257.8	251.5	246.9	242.1	239.6	239.1	239.6	242.1	246.9
160°	272.1	266.0	259.8	254.2	250.2	246.1	244.1	243.6	244.1	246.1	250.2
162.5°	271.6	266.4	261.1	256.7	253.1	249.8	247.7	248.1	247.7	249.8	253.1
165°	270.5	267.0	262.4	259.3	256.8	253.8	252.7	253.2	252.7	253.8	256.8
167.5°	269.8	266.9	263.5	261.6	259.8	257.8	256.9	257.5	256.9	257.8	259.8
170°	269.0	266.4	263.9	262.4	261.4	259.8	259.3	260.4	259.3	259.8	261.4
172.5°	267.8	266.1	264.3	263.2	262.6	261.1	261.4	262.0	261.4	261.1	262.6
175°	266.4	265.5	264.4	263.9	263.9	262.9	263.4	263.9	263.4	262.9	263.9
177.5°	265.6	264.8	264.4	264.4	264.4	263.6	264.0	264.8	264.0	263.6	264.4
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1754.6	1751.3	1739.8	1733.8	1724.0	1714.7	1708.7	1711.5	1713.6	1712.5	1710.8
5°	1704.3	1691.3	1671.5	1654.4	1642.1	1619.6	1610.0	1605.3	1601.2	1596.3	1591.5
7.5°	1644.4	1624.0	1595.5	1571.2	1548.2	1520.2	1504.2	1494.7	1484.8	1474.0	1464.5
10°	1601.8	1573.1	1543.0	1508.9	1481.6	1456.3	1433.7	1418.6	1405.0	1392.0	1382.4
12.5°	1557.0	1523.9	1486.7	1440.0	1409.9	1373.7	1370.3	1343.8	1322.4	1314.4	1303.1
15°	1485.6	1439.1	1392.0	1336.7	1312.8	1280.0	1259.5	1238.9	1220.5	1207.5	1204.1
17.5°	1404.6	1344.4	1297.5	1257.8	1218.6	1185.0	1166.1	1149.7	1134.5	1117.1	1114.8
20°	1342.8	1290.8	1239.7	1204.8	1164.5	1130.2	1107.1	1090.7	1077.6	1067.4	1058.5
22.5°	1284.3	1227.4	1180.5	1142.5	1102.7	1075.0	1056.8	1040.9	1030.1	1018.8	1010.4
25°	1190.4	1146.0	1094.8	1051.7	1018.9	1001.1	986.1	972.4	965.6	958.1	948.5
27.5°	1108.3	1058.9	1010.9	977.6	948.8	933.1	922.4	913.1	906.7	902.3	896.9
30°	1050.3	1000.4	962.9	930.1	906.2	890.5	883.6	878.2	870.6	867.9	865.1
32.5°	994.5	949.6	917.5	889.0	866.2	856.0	849.7	844.8	838.9	836.2	830.7
35°	915.7	878.2	846.7	831.0	812.5	803.6	798.9	792.0	786.6	783.8	783.1
37.5°	841.5	808.9	788.2	767.9	760.2	754.7	748.1	743.5	741.9	741.5	740.7
40°	793.4	766.7	748.3	731.9	728.4	720.2	714.8	710.7	710.7	711.4	710.7
42.5°	749.7	725.8	709.4	695.3	691.3	686.3	680.9	680.6	681.7	684.0	681.7
45°	683.4	666.3	654.7	647.8	640.3	635.5	634.8	636.9	637.6	638.3	640.3
47.5°	622.4	611.1	600.6	593.0	589.8	588.9	588.1	591.7	594.9	596.2	599.3
50°	586.3	573.4	564.5	559.6	557.0	555.5	557.0	561.1	563.7	567.2	569.3
52.5°	545.9	536.7	530.6	526.9	525.8	526.6	526.9	531.5	535.9	537.2	538.1
55°	490.0	483.1	481.8	475.6	478.3	477.7	481.1	483.8	487.9	492.0	492.7
57.5°	434.2	428.7	425.1	425.6	426.4	429.4	432.3	437.1	441.5	445.9	446.2
60°	397.1	394.3	392.3	392.3	393.6	397.7	401.1	405.9	408.7	411.3	413.4
62.5°	363.1	360.4	358.4	359.4	363.0	365.4	369.4	372.0	374.8	377.5	378.4
65°	309.6	308.2	310.2	311.7	312.3	315.8	320.5	322.5	325.3	326.6	331.4
67.5°	260.2	260.5	260.2	262.2	266.1	266.9	271.4	276.3	276.8	279.4	282.5
70°	226.9	228.3	229.6	231.0	234.4	235.8	239.2	241.2	244.0	246.0	248.1
72.5°	196.3	196.5	197.9	197.6	200.5	203.5	206.3	208.4	211.2	213.7	215.8
75°	151.1	151.1	152.4	153.1	156.5	159.9	159.3	160.6	163.4	166.0	167.5
77.5°	110.3	108.8	110.3	111.0	112.1	114.9	115.5	117.4	120.6	119.6	121.1
80°	84.1	82.0	84.1	84.7	84.7	88.2	88.2	89.5	91.6	89.5	91.6
82.5°	60.0	59.0	60.5	60.7	61.8	61.9	63.0	63.3	65.4	64.4	65.4
85°	30.1	29.4	30.1	29.4	30.1	30.8	30.8	30.1	30.1	31.5	29.4
87.5°	10.5	10.3	10.3	11.0	11.0	10.5	9.9	9.8	9.6	8.7	8.8
90°	6.1	7.7	10.2	13.7	16.8	17.3	16.8	16.2	15.2	16.2	16.8
92.5°	18.3	23.1	34.6	50.7	65.2	66.1	55.8	44.3	38.1	33.8	30.6
95°	37.6	49.8	73.2	117.4	176.5	199.4	174.4	133.2	102.2	80.9	69.6
97.5°	53.4	67.2	96.7	158.3	256.3	340.3	357.0	310.9	254.4	199.4	162.6
100°	63.6	77.8	104.8	166.8	276.6	401.7	474.9	464.3	401.3	331.5	270.0
102.5°	72.9	87.1	112.1	167.2	268.9	403.8	518.9	564.8	550.5	499.6	434.4
105°	86.4	100.7	124.6	169.9	253.8	376.8	512.1	617.9	675.3	682.0	665.1
107.5°	99.9	114.2	137.4	176.8	246.2	347.9	467.4	579.6	666.2	719.1	743.7
110°	108.8	123.6	146.0	182.5	244.6	334.1	439.3	546.7	637.7	702.8	744.5



TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	117.3	132.5	154.1	188.7	245.0	325.1	419.8	516.6	604.0	673.5	721.3
115°	131.2	144.9	166.8	197.8	247.2	315.3	395.7	479.6	557.9	624.5	676.9
117.5°	144.0	158.3	178.5	207.6	250.8	310.5	380.4	451.7	520.4	580.9	630.0
120°	152.6	166.8	186.6	214.1	253.2	307.6	372.3	437.8	500.9	554.8	601.1
122.5°	161.1	175.8	194.4	219.8	256.1	306.0	365.3	426.9	484.6	535.7	577.5
125°	173.4	187.6	206.0	228.8	260.4	303.1	355.4	410.9	463.2	508.0	546.2
127.5°	184.3	198.9	216.8	237.3	264.7	301.4	346.3	395.1	442.6	484.7	520.0
130°	191.2	205.5	223.3	242.5	268.0	300.5	340.2	385.0	428.7	468.9	502.4
132.5°	197.7	212.0	228.9	247.9	271.3	300.1	335.3	375.2	415.7	452.6	484.1
135°	206.4	220.7	237.0	254.8	275.1	299.5	328.5	361.6	395.1	428.7	457.2
137.5°	214.2	227.4	243.5	260.0	278.6	299.4	323.7	350.7	378.8	405.4	430.3
140°	218.6	231.9	247.2	262.9	280.2	299.0	320.9	343.8	368.2	391.6	413.9
142.5°	222.7	235.1	250.0	265.4	281.4	299.0	318.1	338.0	358.8	379.0	397.7
145°	229.3	240.5	254.2	268.5	282.8	298.0	314.2	330.0	346.8	362.6	377.4
147.5°	234.9	244.8	257.7	270.3	283.1	296.1	310.4	323.9	337.1	349.4	360.2
150°	238.5	247.6	259.3	271.1	282.8	295.0	307.2	319.3	330.6	341.3	350.4
152.5°	242.2	250.5	261.0	271.4	282.0	292.9	304.3	314.9	325.3	334.3	342.2
155°	247.2	254.8	263.4	272.1	280.7	289.4	299.0	308.7	316.8	324.4	330.0
157.5°	251.5	257.8	265.1	272.1	278.4	285.7	294.0	301.5	308.3	314.7	319.1
160°	254.2	259.8	266.0	272.1	277.1	283.3	290.3	296.9	302.6	308.2	311.7
162.5°	256.7	261.1	266.4	271.6	275.9	281.2	287.1	292.5	297.3	302.1	304.8
165°	259.3	262.4	267.0	270.5	273.6	277.1	281.7	285.8	289.4	292.9	295.0
167.5°	261.6	263.5	266.9	269.8	271.3	273.6	276.4	279.4	282.1	284.5	286.4
170°	262.4	263.9	266.4	269.0	270.0	271.5	273.6	276.2	277.7	279.7	280.7
172.5°	263.2	264.3	266.1	267.8	268.4	269.1	270.7	272.5	273.6	275.2	275.8
175°	263.9	264.4	265.5	266.4	266.0	266.4	267.0	268.5	269.0	269.6	270.0
177.5°	264.4	264.4	264.8	265.6	264.8	264.4	264.8	265.6	265.6	266.1	266.1
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1705.4	1704.3	1704.3	1699.4	1704.3	1704.3	1705.4	1710.8	1712.5	1713.6	1711.5
5°	1582.0	1579.9	1576.5	1579.9	1576.5	1579.9	1582.0	1591.5	1596.3	1601.2	1605.3
7.5°	1459.9	1451.7	1450.5	1442.4	1450.5	1451.7	1459.9	1464.5	1474.0	1484.8	1494.7
10°	1370.8	1365.4	1364.7	1351.7	1364.7	1365.4	1370.8	1382.4	1392.0	1405.0	1418.6
12.5°	1303.1	1289.9	1292.5	1285.0	1292.5	1289.9	1303.1	1303.1	1314.4	1322.4	1343.8
15°	1185.6	1185.6	1182.9	1171.3	1182.9	1185.6	1185.6	1204.1	1207.5	1220.5	1238.9
17.5°	1101.4	1099.9	1093.4	1096.6	1093.4	1099.9	1101.4	1114.8	1117.1	1134.5	1149.7
20°	1051.0	1047.0	1038.8	1038.8	1038.8	1047.0	1051.0	1058.5	1067.4	1077.6	1090.7
22.5°	1003.4	1003.2	994.4	997.2	994.4	1003.2	1003.4	1010.4	1018.8	1030.1	1040.9
25°	947.8	942.4	938.3	940.3	938.3	942.4	947.8	948.5	958.1	965.6	972.4
27.5°	895.1	892.1	891.8	886.2	891.8	892.1	895.1	896.9	902.3	906.7	913.1
30°	864.4	857.6	859.0	855.6	859.0	857.6	864.4	865.1	867.9	870.6	878.2
32.5°	829.5	827.0	825.6	822.8	825.6	827.0	829.5	830.7	836.2	838.9	844.8
35°	781.8	782.5	779.0	780.4	779.0	782.5	781.8	783.1	783.8	786.6	792.0
37.5°	740.1	742.3	740.7	741.0	740.7	742.3	740.1	740.7	741.5	741.9	743.5
40°	712.7	712.7	712.7	714.8	712.7	712.7	712.7	710.7	711.4	710.7	710.7
42.5°	686.5	685.5	684.3	684.2	684.3	685.5	686.5	681.7	684.0	681.7	680.6
45°	641.7	643.7	644.4	641.0	644.4	643.7	641.7	640.3	638.3	637.6	636.9
47.5°	601.1	601.4	601.1	604.1	601.1	601.4	601.1	599.3	596.2	594.9	591.7
50°	572.7	571.3	572.7	571.3	572.7	571.3	572.7	569.3	567.2	563.7	561.1
52.5°	542.6	542.9	542.1	541.8	542.1	542.9	542.6	538.1	537.2	535.9	531.5
55°	495.4	496.8	496.1	496.1	496.1	496.8	495.4	492.7	492.0	487.9	483.8
57.5°	446.7	447.9	448.8	445.9	448.8	447.9	446.7	446.2	445.9	441.5	437.1
60°	412.8	416.2	415.4	414.1	415.4	416.2	412.8	413.4	411.3	408.7	405.9
62.5°	381.6	382.8	382.7	382.5	382.7	382.8	381.6	378.4	377.5	374.8	372.0
65°	333.5	334.8	332.8	334.8	332.8	334.8	333.5	331.4	326.6	325.3	322.5
67.5°	281.7	282.1	283.6	284.5	283.6	282.1	281.7	282.5	279.4	276.8	276.3
70°	249.4	248.8	250.8	252.9	250.8	248.8	249.4	248.1	246.0	244.0	241.2
72.5°	215.5	217.0	216.3	217.8	216.3	217.0	215.5	215.8	213.7	211.2	208.4
75°	166.0	168.1	167.5	169.5	167.5	168.1	166.0	167.5	166.0	163.4	160.6
77.5°	120.0	120.3	120.0	121.1	120.0	120.3	120.0	121.1	119.6	120.6	117.4
80°	91.6	90.2	88.8	91.6	88.8	90.2	91.6	91.6	89.5	91.6	89.5
82.5°	63.7	64.5	63.1	63.1	63.1	64.5	63.7	65.4	64.4	65.4	63.3
85°	29.4	28.7	27.4	27.4	27.4	28.7	29.4	29.4	31.5	30.1	30.1
87.5°	8.8	8.3	8.3	7.8	8.3	8.3	8.8	8.8	8.7	9.6	9.8
90°	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.2	15.2	16.2
92.5°	30.2	28.6	29.0	28.2	29.0	28.6	30.2	30.6	33.8	38.1	44.3
95°	63.0	59.0	57.4	58.0	57.4	59.0	63.0	69.6	80.9	102.2	133.2
97.5°	138.3	125.8	118.4	114.1	118.4	125.8	138.3	162.6	199.4	254.4	310.9
100°	227.8	206.0	191.2	182.1	191.2	206.0	227.8	270.0	331.5	401.3	464.3
102.5°	388.5	351.2	332.8	320.4	332.8	351.2	388.5	434.4	499.6	550.5	564.8
105°	633.6	602.1	580.2	573.1	580.2	602.1	633.6	665.1	682.0	675.3	617.9
107.5°	747.6	745.9	741.5	732.1	741.5	745.9	747.6	743.7	719.1	666.2	579.6
110°	766.3	776.1	780.6	780.1	780.6	776.1	766.3	744.5	702.8	637.7	546.7



TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	751.7	767.9	776.5	779.3	776.5	767.9	751.7	721.3	673.5	604.0	516.6
115°	712.9	736.4	749.6	754.1	749.6	736.4	712.9	676.9	624.5	557.9	479.6
117.5°	666.8	691.5	705.4	709.3	705.4	691.5	666.8	630.0	580.9	520.4	451.7
120°	636.7	660.6	675.3	680.4	675.3	660.6	636.7	601.1	554.8	500.9	437.8
122.5°	609.4	632.9	646.0	650.3	646.0	632.9	609.4	577.5	535.7	484.6	426.9
125°	575.7	594.9	607.7	611.8	607.7	594.9	575.7	546.2	508.0	463.2	410.9
127.5°	545.6	563.7	574.7	578.0	574.7	563.7	545.6	520.0	484.7	442.6	395.1
130°	527.4	544.7	554.8	558.8	554.8	544.7	527.4	502.4	468.9	428.7	385.0
132.5°	508.6	525.9	535.3	539.0	535.3	525.9	508.6	484.1	452.6	415.7	375.2
135°	479.0	495.8	505.0	507.0	505.0	495.8	479.0	457.2	428.7	395.1	361.6
137.5°	450.1	464.6	472.6	475.6	472.6	464.6	450.1	430.3	405.4	378.8	350.7
140°	430.3	443.4	451.0	454.1	451.0	443.4	430.3	413.9	391.6	368.2	343.8
142.5°	413.1	425.2	431.9	432.6	431.9	425.2	413.1	397.7	379.0	358.8	338.0
145°	389.5	398.1	403.2	404.7	403.2	398.1	389.5	377.4	362.6	346.8	330.0
147.5°	370.2	377.1	380.6	381.5	380.6	377.1	370.2	360.2	349.4	337.1	323.9
150°	358.0	364.1	367.1	367.7	367.1	364.1	358.0	350.4	341.3	330.6	319.3
152.5°	348.2	353.6	355.8	355.9	355.8	353.6	348.2	342.2	334.3	325.3	314.9
155°	335.6	339.2	341.3	340.2	341.3	339.2	335.6	330.0	324.4	316.8	308.7
157.5°	323.0	326.0	326.9	326.9	326.9	326.0	323.0	319.1	314.7	308.3	301.5
160°	315.3	317.8	318.3	318.3	318.3	317.8	315.3	311.7	308.2	302.6	296.9
162.5°	308.4	310.1	310.6	310.2	310.6	310.1	308.4	304.8	302.1	297.3	292.5
165°	296.9	299.0	299.0	298.5	299.0	299.0	296.9	295.0	292.9	289.4	285.8
167.5°	287.3	288.5	288.4	287.8	288.4	288.5	287.3	286.4	284.5	282.1	279.4
170°	281.2	282.8	282.2	281.2	282.2	282.8	281.2	280.7	279.7	277.7	276.2
172.5°	276.3	277.1	276.5	275.9	276.5	277.1	276.3	275.8	275.2	273.6	272.5
175°	270.0	270.5	270.0	269.0	270.0	270.5	270.0	270.0	269.6	269.0	268.5
177.5°	266.1	266.1	265.6	264.8	265.6	266.1	266.1	266.1	266.1	265.6	265.6
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331431-940  
 CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1708.7	1714.7	1724.0	1733.8	1739.8	1751.3	1754.6	1760.1	1765.0	1776.5	1788.5
5°	1610.0	1619.6	1642.1	1654.4	1671.5	1691.3	1704.3	1718.0	1733.0	1759.0	1782.9
7.5°	1504.2	1520.2	1548.2	1571.2	1595.5	1624.0	1644.4	1671.5	1693.9	1730.5	1765.5
10°	1433.7	1456.3	1481.6	1508.9	1543.0	1573.1	1601.8	1635.9	1663.3	1707.0	1748.0
12.5°	1370.3	1373.7	1409.9	1440.0	1486.7	1523.9	1557.0	1601.0	1627.7	1679.7	1722.9
15°	1259.5	1280.0	1312.8	1336.7	1392.0	1439.1	1485.6	1531.4	1562.2	1626.4	1683.1
17.5°	1166.1	1185.0	1218.6	1257.8	1297.5	1344.4	1404.6	1452.9	1494.7	1568.1	1635.1
20°	1107.1	1130.2	1164.5	1204.8	1239.7	1290.8	1342.8	1398.2	1443.2	1526.0	1604.5
22.5°	1056.8	1075.0	1102.7	1142.5	1180.5	1227.4	1284.3	1344.6	1391.9	1481.1	1560.8
25°	986.1	1001.1	1018.9	1051.7	1094.8	1146.0	1190.4	1256.7	1325.7	1409.1	1505.5
27.5°	922.4	933.1	948.8	977.6	1010.9	1058.9	1108.3	1171.2	1240.5	1331.1	1432.7
30°	883.6	890.5	906.2	930.1	962.9	1000.4	1050.3	1110.4	1181.5	1273.1	1374.2
32.5°	849.7	856.0	866.2	889.0	917.5	949.6	994.5	1054.7	1122.5	1212.5	1324.5
35°	798.9	803.6	812.5	831.0	846.7	878.2	915.7	970.4	1033.9	1120.1	1236.2
37.5°	748.1	754.7	760.2	767.9	788.2	808.9	841.5	887.7	950.0	1037.0	1147.6
40°	714.8	720.2	728.4	731.9	748.3	766.7	793.4	835.7	898.7	977.9	1085.8
42.5°	680.9	686.3	691.3	695.3	709.4	725.8	749.7	786.0	841.8	918.8	1025.7
45°	634.8	635.5	640.3	647.8	654.7	666.3	683.4	714.8	757.9	830.3	927.3
47.5°	588.1	588.9	589.8	593.0	600.6	611.1	622.4	648.0	686.5	744.3	838.7
50°	557.0	555.5	557.0	559.6	564.5	573.4	586.3	604.8	636.2	690.2	776.9
52.5°	526.9	526.6	525.8	526.9	530.6	536.7	545.9	561.6	589.8	639.4	715.8
55°	481.1	477.7	478.3	475.6	481.8	483.1	490.0	502.9	527.5	561.7	633.5
57.5°	432.3	429.4	426.4	425.6	425.1	428.7	434.2	444.4	463.3	493.3	551.4
60°	401.1	397.7	393.6	392.3	392.3	394.3	397.1	404.6	422.3	449.0	496.8
62.5°	369.4	365.4	363.0	359.4	358.4	360.4	363.1	368.5	381.3	406.4	447.6
65°	320.5	315.8	312.3	311.7	310.2	308.2	309.6	315.0	325.3	345.1	377.9
67.5°	271.4	266.9	266.1	262.2	260.2	260.5	260.2	264.8	271.0	288.1	312.5
70°	239.2	235.8	234.4	231.0	229.6	228.3	226.9	231.0	237.1	251.5	272.7
72.5°	206.3	203.5	200.5	197.6	197.9	196.5	196.3	198.8	203.8	217.0	233.3
75°	159.3	159.9	156.5	153.1	152.4	151.1	151.1	153.1	155.2	165.4	178.3
77.5°	115.5	114.9	112.1	111.0	110.3	108.8	110.3	111.6	112.7	119.6	129.1
80°	88.2	88.2	84.7	84.7	84.1	82.0	84.1	82.7	85.4	92.3	99.1
82.5°	63.0	61.9	61.8	60.7	60.5	59.0	60.0	61.3	62.4	67.1	71.2
85°	30.8	30.8	30.1	29.4	30.1	29.4	30.1	30.8	31.5	33.5	36.9
87.5°	9.9	10.5	11.0	11.0	10.3	10.3	10.5	10.9	11.8	11.9	12.1
90°	16.8	17.3	16.8	13.7	10.2	7.7	6.1	5.1	4.1	2.1	0.5
92.5°	55.8	66.1	65.2	50.7	34.6	23.1	18.3	14.9	12.6	8.9	6.2
95°	174.4	199.4	176.5	117.4	73.2	49.8	37.6	29.5	24.9	19.8	17.8
97.5°	357.0	340.3	256.3	158.3	96.7	67.2	53.4	44.1	37.1	31.7	29.0
100°	474.9	401.7	276.6	166.8	104.8	77.8	63.6	53.4	45.3	40.7	39.1
102.5°	518.9	403.8	268.9	167.2	112.1	87.1	72.9	62.3	54.2	49.7	48.5
105°	512.1	376.8	253.8	169.9	124.6	100.7	86.4	75.3	67.6	64.1	62.1
107.5°	467.4	347.9	246.2	176.8	137.4	114.2	99.9	88.8	81.8	78.3	76.7
110°	439.3	334.1	244.6	182.5	146.0	123.6	108.8	98.2	91.6	88.5	86.4



TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	419.8	325.1	245.0	188.7	154.1	132.5	117.3	107.1	100.9	97.5	95.4
115°	395.7	315.3	247.2	197.8	166.8	144.9	131.2	121.0	114.9	111.9	109.3
117.5°	380.4	310.5	250.8	207.6	178.5	158.3	144.0	134.3	128.9	125.8	123.8
120°	372.3	307.6	253.2	214.1	186.6	166.8	152.6	142.4	137.8	134.7	132.7
122.5°	365.3	306.0	256.1	219.8	194.4	175.8	161.1	151.0	146.0	142.9	141.2
125°	355.4	303.1	260.4	228.8	206.0	187.6	173.4	163.3	157.1	154.1	152.6
127.5°	346.3	301.4	264.7	237.3	216.8	198.9	184.3	174.5	167.8	163.5	161.5
130°	340.2	300.5	268.0	242.5	223.3	205.5	191.2	181.0	173.9	168.8	166.8
132.5°	335.3	300.1	271.3	247.9	228.9	212.0	197.7	187.2	179.6	174.2	171.7
135°	328.5	299.5	275.1	254.8	237.0	220.7	206.4	194.7	187.2	181.0	179.0
137.5°	323.7	299.4	278.6	260.0	243.5	227.4	214.2	202.6	194.5	188.3	185.9
140°	320.9	299.0	280.2	262.9	247.2	231.9	218.6	207.5	199.4	193.2	191.2
142.5°	318.1	299.0	281.4	265.4	250.0	235.1	222.7	212.0	203.8	198.1	196.5
145°	314.2	298.0	282.8	268.5	254.2	240.5	229.3	219.2	211.5	206.4	204.5
147.5°	310.4	296.1	283.1	270.3	257.7	244.8	234.9	226.4	219.4	214.5	212.9
150°	307.2	295.0	282.8	271.1	259.3	247.6	238.5	230.9	224.3	220.2	218.6
152.5°	304.3	292.9	282.0	271.4	261.0	250.5	242.2	235.0	229.2	225.1	224.4
155°	299.0	289.4	280.7	272.1	263.4	254.8	247.2	241.6	235.9	232.9	232.4
157.5°	294.0	285.7	278.4	272.1	265.1	257.8	251.5	246.9	242.1	239.6	239.1
160°	290.3	283.3	277.1	272.1	266.0	259.8	254.2	250.2	246.1	244.1	243.6
162.5°	287.1	281.2	275.9	271.6	266.4	261.1	256.7	253.1	249.8	247.7	248.1
165°	281.7	277.1	273.6	270.5	267.0	262.4	259.3	256.8	253.8	252.7	253.2
167.5°	276.4	273.6	271.3	269.8	266.9	263.5	261.6	259.8	257.8	256.9	257.5
170°	273.6	271.5	270.0	269.0	266.4	263.9	262.4	261.4	259.8	259.3	260.4
172.5°	270.7	269.1	268.4	267.8	266.1	264.3	263.2	262.6	261.1	261.4	262.0
175°	267.0	266.4	266.0	266.4	265.5	264.4	263.9	263.9	262.9	263.4	263.9
177.5°	264.8	264.4	264.8	265.6	264.8	264.4	264.4	264.4	263.6	264.0	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1787.4	1790.1	1798.8	1807.7	1817.5	1820.2	1824.6	1820.8	1819.6	1830.1	1837.7
5°	1792.4	1804.7	1828.7	1850.6	1869.0	1882.0	1895.7	1901.1	1911.4	1925.7	1943.5
7.5°	1786.7	1810.6	1848.2	1880.1	1914.8	1939.8	1959.4	1976.0	1996.3	2023.5	2053.1
10°	1780.1	1812.3	1858.1	1897.0	1939.4	1971.5	1998.1	2024.1	2054.2	2091.8	2130.7
12.5°	1768.2	1806.2	1863.5	1909.6	1964.0	1995.6	2031.5	2087.6	2119.8	2172.1	2227.0
15°	1743.9	1786.3	1866.3	1923.0	1984.5	2044.6	2110.9	2164.2	2217.5	2248.3	2325.5
17.5°	1708.0	1770.2	1858.8	1924.9	2003.0	2097.7	2172.3	2232.7	2294.2	2344.0	2382.7
20°	1679.0	1746.7	1847.8	1927.1	2020.0	2121.8	2207.3	2268.8	2322.1	2363.7	2387.6
22.5°	1642.4	1727.5	1826.0	1918.9	2037.6	2138.2	2228.0	2276.4	2320.9	2341.4	2350.5
25°	1584.7	1687.2	1798.6	1912.1	2046.0	2152.6	2234.6	2264.0	2277.0	2257.2	2224.4
27.5°	1522.5	1636.8	1767.0	1899.2	2040.8	2143.3	2202.1	2197.4	2175.4	2111.3	2060.0
30°	1476.0	1601.8	1741.9	1886.1	2028.2	2128.0	2162.1	2128.0	2078.1	2006.3	1933.2
32.5°	1427.5	1557.6	1715.1	1867.5	2005.3	2093.0	2100.4	2041.7	1964.4	1882.8	1791.6
35°	1353.7	1494.5	1664.6	1826.0	1956.5	2011.8	1979.1	1875.2	1783.6	1672.2	1547.8
37.5°	1270.5	1425.9	1596.6	1765.1	1883.4	1897.8	1816.4	1707.0	1577.9	1447.0	1300.6
40°	1208.2	1372.9	1548.5	1718.7	1823.2	1808.2	1704.3	1584.0	1430.3	1270.3	1134.3
42.5°	1152.4	1317.1	1496.0	1662.9	1746.7	1705.4	1584.0	1436.5	1271.2	1120.6	996.0
45°	1055.8	1225.3	1408.5	1569.7	1617.6	1543.0	1382.4	1218.4	1055.8	930.1	831.7
47.5°	962.1	1129.6	1311.0	1452.7	1469.6	1369.5	1194.0	1025.2	885.4	783.0	713.5
50°	893.1	1061.2	1241.0	1367.4	1361.9	1241.0	1060.6	900.0	783.1	700.4	654.0
52.5°	831.3	990.2	1162.8	1277.7	1248.8	1116.9	944.7	802.1	706.1	641.4	599.3
55°	735.3	882.3	1046.2	1138.4	1085.2	939.0	793.4	678.6	607.5	559.0	526.2
57.5°	639.9	777.7	918.0	974.9	916.0	781.0	659.6	576.3	522.9	487.0	465.7
60°	580.9	701.2	826.2	875.4	805.0	684.7	589.1	514.6	471.5	442.1	423.0
62.5°	521.8	629.5	747.4	774.3	709.9	608.2	523.4	461.5	426.1	400.0	382.0
65°	441.5	529.6	619.1	636.9	577.5	498.8	431.9	391.6	360.2	341.0	326.6
67.5°	362.0	432.8	496.2	510.6	458.5	404.0	355.6	320.5	299.2	283.3	271.2
70°	315.0	371.0	423.0	434.6	393.0	344.4	307.6	279.5	260.4	246.7	235.1
72.5°	265.3	312.0	355.2	363.0	329.0	291.9	261.6	239.6	222.7	213.9	202.9
75°	203.0	230.3	263.8	265.8	243.3	220.7	197.5	183.2	174.2	163.4	157.8
77.5°	143.2	164.7	183.8	187.5	174.2	158.8	145.8	134.5	127.0	121.9	116.8
80°	109.3	126.4	134.6	139.4	129.8	118.9	111.4	103.9	99.1	95.7	92.3
82.5°	78.2	88.7	96.4	100.0	94.9	88.3	80.8	76.5	72.9	70.0	68.8
85°	39.6	44.4	49.2	50.6	49.2	46.5	42.4	42.4	40.3	39.6	39.6
87.5°	14.1	16.7	16.9	18.7	17.9	18.5	19.2	19.2	18.7	18.1	17.5
90°	2.1	4.1	5.1	6.1	7.7	10.2	13.7	16.8	17.3	16.8	16.2
92.5°	8.9	12.6	14.9	18.3	23.1	34.6	50.7	65.2	66.1	55.8	44.3
95°	19.8	24.9	29.5	37.6	49.8	73.2	117.4	176.5	199.4	174.4	133.2
97.5°	31.7	37.1	44.1	53.4	67.2	96.7	158.3	256.3	340.3	357.0	310.9
100°	40.7	45.3	53.4	63.6	77.8	104.8	166.8	276.6	401.7	474.9	464.3
102.5°	49.7	54.2	62.3	72.9	87.1	112.1	167.2	268.9	403.8	518.9	564.8
105°	64.1	67.6	75.3	86.4	100.7	124.6	169.9	253.8	376.8	512.1	617.9
107.5°	78.3	81.8	88.8	99.9	114.2	137.4	176.8	246.2	347.9	467.4	579.6
110°	88.5	91.6	98.2	108.8	123.6	146.0	182.5	244.6	334.1	439.3	546.7





TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	97.5	100.9	107.1	117.3	132.5	154.1	188.7	245.0	325.1	419.8	516.6
115°	111.9	114.9	121.0	131.2	144.9	166.8	197.8	247.2	315.3	395.7	479.6
117.5°	125.8	128.9	134.3	144.0	158.3	178.5	207.6	250.8	310.5	380.4	451.7
120°	134.7	137.8	142.4	152.6	166.8	186.6	214.1	253.2	307.6	372.3	437.8
122.5°	142.9	146.0	151.0	161.1	175.8	194.4	219.8	256.1	306.0	365.3	426.9
125°	154.1	157.1	163.3	173.4	187.6	206.0	228.8	260.4	303.1	355.4	410.9
127.5°	163.5	167.8	174.5	184.3	198.9	216.8	237.3	264.7	301.4	346.3	395.1
130°	168.8	173.9	181.0	191.2	205.5	223.3	242.5	268.0	300.5	340.2	385.0
132.5°	174.2	179.6	187.2	197.7	212.0	228.9	247.9	271.3	300.1	335.3	375.2
135°	181.0	187.2	194.7	206.4	220.7	237.0	254.8	275.1	299.5	328.5	361.6
137.5°	188.3	194.5	202.6	214.2	227.4	243.5	260.0	278.6	299.4	323.7	350.7
140°	193.2	199.4	207.5	218.6	231.9	247.2	262.9	280.2	299.0	320.9	343.8
142.5°	198.1	203.8	212.0	222.7	235.1	250.0	265.4	281.4	299.0	318.1	338.0
145°	206.4	211.5	219.2	229.3	240.5	254.2	268.5	282.8	298.0	314.2	330.0
147.5°	214.5	219.4	226.4	234.9	244.8	257.7	270.3	283.1	296.1	310.4	323.9
150°	220.2	224.3	230.9	238.5	247.6	259.3	271.1	282.8	295.0	307.2	319.3
152.5°	225.1	229.2	235.0	242.2	250.5	261.0	271.4	282.0	292.9	304.3	314.9
155°	232.9	235.9	241.6	247.2	254.8	263.4	272.1	280.7	289.4	299.0	308.7
157.5°	239.6	242.1	246.9	251.5	257.8	265.1	272.1	278.4	285.7	294.0	301.5
160°	244.1	246.1	250.2	254.2	259.8	266.0	272.1	277.1	283.3	290.3	296.9
162.5°	247.7	249.8	253.1	256.7	261.1	266.4	271.6	275.9	281.2	287.1	292.5
165°	252.7	253.8	256.8	259.3	262.4	267.0	270.5	273.6	277.1	281.7	285.8
167.5°	256.9	257.8	259.8	261.6	263.5	266.9	269.8	271.3	273.6	276.4	279.4
170°	259.3	259.8	261.4	262.4	263.9	266.4	269.0	270.0	271.5	273.6	276.2
172.5°	261.4	261.1	262.6	263.2	264.3	266.1	267.8	268.4	269.1	270.7	272.5
175°	263.4	262.9	263.9	263.9	264.4	265.5	266.4	266.0	266.4	267.0	268.5
177.5°	264.0	263.6	264.4	264.4	264.4	264.8	265.6	264.8	264.4	264.8	265.6
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331431-940  
 CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1844.2	1851.9	1851.9	1853.0	1861.7	1860.6	1860.1
5°	1962.7	1974.2	1975.6	1987.9	1996.1	1993.3	1985.8
7.5°	2074.3	2095.9	2112.3	2121.5	2132.3	2138.9	2135.9
10°	2162.8	2194.3	2213.4	2226.4	2242.1	2253.7	2249.6
12.5°	2243.2	2280.6	2306.9	2329.1	2331.2	2346.1	2336.0
15°	2368.6	2408.2	2412.3	2428.7	2441.7	2440.3	2441.0
17.5°	2409.9	2422.7	2425.3	2425.6	2425.8	2421.0	2410.7
20°	2395.2	2390.4	2378.8	2369.9	2354.2	2352.2	2338.5
22.5°	2325.2	2310.1	2280.9	2261.6	2237.2	2230.8	2227.0
25°	2187.5	2153.9	2107.5	2063.1	2050.8	2026.9	2033.7
27.5°	1998.4	1946.2	1896.0	1859.8	1827.2	1791.4	1801.6
30°	1865.5	1806.8	1735.7	1681.1	1646.2	1612.0	1605.9
32.5°	1707.0	1621.0	1541.7	1493.5	1440.1	1418.5	1394.9
35°	1433.7	1349.6	1271.0	1203.4	1164.5	1134.3	1107.1
37.5°	1187.8	1091.1	1027.6	972.9	944.7	927.5	931.8
40°	1035.3	950.6	904.1	862.4	836.4	824.1	826.9
42.5°	911.8	848.3	810.0	781.5	763.2	756.3	754.7
45°	771.5	736.0	704.5	688.1	679.3	671.7	667.0
47.5°	675.8	646.8	629.1	619.4	611.6	604.0	603.8
50°	618.4	599.3	587.0	576.8	570.6	565.2	569.9
52.5°	574.7	557.2	544.9	535.7	533.4	528.5	528.3
55°	509.8	496.1	487.2	479.0	474.9	472.2	468.8
57.5°	450.8	437.7	429.5	424.4	416.6	413.8	412.8
60°	408.7	398.4	390.2	383.3	380.0	374.5	374.5
62.5°	369.8	359.6	352.0	346.7	341.2	338.9	339.5
65°	313.7	305.5	297.9	292.5	291.1	287.0	288.4
67.5°	262.0	256.5	248.6	245.6	243.0	240.9	239.2
70°	227.6	222.1	218.0	213.9	211.9	211.9	211.9
72.5°	198.6	192.0	189.6	184.4	185.6	183.4	181.2
75°	153.7	149.6	147.6	145.5	142.1	142.1	142.1
77.5°	113.2	111.9	109.5	107.3	106.5	105.8	106.0
80°	87.5	86.8	85.4	85.4	84.1	83.4	82.0
82.5°	67.2	65.5	64.6	64.1	63.8	63.7	63.4
85°	38.3	36.9	36.9	37.5	36.2	36.2	36.9
87.5°	17.8	18.0	17.6	17.6	18.1	17.6	17.6
90°	15.2	16.2	16.8	16.8	16.8	16.8	16.8
92.5°	38.1	33.8	30.6	30.2	28.6	29.0	28.2
95°	102.2	80.9	69.6	63.0	59.0	57.4	58.0
97.5°	254.4	199.4	162.6	138.3	125.8	118.4	114.1
100°	401.3	331.5	270.0	227.8	206.0	191.2	182.1
102.5°	550.5	499.6	434.4	388.5	351.2	332.8	320.4
105°	675.3	682.0	665.1	633.6	602.1	580.2	573.1
107.5°	666.2	719.1	743.7	747.6	745.9	741.5	732.1
110°	637.7	702.8	744.5	766.3	776.1	780.6	780.1



TEST NUMBER: P331431-940

CATALOG NUMBER: SA2XXDIP-C1005D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	604.0	673.5	721.3	751.7	767.9	776.5	779.3
115°	557.9	624.5	676.9	712.9	736.4	749.6	754.1
117.5°	520.4	580.9	630.0	666.8	691.5	705.4	709.3
120°	500.9	554.8	601.1	636.7	660.6	675.3	680.4
122.5°	484.6	535.7	577.5	609.4	632.9	646.0	650.3
125°	463.2	508.0	546.2	575.7	594.9	607.7	611.8
127.5°	442.6	484.7	520.0	545.6	563.7	574.7	578.0
130°	428.7	468.9	502.4	527.4	544.7	554.8	558.8
132.5°	415.7	452.6	484.1	508.6	525.9	535.3	539.0
135°	395.1	428.7	457.2	479.0	495.8	505.0	507.0
137.5°	378.8	405.4	430.3	450.1	464.6	472.6	475.6
140°	368.2	391.6	413.9	430.3	443.4	451.0	454.1
142.5°	358.8	379.0	397.7	413.1	425.2	431.9	432.6
145°	346.8	362.6	377.4	389.5	398.1	403.2	404.7
147.5°	337.1	349.4	360.2	370.2	377.1	380.6	381.5
150°	330.6	341.3	350.4	358.0	364.1	367.1	367.7
152.5°	325.3	334.3	342.2	348.2	353.6	355.8	355.9
155°	316.8	324.4	330.0	335.6	339.2	341.3	340.2
157.5°	308.3	314.7	319.1	323.0	326.0	326.9	326.9
160°	302.6	308.2	311.7	315.3	317.8	318.3	318.3
162.5°	297.3	302.1	304.8	308.4	310.1	310.6	310.2
165°	289.4	292.9	295.0	296.9	299.0	299.0	298.5
167.5°	282.1	284.5	286.4	287.3	288.5	288.4	287.8
170°	277.7	279.7	280.7	281.2	282.8	282.2	281.2
172.5°	273.6	275.2	275.8	276.3	277.1	276.5	275.9
175°	269.0	269.6	270.0	270.0	270.5	270.0	269.0
177.5°	265.6	266.1	266.1	266.1	266.1	265.6	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4

(END OF REPORT)