

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331448-940

Luminaire Tested: **SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331448-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6875.7 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331448-940
CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	73	85	79	74	69	68	65	61	59	56	54	50	48	46	42
3	84	75	67	62	78	70	64	58	61	56	52	53	49	46	45	42	40	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	41	37	35	32
5	71	59	52	46	66	56	49	43	49	43	39	43	38	35	37	34	31	28
6	65	54	46	40	61	50	43	38	44	39	35	39	34	31	34	30	27	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	28	25	22	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20	18
10	49	37	30	26	46	35	29	25	32	26	22	28	24	20	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28709	28709	28709	28709
5°	32185	28896	25606	28896
10°	36882	28658	22161	28658
15°	40802	28134	19579	28134
20°	40180	27569	17849	27569
25°	36230	26820	16751	26820
30°	29940	25620	15951	25620
35°	21821	24366	15382	24366
40°	17428	22885	15066	22885
45°	15230	21174	14636	21174
50°	14315	19515	14350	19515
55°	13196	17833	13965	17833
60°	12093	16043	13372	16043
65°	11018	14437	12791	14437
70°	10003	12873	11939	12873
75°	8865	11123	10574	11123
80°	7624	9214	8517	9214
85°	6836	6836	5076	6836



TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.3	2.5
10°-20°	492.3	7.2
20°-30°	714.5	10.4
30°-40°	754.0	11.0
40°-50°	667.6	9.7
50°-60°	532.7	7.7
60°-70°	362.1	5.3
70°-80°	185.6	2.7
80°-90°	49.0	0.7
90°-100°	66.8	1.0
100°-110°	207.5	3.0
110°-120°	354.7	5.2
120°-130°	466.5	6.8
130°-140°	523.6	7.6
140°-150°	513.4	7.5
150°-160°	430.6	6.3
160°-170°	285.6	4.2
170°-180°	99.8	1.5
0°-30°	1376.1	20.0
0°-40°	2130.1	31.0
0°-60°	3330.4	48.4
0°-90°	3927.1	57.1
90°-120°	629.1	9.1
90°-150°	2132.6	31.0
90°-180°	2949.0	42.9
0°-180°	6875.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1778	1778	1778	1778	1778	
5°	1986	1783	1580	1783	1986	198
15°	2441	1683	1171	1683	2441	674
25°	2034	1506	940	1506	2034	919
35°	1107	1236	780	1236	1107	720
45°	667	927	641	927	667	524
55°	469	634	496	634	469	420
65°	288	378	335	378	288	287
75°	142	178	170	178	142	152
85°	37	37	27	37	37	41
90°	30	1	30	1	30	15
95°	55	46	55	46	55	62
105°	198	191	198	191	198	208
115°	356	356	356	356	356	352
125°	520	518	520	518	520	463
135°	678	670	678	670	678	522
145°	822	813	822	813	822	513
155°	937	930	937	930	937	431
165°	1013	1012	1013	1012	1013	286
175°	1049	1053	1049	1053	1049	100
180°	1054	1054	1054	1054	1054	



TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1860.1	1860.6	1861.7	1853.0	1851.9	1851.9	1844.2	1837.7	1830.1	1819.6	1820.8
5°	1985.8	1993.3	1996.1	1987.9	1975.6	1974.2	1962.7	1943.5	1925.7	1911.4	1901.1
7.5°	2135.9	2138.9	2132.3	2121.5	2112.3	2095.9	2074.3	2053.1	2023.5	1996.3	1976.0
10°	2249.6	2253.7	2242.1	2226.4	2213.4	2194.3	2162.8	2130.7	2091.8	2054.2	2024.1
12.5°	2336.0	2346.1	2331.2	2329.1	2306.9	2280.6	2243.2	2227.0	2172.1	2119.8	2087.6
15°	2441.0	2440.3	2441.7	2428.7	2412.3	2408.2	2368.6	2325.5	2248.3	2217.5	2164.2
17.5°	2410.7	2421.0	2425.8	2425.6	2425.3	2422.7	2409.9	2382.7	2344.0	2294.2	2232.7
20°	2338.5	2352.2	2354.2	2369.9	2378.8	2390.4	2395.2	2387.6	2363.7	2322.1	2268.8
22.5°	2227.0	2230.8	2237.2	2261.6	2280.9	2310.1	2325.2	2350.5	2341.4	2320.9	2276.4
25°	2033.7	2026.9	2050.8	2063.1	2107.5	2153.9	2187.5	2224.4	2257.2	2277.0	2264.0
27.5°	1801.6	1791.4	1827.2	1859.8	1896.0	1946.2	1998.4	2060.0	2111.3	2175.4	2197.4
30°	1605.9	1612.0	1646.2	1681.1	1735.7	1806.8	1865.5	1933.2	2006.3	2078.1	2128.0
32.5°	1394.9	1418.5	1440.1	1493.5	1541.7	1621.0	1707.0	1791.6	1882.8	1964.4	2041.7
35°	1107.1	1134.3	1164.5	1203.4	1271.0	1349.6	1433.7	1547.8	1672.2	1783.6	1875.2
37.5°	931.8	927.5	944.7	972.9	1027.6	1091.1	1187.8	1300.6	1447.0	1577.9	1707.0
40°	826.9	824.1	836.4	862.4	904.1	950.6	1035.3	1134.3	1270.3	1430.3	1584.0
42.5°	754.7	756.3	763.2	781.5	810.0	848.3	911.8	996.0	1120.6	1271.2	1436.5
45°	667.0	671.7	679.3	688.1	704.5	736.0	771.5	831.7	930.1	1055.8	1218.4
47.5°	603.8	604.0	611.6	619.4	629.1	646.8	675.8	713.5	783.0	885.4	1025.2
50°	569.9	565.2	570.6	576.8	587.0	599.3	618.4	654.0	700.4	783.1	900.0
52.5°	528.3	528.5	533.4	535.7	544.9	557.2	574.7	599.3	641.4	706.1	802.1
55°	468.8	472.2	474.9	479.0	487.2	496.1	509.8	526.2	559.0	607.5	678.6
57.5°	412.8	413.8	416.6	424.4	429.5	437.7	450.8	465.7	487.0	522.9	576.3
60°	374.5	374.5	380.0	383.3	390.2	398.4	408.7	423.0	442.1	471.5	514.6
62.5°	339.5	338.9	341.2	346.7	352.0	359.6	369.8	382.0	400.0	426.1	461.5
65°	288.4	287.0	291.1	292.5	297.9	305.5	313.7	326.6	341.0	360.2	391.6
67.5°	239.2	240.9	243.0	245.6	248.6	256.5	262.0	271.2	283.3	299.2	320.5
70°	211.9	211.9	211.9	213.9	218.0	222.1	227.6	235.1	246.7	260.4	279.5
72.5°	181.2	183.4	185.6	184.4	189.6	192.0	198.6	202.9	213.9	222.7	239.6
75°	142.1	142.1	142.1	145.5	147.6	149.6	153.7	157.8	163.4	174.2	183.2
77.5°	106.0	105.8	106.5	107.3	109.5	111.9	113.2	116.8	121.9	127.0	134.5
80°	82.0	83.4	84.1	85.4	85.4	86.8	87.5	92.3	95.7	99.1	103.9
82.5°	63.4	63.7	63.8	64.1	64.6	65.5	67.2	68.8	70.0	72.9	76.5
85°	36.9	36.2	36.2	37.5	36.9	36.9	38.3	39.6	39.6	40.3	42.4
87.5°	20.2	20.2	20.8	20.2	20.1	20.7	20.8	20.2	21.0	21.6	21.2
90°	30.2	30.1	29.9	29.7	29.4	29.6	30.0	30.3	30.8	31.1	26.8
92.5°	28.8	28.8	28.7	28.7	28.7	28.6	28.5	28.4	28.4	28.3	27.3
95°	55.2	55.6	56.0	56.4	56.7	57.0	57.0	57.0	57.0	57.0	56.5
97.5°	95.6	95.6	95.7	95.7	95.8	95.8	95.8	95.8	95.8	95.8	95.0
100°	121.9	122.1	122.3	122.5	122.7	122.8	122.8	122.8	122.8	122.8	122.3
102.5°	151.9	152.0	152.2	152.4	152.6	152.7	152.5	152.3	152.1	152.0	151.2
105°	197.5	197.5	197.5	197.5	197.5	197.3	197.0	196.5	196.2	195.7	195.4
107.5°	240.6	241.6	242.5	243.3	244.2	244.6	244.5	244.3	244.2	244.0	244.0
110°	274.1	274.6	275.3	275.9	276.4	276.8	276.8	276.8	276.8	276.8	276.8



TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	306.1	306.6	307.0	307.5	307.8	308.4	308.8	309.2	309.8	310.2	310.4
115°	356.0	356.5	357.1	357.8	358.3	358.7	358.9	359.1	359.4	359.5	359.9
117.5°	403.5	404.0	404.7	405.3	405.8	406.4	406.9	407.3	407.8	408.3	409.4
120°	436.9	437.6	438.1	438.7	439.3	439.6	439.6	439.6	439.6	439.6	441.2
122.5°	469.7	470.1	470.6	471.0	471.4	471.9	472.3	472.8	473.3	473.8	474.9
125°	519.7	519.9	520.0	520.3	520.5	520.8	521.5	522.1	522.6	523.3	523.9
127.5°	565.3	565.9	566.5	567.1	567.8	568.5	569.2	569.9	570.6	571.3	572.0
130°	598.0	598.8	599.6	600.4	601.2	601.7	602.2	602.5	603.0	603.3	603.8
132.5°	629.4	630.0	630.6	631.2	631.9	632.6	633.5	634.4	635.3	636.1	636.0
135°	678.1	678.7	679.3	679.8	680.5	680.8	681.1	681.3	681.4	681.6	681.3
137.5°	722.2	723.0	723.8	724.6	725.4	725.9	726.0	726.2	726.4	726.5	726.0
140°	752.9	753.7	754.4	755.2	756.0	756.4	756.4	756.4	756.4	756.4	755.5
142.5°	780.6	781.4	782.2	783.0	783.8	784.1	783.9	783.8	783.6	783.5	782.7
145°	822.2	823.0	823.9	824.7	825.5	825.7	825.5	825.3	825.1	824.9	823.8
147.5°	859.4	860.2	860.9	861.7	862.5	862.6	862.2	861.7	861.3	860.9	860.1
150°	883.7	884.2	884.8	885.5	886.0	886.0	885.5	884.8	884.2	883.7	882.9
152.5°	906.4	907.2	907.9	908.7	909.5	909.5	908.7	907.9	907.2	906.4	905.4
155°	937.0	937.6	938.3	938.8	939.4	939.2	938.3	937.3	936.3	935.2	934.7
157.5°	963.4	964.3	965.3	966.3	967.1	967.0	965.6	964.3	963.0	961.6	961.3
160°	979.7	980.5	981.3	982.1	982.9	982.8	981.5	980.3	979.2	977.9	977.8
162.5°	994.0	995.0	995.9	996.8	997.8	997.6	996.2	994.9	993.5	992.2	992.0
165°	1012.7	1013.7	1014.7	1015.7	1016.6	1016.5	1015.0	1013.7	1012.3	1010.9	1010.9
167.5°	1028.0	1029.0	1030.0	1031.1	1032.1	1031.9	1030.6	1029.1	1027.8	1026.4	1026.4
170°	1035.8	1037.0	1038.2	1039.4	1040.5	1040.4	1039.1	1037.7	1036.3	1034.9	1035.1
172.5°	1042.2	1043.4	1044.6	1045.8	1047.0	1046.9	1045.5	1044.1	1042.8	1041.3	1041.5
175°	1049.2	1050.3	1051.5	1052.8	1053.9	1053.8	1052.4	1051.1	1049.6	1048.3	1048.7
177.5°	1052.4	1053.3	1054.3	1055.3	1056.1	1056.1	1055.3	1054.3	1053.3	1052.4	1052.7
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1824.6	1820.2	1817.5	1807.7	1798.8	1790.1	1787.4	1788.5	1776.5	1765.0	1760.1
5°	1895.7	1882.0	1869.0	1850.6	1828.7	1804.7	1792.4	1782.9	1759.0	1733.0	1718.0
7.5°	1959.4	1939.8	1914.8	1880.1	1848.2	1810.6	1786.7	1765.5	1730.5	1693.9	1671.5
10°	1998.1	1971.5	1939.4	1897.0	1858.1	1812.3	1780.1	1748.0	1707.0	1663.3	1635.9
12.5°	2031.5	1995.6	1964.0	1909.6	1863.5	1806.2	1768.2	1722.9	1679.7	1627.7	1601.0
15°	2110.9	2044.6	1984.5	1923.0	1866.3	1786.3	1743.9	1683.1	1626.4	1562.2	1531.4
17.5°	2172.3	2097.7	2003.0	1924.9	1858.8	1770.2	1708.0	1635.1	1568.1	1494.7	1452.9
20°	2207.3	2121.8	2020.0	1927.1	1847.8	1746.7	1679.0	1604.5	1526.0	1443.2	1398.2
22.5°	2228.0	2138.2	2037.6	1918.9	1826.0	1727.5	1642.4	1560.8	1481.1	1391.9	1344.6
25°	2234.6	2152.6	2046.0	1912.1	1798.6	1687.2	1584.7	1505.5	1409.1	1325.7	1256.7
27.5°	2202.1	2143.3	2040.8	1899.2	1767.0	1636.8	1522.5	1432.7	1331.1	1240.5	1171.2
30°	2162.1	2128.0	2028.2	1886.1	1741.9	1601.8	1476.0	1374.2	1273.1	1181.5	1110.4
32.5°	2100.4	2093.0	2005.3	1867.5	1715.1	1557.6	1427.5	1324.5	1212.5	1122.5	1054.7
35°	1979.1	2011.8	1956.5	1826.0	1664.6	1494.5	1353.7	1236.2	1120.1	1033.9	970.4
37.5°	1816.4	1897.8	1883.4	1765.1	1596.6	1425.9	1270.5	1147.6	1037.0	950.0	887.7
40°	1704.3	1808.2	1823.2	1718.7	1548.5	1372.9	1208.2	1085.8	977.9	898.7	835.7
42.5°	1584.0	1705.4	1746.7	1662.9	1496.0	1317.1	1152.4	1025.7	918.8	841.8	786.0
45°	1382.4	1543.0	1617.6	1569.7	1408.5	1225.3	1055.8	927.3	830.3	757.9	714.8
47.5°	1194.0	1369.5	1469.6	1452.7	1311.0	1129.6	962.1	838.7	744.3	686.5	648.0
50°	1060.6	1241.0	1361.9	1367.4	1241.0	1061.2	893.1	776.9	690.2	636.2	604.8
52.5°	944.7	1116.9	1248.8	1277.7	1162.8	990.2	831.3	715.8	639.4	589.8	561.6
55°	793.4	939.0	1085.2	1138.4	1046.2	882.3	735.3	633.5	561.7	527.5	502.9
57.5°	659.6	781.0	916.0	974.9	918.0	777.7	639.9	551.4	493.3	463.3	444.4
60°	589.1	684.7	805.0	875.4	826.2	701.2	580.9	496.8	449.0	422.3	404.6
62.5°	523.4	608.2	709.9	774.3	747.4	629.5	521.8	447.6	406.4	381.3	368.5
65°	431.9	498.8	577.5	636.9	619.1	529.6	441.5	377.9	345.1	325.3	315.0
67.5°	355.6	404.0	458.5	510.6	496.2	432.8	362.0	312.5	288.1	271.0	264.8
70°	307.6	344.4	393.0	434.6	423.0	371.0	315.0	272.7	251.5	237.1	231.0
72.5°	261.6	291.9	329.0	363.0	355.2	312.0	265.3	233.3	217.0	203.8	198.8
75°	197.5	220.7	243.3	265.8	263.8	230.3	203.0	178.3	165.4	155.2	153.1
77.5°	145.8	158.8	174.2	187.5	183.8	164.7	143.2	129.1	119.6	112.7	111.6
80°	111.4	118.9	129.8	139.4	134.6	126.4	109.3	99.1	92.3	85.4	82.7
82.5°	80.8	88.3	94.9	100.0	96.4	88.7	78.2	71.2	67.1	62.4	61.3
85°	42.4	46.5	49.2	50.6	49.2	44.4	39.6	36.9	33.5	31.5	30.8
87.5°	20.9	20.1	19.2	19.5	17.5	16.9	14.4	12.2	12.1	12.0	11.4
90°	22.5	18.1	13.7	10.3	8.0	5.6	3.3	0.9	3.3	5.6	8.0
92.5°	26.2	25.2	24.2	22.8	21.0	19.4	17.6	15.9	17.6	19.4	21.0
95°	56.2	55.7	55.4	54.2	52.2	50.2	48.2	46.3	48.2	50.2	52.2
97.5°	94.3	93.5	92.7	91.5	89.8	88.0	86.3	84.5	86.3	88.0	89.8
100°	121.6	121.0	120.5	119.3	117.8	116.2	114.6	113.0	114.6	116.2	117.8
102.5°	150.5	149.7	149.0	147.9	146.7	145.4	144.2	142.9	144.2	145.4	146.7
105°	195.0	194.6	194.2	193.7	193.1	192.5	191.9	191.4	191.9	192.5	193.1
107.5°	244.0	244.0	244.0	243.6	242.7	241.8	240.9	240.0	240.9	241.8	242.7
110°	276.8	276.8	276.8	276.2	275.0	273.8	272.6	271.4	272.6	273.8	275.0



TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	310.5	310.7	310.9	310.3	309.2	308.0	306.7	305.6	306.7	308.0	309.2
115°	360.3	360.7	361.1	360.7	359.5	358.3	357.1	356.0	357.1	358.3	359.5
117.5°	410.5	411.6	412.7	412.5	410.9	409.3	407.7	406.2	407.7	409.3	410.9
120°	442.7	444.3	445.9	445.9	444.3	442.7	441.2	439.6	441.2	442.7	444.3
122.5°	476.0	477.1	478.2	477.8	475.9	474.0	472.1	470.2	472.1	474.0	475.9
125°	524.4	525.0	525.7	525.0	523.3	521.5	519.7	517.9	519.7	521.5	523.3
127.5°	572.7	573.5	574.2	573.4	571.1	568.9	566.6	564.4	566.6	568.9	571.1
130°	604.1	604.5	604.9	603.9	601.3	598.7	596.1	593.5	596.1	598.7	601.3
132.5°	636.0	635.9	635.8	634.7	632.6	630.5	628.4	626.3	628.4	630.5	632.6
135°	680.8	680.5	680.1	678.8	676.6	674.4	672.3	670.1	672.3	674.4	676.6
137.5°	725.5	725.0	724.4	723.3	721.5	719.7	717.9	716.2	717.9	719.7	721.5
140°	754.4	753.4	752.4	751.1	749.3	747.5	745.7	744.0	745.7	747.5	749.3
142.5°	782.1	781.4	780.8	779.5	777.8	776.0	774.2	772.4	774.2	776.0	777.8
145°	822.5	821.4	820.2	818.9	817.5	816.1	814.8	813.3	814.8	816.1	817.5
147.5°	859.3	858.5	857.7	856.5	854.8	853.2	851.5	849.8	851.5	853.2	854.8
150°	882.1	881.3	880.5	879.5	878.3	877.1	875.9	874.8	875.9	877.1	878.3
152.5°	904.6	903.6	902.7	901.6	900.4	899.2	898.0	896.8	898.0	899.2	900.4
155°	934.1	933.5	932.9	932.3	931.7	931.1	930.5	930.0	930.5	931.1	931.7
157.5°	960.9	960.6	960.2	959.8	959.4	959.0	958.6	958.2	958.6	959.0	959.4
160°	977.6	977.4	977.2	976.9	976.5	976.1	975.7	975.4	975.7	976.1	976.5
162.5°	991.8	991.7	991.4	991.3	991.2	991.1	991.0	991.0	991.0	991.1	991.2
165°	1010.9	1010.9	1010.9	1011.0	1011.2	1011.4	1011.6	1011.8	1011.6	1011.4	1011.2
167.5°	1026.4	1026.5	1026.5	1026.9	1027.4	1028.1	1028.7	1029.2	1028.7	1028.1	1027.4
170°	1035.4	1035.5	1035.7	1036.1	1036.7	1037.3	1037.9	1038.5	1037.9	1037.3	1036.7
172.5°	1041.7	1042.0	1042.1	1042.5	1043.1	1043.7	1044.3	1044.9	1044.3	1043.7	1043.1
175°	1049.1	1049.5	1049.9	1050.3	1051.0	1051.5	1052.1	1052.8	1052.1	1051.5	1051.0
177.5°	1053.0	1053.3	1053.6	1054.0	1054.5	1055.0	1055.4	1056.0	1055.4	1055.0	1054.5
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1754.6	1751.3	1739.8	1733.8	1724.0	1714.7	1708.7	1711.5	1713.6	1712.5	1710.8
5°	1704.3	1691.3	1671.5	1654.4	1642.1	1619.6	1610.0	1605.3	1601.2	1596.3	1591.5
7.5°	1644.4	1624.0	1595.5	1571.2	1548.2	1520.2	1504.2	1494.7	1484.8	1474.0	1464.5
10°	1601.8	1573.1	1543.0	1508.9	1481.6	1456.3	1433.7	1418.6	1405.0	1392.0	1382.4
12.5°	1557.0	1523.9	1486.7	1440.0	1409.9	1373.7	1370.3	1343.8	1322.4	1314.4	1303.1
15°	1485.6	1439.1	1392.0	1336.7	1312.8	1280.0	1259.5	1238.9	1220.5	1207.5	1204.1
17.5°	1404.6	1344.4	1297.5	1257.8	1218.6	1185.0	1166.1	1149.7	1134.5	1117.1	1114.8
20°	1342.8	1290.8	1239.7	1204.8	1164.5	1130.2	1107.1	1090.7	1077.6	1067.4	1058.5
22.5°	1284.3	1227.4	1180.5	1142.5	1102.7	1075.0	1056.8	1040.9	1030.1	1018.8	1010.4
25°	1190.4	1146.0	1094.8	1051.7	1018.9	1001.1	986.1	972.4	965.6	958.1	948.5
27.5°	1108.3	1058.9	1010.9	977.6	948.8	933.1	922.4	913.1	906.7	902.3	896.9
30°	1050.3	1000.4	962.9	930.1	906.2	890.5	883.6	878.2	870.6	867.9	865.1
32.5°	994.5	949.6	917.5	889.0	866.2	856.0	849.7	844.8	838.9	836.2	830.7
35°	915.7	878.2	846.7	831.0	812.5	803.6	798.9	792.0	786.6	783.8	783.1
37.5°	841.5	808.9	788.2	767.9	760.2	754.7	748.1	743.5	741.9	741.5	740.7
40°	793.4	766.7	748.3	731.9	728.4	720.2	714.8	710.7	710.7	711.4	710.7
42.5°	749.7	725.8	709.4	695.3	691.3	686.3	680.9	680.6	681.7	684.0	681.7
45°	683.4	666.3	654.7	647.8	640.3	635.5	634.8	636.9	637.6	638.3	640.3
47.5°	622.4	611.1	600.6	593.0	589.8	588.9	588.1	591.7	594.9	596.2	599.3
50°	586.3	573.4	564.5	559.6	557.0	555.5	557.0	561.1	563.7	567.2	569.3
52.5°	545.9	536.7	530.6	526.9	525.8	526.6	526.9	531.5	535.9	537.2	538.1
55°	490.0	483.1	481.8	475.6	478.3	477.7	481.1	483.8	487.9	492.0	492.7
57.5°	434.2	428.7	425.1	425.6	426.4	429.4	432.3	437.1	441.5	445.9	446.2
60°	397.1	394.3	392.3	392.3	393.6	397.7	401.1	405.9	408.7	411.3	413.4
62.5°	363.1	360.4	358.4	359.4	363.0	365.4	369.4	372.0	374.8	377.5	378.4
65°	309.6	308.2	310.2	311.7	312.3	315.8	320.5	322.5	325.3	326.6	331.4
67.5°	260.2	260.5	260.2	262.2	266.1	266.9	271.4	276.3	276.8	279.4	282.5
70°	226.9	228.3	229.6	231.0	234.4	235.8	239.2	241.2	244.0	246.0	248.1
72.5°	196.3	196.5	197.9	197.6	200.5	203.5	206.3	208.4	211.2	213.7	215.8
75°	151.1	151.1	152.4	153.1	156.5	159.9	159.3	160.6	163.4	166.0	167.5
77.5°	110.3	108.8	110.3	111.0	112.1	114.9	115.5	117.4	120.6	119.6	121.1
80°	84.1	82.0	84.1	84.7	84.7	88.2	88.2	89.5	91.6	89.5	91.6
82.5°	60.0	59.0	60.5	60.7	61.8	61.9	63.0	63.3	65.4	64.4	65.4
85°	30.1	29.4	30.1	29.4	30.1	30.8	30.8	30.1	30.1	31.5	29.4
87.5°	11.4	11.5	11.9	12.7	13.0	13.4	12.8	12.7	12.6	11.4	11.3
90°	10.3	13.7	18.1	22.5	26.8	31.1	30.8	30.3	30.0	29.6	29.4
92.5°	22.8	24.2	25.2	26.2	27.3	28.3	28.4	28.4	28.5	28.6	28.7
95°	54.2	55.4	55.7	56.2	56.5	57.0	57.0	57.0	57.0	57.0	56.7
97.5°	91.5	92.7	93.5	94.3	95.0	95.8	95.8	95.8	95.8	95.8	95.8
100°	119.3	120.5	121.0	121.6	122.3	122.8	122.8	122.8	122.8	122.8	122.7
102.5°	147.9	149.0	149.7	150.5	151.2	152.0	152.1	152.3	152.5	152.7	152.6
105°	193.7	194.2	194.6	195.0	195.4	195.7	196.2	196.5	197.0	197.3	197.5
107.5°	243.6	244.0	244.0	244.0	244.0	244.0	244.2	244.3	244.5	244.6	244.2
110°	276.2	276.8	276.8	276.8	276.8	276.8	276.8	276.8	276.8	276.8	276.4



TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	310.3	310.9	310.7	310.5	310.4	310.2	309.8	309.2	308.8	308.4	307.8
115°	360.7	361.1	360.7	360.3	359.9	359.5	359.4	359.1	358.9	358.7	358.3
117.5°	412.5	412.7	411.6	410.5	409.4	408.3	407.8	407.3	406.9	406.4	405.8
120°	445.9	445.9	444.3	442.7	441.2	439.6	439.6	439.6	439.6	439.6	439.3
122.5°	477.8	478.2	477.1	476.0	474.9	473.8	473.3	472.8	472.3	471.9	471.4
125°	525.0	525.7	525.0	524.4	523.9	523.3	522.6	522.1	521.5	520.8	520.5
127.5°	573.4	574.2	573.5	572.7	572.0	571.3	570.6	569.9	569.2	568.5	567.8
130°	603.9	604.9	604.5	604.1	603.8	603.3	603.0	602.5	602.2	601.7	601.2
132.5°	634.7	635.8	635.9	636.0	636.0	636.1	635.3	634.4	633.5	632.6	631.9
135°	678.8	680.1	680.5	680.8	681.3	681.6	681.4	681.3	681.1	680.8	680.5
137.5°	723.3	724.4	725.0	725.5	726.0	726.5	726.4	726.2	726.0	725.9	725.4
140°	751.1	752.4	753.4	754.4	755.5	756.4	756.4	756.4	756.4	756.4	756.0
142.5°	779.5	780.8	781.4	782.1	782.7	783.5	783.6	783.8	783.9	784.1	783.8
145°	818.9	820.2	821.4	822.5	823.8	824.9	825.1	825.3	825.5	825.7	825.5
147.5°	856.5	857.7	858.5	859.3	860.1	860.9	861.3	861.7	862.2	862.6	862.5
150°	879.5	880.5	881.3	882.1	882.9	883.7	884.2	884.8	885.5	886.0	886.0
152.5°	901.6	902.7	903.6	904.6	905.4	906.4	907.2	907.9	908.7	909.5	909.5
155°	932.3	932.9	933.5	934.1	934.7	935.2	936.3	937.3	938.3	939.2	939.4
157.5°	959.8	960.2	960.6	960.9	961.3	961.6	963.0	964.3	965.6	967.0	967.1
160°	976.9	977.2	977.4	977.6	977.8	977.9	979.2	980.3	981.5	982.8	982.9
162.5°	991.3	991.4	991.7	991.8	992.0	992.2	993.5	994.9	996.2	997.6	997.8
165°	1011.0	1010.9	1010.9	1010.9	1010.9	1010.9	1012.3	1013.7	1015.0	1016.5	1016.6
167.5°	1026.9	1026.5	1026.5	1026.4	1026.4	1026.4	1027.8	1029.1	1030.6	1031.9	1032.1
170°	1036.1	1035.7	1035.5	1035.4	1035.1	1034.9	1036.3	1037.7	1039.1	1040.4	1040.5
172.5°	1042.5	1042.1	1042.0	1041.7	1041.5	1041.3	1042.8	1044.1	1045.5	1046.9	1047.0
175°	1050.3	1049.9	1049.5	1049.1	1048.7	1048.3	1049.6	1051.1	1052.4	1053.8	1053.9
177.5°	1054.0	1053.6	1053.3	1053.0	1052.7	1052.4	1053.3	1054.3	1055.3	1056.1	1056.1
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1705.4	1704.3	1704.3	1699.4	1704.3	1704.3	1705.4	1710.8	1712.5	1713.6	1711.5
5°	1582.0	1579.9	1576.5	1579.9	1576.5	1579.9	1582.0	1591.5	1596.3	1601.2	1605.3
7.5°	1459.9	1451.7	1450.5	1442.4	1450.5	1451.7	1459.9	1464.5	1474.0	1484.8	1494.7
10°	1370.8	1365.4	1364.7	1351.7	1364.7	1365.4	1370.8	1382.4	1392.0	1405.0	1418.6
12.5°	1303.1	1289.9	1292.5	1285.0	1292.5	1289.9	1303.1	1303.1	1314.4	1322.4	1343.8
15°	1185.6	1185.6	1182.9	1171.3	1182.9	1185.6	1185.6	1204.1	1207.5	1220.5	1238.9
17.5°	1101.4	1099.9	1093.4	1096.6	1093.4	1099.9	1101.4	1114.8	1117.1	1134.5	1149.7
20°	1051.0	1047.0	1038.8	1038.8	1038.8	1047.0	1051.0	1058.5	1067.4	1077.6	1090.7
22.5°	1003.4	1003.2	994.4	997.2	994.4	1003.2	1003.4	1010.4	1018.8	1030.1	1040.9
25°	947.8	942.4	938.3	940.3	938.3	942.4	947.8	948.5	958.1	965.6	972.4
27.5°	895.1	892.1	891.8	886.2	891.8	892.1	895.1	896.9	902.3	906.7	913.1
30°	864.4	857.6	859.0	855.6	859.0	857.6	864.4	865.1	867.9	870.6	878.2
32.5°	829.5	827.0	825.6	822.8	825.6	827.0	829.5	830.7	836.2	838.9	844.8
35°	781.8	782.5	779.0	780.4	779.0	782.5	781.8	783.1	783.8	786.6	792.0
37.5°	740.1	742.3	740.7	741.0	740.7	742.3	740.1	740.7	741.5	741.9	743.5
40°	712.7	712.7	712.7	714.8	712.7	712.7	712.7	710.7	711.4	710.7	710.7
42.5°	686.5	685.5	684.3	684.2	684.3	685.5	686.5	681.7	684.0	681.7	680.6
45°	641.7	643.7	644.4	641.0	644.4	643.7	641.7	640.3	638.3	637.6	636.9
47.5°	601.1	601.4	601.1	604.1	601.1	601.4	601.1	599.3	596.2	594.9	591.7
50°	572.7	571.3	572.7	571.3	572.7	571.3	572.7	569.3	567.2	563.7	561.1
52.5°	542.6	542.9	542.1	541.8	542.1	542.9	542.6	538.1	537.2	535.9	531.5
55°	495.4	496.8	496.1	496.1	496.1	496.8	495.4	492.7	492.0	487.9	483.8
57.5°	446.7	447.9	448.8	445.9	448.8	447.9	446.7	446.2	445.9	441.5	437.1
60°	412.8	416.2	415.4	414.1	415.4	416.2	412.8	413.4	411.3	408.7	405.9
62.5°	381.6	382.8	382.7	382.5	382.7	382.8	381.6	378.4	377.5	374.8	372.0
65°	333.5	334.8	332.8	334.8	332.8	334.8	333.5	331.4	326.6	325.3	322.5
67.5°	281.7	282.1	283.6	284.5	283.6	282.1	281.7	282.5	279.4	276.8	276.3
70°	249.4	248.8	250.8	252.9	250.8	248.8	249.4	248.1	246.0	244.0	241.2
72.5°	215.5	217.0	216.3	217.8	216.3	217.0	215.5	215.8	213.7	211.2	208.4
75°	166.0	168.1	167.5	169.5	167.5	168.1	166.0	167.5	166.0	163.4	160.6
77.5°	120.0	120.3	120.0	121.1	120.0	120.3	120.0	121.1	119.6	120.6	117.4
80°	91.6	90.2	88.8	91.6	88.8	90.2	91.6	91.6	89.5	91.6	89.5
82.5°	63.7	64.5	63.1	63.1	63.1	64.5	63.7	65.4	64.4	65.4	63.3
85°	29.4	28.7	27.4	27.4	27.4	28.7	29.4	29.4	31.5	30.1	30.1
87.5°	11.4	10.9	11.0	10.4	11.0	10.9	11.4	11.3	11.4	12.6	12.7
90°	29.7	29.9	30.1	30.2	30.1	29.9	29.7	29.4	29.6	30.0	30.3
92.5°	28.7	28.7	28.8	28.8	28.8	28.7	28.7	28.7	28.6	28.5	28.4
95°	56.4	56.0	55.6	55.2	55.6	56.0	56.4	56.7	57.0	57.0	57.0
97.5°	95.7	95.7	95.6	95.6	95.6	95.7	95.7	95.8	95.8	95.8	95.8
100°	122.5	122.3	122.1	121.9	122.1	122.3	122.5	122.7	122.8	122.8	122.8
102.5°	152.4	152.2	152.0	151.9	152.0	152.2	152.4	152.6	152.7	152.5	152.3
105°	197.5	197.5	197.5	197.5	197.5	197.5	197.5	197.5	197.3	197.0	196.5
107.5°	243.3	242.5	241.6	240.6	241.6	242.5	243.3	244.2	244.6	244.5	244.3
110°	275.9	275.3	274.6	274.1	274.6	275.3	275.9	276.4	276.8	276.8	276.8



TEST NUMBER: P331448-940
 CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	307.5	307.0	306.6	306.1	306.6	307.0	307.5	307.8	308.4	308.8	309.2
115°	357.8	357.1	356.5	356.0	356.5	357.1	357.8	358.3	358.7	358.9	359.1
117.5°	405.3	404.7	404.0	403.5	404.0	404.7	405.3	405.8	406.4	406.9	407.3
120°	438.7	438.1	437.6	436.9	437.6	438.1	438.7	439.3	439.6	439.6	439.6
122.5°	471.0	470.6	470.1	469.7	470.1	470.6	471.0	471.4	471.9	472.3	472.8
125°	520.3	520.0	519.9	519.7	519.9	520.0	520.3	520.5	520.8	521.5	522.1
127.5°	567.1	566.5	565.9	565.3	565.9	566.5	567.1	567.8	568.5	569.2	569.9
130°	600.4	599.6	598.8	598.0	598.8	599.6	600.4	601.2	601.7	602.2	602.5
132.5°	631.2	630.6	630.0	629.4	630.0	630.6	631.2	631.9	632.6	633.5	634.4
135°	679.8	679.3	678.7	678.1	678.7	679.3	679.8	680.5	680.8	681.1	681.3
137.5°	724.6	723.8	723.0	722.2	723.0	723.8	724.6	725.4	725.9	726.0	726.2
140°	755.2	754.4	753.7	752.9	753.7	754.4	755.2	756.0	756.4	756.4	756.4
142.5°	783.0	782.2	781.4	780.6	781.4	782.2	783.0	783.8	784.1	783.9	783.8
145°	824.7	823.9	823.0	822.2	823.0	823.9	824.7	825.5	825.7	825.5	825.3
147.5°	861.7	860.9	860.2	859.4	860.2	860.9	861.7	862.5	862.6	862.2	861.7
150°	885.5	884.8	884.2	883.7	884.2	884.8	885.5	886.0	886.0	885.5	884.8
152.5°	908.7	907.9	907.2	906.4	907.2	907.9	908.7	909.5	909.5	908.7	907.9
155°	938.8	938.3	937.6	937.0	937.6	938.3	938.8	939.4	939.2	938.3	937.3
157.5°	966.3	965.3	964.3	963.4	964.3	965.3	966.3	967.1	967.0	965.6	964.3
160°	982.1	981.3	980.5	979.7	980.5	981.3	982.1	982.9	982.8	981.5	980.3
162.5°	996.8	995.9	995.0	994.0	995.0	995.9	996.8	997.8	997.6	996.2	994.9
165°	1015.7	1014.7	1013.7	1012.7	1013.7	1014.7	1015.7	1016.6	1016.5	1015.0	1013.7
167.5°	1031.1	1030.0	1029.0	1028.0	1029.0	1030.0	1031.1	1032.1	1031.9	1030.6	1029.1
170°	1039.4	1038.2	1037.0	1035.8	1037.0	1038.2	1039.4	1040.5	1040.4	1039.1	1037.7
172.5°	1045.8	1044.6	1043.4	1042.2	1043.4	1044.6	1045.8	1047.0	1046.9	1045.5	1044.1
175°	1052.8	1051.5	1050.3	1049.2	1050.3	1051.5	1052.8	1053.9	1053.8	1052.4	1051.1
177.5°	1055.3	1054.3	1053.3	1052.4	1053.3	1054.3	1055.3	1056.1	1056.1	1055.3	1054.3
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1708.7	1714.7	1724.0	1733.8	1739.8	1751.3	1754.6	1760.1	1765.0	1776.5	1788.5
5°	1610.0	1619.6	1642.1	1654.4	1671.5	1691.3	1704.3	1718.0	1733.0	1759.0	1782.9
7.5°	1504.2	1520.2	1548.2	1571.2	1595.5	1624.0	1644.4	1671.5	1693.9	1730.5	1765.5
10°	1433.7	1456.3	1481.6	1508.9	1543.0	1573.1	1601.8	1635.9	1663.3	1707.0	1748.0
12.5°	1370.3	1373.7	1409.9	1440.0	1486.7	1523.9	1557.0	1601.0	1627.7	1679.7	1722.9
15°	1259.5	1280.0	1312.8	1336.7	1392.0	1439.1	1485.6	1531.4	1562.2	1626.4	1683.1
17.5°	1166.1	1185.0	1218.6	1257.8	1297.5	1344.4	1404.6	1452.9	1494.7	1568.1	1635.1
20°	1107.1	1130.2	1164.5	1204.8	1239.7	1290.8	1342.8	1398.2	1443.2	1526.0	1604.5
22.5°	1056.8	1075.0	1102.7	1142.5	1180.5	1227.4	1284.3	1344.6	1391.9	1481.1	1560.8
25°	986.1	1001.1	1018.9	1051.7	1094.8	1146.0	1190.4	1256.7	1325.7	1409.1	1505.5
27.5°	922.4	933.1	948.8	977.6	1010.9	1058.9	1108.3	1171.2	1240.5	1331.1	1432.7
30°	883.6	890.5	906.2	930.1	962.9	1000.4	1050.3	1110.4	1181.5	1273.1	1374.2
32.5°	849.7	856.0	866.2	889.0	917.5	949.6	994.5	1054.7	1122.5	1212.5	1324.5
35°	798.9	803.6	812.5	831.0	846.7	878.2	915.7	970.4	1033.9	1120.1	1236.2
37.5°	748.1	754.7	760.2	767.9	788.2	808.9	841.5	887.7	950.0	1037.0	1147.6
40°	714.8	720.2	728.4	731.9	748.3	766.7	793.4	835.7	898.7	977.9	1085.8
42.5°	680.9	686.3	691.3	695.3	709.4	725.8	749.7	786.0	841.8	918.8	1025.7
45°	634.8	635.5	640.3	647.8	654.7	666.3	683.4	714.8	757.9	830.3	927.3
47.5°	588.1	588.9	589.8	593.0	600.6	611.1	622.4	648.0	686.5	744.3	838.7
50°	557.0	555.5	557.0	559.6	564.5	573.4	586.3	604.8	636.2	690.2	776.9
52.5°	526.9	526.6	525.8	526.9	530.6	536.7	545.9	561.6	589.8	639.4	715.8
55°	481.1	477.7	478.3	475.6	481.8	483.1	490.0	502.9	527.5	561.7	633.5
57.5°	432.3	429.4	426.4	425.6	425.1	428.7	434.2	444.4	463.3	493.3	551.4
60°	401.1	397.7	393.6	392.3	392.3	394.3	397.1	404.6	422.3	449.0	496.8
62.5°	369.4	365.4	363.0	359.4	358.4	360.4	363.1	368.5	381.3	406.4	447.6
65°	320.5	315.8	312.3	311.7	310.2	308.2	309.6	315.0	325.3	345.1	377.9
67.5°	271.4	266.9	266.1	262.2	260.2	260.5	260.2	264.8	271.0	288.1	312.5
70°	239.2	235.8	234.4	231.0	229.6	228.3	226.9	231.0	237.1	251.5	272.7
72.5°	206.3	203.5	200.5	197.6	197.9	196.5	196.3	198.8	203.8	217.0	233.3
75°	159.3	159.9	156.5	153.1	152.4	151.1	151.1	153.1	155.2	165.4	178.3
77.5°	115.5	114.9	112.1	111.0	110.3	108.8	110.3	111.6	112.7	119.6	129.1
80°	88.2	88.2	84.7	84.7	84.1	82.0	84.1	82.7	85.4	92.3	99.1
82.5°	63.0	61.9	61.8	60.7	60.5	59.0	60.0	61.3	62.4	67.1	71.2
85°	30.8	30.8	30.1	29.4	30.1	29.4	30.1	30.8	31.5	33.5	36.9
87.5°	12.8	13.4	13.0	12.7	11.9	11.5	11.4	11.4	12.0	12.1	12.2
90°	30.8	31.1	26.8	22.5	18.1	13.7	10.3	8.0	5.6	3.3	0.9
92.5°	28.4	28.3	27.3	26.2	25.2	24.2	22.8	21.0	19.4	17.6	15.9
95°	57.0	57.0	56.5	56.2	55.7	55.4	54.2	52.2	50.2	48.2	46.3
97.5°	95.8	95.8	95.0	94.3	93.5	92.7	91.5	89.8	88.0	86.3	84.5
100°	122.8	122.8	122.3	121.6	121.0	120.5	119.3	117.8	116.2	114.6	113.0
102.5°	152.1	152.0	151.2	150.5	149.7	149.0	147.9	146.7	145.4	144.2	142.9
105°	196.2	195.7	195.4	195.0	194.6	194.2	193.7	193.1	192.5	191.9	191.4
107.5°	244.2	244.0	244.0	244.0	244.0	244.0	243.6	242.7	241.8	240.9	240.0
110°	276.8	276.8	276.8	276.8	276.8	276.8	276.2	275.0	273.8	272.6	271.4



TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	309.8	310.2	310.4	310.5	310.7	310.9	310.3	309.2	308.0	306.7	305.6
115°	359.4	359.5	359.9	360.3	360.7	361.1	360.7	359.5	358.3	357.1	356.0
117.5°	407.8	408.3	409.4	410.5	411.6	412.7	412.5	410.9	409.3	407.7	406.2
120°	439.6	439.6	441.2	442.7	444.3	445.9	445.9	444.3	442.7	441.2	439.6
122.5°	473.3	473.8	474.9	476.0	477.1	478.2	477.8	475.9	474.0	472.1	470.2
125°	522.6	523.3	523.9	524.4	525.0	525.7	525.0	523.3	521.5	519.7	517.9
127.5°	570.6	571.3	572.0	572.7	573.5	574.2	573.4	571.1	568.9	566.6	564.4
130°	603.0	603.3	603.8	604.1	604.5	604.9	603.9	601.3	598.7	596.1	593.5
132.5°	635.3	636.1	636.0	636.0	635.9	635.8	634.7	632.6	630.5	628.4	626.3
135°	681.4	681.6	681.3	680.8	680.5	680.1	678.8	676.6	674.4	672.3	670.1
137.5°	726.4	726.5	726.0	725.5	725.0	724.4	723.3	721.5	719.7	717.9	716.2
140°	756.4	756.4	755.5	754.4	753.4	752.4	751.1	749.3	747.5	745.7	744.0
142.5°	783.6	783.5	782.7	782.1	781.4	780.8	779.5	777.8	776.0	774.2	772.4
145°	825.1	824.9	823.8	822.5	821.4	820.2	818.9	817.5	816.1	814.8	813.3
147.5°	861.3	860.9	860.1	859.3	858.5	857.7	856.5	854.8	853.2	851.5	849.8
150°	884.2	883.7	882.9	882.1	881.3	880.5	879.5	878.3	877.1	875.9	874.8
152.5°	907.2	906.4	905.4	904.6	903.6	902.7	901.6	900.4	899.2	898.0	896.8
155°	936.3	935.2	934.7	934.1	933.5	932.9	932.3	931.7	931.1	930.5	930.0
157.5°	963.0	961.6	961.3	960.9	960.6	960.2	959.8	959.4	959.0	958.6	958.2
160°	979.2	977.9	977.8	977.6	977.4	977.2	976.9	976.5	976.1	975.7	975.4
162.5°	993.5	992.2	992.0	991.8	991.7	991.4	991.3	991.2	991.1	991.0	991.0
165°	1012.3	1010.9	1010.9	1010.9	1010.9	1010.9	1011.0	1011.2	1011.4	1011.6	1011.8
167.5°	1027.8	1026.4	1026.4	1026.4	1026.5	1026.5	1026.9	1027.4	1028.1	1028.7	1029.2
170°	1036.3	1034.9	1035.1	1035.4	1035.5	1035.7	1036.1	1036.7	1037.3	1037.9	1038.5
172.5°	1042.8	1041.3	1041.5	1041.7	1042.0	1042.1	1042.5	1043.1	1043.7	1044.3	1044.9
175°	1049.6	1048.3	1048.7	1049.1	1049.5	1049.9	1050.3	1051.0	1051.5	1052.1	1052.8
177.5°	1053.3	1052.4	1052.7	1053.0	1053.3	1053.6	1054.0	1054.5	1055.0	1055.4	1056.0
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331448-940
 CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1787.4	1790.1	1798.8	1807.7	1817.5	1820.2	1824.6	1820.8	1819.6	1830.1	1837.7
5°	1792.4	1804.7	1828.7	1850.6	1869.0	1882.0	1895.7	1901.1	1911.4	1925.7	1943.5
7.5°	1786.7	1810.6	1848.2	1880.1	1914.8	1939.8	1959.4	1976.0	1996.3	2023.5	2053.1
10°	1780.1	1812.3	1858.1	1897.0	1939.4	1971.5	1998.1	2024.1	2054.2	2091.8	2130.7
12.5°	1768.2	1806.2	1863.5	1909.6	1964.0	1995.6	2031.5	2087.6	2119.8	2172.1	2227.0
15°	1743.9	1786.3	1866.3	1923.0	1984.5	2044.6	2110.9	2164.2	2217.5	2248.3	2325.5
17.5°	1708.0	1770.2	1858.8	1924.9	2003.0	2097.7	2172.3	2232.7	2294.2	2344.0	2382.7
20°	1679.0	1746.7	1847.8	1927.1	2020.0	2121.8	2207.3	2268.8	2322.1	2363.7	2387.6
22.5°	1642.4	1727.5	1826.0	1918.9	2037.6	2138.2	2228.0	2276.4	2320.9	2341.4	2350.5
25°	1584.7	1687.2	1798.6	1912.1	2046.0	2152.6	2234.6	2264.0	2277.0	2257.2	2224.4
27.5°	1522.5	1636.8	1767.0	1899.2	2040.8	2143.3	2202.1	2197.4	2175.4	2111.3	2060.0
30°	1476.0	1601.8	1741.9	1886.1	2028.2	2128.0	2162.1	2128.0	2078.1	2006.3	1933.2
32.5°	1427.5	1557.6	1715.1	1867.5	2005.3	2093.0	2100.4	2041.7	1964.4	1882.8	1791.6
35°	1353.7	1494.5	1664.6	1826.0	1956.5	2011.8	1979.1	1875.2	1783.6	1672.2	1547.8
37.5°	1270.5	1425.9	1596.6	1765.1	1883.4	1897.8	1816.4	1707.0	1577.9	1447.0	1300.6
40°	1208.2	1372.9	1548.5	1718.7	1823.2	1808.2	1704.3	1584.0	1430.3	1270.3	1134.3
42.5°	1152.4	1317.1	1496.0	1662.9	1746.7	1705.4	1584.0	1436.5	1271.2	1120.6	996.0
45°	1055.8	1225.3	1408.5	1569.7	1617.6	1543.0	1382.4	1218.4	1055.8	930.1	831.7
47.5°	962.1	1129.6	1311.0	1452.7	1469.6	1369.5	1194.0	1025.2	885.4	783.0	713.5
50°	893.1	1061.2	1241.0	1367.4	1361.9	1241.0	1060.6	900.0	783.1	700.4	654.0
52.5°	831.3	990.2	1162.8	1277.7	1248.8	1116.9	944.7	802.1	706.1	641.4	599.3
55°	735.3	882.3	1046.2	1138.4	1085.2	939.0	793.4	678.6	607.5	559.0	526.2
57.5°	639.9	777.7	918.0	974.9	916.0	781.0	659.6	576.3	522.9	487.0	465.7
60°	580.9	701.2	826.2	875.4	805.0	684.7	589.1	514.6	471.5	442.1	423.0
62.5°	521.8	629.5	747.4	774.3	709.9	608.2	523.4	461.5	426.1	400.0	382.0
65°	441.5	529.6	619.1	636.9	577.5	498.8	431.9	391.6	360.2	341.0	326.6
67.5°	362.0	432.8	496.2	510.6	458.5	404.0	355.6	320.5	299.2	283.3	271.2
70°	315.0	371.0	423.0	434.6	393.0	344.4	307.6	279.5	260.4	246.7	235.1
72.5°	265.3	312.0	355.2	363.0	329.0	291.9	261.6	239.6	222.7	213.9	202.9
75°	203.0	230.3	263.8	265.8	243.3	220.7	197.5	183.2	174.2	163.4	157.8
77.5°	143.2	164.7	183.8	187.5	174.2	158.8	145.8	134.5	127.0	121.9	116.8
80°	109.3	126.4	134.6	139.4	129.8	118.9	111.4	103.9	99.1	95.7	92.3
82.5°	78.2	88.7	96.4	100.0	94.9	88.3	80.8	76.5	72.9	70.0	68.8
85°	39.6	44.4	49.2	50.6	49.2	46.5	42.4	42.4	40.3	39.6	39.6
87.5°	14.4	16.9	17.5	19.5	19.2	20.1	20.9	21.2	21.6	21.0	20.2
90°	3.3	5.6	8.0	10.3	13.7	18.1	22.5	26.8	31.1	30.8	30.3
92.5°	17.6	19.4	21.0	22.8	24.2	25.2	26.2	27.3	28.3	28.4	28.4
95°	48.2	50.2	52.2	54.2	55.4	55.7	56.2	56.5	57.0	57.0	57.0
97.5°	86.3	88.0	89.8	91.5	92.7	93.5	94.3	95.0	95.8	95.8	95.8
100°	114.6	116.2	117.8	119.3	120.5	121.0	121.6	122.3	122.8	122.8	122.8
102.5°	144.2	145.4	146.7	147.9	149.0	149.7	150.5	151.2	152.0	152.1	152.3
105°	191.9	192.5	193.1	193.7	194.2	194.6	195.0	195.4	195.7	196.2	196.5
107.5°	240.9	241.8	242.7	243.6	244.0	244.0	244.0	244.0	244.0	244.2	244.3
110°	272.6	273.8	275.0	276.2	276.8	276.8	276.8	276.8	276.8	276.8	276.8



TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	306.7	308.0	309.2	310.3	310.9	310.7	310.5	310.4	310.2	309.8	309.2
115°	357.1	358.3	359.5	360.7	361.1	360.7	360.3	359.9	359.5	359.4	359.1
117.5°	407.7	409.3	410.9	412.5	412.7	411.6	410.5	409.4	408.3	407.8	407.3
120°	441.2	442.7	444.3	445.9	445.9	444.3	442.7	441.2	439.6	439.6	439.6
122.5°	472.1	474.0	475.9	477.8	478.2	477.1	476.0	474.9	473.8	473.3	472.8
125°	519.7	521.5	523.3	525.0	525.7	525.0	524.4	523.9	523.3	522.6	522.1
127.5°	566.6	568.9	571.1	573.4	574.2	573.5	572.7	572.0	571.3	570.6	569.9
130°	596.1	598.7	601.3	603.9	604.9	604.5	604.1	603.8	603.3	603.0	602.5
132.5°	628.4	630.5	632.6	634.7	635.8	635.9	636.0	636.0	636.1	635.3	634.4
135°	672.3	674.4	676.6	678.8	680.1	680.5	680.8	681.3	681.6	681.4	681.3
137.5°	717.9	719.7	721.5	723.3	724.4	725.0	725.5	726.0	726.5	726.4	726.2
140°	745.7	747.5	749.3	751.1	752.4	753.4	754.4	755.5	756.4	756.4	756.4
142.5°	774.2	776.0	777.8	779.5	780.8	781.4	782.1	782.7	783.5	783.6	783.8
145°	814.8	816.1	817.5	818.9	820.2	821.4	822.5	823.8	824.9	825.1	825.3
147.5°	851.5	853.2	854.8	856.5	857.7	858.5	859.3	860.1	860.9	861.3	861.7
150°	875.9	877.1	878.3	879.5	880.5	881.3	882.1	882.9	883.7	884.2	884.8
152.5°	898.0	899.2	900.4	901.6	902.7	903.6	904.6	905.4	906.4	907.2	907.9
155°	930.5	931.1	931.7	932.3	932.9	933.5	934.1	934.7	935.2	936.3	937.3
157.5°	958.6	959.0	959.4	959.8	960.2	960.6	960.9	961.3	961.6	963.0	964.3
160°	975.7	976.1	976.5	976.9	977.2	977.4	977.6	977.8	977.9	979.2	980.3
162.5°	991.0	991.1	991.2	991.3	991.4	991.7	991.8	992.0	992.2	993.5	994.9
165°	1011.6	1011.4	1011.2	1011.0	1010.9	1010.9	1010.9	1010.9	1010.9	1012.3	1013.7
167.5°	1028.7	1028.1	1027.4	1026.9	1026.5	1026.5	1026.4	1026.4	1026.4	1027.8	1029.1
170°	1037.9	1037.3	1036.7	1036.1	1035.7	1035.5	1035.4	1035.1	1034.9	1036.3	1037.7
172.5°	1044.3	1043.7	1043.1	1042.5	1042.1	1042.0	1041.7	1041.5	1041.3	1042.8	1044.1
175°	1052.1	1051.5	1051.0	1050.3	1049.9	1049.5	1049.1	1048.7	1048.3	1049.6	1051.1
177.5°	1055.4	1055.0	1054.5	1054.0	1053.6	1053.3	1053.0	1052.7	1052.4	1053.3	1054.3
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1844.2	1851.9	1851.9	1853.0	1861.7	1860.6	1860.1
5°	1962.7	1974.2	1975.6	1987.9	1996.1	1993.3	1985.8
7.5°	2074.3	2095.9	2112.3	2121.5	2132.3	2138.9	2135.9
10°	2162.8	2194.3	2213.4	2226.4	2242.1	2253.7	2249.6
12.5°	2243.2	2280.6	2306.9	2329.1	2331.2	2346.1	2336.0
15°	2368.6	2408.2	2412.3	2428.7	2441.7	2440.3	2441.0
17.5°	2409.9	2422.7	2425.3	2425.6	2425.8	2421.0	2410.7
20°	2395.2	2390.4	2378.8	2369.9	2354.2	2352.2	2338.5
22.5°	2325.2	2310.1	2280.9	2261.6	2237.2	2230.8	2227.0
25°	2187.5	2153.9	2107.5	2063.1	2050.8	2026.9	2033.7
27.5°	1998.4	1946.2	1896.0	1859.8	1827.2	1791.4	1801.6
30°	1865.5	1806.8	1735.7	1681.1	1646.2	1612.0	1605.9
32.5°	1707.0	1621.0	1541.7	1493.5	1440.1	1418.5	1394.9
35°	1433.7	1349.6	1271.0	1203.4	1164.5	1134.3	1107.1
37.5°	1187.8	1091.1	1027.6	972.9	944.7	927.5	931.8
40°	1035.3	950.6	904.1	862.4	836.4	824.1	826.9
42.5°	911.8	848.3	810.0	781.5	763.2	756.3	754.7
45°	771.5	736.0	704.5	688.1	679.3	671.7	667.0
47.5°	675.8	646.8	629.1	619.4	611.6	604.0	603.8
50°	618.4	599.3	587.0	576.8	570.6	565.2	569.9
52.5°	574.7	557.2	544.9	535.7	533.4	528.5	528.3
55°	509.8	496.1	487.2	479.0	474.9	472.2	468.8
57.5°	450.8	437.7	429.5	424.4	416.6	413.8	412.8
60°	408.7	398.4	390.2	383.3	380.0	374.5	374.5
62.5°	369.8	359.6	352.0	346.7	341.2	338.9	339.5
65°	313.7	305.5	297.9	292.5	291.1	287.0	288.4
67.5°	262.0	256.5	248.6	245.6	243.0	240.9	239.2
70°	227.6	222.1	218.0	213.9	211.9	211.9	211.9
72.5°	198.6	192.0	189.6	184.4	185.6	183.4	181.2
75°	153.7	149.6	147.6	145.5	142.1	142.1	142.1
77.5°	113.2	111.9	109.5	107.3	106.5	105.8	106.0
80°	87.5	86.8	85.4	85.4	84.1	83.4	82.0
82.5°	67.2	65.5	64.6	64.1	63.8	63.7	63.4
85°	38.3	36.9	36.9	37.5	36.2	36.2	36.9
87.5°	20.8	20.7	20.1	20.2	20.8	20.2	20.2
90°	30.0	29.6	29.4	29.7	29.9	30.1	30.2
92.5°	28.5	28.6	28.7	28.7	28.7	28.8	28.8
95°	57.0	57.0	56.7	56.4	56.0	55.6	55.2
97.5°	95.8	95.8	95.8	95.7	95.7	95.6	95.6
100°	122.8	122.8	122.7	122.5	122.3	122.1	121.9
102.5°	152.5	152.7	152.6	152.4	152.2	152.0	151.9
105°	197.0	197.3	197.5	197.5	197.5	197.5	197.5
107.5°	244.5	244.6	244.2	243.3	242.5	241.6	240.6
110°	276.8	276.8	276.4	275.9	275.3	274.6	274.1



TEST NUMBER: P331448-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	308.8	308.4	307.8	307.5	307.0	306.6	306.1
115°	358.9	358.7	358.3	357.8	357.1	356.5	356.0
117.5°	406.9	406.4	405.8	405.3	404.7	404.0	403.5
120°	439.6	439.6	439.3	438.7	438.1	437.6	436.9
122.5°	472.3	471.9	471.4	471.0	470.6	470.1	469.7
125°	521.5	520.8	520.5	520.3	520.0	519.9	519.7
127.5°	569.2	568.5	567.8	567.1	566.5	565.9	565.3
130°	602.2	601.7	601.2	600.4	599.6	598.8	598.0
132.5°	633.5	632.6	631.9	631.2	630.6	630.0	629.4
135°	681.1	680.8	680.5	679.8	679.3	678.7	678.1
137.5°	726.0	725.9	725.4	724.6	723.8	723.0	722.2
140°	756.4	756.4	756.0	755.2	754.4	753.7	752.9
142.5°	783.9	784.1	783.8	783.0	782.2	781.4	780.6
145°	825.5	825.7	825.5	824.7	823.9	823.0	822.2
147.5°	862.2	862.6	862.5	861.7	860.9	860.2	859.4
150°	885.5	886.0	886.0	885.5	884.8	884.2	883.7
152.5°	908.7	909.5	909.5	908.7	907.9	907.2	906.4
155°	938.3	939.2	939.4	938.8	938.3	937.6	937.0
157.5°	965.6	967.0	967.1	966.3	965.3	964.3	963.4
160°	981.5	982.8	982.9	982.1	981.3	980.5	979.7
162.5°	996.2	997.6	997.8	996.8	995.9	995.0	994.0
165°	1015.0	1016.5	1016.6	1015.7	1014.7	1013.7	1012.7
167.5°	1030.6	1031.9	1032.1	1031.1	1030.0	1029.0	1028.0
170°	1039.1	1040.4	1040.5	1039.4	1038.2	1037.0	1035.8
172.5°	1045.5	1046.9	1047.0	1045.8	1044.6	1043.4	1042.2
175°	1052.4	1053.8	1053.9	1052.8	1051.5	1050.3	1049.2
177.5°	1055.3	1056.1	1056.1	1055.3	1054.3	1053.3	1052.4
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5

(END OF REPORT)