

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332945-830

Luminaire Tested: **SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332945-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6630.9 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	98	94	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26
5	69	58	50	44	63	53	46	41	46	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15
10	47	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10044	10044	10044	10044
5°	11651	10075	8904	10075
10°	13782	10030	7947	10030
15°	15921	9937	6829	9937
20°	17725	9810	6176	9810
25°	18299	9685	5734	9685
30°	16018	9533	5466	9533
35°	12470	9307	5306	9307
40°	9351	9049	5220	9049
45°	7383	8636	5174	8636
50°	6232	8160	5024	8160
55°	5433	7633	4756	7633
60°	4887	7090	4209	7090
65°	4309	6502	3620	6502
70°	3880	5894	3267	5894
75°	3250	5221	2785	5221
80°	2752	4454	2613	4454
85°	2325	3483	2325	3483



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.6	1.8
10°-20°	363.6	5.5
20°-30°	568.8	8.6
30°-40°	632.3	9.5
40°-50°	561.0	8.5
50°-60°	437.1	6.6
60°-70°	286.2	4.3
70°-80°	140.7	2.1
80°-90°	37.4	0.6
90°-100°	345.9	5.2
100°-110°	720.0	10.9
110°-120°	644.9	9.7
120°-130°	542.4	8.2
130°-140°	452.3	6.8
140°-150°	345.5	5.2
150°-160°	242.9	3.7
160°-170°	142.9	2.2
170°-180°	46.5	0.7
0°-30°	1052.9	15.9
0°-40°	1685.2	25.4
0°-60°	2683.3	40.5
0°-90°	3147.6	47.5
90°-120°	1710.8	25.8
90°-150°	3051.1	46.0
90°-180°	3483.0	52.5
0°-180°	6630.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1244	1244	1244	1244	1244	
5°	1438	1243	1099	1243	1438	145
15°	1905	1189	817	1189	1905	542
25°	2054	1087	644	1087	2054	911
35°	1265	944	538	944	1265	793
45°	647	756	453	756	647	512
55°	386	542	338	542	386	351
65°	226	340	190	340	226	227
75°	104	167	89	167	104	115
85°	25	38	25	38	25	29
90°	20	1	20	1	20	17
95°	230	31	230	31	230	356
105°	1324	110	1324	110	1324	1309
115°	1271	194	1271	194	1271	1262
125°	1014	270	1014	270	1014	922
135°	907	321	907	321	907	700
145°	741	370	741	370	741	469
155°	620	421	620	421	620	289
165°	541	458	541	458	541	155
175°	487	478	487	478	487	47
180°	479	479	479	479	479	



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1312.3	1316.0	1312.3	1311.9	1308.0	1306.7	1305.1	1300.0	1290.2	1284.7	1285.9
5°	1437.7	1450.2	1443.2	1442.2	1431.2	1420.1	1413.1	1397.0	1380.0	1368.5	1359.0
7.5°	1582.6	1589.9	1585.5	1578.4	1560.6	1550.5	1534.2	1513.1	1482.5	1459.2	1437.8
10°	1681.3	1687.3	1685.3	1672.3	1659.3	1632.7	1617.6	1588.1	1549.4	1518.9	1490.3
12.5°	1778.3	1784.8	1767.1	1767.7	1743.0	1722.1	1698.3	1661.0	1616.5	1577.1	1541.2
15°	1904.9	1896.9	1896.9	1886.8	1859.3	1830.1	1805.6	1766.5	1710.3	1663.2	1613.6
17.5°	2003.9	2006.7	2002.6	1979.0	1957.3	1927.2	1882.2	1836.5	1784.4	1721.2	1670.5
20°	2063.2	2063.2	2058.8	2042.7	2014.7	1982.5	1933.9	1884.3	1818.2	1754.4	1697.3
22.5°	2087.4	2089.0	2083.6	2070.4	2045.1	2013.8	1972.5	1922.0	1853.8	1782.2	1711.4
25°	2054.3	2063.8	2064.7	2061.2	2053.7	2034.7	1999.1	1947.5	1886.3	1808.6	1732.4
27.5°	1886.0	1898.0	1908.6	1925.9	1949.0	1961.0	1962.6	1936.4	1883.0	1808.2	1731.5
30°	1718.3	1728.4	1761.0	1803.6	1836.7	1866.8	1892.8	1899.9	1869.8	1802.6	1721.9
32.5°	1532.3	1546.0	1578.6	1624.4	1679.5	1730.4	1788.9	1818.8	1818.1	1777.7	1703.1
35°	1265.3	1275.3	1305.3	1353.5	1419.7	1495.3	1588.1	1660.2	1709.4	1705.8	1660.2
37.5°	1020.4	1031.7	1062.2	1102.0	1166.2	1259.9	1349.6	1449.1	1539.9	1590.9	1575.7
40°	887.3	887.8	917.4	958.5	1018.6	1100.3	1198.1	1308.3	1409.6	1492.3	1508.4
42.5°	782.2	782.3	801.8	846.1	889.5	966.4	1059.7	1169.2	1287.7	1383.3	1425.8
45°	646.7	651.2	667.2	693.8	727.8	793.1	867.7	969.5	1102.3	1215.6	1286.3
47.5°	547.6	554.2	564.4	586.1	613.2	656.7	718.4	809.8	917.9	1042.5	1143.1
50°	496.2	497.3	510.3	522.4	545.9	580.5	634.6	710.8	810.0	929.9	1041.7
52.5°	452.1	451.9	459.8	475.0	494.2	521.1	564.9	634.2	722.3	829.6	945.0
55°	386.0	388.5	394.5	406.5	421.0	440.2	474.7	526.9	596.1	687.8	792.5
57.5°	335.6	337.0	341.7	346.8	360.1	374.0	399.9	436.1	494.5	569.6	667.2
60°	302.7	303.3	304.8	312.3	322.8	335.8	353.4	384.0	433.1	501.8	579.0
62.5°	270.7	271.5	273.9	279.4	287.6	296.5	314.9	339.5	380.1	438.8	508.4
65°	225.6	226.1	229.6	231.6	238.1	246.1	259.7	276.2	304.3	353.4	406.0
67.5°	188.5	188.5	188.7	191.4	195.9	201.2	209.3	222.5	243.7	273.9	320.3
70°	164.4	164.4	165.4	166.9	169.5	173.9	178.4	188.5	204.1	228.6	264.2
72.5°	141.9	142.3	143.4	143.6	145.0	148.6	152.0	158.4	169.9	188.5	217.3
75°	104.2	105.8	108.3	110.3	112.8	112.3	115.8	119.8	123.3	134.3	150.9
77.5°	77.6	76.8	77.1	78.8	79.1	79.6	82.1	85.2	87.8	93.0	99.0
80°	59.2	59.2	60.7	61.2	60.7	61.2	63.6	65.1	66.2	68.1	73.7
82.5°	44.7	45.5	45.1	45.5	45.8	46.3	48.4	48.7	49.8	50.5	52.9
85°	25.1	25.5	26.1	25.1	25.1	25.1	26.1	26.6	27.6	27.1	28.1
87.5°	12.8	12.3	13.0	12.8	13.0	12.6	12.8	13.4	12.4	13.0	12.6
90°	19.8	19.8	20.7	19.8	18.9	18.9	17.9	17.0	16.0	17.0	15.1
92.5°	72.5	72.5	75.7	80.8	91.8	110.7	139.1	184.8	248.6	298.5	261.2
95°	229.6	241.9	258.7	287.9	334.0	425.3	551.4	697.2	788.5	766.9	578.7
97.5°	613.7	633.3	661.5	718.1	785.7	883.9	975.9	1030.2	990.6	807.7	541.6
100°	862.9	870.3	898.6	956.0	1037.8	1107.5	1153.6	1134.8	997.4	756.5	491.2
102.5°	1079.7	1085.7	1115.4	1157.0	1207.2	1236.2	1222.9	1129.5	940.9	692.6	457.3
105°	1323.9	1329.6	1342.7	1350.3	1348.4	1309.8	1216.6	1053.9	838.4	617.3	428.1
107.5°	1414.7	1412.2	1402.8	1381.3	1334.8	1250.9	1119.7	946.4	755.5	575.1	422.8
110°	1416.2	1407.7	1390.7	1351.2	1284.4	1180.9	1044.4	881.7	714.2	560.8	424.3



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1371.7	1358.0	1334.3	1286.5	1210.6	1107.1	978.2	834.2	690.9	554.0	428.9
115°	1271.2	1263.7	1233.6	1177.1	1102.8	1012.5	902.4	786.6	669.0	550.4	437.5
117.5°	1169.4	1163.6	1133.1	1085.7	1022.3	945.7	859.1	763.3	659.2	549.5	446.8
120°	1112.2	1101.8	1077.4	1035.9	982.3	915.6	840.3	752.7	653.9	549.5	453.6
122.5°	1067.1	1056.7	1035.9	1000.6	955.3	896.7	828.2	743.8	647.9	548.7	460.3
125°	1014.4	1008.7	990.8	963.6	925.9	874.1	809.2	728.3	638.0	547.6	470.5
127.5°	983.4	977.8	962.8	938.5	900.7	851.6	786.8	709.5	624.6	545.5	478.5
130°	965.4	959.8	944.7	921.1	882.6	832.7	768.7	694.5	616.3	544.8	484.6
132.5°	945.1	939.4	925.1	898.6	860.8	810.9	748.5	678.6	608.8	544.0	489.8
135°	907.1	901.4	886.4	860.1	822.4	775.3	717.9	656.8	597.5	542.9	497.8
137.5°	860.1	853.3	840.8	814.8	779.7	737.2	688.8	637.1	587.7	542.7	502.5
140°	826.1	818.6	805.5	784.8	751.8	712.3	670.0	625.8	582.5	542.0	506.2
142.5°	790.0	784.8	773.1	753.8	724.7	690.5	654.1	615.2	578.0	542.0	509.3
145°	740.6	735.8	726.4	710.4	686.9	660.5	632.4	600.3	570.2	540.1	511.0
147.5°	696.6	695.0	687.9	674.1	656.8	636.1	613.5	588.1	563.3	536.7	511.9
150°	671.8	670.9	665.2	653.0	638.0	621.0	602.2	580.6	558.0	534.4	511.9
152.5°	649.2	648.3	644.9	635.0	622.2	608.2	590.9	572.3	552.0	530.7	510.4
155°	620.1	620.1	617.3	609.7	600.3	589.0	575.0	559.9	542.9	525.1	508.1
157.5°	594.5	594.5	592.8	587.1	580.0	571.0	559.1	546.5	533.7	519.2	505.7
160°	578.7	578.7	577.8	572.1	566.5	558.9	548.6	538.2	527.0	514.7	503.4
162.5°	563.6	564.4	563.5	557.8	553.6	546.9	538.8	529.9	520.9	510.2	501.1
165°	541.0	542.0	542.9	539.1	535.4	530.7	524.1	518.5	511.0	503.4	496.8
167.5°	523.2	524.0	524.1	521.7	519.8	517.0	511.7	507.4	501.9	496.6	492.3
170°	511.9	511.9	512.8	511.9	510.0	507.2	503.4	500.6	495.9	492.1	489.3
172.5°	500.6	502.1	503.0	502.1	501.0	498.9	496.6	494.6	490.6	487.6	486.3
175°	487.4	489.3	491.2	489.3	489.3	489.3	487.4	486.4	484.6	482.7	482.7
177.5°	479.7	481.2	482.7	481.9	482.7	481.9	481.9	481.2	480.4	479.7	479.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1281.9	1276.3	1273.5	1267.1	1259.4	1255.4	1251.8	1246.6	1239.7	1232.6	1227.3
5°	1346.9	1334.9	1319.8	1301.8	1285.8	1270.3	1256.7	1243.2	1227.7	1211.5	1195.5
7.5°	1413.7	1390.1	1364.5	1334.9	1306.2	1280.0	1255.9	1232.8	1206.7	1183.5	1162.2
10°	1460.2	1428.1	1392.5	1355.0	1317.4	1284.8	1252.7	1223.6	1191.6	1163.0	1138.9
12.5°	1497.9	1460.2	1417.4	1370.6	1325.4	1286.0	1249.1	1211.2	1174.7	1143.7	1111.6
15°	1560.5	1508.8	1451.2	1395.1	1336.4	1282.8	1233.1	1189.0	1147.5	1103.8	1073.3
17.5°	1603.5	1542.2	1472.2	1404.7	1335.4	1272.1	1214.9	1162.3	1114.4	1069.8	1033.4
20°	1629.2	1561.5	1483.8	1407.1	1329.4	1261.7	1200.0	1141.9	1092.3	1044.1	1006.5
22.5°	1643.6	1568.7	1483.8	1403.4	1323.0	1249.7	1182.0	1121.4	1067.4	1019.3	977.7
25°	1648.2	1568.0	1481.3	1389.0	1300.8	1223.1	1152.9	1087.3	1027.1	979.0	934.9
27.5°	1641.8	1547.4	1458.5	1363.9	1272.8	1190.9	1117.3	1048.3	988.1	936.4	891.2
30°	1632.2	1530.9	1435.7	1337.4	1245.2	1166.5	1088.7	1022.6	960.0	906.3	860.7
32.5°	1611.3	1510.9	1408.3	1307.8	1214.3	1133.2	1059.5	993.0	931.5	876.7	828.2
35°	1570.0	1468.3	1357.0	1253.7	1162.0	1077.7	1008.6	944.4	885.8	827.1	776.0
37.5°	1515.6	1411.6	1300.9	1187.8	1096.0	1016.5	953.0	892.8	835.6	782.0	725.4
40°	1464.2	1369.5	1255.2	1142.9	1048.7	971.9	913.3	858.7	801.1	747.9	691.3
42.5°	1402.0	1321.4	1205.9	1093.2	1000.1	926.2	871.7	818.2	765.7	714.3	655.2
45°	1298.4	1237.2	1128.9	1020.6	926.9	853.7	803.5	756.4	710.3	661.2	605.6
47.5°	1179.4	1138.0	1044.5	933.7	847.0	781.1	732.6	694.2	655.2	606.1	557.2
50°	1096.8	1070.3	980.0	878.7	796.1	735.4	685.8	649.7	617.1	570.0	526.3
52.5°	1008.6	994.5	918.2	821.4	741.5	682.0	639.6	607.2	574.2	535.1	494.3
55°	874.2	881.7	817.1	733.4	658.2	608.0	569.5	542.3	514.3	481.3	449.7
57.5°	736.9	764.3	721.0	647.4	576.9	530.7	501.6	478.8	455.2	427.8	400.9
60°	654.7	677.7	653.2	588.5	526.9	483.7	456.7	439.1	415.6	390.5	369.9
62.5°	574.5	599.2	584.6	532.3	475.1	438.0	414.2	397.8	380.3	358.4	337.1
65°	473.7	489.7	482.8	446.7	406.0	374.5	352.4	340.4	324.3	308.3	289.3
67.5°	362.8	393.8	389.7	370.5	335.5	310.8	296.3	285.7	271.1	259.2	246.2
70°	298.2	326.9	326.3	310.8	291.7	268.7	258.6	249.7	236.6	225.1	214.5
72.5°	244.1	270.3	274.2	262.3	249.2	231.8	222.2	215.9	203.3	195.4	186.9
75°	171.0	190.0	195.0	195.0	189.0	179.9	171.4	167.4	158.4	151.4	146.4
77.5°	112.1	124.1	132.0	133.7	134.7	131.7	124.6	121.8	114.9	112.4	107.5
80°	79.2	87.2	96.2	99.2	101.8	100.8	97.7	95.8	89.3	86.7	84.7
82.5°	54.8	59.2	66.5	73.1	72.5	75.1	72.5	70.9	66.0	65.0	63.1
85°	28.6	29.0	30.1	34.6	37.1	38.1	38.6	37.6	36.1	36.1	32.6
87.5°	12.3	11.9	11.5	11.5	11.8	13.2	13.8	13.9	13.0	12.3	11.3
90°	13.2	13.2	7.5	7.5	6.6	5.7	2.8	0.9	2.8	5.7	6.6
92.5°	190.1	117.1	69.3	49.7	35.9	24.5	15.6	10.7	15.6	24.5	35.9
95°	353.8	199.4	117.6	78.1	55.5	43.3	33.8	31.0	33.8	43.3	55.5
97.5°	318.0	190.7	127.6	94.4	75.1	63.8	55.7	55.7	55.7	63.8	75.1
100°	299.3	192.9	137.4	107.3	89.4	78.1	71.5	71.5	71.5	78.1	89.4
102.5°	294.0	200.4	150.1	121.6	104.4	93.9	88.0	86.5	88.0	93.9	104.4
105°	296.4	218.3	173.1	145.8	128.9	117.6	112.9	110.1	112.9	117.6	128.9
107.5°	310.3	239.2	197.7	170.9	154.7	142.6	138.0	136.1	138.0	142.6	154.7
110°	320.8	255.0	213.6	188.2	171.3	159.9	155.2	153.4	155.2	159.9	171.3



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	332.2	270.0	230.2	204.7	187.8	177.3	171.8	169.9	171.8	177.3	187.8
115°	350.1	293.6	255.9	230.5	212.6	203.2	196.6	193.9	196.6	203.2	212.6
117.5°	368.3	316.3	280.6	254.2	237.5	227.2	221.3	218.7	221.3	227.2	237.5
120°	381.1	332.2	296.4	270.0	254.0	243.7	237.1	235.3	237.1	243.7	254.0
122.5°	393.1	347.2	311.4	285.9	268.3	258.7	252.1	250.3	252.1	258.7	268.3
125°	411.2	367.9	334.0	307.6	289.8	279.5	273.8	270.0	273.8	279.5	289.8
127.5°	426.8	387.1	354.4	327.8	309.2	297.4	290.6	287.6	290.6	297.4	309.2
130°	436.6	399.9	367.9	340.6	322.7	308.6	301.1	297.4	301.1	308.6	322.7
132.5°	446.4	410.5	378.4	352.7	333.3	319.9	310.1	307.1	310.1	319.9	333.3
135°	459.2	425.3	394.3	369.8	350.1	334.0	324.6	320.8	324.6	334.0	350.1
137.5°	468.3	436.6	407.6	384.3	363.7	348.6	338.2	334.6	338.2	348.6	363.7
140°	474.2	444.1	415.9	393.3	373.5	357.6	347.2	344.4	347.2	357.6	373.5
142.5°	478.7	450.9	423.4	401.6	382.6	367.3	357.8	355.0	357.8	367.3	382.6
145°	483.6	458.3	433.8	413.1	395.2	382.0	372.6	369.8	372.6	382.0	395.2
147.5°	488.0	465.8	442.8	424.1	409.3	395.8	387.5	386.5	387.5	395.8	409.3
150°	490.2	469.6	448.8	430.9	416.9	405.6	398.0	397.1	398.0	405.6	416.9
152.5°	491.7	472.6	454.1	437.7	425.1	414.6	407.1	406.9	407.1	414.6	425.1
155°	493.0	477.0	461.1	447.0	436.6	427.2	421.5	420.6	421.5	427.2	436.6
157.5°	493.0	480.2	466.7	455.6	446.6	439.2	433.9	433.9	433.9	439.2	446.6
160°	493.0	481.7	470.5	460.1	452.6	446.0	442.2	442.2	442.2	446.0	452.6
162.5°	493.0	483.2	472.8	464.7	457.9	452.0	449.0	449.8	449.0	452.0	457.9
165°	491.2	483.6	475.1	469.6	464.9	460.1	458.3	458.3	458.3	460.1	464.9
167.5°	488.9	483.4	477.2	473.0	470.3	466.7	465.8	466.7	465.8	466.7	470.3
170°	487.4	482.7	478.0	475.1	473.3	470.5	469.6	470.5	469.6	470.5	473.3
172.5°	485.9	481.9	478.7	476.6	475.5	473.4	473.3	474.2	473.3	473.4	475.5
175°	483.6	480.8	478.9	478.9	478.0	477.0	477.0	478.0	477.0	477.0	478.0
177.5°	481.2	479.7	478.9	478.9	478.9	478.2	478.9	479.7	478.9	478.2	478.9
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1221.7	1217.7	1212.5	1206.5	1199.3	1192.9	1190.1	1192.4	1193.6	1190.4	1190.1
5°	1184.5	1172.0	1162.0	1146.9	1134.9	1124.8	1117.9	1114.8	1115.9	1107.9	1105.8
7.5°	1142.7	1127.8	1111.4	1093.6	1076.9	1062.2	1054.5	1050.3	1041.8	1038.1	1032.0
10°	1115.9	1095.8	1079.8	1058.7	1039.6	1022.1	1013.6	1006.5	998.1	994.0	985.5
12.5°	1088.2	1064.9	1047.3	1025.4	1006.0	984.8	976.7	963.7	950.4	941.9	930.9
15°	1049.1	1021.2	999.6	973.5	950.5	926.3	904.8	880.7	871.8	852.7	841.7
17.5°	1003.5	975.1	948.4	913.4	877.9	848.0	825.0	801.9	788.2	776.0	770.3
20°	973.5	947.4	910.3	869.7	830.1	797.0	778.4	763.5	748.4	739.9	733.9
22.5°	945.0	911.7	868.6	824.8	785.2	759.3	743.6	728.1	716.0	707.8	699.7
25°	897.3	853.7	808.0	757.9	730.8	708.3	691.3	678.7	671.2	660.7	656.7
27.5°	848.3	795.4	745.1	711.4	683.2	662.6	647.7	638.3	628.8	622.1	616.9
30°	810.6	757.0	711.8	679.8	651.2	634.1	622.1	611.1	603.5	598.0	594.0
32.5°	773.3	719.6	681.7	647.2	624.7	608.0	595.2	587.0	581.1	574.0	571.6
35°	719.3	671.8	638.7	607.6	584.5	569.5	559.4	550.9	545.9	543.8	542.3
37.5°	667.5	628.5	593.0	567.4	546.9	535.1	523.2	519.1	515.6	512.0	513.6
40°	634.6	598.0	566.5	539.4	522.8	509.8	502.8	497.8	494.7	494.7	494.7
42.5°	606.1	570.3	539.6	515.3	498.8	487.8	479.9	475.7	474.7	474.3	476.7
45°	561.9	528.9	497.8	477.7	463.6	452.6	448.2	444.6	444.6	446.7	447.1
47.5°	518.1	487.1	462.2	439.7	426.9	420.0	416.0	414.2	414.4	416.5	418.8
50°	491.3	460.7	436.1	416.0	404.1	397.5	394.0	393.0	394.0	394.0	397.5
52.5°	461.9	434.6	410.5	393.6	379.9	373.8	371.9	370.5	371.2	372.8	374.3
55°	419.1	394.5	371.5	355.4	345.3	341.4	336.9	337.3	336.4	337.3	337.3
57.5°	376.1	354.0	332.5	319.8	311.0	305.2	300.3	301.7	300.2	300.0	299.2
60°	348.4	324.3	307.3	295.8	285.7	280.7	276.2	277.2	275.7	274.7	272.7
62.5°	318.3	298.2	282.0	270.9	262.9	257.0	252.5	251.6	248.1	244.6	240.3
65°	274.7	258.2	243.6	233.1	225.6	221.0	217.5	214.5	207.0	199.0	195.0
67.5°	232.3	220.4	206.8	197.9	191.8	185.9	179.2	174.1	167.0	162.6	160.1
70°	205.0	193.5	182.0	173.4	166.9	161.5	153.9	150.4	145.3	143.4	140.8
72.5°	179.0	168.2	157.5	149.8	142.9	138.6	132.6	129.1	127.0	126.1	123.7
75°	139.4	130.8	122.8	115.8	110.3	107.3	104.8	102.3	101.2	96.7	94.3
77.5°	101.7	96.0	91.0	86.1	82.1	80.1	75.3	72.4	70.7	68.6	68.1
80°	79.2	75.2	70.2	67.2	61.6	59.7	57.7	57.1	56.6	56.2	55.6
82.5°	59.6	55.5	50.5	48.7	47.2	46.0	44.8	44.3	43.8	44.1	44.0
85°	30.1	28.1	28.1	27.6	27.1	26.6	26.1	26.1	25.5	26.1	25.5
87.5°	11.5	11.1	12.3	11.5	12.3	12.6	12.1	12.3	12.8	12.2	12.2
90°	7.5	7.5	13.2	13.2	15.1	17.0	16.0	17.0	17.9	18.9	18.9
92.5°	49.7	69.3	117.1	190.1	261.2	298.5	248.6	184.8	139.1	110.7	91.8
95°	78.1	117.6	199.4	353.8	578.7	766.9	788.5	697.2	551.4	425.3	334.0
97.5°	94.4	127.6	190.7	318.0	541.6	807.7	990.6	1030.2	975.9	883.9	785.7
100°	107.3	137.4	192.9	299.3	491.2	756.5	997.4	1134.8	1153.6	1107.5	1037.8
102.5°	121.6	150.1	200.4	294.0	457.3	692.6	940.9	1129.5	1222.9	1236.2	1207.2
105°	145.8	173.1	218.3	296.4	428.1	617.3	838.4	1053.9	1216.6	1309.8	1348.4
107.5°	170.9	197.7	239.2	310.3	422.8	575.1	755.5	946.4	1119.7	1250.9	1334.8
110°	188.2	213.6	255.0	320.8	424.3	560.8	714.2	881.7	1044.4	1180.9	1284.4



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.7	230.2	270.0	332.2	428.9	554.0	690.9	834.2	978.2	1107.1	1210.6
115°	230.5	255.9	293.6	350.1	437.5	550.4	669.0	786.6	902.4	1012.5	1102.8
117.5°	254.2	280.6	316.3	368.3	446.8	549.5	659.2	763.3	859.1	945.7	1022.3
120°	270.0	296.4	332.2	381.1	453.6	549.5	653.9	752.7	840.3	915.6	982.3
122.5°	285.9	311.4	347.2	393.1	460.3	548.7	647.9	743.8	828.2	896.7	955.3
125°	307.6	334.0	367.9	411.2	470.5	547.6	638.0	728.3	809.2	874.1	925.9
127.5°	327.8	354.4	387.1	426.8	478.5	545.5	624.6	709.5	786.8	851.6	900.7
130°	340.6	367.9	399.9	436.6	484.6	544.8	616.3	694.5	768.7	832.7	882.6
132.5°	352.7	378.4	410.5	446.4	489.8	544.0	608.8	678.6	748.5	810.9	860.8
135°	369.8	394.3	425.3	459.2	497.8	542.9	597.5	656.8	717.9	775.3	822.4
137.5°	384.3	407.6	436.6	468.3	502.5	542.7	587.7	637.1	688.8	737.2	779.7
140°	393.3	415.9	444.1	474.2	506.2	542.0	582.5	625.8	670.0	712.3	751.8
142.5°	401.6	423.4	450.9	478.7	509.3	542.0	578.0	615.2	654.1	690.5	724.7
145°	413.1	433.8	458.3	483.6	511.0	540.1	570.2	600.3	632.4	660.5	686.9
147.5°	424.1	442.8	465.8	488.0	511.9	536.7	563.3	588.1	613.5	636.1	656.8
150°	430.9	448.8	469.6	490.2	511.9	534.4	558.0	580.6	602.2	621.0	638.0
152.5°	437.7	454.1	472.6	491.7	510.4	530.7	552.0	572.3	590.9	608.2	622.2
155°	447.0	461.1	477.0	493.0	508.1	525.1	542.9	559.9	575.0	589.0	600.3
157.5°	455.6	466.7	480.2	493.0	505.7	519.2	533.7	546.5	559.1	571.0	580.0
160°	460.1	470.5	481.7	493.0	503.4	514.7	527.0	538.2	548.6	558.9	566.5
162.5°	464.7	472.8	483.2	493.0	501.1	510.2	520.9	529.9	538.8	546.9	553.6
165°	469.6	475.1	483.6	491.2	496.8	503.4	511.0	518.5	524.1	530.7	535.4
167.5°	473.0	477.2	483.4	488.9	492.3	496.6	501.9	507.4	511.7	517.0	519.8
170°	475.1	478.0	482.7	487.4	489.3	492.1	495.9	500.6	503.4	507.2	510.0
172.5°	476.6	478.7	481.9	485.9	486.3	487.6	490.6	494.6	496.6	498.9	501.0
175°	478.9	478.9	480.8	483.6	482.7	482.7	484.6	486.4	487.4	489.3	489.3
177.5°	478.9	478.9	479.7	481.2	479.7	479.7	480.4	481.2	481.9	481.9	482.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1187.6	1188.5	1185.6	1184.8	1185.6	1188.5	1187.6	1190.1	1190.4	1193.6	1192.4
5°	1101.8	1100.8	1098.3	1098.8	1098.3	1100.8	1101.8	1105.8	1107.9	1115.9	1114.8
7.5°	1028.4	1024.5	1025.6	1021.6	1025.6	1024.5	1028.4	1032.0	1038.1	1041.8	1050.3
10°	983.5	978.0	973.5	969.5	973.5	978.0	983.5	985.5	994.0	998.1	1006.5
12.5°	922.2	917.5	911.3	912.6	911.3	917.5	922.2	930.9	941.9	950.4	963.7
15°	835.1	827.6	815.6	817.1	815.6	827.6	835.1	841.7	852.7	871.8	880.7
17.5°	761.5	761.6	756.0	757.3	756.0	761.6	761.5	770.3	776.0	788.2	801.9
20°	723.3	719.8	720.3	718.9	720.3	719.8	723.3	733.9	739.9	748.4	763.5
22.5°	696.9	692.6	689.1	686.0	689.1	692.6	696.9	699.7	707.8	716.0	728.1
25°	652.1	649.1	644.6	643.7	644.6	649.1	652.1	656.7	660.7	671.2	678.7
27.5°	612.8	612.3	610.5	608.1	610.5	612.3	612.8	616.9	622.1	628.8	638.3
30°	590.0	589.0	588.0	586.4	588.0	589.0	590.0	594.0	598.0	603.5	611.1
32.5°	569.6	568.9	568.0	568.1	568.0	568.9	569.6	571.6	574.0	581.1	587.0
35°	540.4	539.9	538.9	538.4	538.9	539.9	540.4	542.3	543.8	545.9	550.9
37.5°	513.1	514.4	513.8	513.7	513.8	514.4	513.1	513.6	512.0	515.6	519.1
40°	494.3	494.7	495.8	495.3	495.8	494.7	494.3	494.7	494.7	494.7	497.8
42.5°	478.6	478.7	480.1	478.4	480.1	478.7	478.6	476.7	474.3	474.7	475.7
45°	450.6	453.6	453.2	453.2	453.2	453.6	450.6	447.1	446.7	444.6	444.6
47.5°	420.1	422.6	423.4	423.3	423.4	422.6	420.1	418.8	416.5	414.4	414.2
50°	400.0	399.0	400.5	400.0	400.5	399.0	400.0	397.5	394.0	394.0	393.0
52.5°	375.6	375.8	375.7	375.1	375.7	375.8	375.6	374.3	372.8	371.2	370.5
55°	337.9	338.4	337.3	337.9	337.3	338.4	337.9	337.3	337.3	336.4	337.3
57.5°	297.0	294.5	295.6	294.4	295.6	294.5	297.0	299.2	300.0	300.2	301.7
60°	267.7	263.6	262.7	260.7	262.7	263.6	267.7	272.7	274.7	275.7	277.2
62.5°	234.8	232.0	228.6	230.2	228.6	232.0	234.8	240.3	244.6	248.1	251.6
65°	191.0	189.0	187.5	189.5	187.5	189.0	191.0	195.0	199.0	207.0	214.5
67.5°	158.1	157.0	157.0	156.0	157.0	157.0	158.1	160.1	162.6	167.0	174.1
70°	140.8	139.4	139.4	138.4	139.4	139.4	140.8	140.8	143.4	145.3	150.4
72.5°	123.2	121.7	122.2	121.5	122.2	121.7	123.2	123.7	126.1	127.0	129.1
75°	91.2	88.7	88.7	89.3	88.7	88.7	91.2	94.3	96.7	101.2	102.3
77.5°	68.1	67.6	68.2	67.4	68.2	67.6	68.1	68.1	68.6	70.7	72.4
80°	55.6	55.1	54.7	56.2	54.7	55.1	55.6	55.6	56.2	56.6	57.1
82.5°	43.2	43.1	43.0	45.0	43.0	43.1	43.2	44.0	44.1	43.8	44.3
85°	26.1	25.1	26.1	25.1	26.1	25.1	26.1	25.5	26.1	25.5	26.1
87.5°	13.2	13.0	12.3	12.8	12.3	13.0	13.2	12.2	12.2	12.8	12.3
90°	19.8	20.7	19.8	19.8	19.8	20.7	19.8	18.9	18.9	17.9	17.0
92.5°	80.8	75.7	72.5	72.5	72.5	75.7	80.8	91.8	110.7	139.1	184.8
95°	287.9	258.7	241.9	229.6	241.9	258.7	287.9	334.0	425.3	551.4	697.2
97.5°	718.1	661.5	633.3	613.7	633.3	661.5	718.1	785.7	883.9	975.9	1030.2
100°	956.0	898.6	870.3	862.9	870.3	898.6	956.0	1037.8	1107.5	1153.6	1134.8
102.5°	1157.0	1115.4	1085.7	1079.7	1085.7	1115.4	1157.0	1207.2	1236.2	1222.9	1129.5
105°	1350.3	1342.7	1329.6	1323.9	1329.6	1342.7	1350.3	1348.4	1309.8	1216.6	1053.9
107.5°	1381.3	1402.8	1412.2	1414.7	1412.2	1402.8	1381.3	1334.8	1250.9	1119.7	946.4
110°	1351.2	1390.7	1407.7	1416.2	1407.7	1390.7	1351.2	1284.4	1180.9	1044.4	881.7



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1286.5	1334.3	1358.0	1371.7	1358.0	1334.3	1286.5	1210.6	1107.1	978.2	834.2
115°	1177.1	1233.6	1263.7	1271.2	1263.7	1233.6	1177.1	1102.8	1012.5	902.4	786.6
117.5°	1085.7	1133.1	1163.6	1169.4	1163.6	1133.1	1085.7	1022.3	945.7	859.1	763.3
120°	1035.9	1077.4	1101.8	1112.2	1101.8	1077.4	1035.9	982.3	915.6	840.3	752.7
122.5°	1000.6	1035.9	1056.7	1067.1	1056.7	1035.9	1000.6	955.3	896.7	828.2	743.8
125°	963.6	990.8	1008.7	1014.4	1008.7	990.8	963.6	925.9	874.1	809.2	728.3
127.5°	938.5	962.8	977.8	983.4	977.8	962.8	938.5	900.7	851.6	786.8	709.5
130°	921.1	944.7	959.8	965.4	959.8	944.7	921.1	882.6	832.7	768.7	694.5
132.5°	898.6	925.1	939.4	945.1	939.4	925.1	898.6	860.8	810.9	748.5	678.6
135°	860.1	886.4	901.4	907.1	901.4	886.4	860.1	822.4	775.3	717.9	656.8
137.5°	814.8	840.8	853.3	860.1	853.3	840.8	814.8	779.7	737.2	688.8	637.1
140°	784.8	805.5	818.6	826.1	818.6	805.5	784.8	751.8	712.3	670.0	625.8
142.5°	753.8	773.1	784.8	790.0	784.8	773.1	753.8	724.7	690.5	654.1	615.2
145°	710.4	726.4	735.8	740.6	735.8	726.4	710.4	686.9	660.5	632.4	600.3
147.5°	674.1	687.9	695.0	696.6	695.0	687.9	674.1	656.8	636.1	613.5	588.1
150°	653.0	665.2	670.9	671.8	670.9	665.2	653.0	638.0	621.0	602.2	580.6
152.5°	635.0	644.9	648.3	649.2	648.3	644.9	635.0	622.2	608.2	590.9	572.3
155°	609.7	617.3	620.1	620.1	620.1	617.3	609.7	600.3	589.0	575.0	559.9
157.5°	587.1	592.8	594.5	594.5	594.5	592.8	587.1	580.0	571.0	559.1	546.5
160°	572.1	577.8	578.7	578.7	578.7	577.8	572.1	566.5	558.9	548.6	538.2
162.5°	557.8	563.5	564.4	563.6	564.4	563.5	557.8	553.6	546.9	538.8	529.9
165°	539.1	542.9	542.0	541.0	542.0	542.9	539.1	535.4	530.7	524.1	518.5
167.5°	521.7	524.1	524.0	523.2	524.0	524.1	521.7	519.8	517.0	511.7	507.4
170°	511.9	512.8	511.9	511.9	511.9	512.8	511.9	510.0	507.2	503.4	500.6
172.5°	502.1	503.0	502.1	500.6	502.1	503.0	502.1	501.0	498.9	496.6	494.6
175°	489.3	491.2	489.3	487.4	489.3	491.2	489.3	489.3	489.3	487.4	486.4
177.5°	481.9	482.7	481.2	479.7	481.2	482.7	481.9	482.7	481.9	481.9	481.2
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1190.1	1192.9	1199.3	1206.5	1212.5	1217.7	1221.7	1227.3	1232.6	1239.7	1246.6
5°	1117.9	1124.8	1134.9	1146.9	1162.0	1172.0	1184.5	1195.5	1211.5	1227.7	1243.2
7.5°	1054.5	1062.2	1076.9	1093.6	1111.4	1127.8	1142.7	1162.2	1183.5	1206.7	1232.8
10°	1013.6	1022.1	1039.6	1058.7	1079.8	1095.8	1115.9	1138.9	1163.0	1191.6	1223.6
12.5°	976.7	984.8	1006.0	1025.4	1047.3	1064.9	1088.2	1111.6	1143.7	1174.7	1211.2
15°	904.8	926.3	950.5	973.5	999.6	1021.2	1049.1	1073.3	1103.8	1147.5	1189.0
17.5°	825.0	848.0	877.9	913.4	948.4	975.1	1003.5	1033.4	1069.8	1114.4	1162.3
20°	778.4	797.0	830.1	869.7	910.3	947.4	973.5	1006.5	1044.1	1092.3	1141.9
22.5°	743.6	759.3	785.2	824.8	868.6	911.7	945.0	977.7	1019.3	1067.4	1121.4
25°	691.3	708.3	730.8	757.9	808.0	853.7	897.3	934.9	979.0	1027.1	1087.3
27.5°	647.7	662.6	683.2	711.4	745.1	795.4	848.3	891.2	936.4	988.1	1048.3
30°	622.1	634.1	651.2	679.8	711.8	757.0	810.6	860.7	906.3	960.0	1022.6
32.5°	595.2	608.0	624.7	647.2	681.7	719.6	773.3	828.2	876.7	931.5	993.0
35°	559.4	569.5	584.5	607.6	638.7	671.8	719.3	776.0	827.1	885.8	944.4
37.5°	523.2	535.1	546.9	567.4	593.0	628.5	667.5	725.4	782.0	835.6	892.8
40°	502.8	509.8	522.8	539.4	566.5	598.0	634.6	691.3	747.9	801.1	858.7
42.5°	479.9	487.8	498.8	515.3	539.6	570.3	606.1	655.2	714.3	765.7	818.2
45°	448.2	452.6	463.6	477.7	497.8	528.9	561.9	605.6	661.2	710.3	756.4
47.5°	416.0	420.0	426.9	439.7	462.2	487.1	518.1	557.2	606.1	655.2	694.2
50°	394.0	397.5	404.1	416.0	436.1	460.7	491.3	526.3	570.0	617.1	649.7
52.5°	371.9	373.8	379.9	393.6	410.5	434.6	461.9	494.3	535.1	574.2	607.2
55°	336.9	341.4	345.3	355.4	371.5	394.5	419.1	449.7	481.3	514.3	542.3
57.5°	300.3	305.2	311.0	319.8	332.5	354.0	376.1	400.9	427.8	455.2	478.8
60°	276.2	280.7	285.7	295.8	307.3	324.3	348.4	369.9	390.5	415.6	439.1
62.5°	252.5	257.0	262.9	270.9	282.0	298.2	318.3	337.1	358.4	380.3	397.8
65°	217.5	221.0	225.6	233.1	243.6	258.2	274.7	289.3	308.3	324.3	340.4
67.5°	179.2	185.9	191.8	197.9	206.8	220.4	232.3	246.2	259.2	271.1	285.7
70°	153.9	161.5	166.9	173.4	182.0	193.5	205.0	214.5	225.1	236.6	249.7
72.5°	132.6	138.6	142.9	149.8	157.5	168.2	179.0	186.9	195.4	203.3	215.9
75°	104.8	107.3	110.3	115.8	122.8	130.8	139.4	146.4	151.4	158.4	167.4
77.5°	75.3	80.1	82.1	86.1	91.0	96.0	101.7	107.5	112.4	114.9	121.8
80°	57.7	59.7	61.6	67.2	70.2	75.2	79.2	84.7	86.7	89.3	95.8
82.5°	44.8	46.0	47.2	48.7	50.5	55.5	59.6	63.1	65.0	66.0	70.9
85°	26.1	26.6	27.1	27.6	28.1	28.1	30.1	32.6	36.1	36.1	37.6
87.5°	12.1	12.6	12.3	11.5	12.3	11.1	11.5	11.3	12.3	13.0	13.9
90°	16.0	17.0	15.1	13.2	13.2	7.5	7.5	6.6	5.7	2.8	0.9
92.5°	248.6	298.5	261.2	190.1	117.1	69.3	49.7	35.9	24.5	15.6	10.7
95°	788.5	766.9	578.7	353.8	199.4	117.6	78.1	55.5	43.3	33.8	31.0
97.5°	990.6	807.7	541.6	318.0	190.7	127.6	94.4	75.1	63.8	55.7	55.7
100°	997.4	756.5	491.2	299.3	192.9	137.4	107.3	89.4	78.1	71.5	71.5
102.5°	940.9	692.6	457.3	294.0	200.4	150.1	121.6	104.4	93.9	88.0	86.5
105°	838.4	617.3	428.1	296.4	218.3	173.1	145.8	128.9	117.6	112.9	110.1
107.5°	755.5	575.1	422.8	310.3	239.2	197.7	170.9	154.7	142.6	138.0	136.1
110°	714.2	560.8	424.3	320.8	255.0	213.6	188.2	171.3	159.9	155.2	153.4



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	690.9	554.0	428.9	332.2	270.0	230.2	204.7	187.8	177.3	171.8	169.9
115°	669.0	550.4	437.5	350.1	293.6	255.9	230.5	212.6	203.2	196.6	193.9
117.5°	659.2	549.5	446.8	368.3	316.3	280.6	254.2	237.5	227.2	221.3	218.7
120°	653.9	549.5	453.6	381.1	332.2	296.4	270.0	254.0	243.7	237.1	235.3
122.5°	647.9	548.7	460.3	393.1	347.2	311.4	285.9	268.3	258.7	252.1	250.3
125°	638.0	547.6	470.5	411.2	367.9	334.0	307.6	289.8	279.5	273.8	270.0
127.5°	624.6	545.5	478.5	426.8	387.1	354.4	327.8	309.2	297.4	290.6	287.6
130°	616.3	544.8	484.6	436.6	399.9	367.9	340.6	322.7	308.6	301.1	297.4
132.5°	608.8	544.0	489.8	446.4	410.5	378.4	352.7	333.3	319.9	310.1	307.1
135°	597.5	542.9	497.8	459.2	425.3	394.3	369.8	350.1	334.0	324.6	320.8
137.5°	587.7	542.7	502.5	468.3	436.6	407.6	384.3	363.7	348.6	338.2	334.6
140°	582.5	542.0	506.2	474.2	444.1	415.9	393.3	373.5	357.6	347.2	344.4
142.5°	578.0	542.0	509.3	478.7	450.9	423.4	401.6	382.6	367.3	357.8	355.0
145°	570.2	540.1	511.0	483.6	458.3	433.8	413.1	395.2	382.0	372.6	369.8
147.5°	563.3	536.7	511.9	488.0	465.8	442.8	424.1	409.3	395.8	387.5	386.5
150°	558.0	534.4	511.9	490.2	469.6	448.8	430.9	416.9	405.6	398.0	397.1
152.5°	552.0	530.7	510.4	491.7	472.6	454.1	437.7	425.1	414.6	407.1	406.9
155°	542.9	525.1	508.1	493.0	477.0	461.1	447.0	436.6	427.2	421.5	420.6
157.5°	533.7	519.2	505.7	493.0	480.2	466.7	455.6	446.6	439.2	433.9	433.9
160°	527.0	514.7	503.4	493.0	481.7	470.5	460.1	452.6	446.0	442.2	442.2
162.5°	520.9	510.2	501.1	493.0	483.2	472.8	464.7	457.9	452.0	449.0	449.8
165°	511.0	503.4	496.8	491.2	483.6	475.1	469.6	464.9	460.1	458.3	458.3
167.5°	501.9	496.6	492.3	488.9	483.4	477.2	473.0	470.3	466.7	465.8	466.7
170°	495.9	492.1	489.3	487.4	482.7	478.0	475.1	473.3	470.5	469.6	470.5
172.5°	490.6	487.6	486.3	485.9	481.9	478.7	476.6	475.5	473.4	473.3	474.2
175°	484.6	482.7	482.7	483.6	480.8	478.9	478.9	478.0	477.0	477.0	478.0
177.5°	480.4	479.7	479.7	481.2	479.7	478.9	478.9	478.9	478.2	478.9	479.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1251.8	1255.4	1259.4	1267.1	1273.5	1276.3	1281.9	1285.9	1284.7	1290.2	1300.0
5°	1256.7	1270.3	1285.8	1301.8	1319.8	1334.9	1346.9	1359.0	1368.5	1380.0	1397.0
7.5°	1255.9	1280.0	1306.2	1334.9	1364.5	1390.1	1413.7	1437.8	1459.2	1482.5	1513.1
10°	1252.7	1284.8	1317.4	1355.0	1392.5	1428.1	1460.2	1490.3	1518.9	1549.4	1588.1
12.5°	1249.1	1286.0	1325.4	1370.6	1417.4	1460.2	1497.9	1541.2	1577.1	1616.5	1661.0
15°	1233.1	1282.8	1336.4	1395.1	1451.2	1508.8	1560.5	1613.6	1663.2	1710.3	1766.5
17.5°	1214.9	1272.1	1335.4	1404.7	1472.2	1542.2	1603.5	1670.5	1721.2	1784.4	1836.5
20°	1200.0	1261.7	1329.4	1407.1	1483.8	1561.5	1629.2	1697.3	1754.4	1818.2	1884.3
22.5°	1182.0	1249.7	1323.0	1403.4	1483.8	1568.7	1643.6	1711.4	1782.2	1853.8	1922.0
25°	1152.9	1223.1	1300.8	1389.0	1481.3	1568.0	1648.2	1732.4	1808.6	1886.3	1947.5
27.5°	1117.3	1190.9	1272.8	1363.9	1458.5	1547.4	1641.8	1731.5	1808.2	1883.0	1936.4
30°	1088.7	1166.5	1245.2	1337.4	1435.7	1530.9	1632.2	1721.9	1802.6	1869.8	1899.9
32.5°	1059.5	1133.2	1214.3	1307.8	1408.3	1510.9	1611.3	1703.1	1777.7	1818.1	1818.8
35°	1008.6	1077.7	1162.0	1253.7	1357.0	1468.3	1570.0	1660.2	1705.8	1709.4	1660.2
37.5°	953.0	1016.5	1096.0	1187.8	1300.9	1411.6	1515.6	1575.7	1590.9	1539.9	1449.1
40°	913.3	971.9	1048.7	1142.9	1255.2	1369.5	1464.2	1508.4	1492.3	1409.6	1308.3
42.5°	871.7	926.2	1000.1	1093.2	1205.9	1321.4	1402.0	1425.8	1383.3	1287.7	1169.2
45°	803.5	853.7	926.9	1020.6	1128.9	1237.2	1298.4	1286.3	1215.6	1102.3	969.5
47.5°	732.6	781.1	847.0	933.7	1044.5	1138.0	1179.4	1143.1	1042.5	917.9	809.8
50°	685.8	735.4	796.1	878.7	980.0	1070.3	1096.8	1041.7	929.9	810.0	710.8
52.5°	639.6	682.0	741.5	821.4	918.2	994.5	1008.6	945.0	829.6	722.3	634.2
55°	569.5	608.0	658.2	733.4	817.1	881.7	874.2	792.5	687.8	596.1	526.9
57.5°	501.6	530.7	576.9	647.4	721.0	764.3	736.9	667.2	569.6	494.5	436.1
60°	456.7	483.7	526.9	588.5	653.2	677.7	654.7	579.0	501.8	433.1	384.0
62.5°	414.2	438.0	475.1	532.3	584.6	599.2	574.5	508.4	438.8	380.1	339.5
65°	352.4	374.5	406.0	446.7	482.8	489.7	473.7	406.0	353.4	304.3	276.2
67.5°	296.3	310.8	335.5	370.5	389.7	393.8	362.8	320.3	273.9	243.7	222.5
70°	258.6	268.7	291.7	310.8	326.3	326.9	298.2	264.2	228.6	204.1	188.5
72.5°	222.2	231.8	249.2	262.3	274.2	270.3	244.1	217.3	188.5	169.9	158.4
75°	171.4	179.9	189.0	195.0	195.0	190.0	171.0	150.9	134.3	123.3	119.8
77.5°	124.6	131.7	134.7	133.7	132.0	124.1	112.1	99.0	93.0	87.8	85.2
80°	97.7	100.8	101.8	99.2	96.2	87.2	79.2	73.7	68.1	66.2	65.1
82.5°	72.5	75.1	72.5	73.1	66.5	59.2	54.8	52.9	50.5	49.8	48.7
85°	38.6	38.1	37.1	34.6	30.1	29.0	28.6	28.1	27.1	27.6	26.6
87.5°	13.8	13.2	11.8	11.5	11.5	11.9	12.3	12.6	13.0	12.4	13.4
90°	2.8	5.7	6.6	7.5	7.5	13.2	13.2	15.1	17.0	16.0	17.0
92.5°	15.6	24.5	35.9	49.7	69.3	117.1	190.1	261.2	298.5	248.6	184.8
95°	33.8	43.3	55.5	78.1	117.6	199.4	353.8	578.7	766.9	788.5	697.2
97.5°	55.7	63.8	75.1	94.4	127.6	190.7	318.0	541.6	807.7	990.6	1030.2
100°	71.5	78.1	89.4	107.3	137.4	192.9	299.3	491.2	756.5	997.4	1134.8
102.5°	88.0	93.9	104.4	121.6	150.1	200.4	294.0	457.3	692.6	940.9	1129.5
105°	112.9	117.6	128.9	145.8	173.1	218.3	296.4	428.1	617.3	838.4	1053.9
107.5°	138.0	142.6	154.7	170.9	197.7	239.2	310.3	422.8	575.1	755.5	946.4
110°	155.2	159.9	171.3	188.2	213.6	255.0	320.8	424.3	560.8	714.2	881.7



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	171.8	177.3	187.8	204.7	230.2	270.0	332.2	428.9	554.0	690.9	834.2
115°	196.6	203.2	212.6	230.5	255.9	293.6	350.1	437.5	550.4	669.0	786.6
117.5°	221.3	227.2	237.5	254.2	280.6	316.3	368.3	446.8	549.5	659.2	763.3
120°	237.1	243.7	254.0	270.0	296.4	332.2	381.1	453.6	549.5	653.9	752.7
122.5°	252.1	258.7	268.3	285.9	311.4	347.2	393.1	460.3	548.7	647.9	743.8
125°	273.8	279.5	289.8	307.6	334.0	367.9	411.2	470.5	547.6	638.0	728.3
127.5°	290.6	297.4	309.2	327.8	354.4	387.1	426.8	478.5	545.5	624.6	709.5
130°	301.1	308.6	322.7	340.6	367.9	399.9	436.6	484.6	544.8	616.3	694.5
132.5°	310.1	319.9	333.3	352.7	378.4	410.5	446.4	489.8	544.0	608.8	678.6
135°	324.6	334.0	350.1	369.8	394.3	425.3	459.2	497.8	542.9	597.5	656.8
137.5°	338.2	348.6	363.7	384.3	407.6	436.6	468.3	502.5	542.7	587.7	637.1
140°	347.2	357.6	373.5	393.3	415.9	444.1	474.2	506.2	542.0	582.5	625.8
142.5°	357.8	367.3	382.6	401.6	423.4	450.9	478.7	509.3	542.0	578.0	615.2
145°	372.6	382.0	395.2	413.1	433.8	458.3	483.6	511.0	540.1	570.2	600.3
147.5°	387.5	395.8	409.3	424.1	442.8	465.8	488.0	511.9	536.7	563.3	588.1
150°	398.0	405.6	416.9	430.9	448.8	469.6	490.2	511.9	534.4	558.0	580.6
152.5°	407.1	414.6	425.1	437.7	454.1	472.6	491.7	510.4	530.7	552.0	572.3
155°	421.5	427.2	436.6	447.0	461.1	477.0	493.0	508.1	525.1	542.9	559.9
157.5°	433.9	439.2	446.6	455.6	466.7	480.2	493.0	505.7	519.2	533.7	546.5
160°	442.2	446.0	452.6	460.1	470.5	481.7	493.0	503.4	514.7	527.0	538.2
162.5°	449.0	452.0	457.9	464.7	472.8	483.2	493.0	501.1	510.2	520.9	529.9
165°	458.3	460.1	464.9	469.6	475.1	483.6	491.2	496.8	503.4	511.0	518.5
167.5°	465.8	466.7	470.3	473.0	477.2	483.4	488.9	492.3	496.6	501.9	507.4
170°	469.6	470.5	473.3	475.1	478.0	482.7	487.4	489.3	492.1	495.9	500.6
172.5°	473.3	473.4	475.5	476.6	478.7	481.9	485.9	486.3	487.6	490.6	494.6
175°	477.0	477.0	478.0	478.9	478.9	480.8	483.6	482.7	482.7	484.6	486.4
177.5°	478.9	478.2	478.9	478.9	478.9	479.7	481.2	479.7	479.7	480.4	481.2
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1305.1	1306.7	1308.0	1311.9	1312.3	1316.0	1312.3
5°	1413.1	1420.1	1431.2	1442.2	1443.2	1450.2	1437.7
7.5°	1534.2	1550.5	1560.6	1578.4	1585.5	1589.9	1582.6
10°	1617.6	1632.7	1659.3	1672.3	1685.3	1687.3	1681.3
12.5°	1698.3	1722.1	1743.0	1767.7	1767.1	1784.8	1778.3
15°	1805.6	1830.1	1859.3	1886.8	1896.9	1896.9	1904.9
17.5°	1882.2	1927.2	1957.3	1979.0	2002.6	2006.7	2003.9
20°	1933.9	1982.5	2014.7	2042.7	2058.8	2063.2	2063.2
22.5°	1972.5	2013.8	2045.1	2070.4	2083.6	2089.0	2087.4
25°	1999.1	2034.7	2053.7	2061.2	2064.7	2063.8	2054.3
27.5°	1962.6	1961.0	1949.0	1925.9	1908.6	1898.0	1886.0
30°	1892.8	1866.8	1836.7	1803.6	1761.0	1728.4	1718.3
32.5°	1788.9	1730.4	1679.5	1624.4	1578.6	1546.0	1532.3
35°	1588.1	1495.3	1419.7	1353.5	1305.3	1275.3	1265.3
37.5°	1349.6	1259.9	1166.2	1102.0	1062.2	1031.7	1020.4
40°	1198.1	1100.3	1018.6	958.5	917.4	887.8	887.3
42.5°	1059.7	966.4	889.5	846.1	801.8	782.3	782.2
45°	867.7	793.1	727.8	693.8	667.2	651.2	646.7
47.5°	718.4	656.7	613.2	586.1	564.4	554.2	547.6
50°	634.6	580.5	545.9	522.4	510.3	497.3	496.2
52.5°	564.9	521.1	494.2	475.0	459.8	451.9	452.1
55°	474.7	440.2	421.0	406.5	394.5	388.5	386.0
57.5°	399.9	374.0	360.1	346.8	341.7	337.0	335.6
60°	353.4	335.8	322.8	312.3	304.8	303.3	302.7
62.5°	314.9	296.5	287.6	279.4	273.9	271.5	270.7
65°	259.7	246.1	238.1	231.6	229.6	226.1	225.6
67.5°	209.3	201.2	195.9	191.4	188.7	188.5	188.5
70°	178.4	173.9	169.5	166.9	165.4	164.4	164.4
72.5°	152.0	148.6	145.0	143.6	143.4	142.3	141.9
75°	115.8	112.3	112.8	110.3	108.3	105.8	104.2
77.5°	82.1	79.6	79.1	78.8	77.1	76.8	77.6
80°	63.6	61.2	60.7	61.2	60.7	59.2	59.2
82.5°	48.4	46.3	45.8	45.5	45.1	45.5	44.7
85°	26.1	25.1	25.1	25.1	26.1	25.5	25.1
87.5°	12.8	12.6	13.0	12.8	13.0	12.3	12.8
90°	17.9	18.9	18.9	19.8	20.7	19.8	19.8
92.5°	139.1	110.7	91.8	80.8	75.7	72.5	72.5
95°	551.4	425.3	334.0	287.9	258.7	241.9	229.6
97.5°	975.9	883.9	785.7	718.1	661.5	633.3	613.7
100°	1153.6	1107.5	1037.8	956.0	898.6	870.3	862.9
102.5°	1222.9	1236.2	1207.2	1157.0	1115.4	1085.7	1079.7
105°	1216.6	1309.8	1348.4	1350.3	1342.7	1329.6	1323.9
107.5°	1119.7	1250.9	1334.8	1381.3	1402.8	1412.2	1414.7
110°	1044.4	1180.9	1284.4	1351.2	1390.7	1407.7	1416.2



TEST NUMBER: P332945-830

CATALOG NUMBER: SA4XXRDIP-C795D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	978.2	1107.1	1210.6	1286.5	1334.3	1358.0	1371.7
115°	902.4	1012.5	1102.8	1177.1	1233.6	1263.7	1271.2
117.5°	859.1	945.7	1022.3	1085.7	1133.1	1163.6	1169.4
120°	840.3	915.6	982.3	1035.9	1077.4	1101.8	1112.2
122.5°	828.2	896.7	955.3	1000.6	1035.9	1056.7	1067.1
125°	809.2	874.1	925.9	963.6	990.8	1008.7	1014.4
127.5°	786.8	851.6	900.7	938.5	962.8	977.8	983.4
130°	768.7	832.7	882.6	921.1	944.7	959.8	965.4
132.5°	748.5	810.9	860.8	898.6	925.1	939.4	945.1
135°	717.9	775.3	822.4	860.1	886.4	901.4	907.1
137.5°	688.8	737.2	779.7	814.8	840.8	853.3	860.1
140°	670.0	712.3	751.8	784.8	805.5	818.6	826.1
142.5°	654.1	690.5	724.7	753.8	773.1	784.8	790.0
145°	632.4	660.5	686.9	710.4	726.4	735.8	740.6
147.5°	613.5	636.1	656.8	674.1	687.9	695.0	696.6
150°	602.2	621.0	638.0	653.0	665.2	670.9	671.8
152.5°	590.9	608.2	622.2	635.0	644.9	648.3	649.2
155°	575.0	589.0	600.3	609.7	617.3	620.1	620.1
157.5°	559.1	571.0	580.0	587.1	592.8	594.5	594.5
160°	548.6	558.9	566.5	572.1	577.8	578.7	578.7
162.5°	538.8	546.9	553.6	557.8	563.5	564.4	563.6
165°	524.1	530.7	535.4	539.1	542.9	542.0	541.0
167.5°	511.7	517.0	519.8	521.7	524.1	524.0	523.2
170°	503.4	507.2	510.0	511.9	512.8	511.9	511.9
172.5°	496.6	498.9	501.0	502.1	503.0	502.1	500.6
175°	487.4	489.3	489.3	489.3	491.2	489.3	487.4
177.5°	481.9	481.9	482.7	481.9	482.7	481.2	479.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9

(END OF REPORT)