

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331455-940

Luminaire Tested: **SA2XXDIP-C1005D925U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331455-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D925U940-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6840.3 lumens  
Efficiency: N/A  
Efficacy: 102.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331455-940  
CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331455-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	37
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	22946	22946	22946
5°	23034	22702	22835
10°	22897	22471	22584
15°	22614	22181	22158
20°	22213	21742	21720
25°	21814	21205	21205
30°	21300	20713	20534
35°	20820	20120	19825
40°	20219	19530	19153
45°	19628	18941	18472
50°	18982	18331	17678
55°	18311	17619	16963
60°	17563	16769	16152
65°	16756	15924	15194
70°	15739	14903	14195
75°	14323	13724	13381
80°	12710	12329	11688
85°	10374	9874	8855



TEST NUMBER: P331455-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	133.6	2.0
10°-20°	376.0	5.5
20°-30°	552.7	8.1
30°-40°	642.0	9.4
40°-50°	641.3	9.4
50°-60°	559.3	8.2
60°-70°	413.6	6.0
70°-80°	234.2	3.4
80°-90°	67.2	1.0
90°-100°	185.0	2.7
100°-110°	627.9	9.2
110°-120°	667.1	9.8
120°-130°	549.1	8.0
130°-140°	441.0	6.4
140°-150°	333.2	4.9
150°-160°	234.2	3.4
160°-170°	137.9	2.0
170°-180°	44.9	0.7
0°-30°	1062.4	15.5
0°-40°	1704.4	24.9
0°-60°	2905.1	42.5
0°-90°	3620.0	52.9
90°-120°	1480.0	21.6
90°-150°	2803.4	41.0
90°-180°	3220.0	47.1
0°-180°	6840.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1421	1421	1421	1421	1421	
5°	1421	1415	1401	1411	1409	135
15°	1353	1344	1327	1332	1326	381
25°	1224	1213	1190	1193	1190	563
35°	1056	1042	1021	1013	1006	659
45°	860	849	830	815	809	663
55°	650	642	626	610	603	581
65°	439	430	417	405	398	434
75°	230	227	220	212	214	245
85°	56	55	53	49	48	64
90°	1	12	30	29	29	4
95°	31	77	349	132	102	33
105°	109	164	659	1179	1003	115
115°	191	242	552	1139	1320	190
125°	267	316	530	922	1071	237
135°	313	374	524	775	887	242
145°	358	411	522	647	708	224
155°	407	439	506	573	595	187
165°	443	457	485	514	522	125
175°	462	462	466	472	471	44
180°	463	463	463	463	463	



TEST NUMBER: P331455-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1427.8	1426.6	1425.4	1424.2	1422.9	1421.0	1418.4	1415.7	1413.0	1410.3	1412.7
5°	1421.2	1420.0	1418.8	1417.6	1416.4	1414.1	1410.8	1407.4	1404.1	1400.7	1403.2
7.5°	1408.6	1406.8	1404.9	1403.0	1401.1	1398.5	1395.1	1391.7	1388.3	1384.9	1387.3
10°	1396.6	1394.5	1392.4	1390.3	1388.1	1385.3	1381.6	1378.0	1374.3	1370.6	1373.1
12.5°	1380.3	1378.3	1376.4	1374.6	1372.7	1369.9	1366.3	1362.6	1359.1	1355.4	1357.1
15°	1352.9	1351.1	1349.2	1347.5	1345.6	1342.7	1338.8	1334.8	1330.9	1327.0	1328.2
17.5°	1317.9	1316.1	1314.3	1312.4	1310.6	1307.7	1303.7	1299.7	1295.7	1291.7	1293.1
20°	1292.8	1290.9	1289.1	1287.3	1285.5	1282.5	1278.2	1274.0	1269.7	1265.4	1266.3
22.5°	1267.7	1265.1	1262.6	1260.0	1257.4	1254.2	1250.2	1246.2	1242.2	1238.1	1238.3
25°	1224.5	1222.0	1219.6	1217.2	1214.8	1210.9	1205.8	1200.6	1195.4	1190.3	1190.9
27.5°	1175.3	1173.0	1170.9	1168.7	1166.5	1163.4	1159.3	1155.2	1151.2	1147.1	1146.2
30°	1142.5	1140.1	1137.6	1135.1	1132.7	1129.3	1124.7	1120.2	1115.6	1111.0	1110.1
32.5°	1107.5	1105.5	1103.6	1101.6	1099.7	1096.4	1091.5	1086.7	1081.9	1077.1	1075.5
35°	1056.3	1053.3	1050.3	1047.2	1044.2	1040.3	1035.4	1030.6	1025.7	1020.8	1019.0
37.5°	998.7	996.0	993.4	990.7	988.0	984.3	979.4	974.6	969.6	964.8	962.5
40°	959.3	956.9	954.5	952.1	949.6	946.0	941.1	936.3	931.4	926.6	923.8
42.5°	921.0	918.6	916.2	913.8	911.3	907.7	902.9	898.0	893.1	888.2	885.3
45°	859.6	857.5	855.3	853.2	851.0	847.7	843.2	838.7	834.1	829.5	826.2
47.5°	798.3	796.4	794.3	792.4	790.3	786.9	782.2	777.5	772.8	768.0	764.5
50°	755.7	754.2	752.7	751.2	749.7	746.7	742.5	738.2	734.0	729.8	725.5
52.5°	714.2	712.2	710.2	708.2	706.1	703.1	699.1	695.1	691.2	687.2	683.6
55°	650.5	648.6	646.8	645.1	643.2	640.4	636.9	633.2	629.5	625.9	622.2
57.5°	586.6	585.1	583.6	582.2	580.7	578.0	574.0	570.0	566.0	562.0	558.4
60°	543.9	542.7	541.4	540.3	539.0	536.3	532.1	527.8	523.5	519.3	515.9
62.5°	502.4	500.4	498.5	496.5	494.5	492.0	488.7	485.4	482.1	478.8	475.7
65°	438.6	436.8	435.1	433.2	431.4	428.9	425.9	422.8	419.8	416.8	414.1
67.5°	373.9	372.5	371.0	369.5	368.1	366.0	363.2	360.5	357.8	355.1	352.9
70°	333.4	332.3	331.0	329.8	328.6	326.6	323.9	321.1	318.4	315.7	313.5
72.5°	291.9	290.7	289.4	288.3	287.0	285.5	283.8	282.0	280.3	278.5	276.3
75°	229.6	229.0	228.4	227.7	227.1	226.0	224.5	223.0	221.5	220.0	218.2
77.5°	173.8	172.8	171.7	170.8	169.7	168.9	168.3	167.6	167.0	166.5	165.5
80°	136.7	136.3	136.1	135.7	135.5	135.0	134.4	133.8	133.1	132.6	131.6
82.5°	101.7	101.7	101.6	101.5	101.4	101.2	100.9	100.5	100.1	99.8	98.6
85°	56.0	55.7	55.5	55.1	54.8	54.5	54.2	53.9	53.6	53.3	52.3
87.5°	19.9	19.9	20.2	20.0	19.9	19.9	20.3	21.0	21.7	21.4	20.4
90°	0.9	3.6	7.1	8.9	10.7	13.4	17.8	24.0	29.3	30.2	29.3
92.5°	10.9	15.7	22.1	25.9	32.0	40.4	60.5	88.8	114.0	115.7	97.7
95°	31.1	34.7	43.6	51.6	65.9	87.2	128.1	205.5	308.8	348.8	305.2
97.5°	50.7	55.6	65.0	77.0	93.5	117.6	169.1	277.0	448.5	595.6	624.7
100°	68.5	71.2	79.2	93.5	111.3	136.2	183.3	291.9	484.1	703.0	831.3
102.5°	84.9	86.9	94.9	109.1	127.6	152.6	196.2	292.7	470.6	706.6	908.1
105°	108.6	112.2	118.3	131.7	151.3	176.2	218.0	297.2	444.1	659.4	896.2
107.5°	134.2	137.1	143.1	155.4	174.8	199.9	240.5	309.5	430.9	608.9	818.1
110°	151.3	154.9	160.2	171.7	190.5	216.2	255.4	319.5	428.1	584.7	768.9



TEST NUMBER: P331455-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	166.9	170.5	176.6	187.4	205.4	231.9	269.7	330.2	428.7	569.0	734.8
115°	191.4	195.8	201.2	211.8	229.6	253.6	291.9	346.2	432.5	551.8	692.4
117.5°	216.6	220.2	225.5	235.0	252.0	277.0	312.4	363.3	438.9	543.4	665.7
120°	232.3	235.9	241.2	249.1	267.0	291.9	326.6	374.7	443.2	538.4	651.5
122.5°	247.3	250.0	255.4	264.1	282.0	307.6	340.1	384.6	448.2	535.6	639.4
125°	267.0	269.7	275.0	285.7	303.4	328.4	360.4	400.5	455.7	530.4	622.1
127.5°	282.7	286.2	293.6	305.4	322.5	348.1	379.3	415.3	463.3	527.4	606.1
130°	291.9	295.4	304.3	316.8	334.7	359.5	390.7	424.5	469.0	525.9	595.4
132.5°	300.4	304.7	314.3	327.5	346.0	371.0	400.6	433.7	474.7	525.2	586.8
135°	313.3	316.8	327.5	340.8	361.3	386.2	414.7	445.9	481.4	524.1	574.9
137.5°	325.4	329.7	340.3	354.5	374.9	398.0	426.1	455.1	487.5	524.0	566.5
140°	334.7	338.2	348.8	363.1	382.7	405.8	432.5	460.1	490.4	523.3	561.6
142.5°	343.8	346.7	356.7	371.0	389.8	411.5	437.5	464.4	492.5	523.3	556.6
145°	357.8	361.3	370.2	383.6	401.4	421.0	445.0	469.9	494.8	521.5	550.0
147.5°	372.7	375.4	383.9	396.2	411.0	428.5	451.0	473.0	495.5	518.4	543.2
150°	382.7	385.3	392.4	404.0	417.4	433.4	453.9	474.3	494.8	516.2	537.5
152.5°	392.6	393.9	401.0	411.2	423.8	438.4	456.7	475.0	493.4	512.6	532.5
155°	406.7	407.6	413.0	422.8	432.5	445.9	461.0	476.1	491.2	506.4	523.3
157.5°	418.5	419.4	423.7	432.1	440.0	451.2	464.0	476.1	487.1	500.0	514.6
160°	426.3	427.2	430.7	437.8	445.0	454.8	465.5	476.1	485.0	495.7	508.2
162.5°	434.1	433.5	437.1	442.8	449.2	456.9	466.2	475.4	482.9	492.1	502.5
165°	443.2	442.3	444.1	449.4	453.9	459.2	467.3	473.5	478.8	485.0	493.0
167.5°	450.7	449.6	451.2	454.6	457.8	461.2	467.1	472.3	474.7	478.8	483.8
170°	455.7	453.9	454.8	457.4	459.2	461.9	466.4	470.8	472.6	475.2	478.8
172.5°	458.5	457.4	456.9	459.6	460.7	462.6	465.7	468.7	469.8	471.0	473.9
175°	461.9	461.0	460.1	461.9	461.9	462.8	464.6	466.4	465.5	466.4	467.3
177.5°	463.5	462.1	461.4	462.8	462.8	462.8	463.5	464.9	463.5	462.8	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331455-940  
 CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1415.1	1417.6	1420.0	1421.0	1420.5	1420.0	1419.5	1419.1
5°	1405.6	1408.0	1410.4	1411.4	1410.8	1410.2	1409.5	1408.9
7.5°	1389.7	1392.1	1394.6	1395.5	1394.8	1394.2	1393.5	1392.9
10°	1375.6	1378.0	1380.4	1381.2	1380.3	1379.3	1378.4	1377.5
12.5°	1358.8	1360.5	1362.2	1362.7	1362.0	1361.4	1360.7	1360.0
15°	1329.4	1330.6	1331.8	1331.7	1330.2	1328.6	1327.1	1325.6
17.5°	1294.5	1295.9	1297.3	1297.3	1295.7	1294.3	1292.9	1291.4
20°	1267.3	1268.2	1269.1	1268.9	1267.7	1266.5	1265.3	1264.1
22.5°	1238.5	1238.7	1238.9	1238.6	1237.9	1237.2	1236.4	1235.6
25°	1191.5	1192.1	1192.8	1192.8	1192.1	1191.5	1190.9	1190.3
27.5°	1145.3	1144.3	1143.4	1142.3	1140.9	1139.3	1137.9	1136.5
30°	1109.2	1108.3	1107.4	1106.3	1105.1	1103.8	1102.7	1101.4
32.5°	1073.9	1072.2	1070.6	1069.2	1067.9	1066.8	1065.5	1064.3
35°	1017.2	1015.4	1013.5	1011.9	1010.4	1008.9	1007.3	1005.8
37.5°	960.3	958.1	955.8	954.0	952.5	951.0	949.6	948.2
40°	921.0	918.4	915.6	913.6	912.4	911.2	910.0	908.7
42.5°	882.3	879.3	876.4	874.1	872.4	870.7	869.0	867.2
45°	822.9	819.5	816.2	813.9	812.6	811.5	810.2	809.0
47.5°	761.0	757.4	753.9	751.3	749.5	747.8	746.0	744.2
50°	721.2	717.0	712.7	709.9	708.4	706.9	705.3	703.8
52.5°	680.1	676.5	673.1	670.3	668.2	666.3	664.2	662.3
55°	618.6	614.9	611.4	608.8	607.3	605.7	604.2	602.6
57.5°	554.7	551.2	547.6	545.2	544.1	543.0	541.8	540.6
60°	512.6	509.3	506.0	503.8	502.9	502.0	501.1	500.2
62.5°	472.7	469.6	466.5	464.3	463.2	462.0	460.8	459.7
65°	411.3	408.6	405.9	403.8	402.3	400.7	399.2	397.7
67.5°	350.8	348.7	346.5	344.8	343.7	342.4	341.3	340.0
70°	311.4	309.3	307.2	305.5	304.3	303.1	301.8	300.7
72.5°	274.3	272.2	270.0	268.5	267.5	266.5	265.6	264.6
75°	216.4	214.5	212.8	212.1	212.8	213.3	213.9	214.5
77.5°	164.6	163.7	162.8	161.9	161.0	160.2	159.3	158.5
80°	130.7	129.8	128.9	128.1	127.5	127.0	126.4	125.7
82.5°	97.5	96.3	95.1	94.5	94.3	94.3	94.2	94.0
85°	51.5	50.6	49.7	49.0	48.8	48.4	48.2	47.8
87.5°	19.5	18.5	18.1	17.7	17.6	17.3	17.0	16.8
90°	28.4	26.7	28.4	29.3	29.3	29.3	29.3	29.3
92.5°	77.6	66.6	59.1	53.6	52.9	50.0	50.7	49.3
95°	233.2	178.9	141.5	121.9	110.4	103.3	100.6	101.5
97.5°	544.1	445.1	348.8	284.6	242.1	220.2	207.1	199.7
100°	812.5	702.1	580.2	472.6	398.7	360.4	334.7	318.6
102.5°	988.4	963.5	874.3	760.2	679.9	614.6	582.4	560.7
105°	1081.3	1181.9	1193.5	1164.0	1108.8	1053.7	1015.4	1003.0
107.5°	1014.4	1165.8	1258.4	1301.5	1308.4	1305.4	1297.7	1281.2
110°	956.7	1116.0	1229.9	1302.9	1341.1	1358.1	1366.1	1365.2





TEST NUMBER: P331455-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	904.0	1056.9	1178.7	1262.3	1315.5	1343.8	1359.0	1363.8
115°	839.2	976.2	1092.9	1184.5	1247.7	1288.6	1311.8	1319.8
117.5°	790.4	910.8	1016.5	1102.5	1166.9	1210.1	1234.6	1241.3
120°	766.2	876.6	970.9	1052.0	1114.2	1156.0	1181.9	1190.8
122.5°	747.0	848.1	937.5	1010.7	1066.5	1107.6	1130.6	1138.1
125°	719.1	810.7	889.0	955.8	1007.5	1041.3	1063.5	1070.6
127.5°	691.5	774.5	848.3	909.9	954.9	986.6	1005.8	1011.6
130°	673.7	750.2	820.6	879.3	922.9	953.1	970.9	978.0
132.5°	656.6	727.5	792.0	847.2	890.1	920.4	936.7	943.2
135°	632.8	691.5	750.2	800.0	838.3	867.7	883.7	887.3
137.5°	613.7	662.8	709.4	752.9	787.8	813.1	827.2	832.5
140°	601.6	644.4	685.3	724.4	752.9	776.1	789.4	794.7
142.5°	591.7	627.9	663.2	696.0	723.0	744.0	755.9	757.0
145°	577.6	607.0	634.5	660.3	681.7	696.9	705.7	708.4
147.5°	566.7	589.9	611.4	630.3	647.9	660.0	666.0	667.6
150°	558.9	578.5	597.2	613.1	626.5	637.2	642.6	643.5
152.5°	551.1	569.2	585.1	599.0	609.4	618.7	622.6	622.8
155°	540.2	554.5	567.8	577.6	587.4	593.6	597.2	595.4
157.5°	527.5	539.5	550.7	558.4	565.3	570.4	572.0	572.0
160°	519.7	529.5	539.3	545.5	551.8	556.2	557.1	557.1
162.5°	511.9	520.2	528.6	533.4	539.7	542.7	543.6	542.9
165°	500.2	506.4	512.6	516.2	519.7	523.3	523.3	522.4
167.5°	488.9	493.7	498.0	501.2	502.8	504.8	504.6	503.5
170°	483.2	485.9	489.5	491.2	492.1	494.8	493.9	492.1
172.5°	476.8	478.8	481.6	482.7	483.6	484.8	483.9	482.9
175°	469.9	470.8	471.7	472.6	472.6	473.5	472.6	470.8
177.5°	464.9	464.9	465.7	465.7	465.7	465.7	464.9	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8

(END OF REPORT)