

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332952-830

Luminaire Tested: **SA4XXRDIP-C795D1205U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332952-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D1205U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7558.7 lumens
Efficiency: N/A
Efficacy: 132.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332952-830

CATALOG NUMBER: SA4XXRDIP-C795D1205U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332952-830

CATALOG NUMBER: SA4XXRDIP-C795D1205U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40				
1	96	92	88	84	87	84	80	78	68	66	64	55	53	52	42	41	40	34				
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	35	34	29				
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25				
4	73	63	55	49	66	57	51	46	47	42	39	38	35	32	30	27	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	20	17				
7	57	45	37	32	52	42	35	30	35	29	26	28	24	22	22	20	17	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13				
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10571	10571	10571
5°	10594	10464	10529
10°	10528	10339	10339
15°	10407	10122	10046
20°	10241	9836	9655
25°	10029	9502	9260
30°	9822	9149	8766
35°	9594	8784	8270
40°	9319	8368	7734
45°	9065	7955	7188
50°	8776	7479	6610
55°	8466	6984	5983
60°	8126	6442	5341
65°	7815	5765	4713
70°	7360	5016	4001
75°	6784	4161	3250
80°	5918	3166	2985
85°	5011	2881	2686



TEST NUMBER: P332952-830

CATALOG NUMBER: SA4XXRDIP-C795D1205U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.0	1.6
10°-20°	343.0	4.5
20°-30°	495.3	6.6
30°-40°	561.4	7.4
40°-50°	542.1	7.2
50°-60°	450.8	6.0
60°-70°	311.3	4.1
70°-80°	157.8	2.1
80°-90°	44.7	0.6
90°-100°	50.1	0.7
100°-110°	319.3	4.2
110°-120°	610.8	8.1
120°-130°	775.4	10.3
130°-140°	829.7	11.0
140°-150°	775.8	10.3
150°-160°	625.7	8.3
160°-170°	403.5	5.3
170°-180°	139.1	1.8
0°-30°	961.2	12.7
0°-40°	1522.6	20.1
0°-60°	2515.6	33.3
0°-90°	3029.3	40.1
90°-120°	980.2	13.0
90°-150°	3361.2	44.5
90°-180°	4529.0	59.9
0°-180°	7558.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1309	1309	1309	1309	1309	
5°	1307	1303	1291	1301	1299	124
15°	1245	1235	1211	1209	1202	351
25°	1126	1106	1067	1050	1040	519
35°	974	940	891	858	839	608
45°	794	756	697	649	630	612
55°	602	560	496	446	425	538
65°	409	365	302	260	247	404
75°	218	180	133	111	104	230
85°	54	35	31	29	29	61
90°	3	15	24	30	33	5
95°	60	25	24	30	32	77
105°	330	336	342	349	312	345
115°	616	619	618	620	620	605
125°	865	869	867	871	872	772
135°	1073	1072	1077	1079	1081	827
145°	1238	1241	1241	1242	1244	773
155°	1357	1358	1355	1359	1356	625
165°	1431	1426	1426	1434	1425	404
175°	1464	1458	1459	1467	1456	139
180°	1464	1464	1464	1464	1464	



TEST NUMBER: P332952-830

CATALOG NUMBER: SA4XXRDIP-C795D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4
2.5°	1312.6	1311.8	1311.1	1310.4	1309.7	1308.3	1306.4	1304.5	1302.5	1300.5	1302.5
5°	1307.3	1306.5	1305.5	1304.7	1303.7	1302.0	1299.3	1296.7	1293.9	1291.3	1293.5
7.5°	1295.5	1294.6	1293.6	1292.7	1291.8	1289.6	1286.1	1282.6	1279.1	1275.6	1277.1
10°	1284.3	1283.2	1282.0	1280.9	1279.8	1277.2	1273.3	1269.2	1265.3	1261.2	1262.1
12.5°	1269.8	1268.6	1267.2	1265.9	1264.7	1261.7	1257.0	1252.2	1247.5	1242.7	1243.3
15°	1245.2	1243.2	1241.1	1239.2	1237.2	1233.4	1227.8	1222.2	1216.6	1211.1	1210.6
17.5°	1215.3	1212.4	1209.5	1206.6	1203.7	1198.9	1192.2	1185.5	1178.8	1172.1	1170.9
20°	1192.0	1189.1	1186.3	1183.4	1180.4	1175.3	1167.6	1160.1	1152.4	1144.9	1143.1
22.5°	1166.4	1163.1	1159.9	1156.6	1153.4	1147.6	1139.5	1131.4	1123.3	1115.2	1112.6
25°	1125.9	1121.8	1117.9	1113.8	1109.8	1103.2	1094.1	1085.0	1075.8	1066.7	1062.9
27.5°	1083.4	1078.4	1073.3	1068.3	1063.2	1055.8	1046.0	1036.3	1026.5	1016.8	1012.1
30°	1053.7	1048.1	1042.5	1037.0	1031.4	1023.4	1013.0	1002.5	991.9	981.5	975.9
32.5°	1022.4	1016.2	1009.8	1003.5	997.3	988.7	977.9	967.0	956.2	945.4	939.0
35°	973.5	966.4	959.2	952.1	945.0	935.9	924.7	913.5	902.4	891.3	883.7
37.5°	921.1	913.8	906.4	899.1	891.7	881.9	869.6	857.2	844.9	832.5	824.1
40°	884.3	876.9	869.6	862.2	854.9	844.8	832.1	819.4	806.7	794.0	784.7
42.5°	848.9	841.2	833.6	825.9	818.1	807.7	794.5	781.2	768.0	754.7	745.2
45°	794.0	785.8	777.5	769.3	761.0	750.3	736.9	723.5	710.1	696.8	685.9
47.5°	737.3	728.8	720.3	711.7	703.2	692.0	678.2	664.2	650.4	636.4	625.1
50°	698.8	690.1	681.4	672.7	664.0	652.5	638.3	624.1	609.7	595.5	584.4
52.5°	659.5	651.0	642.4	634.0	625.5	613.9	599.3	584.7	570.0	555.4	544.1
55°	601.5	592.6	583.7	574.8	565.9	554.2	539.7	525.2	510.8	496.2	484.7
57.5°	544.2	534.9	525.7	516.4	507.1	495.3	481.1	466.8	452.6	438.3	426.6
60°	503.3	494.4	485.5	476.5	467.6	456.1	441.8	427.5	413.3	399.0	387.4
62.5°	466.4	457.1	447.9	438.6	429.3	417.4	402.7	388.1	373.5	358.9	348.2
65°	409.1	399.4	389.8	380.3	370.7	358.8	344.5	330.3	316.0	301.8	292.2
67.5°	349.5	340.4	331.1	322.0	312.7	301.6	288.3	275.1	261.8	248.6	240.3
70°	311.8	302.5	293.0	283.7	274.4	263.3	250.6	237.9	225.3	212.5	205.2
72.5°	271.7	263.3	254.8	246.3	237.8	227.6	215.7	203.6	191.6	179.6	173.3
75°	217.5	209.3	201.0	192.8	184.5	175.2	164.8	154.3	143.8	133.4	128.2
77.5°	162.6	155.6	148.6	141.7	134.6	126.9	118.5	110.0	101.5	93.0	90.0
80°	127.3	120.8	114.4	107.9	101.5	94.9	88.2	81.5	74.8	68.1	67.5
82.5°	96.9	91.0	85.0	79.1	73.1	68.2	64.5	60.6	56.7	53.0	52.4
85°	54.1	49.7	45.2	40.8	36.3	33.7	33.1	32.4	31.8	31.1	30.6
87.5°	19.1	18.2	17.3	16.4	15.6	15.2	15.5	15.6	15.8	16.0	16.1
90°	3.3	5.9	8.7	11.3	13.9	16.3	18.3	20.2	22.1	24.1	25.5
92.5°	13.8	13.9	14.1	14.2	14.4	15.5	17.3	19.3	21.3	23.2	24.7
95°	60.2	51.9	43.6	35.4	27.1	23.1	23.4	23.6	23.8	24.1	25.5
97.5°	127.9	133.1	138.3	143.4	148.5	137.5	110.4	83.2	56.1	28.9	29.0
100°	179.6	184.0	188.4	192.7	197.2	182.6	148.9	115.4	81.8	48.2	44.0
102.5°	237.4	240.6	243.8	247.0	250.2	249.7	245.3	240.9	236.6	232.1	187.6
105°	329.6	331.1	332.5	334.0	335.5	336.9	338.1	339.2	340.4	341.7	343.9
107.5°	415.3	416.0	416.8	417.5	418.2	419.4	421.0	422.7	424.3	426.0	427.1
110°	473.2	473.8	474.6	475.3	476.1	477.1	478.6	480.0	481.5	483.0	483.4



TEST NUMBER: P332952-830

CATALOG NUMBER: SA4XXRDIP-C795D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	529.2	530.6	531.8	533.1	534.4	535.5	536.1	536.8	537.5	538.2	538.1
115°	615.5	616.2	617.0	617.6	618.4	618.7	618.4	618.2	617.9	617.6	618.2
117.5°	693.2	694.2	695.2	696.2	697.1	697.9	698.4	699.0	699.6	700.0	699.9
120°	745.8	746.8	747.8	748.8	749.7	750.1	749.9	749.6	749.3	749.1	749.6
122.5°	794.8	795.5	796.1	796.6	797.2	797.7	798.1	798.3	798.7	799.1	799.4
125°	865.2	866.2	867.1	868.1	869.1	869.3	868.8	868.4	867.9	867.4	868.1
127.5°	931.8	932.0	932.3	932.6	932.7	933.4	934.5	935.7	936.8	937.9	937.7
130°	974.7	975.0	975.2	975.4	975.7	976.2	976.9	977.6	978.4	979.1	979.3
132.5°	1014.2	1014.6	1015.0	1015.5	1015.9	1016.6	1017.5	1018.4	1019.4	1020.3	1020.5
135°	1073.3	1073.1	1072.8	1072.5	1072.3	1072.7	1073.7	1074.6	1075.6	1076.6	1077.0
137.5°	1125.7	1125.8	1125.9	1126.0	1126.1	1126.6	1127.7	1128.8	1129.8	1130.9	1131.4
140°	1159.8	1160.3	1160.7	1161.3	1161.8	1162.2	1162.7	1163.2	1163.7	1164.2	1164.9
142.5°	1190.4	1191.4	1192.2	1193.1	1194.0	1194.6	1194.9	1195.1	1195.4	1195.7	1196.3
145°	1237.6	1238.3	1239.1	1239.7	1240.5	1240.9	1240.9	1240.9	1240.9	1240.9	1241.1
147.5°	1275.0	1276.4	1277.7	1279.1	1280.4	1281.0	1280.8	1280.5	1280.3	1280.1	1280.3
150°	1302.2	1303.2	1304.1	1305.1	1306.1	1306.5	1306.2	1306.0	1305.7	1305.4	1305.4
152.5°	1324.9	1325.8	1326.5	1327.3	1328.0	1328.2	1327.9	1327.4	1326.9	1326.5	1326.9
155°	1357.0	1357.2	1357.4	1357.6	1357.9	1357.6	1357.0	1356.2	1355.5	1354.7	1355.8
157.5°	1383.8	1383.7	1383.6	1383.5	1383.3	1382.8	1382.0	1381.2	1380.4	1379.5	1380.7
160°	1399.7	1398.9	1398.2	1397.5	1396.8	1396.3	1396.0	1395.7	1395.5	1395.2	1396.8
162.5°	1413.6	1412.8	1411.8	1410.9	1409.9	1409.4	1409.1	1408.9	1408.6	1408.4	1409.9
165°	1431.4	1430.2	1429.0	1427.8	1426.5	1426.0	1426.0	1426.0	1426.0	1426.0	1427.9
167.5°	1445.4	1444.2	1442.9	1441.6	1440.4	1439.6	1439.5	1439.4	1439.3	1439.1	1441.2
170°	1453.3	1451.9	1450.4	1449.0	1447.5	1446.9	1447.1	1447.4	1447.6	1447.8	1449.8
172.5°	1458.6	1457.1	1455.7	1454.2	1452.7	1452.1	1452.4	1452.6	1452.8	1453.1	1455.0
175°	1464.2	1462.8	1461.3	1459.9	1458.4	1457.8	1458.0	1458.3	1458.6	1458.8	1460.9
177.5°	1466.9	1465.6	1464.1	1462.8	1461.4	1460.9	1461.3	1461.7	1462.2	1462.5	1464.1
180°	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2



TEST NUMBER: P332952-830

CATALOG NUMBER: SA4XXRDIP-C795D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4
2.5°	1304.5	1306.4	1308.3	1309.3	1309.1	1308.9	1308.7	1308.5
5°	1295.7	1298.0	1300.2	1301.1	1300.6	1300.2	1299.8	1299.3
7.5°	1278.5	1280.0	1281.4	1281.7	1281.0	1280.3	1279.6	1278.8
10°	1263.0	1263.9	1264.8	1264.8	1263.9	1263.0	1262.1	1261.2
12.5°	1243.9	1244.3	1244.9	1244.5	1243.3	1242.1	1240.8	1239.5
15°	1210.2	1209.8	1209.3	1208.3	1206.7	1205.1	1203.6	1202.0
17.5°	1169.7	1168.5	1167.2	1165.4	1163.0	1160.6	1158.3	1155.9
20°	1141.3	1139.5	1137.7	1135.5	1132.6	1129.6	1126.7	1123.9
22.5°	1109.9	1107.2	1104.6	1102.0	1099.7	1097.3	1095.0	1092.6
25°	1059.1	1055.4	1051.6	1048.6	1046.3	1044.1	1041.9	1039.6
27.5°	1007.4	1002.8	998.1	994.1	990.9	987.7	984.5	981.3
30°	970.3	964.8	959.2	954.6	951.1	947.5	944.0	940.4
32.5°	932.5	926.0	919.5	914.6	911.3	907.9	904.5	901.1
35°	876.1	868.6	861.0	855.2	851.2	847.2	843.1	839.1
37.5°	815.6	807.1	798.6	792.4	788.4	784.4	780.4	776.4
40°	775.3	765.9	756.6	749.9	745.9	741.9	737.9	733.9
42.5°	735.7	726.1	716.6	709.7	705.5	701.3	697.2	693.0
45°	675.0	664.0	653.1	645.6	641.6	637.6	633.6	629.6
47.5°	613.8	602.5	591.2	583.2	578.9	574.5	570.0	565.6
50°	573.3	562.1	550.9	543.3	539.0	534.8	530.6	526.3
52.5°	532.8	521.5	510.1	502.3	497.9	493.4	489.1	484.7
55°	473.1	461.5	450.0	442.1	437.8	433.6	429.3	425.1
57.5°	414.8	403.0	391.2	383.8	380.6	377.4	374.2	371.0
60°	375.9	364.3	352.7	345.1	341.6	338.0	334.4	330.8
62.5°	337.5	326.9	316.1	309.3	306.5	303.7	300.8	297.9
65°	282.6	273.1	263.4	257.3	254.7	251.9	249.3	246.7
67.5°	232.1	223.9	215.7	210.1	207.2	204.2	201.2	198.3
70°	197.8	190.5	183.1	178.3	176.2	173.9	171.6	169.5
72.5°	167.1	160.8	154.5	150.3	148.4	146.3	144.2	142.1
75°	123.1	118.0	112.8	109.6	108.3	107.0	105.6	104.2
77.5°	87.1	84.1	81.1	79.4	79.0	78.6	78.2	77.8
80°	66.8	66.2	65.5	65.0	64.8	64.6	64.4	64.2
82.5°	51.9	51.5	51.0	50.6	50.4	50.1	50.0	49.8
85°	30.2	29.8	29.3	29.0	29.0	29.0	29.0	29.0
87.5°	16.3	16.4	16.5	16.7	17.0	17.2	17.5	17.8
90°	27.1	28.5	30.0	30.9	31.4	31.9	32.3	32.9
92.5°	26.1	27.6	29.0	29.9	30.0	30.1	30.2	30.3
95°	27.1	28.5	30.0	30.8	31.0	31.3	31.5	31.8
97.5°	29.2	29.3	29.5	29.7	30.0	30.2	30.4	30.6
100°	39.9	35.8	31.7	29.7	30.0	30.2	30.4	30.6
102.5°	142.9	98.3	53.6	31.4	31.4	31.5	31.5	31.6
105°	346.1	348.3	350.4	347.1	338.4	329.6	320.9	312.2
107.5°	428.2	429.2	430.3	431.3	432.3	433.2	434.0	435.0
110°	484.0	484.5	484.9	485.5	486.3	487.0	487.8	488.4



TEST NUMBER: P332952-830

CATALOG NUMBER: SA4XXRDIP-C795D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	538.0	537.9	537.8	538.2	539.1	540.1	541.0	541.9
115°	618.7	619.2	619.6	619.9	619.9	619.9	619.9	619.9
117.5°	699.8	699.7	699.6	699.6	699.5	699.4	699.3	699.2
120°	750.1	750.5	751.0	751.0	750.5	750.1	749.6	749.1
122.5°	799.7	799.9	800.2	800.1	799.7	799.2	798.6	798.1
125°	868.8	869.6	870.3	870.8	871.0	871.3	871.6	871.8
127.5°	937.6	937.5	937.4	937.2	937.0	936.8	936.6	936.4
130°	979.6	979.9	980.1	980.1	980.1	980.1	980.1	980.1
132.5°	1020.8	1021.1	1021.2	1021.2	1021.1	1020.9	1020.7	1020.5
135°	1077.5	1078.0	1078.6	1079.0	1079.5	1080.0	1080.4	1080.9
137.5°	1132.0	1132.5	1133.0	1133.2	1133.1	1132.9	1132.7	1132.7
140°	1165.6	1166.4	1167.2	1167.6	1167.8	1168.1	1168.3	1168.6
142.5°	1196.8	1197.3	1197.9	1198.2	1198.3	1198.3	1198.3	1198.3
145°	1241.3	1241.6	1241.8	1242.2	1242.6	1243.1	1243.7	1244.2
147.5°	1280.4	1280.6	1280.8	1281.0	1281.3	1281.6	1281.8	1282.0
150°	1305.4	1305.4	1305.4	1305.6	1305.8	1306.1	1306.4	1306.6
152.5°	1327.3	1327.7	1328.0	1328.1	1328.0	1327.9	1327.8	1327.6
155°	1356.7	1357.6	1358.7	1358.8	1358.0	1357.3	1356.6	1355.8
157.5°	1382.1	1383.3	1384.6	1384.6	1383.3	1382.1	1380.7	1379.5
160°	1398.2	1399.7	1401.1	1401.1	1399.7	1398.2	1396.8	1395.2
162.5°	1411.4	1412.8	1414.3	1414.2	1412.5	1410.9	1409.2	1407.5
165°	1429.8	1431.8	1433.7	1433.6	1431.4	1429.2	1427.0	1424.8
167.5°	1443.4	1445.5	1447.7	1447.5	1445.1	1442.7	1440.2	1437.8
170°	1451.7	1453.7	1455.7	1455.4	1452.9	1450.5	1448.1	1445.7
172.5°	1457.0	1459.0	1460.8	1460.6	1457.9	1455.3	1452.6	1450.0
175°	1463.2	1465.4	1467.5	1467.2	1464.2	1461.3	1458.4	1455.5
177.5°	1465.7	1467.2	1468.8	1468.4	1466.0	1463.7	1461.3	1459.1
180°	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2

(END OF REPORT)