

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332936-830

Luminaire Tested: **SA4XXRDIP-C795D590U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332936-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D590U830-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5017.0 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332936-830
CATALOG NUMBER: SA4XXRDIP-C795D590U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332936-830

CATALOG NUMBER: SA4XXRDIP-C795D590U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	66	66	66	60	
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	59	57	56	56	56	56	51	
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	48	48	48	44	
3	84	74	67	61	78	70	63	58	61	56	52	54	50	47	46	43	41	41	41	41	37	
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36	36	36	36	32	
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	31	31	31	28	
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	28	28	28	28	25	
7	60	48	40	35	56	46	38	33	40	35	30	36	31	27	31	28	25	25	25	25	22	
8	56	44	36	31	53	41	34	29	37	31	27	33	28	25	29	25	22	22	22	22	20	
9	52	40	33	28	49	38	31	26	34	28	24	30	26	22	27	23	20	20	20	20	18	
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	18	18	18	16	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10571	10571	10571
5°	10594	10464	10529
10°	10528	10339	10339
15°	10407	10122	10046
20°	10241	9836	9655
25°	10029	9502	9260
30°	9822	9149	8766
35°	9594	8784	8270
40°	9319	8368	7734
45°	9065	7955	7188
50°	8776	7479	6610
55°	8466	6984	5983
60°	8126	6442	5341
65°	7815	5765	4713
70°	7360	5016	4001
75°	6784	4161	3250
80°	5918	3166	2985
85°	5011	2881	2686



TEST NUMBER: P332936-830

CATALOG NUMBER: SA4XXRDIP-C795D590U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.0	2.5
10°-20°	343.0	6.8
20°-30°	495.3	9.9
30°-40°	561.4	11.2
40°-50°	542.1	10.8
50°-60°	450.8	9.0
60°-70°	311.3	6.2
70°-80°	157.8	3.1
80°-90°	42.0	0.8
90°-100°	197.7	3.9
100°-110°	411.4	8.2
110°-120°	368.5	7.3
120°-130°	310.0	6.2
130°-140°	258.4	5.2
140°-150°	197.4	3.9
150°-160°	138.8	2.8
160°-170°	81.6	1.6
170°-180°	26.6	0.5
0°-30°	961.2	19.2
0°-40°	1522.6	30.3
0°-60°	2515.6	50.1
0°-90°	3026.6	60.3
90°-120°	977.6	19.5
90°-150°	1743.4	34.8
90°-180°	1990.0	39.7
0°-180°	5017.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1309	1309	1309	1309	1309	
5°	1307	1303	1291	1301	1299	124
15°	1245	1235	1211	1209	1202	351
25°	1126	1106	1067	1050	1040	519
35°	974	940	891	858	839	608
45°	794	756	697	649	630	612
55°	602	560	496	446	425	538
65°	409	365	302	260	247	404
75°	218	180	133	111	104	230
85°	54	35	31	29	29	61
90°	1	4	10	11	11	4
95°	18	56	438	217	131	20
105°	63	91	353	760	756	67
115°	111	139	314	604	726	110
125°	154	183	313	514	580	137
135°	183	218	310	456	518	142
145°	211	242	309	385	423	133
155°	240	259	300	340	354	111
165°	262	270	288	305	309	74
175°	273	274	276	280	278	26
180°	274	274	274	274	274	



TEST NUMBER: P332936-830

CATALOG NUMBER: SA4XXRDIP-C795D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4
2.5°	1312.6	1311.8	1311.1	1310.4	1309.7	1308.3	1306.4	1304.5	1302.5	1300.5	1302.5
5°	1307.3	1306.5	1305.5	1304.7	1303.7	1302.0	1299.3	1296.7	1293.9	1291.3	1293.5
7.5°	1295.5	1294.6	1293.6	1292.7	1291.8	1289.6	1286.1	1282.6	1279.1	1275.6	1277.1
10°	1284.3	1283.2	1282.0	1280.9	1279.8	1277.2	1273.3	1269.2	1265.3	1261.2	1262.1
12.5°	1269.8	1268.6	1267.2	1265.9	1264.7	1261.7	1257.0	1252.2	1247.5	1242.7	1243.3
15°	1245.2	1243.2	1241.1	1239.2	1237.2	1233.4	1227.8	1222.2	1216.6	1211.1	1210.6
17.5°	1215.3	1212.4	1209.5	1206.6	1203.7	1198.9	1192.2	1185.5	1178.8	1172.1	1170.9
20°	1192.0	1189.1	1186.3	1183.4	1180.4	1175.3	1167.6	1160.1	1152.4	1144.9	1143.1
22.5°	1166.4	1163.1	1159.9	1156.6	1153.4	1147.6	1139.5	1131.4	1123.3	1115.2	1112.6
25°	1125.9	1121.8	1117.9	1113.8	1109.8	1103.2	1094.1	1085.0	1075.8	1066.7	1062.9
27.5°	1083.4	1078.4	1073.3	1068.3	1063.2	1055.8	1046.0	1036.3	1026.5	1016.8	1012.1
30°	1053.7	1048.1	1042.5	1037.0	1031.4	1023.4	1013.0	1002.5	991.9	981.5	975.9
32.5°	1022.4	1016.2	1009.8	1003.5	997.3	988.7	977.9	967.0	956.2	945.4	939.0
35°	973.5	966.4	959.2	952.1	945.0	935.9	924.7	913.5	902.4	891.3	883.7
37.5°	921.1	913.8	906.4	899.1	891.7	881.9	869.6	857.2	844.9	832.5	824.1
40°	884.3	876.9	869.6	862.2	854.9	844.8	832.1	819.4	806.7	794.0	784.7
42.5°	848.9	841.2	833.6	825.9	818.1	807.7	794.5	781.2	768.0	754.7	745.2
45°	794.0	785.8	777.5	769.3	761.0	750.3	736.9	723.5	710.1	696.8	685.9
47.5°	737.3	728.8	720.3	711.7	703.2	692.0	678.2	664.2	650.4	636.4	625.1
50°	698.8	690.1	681.4	672.7	664.0	652.5	638.3	624.1	609.7	595.5	584.4
52.5°	659.5	651.0	642.4	634.0	625.5	613.9	599.3	584.7	570.0	555.4	544.1
55°	601.5	592.6	583.7	574.8	565.9	554.2	539.7	525.2	510.8	496.2	484.7
57.5°	544.2	534.9	525.7	516.4	507.1	495.3	481.1	466.8	452.6	438.3	426.6
60°	503.3	494.4	485.5	476.5	467.6	456.1	441.8	427.5	413.3	399.0	387.4
62.5°	466.4	457.1	447.9	438.6	429.3	417.4	402.7	388.1	373.5	358.9	348.2
65°	409.1	399.4	389.8	380.3	370.7	358.8	344.5	330.3	316.0	301.8	292.2
67.5°	349.5	340.4	331.1	322.0	312.7	301.6	288.3	275.1	261.8	248.6	240.3
70°	311.8	302.5	293.0	283.7	274.4	263.3	250.6	237.9	225.3	212.5	205.2
72.5°	271.7	263.3	254.8	246.3	237.8	227.6	215.7	203.6	191.6	179.6	173.3
75°	217.5	209.3	201.0	192.8	184.5	175.2	164.8	154.3	143.8	133.4	128.2
77.5°	162.6	155.6	148.6	141.7	134.6	126.9	118.5	110.0	101.5	93.0	90.0
80°	127.3	120.8	114.4	107.9	101.5	94.9	88.2	81.5	74.8	68.1	67.5
82.5°	96.9	91.0	85.0	79.1	73.1	68.2	64.5	60.6	56.7	53.0	52.4
85°	54.1	49.7	45.2	40.8	36.3	33.7	33.1	32.4	31.8	31.1	30.6
87.5°	18.6	17.3	16.2	14.9	13.6	12.8	13.3	13.1	13.1	13.2	12.9
90°	0.6	1.6	3.2	3.8	4.3	4.3	7.5	7.5	8.6	9.7	9.1
92.5°	6.1	9.0	13.9	20.5	28.4	39.6	66.9	108.6	149.3	170.5	142.0
95°	17.7	19.3	24.7	31.8	44.6	67.2	114.0	202.2	330.6	438.2	450.5
97.5°	31.9	31.9	36.5	42.9	54.0	73.0	109.0	181.7	309.5	461.6	566.1
100°	40.9	40.9	44.6	51.1	61.3	78.5	110.2	171.0	280.7	432.3	570.0
102.5°	49.5	50.3	53.6	59.7	69.5	85.8	114.5	168.0	261.3	395.8	537.6
105°	62.9	64.6	67.2	73.7	83.3	99.0	124.7	169.4	244.7	352.7	479.1
107.5°	77.8	78.8	81.5	88.4	97.6	113.0	136.7	177.3	241.7	328.7	431.8
110°	87.7	88.7	91.4	97.8	107.5	122.1	145.7	183.3	242.5	320.5	408.1



TEST NUMBER: P332936-830

CATALOG NUMBER: SA4XXRDIP-C795D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	97.1	98.2	101.3	107.4	117.0	131.5	154.3	189.8	245.1	316.6	394.7
115°	110.7	112.4	116.1	121.5	131.8	146.3	167.8	200.0	250.1	314.5	382.3
117.5°	125.0	126.5	129.8	135.7	145.2	160.3	180.8	210.5	255.2	314.0	376.7
120°	134.4	135.5	139.2	145.2	154.3	169.4	189.8	217.7	259.2	314.0	373.7
122.5°	143.0	144.1	147.9	153.4	163.3	178.0	198.4	224.6	263.1	313.6	370.2
125°	154.3	156.5	159.7	165.6	175.8	190.9	210.2	235.0	268.8	312.9	364.6
127.5°	164.3	166.1	169.9	176.6	187.3	202.5	221.2	243.9	273.4	311.7	356.9
130°	169.9	172.0	176.3	184.5	194.6	210.2	228.5	249.5	276.9	311.3	352.1
132.5°	175.5	177.2	182.9	190.5	201.5	216.2	234.5	255.1	279.9	310.9	347.9
135°	183.3	185.5	190.9	200.0	211.3	225.3	243.0	262.4	284.5	310.2	341.4
137.5°	191.2	193.2	199.2	207.8	219.6	232.9	249.5	267.6	287.1	310.1	335.8
140°	196.8	198.4	204.3	213.5	224.7	237.6	253.8	271.0	289.3	309.7	332.8
142.5°	202.8	204.4	209.9	218.6	229.5	242.0	257.7	273.5	291.0	309.7	330.3
145°	211.3	212.9	218.3	225.8	236.0	247.9	261.8	276.4	292.0	308.6	325.8
147.5°	220.8	221.4	226.1	233.8	242.4	253.1	266.2	278.8	292.5	306.7	321.9
150°	226.9	227.4	231.8	238.2	246.3	256.5	268.3	280.1	292.5	305.4	318.9
152.5°	232.5	232.6	236.9	242.9	250.2	259.5	270.0	281.0	291.6	303.2	315.4
155°	240.3	240.9	244.1	249.5	255.4	263.4	272.6	281.7	290.3	300.0	310.2
157.5°	248.0	248.0	251.0	255.1	260.3	266.6	274.5	281.7	289.0	296.7	305.0
160°	252.7	252.7	254.9	258.6	262.9	268.8	275.3	281.7	287.7	294.1	301.1
162.5°	257.0	256.6	258.3	261.6	265.5	270.1	276.2	281.7	286.3	291.5	297.7
165°	261.8	261.8	262.9	265.6	268.3	271.5	276.4	280.7	283.9	287.7	292.0
167.5°	266.6	266.2	266.6	268.7	270.2	272.7	276.3	279.4	281.3	283.8	286.8
170°	268.8	268.3	268.8	270.4	271.5	273.1	275.8	278.5	279.6	281.2	283.3
172.5°	271.0	270.4	270.5	271.7	272.4	273.5	275.4	277.7	277.9	278.6	280.3
175°	273.1	272.6	272.6	273.1	273.7	273.7	274.8	276.4	275.8	275.8	276.9
177.5°	274.1	273.7	273.2	273.7	273.7	273.7	274.1	274.9	274.1	274.1	274.6
180°	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7



TEST NUMBER: P332936-830

CATALOG NUMBER: SA4XXRDIP-C795D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4
2.5°	1304.5	1306.4	1308.3	1309.3	1309.1	1308.9	1308.7	1308.5
5°	1295.7	1298.0	1300.2	1301.1	1300.6	1300.2	1299.8	1299.3
7.5°	1278.5	1280.0	1281.4	1281.7	1281.0	1280.3	1279.6	1278.8
10°	1263.0	1263.9	1264.8	1264.8	1263.9	1263.0	1262.1	1261.2
12.5°	1243.9	1244.3	1244.9	1244.5	1243.3	1242.1	1240.8	1239.5
15°	1210.2	1209.8	1209.3	1208.3	1206.7	1205.1	1203.6	1202.0
17.5°	1169.7	1168.5	1167.2	1165.4	1163.0	1160.6	1158.3	1155.9
20°	1141.3	1139.5	1137.7	1135.5	1132.6	1129.6	1126.7	1123.9
22.5°	1109.9	1107.2	1104.6	1102.0	1099.7	1097.3	1095.0	1092.6
25°	1059.1	1055.4	1051.6	1048.6	1046.3	1044.1	1041.9	1039.6
27.5°	1007.4	1002.8	998.1	994.1	990.9	987.7	984.5	981.3
30°	970.3	964.8	959.2	954.6	951.1	947.5	944.0	940.4
32.5°	932.5	926.0	919.5	914.6	911.3	907.9	904.5	901.1
35°	876.1	868.6	861.0	855.2	851.2	847.2	843.1	839.1
37.5°	815.6	807.1	798.6	792.4	788.4	784.4	780.4	776.4
40°	775.3	765.9	756.6	749.9	745.9	741.9	737.9	733.9
42.5°	735.7	726.1	716.6	709.7	705.5	701.3	697.2	693.0
45°	675.0	664.0	653.1	645.6	641.6	637.6	633.6	629.6
47.5°	613.8	602.5	591.2	583.2	578.9	574.5	570.0	565.6
50°	573.3	562.1	550.9	543.3	539.0	534.8	530.6	526.3
52.5°	532.8	521.5	510.1	502.3	497.9	493.4	489.1	484.7
55°	473.1	461.5	450.0	442.1	437.8	433.6	429.3	425.1
57.5°	414.8	403.0	391.2	383.8	380.6	377.4	374.2	371.0
60°	375.9	364.3	352.7	345.1	341.6	338.0	334.4	330.8
62.5°	337.5	326.9	316.1	309.3	306.5	303.7	300.8	297.9
65°	282.6	273.1	263.4	257.3	254.7	251.9	249.3	246.7
67.5°	232.1	223.9	215.7	210.1	207.2	204.2	201.2	198.3
70°	197.8	190.5	183.1	178.3	176.2	173.9	171.6	169.5
72.5°	167.1	160.8	154.5	150.3	148.4	146.3	144.2	142.1
75°	123.1	118.0	112.8	109.6	108.3	107.0	105.6	104.2
77.5°	87.1	84.1	81.1	79.4	79.0	78.6	78.2	77.8
80°	66.8	66.2	65.5	65.0	64.8	64.6	64.4	64.2
82.5°	51.9	51.5	51.0	50.6	50.4	50.1	50.0	49.8
85°	30.2	29.8	29.3	29.0	29.0	29.0	29.0	29.0
87.5°	12.8	12.7	12.6	12.6	12.9	13.2	13.3	13.5
90°	9.7	10.2	10.7	10.7	11.3	11.8	11.3	11.3
92.5°	105.6	79.5	63.2	52.5	46.1	43.3	41.4	41.4
95°	398.4	315.1	243.0	190.9	164.6	147.9	138.2	131.2
97.5°	588.6	557.7	505.1	448.9	410.4	378.0	361.8	350.6
100°	648.5	659.2	632.8	593.0	546.3	513.5	497.4	493.0
102.5°	645.5	698.8	706.4	689.8	661.1	637.3	620.4	616.9
105°	602.2	695.2	748.5	770.5	771.6	767.2	759.7	756.5
107.5°	540.8	639.8	714.8	762.7	789.3	801.5	806.9	808.3
110°	503.8	596.8	674.8	734.0	772.1	794.7	804.4	809.2



TEST NUMBER: P332936-830

CATALOG NUMBER: SA4XXRDIP-C795D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	476.7	558.9	632.6	691.7	735.1	762.4	776.0	783.8
115°	449.5	515.7	578.5	630.2	672.6	704.9	722.1	726.4
117.5°	436.1	490.9	540.4	584.1	620.4	647.4	664.9	668.3
120°	430.2	480.1	523.1	561.3	592.0	615.7	629.6	635.6
122.5°	425.0	473.3	512.4	545.8	571.7	592.0	603.8	609.7
125°	416.1	462.4	499.5	529.0	550.5	566.2	576.4	579.6
127.5°	405.4	449.6	486.6	514.6	536.3	550.2	558.7	561.9
130°	396.8	439.3	475.8	504.4	526.4	539.8	548.5	551.7
132.5°	387.8	427.6	463.4	491.8	513.5	528.7	536.8	540.1
135°	375.3	410.3	443.0	470.0	491.4	506.5	515.1	518.3
137.5°	364.0	393.6	421.2	445.5	465.6	480.5	487.6	491.4
140°	357.5	382.9	407.0	429.6	448.5	460.2	467.8	472.1
142.5°	351.6	373.8	394.5	414.2	430.7	441.8	448.5	451.4
145°	343.0	361.3	377.5	392.5	406.0	415.1	420.5	423.1
147.5°	336.0	350.5	363.4	375.3	385.2	393.0	397.1	398.1
150°	331.8	344.1	354.9	364.6	373.2	380.1	383.3	383.9
152.5°	327.0	337.6	347.5	355.5	362.8	368.5	370.4	371.0
155°	319.9	328.5	336.6	343.0	348.5	352.7	354.3	354.3
157.5°	312.3	319.5	326.2	331.4	335.5	338.7	339.7	339.7
160°	307.6	313.5	319.3	323.7	326.9	330.2	330.6	330.6
162.5°	302.8	307.8	312.5	316.4	318.8	322.0	322.5	322.1
165°	296.2	299.4	303.2	305.9	308.1	310.2	309.7	309.2
167.5°	289.9	292.4	295.4	297.0	298.1	299.4	299.4	299.0
170°	286.1	287.7	289.8	291.4	292.5	293.0	292.5	292.5
172.5°	282.6	283.8	285.1	286.3	286.9	287.5	286.9	286.1
175°	278.0	278.5	279.6	279.6	279.6	280.7	279.6	278.5
177.5°	274.9	275.4	275.4	275.8	275.4	275.8	274.9	274.1
180°	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7

(END OF REPORT)