

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331258-940

Luminaire Tested: **SA2XXDIP-C290D725U940-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331258-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D725U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3748.4 lumens
Efficiency: N/A
Efficacy: 120.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331258-940
CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	31	30	28	23
3	78	69	62	57	70	63	57	52	50	46	43	38	36	33	28	26	25	20
4	72	61	54	48	64	56	49	44	45	40	36	34	31	29	25	23	21	17
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	22	20	19	15
6	61	49	41	36	54	45	38	33	36	31	28	28	25	22	20	18	17	13
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	22	23	20	17	17	15	13	11
9	48	37	30	25	43	33	27	23	27	23	19	21	18	16	16	14	12	10
10	45	34	27	22	41	31	25	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8510	8510	8510	8510
5°	9540	8566	7590	8566
10°	10932	8496	6568	8496
15°	12094	8339	5804	8339
20°	11911	8172	5290	8172
25°	10739	7949	4965	7949
30°	8874	7594	4728	7594
35°	6467	7222	4559	7222
40°	5166	6785	4466	6785
45°	4514	6277	4338	6277
50°	4245	5785	4253	5785
55°	3910	5286	4138	5286
60°	3584	4753	3965	4753
65°	3266	4279	3790	4279
70°	2965	3814	3541	3814
75°	2633	3300	3132	3300
80°	2259	2724	2520	2724
85°	2038	2038	1501	2038



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	1.3
10°-20°	145.9	3.9
20°-30°	211.8	5.7
30°-40°	223.5	6.0
40°-50°	197.9	5.3
50°-60°	157.9	4.2
60°-70°	107.3	2.9
70°-80°	55.0	1.5
80°-90°	15.4	0.4
90°-100°	29.4	0.8
100°-110°	107.8	2.9
110°-120°	288.3	7.7
120°-130°	475.8	12.7
130°-140°	506.0	13.5
140°-150°	470.3	12.5
150°-160°	378.1	10.1
160°-170°	243.7	6.5
170°-180°	83.9	2.2
0°-30°	407.9	10.9
0°-40°	631.4	16.8
0°-60°	987.2	26.3
0°-90°	1165.0	31.1
90°-120°	425.5	11.4
90°-150°	1877.7	50.1
90°-180°	2583.0	68.9
0°-180°	3748.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	589	528	468	528	589	59
15°	724	499	347	499	724	200
25°	603	446	279	446	603	272
35°	328	366	231	366	328	213
45°	198	275	190	275	198	155
55°	139	188	147	188	139	125
65°	86	112	99	112	86	85
75°	42	53	50	53	42	45
85°	11	11	8	11	11	12
90°	17	1	17	1	17	8
95°	28	42	28	42	28	26
105°	48	194	48	194	48	50
115°	52	367	52	367	52	131
125°	545	519	545	519	545	472
135°	663	642	663	642	663	511
145°	756	744	756	744	756	473
155°	820	820	820	820	820	379
165°	862	864	862	864	862	243
175°	878	883	878	883	878	84
180°	882	882	882	882	882	



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	551.3	551.5	551.9	549.3	548.9	548.9	546.7	544.7	542.4	539.4	539.8
5°	588.6	590.8	591.7	589.2	585.6	585.2	581.8	576.1	570.8	566.6	563.6
7.5°	633.1	634.0	632.0	628.8	626.2	621.3	614.8	608.6	599.8	591.7	585.8
10°	666.8	668.1	664.6	660.0	656.1	650.4	641.1	631.6	620.1	608.9	600.0
12.5°	692.4	695.4	691.0	690.5	683.9	676.0	664.9	660.1	643.9	628.4	618.8
15°	723.5	723.4	723.8	719.9	715.1	713.8	702.1	689.3	666.5	657.3	641.5
17.5°	714.5	717.6	719.1	719.0	718.9	718.1	714.3	706.3	694.8	680.0	661.8
20°	693.2	697.2	697.9	702.5	705.2	708.6	710.0	707.8	700.7	688.3	672.5
22.5°	660.1	661.3	663.2	670.4	676.1	684.7	689.2	696.8	694.0	688.0	674.8
25°	602.8	600.8	607.9	611.5	624.7	638.5	648.5	659.3	669.1	674.9	671.1
27.5°	534.0	531.0	541.6	551.3	562.0	576.9	592.4	610.6	625.8	644.9	651.4
30°	476.0	477.9	487.9	498.3	514.5	535.6	553.0	573.0	594.8	616.0	630.8
32.5°	413.5	420.4	426.9	442.7	457.0	480.5	506.0	531.1	558.1	582.3	605.2
35°	328.1	336.3	345.2	356.7	376.7	400.0	425.0	458.8	495.7	528.7	555.8
37.5°	276.3	274.9	280.0	288.4	304.6	323.4	352.1	385.5	428.9	467.7	506.0
40°	245.1	244.3	247.9	255.7	268.0	281.8	306.9	336.3	376.6	424.0	469.6
42.5°	223.7	224.2	226.2	231.7	240.1	251.5	270.3	295.2	332.2	376.8	425.8
45°	197.7	199.1	201.3	204.0	208.8	218.2	228.7	246.6	275.7	313.0	361.1
47.5°	179.0	179.1	181.3	183.6	186.5	191.7	200.4	211.5	232.1	262.4	303.9
50°	169.0	167.6	169.2	170.9	174.0	177.6	183.3	193.9	207.6	232.1	266.8
52.5°	156.6	156.7	158.1	158.8	161.5	165.1	170.3	177.6	190.1	209.3	237.7
55°	138.9	140.0	140.8	142.0	144.5	147.0	151.1	156.0	165.7	180.0	201.2
57.5°	122.3	122.7	123.5	125.8	127.3	129.7	133.6	138.0	144.4	155.0	170.9
60°	111.0	111.0	112.6	113.6	115.7	118.1	121.1	125.4	131.1	139.7	152.6
62.5°	100.7	100.5	101.1	102.8	104.3	106.6	109.6	113.2	118.6	126.4	136.8
65°	85.5	85.1	86.3	86.7	88.3	90.5	93.0	96.8	101.1	106.7	116.1
67.5°	70.9	71.4	72.1	72.8	73.7	76.1	77.7	80.3	84.0	88.7	95.0
70°	62.8	62.8	62.8	63.4	64.6	65.8	67.4	69.6	73.1	77.1	82.8
72.5°	53.7	54.4	55.0	54.7	56.2	56.9	58.9	60.1	63.4	66.0	71.0
75°	42.2	42.2	42.2	43.2	43.8	44.3	45.6	46.8	48.4	51.6	54.3
77.5°	31.5	31.4	31.6	31.8	32.5	33.2	33.5	34.6	36.1	37.6	39.9
80°	24.3	24.7	24.9	25.3	25.3	25.7	25.9	27.4	28.4	29.3	30.8
82.5°	18.8	18.9	18.9	19.0	19.2	19.4	20.0	20.4	20.8	21.6	22.6
85°	11.0	10.7	10.7	11.1	11.0	11.0	11.3	11.8	11.8	11.9	12.6
87.5°	7.7	7.6	7.7	7.5	7.4	7.5	7.3	7.0	7.0	7.0	7.0
90°	17.2	16.9	16.7	16.4	16.1	15.6	14.9	14.2	13.5	12.8	11.6
92.5°	17.2	17.0	16.9	16.7	16.6	16.2	15.9	15.5	15.2	14.8	14.3
95°	27.5	27.6	27.7	27.8	28.0	27.7	27.0	26.3	25.6	24.9	23.9
97.5°	36.6	36.5	36.3	36.1	35.9	35.6	35.0	34.4	33.9	33.3	31.0
100°	42.7	42.4	42.2	41.9	41.6	40.9	39.8	38.6	37.5	36.4	34.0
102.5°	45.8	45.4	45.0	44.6	44.2	43.2	41.8	40.3	38.9	37.4	57.5
105°	48.5	47.9	47.3	46.8	46.2	45.1	43.6	42.0	40.5	38.9	77.6
107.5°	49.8	49.3	48.8	48.2	47.6	48.2	49.7	51.3	52.9	54.5	100.9
110°	50.4	49.8	49.2	48.7	48.2	54.9	69.1	83.3	97.5	111.6	152.6



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	50.9	50.5	50.0	49.6	49.0	74.7	126.4	178.2	229.9	281.5	291.7
115°	52.3	62.5	72.7	82.9	93.1	131.1	196.7	262.3	328.0	393.6	390.0
117.5°	213.6	247.1	280.6	314.1	347.7	372.4	388.3	404.2	420.1	436.0	433.5
120°	389.1	408.2	427.4	446.5	465.7	474.4	472.7	471.0	469.2	467.5	465.0
122.5°	485.5	489.3	492.9	496.7	500.4	501.8	500.7	499.7	498.6	497.7	494.9
125°	545.4	544.9	544.6	544.1	543.7	543.0	542.0	541.0	540.0	539.0	536.3
127.5°	583.2	583.1	583.0	582.9	582.8	582.0	580.6	579.2	577.7	576.2	574.3
130°	606.6	606.7	606.9	607.1	607.2	606.5	604.9	603.3	601.8	600.2	598.7
132.5°	629.5	629.7	629.9	630.0	630.2	629.5	628.2	626.9	625.5	624.2	622.7
135°	662.7	663.0	663.3	663.6	663.9	663.3	661.9	660.5	659.1	657.6	656.4
137.5°	692.9	693.5	693.9	694.5	694.9	694.5	693.0	691.7	690.3	688.9	687.4
140°	711.9	712.6	713.3	714.0	714.7	714.4	713.1	711.9	710.6	709.4	707.8
142.5°	730.2	730.9	731.6	732.4	733.1	732.8	731.6	730.5	729.3	728.2	726.4
145°	755.9	756.6	757.3	758.0	758.7	758.6	757.6	756.6	755.6	754.6	752.2
147.5°	778.5	779.1	779.6	780.2	780.9	780.8	780.1	779.3	778.6	777.8	775.4
150°	792.2	792.9	793.6	794.3	795.0	795.0	794.2	793.3	792.5	791.6	789.3
152.5°	804.0	804.9	805.8	806.8	807.7	807.8	806.9	806.0	805.2	804.3	802.2
155°	820.3	821.4	822.6	823.7	824.8	825.0	824.1	823.3	822.4	821.5	819.8
157.5°	835.3	836.3	837.4	838.6	839.6	839.7	838.7	837.8	836.9	835.9	834.6
160°	843.9	844.9	845.9	846.9	847.8	847.9	847.1	846.2	845.4	844.5	843.6
162.5°	851.0	852.3	853.5	854.7	856.0	856.0	855.1	854.1	853.2	852.2	851.5
165°	861.7	862.7	863.7	864.8	865.8	865.8	864.8	863.7	862.7	861.7	861.3
167.5°	868.5	869.8	871.1	872.4	873.6	873.8	872.8	871.8	870.8	869.8	869.4
170°	872.6	873.9	875.1	876.5	877.7	877.9	876.8	875.8	874.9	873.9	873.6
172.5°	875.7	876.9	878.2	879.5	880.7	880.9	879.9	879.0	878.0	876.9	876.6
175°	878.3	879.8	881.2	882.6	884.0	884.2	883.2	882.3	881.3	880.3	879.9
177.5°	880.0	881.0	882.1	883.1	884.1	884.2	883.4	882.6	881.8	881.0	880.9
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	540.8	539.6	538.8	535.8	533.2	530.7	529.9	530.1	526.6	523.2	521.7
5°	562.0	557.9	554.0	548.6	542.1	534.9	531.4	528.5	521.4	513.7	509.3
7.5°	580.8	575.0	567.6	557.3	547.9	536.7	529.6	523.3	513.0	502.1	495.4
10°	592.3	584.4	574.9	562.3	550.8	537.2	527.7	518.2	506.0	493.0	484.9
12.5°	602.2	591.6	582.2	566.1	552.4	535.4	524.1	510.7	497.9	482.5	474.6
15°	625.7	606.1	588.3	570.0	553.2	529.5	516.9	498.9	482.1	463.1	454.0
17.5°	643.9	621.8	593.8	570.6	551.0	524.7	506.3	484.7	464.8	443.1	430.7
20°	654.2	628.9	598.8	571.2	547.8	517.7	497.7	475.6	452.4	427.8	414.5
22.5°	660.4	633.8	604.0	568.8	541.3	512.1	486.9	462.6	439.1	412.6	398.6
25°	662.4	638.1	606.5	566.8	533.2	500.2	469.8	446.2	417.7	393.0	372.6
27.5°	652.7	635.3	604.9	562.9	523.8	485.2	451.3	424.7	394.6	367.7	347.1
30°	640.9	630.8	601.2	559.1	516.3	474.8	437.6	407.3	377.4	350.3	329.1
32.5°	622.6	620.5	594.4	553.6	508.4	461.7	423.1	392.6	359.4	332.7	312.6
35°	586.7	596.4	580.0	541.3	493.5	443.0	401.3	366.4	332.0	306.5	287.7
37.5°	538.4	562.6	558.3	523.3	473.2	422.7	376.6	340.2	307.4	281.6	263.1
40°	505.2	536.0	540.5	509.4	459.1	407.0	358.1	321.9	289.9	266.4	247.7
42.5°	469.6	505.5	517.7	492.9	443.4	390.4	341.6	304.1	272.3	249.5	233.0
45°	409.8	457.4	479.5	465.3	417.5	363.2	313.0	274.9	246.1	224.6	211.9
47.5°	353.9	405.9	435.6	430.6	388.6	334.8	285.2	248.6	220.6	203.5	192.1
50°	314.4	367.8	403.7	405.4	367.8	314.6	264.7	230.3	204.6	188.6	179.2
52.5°	280.0	331.1	370.1	378.8	344.6	293.6	246.5	212.1	189.5	174.8	166.5
55°	235.1	278.3	321.6	337.5	310.1	261.5	217.9	187.8	166.5	156.4	149.1
57.5°	195.6	231.5	271.5	289.0	272.2	230.5	189.7	163.5	146.2	137.3	131.7
60°	174.6	203.0	238.6	259.5	244.9	207.9	172.2	147.2	133.0	125.2	119.9
62.5°	155.2	180.3	210.4	229.5	221.6	186.6	154.7	132.7	120.5	113.1	109.2
65°	128.0	147.8	171.2	188.8	183.5	157.0	130.8	112.0	102.3	96.4	93.4
67.5°	105.4	119.8	135.9	151.3	147.1	128.3	107.4	92.6	85.4	80.3	78.5
70°	91.1	102.1	116.5	128.9	125.4	110.0	93.4	80.8	74.5	70.3	68.5
72.5°	77.6	86.5	97.6	107.6	105.3	92.5	78.6	69.2	64.3	60.4	58.9
75°	58.6	65.5	72.1	78.8	78.2	68.3	60.2	52.9	49.0	46.0	45.4
77.5°	43.2	47.1	51.6	55.6	54.5	48.8	42.4	38.3	35.5	33.4	33.1
80°	33.0	35.2	38.5	41.3	39.9	37.5	32.4	29.3	27.4	25.3	24.5
82.5°	24.0	26.1	28.1	29.7	28.5	26.3	23.2	21.1	19.9	18.5	18.2
85°	12.6	13.7	14.6	15.0	14.6	13.2	11.8	11.0	9.9	9.3	9.1
87.5°	7.0	6.8	6.5	6.6	5.8	5.4	4.5	3.7	3.8	4.0	4.0
90°	10.5	9.4	8.2	6.9	5.4	3.7	2.2	0.6	2.2	3.7	5.4
92.5°	13.6	13.1	12.6	12.3	12.5	12.6	12.8	12.8	12.8	12.6	12.5
95°	22.9	21.9	20.9	22.7	27.5	32.1	36.8	41.5	36.8	32.1	27.5
97.5°	28.7	26.4	24.1	29.5	42.7	55.9	69.1	82.3	69.1	55.9	42.7
100°	31.6	29.2	26.8	35.2	54.7	74.1	93.5	112.9	93.5	74.1	54.7
102.5°	77.7	97.8	118.0	130.1	134.3	138.4	142.5	146.6	142.5	138.4	134.3
105°	116.3	155.0	193.7	210.9	206.7	202.4	198.1	193.9	198.1	202.4	206.7
107.5°	147.3	193.7	240.1	261.6	258.2	254.8	251.3	247.9	251.3	254.8	258.2
110°	193.6	234.5	275.4	294.4	291.5	288.6	285.5	282.6	285.5	288.6	291.5



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	301.8	311.9	322.0	325.7	323.2	320.5	317.9	315.2	317.9	320.5	323.2
115°	386.5	382.9	379.4	376.4	374.0	371.6	369.2	366.8	369.2	371.6	374.0
117.5°	431.1	428.6	426.1	423.6	420.9	418.2	415.5	412.9	415.5	418.2	420.9
120°	462.4	459.9	457.4	455.0	452.9	450.8	448.6	446.5	448.6	450.8	452.9
122.5°	492.1	489.4	486.5	484.0	481.8	479.6	477.3	475.1	477.3	479.6	481.8
125°	533.6	530.9	528.2	525.9	524.1	522.3	520.4	518.6	520.4	522.3	524.1
127.5°	572.2	570.2	568.2	566.1	564.1	562.1	560.1	558.0	560.1	562.1	564.1
130°	597.1	595.6	594.0	592.1	589.8	587.5	585.3	583.0	585.3	587.5	589.8
132.5°	621.1	619.6	618.0	616.3	614.3	612.4	610.5	608.5	610.5	612.4	614.3
135°	655.1	653.8	652.6	650.8	648.5	646.2	644.0	641.7	644.0	646.2	648.5
137.5°	686.0	684.6	683.1	681.6	680.0	678.4	676.8	675.3	676.8	678.4	680.0
140°	706.2	704.6	703.1	701.7	700.6	699.5	698.3	697.2	698.3	699.5	700.6
142.5°	724.6	722.8	721.0	719.6	718.6	717.6	716.6	715.6	716.6	717.6	718.6
145°	749.8	747.3	744.9	743.9	744.0	744.1	744.2	744.4	744.2	744.1	744.0
147.5°	773.0	770.7	768.3	767.4	767.9	768.5	769.0	769.5	769.0	768.5	767.9
150°	787.0	784.8	782.6	781.9	782.9	783.9	784.9	785.9	784.9	783.9	782.9
152.5°	800.0	797.9	795.8	795.2	796.3	797.5	798.5	799.6	798.5	797.5	796.3
155°	818.1	816.5	814.8	814.6	815.8	817.1	818.4	819.7	818.4	817.1	815.8
157.5°	833.5	832.3	831.1	831.1	832.1	833.2	834.3	835.4	834.3	833.2	832.1
160°	842.8	842.0	841.2	841.2	842.0	842.8	843.6	844.5	843.6	842.8	842.0
162.5°	850.7	850.0	849.3	849.3	850.2	851.0	851.9	852.7	851.9	851.0	850.2
165°	860.9	860.5	860.1	860.2	861.1	862.0	862.8	863.7	862.8	862.0	861.1
167.5°	869.0	868.6	868.2	868.4	869.3	870.1	871.0	871.8	871.0	870.1	869.3
170°	873.3	873.1	872.7	873.1	873.9	874.8	875.6	876.5	875.6	874.8	873.9
172.5°	876.4	876.1	875.8	876.1	876.9	877.8	878.6	879.5	878.6	877.8	876.9
175°	879.7	879.4	879.1	879.5	880.5	881.5	882.4	883.4	882.4	881.5	880.5
177.5°	880.8	880.7	880.6	880.9	881.7	882.5	883.3	884.1	883.3	882.5	881.7
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	520.1	519.2	515.8	514.0	511.0	508.3	506.5	507.3	507.9	507.7	507.1
5°	505.2	501.3	495.4	490.4	486.8	480.1	477.2	475.8	474.6	473.2	471.8
7.5°	487.4	481.3	473.0	465.7	459.0	450.6	445.9	443.1	440.1	436.9	434.1
10°	474.8	466.3	457.4	447.3	439.2	431.7	425.0	420.5	416.4	412.6	409.8
12.5°	461.5	451.7	440.7	426.9	417.9	407.2	406.2	398.3	392.0	389.6	386.3
15°	440.4	426.6	412.6	396.2	389.1	379.4	373.4	367.2	361.8	357.9	357.0
17.5°	416.3	398.5	384.6	372.8	361.2	351.2	345.6	340.8	336.3	331.2	330.5
20°	398.1	382.6	367.5	357.1	345.2	335.0	328.1	323.3	319.4	316.4	313.8
22.5°	380.7	363.8	349.9	338.7	326.9	318.7	313.3	308.5	305.3	302.0	299.5
25°	352.8	339.7	324.5	311.7	302.0	296.8	292.3	288.3	286.2	284.0	281.2
27.5°	328.5	313.9	299.7	289.8	281.2	276.6	273.4	270.6	268.8	267.4	265.8
30°	311.4	296.6	285.4	275.7	268.6	263.9	261.9	260.3	258.1	257.3	256.5
32.5°	294.8	281.5	272.0	263.5	256.8	253.7	251.9	250.4	248.7	247.9	246.2
35°	271.4	260.3	251.0	246.3	240.9	238.2	236.8	234.8	233.2	232.4	232.1
37.5°	249.4	239.8	233.6	227.7	225.3	223.7	221.8	220.4	219.9	219.8	219.5
40°	235.1	227.3	221.8	217.0	216.0	213.5	211.9	210.7	210.7	210.9	210.7
42.5°	222.2	215.1	210.3	206.1	204.9	203.5	201.8	201.8	202.1	202.8	202.1
45°	202.6	197.5	194.0	192.1	189.8	188.4	188.2	188.8	189.0	189.2	189.8
47.5°	184.5	181.1	178.0	175.8	174.8	174.6	174.3	175.4	176.4	176.7	177.6
50°	173.8	170.0	167.3	165.9	165.1	164.7	165.1	166.3	167.1	168.1	168.7
52.5°	161.8	159.1	157.3	156.1	155.9	156.1	156.1	157.6	158.8	159.3	159.5
55°	145.3	143.2	142.9	141.0	141.8	141.6	142.6	143.4	144.6	145.9	146.1
57.5°	128.7	127.1	126.0	126.2	126.4	127.3	128.1	129.6	130.8	132.2	132.2
60°	117.7	116.9	116.3	116.3	116.6	117.9	118.9	120.3	121.1	122.0	122.5
62.5°	107.6	106.8	106.2	106.6	107.6	108.3	109.5	110.3	111.1	111.9	112.2
65°	91.8	91.4	91.9	92.4	92.6	93.5	95.0	95.6	96.4	96.8	98.3
67.5°	77.1	77.2	77.1	77.7	78.9	79.1	80.4	81.9	82.0	82.8	83.7
70°	67.2	67.7	68.0	68.5	69.5	69.9	70.9	71.5	72.3	72.9	73.6
72.5°	58.1	58.2	58.7	58.6	59.5	60.3	61.2	61.8	62.6	63.4	63.9
75°	44.8	44.8	45.2	45.4	46.4	47.4	47.2	47.6	48.4	49.2	49.7
77.5°	32.7	32.3	32.7	32.9	33.3	34.1	34.2	34.8	35.8	35.5	35.9
80°	24.9	24.3	24.9	25.1	25.1	26.1	26.1	26.6	27.1	26.6	27.1
82.5°	17.7	17.5	17.9	18.0	18.3	18.4	18.6	18.7	19.4	19.1	19.4
85°	8.9	8.7	8.9	8.7	8.9	9.1	9.1	8.9	8.9	9.3	8.7
87.5°	4.1	4.3	4.3	4.5	4.6	4.6	4.6	4.8	4.9	4.7	4.8
90°	6.9	8.2	9.4	10.5	11.6	12.8	13.5	14.2	14.9	15.6	16.1
92.5°	12.3	12.6	13.1	13.6	14.3	14.8	15.2	15.5	15.9	16.2	16.6
95°	22.7	20.9	21.9	22.9	23.9	24.9	25.6	26.3	27.0	27.7	28.0
97.5°	29.5	24.1	26.4	28.7	31.0	33.3	33.9	34.4	35.0	35.6	35.9
100°	35.2	26.8	29.2	31.6	34.0	36.4	37.5	38.6	39.8	40.9	41.6
102.5°	130.1	118.0	97.8	77.7	57.5	37.4	38.9	40.3	41.8	43.2	44.2
105°	210.9	193.7	155.0	116.3	77.6	38.9	40.5	42.0	43.6	45.1	46.2
107.5°	261.6	240.1	193.7	147.3	100.9	54.5	52.9	51.3	49.7	48.2	47.6
110°	294.4	275.4	234.5	193.6	152.6	111.6	97.5	83.3	69.1	54.9	48.2



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	325.7	322.0	311.9	301.8	291.7	281.5	229.9	178.2	126.4	74.7	49.0
115°	376.4	379.4	382.9	386.5	390.0	393.6	328.0	262.3	196.7	131.1	93.1
117.5°	423.6	426.1	428.6	431.1	433.5	436.0	420.1	404.2	388.3	372.4	347.7
120°	455.0	457.4	459.9	462.4	465.0	467.5	469.2	471.0	472.7	474.4	465.7
122.5°	484.0	486.5	489.4	492.1	494.9	497.7	498.6	499.7	500.7	501.8	500.4
125°	525.9	528.2	530.9	533.6	536.3	539.0	540.0	541.0	542.0	543.0	543.7
127.5°	566.1	568.2	570.2	572.2	574.3	576.2	577.7	579.2	580.6	582.0	582.8
130°	592.1	594.0	595.6	597.1	598.7	600.2	601.8	603.3	604.9	606.5	607.2
132.5°	616.3	618.0	619.6	621.1	622.7	624.2	625.5	626.9	628.2	629.5	630.2
135°	650.8	652.6	653.8	655.1	656.4	657.6	659.1	660.5	661.9	663.3	663.9
137.5°	681.6	683.1	684.6	686.0	687.4	688.9	690.3	691.7	693.0	694.5	694.9
140°	701.7	703.1	704.6	706.2	707.8	709.4	710.6	711.9	713.1	714.4	714.7
142.5°	719.6	721.0	722.8	724.6	726.4	728.2	729.3	730.5	731.6	732.8	733.1
145°	743.9	744.9	747.3	749.8	752.2	754.6	755.6	756.6	757.6	758.6	758.7
147.5°	767.4	768.3	770.7	773.0	775.4	777.8	778.6	779.3	780.1	780.8	780.9
150°	781.9	782.6	784.8	787.0	789.3	791.6	792.5	793.3	794.2	795.0	795.0
152.5°	795.2	795.8	797.9	800.0	802.2	804.3	805.2	806.0	806.9	807.8	807.7
155°	814.6	814.8	816.5	818.1	819.8	821.5	822.4	823.3	824.1	825.0	824.8
157.5°	831.1	831.1	832.3	833.5	834.6	835.9	836.9	837.8	838.7	839.7	839.6
160°	841.2	841.2	842.0	842.8	843.6	844.5	845.4	846.2	847.1	847.9	847.8
162.5°	849.3	849.3	850.0	850.7	851.5	852.2	853.2	854.1	855.1	856.0	856.0
165°	860.2	860.1	860.5	860.9	861.3	861.7	862.7	863.7	864.8	865.8	865.8
167.5°	868.4	868.2	868.6	869.0	869.4	869.8	870.8	871.8	872.8	873.8	873.6
170°	873.1	872.7	873.1	873.3	873.6	873.9	874.9	875.8	876.8	877.9	877.7
172.5°	876.1	875.8	876.1	876.4	876.6	876.9	878.0	879.0	879.9	880.9	880.7
175°	879.5	879.1	879.4	879.7	879.9	880.3	881.3	882.3	883.2	884.2	884.0
177.5°	880.9	880.6	880.7	880.8	880.9	881.0	881.8	882.6	883.4	884.2	884.1
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	505.5	505.2	505.2	503.7	505.2	505.2	505.5	507.1	507.7	507.9	507.3
5°	469.0	468.3	467.3	468.3	467.3	468.3	469.0	471.8	473.2	474.6	475.8
7.5°	432.7	430.3	430.0	427.6	430.0	430.3	432.7	434.1	436.9	440.1	443.1
10°	406.4	404.7	404.5	400.6	404.5	404.7	406.4	409.8	412.6	416.4	420.5
12.5°	386.3	382.4	383.2	380.9	383.2	382.4	386.3	386.3	389.6	392.0	398.3
15°	351.4	351.4	350.6	347.2	350.6	351.4	351.4	357.0	357.9	361.8	367.2
17.5°	326.5	326.0	324.1	325.1	324.1	326.0	326.5	330.5	331.2	336.3	340.8
20°	311.6	310.3	307.9	307.9	307.9	310.3	311.6	313.8	316.4	319.4	323.3
22.5°	297.5	297.4	294.8	295.6	294.8	297.4	297.5	299.5	302.0	305.3	308.5
25°	281.0	279.4	278.1	278.7	278.1	279.4	281.0	281.2	284.0	286.2	288.3
27.5°	265.3	264.4	264.3	262.7	264.3	264.4	265.3	265.8	267.4	268.8	270.6
30°	256.3	254.2	254.6	253.6	254.6	254.2	256.3	256.5	257.3	258.1	260.3
32.5°	245.8	245.1	244.8	243.9	244.8	245.1	245.8	246.2	247.9	248.7	250.4
35°	231.8	231.9	231.0	231.3	231.0	231.9	231.8	232.1	232.4	233.2	234.8
37.5°	219.4	220.0	219.5	219.6	219.5	220.0	219.4	219.5	219.8	219.9	220.4
40°	211.2	211.2	211.2	211.9	211.2	211.2	211.2	210.7	210.9	210.7	210.7
42.5°	203.5	203.1	202.9	202.8	202.9	203.1	203.5	202.1	202.8	202.1	201.8
45°	190.2	190.8	191.0	190.0	191.0	190.8	190.2	189.8	189.2	189.0	188.8
47.5°	178.2	178.3	178.2	179.1	178.2	178.3	178.2	177.6	176.7	176.4	175.4
50°	169.8	169.3	169.8	169.3	169.8	169.3	169.8	168.7	168.1	167.1	166.3
52.5°	160.9	161.0	160.7	160.6	160.7	161.0	160.9	159.5	159.3	158.8	157.6
55°	146.9	147.2	147.0	147.0	147.0	147.2	146.9	146.1	145.9	144.6	143.4
57.5°	132.4	132.8	133.0	132.2	133.0	132.8	132.4	132.2	132.2	130.8	129.6
60°	122.3	123.3	123.1	122.8	123.1	123.3	122.3	122.5	122.0	121.1	120.3
62.5°	113.1	113.5	113.4	113.3	113.4	113.5	113.1	112.2	111.9	111.1	110.3
65°	98.9	99.2	98.6	99.2	98.6	99.2	98.9	98.3	96.8	96.4	95.6
67.5°	83.5	83.6	84.1	84.4	84.1	83.6	83.5	83.7	82.8	82.0	81.9
70°	73.9	73.7	74.4	75.0	74.4	73.7	73.9	73.6	72.9	72.3	71.5
72.5°	63.8	64.3	64.1	64.6	64.1	64.3	63.8	63.9	63.4	62.6	61.8
75°	49.2	49.8	49.7	50.2	49.7	49.8	49.2	49.7	49.2	48.4	47.6
77.5°	35.6	35.7	35.6	35.9	35.6	35.7	35.6	35.9	35.5	35.8	34.8
80°	27.1	26.8	26.3	27.1	26.3	26.8	27.1	27.1	26.6	27.1	26.6
82.5°	18.9	19.1	18.7	18.7	18.7	19.1	18.9	19.4	19.1	19.4	18.7
85°	8.7	8.5	8.1	8.1	8.1	8.5	8.7	8.7	9.3	8.9	8.9
87.5°	4.9	4.8	4.8	4.7	4.8	4.8	4.9	4.8	4.7	4.9	4.8
90°	16.4	16.7	16.9	17.2	16.9	16.7	16.4	16.1	15.6	14.9	14.2
92.5°	16.7	16.9	17.0	17.2	17.0	16.9	16.7	16.6	16.2	15.9	15.5
95°	27.8	27.7	27.6	27.5	27.6	27.7	27.8	28.0	27.7	27.0	26.3
97.5°	36.1	36.3	36.5	36.6	36.5	36.3	36.1	35.9	35.6	35.0	34.4
100°	41.9	42.2	42.4	42.7	42.4	42.2	41.9	41.6	40.9	39.8	38.6
102.5°	44.6	45.0	45.4	45.8	45.4	45.0	44.6	44.2	43.2	41.8	40.3
105°	46.8	47.3	47.9	48.5	47.9	47.3	46.8	46.2	45.1	43.6	42.0
107.5°	48.2	48.8	49.3	49.8	49.3	48.8	48.2	47.6	48.2	49.7	51.3
110°	48.7	49.2	49.8	50.4	49.8	49.2	48.7	48.2	54.9	69.1	83.3



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	49.6	50.0	50.5	50.9	50.5	50.0	49.6	49.0	74.7	126.4	178.2
115°	82.9	72.7	62.5	52.3	62.5	72.7	82.9	93.1	131.1	196.7	262.3
117.5°	314.1	280.6	247.1	213.6	247.1	280.6	314.1	347.7	372.4	388.3	404.2
120°	446.5	427.4	408.2	389.1	408.2	427.4	446.5	465.7	474.4	472.7	471.0
122.5°	496.7	492.9	489.3	485.5	489.3	492.9	496.7	500.4	501.8	500.7	499.7
125°	544.1	544.6	544.9	545.4	544.9	544.6	544.1	543.7	543.0	542.0	541.0
127.5°	582.9	583.0	583.1	583.2	583.1	583.0	582.9	582.8	582.0	580.6	579.2
130°	607.1	606.9	606.7	606.6	606.7	606.9	607.1	607.2	606.5	604.9	603.3
132.5°	630.0	629.9	629.7	629.5	629.7	629.9	630.0	630.2	629.5	628.2	626.9
135°	663.6	663.3	663.0	662.7	663.0	663.3	663.6	663.9	663.3	661.9	660.5
137.5°	694.5	693.9	693.5	692.9	693.5	693.9	694.5	694.9	694.5	693.0	691.7
140°	714.0	713.3	712.6	711.9	712.6	713.3	714.0	714.7	714.4	713.1	711.9
142.5°	732.4	731.6	730.9	730.2	730.9	731.6	732.4	733.1	732.8	731.6	730.5
145°	758.0	757.3	756.6	755.9	756.6	757.3	758.0	758.7	758.6	757.6	756.6
147.5°	780.2	779.6	779.1	778.5	779.1	779.6	780.2	780.9	780.8	780.1	779.3
150°	794.3	793.6	792.9	792.2	792.9	793.6	794.3	795.0	795.0	794.2	793.3
152.5°	806.8	805.8	804.9	804.0	804.9	805.8	806.8	807.7	807.8	806.9	806.0
155°	823.7	822.6	821.4	820.3	821.4	822.6	823.7	824.8	825.0	824.1	823.3
157.5°	838.6	837.4	836.3	835.3	836.3	837.4	838.6	839.6	839.7	838.7	837.8
160°	846.9	845.9	844.9	843.9	844.9	845.9	846.9	847.8	847.9	847.1	846.2
162.5°	854.7	853.5	852.3	851.0	852.3	853.5	854.7	856.0	856.0	855.1	854.1
165°	864.8	863.7	862.7	861.7	862.7	863.7	864.8	865.8	865.8	864.8	863.7
167.5°	872.4	871.1	869.8	868.5	869.8	871.1	872.4	873.6	873.8	872.8	871.8
170°	876.5	875.1	873.9	872.6	873.9	875.1	876.5	877.7	877.9	876.8	875.8
172.5°	879.5	878.2	876.9	875.7	876.9	878.2	879.5	880.7	880.9	879.9	879.0
175°	882.6	881.2	879.8	878.3	879.8	881.2	882.6	884.0	884.2	883.2	882.3
177.5°	883.1	882.1	881.0	880.0	881.0	882.1	883.1	884.1	884.2	883.4	882.6
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	506.5	508.3	511.0	514.0	515.8	519.2	520.1	521.7	523.2	526.6	530.1
5°	477.2	480.1	486.8	490.4	495.4	501.3	505.2	509.3	513.7	521.4	528.5
7.5°	445.9	450.6	459.0	465.7	473.0	481.3	487.4	495.4	502.1	513.0	523.3
10°	425.0	431.7	439.2	447.3	457.4	466.3	474.8	484.9	493.0	506.0	518.2
12.5°	406.2	407.2	417.9	426.9	440.7	451.7	461.5	474.6	482.5	497.9	510.7
15°	373.4	379.4	389.1	396.2	412.6	426.6	440.4	454.0	463.1	482.1	498.9
17.5°	345.6	351.2	361.2	372.8	384.6	398.5	416.3	430.7	443.1	464.8	484.7
20°	328.1	335.0	345.2	357.1	367.5	382.6	398.1	414.5	427.8	452.4	475.6
22.5°	313.3	318.7	326.9	338.7	349.9	363.8	380.7	398.6	412.6	439.1	462.6
25°	292.3	296.8	302.0	311.7	324.5	339.7	352.8	372.6	393.0	417.7	446.2
27.5°	273.4	276.6	281.2	289.8	299.7	313.9	328.5	347.1	367.7	394.6	424.7
30°	261.9	263.9	268.6	275.7	285.4	296.6	311.4	329.1	350.3	377.4	407.3
32.5°	251.9	253.7	256.8	263.5	272.0	281.5	294.8	312.6	332.7	359.4	392.6
35°	236.8	238.2	240.9	246.3	251.0	260.3	271.4	287.7	306.5	332.0	366.4
37.5°	221.8	223.7	225.3	227.7	233.6	239.8	249.4	263.1	281.6	307.4	340.2
40°	211.9	213.5	216.0	217.0	221.8	227.3	235.1	247.7	266.4	289.9	321.9
42.5°	201.8	203.5	204.9	206.1	210.3	215.1	222.2	233.0	249.5	272.3	304.1
45°	188.2	188.4	189.8	192.1	194.0	197.5	202.6	211.9	224.6	246.1	274.9
47.5°	174.3	174.6	174.8	175.8	178.0	181.1	184.5	192.1	203.5	220.6	248.6
50°	165.1	164.7	165.1	165.9	167.3	170.0	173.8	179.2	188.6	204.6	230.3
52.5°	156.1	156.1	155.9	156.1	157.3	159.1	161.8	166.5	174.8	189.5	212.1
55°	142.6	141.6	141.8	141.0	142.9	143.2	145.3	149.1	156.4	166.5	187.8
57.5°	128.1	127.3	126.4	126.2	126.0	127.1	128.7	131.7	137.3	146.2	163.5
60°	118.9	117.9	116.6	116.3	116.3	116.9	117.7	119.9	125.2	133.0	147.2
62.5°	109.5	108.3	107.6	106.6	106.2	106.8	107.6	109.2	113.1	120.5	132.7
65°	95.0	93.5	92.6	92.4	91.9	91.4	91.8	93.4	96.4	102.3	112.0
67.5°	80.4	79.1	78.9	77.7	77.1	77.2	77.1	78.5	80.3	85.4	92.6
70°	70.9	69.9	69.5	68.5	68.0	67.7	67.2	68.5	70.3	74.5	80.8
72.5°	61.2	60.3	59.5	58.6	58.7	58.2	58.1	58.9	60.4	64.3	69.2
75°	47.2	47.4	46.4	45.4	45.2	44.8	44.8	45.4	46.0	49.0	52.9
77.5°	34.2	34.1	33.3	32.9	32.7	32.3	32.7	33.1	33.4	35.5	38.3
80°	26.1	26.1	25.1	25.1	24.9	24.3	24.9	24.5	25.3	27.4	29.3
82.5°	18.6	18.4	18.3	18.0	17.9	17.5	17.7	18.2	18.5	19.9	21.1
85°	9.1	9.1	8.9	8.7	8.9	8.7	8.9	9.1	9.3	9.9	11.0
87.5°	4.6	4.6	4.6	4.5	4.3	4.3	4.1	4.0	4.0	3.8	3.7
90°	13.5	12.8	11.6	10.5	9.4	8.2	6.9	5.4	3.7	2.2	0.6
92.5°	15.2	14.8	14.3	13.6	13.1	12.6	12.3	12.5	12.6	12.8	12.8
95°	25.6	24.9	23.9	22.9	21.9	20.9	22.7	27.5	32.1	36.8	41.5
97.5°	33.9	33.3	31.0	28.7	26.4	24.1	29.5	42.7	55.9	69.1	82.3
100°	37.5	36.4	34.0	31.6	29.2	26.8	35.2	54.7	74.1	93.5	112.9
102.5°	38.9	37.4	57.5	77.7	97.8	118.0	130.1	134.3	138.4	142.5	146.6
105°	40.5	38.9	77.6	116.3	155.0	193.7	210.9	206.7	202.4	198.1	193.9
107.5°	52.9	54.5	100.9	147.3	193.7	240.1	261.6	258.2	254.8	251.3	247.9
110°	97.5	111.6	152.6	193.6	234.5	275.4	294.4	291.5	288.6	285.5	282.6



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	229.9	281.5	291.7	301.8	311.9	322.0	325.7	323.2	320.5	317.9	315.2
115°	328.0	393.6	390.0	386.5	382.9	379.4	376.4	374.0	371.6	369.2	366.8
117.5°	420.1	436.0	433.5	431.1	428.6	426.1	423.6	420.9	418.2	415.5	412.9
120°	469.2	467.5	465.0	462.4	459.9	457.4	455.0	452.9	450.8	448.6	446.5
122.5°	498.6	497.7	494.9	492.1	489.4	486.5	484.0	481.8	479.6	477.3	475.1
125°	540.0	539.0	536.3	533.6	530.9	528.2	525.9	524.1	522.3	520.4	518.6
127.5°	577.7	576.2	574.3	572.2	570.2	568.2	566.1	564.1	562.1	560.1	558.0
130°	601.8	600.2	598.7	597.1	595.6	594.0	592.1	589.8	587.5	585.3	583.0
132.5°	625.5	624.2	622.7	621.1	619.6	618.0	616.3	614.3	612.4	610.5	608.5
135°	659.1	657.6	656.4	655.1	653.8	652.6	650.8	648.5	646.2	644.0	641.7
137.5°	690.3	688.9	687.4	686.0	684.6	683.1	681.6	680.0	678.4	676.8	675.3
140°	710.6	709.4	707.8	706.2	704.6	703.1	701.7	700.6	699.5	698.3	697.2
142.5°	729.3	728.2	726.4	724.6	722.8	721.0	719.6	718.6	717.6	716.6	715.6
145°	755.6	754.6	752.2	749.8	747.3	744.9	743.9	744.0	744.1	744.2	744.4
147.5°	778.6	777.8	775.4	773.0	770.7	768.3	767.4	767.9	768.5	769.0	769.5
150°	792.5	791.6	789.3	787.0	784.8	782.6	781.9	782.9	783.9	784.9	785.9
152.5°	805.2	804.3	802.2	800.0	797.9	795.8	795.2	796.3	797.5	798.5	799.6
155°	822.4	821.5	819.8	818.1	816.5	814.8	814.6	815.8	817.1	818.4	819.7
157.5°	836.9	835.9	834.6	833.5	832.3	831.1	831.1	832.1	833.2	834.3	835.4
160°	845.4	844.5	843.6	842.8	842.0	841.2	841.2	842.0	842.8	843.6	844.5
162.5°	853.2	852.2	851.5	850.7	850.0	849.3	849.3	850.2	851.0	851.9	852.7
165°	862.7	861.7	861.3	860.9	860.5	860.1	860.2	861.1	862.0	862.8	863.7
167.5°	870.8	869.8	869.4	869.0	868.6	868.2	868.4	869.3	870.1	871.0	871.8
170°	874.9	873.9	873.6	873.3	873.1	872.7	873.1	873.9	874.8	875.6	876.5
172.5°	878.0	876.9	876.6	876.4	876.1	875.8	876.1	876.9	877.8	878.6	879.5
175°	881.3	880.3	879.9	879.7	879.4	879.1	879.5	880.5	881.5	882.4	883.4
177.5°	881.8	881.0	880.9	880.8	880.7	880.6	880.9	881.7	882.5	883.3	884.1
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331258-940
 CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	529.9	530.7	533.2	535.8	538.8	539.6	540.8	539.8	539.4	542.4	544.7
5°	531.4	534.9	542.1	548.6	554.0	557.9	562.0	563.6	566.6	570.8	576.1
7.5°	529.6	536.7	547.9	557.3	567.6	575.0	580.8	585.8	591.7	599.8	608.6
10°	527.7	537.2	550.8	562.3	574.9	584.4	592.3	600.0	608.9	620.1	631.6
12.5°	524.1	535.4	552.4	566.1	582.2	591.6	602.2	618.8	628.4	643.9	660.1
15°	516.9	529.5	553.2	570.0	588.3	606.1	625.7	641.5	657.3	666.5	689.3
17.5°	506.3	524.7	551.0	570.6	593.8	621.8	643.9	661.8	680.0	694.8	706.3
20°	497.7	517.7	547.8	571.2	598.8	628.9	654.2	672.5	688.3	700.7	707.8
22.5°	486.9	512.1	541.3	568.8	604.0	633.8	660.4	674.8	688.0	694.0	696.8
25°	469.8	500.2	533.2	566.8	606.5	638.1	662.4	671.1	674.9	669.1	659.3
27.5°	451.3	485.2	523.8	562.9	604.9	635.3	652.7	651.4	644.9	625.8	610.6
30°	437.6	474.8	516.3	559.1	601.2	630.8	640.9	630.8	616.0	594.8	573.0
32.5°	423.1	461.7	508.4	553.6	594.4	620.5	622.6	605.2	582.3	558.1	531.1
35°	401.3	443.0	493.5	541.3	580.0	596.4	586.7	555.8	528.7	495.7	458.8
37.5°	376.6	422.7	473.2	523.3	558.3	562.6	538.4	506.0	467.7	428.9	385.5
40°	358.1	407.0	459.1	509.4	540.5	536.0	505.2	469.6	424.0	376.6	336.3
42.5°	341.6	390.4	443.4	492.9	517.7	505.5	469.6	425.8	376.8	332.2	295.2
45°	313.0	363.2	417.5	465.3	479.5	457.4	409.8	361.1	313.0	275.7	246.6
47.5°	285.2	334.8	388.6	430.6	435.6	405.9	353.9	303.9	262.4	232.1	211.5
50°	264.7	314.6	367.8	405.4	403.7	367.8	314.4	266.8	232.1	207.6	193.9
52.5°	246.5	293.6	344.6	378.8	370.1	331.1	280.0	237.7	209.3	190.1	177.6
55°	217.9	261.5	310.1	337.5	321.6	278.3	235.1	201.2	180.0	165.7	156.0
57.5°	189.7	230.5	272.2	289.0	271.5	231.5	195.6	170.9	155.0	144.4	138.0
60°	172.2	207.9	244.9	259.5	238.6	203.0	174.6	152.6	139.7	131.1	125.4
62.5°	154.7	186.6	221.6	229.5	210.4	180.3	155.2	136.8	126.4	118.6	113.2
65°	130.8	157.0	183.5	188.8	171.2	147.8	128.0	116.1	106.7	101.1	96.8
67.5°	107.4	128.3	147.1	151.3	135.9	119.8	105.4	95.0	88.7	84.0	80.3
70°	93.4	110.0	125.4	128.9	116.5	102.1	91.1	82.8	77.1	73.1	69.6
72.5°	78.6	92.5	105.3	107.6	97.6	86.5	77.6	71.0	66.0	63.4	60.1
75°	60.2	68.3	78.2	78.8	72.1	65.5	58.6	54.3	51.6	48.4	46.8
77.5°	42.4	48.8	54.5	55.6	51.6	47.1	43.2	39.9	37.6	36.1	34.6
80°	32.4	37.5	39.9	41.3	38.5	35.2	33.0	30.8	29.3	28.4	27.4
82.5°	23.2	26.3	28.5	29.7	28.1	26.1	24.0	22.6	21.6	20.8	20.4
85°	11.8	13.2	14.6	15.0	14.6	13.7	12.6	12.6	11.9	11.8	11.8
87.5°	4.5	5.4	5.8	6.6	6.5	6.8	7.0	7.0	7.0	7.0	7.0
90°	2.2	3.7	5.4	6.9	8.2	9.4	10.5	11.6	12.8	13.5	14.2
92.5°	12.8	12.6	12.5	12.3	12.6	13.1	13.6	14.3	14.8	15.2	15.5
95°	36.8	32.1	27.5	22.7	20.9	21.9	22.9	23.9	24.9	25.6	26.3
97.5°	69.1	55.9	42.7	29.5	24.1	26.4	28.7	31.0	33.3	33.9	34.4
100°	93.5	74.1	54.7	35.2	26.8	29.2	31.6	34.0	36.4	37.5	38.6
102.5°	142.5	138.4	134.3	130.1	118.0	97.8	77.7	57.5	37.4	38.9	40.3
105°	198.1	202.4	206.7	210.9	193.7	155.0	116.3	77.6	38.9	40.5	42.0
107.5°	251.3	254.8	258.2	261.6	240.1	193.7	147.3	100.9	54.5	52.9	51.3
110°	285.5	288.6	291.5	294.4	275.4	234.5	193.6	152.6	111.6	97.5	83.3



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	317.9	320.5	323.2	325.7	322.0	311.9	301.8	291.7	281.5	229.9	178.2
115°	369.2	371.6	374.0	376.4	379.4	382.9	386.5	390.0	393.6	328.0	262.3
117.5°	415.5	418.2	420.9	423.6	426.1	428.6	431.1	433.5	436.0	420.1	404.2
120°	448.6	450.8	452.9	455.0	457.4	459.9	462.4	465.0	467.5	469.2	471.0
122.5°	477.3	479.6	481.8	484.0	486.5	489.4	492.1	494.9	497.7	498.6	499.7
125°	520.4	522.3	524.1	525.9	528.2	530.9	533.6	536.3	539.0	540.0	541.0
127.5°	560.1	562.1	564.1	566.1	568.2	570.2	572.2	574.3	576.2	577.7	579.2
130°	585.3	587.5	589.8	592.1	594.0	595.6	597.1	598.7	600.2	601.8	603.3
132.5°	610.5	612.4	614.3	616.3	618.0	619.6	621.1	622.7	624.2	625.5	626.9
135°	644.0	646.2	648.5	650.8	652.6	653.8	655.1	656.4	657.6	659.1	660.5
137.5°	676.8	678.4	680.0	681.6	683.1	684.6	686.0	687.4	688.9	690.3	691.7
140°	698.3	699.5	700.6	701.7	703.1	704.6	706.2	707.8	709.4	710.6	711.9
142.5°	716.6	717.6	718.6	719.6	721.0	722.8	724.6	726.4	728.2	729.3	730.5
145°	744.2	744.1	744.0	743.9	744.9	747.3	749.8	752.2	754.6	755.6	756.6
147.5°	769.0	768.5	767.9	767.4	768.3	770.7	773.0	775.4	777.8	778.6	779.3
150°	784.9	783.9	782.9	781.9	782.6	784.8	787.0	789.3	791.6	792.5	793.3
152.5°	798.5	797.5	796.3	795.2	795.8	797.9	800.0	802.2	804.3	805.2	806.0
155°	818.4	817.1	815.8	814.6	814.8	816.5	818.1	819.8	821.5	822.4	823.3
157.5°	834.3	833.2	832.1	831.1	831.1	832.3	833.5	834.6	835.9	836.9	837.8
160°	843.6	842.8	842.0	841.2	841.2	842.0	842.8	843.6	844.5	845.4	846.2
162.5°	851.9	851.0	850.2	849.3	849.3	850.0	850.7	851.5	852.2	853.2	854.1
165°	862.8	862.0	861.1	860.2	860.1	860.5	860.9	861.3	861.7	862.7	863.7
167.5°	871.0	870.1	869.3	868.4	868.2	868.6	869.0	869.4	869.8	870.8	871.8
170°	875.6	874.8	873.9	873.1	872.7	873.1	873.3	873.6	873.9	874.9	875.8
172.5°	878.6	877.8	876.9	876.1	875.8	876.1	876.4	876.6	876.9	878.0	879.0
175°	882.4	881.5	880.5	879.5	879.1	879.4	879.7	879.9	880.3	881.3	882.3
177.5°	883.3	882.5	881.7	880.9	880.6	880.7	880.8	880.9	881.0	881.8	882.6
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	546.7	548.9	548.9	549.3	551.9	551.5	551.3
5°	581.8	585.2	585.6	589.2	591.7	590.8	588.6
7.5°	614.8	621.3	626.2	628.8	632.0	634.0	633.1
10°	641.1	650.4	656.1	660.0	664.6	668.1	666.8
12.5°	664.9	676.0	683.9	690.5	691.0	695.4	692.4
15°	702.1	713.8	715.1	719.9	723.8	723.4	723.5
17.5°	714.3	718.1	718.9	719.0	719.1	717.6	714.5
20°	710.0	708.6	705.2	702.5	697.9	697.2	693.2
22.5°	689.2	684.7	676.1	670.4	663.2	661.3	660.1
25°	648.5	638.5	624.7	611.5	607.9	600.8	602.8
27.5°	592.4	576.9	562.0	551.3	541.6	531.0	534.0
30°	553.0	535.6	514.5	498.3	487.9	477.9	476.0
32.5°	506.0	480.5	457.0	442.7	426.9	420.4	413.5
35°	425.0	400.0	376.7	356.7	345.2	336.3	328.1
37.5°	352.1	323.4	304.6	288.4	280.0	274.9	276.3
40°	306.9	281.8	268.0	255.7	247.9	244.3	245.1
42.5°	270.3	251.5	240.1	231.7	226.2	224.2	223.7
45°	228.7	218.2	208.8	204.0	201.3	199.1	197.7
47.5°	200.4	191.7	186.5	183.6	181.3	179.1	179.0
50°	183.3	177.6	174.0	170.9	169.2	167.6	169.0
52.5°	170.3	165.1	161.5	158.8	158.1	156.7	156.6
55°	151.1	147.0	144.5	142.0	140.8	140.0	138.9
57.5°	133.6	129.7	127.3	125.8	123.5	122.7	122.3
60°	121.1	118.1	115.7	113.6	112.6	111.0	111.0
62.5°	109.6	106.6	104.3	102.8	101.1	100.5	100.7
65°	93.0	90.5	88.3	86.7	86.3	85.1	85.5
67.5°	77.7	76.1	73.7	72.8	72.1	71.4	70.9
70°	67.4	65.8	64.6	63.4	62.8	62.8	62.8
72.5°	58.9	56.9	56.2	54.7	55.0	54.4	53.7
75°	45.6	44.3	43.8	43.2	42.2	42.2	42.2
77.5°	33.5	33.2	32.5	31.8	31.6	31.4	31.5
80°	25.9	25.7	25.3	25.3	24.9	24.7	24.3
82.5°	20.0	19.4	19.2	19.0	18.9	18.9	18.8
85°	11.3	11.0	11.0	11.1	10.7	10.7	11.0
87.5°	7.3	7.5	7.4	7.5	7.7	7.6	7.7
90°	14.9	15.6	16.1	16.4	16.7	16.9	17.2
92.5°	15.9	16.2	16.6	16.7	16.9	17.0	17.2
95°	27.0	27.7	28.0	27.8	27.7	27.6	27.5
97.5°	35.0	35.6	35.9	36.1	36.3	36.5	36.6
100°	39.8	40.9	41.6	41.9	42.2	42.4	42.7
102.5°	41.8	43.2	44.2	44.6	45.0	45.4	45.8
105°	43.6	45.1	46.2	46.8	47.3	47.9	48.5
107.5°	49.7	48.2	47.6	48.2	48.8	49.3	49.8
110°	69.1	54.9	48.2	48.7	49.2	49.8	50.4



TEST NUMBER: P331258-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	126.4	74.7	49.0	49.6	50.0	50.5	50.9
115°	196.7	131.1	93.1	82.9	72.7	62.5	52.3
117.5°	388.3	372.4	347.7	314.1	280.6	247.1	213.6
120°	472.7	474.4	465.7	446.5	427.4	408.2	389.1
122.5°	500.7	501.8	500.4	496.7	492.9	489.3	485.5
125°	542.0	543.0	543.7	544.1	544.6	544.9	545.4
127.5°	580.6	582.0	582.8	582.9	583.0	583.1	583.2
130°	604.9	606.5	607.2	607.1	606.9	606.7	606.6
132.5°	628.2	629.5	630.2	630.0	629.9	629.7	629.5
135°	661.9	663.3	663.9	663.6	663.3	663.0	662.7
137.5°	693.0	694.5	694.9	694.5	693.9	693.5	692.9
140°	713.1	714.4	714.7	714.0	713.3	712.6	711.9
142.5°	731.6	732.8	733.1	732.4	731.6	730.9	730.2
145°	757.6	758.6	758.7	758.0	757.3	756.6	755.9
147.5°	780.1	780.8	780.9	780.2	779.6	779.1	778.5
150°	794.2	795.0	795.0	794.3	793.6	792.9	792.2
152.5°	806.9	807.8	807.7	806.8	805.8	804.9	804.0
155°	824.1	825.0	824.8	823.7	822.6	821.4	820.3
157.5°	838.7	839.7	839.6	838.6	837.4	836.3	835.3
160°	847.1	847.9	847.8	846.9	845.9	844.9	843.9
162.5°	855.1	856.0	856.0	854.7	853.5	852.3	851.0
165°	864.8	865.8	865.8	864.8	863.7	862.7	861.7
167.5°	872.8	873.8	873.6	872.4	871.1	869.8	868.5
170°	876.8	877.9	877.7	876.5	875.1	873.9	872.6
172.5°	879.9	880.9	880.7	879.5	878.2	876.9	875.7
175°	883.2	884.2	884.0	882.6	881.2	879.8	878.3
177.5°	883.4	884.2	884.1	883.1	882.1	881.0	880.0
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5

(END OF REPORT)