

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332655-930

Luminaire Tested: **SA4XXDIP-C1020D1035U930-4F0-1E-UDD-D**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332655-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D1035U930-4F0-1E-UDD-D
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6800.6 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.08')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332655-930
CATALOG NUMBER: SA4XXDIP-C1020D1035U930-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P332655-930

CATALOG NUMBER: SA4XXDIP-C1020D1035U930-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47				47
1	96	91	87	83	88	84	80	77	70	67	65	57	55	54	45	44	43	37				37
2	87	79	73	67	80	73	67	62	61	57	53	50	47	44	39	37	35	31				31
3	79	69	62	56	72	64	57	52	53	48	44	44	40	37	35	32	30	25				25
4	72	61	53	47	66	56	49	43	47	42	37	39	34	31	31	28	25	21				21
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	28	24	22	18				18
6	61	49	40	34	56	45	37	32	38	32	28	31	27	23	25	22	19	16				16
7	56	44	36	30	51	40	33	28	34	28	24	28	24	20	23	19	17	14				14
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	17	15	13				13
9	48	36	28	23	44	33	27	22	28	23	19	24	19	16	19	16	14	11				11
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	15	12	10				10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8127	8127	8127
5°	8151	7942	7965
10°	8102	7812	7807
15°	8029	7662	7620
20°	7920	7496	7438
25°	7797	7310	7239
30°	7663	7125	7034
35°	7511	6935	6855
40°	7390	6755	6667
45°	7210	6588	6507
50°	7059	6397	6337
55°	6902	6217	6138
60°	6657	5986	5956
65°	6389	5740	5734
70°	6066	5458	5474
75°	5612	5146	5239
80°	5110	4847	5007
85°	4474	4583	4872



TEST NUMBER: P332655-930

CATALOG NUMBER: SA4XXDIP-C1020D1035U930-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.3	1.4
10°-20°	273.1	4.0
20°-30°	413.0	6.1
30°-40°	499.7	7.3
40°-50°	528.2	7.8
50°-60°	497.1	7.3
60°-70°	412.5	6.1
70°-80°	289.7	4.3
80°-90°	166.9	2.5
90°-100°	134.5	2.0
100°-110°	309.3	4.5
110°-120°	502.3	7.4
120°-130°	603.5	8.9
130°-140°	628.3	9.2
140°-150°	578.9	8.5
150°-160°	465.0	6.8
160°-170°	299.9	4.4
170°-180°	103.4	1.5
0°-30°	781.4	11.5
0°-40°	1281.1	18.8
0°-60°	2306.5	33.9
0°-90°	3175.6	46.7
90°-120°	946.0	13.9
90°-150°	2756.8	40.5
90°-180°	3625.0	53.3
0°-180°	6800.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1007	1007	1007	1007	1007	
5°	1008	1004	996	1005	1004	96
15°	966	967	964	973	973	272
25°	884	890	894	906	907	407
35°	773	787	798	813	817	484
45°	645	666	688	706	712	498
55°	505	529	562	584	592	450
65°	349	386	424	451	461	346
75°	194	236	283	313	325	206
85°	60	107	158	190	203	64
90°	20	75	130	166	178	14
95°	59	71	116	150	162	69
105°	255	284	328	361	344	268
115°	464	478	512	537	546	457
125°	648	651	676	699	708	578
135°	800	800	810	829	838	616
145°	921	922	922	930	936	575
155°	1008	1009	1007	1010	1008	465
165°	1064	1060	1060	1065	1059	300
175°	1088	1084	1084	1090	1082	104
180°	1088	1088	1088	1088	1088	



TEST NUMBER: P332655-930

CATALOG NUMBER: SA4XXDIP-C1020D1035U930-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1006.7	1006.7	1006.7	1006.7	1006.7	1006.7	1006.7	1006.7	1006.7	1006.7	1006.7
2.5°	1010.2	1009.7	1009.0	1008.4	1007.8	1006.7	1005.1	1003.6	1001.9	1000.3	1001.7
5°	1007.7	1007.0	1006.2	1005.5	1004.8	1003.5	1001.8	1000.0	998.3	996.5	998.5
7.5°	999.1	998.7	998.3	997.8	997.4	996.5	995.0	993.5	992.1	990.6	992.9
10°	992.0	991.7	991.5	991.2	991.0	990.2	989.0	987.7	986.4	985.2	987.5
12.5°	982.0	982.0	981.9	981.9	981.9	981.4	980.6	979.7	978.8	978.0	980.1
15°	966.0	966.3	966.5	966.8	967.0	966.8	966.0	965.3	964.5	963.8	966.0
17.5°	944.2	944.9	945.7	946.4	947.2	947.5	947.3	947.2	947.1	946.9	949.2
20°	928.9	929.6	930.3	931.1	931.9	932.4	932.6	932.9	933.1	933.4	935.9
22.5°	911.7	912.6	913.6	914.6	915.5	916.2	916.6	917.1	917.5	918.0	920.6
25°	883.8	885.3	886.7	888.3	889.7	890.9	891.6	892.4	893.2	893.9	896.7
27.5°	852.6	854.8	857.0	859.2	861.4	863.2	864.3	865.4	866.6	867.7	870.3
30°	831.9	833.9	835.9	837.9	839.9	841.8	843.5	845.3	847.0	848.8	851.6
32.5°	809.3	811.8	814.2	816.6	819.0	821.2	823.1	825.1	827.0	829.0	832.1
35°	773.3	776.3	779.3	782.3	785.3	788.1	790.6	793.0	795.6	798.1	801.6
37.5°	736.9	740.5	743.9	747.4	750.8	754.1	757.2	760.3	763.4	766.5	770.1
40°	713.5	716.8	720.1	723.3	726.6	729.9	733.4	736.9	740.5	744.0	747.7
42.5°	686.5	690.2	693.8	697.5	701.1	705.0	709.1	713.2	717.3	721.5	725.6
45°	644.7	649.5	654.3	659.1	663.8	668.5	673.4	678.1	682.8	687.6	691.9
47.5°	604.9	609.8	614.7	619.6	624.5	629.7	635.2	640.7	646.3	651.8	656.2
50°	576.0	581.6	587.0	592.6	598.0	603.6	609.1	614.6	620.1	625.6	630.6
52.5°	547.1	552.7	558.2	563.7	569.2	575.1	581.4	587.7	594.0	600.4	605.4
55°	505.0	510.3	515.5	520.8	526.0	532.4	540.0	547.5	555.0	562.5	567.5
57.5°	457.9	464.4	470.9	477.4	484.0	490.9	498.4	505.9	513.3	520.8	526.8
60°	427.2	433.7	440.3	446.8	453.3	460.6	469.0	477.2	485.4	493.7	499.5
62.5°	397.5	404.6	411.7	418.8	425.9	433.6	441.9	450.1	458.4	466.7	472.5
65°	349.4	357.4	365.5	373.5	381.5	389.8	398.3	406.8	415.3	423.9	430.1
67.5°	303.2	311.8	320.2	328.8	337.3	346.1	355.2	364.4	373.5	382.6	389.0
70°	271.7	280.2	288.7	297.2	305.7	314.8	324.2	333.8	343.3	352.9	359.6
72.5°	241.0	249.7	258.4	267.2	275.9	285.3	295.4	305.5	315.7	325.8	332.3
75°	193.9	203.2	212.4	221.7	231.0	240.8	251.4	261.9	272.4	282.9	289.9
77.5°	149.9	159.7	169.6	179.4	189.2	199.6	210.7	221.7	232.7	243.7	250.8
80°	122.9	132.9	142.9	153.0	163.0	173.5	184.5	195.5	206.5	217.5	225.1
82.5°	95.8	106.2	116.7	127.1	137.5	148.2	159.2	170.2	181.3	192.3	200.0
85°	59.8	70.3	80.8	91.3	101.8	112.8	124.0	135.3	146.5	157.8	165.3
87.5°	33.8	44.4	55.1	65.7	76.3	87.2	98.5	109.8	121.1	132.3	139.8
90°	20.5	32.4	44.5	56.5	68.5	80.6	92.9	105.1	117.3	129.5	137.9
92.5°	27.4	36.5	45.7	54.8	63.9	74.6	86.7	99.0	111.2	123.4	131.6
95°	59.4	61.6	63.7	65.8	67.9	74.2	84.6	95.1	105.5	115.9	123.8
97.5°	108.4	119.3	130.3	141.2	152.1	152.6	142.6	132.6	122.6	112.6	119.3
100°	145.9	155.6	165.4	175.2	185.0	182.2	167.1	151.9	136.6	121.5	125.1
102.5°	188.8	197.0	205.0	213.1	221.3	228.4	234.7	241.1	247.4	253.7	227.1
105°	255.1	261.2	267.3	273.5	279.5	287.6	297.8	308.0	318.1	328.3	336.2
107.5°	318.5	323.2	327.8	332.5	337.1	344.5	354.5	364.4	374.5	384.5	391.4
110°	360.6	364.7	368.7	372.8	376.8	383.8	393.6	403.5	413.4	423.1	429.3



TEST NUMBER: P332655-930

CATALOG NUMBER: SA4XXDIP-C1020D1035U930-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	401.4	405.4	409.5	413.6	417.7	424.2	433.1	442.0	450.8	459.7	465.2
115°	464.1	467.0	469.8	472.5	475.3	480.7	488.5	496.4	504.2	512.0	517.9
117.5°	521.7	523.8	525.9	528.0	530.0	535.0	542.8	550.7	558.6	566.5	571.6
120°	559.9	561.3	562.9	564.4	565.8	570.1	577.2	584.2	591.3	598.4	603.8
122.5°	596.4	597.0	597.5	598.1	598.7	602.5	609.7	616.8	623.9	631.0	636.3
125°	647.5	647.9	648.4	648.9	649.4	652.6	658.4	664.4	670.3	676.1	681.4
127.5°	696.8	696.7	696.6	696.5	696.4	699.3	704.9	710.5	716.2	721.8	726.2
130°	727.7	727.7	727.6	727.6	727.5	729.7	734.3	738.8	743.4	747.9	752.6
132.5°	757.0	757.1	757.2	757.2	757.3	759.3	763.2	767.1	771.0	774.9	779.4
135°	799.9	799.6	799.5	799.3	799.2	800.3	802.7	805.3	807.7	810.2	814.6
137.5°	838.8	838.6	838.4	838.2	838.0	838.8	840.4	842.1	843.8	845.4	849.5
140°	864.1	864.3	864.4	864.5	864.6	865.0	865.6	866.2	866.8	867.4	871.2
142.5°	886.1	886.6	887.3	887.9	888.4	888.8	888.8	888.9	889.0	889.1	892.3
145°	920.8	921.1	921.4	921.7	922.0	922.1	922.1	922.1	922.1	922.1	923.8
147.5°	948.7	949.4	950.1	951.0	951.7	952.0	951.8	951.6	951.5	951.3	951.6
150°	968.8	969.3	969.8	970.3	970.7	970.9	970.7	970.5	970.4	970.1	970.1
152.5°	984.9	985.4	985.9	986.4	987.0	987.1	986.8	986.4	986.1	985.8	986.1
155°	1008.4	1008.6	1008.8	1008.9	1009.1	1008.9	1008.4	1007.9	1007.3	1006.8	1007.5
157.5°	1028.4	1028.3	1028.2	1028.1	1028.0	1027.6	1027.0	1026.4	1025.8	1025.2	1026.1
160°	1040.2	1039.6	1039.1	1038.5	1038.0	1037.6	1037.5	1037.2	1037.1	1036.9	1038.0
162.5°	1050.6	1049.9	1049.2	1048.5	1047.8	1047.4	1047.2	1047.0	1046.8	1046.7	1047.7
165°	1063.7	1062.8	1061.9	1061.0	1060.1	1059.6	1059.6	1059.6	1059.6	1059.6	1061.1
167.5°	1074.2	1073.3	1072.3	1071.4	1070.4	1069.9	1069.8	1069.7	1069.6	1069.4	1071.1
170°	1080.0	1079.0	1077.8	1076.8	1075.7	1075.2	1075.4	1075.6	1075.8	1076.0	1077.4
172.5°	1083.9	1082.9	1081.7	1080.7	1079.6	1079.1	1079.3	1079.5	1079.7	1079.9	1081.3
175°	1088.2	1087.1	1086.0	1084.9	1083.9	1083.4	1083.5	1083.8	1083.9	1084.1	1085.7
177.5°	1090.1	1089.1	1088.1	1087.1	1086.1	1085.7	1086.0	1086.3	1086.5	1086.9	1088.0
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2



TEST NUMBER: P332655-930

CATALOG NUMBER: SA4XXDIP-C1020D1035U930-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1006.7	1006.7	1006.7	1006.7	1006.7	1006.7	1006.7	1006.7
2.5°	1003.1	1004.5	1005.9	1006.5	1006.3	1006.1	1005.9	1005.8
5°	1000.5	1002.5	1004.5	1005.3	1005.1	1004.9	1004.6	1004.4
7.5°	995.2	997.4	999.6	1000.6	1000.4	1000.1	999.9	999.6
10°	989.7	992.0	994.3	995.2	995.0	994.7	994.5	994.3
12.5°	982.1	984.1	986.2	987.2	987.2	987.1	987.1	987.0
15°	968.3	970.5	972.8	973.8	973.5	973.3	973.1	972.8
17.5°	951.5	953.8	956.1	957.2	956.9	956.8	956.5	956.3
20°	938.3	940.9	943.4	944.6	944.6	944.6	944.6	944.6
22.5°	923.0	925.5	928.1	929.5	929.9	930.3	930.7	931.1
25°	899.4	902.1	904.9	906.4	906.7	906.9	907.2	907.4
27.5°	872.9	875.4	878.0	879.4	879.7	880.0	880.3	880.6
30°	854.4	857.0	859.8	861.4	861.9	862.4	863.0	863.5
32.5°	835.3	838.5	841.6	843.4	843.9	844.4	844.9	845.5
35°	805.1	808.6	812.1	814.2	815.0	815.7	816.5	817.3
37.5°	773.6	777.2	780.7	782.9	783.7	784.6	785.3	786.1
40°	751.5	755.2	759.0	761.4	762.4	763.4	764.4	765.4
42.5°	729.8	733.9	738.1	740.5	741.4	742.2	743.0	743.7
45°	696.1	700.4	704.7	707.4	708.7	709.9	711.2	712.4
47.5°	660.6	665.0	669.4	672.4	673.8	675.4	676.9	678.4
50°	635.6	640.7	645.6	648.9	650.4	651.9	653.4	654.9
52.5°	610.4	615.4	620.4	623.6	625.2	626.6	628.2	629.7
55°	572.5	577.6	582.5	585.8	587.3	588.8	590.3	591.8
57.5°	532.7	538.7	544.6	548.3	549.7	551.1	552.5	553.9
60°	505.2	511.0	516.7	520.7	522.7	524.6	526.7	528.6
62.5°	478.2	484.0	489.8	493.6	495.6	497.6	499.6	501.7
65°	436.3	442.6	448.9	453.1	455.0	457.1	459.0	461.1
67.5°	395.3	401.7	408.1	412.2	414.2	416.1	418.1	420.0
70°	366.3	373.1	379.8	384.2	385.9	387.7	389.4	391.2
72.5°	338.9	345.4	352.0	356.3	358.2	360.2	362.2	364.1
75°	296.9	303.9	311.0	315.6	317.9	320.2	322.4	324.7
77.5°	258.0	265.1	272.1	277.0	279.3	281.8	284.1	286.6
80°	232.6	240.1	247.6	252.3	254.4	256.4	258.4	260.4
82.5°	207.7	215.5	223.1	228.1	230.3	232.5	234.7	236.9
85°	172.8	180.3	187.8	192.9	195.4	197.9	200.4	202.9
87.5°	147.2	154.7	162.2	167.1	169.4	171.7	174.0	176.2
90°	146.2	154.6	162.9	168.3	170.6	173.0	175.4	177.7
92.5°	139.7	147.9	156.0	161.2	163.2	165.3	167.4	169.4
95°	131.7	139.5	147.4	152.5	154.9	157.4	159.8	162.2
97.5°	125.9	132.6	139.3	143.7	146.1	148.5	150.7	153.1
100°	128.9	132.6	136.2	139.0	141.0	142.9	144.9	146.8
102.5°	200.5	173.9	147.2	134.9	137.0	138.9	141.0	142.9
105°	344.1	352.0	359.9	361.6	357.1	352.5	348.1	343.6
107.5°	398.4	405.4	412.3	417.0	419.5	422.0	424.5	427.0
110°	435.5	441.6	447.7	452.0	454.5	457.1	459.7	462.2



TEST NUMBER: P332655-930

CATALOG NUMBER: SA4XXDIP-C1020D1035U930-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	470.7	476.1	481.7	485.8	488.4	491.1	493.8	496.5
115°	523.7	529.6	535.5	539.3	541.0	542.8	544.5	546.3
117.5°	576.7	581.9	587.0	590.5	592.5	594.4	596.3	598.3
120°	609.1	614.5	619.9	623.4	625.0	626.7	628.4	630.0
122.5°	641.5	646.7	651.9	655.3	656.7	658.1	659.6	661.0
125°	686.7	692.1	697.4	700.8	702.5	704.3	705.9	707.6
127.5°	730.6	735.0	739.4	742.4	744.0	745.5	747.1	748.6
130°	757.2	762.0	766.6	769.7	771.3	772.7	774.3	775.8
132.5°	783.9	788.4	792.9	795.8	797.1	798.5	799.9	801.2
135°	819.0	823.3	827.7	830.8	832.7	834.5	836.4	838.3
137.5°	853.5	857.5	861.6	864.2	865.4	866.5	867.6	868.8
140°	875.0	878.8	882.6	885.3	886.6	888.1	889.5	891.0
142.5°	895.5	898.8	902.0	904.2	905.3	906.4	907.5	908.6
145°	925.5	927.2	928.9	930.4	931.7	933.1	934.5	935.9
147.5°	951.9	952.3	952.7	953.3	954.3	955.3	956.3	957.2
150°	970.1	970.1	970.1	970.2	970.5	970.6	970.8	970.9
152.5°	986.3	986.7	986.9	987.0	986.9	986.8	986.7	986.6
155°	1008.2	1008.9	1009.7	1009.7	1009.3	1008.7	1008.1	1007.6
157.5°	1027.0	1028.0	1028.9	1028.9	1028.0	1027.0	1026.1	1025.2
160°	1039.1	1040.2	1041.2	1041.2	1040.2	1039.1	1038.0	1036.9
162.5°	1048.8	1049.9	1051.0	1050.9	1049.7	1048.5	1047.3	1046.0
165°	1062.6	1064.0	1065.4	1065.4	1063.7	1062.1	1060.5	1058.8
167.5°	1072.6	1074.2	1075.8	1075.7	1073.9	1072.1	1070.2	1068.4
170°	1078.9	1080.3	1081.7	1081.6	1079.8	1078.0	1076.1	1074.3
172.5°	1082.8	1084.2	1085.7	1085.4	1083.5	1081.5	1079.5	1077.6
175°	1087.4	1089.0	1090.6	1090.3	1088.2	1086.0	1083.9	1081.7
177.5°	1089.2	1090.3	1091.5	1091.2	1089.5	1087.8	1086.0	1084.3
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2

(END OF REPORT)