

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332632-930

Luminaire Tested: **SA4XXDIP-C1020D365U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332632-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D365U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4644.7 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332632-930
CATALOG NUMBER: SA4XXDIP-C1020D365U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332632-930

CATALOG NUMBER: SA4XXDIP-C1020D365U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78		
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	65		
2	95	87	80	75	90	83	77	72	76	71	67	69	66	63	63	61	58	55		
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	53	49	46		
4	79	68	59	53	75	65	57	51	60	53	48	55	50	45	50	46	43	40		
5	73	61	52	46	69	58	50	44	54	47	42	49	44	40	45	41	37	35		
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	36	33	30		
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29	27		
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	35	30	26	24		
9	54	41	33	28	52	40	32	27	37	31	26	34	29	25	32	27	24	22		
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11357	11357	11357
5°	11391	11255	11336
10°	11320	11163	11218
15°	11183	11004	11032
20°	11001	10808	10817
25°	10794	10583	10553
30°	10540	10318	10224
35°	10276	10042	9909
40°	10003	9729	9551
45°	9717	9421	9240
50°	9401	9146	8862
55°	9060	8790	8504
60°	8719	8391	8136
65°	8334	8010	7687
70°	7903	7504	7211
75°	7243	6890	6716
80°	6448	6183	6025
85°	5641	5428	5326



TEST NUMBER: P332632-930

CATALOG NUMBER: SA4XXDIP-C1020D365U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.5	2.9
10°-20°	373.3	8.0
20°-30°	549.4	11.8
30°-40°	638.7	13.8
40°-50°	638.7	13.8
50°-60°	558.7	12.0
60°-70°	414.9	8.9
70°-80°	235.7	5.1
80°-90°	69.1	1.5
90°-100°	24.6	0.5
100°-110°	72.8	1.6
110°-120°	123.5	2.7
120°-130°	162.9	3.5
130°-140°	182.9	3.9
140°-150°	179.8	3.9
150°-160°	151.2	3.3
160°-170°	100.6	2.2
170°-180°	35.2	0.8
0°-30°	1055.2	22.7
0°-40°	1693.9	36.5
0°-60°	2891.3	62.3
0°-90°	3611.2	77.7
90°-120°	220.9	4.8
90°-150°	746.5	16.1
90°-180°	1034.0	22.3
0°-180°	4644.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1407	1407	1407	1407	1407	
5°	1406	1401	1389	1400	1399	133
15°	1338	1333	1317	1323	1320	377
25°	1212	1204	1188	1189	1185	557
35°	1043	1034	1019	1011	1006	652
45°	851	843	825	813	809	656
55°	644	640	624	611	604	576
65°	436	430	419	408	402	432
75°	232	227	221	217	215	247
85°	61	61	59	59	58	67
90°	1	4	6	8	9	4
95°	17	20	22	23	23	19
105°	67	67	69	69	70	71
115°	126	126	125	125	124	124
125°	183	183	183	182	182	163
135°	236	238	238	237	236	182
145°	287	288	288	288	287	179
155°	328	328	328	329	328	151
165°	358	357	356	358	357	101
175°	372	371	370	372	370	35
180°	372	372	372	372	372	



TEST NUMBER: P332632-930

CATALOG NUMBER: SA4XXDIP-C1020D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1410.4	1409.8	1409.2	1408.6	1408.0	1406.6	1404.4	1402.2	1400.0	1397.7	1399.8
5°	1405.7	1404.7	1403.7	1402.6	1401.7	1399.8	1397.0	1394.2	1391.6	1388.8	1391.6
7.5°	1392.6	1391.6	1390.6	1389.6	1388.6	1386.6	1383.5	1380.5	1377.4	1374.4	1376.6
10°	1380.9	1379.9	1378.8	1377.9	1376.9	1374.8	1371.5	1368.2	1365.0	1361.7	1363.7
12.5°	1365.5	1364.6	1363.5	1362.5	1361.5	1359.3	1355.8	1352.4	1348.9	1345.5	1347.7
15°	1338.1	1337.0	1336.0	1335.1	1334.0	1331.6	1327.9	1324.1	1320.4	1316.6	1318.1
17.5°	1304.9	1303.7	1302.4	1301.1	1299.9	1297.5	1293.9	1290.4	1286.8	1283.3	1284.2
20°	1280.5	1279.3	1278.1	1276.8	1275.5	1273.0	1269.3	1265.5	1261.8	1258.0	1258.7
22.5°	1254.4	1252.7	1251.1	1249.4	1247.8	1245.0	1241.3	1237.5	1233.8	1230.0	1231.4
25°	1211.8	1210.1	1208.3	1206.5	1204.8	1202.2	1198.7	1195.1	1191.6	1188.1	1188.4
27.5°	1163.1	1161.3	1159.4	1157.6	1155.8	1153.3	1150.1	1146.8	1143.5	1140.3	1139.7
30°	1130.7	1128.6	1126.6	1124.6	1122.6	1120.0	1116.7	1113.5	1110.2	1106.9	1106.0
32.5°	1096.3	1094.5	1092.7	1091.0	1089.2	1086.5	1083.0	1079.6	1076.1	1072.7	1071.5
35°	1042.7	1041.0	1039.2	1037.5	1035.7	1033.1	1029.6	1026.1	1022.5	1019.0	1017.2
37.5°	986.1	984.5	982.9	981.3	979.7	977.1	973.2	969.5	965.7	962.0	960.1
40°	949.2	947.1	945.1	943.1	941.1	938.2	934.5	930.7	927.0	923.2	920.7
42.5°	909.5	908.2	907.0	905.9	904.7	902.0	897.8	893.6	889.5	885.3	882.4
45°	851.1	849.3	847.6	845.8	844.1	841.1	837.1	833.2	829.2	825.2	822.4
47.5°	789.9	788.8	787.6	786.4	785.1	782.7	779.0	775.3	771.6	767.8	764.8
50°	748.5	747.5	746.5	745.5	744.4	742.2	738.7	735.2	731.7	728.2	724.7
52.5°	707.9	706.7	705.5	704.3	703.1	700.7	696.9	693.2	689.5	685.8	682.7
55°	643.7	642.9	642.1	641.4	640.7	638.5	635.0	631.5	628.0	624.5	621.5
57.5°	582.4	581.5	580.7	579.8	578.9	576.7	573.3	569.9	566.4	563.0	560.1
60°	540.0	538.7	537.4	536.2	534.9	532.7	529.5	526.2	522.9	519.7	517.4
62.5°	498.5	497.4	496.4	495.3	494.2	492.0	488.5	485.1	481.6	478.2	476.1
65°	436.3	435.0	433.7	432.5	431.2	429.3	426.8	424.4	421.8	419.3	416.9
67.5°	373.6	372.4	371.3	370.1	368.9	367.2	364.8	362.4	360.0	357.6	355.1
70°	334.8	333.0	331.3	329.5	327.8	325.9	323.9	321.9	319.9	317.9	315.8
72.5°	293.3	291.6	289.8	288.0	286.3	284.6	283.0	281.4	279.8	278.2	276.6
75°	232.2	231.0	229.7	228.4	227.2	225.9	224.7	223.5	222.2	220.9	220.0
77.5°	173.8	173.3	172.7	172.2	171.6	170.8	169.7	168.6	167.5	166.4	166.1
80°	138.7	137.9	137.1	136.4	135.7	135.0	134.5	134.0	133.5	133.0	132.5
82.5°	104.4	104.0	103.7	103.3	103.0	102.7	102.6	102.6	102.5	102.3	102.1
85°	60.9	60.9	60.9	60.9	60.9	60.7	60.1	59.6	59.1	58.6	58.6
87.5°	23.6	23.6	23.5	23.5	23.4	23.3	23.2	23.1	23.0	22.9	23.0
90°	0.9	1.5	2.3	3.0	3.7	4.3	4.8	5.3	5.8	6.4	6.7
92.5°	6.2	7.0	7.7	8.6	9.4	9.9	10.4	10.7	11.1	11.4	11.7
95°	17.3	17.9	18.4	19.0	19.6	20.1	20.5	21.0	21.4	21.9	22.1
97.5°	30.2	30.7	31.1	31.6	32.0	32.5	33.0	33.6	34.1	34.7	34.9
100°	40.4	40.6	40.8	41.1	41.3	41.7	42.3	43.0	43.5	44.1	44.2
102.5°	51.0	51.0	51.1	51.3	51.4	51.7	52.2	52.7	53.2	53.7	54.0
105°	67.1	67.2	67.3	67.3	67.3	67.5	67.8	68.1	68.3	68.6	68.7
107.5°	84.1	84.2	84.3	84.4	84.5	84.5	84.5	84.5	84.6	84.6	84.8
110°	95.6	95.8	95.9	96.0	96.1	96.2	96.1	96.0	96.0	96.0	95.8



TEST NUMBER: P332632-930

CATALOG NUMBER: SA4XXDIP-C1020D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	107.6	107.6	107.7	107.7	107.7	107.7	107.5	107.5	107.4	107.2	107.2
115°	125.6	125.6	125.6	125.6	125.6	125.6	125.4	125.3	125.1	125.1	125.0
117.5°	142.5	142.6	142.7	142.7	142.8	142.8	142.7	142.6	142.4	142.4	142.2
120°	153.8	154.1	154.3	154.6	154.9	154.9	154.7	154.5	154.3	154.2	153.8
122.5°	165.6	165.7	165.8	165.9	166.0	166.0	165.9	165.8	165.8	165.7	165.4
125°	183.0	183.0	183.0	183.0	183.0	182.9	182.9	182.8	182.7	182.6	182.5
127.5°	198.7	198.9	199.1	199.3	199.4	199.5	199.4	199.3	199.2	199.1	198.9
130°	209.8	209.9	210.1	210.3	210.5	210.6	210.6	210.6	210.6	210.6	210.5
132.5°	221.0	221.2	221.3	221.4	221.6	221.6	221.6	221.5	221.5	221.4	221.3
135°	235.9	236.4	236.7	237.1	237.5	237.7	237.7	237.7	237.7	237.7	237.6
137.5°	252.2	252.4	252.6	252.7	252.9	253.1	253.2	253.2	253.4	253.5	253.3
140°	263.0	263.2	263.3	263.4	263.6	263.6	263.6	263.6	263.6	263.6	263.6
142.5°	273.0	273.0	273.2	273.3	273.5	273.5	273.5	273.4	273.4	273.3	273.3
145°	286.7	286.9	287.1	287.4	287.7	287.9	287.9	288.0	288.0	288.1	288.0
147.5°	300.3	300.6	300.8	301.2	301.5	301.6	301.6	301.5	301.5	301.4	301.3
150°	308.6	308.8	309.1	309.3	309.6	309.7	309.7	309.7	309.7	309.7	309.7
152.5°	316.4	316.6	316.7	316.8	317.0	317.1	317.2	317.2	317.2	317.3	317.5
155°	328.4	328.4	328.4	328.4	328.4	328.4	328.3	328.2	328.2	328.2	328.4
157.5°	338.6	338.4	338.3	338.3	338.1	338.0	338.0	338.0	338.0	338.0	338.2
160°	344.5	344.5	344.5	344.4	344.3	344.2	344.2	344.1	344.1	344.0	344.2
162.5°	350.1	349.9	349.8	349.6	349.4	349.4	349.3	349.2	349.1	349.0	349.4
165°	357.5	357.3	357.2	356.9	356.8	356.6	356.4	356.4	356.2	356.1	356.4
167.5°	363.2	363.0	362.7	362.4	362.2	362.0	362.1	362.1	362.1	362.1	362.5
170°	366.5	366.2	365.8	365.5	365.2	365.1	365.1	365.2	365.3	365.3	365.7
172.5°	368.8	368.5	368.2	367.9	367.7	367.5	367.5	367.6	367.6	367.6	368.0
175°	371.9	371.6	371.3	371.0	370.6	370.5	370.4	370.3	370.3	370.2	370.6
177.5°	373.0	372.8	372.4	372.2	371.9	371.9	371.9	371.9	371.9	371.9	372.2
180°	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5



TEST NUMBER: P332632-930

CATALOG NUMBER: SA4XXDIP-C1020D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1401.7	1403.8	1405.8	1406.7	1406.5	1406.3	1406.1	1405.9
5°	1394.2	1397.0	1399.8	1400.9	1400.4	1399.9	1399.4	1398.9
7.5°	1378.8	1381.0	1383.2	1384.1	1383.8	1383.5	1383.2	1382.9
10°	1365.7	1367.7	1369.7	1370.4	1369.9	1369.5	1369.0	1368.5
12.5°	1349.9	1352.1	1354.3	1355.0	1354.4	1353.6	1352.9	1352.3
15°	1319.6	1321.1	1322.7	1323.0	1322.3	1321.5	1320.8	1320.0
17.5°	1285.2	1286.1	1287.0	1287.3	1286.8	1286.3	1285.8	1285.2
20°	1259.5	1260.3	1261.0	1261.1	1260.6	1260.1	1259.6	1259.1
22.5°	1232.7	1234.1	1235.4	1235.7	1234.8	1233.9	1233.0	1232.1
25°	1188.6	1188.9	1189.1	1188.7	1187.7	1186.7	1185.7	1184.7
27.5°	1139.1	1138.5	1137.9	1137.0	1135.7	1134.5	1133.2	1132.0
30°	1105.0	1103.9	1102.9	1101.8	1100.6	1099.3	1098.0	1096.8
32.5°	1070.2	1069.1	1067.9	1066.7	1065.4	1064.1	1062.9	1061.6
35°	1015.5	1013.7	1012.0	1010.5	1009.3	1008.0	1006.7	1005.5
37.5°	958.1	956.3	954.4	952.6	951.0	949.3	947.6	946.0
40°	918.2	915.7	913.2	911.3	910.0	908.8	907.6	906.3
42.5°	879.5	876.6	873.7	871.8	871.0	870.1	869.3	868.5
45°	819.6	816.8	814.1	812.4	811.6	810.9	810.1	809.3
47.5°	761.7	758.6	755.5	752.9	751.1	749.1	747.2	745.3
50°	721.2	717.7	714.2	711.7	710.1	708.7	707.2	705.6
52.5°	679.6	676.5	673.4	670.9	669.0	667.1	665.2	663.2
55°	618.5	615.5	612.5	610.3	608.7	607.2	605.7	604.2
57.5°	557.3	554.4	551.5	549.3	547.9	546.5	545.0	543.6
60°	515.2	512.9	510.6	508.9	507.6	506.4	505.2	503.9
62.5°	474.1	472.0	469.9	468.3	467.1	465.8	464.6	463.3
65°	414.3	411.8	409.3	407.4	406.2	405.0	403.7	402.4
67.5°	352.8	350.3	348.0	346.6	346.2	345.8	345.5	345.2
70°	313.9	311.9	309.9	308.5	307.8	307.0	306.2	305.5
72.5°	275.0	273.4	271.8	270.6	269.9	269.1	268.4	267.6
75°	218.9	217.9	217.0	216.3	216.1	215.8	215.6	215.3
77.5°	165.8	165.5	165.2	164.7	164.0	163.4	162.7	162.1
80°	132.0	131.5	131.0	130.6	130.4	130.1	129.9	129.6
82.5°	101.7	101.4	101.2	100.9	100.6	100.4	100.1	99.9
85°	58.6	58.6	58.6	58.5	58.2	58.0	57.7	57.5
87.5°	23.1	23.2	23.2	23.2	23.3	23.3	23.3	23.4
90°	7.1	7.5	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	11.9	12.1	12.3	12.5	12.6	12.6	12.7	12.8
95°	22.3	22.5	22.7	22.7	22.7	22.7	22.7	22.7
97.5°	35.1	35.3	35.5	35.6	35.6	35.6	35.6	35.6
100°	44.4	44.4	44.6	44.7	44.7	44.7	44.7	44.7
102.5°	54.1	54.3	54.5	54.6	54.6	54.7	54.7	54.8
105°	69.0	69.1	69.3	69.5	69.7	70.0	70.1	70.3
107.5°	85.0	85.2	85.4	85.4	85.4	85.4	85.4	85.4
110°	95.7	95.6	95.4	95.5	95.6	95.9	96.0	96.2



TEST NUMBER: P332632-930

CATALOG NUMBER: SA4XXDIP-C1020D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	107.2	107.1	107.1	107.1	107.2	107.2	107.2	107.3
115°	124.9	124.8	124.7	124.7	124.7	124.6	124.5	124.5
117.5°	141.9	141.7	141.5	141.4	141.2	141.0	141.0	140.8
120°	153.5	153.2	152.9	152.8	152.9	153.0	153.1	153.3
122.5°	165.3	165.0	164.8	164.5	164.4	164.1	163.9	163.6
125°	182.4	182.3	182.1	182.0	181.9	181.7	181.6	181.5
127.5°	198.9	198.7	198.5	198.4	198.4	198.3	198.1	198.0
130°	210.3	210.2	210.1	209.9	209.6	209.4	209.1	208.9
132.5°	221.2	221.0	220.9	220.8	220.7	220.6	220.5	220.4
135°	237.4	237.3	237.2	237.0	236.8	236.6	236.4	236.3
137.5°	253.2	253.0	252.8	252.7	252.7	252.8	252.8	252.9
140°	263.5	263.4	263.3	263.3	263.3	263.2	263.1	263.0
142.5°	273.3	273.3	273.2	273.2	273.2	273.2	273.2	273.2
145°	288.0	287.9	287.9	287.7	287.6	287.3	287.1	287.0
147.5°	301.3	301.3	301.2	301.2	301.1	301.0	300.9	300.9
150°	309.7	309.7	309.7	309.7	309.7	309.6	309.5	309.4
152.5°	317.6	317.8	318.0	317.9	317.7	317.6	317.4	317.2
155°	328.6	328.9	329.1	329.1	328.9	328.6	328.4	328.2
157.5°	338.3	338.6	338.8	338.8	338.5	338.3	338.1	337.9
160°	344.4	344.5	344.8	344.7	344.4	344.1	343.7	343.4
162.5°	349.8	350.1	350.4	350.4	350.2	349.8	349.5	349.2
165°	356.9	357.3	357.6	357.7	357.4	357.2	356.9	356.7
167.5°	362.9	363.2	363.6	363.6	363.2	362.8	362.4	362.0
170°	366.1	366.5	366.9	366.8	366.4	365.9	365.5	365.0
172.5°	368.5	368.9	369.3	369.3	368.9	368.4	368.0	367.5
175°	371.1	371.5	372.0	372.0	371.5	371.1	370.6	370.2
177.5°	372.5	372.9	373.2	373.2	372.8	372.4	372.0	371.6
180°	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5

(END OF REPORT)