

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331329-940

Luminaire Tested: **SA2XXDIP-C485D1080U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331329-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D1080U940-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5515.2 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331329-940
CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331329-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32				
1	94	90	86	82	84	81	78	75	64	62	60	49	48	46	35	34	33	27				
2	85	78	72	67	77	70	65	61	56	53	50	43	41	39	31	29	28	23				
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	25	24	19				
4	71	61	53	47	64	55	48	43	44	39	35	34	31	28	24	22	21	16				
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14				
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13				
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11				
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11183	11183	11183
5°	11225	11063	11128
10°	11158	10952	11006
15°	11020	10810	10798
20°	10825	10596	10584
25°	10630	10334	10334
30°	10381	10094	10006
35°	10147	9806	9662
40°	9853	9518	9333
45°	9565	9229	9001
50°	9251	8932	8616
55°	8923	8586	8267
60°	8557	8173	7869
65°	8164	7759	7404
70°	7671	7260	6916
75°	6981	6687	6525
80°	6192	6007	5700
85°	5057	4798	4316



TEST NUMBER: P331329-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.1	1.2
10°-20°	183.3	3.3
20°-30°	269.4	4.9
30°-40°	312.9	5.7
40°-50°	312.5	5.7
50°-60°	272.6	4.9
60°-70°	201.5	3.7
70°-80°	114.1	2.1
80°-90°	35.5	0.6
90°-100°	215.4	3.9
100°-110°	730.9	13.3
110°-120°	776.4	14.1
120°-130°	639.2	11.6
130°-140°	513.3	9.3
140°-150°	387.9	7.0
150°-160°	272.6	4.9
160°-170°	160.5	2.9
170°-180°	52.2	0.9
0°-30°	517.7	9.4
0°-40°	830.6	15.1
0°-60°	1415.7	25.7
0°-90°	1766.9	32.0
90°-120°	1722.7	31.2
90°-150°	3263.0	59.2
90°-180°	3748.0	68.0
0°-180°	5515.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	693	693	693	693	693	
5°	693	690	683	688	687	66
15°	659	655	647	649	646	186
25°	597	591	580	581	580	274
35°	515	508	498	494	490	321
45°	419	414	404	397	394	323
55°	317	313	305	297	294	283
65°	214	210	203	197	194	211
75°	112	110	107	104	105	120
85°	27	27	26	24	23	31
90°	1	14	35	34	34	3
95°	36	89	406	153	118	38
105°	126	191	768	1372	1167	134
115°	223	281	642	1325	1536	221
125°	311	368	617	1074	1246	276
135°	365	435	610	902	1033	282
145°	416	479	607	754	825	261
155°	473	511	589	667	693	218
165°	516	531	564	599	608	145
175°	538	538	543	550	548	51
180°	539	539	539	539	539	



TEST NUMBER: P331329-940
 CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	695.8	695.2	694.6	694.0	693.4	692.5	691.2	689.9	688.6	687.2	688.5
5°	692.6	692.0	691.4	690.8	690.3	689.1	687.5	685.9	684.2	682.6	683.8
7.5°	686.4	685.5	684.7	683.7	682.8	681.5	679.8	678.2	676.5	674.8	676.1
10°	680.6	679.6	678.5	677.5	676.5	675.0	673.2	671.5	669.8	668.0	669.1
12.5°	672.6	671.7	670.7	669.9	669.0	667.6	665.8	664.1	662.3	660.5	661.3
15°	659.3	658.4	657.5	656.7	655.8	654.3	652.4	650.5	648.5	646.7	647.2
17.5°	642.2	641.4	640.5	639.6	638.7	637.3	635.3	633.4	631.4	629.5	630.2
20°	630.0	629.1	628.2	627.3	626.4	625.0	622.9	620.8	618.8	616.7	617.2
22.5°	617.8	616.5	615.3	614.0	612.8	611.2	609.2	607.3	605.3	603.3	603.4
25°	596.7	595.5	594.3	593.2	592.0	590.1	587.6	585.1	582.6	580.1	580.3
27.5°	572.7	571.7	570.6	569.5	568.5	566.9	565.0	562.9	561.0	559.0	558.6
30°	556.8	555.5	554.4	553.2	552.0	550.3	548.0	545.9	543.7	541.4	541.0
32.5°	539.7	538.8	537.8	536.8	535.9	534.2	531.9	529.6	527.3	525.0	524.1
35°	514.8	513.3	511.8	510.3	508.9	506.9	504.6	502.2	499.8	497.5	496.6
37.5°	486.7	485.4	484.1	482.8	481.4	479.7	477.2	474.9	472.5	470.2	469.0
40°	467.5	466.3	465.1	464.0	462.8	461.0	458.6	456.3	453.9	451.6	450.2
42.5°	448.9	447.6	446.5	445.3	444.2	442.4	440.0	437.7	435.2	432.8	431.4
45°	418.9	417.9	416.8	415.8	414.7	413.1	410.9	408.7	406.4	404.2	402.6
47.5°	389.1	388.1	387.1	386.1	385.1	383.5	381.2	378.9	376.6	374.3	372.6
50°	368.3	367.6	366.8	366.0	365.3	363.9	361.9	359.8	357.7	355.6	353.6
52.5°	348.0	347.1	346.1	345.1	344.1	342.7	340.7	338.8	336.8	334.8	333.1
55°	317.0	316.1	315.2	314.3	313.4	312.1	310.3	308.5	306.7	305.0	303.3
57.5°	285.8	285.1	284.4	283.7	283.0	281.7	279.7	277.8	275.8	273.8	272.1
60°	265.0	264.5	263.9	263.2	262.7	261.4	259.3	257.2	255.1	253.1	251.5
62.5°	244.8	243.9	242.9	241.9	241.0	239.8	238.2	236.6	235.0	233.4	231.8
65°	213.7	212.9	212.0	211.1	210.3	209.0	207.6	206.1	204.6	203.1	201.8
67.5°	182.2	181.5	180.7	180.0	179.3	178.3	177.0	175.7	174.3	173.0	172.0
70°	162.5	161.9	161.3	160.7	160.2	159.2	157.8	156.5	155.2	153.8	152.8
72.5°	142.2	141.7	141.1	140.4	139.9	139.2	138.3	137.4	136.6	135.7	134.6
75°	111.9	111.6	111.3	111.0	110.7	110.2	109.4	108.7	108.0	107.2	106.3
77.5°	84.7	84.2	83.7	83.2	82.7	82.3	82.0	81.7	81.4	81.1	80.7
80°	66.6	66.4	66.3	66.2	66.0	65.8	65.5	65.2	64.9	64.6	64.1
82.5°	49.6	49.5	49.5	49.5	49.4	49.3	49.1	49.0	48.8	48.6	48.1
85°	27.3	27.2	27.0	26.8	26.8	26.6	26.4	26.3	26.1	25.9	25.5
87.5°	9.8	10.2	10.8	11.0	11.1	11.5	12.3	13.6	14.5	14.5	13.9
90°	1.1	4.1	8.3	10.3	12.4	15.5	20.7	28.0	34.2	35.2	34.2
92.5°	12.7	18.2	25.7	30.2	37.3	47.0	70.4	103.3	132.8	134.6	113.8
95°	36.3	40.4	50.7	60.1	76.7	101.5	149.2	239.2	359.4	406.1	355.3
97.5°	59.0	64.6	75.6	89.7	108.8	137.0	196.8	322.4	522.1	693.2	727.2
100°	79.7	82.8	92.2	108.8	129.5	158.5	213.4	339.7	563.5	818.3	967.5
102.5°	98.8	101.1	110.4	127.0	148.6	177.5	228.3	340.6	547.8	822.5	1057.0
105°	126.4	130.5	137.8	153.3	176.1	205.1	253.8	346.0	516.9	767.6	1043.1
107.5°	156.2	159.5	166.6	180.8	203.5	232.6	279.9	360.3	501.6	708.7	952.2
110°	176.1	180.2	186.5	199.9	221.7	251.7	297.3	371.8	498.3	680.6	895.0



TEST NUMBER: P331329-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	194.3	198.5	205.5	218.1	239.1	269.9	313.9	384.3	499.1	662.4	855.2
115°	222.7	227.9	234.1	246.6	267.2	295.2	339.7	403.0	503.5	642.2	805.9
117.5°	252.2	256.3	262.5	273.5	293.4	322.4	363.6	422.8	510.9	632.5	774.8
120°	270.4	274.5	280.7	290.1	310.8	339.7	380.1	436.1	515.9	626.7	758.2
122.5°	287.8	291.1	297.3	307.5	328.1	358.0	395.9	447.7	521.7	623.4	744.1
125°	310.8	313.9	320.1	332.5	353.2	382.3	419.5	466.2	530.4	617.4	724.1
127.5°	329.0	333.1	341.9	355.5	375.4	405.2	441.5	483.3	539.3	613.9	705.4
130°	339.7	343.9	354.3	368.8	389.5	418.5	454.8	494.1	545.9	612.2	693.0
132.5°	349.7	354.7	365.9	381.2	402.8	431.8	466.4	504.9	552.5	611.4	683.1
135°	364.6	368.8	381.2	396.7	420.5	449.6	482.7	519.0	560.4	610.1	669.1
137.5°	378.7	383.7	396.1	412.7	436.3	463.2	496.0	529.8	567.5	609.9	659.4
140°	389.5	393.6	406.1	422.7	445.4	472.3	503.5	535.6	570.8	609.1	653.6
142.5°	400.3	403.6	415.2	431.8	453.7	479.0	509.3	540.6	573.3	609.1	647.8
145°	416.4	420.5	431.0	446.5	467.2	490.0	517.9	547.0	576.0	607.0	640.2
147.5°	433.8	436.9	446.8	461.2	478.4	498.6	525.0	550.5	576.8	603.3	632.3
150°	445.4	448.5	456.8	470.3	485.8	504.4	528.3	552.1	576.0	600.8	625.6
152.5°	457.0	458.5	466.7	478.6	493.3	510.2	531.6	552.9	574.3	596.6	619.8
155°	473.4	474.4	480.6	492.0	503.5	519.0	536.5	554.2	571.8	589.4	609.1
157.5°	487.1	488.1	493.1	503.0	512.1	525.2	540.1	554.2	567.0	581.9	599.0
160°	496.1	497.2	501.3	509.6	517.9	529.3	541.8	554.2	564.5	577.0	591.5
162.5°	505.3	504.7	508.8	515.4	522.9	531.8	542.6	553.4	562.0	572.8	584.9
165°	515.9	514.9	516.9	523.1	528.3	534.5	543.9	551.1	557.3	564.5	573.9
167.5°	524.6	523.3	525.2	529.1	532.9	536.8	543.6	549.7	552.5	557.3	563.1
170°	530.4	528.3	529.3	532.4	534.5	537.6	542.8	548.0	550.0	553.1	557.3
172.5°	533.7	532.4	531.8	534.9	536.2	538.4	542.0	545.5	546.7	548.2	551.5
175°	537.6	536.5	535.6	537.6	537.6	538.7	540.7	542.8	541.8	542.8	543.9
177.5°	539.5	537.8	537.0	538.7	538.7	538.7	539.5	541.2	539.5	538.7	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331329-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	689.6	690.8	692.0	692.5	692.2	692.0	691.8	691.5
5°	685.0	686.2	687.3	687.8	687.5	687.2	686.9	686.6
7.5°	677.3	678.4	679.7	680.0	679.8	679.4	679.0	678.8
10°	670.3	671.5	672.7	673.1	672.6	672.2	671.7	671.3
12.5°	662.2	663.0	663.8	664.1	663.7	663.4	663.1	662.7
15°	647.8	648.5	649.0	648.9	648.2	647.5	646.8	646.0
17.5°	630.8	631.5	632.2	632.1	631.4	630.8	630.1	629.4
20°	617.6	618.0	618.5	618.4	617.8	617.2	616.6	616.0
22.5°	603.5	603.6	603.7	603.6	603.2	602.9	602.5	602.2
25°	580.7	580.9	581.2	581.2	580.9	580.7	580.3	580.1
27.5°	558.1	557.7	557.2	556.7	556.0	555.3	554.6	553.8
30°	540.6	540.1	539.7	539.1	538.5	538.0	537.3	536.7
32.5°	523.3	522.5	521.7	521.0	520.4	519.9	519.2	518.6
35°	495.7	494.8	493.9	493.1	492.4	491.6	490.9	490.2
37.5°	468.0	466.9	465.8	464.8	464.1	463.4	462.7	462.1
40°	448.9	447.5	446.2	445.2	444.6	444.1	443.4	442.8
42.5°	430.0	428.6	427.0	426.0	425.1	424.3	423.5	422.6
45°	401.0	399.4	397.7	396.6	396.0	395.5	394.8	394.2
47.5°	370.9	369.1	367.4	366.1	365.2	364.4	363.6	362.7
50°	351.5	349.4	347.3	345.9	345.2	344.5	343.7	343.0
52.5°	331.4	329.7	328.0	326.6	325.7	324.7	323.7	322.7
55°	301.5	299.7	297.9	296.7	295.9	295.2	294.4	293.7
57.5°	270.4	268.6	266.9	265.7	265.1	264.6	264.0	263.4
60°	249.8	248.2	246.6	245.5	245.0	244.6	244.2	243.7
62.5°	230.3	228.8	227.3	226.3	225.7	225.2	224.6	224.0
65°	200.5	199.1	197.8	196.7	196.0	195.3	194.6	193.8
67.5°	170.9	169.9	168.9	168.1	167.5	166.8	166.3	165.7
70°	151.8	150.7	149.7	148.9	148.3	147.7	147.1	146.5
72.5°	133.7	132.6	131.6	130.8	130.4	129.8	129.4	128.9
75°	105.4	104.6	103.7	103.3	103.7	104.0	104.2	104.6
77.5°	80.3	79.8	79.4	78.9	78.5	78.1	77.7	77.2
80°	63.7	63.2	62.9	62.4	62.2	61.9	61.5	61.3
82.5°	47.5	46.9	46.4	46.0	46.0	45.9	45.8	45.8
85°	25.1	24.6	24.2	23.9	23.7	23.6	23.5	23.3
87.5°	13.4	12.6	12.7	12.7	12.5	12.4	12.3	12.1
90°	33.2	31.1	33.2	34.2	34.2	34.2	34.2	34.2
92.5°	90.3	77.5	68.8	62.3	61.5	58.2	59.0	57.4
95°	271.4	208.2	164.7	141.9	128.4	120.2	117.1	118.1
97.5°	633.3	518.2	406.1	331.3	281.8	256.3	241.1	232.5
100°	945.7	817.3	675.4	550.0	464.0	419.5	389.5	370.9
102.5°	1150.5	1121.4	1017.6	884.8	791.4	715.4	677.9	652.6
105°	1258.6	1375.6	1389.1	1355.0	1290.7	1226.5	1182.0	1167.4
107.5°	1180.7	1357.0	1464.7	1514.8	1523.0	1519.4	1510.5	1491.2
110°	1113.6	1299.0	1431.6	1516.5	1561.0	1580.7	1590.1	1589.0



TEST NUMBER: P331329-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1052.2	1230.2	1371.9	1469.3	1531.2	1564.1	1581.8	1587.3
115°	976.9	1136.4	1272.0	1378.8	1452.3	1499.9	1526.9	1536.2
117.5°	920.1	1060.2	1183.2	1283.3	1358.3	1408.5	1437.0	1444.8
120°	891.9	1020.3	1130.2	1224.4	1296.9	1345.6	1375.6	1386.0
122.5°	869.5	987.2	1091.2	1176.3	1241.4	1289.2	1316.0	1324.6
125°	837.0	943.7	1034.8	1112.5	1172.6	1212.0	1237.9	1246.2
127.5°	804.9	901.4	987.4	1059.1	1111.5	1148.3	1170.7	1177.4
130°	784.2	873.3	955.1	1023.4	1074.2	1109.5	1130.2	1138.4
132.5°	764.3	846.8	921.9	986.1	1036.1	1071.3	1090.4	1097.8
135°	736.5	804.9	873.3	931.2	975.8	1010.0	1028.6	1032.8
137.5°	714.3	771.5	825.8	876.4	916.9	946.4	962.8	968.9
140°	700.3	750.0	797.6	843.2	876.4	903.3	918.8	925.1
142.5°	688.7	730.9	772.0	810.0	841.5	866.0	879.9	881.1
145°	672.3	706.5	738.6	768.7	793.4	811.1	821.4	824.6
147.5°	659.7	686.6	711.7	733.6	754.1	768.2	775.3	777.1
150°	650.5	673.3	695.1	713.7	729.2	741.7	747.9	748.9
152.5°	641.4	662.5	681.0	697.1	709.4	720.1	724.7	724.9
155°	628.7	645.3	660.8	672.3	683.7	690.9	695.1	693.0
157.5°	614.0	627.9	641.0	649.9	658.0	664.0	665.8	665.8
160°	604.9	616.4	627.8	635.0	642.2	647.4	648.5	648.5
162.5°	595.8	605.6	615.3	620.9	628.1	631.7	632.7	631.9
165°	582.2	589.4	596.6	600.8	604.9	609.1	609.1	608.1
167.5°	569.1	574.7	579.7	583.4	585.2	587.5	587.4	586.1
170°	562.5	565.6	569.7	571.8	572.8	576.0	574.9	572.8
172.5°	555.0	557.3	560.6	561.9	562.9	564.4	563.3	562.0
175°	547.0	548.0	549.0	550.0	550.0	551.1	550.0	548.0
177.5°	541.2	541.2	542.0	542.0	542.0	542.0	541.2	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7

(END OF REPORT)