

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332636-930

Luminaire Tested: **SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332636-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5476.9 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332636-930
CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	65	64	62	58
2	93	86	80	74	88	81	76	71	73	69	65	65	62	59	58	55	53	49
3	85	76	68	62	80	72	65	60	65	59	55	58	54	50	51	48	46	42
4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	46	43	39	36
5	72	60	52	46	68	57	50	44	52	46	41	47	42	38	42	38	35	32
6	67	54	46	40	63	52	44	39	47	41	36	42	37	33	38	34	31	28
7	62	49	41	35	58	47	40	34	43	36	32	39	33	30	35	31	27	25
8	57	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	25	22	20
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10984	10984	10984	10984
5°	12935	11012	9720	11012
10°	15488	10964	8751	10964
15°	18324	10853	8037	10853
20°	20405	10740	7399	10740
25°	20735	10573	6959	10573
30°	17643	10413	6820	10413
35°	13565	10154	6821	10154
40°	10572	9848	6949	9848
45°	8816	9388	7066	9388
50°	7759	8828	7304	8828
55°	7108	8155	7600	8155
60°	6660	7553	7953	7553
65°	6202	6879	8246	6879
70°	5667	6212	8434	6212
75°	5062	5468	8334	5468
80°	4245	4482	8071	4482
85°	3131	3242	7725	3242



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.5	2.4
10°-20°	408.6	7.5
20°-30°	647.9	11.8
30°-40°	721.0	13.2
40°-50°	656.3	12.0
50°-60°	536.3	9.8
60°-70°	382.9	7.0
70°-80°	210.8	3.8
80°-90°	58.9	1.1
90°-100°	171.0	3.1
100°-110°	355.9	6.5
110°-120°	318.7	5.8
120°-130°	268.1	4.9
130°-140°	223.6	4.1
140°-150°	170.8	3.1
150°-160°	120.0	2.2
160°-170°	70.6	1.3
170°-180°	23.0	0.4
0°-30°	1189.0	21.7
0°-40°	1910.0	34.9
0°-60°	3102.6	56.6
0°-90°	3755.2	68.6
90°-120°	845.6	15.4
90°-150°	1508.1	27.5
90°-180°	1722.0	31.4
0°-180°	5476.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1361	1361	1361	1361	1361	
5°	1596	1359	1199	1359	1596	162
15°	2192	1299	962	1299	2192	619
25°	2328	1187	781	1187	2328	1026
35°	1376	1030	692	1030	1376	874
45°	772	822	619	822	772	608
55°	505	579	540	579	505	456
65°	325	360	432	360	325	321
75°	162	175	267	175	162	173
85°	34	35	83	35	34	41
90°	10	0	10	0	10	9
95°	114	15	114	15	114	176
105°	654	54	654	54	654	647
115°	628	96	628	96	628	624
125°	501	134	501	134	501	456
135°	448	159	448	159	448	346
145°	366	183	366	183	366	232
155°	306	208	306	208	306	143
165°	267	226	267	226	267	77
175°	241	236	241	236	241	23
180°	237	237	237	237	237	



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1448.1	1447.6	1443.1	1442.2	1439.0	1435.0	1434.1	1426.9	1412.4	1405.7	1403.9
5°	1596.2	1607.4	1592.8	1590.0	1588.3	1569.7	1560.1	1548.8	1522.9	1507.7	1495.8
7.5°	1772.9	1774.3	1767.9	1762.7	1748.3	1732.1	1707.8	1681.9	1651.0	1618.9	1594.6
10°	1889.3	1893.8	1886.4	1885.3	1856.6	1838.5	1802.5	1772.1	1737.1	1698.2	1662.7
12.5°	2011.9	2005.6	2001.9	1977.8	1972.5	1939.5	1897.6	1866.3	1812.4	1767.7	1720.4
15°	2192.5	2180.1	2172.2	2138.9	2122.6	2077.0	2032.4	1998.1	1927.6	1860.5	1809.8
17.5°	2298.4	2310.9	2292.6	2278.9	2236.7	2204.7	2159.2	2087.0	2031.9	1948.6	1884.6
20°	2375.1	2376.2	2366.1	2352.0	2318.7	2278.2	2228.5	2149.6	2083.7	2000.8	1912.9
22.5°	2395.8	2396.1	2391.8	2378.6	2353.4	2320.5	2270.5	2204.7	2124.8	2034.7	1946.8
25°	2327.8	2325.5	2330.6	2345.2	2335.7	2325.5	2296.8	2247.7	2173.3	2078.0	1983.4
27.5°	2074.8	2090.3	2119.0	2155.1	2189.8	2216.3	2223.7	2213.7	2167.6	2089.2	1990.1
30°	1892.6	1911.8	1933.2	1969.3	2039.1	2079.2	2123.2	2156.4	2137.8	2075.3	1982.8
32.5°	1692.5	1697.2	1729.0	1770.0	1834.0	1911.0	1980.7	2048.2	2070.6	2037.8	1960.7
35°	1376.4	1384.2	1418.6	1459.2	1537.6	1631.7	1736.5	1830.1	1907.3	1938.3	1898.8
37.5°	1123.2	1145.8	1170.1	1213.7	1282.7	1367.4	1476.3	1597.4	1712.5	1789.6	1802.7
40°	1003.2	1017.3	1034.8	1068.0	1126.7	1210.1	1303.7	1442.3	1564.6	1675.1	1711.2
42.5°	908.6	916.8	927.5	957.6	1002.2	1085.2	1170.6	1292.6	1415.4	1547.4	1607.9
45°	772.2	780.6	798.7	816.1	849.9	907.4	986.9	1087.2	1210.6	1338.1	1449.6
47.5°	673.6	679.1	689.7	708.5	737.2	775.1	839.8	923.6	1038.0	1161.6	1280.5
50°	617.8	622.2	630.7	647.6	669.6	703.4	756.4	834.7	924.3	1048.9	1165.6
52.5°	573.6	575.4	581.6	593.0	610.5	639.0	682.4	747.2	830.5	941.6	1057.8
55°	505.0	507.3	512.9	521.4	536.5	554.6	587.8	636.3	709.1	805.4	906.3
57.5°	448.7	450.2	454.9	458.2	470.8	485.4	510.9	545.6	600.7	682.4	772.5
60°	412.5	411.5	417.1	419.9	428.4	440.8	460.5	493.7	541.6	607.6	690.4
62.5°	377.4	375.9	380.6	384.3	389.1	399.7	415.8	441.9	480.8	540.4	612.0
65°	324.7	322.4	325.2	329.7	334.2	339.9	351.7	374.8	405.8	448.7	503.3
67.5°	271.7	274.0	274.5	276.7	279.3	287.0	295.1	311.4	333.3	367.6	413.9
70°	240.1	240.7	243.0	243.0	244.6	251.4	258.1	267.7	289.1	320.7	358.5
72.5°	208.6	210.9	210.0	211.8	213.0	217.5	222.5	231.6	249.9	273.4	305.2
75°	162.3	164.0	164.0	164.6	166.2	168.0	171.9	178.6	191.6	209.1	231.1
77.5°	118.4	118.6	119.4	121.4	121.4	124.1	127.0	132.5	138.8	150.8	164.2
80°	91.3	92.5	91.9	93.0	93.0	95.2	96.4	103.1	106.0	113.8	124.6
82.5°	66.9	68.1	68.0	69.5	70.4	70.9	72.5	75.2	78.0	85.0	89.4
85°	33.8	35.0	33.8	35.0	36.6	37.2	38.9	39.5	41.7	43.4	47.4
87.5°	11.9	13.2	13.3	13.7	14.5	14.9	15.3	14.8	16.5	17.0	18.6
90°	9.8	9.8	10.2	9.8	9.3	9.3	8.8	8.4	7.9	8.4	7.4
92.5°	35.8	35.8	37.4	39.9	45.4	54.7	68.7	91.3	122.9	147.5	129.1
95°	113.5	119.5	127.9	142.4	165.1	210.2	272.6	344.6	389.7	379.0	286.0
97.5°	303.3	313.0	326.9	355.0	388.3	436.9	482.4	509.2	489.7	399.3	267.7
100°	426.5	430.2	444.2	472.5	513.0	547.4	570.2	560.9	493.0	373.9	242.8
102.5°	533.6	536.6	551.3	571.9	596.7	611.1	604.5	558.3	465.0	342.3	226.0
105°	654.4	657.1	663.7	667.4	666.5	647.4	601.4	520.9	414.4	305.1	211.7
107.5°	699.2	698.0	693.3	682.7	659.7	618.3	553.4	467.8	373.5	284.3	209.0
110°	699.9	695.8	687.4	667.9	634.9	583.7	516.2	435.8	353.0	277.2	209.8



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	678.0	671.2	659.5	635.9	598.3	547.2	483.5	412.4	341.4	273.9	212.0
115°	628.4	624.6	609.8	581.8	545.1	500.4	446.1	388.8	330.7	272.1	216.3
117.5°	578.0	575.1	560.0	536.6	505.2	467.4	424.6	377.2	325.9	271.6	220.8
120°	549.8	544.6	532.6	512.1	485.5	452.5	415.3	372.1	323.3	271.6	224.2
122.5°	527.4	522.3	512.1	494.6	472.1	443.2	409.4	367.6	320.2	271.3	227.6
125°	501.3	498.6	489.8	476.2	457.6	432.0	400.0	360.0	315.4	270.7	232.5
127.5°	486.1	483.3	475.9	463.9	445.2	420.9	388.9	350.7	308.8	269.6	236.5
130°	477.2	474.4	466.9	455.3	436.3	411.6	380.0	343.2	304.6	269.3	239.5
132.5°	467.2	464.3	457.3	444.2	425.4	400.8	369.9	335.4	300.9	268.9	242.1
135°	448.3	445.6	438.1	425.1	406.5	383.2	354.9	324.7	295.3	268.3	246.1
137.5°	425.1	421.8	415.6	402.8	385.4	364.4	340.5	314.9	290.5	268.2	248.3
140°	408.4	404.6	398.1	387.9	371.6	352.0	331.2	309.2	287.9	267.9	250.2
142.5°	390.4	387.9	382.1	372.6	358.2	341.3	323.3	304.1	285.7	267.9	251.7
145°	366.0	363.7	359.1	351.1	339.5	326.5	312.5	296.7	281.8	266.9	252.6
147.5°	344.4	343.5	340.0	333.2	324.7	314.4	303.2	290.7	278.4	265.3	253.0
150°	332.1	331.6	328.8	322.8	315.4	307.0	297.7	287.0	275.8	264.2	253.0
152.5°	320.9	320.4	318.8	313.8	307.5	300.6	292.0	282.8	272.8	262.3	252.3
155°	306.5	306.5	305.1	301.4	296.7	291.1	284.1	276.7	268.3	259.5	251.1
157.5°	293.8	293.8	293.0	290.2	286.7	282.2	276.4	270.1	263.8	256.7	250.0
160°	286.0	286.0	285.6	282.7	280.0	276.2	271.2	266.0	260.5	254.4	248.8
162.5°	278.6	279.0	278.5	275.7	273.7	270.3	266.3	262.0	257.5	252.2	247.7
165°	267.4	267.9	268.3	266.5	264.6	262.3	259.0	256.2	252.6	248.8	245.6
167.5°	258.6	258.9	259.0	257.9	256.9	255.5	252.9	250.8	248.1	245.5	243.4
170°	253.0	253.0	253.5	253.0	252.1	250.7	248.8	247.4	245.1	243.2	241.8
172.5°	247.4	248.2	248.7	248.2	247.6	246.6	245.5	244.4	242.5	241.0	240.4
175°	240.9	241.8	242.8	241.8	241.8	241.8	240.9	240.4	239.5	238.6	238.6
177.5°	237.1	237.8	238.6	238.2	238.6	238.2	238.2	237.8	237.5	237.1	237.1
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1404.4	1398.0	1393.5	1389.9	1380.0	1374.1	1369.6	1363.3	1356.1	1348.4	1339.0
5°	1484.0	1464.8	1450.7	1429.4	1409.1	1392.1	1374.7	1358.9	1339.7	1318.9	1303.7
7.5°	1567.7	1539.3	1502.8	1471.0	1435.4	1404.4	1376.7	1348.3	1318.7	1290.1	1263.9
10°	1621.0	1584.4	1543.8	1495.8	1450.7	1410.7	1373.5	1337.5	1302.5	1267.5	1237.7
12.5°	1678.2	1632.6	1572.6	1516.6	1466.1	1412.6	1367.7	1323.5	1281.3	1244.6	1209.7
15°	1755.1	1689.1	1619.8	1544.9	1478.4	1415.8	1354.4	1298.6	1251.2	1202.7	1169.0
17.5°	1802.4	1720.8	1641.5	1563.2	1482.6	1403.8	1337.5	1273.1	1213.8	1165.7	1123.1
20°	1833.4	1752.3	1653.7	1575.3	1479.5	1398.3	1321.7	1250.1	1188.1	1136.9	1092.8
22.5°	1860.5	1766.8	1668.1	1565.0	1469.6	1383.5	1299.6	1227.6	1164.2	1110.2	1068.0
25°	1875.2	1767.5	1660.4	1557.9	1449.6	1347.6	1271.5	1187.0	1119.3	1062.4	1017.3
27.5°	1876.7	1761.6	1640.5	1526.5	1414.8	1319.8	1223.8	1148.2	1078.0	1017.8	974.5
30°	1871.8	1751.8	1621.5	1498.1	1385.9	1282.8	1199.4	1117.1	1045.5	985.8	940.7
32.5°	1856.0	1731.0	1597.2	1466.6	1350.3	1249.4	1163.4	1085.1	1015.3	956.4	909.1
35°	1810.4	1686.9	1544.3	1408.5	1289.6	1187.6	1109.8	1030.3	960.4	904.6	859.0
37.5°	1739.0	1627.4	1482.5	1341.9	1225.1	1122.6	1045.5	973.7	910.7	854.0	807.2
40°	1676.7	1578.7	1433.3	1296.3	1170.1	1072.6	1000.5	934.5	872.0	818.4	773.9
42.5°	1605.1	1519.6	1385.5	1240.4	1118.7	1020.8	950.4	891.2	832.3	782.8	738.3
45°	1477.2	1420.9	1294.6	1160.5	1033.7	941.3	874.2	822.3	772.7	724.2	687.1
47.5°	1330.2	1302.3	1196.0	1068.6	948.3	857.1	799.0	751.1	707.6	666.5	633.7
50°	1231.5	1218.0	1126.1	1003.2	888.3	802.6	744.0	702.9	665.6	629.6	598.6
52.5°	1134.1	1133.7	1050.8	938.3	831.9	749.4	691.2	652.8	620.5	591.3	563.4
55°	985.2	1001.0	936.2	835.8	740.6	666.2	613.8	579.4	556.8	532.6	511.8
57.5°	848.5	874.7	821.2	732.8	653.4	584.8	539.2	513.3	489.3	474.7	459.5
60°	759.2	784.0	742.3	667.9	593.0	534.3	490.9	467.8	446.9	436.8	426.1
62.5°	679.9	702.0	671.1	602.1	537.0	480.6	444.0	421.8	407.7	396.6	389.6
65°	566.5	585.1	558.6	508.4	452.6	407.5	377.6	360.1	346.7	342.1	334.2
67.5°	457.9	474.8	460.5	417.8	373.1	339.0	315.6	298.8	290.8	286.9	281.3
70°	393.4	410.3	395.1	357.9	323.5	294.8	272.8	263.2	254.8	253.1	245.2
72.5°	338.8	350.3	335.2	306.1	276.6	252.4	235.4	225.3	220.9	217.9	213.6
75°	254.2	264.3	254.2	231.6	210.8	193.9	179.2	175.3	170.2	168.5	165.7
77.5°	179.9	188.7	180.9	166.8	151.2	138.2	130.3	125.2	124.1	121.2	122.5
80°	137.5	143.2	135.8	126.3	113.8	104.8	99.2	96.4	93.0	91.9	94.1
82.5°	98.7	101.3	97.5	91.1	81.9	76.0	72.2	68.9	68.2	68.4	68.4
85°	51.3	50.7	50.1	44.5	41.7	37.7	35.5	35.0	34.4	35.5	36.6
87.5°	18.4	18.9	17.9	16.1	14.6	13.2	12.5	11.8	12.5	13.2	13.7
90°	6.5	6.5	3.8	3.8	3.3	2.8	1.4	0.5	1.4	2.8	3.3
92.5°	93.9	57.9	34.2	24.5	17.8	12.1	7.7	5.3	7.7	12.1	17.8
95°	174.9	98.6	58.1	38.6	27.5	21.4	16.7	15.3	16.7	21.4	27.5
97.5°	157.2	94.2	63.1	46.7	37.1	31.6	27.6	27.6	27.6	31.6	37.1
100°	147.9	95.3	67.9	53.0	44.2	38.6	35.4	35.4	35.4	38.6	44.2
102.5°	145.3	99.1	74.2	60.1	51.6	46.4	43.5	42.8	43.5	46.4	51.6
105°	146.5	107.9	85.6	72.1	63.8	58.1	55.8	54.4	55.8	58.1	63.8
107.5°	153.4	118.2	97.8	84.5	76.5	70.5	68.2	67.3	68.2	70.5	76.5
110°	158.6	126.0	105.6	93.0	84.6	79.1	76.7	75.8	76.7	79.1	84.6



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	164.2	133.5	113.7	101.2	92.9	87.6	85.0	84.0	85.0	87.6	92.9
115°	173.0	145.1	126.5	114.0	105.1	100.4	97.2	95.8	97.2	100.4	105.1
117.5°	182.1	156.4	138.7	125.6	117.4	112.3	109.4	108.1	109.4	112.3	117.4
120°	188.3	164.2	146.5	133.5	125.6	120.4	117.2	116.3	117.2	120.4	125.6
122.5°	194.3	171.6	153.9	141.3	132.6	127.9	124.7	123.7	124.7	127.9	132.6
125°	203.3	181.8	165.1	152.1	143.2	138.1	135.3	133.5	135.3	138.1	143.2
127.5°	211.0	191.4	175.1	162.0	152.8	147.0	143.7	142.1	143.7	147.0	152.8
130°	215.8	197.6	181.8	168.4	159.6	152.5	148.8	147.0	148.8	152.5	159.6
132.5°	220.6	202.8	187.0	174.3	164.8	158.2	153.3	151.8	153.3	158.2	164.8
135°	227.0	210.2	194.9	182.8	173.0	165.1	160.5	158.6	160.5	165.1	173.0
137.5°	231.5	215.8	201.5	190.0	179.8	172.3	167.1	165.4	167.1	172.3	179.8
140°	234.4	219.6	205.5	194.4	184.7	176.8	171.6	170.2	171.6	176.8	184.7
142.5°	236.6	222.9	209.3	198.5	189.1	181.6	176.8	175.5	176.8	181.6	189.1
145°	239.0	226.5	214.4	204.2	195.3	188.8	184.2	182.8	184.2	188.8	195.3
147.5°	241.2	230.2	218.9	209.7	202.3	195.6	191.5	191.0	191.5	195.6	202.3
150°	242.3	232.1	221.8	213.0	206.0	200.5	196.7	196.2	196.7	200.5	206.0
152.5°	243.0	233.6	224.5	216.4	210.1	204.9	201.2	201.1	201.2	204.9	210.1
155°	243.7	235.8	227.9	220.9	215.8	211.2	208.4	207.9	208.4	211.2	215.8
157.5°	243.7	237.4	230.6	225.2	220.7	217.1	214.5	214.5	214.5	217.1	220.7
160°	243.7	238.1	232.5	227.4	223.7	220.5	218.6	218.6	218.6	220.5	223.7
162.5°	243.7	238.9	233.7	229.7	226.3	223.4	221.9	222.3	221.9	223.4	226.3
165°	242.8	239.0	234.9	232.1	229.8	227.4	226.5	226.5	226.5	227.4	229.8
167.5°	241.7	239.0	235.9	233.7	232.4	230.6	230.2	230.6	230.2	230.6	232.4
170°	240.9	238.6	236.3	234.9	233.9	232.5	232.1	232.5	232.1	232.5	233.9
172.5°	240.2	238.2	236.6	235.6	235.1	234.0	233.9	234.4	233.9	234.0	235.1
175°	239.0	237.7	236.8	236.8	236.3	235.8	235.8	236.3	235.8	235.8	236.3
177.5°	237.8	237.1	236.8	236.8	236.8	236.4	236.8	237.1	236.8	236.4	236.8
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1334.4	1330.4	1324.5	1316.4	1309.6	1302.4	1300.6	1297.9	1303.3	1298.8	1297.5
5°	1290.7	1278.9	1263.6	1246.2	1236.0	1221.4	1218.5	1212.9	1207.3	1206.7	1201.1
7.5°	1244.4	1227.0	1207.1	1189.3	1172.8	1156.7	1146.3	1144.0	1135.7	1130.8	1125.2
10°	1214.6	1193.2	1170.1	1153.2	1134.0	1117.1	1105.3	1098.5	1092.8	1086.6	1081.0
12.5°	1179.4	1156.7	1137.6	1119.3	1096.6	1083.7	1064.2	1052.5	1051.4	1051.5	1036.8
15°	1138.5	1116.0	1086.6	1060.7	1048.3	1023.5	1012.8	999.3	990.8	982.4	975.7
17.5°	1091.8	1063.6	1040.8	1011.1	987.3	967.6	953.6	945.4	932.7	920.7	912.1
20°	1062.4	1032.6	1008.3	976.7	950.8	926.6	914.8	903.5	893.9	883.8	874.2
22.5°	1032.7	1001.4	971.8	941.1	917.0	891.4	880.0	864.7	855.6	849.9	840.3
25°	985.8	951.9	918.1	888.8	864.1	841.5	826.3	814.4	804.3	799.8	793.6
27.5°	934.8	901.2	868.5	835.3	807.1	790.8	778.6	769.6	763.9	757.8	755.0
30°	902.4	867.4	832.5	801.4	775.5	759.2	748.0	741.8	737.2	734.4	731.6
32.5°	869.4	834.9	798.2	769.9	746.7	732.1	723.6	717.4	715.1	714.1	713.1
35°	816.7	781.7	748.0	722.6	700.6	695.0	687.6	684.2	683.1	687.1	688.8
37.5°	765.6	733.2	702.1	677.4	663.1	654.8	652.3	652.5	656.5	660.0	664.1
40°	732.7	701.2	671.8	650.4	636.9	631.9	630.7	633.5	638.1	642.0	646.5
42.5°	700.7	669.6	642.9	622.9	613.4	608.8	609.5	612.3	618.6	623.5	630.2
45°	651.0	625.1	599.2	582.8	574.9	576.0	576.0	581.1	587.3	594.6	601.9
47.5°	604.2	578.0	556.8	543.0	538.9	537.9	541.1	547.7	556.6	565.7	575.9
50°	572.7	547.8	529.2	516.8	512.3	514.0	518.5	524.7	535.4	546.7	557.4
52.5°	540.6	518.0	500.8	489.3	486.2	489.3	493.7	503.5	512.9	525.1	538.0
55°	490.9	471.7	458.2	449.8	448.7	450.4	455.4	466.1	479.6	494.9	507.3
57.5°	441.4	425.4	413.0	407.2	407.7	409.3	417.7	430.4	444.8	461.1	477.0
60°	408.1	393.4	383.3	378.8	379.3	382.7	392.8	404.7	422.7	438.5	455.4
62.5°	376.5	363.6	353.9	349.9	349.1	356.5	366.2	378.5	396.6	414.2	432.4
65°	325.8	315.6	307.8	305.5	307.2	312.8	325.2	341.5	356.8	375.4	394.5
67.5°	276.1	267.8	262.4	263.4	265.5	273.8	284.2	298.2	315.5	334.8	353.8
70°	244.6	236.7	232.2	232.8	236.2	246.3	255.4	269.4	288.0	307.8	323.5
72.5°	212.1	206.9	202.9	205.3	208.6	215.6	226.9	241.0	257.4	275.7	292.4
75°	162.9	162.9	160.6	162.3	167.4	174.1	182.6	197.3	213.6	228.3	241.8
77.5°	120.8	119.6	121.1	123.1	126.0	134.0	143.7	154.2	166.5	181.2	192.3
80°	92.5	93.0	95.8	99.2	100.4	106.6	116.7	126.3	135.8	148.2	158.9
82.5°	69.5	70.0	71.5	75.7	76.9	83.6	90.1	99.6	108.4	116.7	125.6
85°	37.7	37.7	40.6	42.2	45.1	49.6	53.6	59.2	67.1	72.7	81.1
87.5°	15.2	15.2	17.5	18.4	20.0	22.4	23.2	28.3	30.2	32.5	36.6
90°	3.8	3.8	6.5	6.5	7.4	8.4	7.9	8.4	8.8	9.3	9.3
92.5°	24.5	34.2	57.9	93.9	129.1	147.5	122.9	91.3	68.7	54.7	45.4
95°	38.6	58.1	98.6	174.9	286.0	379.0	389.7	344.6	272.6	210.2	165.1
97.5°	46.7	63.1	94.2	157.2	267.7	399.3	489.7	509.2	482.4	436.9	388.3
100°	53.0	67.9	95.3	147.9	242.8	373.9	493.0	560.9	570.2	547.4	513.0
102.5°	60.1	74.2	99.1	145.3	226.0	342.3	465.0	558.3	604.5	611.1	596.7
105°	72.1	85.6	107.9	146.5	211.7	305.1	414.4	520.9	601.4	647.4	666.5
107.5°	84.5	97.8	118.2	153.4	209.0	284.3	373.5	467.8	553.4	618.3	659.7
110°	93.0	105.6	126.0	158.6	209.8	277.2	353.0	435.8	516.2	583.7	634.9



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	101.2	113.7	133.5	164.2	212.0	273.9	341.4	412.4	483.5	547.2	598.3
115°	114.0	126.5	145.1	173.0	216.3	272.1	330.7	388.8	446.1	500.4	545.1
117.5°	125.6	138.7	156.4	182.1	220.8	271.6	325.9	377.2	424.6	467.4	505.2
120°	133.5	146.5	164.2	188.3	224.2	271.6	323.3	372.1	415.3	452.5	485.5
122.5°	141.3	153.9	171.6	194.3	227.6	271.3	320.2	367.6	409.4	443.2	472.1
125°	152.1	165.1	181.8	203.3	232.5	270.7	315.4	360.0	400.0	432.0	457.6
127.5°	162.0	175.1	191.4	211.0	236.5	269.6	308.8	350.7	388.9	420.9	445.2
130°	168.4	181.8	197.6	215.8	239.5	269.3	304.6	343.2	380.0	411.6	436.3
132.5°	174.3	187.0	202.8	220.6	242.1	268.9	300.9	335.4	369.9	400.8	425.4
135°	182.8	194.9	210.2	227.0	246.1	268.3	295.3	324.7	354.9	383.2	406.5
137.5°	190.0	201.5	215.8	231.5	248.3	268.2	290.5	314.9	340.5	364.4	385.4
140°	194.4	205.5	219.6	234.4	250.2	267.9	287.9	309.2	331.2	352.0	371.6
142.5°	198.5	209.3	222.9	236.6	251.7	267.9	285.7	304.1	323.3	341.3	358.2
145°	204.2	214.4	226.5	239.0	252.6	266.9	281.8	296.7	312.5	326.5	339.5
147.5°	209.7	218.9	230.2	241.2	253.0	265.3	278.4	290.7	303.2	314.4	324.7
150°	213.0	221.8	232.1	242.3	253.0	264.2	275.8	287.0	297.7	307.0	315.4
152.5°	216.4	224.5	233.6	243.0	252.3	262.3	272.8	282.8	292.0	300.6	307.5
155°	220.9	227.9	235.8	243.7	251.1	259.5	268.3	276.7	284.1	291.1	296.7
157.5°	225.2	230.6	237.4	243.7	250.0	256.7	263.8	270.1	276.4	282.2	286.7
160°	227.4	232.5	238.1	243.7	248.8	254.4	260.5	266.0	271.2	276.2	280.0
162.5°	229.7	233.7	238.9	243.7	247.7	252.2	257.5	262.0	266.3	270.3	273.7
165°	232.1	234.9	239.0	242.8	245.6	248.8	252.6	256.2	259.0	262.3	264.6
167.5°	233.7	235.9	239.0	241.7	243.4	245.5	248.1	250.8	252.9	255.5	256.9
170°	234.9	236.3	238.6	240.9	241.8	243.2	245.1	247.4	248.8	250.7	252.1
172.5°	235.6	236.6	238.2	240.2	240.4	241.0	242.5	244.4	245.5	246.6	247.6
175°	236.8	236.8	237.7	239.0	238.6	238.6	239.5	240.4	240.9	241.8	241.8
177.5°	236.8	236.8	237.1	237.8	237.1	237.1	237.5	237.8	238.2	238.2	238.6
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1296.6	1295.7	1292.5	1292.1	1292.5	1295.7	1296.6	1297.5	1298.8	1303.3	1297.9
5°	1197.7	1194.9	1193.2	1199.4	1193.2	1194.9	1197.7	1201.1	1206.7	1207.3	1212.9
7.5°	1123.2	1121.0	1116.0	1114.4	1116.0	1121.0	1123.2	1125.2	1130.8	1135.7	1144.0
10°	1075.4	1073.1	1068.6	1067.5	1068.6	1073.1	1075.4	1081.0	1086.6	1092.8	1098.5
12.5°	1029.4	1024.9	1024.0	1025.1	1024.0	1024.9	1029.4	1036.8	1051.5	1051.4	1052.5
15°	968.3	966.0	959.9	961.6	959.9	966.0	968.3	975.7	982.4	990.8	999.3
17.5°	908.1	905.4	897.9	904.5	897.9	905.4	908.1	912.1	920.7	932.7	945.4
20°	870.3	865.7	861.8	861.2	861.8	865.7	870.3	874.2	883.8	893.9	903.5
22.5°	834.1	830.1	829.7	826.1	829.7	830.1	834.1	840.3	849.9	855.6	864.7
25°	789.0	785.1	784.0	781.2	784.0	785.1	789.0	793.6	799.8	804.3	814.4
27.5°	754.5	752.5	750.5	751.4	750.5	752.5	754.5	755.0	757.8	763.9	769.6
30°	733.3	732.7	731.6	731.6	731.6	732.7	733.3	731.6	734.4	737.2	741.8
32.5°	715.7	715.6	716.2	716.2	716.2	715.6	715.7	713.1	714.1	715.1	717.4
35°	691.0	692.7	693.8	692.1	693.8	692.7	691.0	688.8	687.1	683.1	684.2
37.5°	668.7	670.3	672.0	673.8	672.0	670.3	668.7	664.1	660.0	656.5	652.5
40°	651.5	655.5	656.6	659.4	656.6	655.5	651.5	646.5	642.0	638.1	633.5
42.5°	635.3	639.7	642.6	643.2	642.6	639.7	635.3	630.2	623.5	618.6	612.3
45°	610.4	614.9	618.9	618.9	618.9	614.9	610.4	601.9	594.6	587.3	581.1
47.5°	584.6	591.1	595.1	596.1	595.1	591.1	584.6	575.9	565.7	556.6	547.7
50°	567.0	574.9	578.9	581.6	578.9	574.9	567.0	557.4	546.7	535.4	524.7
52.5°	549.8	557.7	563.0	564.5	563.0	557.7	549.8	538.0	525.1	512.9	503.5
55°	520.2	531.5	537.7	540.0	537.7	531.5	520.2	507.3	494.9	479.6	466.1
57.5°	492.3	502.6	509.9	511.5	509.9	502.6	492.3	477.0	461.1	444.8	430.4
60°	470.6	481.9	490.9	492.6	490.9	481.9	470.6	455.4	438.5	422.7	404.7
62.5°	448.5	460.2	468.4	472.8	468.4	460.2	448.5	432.4	414.2	396.6	378.5
65°	410.3	422.2	430.1	431.7	430.1	422.2	410.3	394.5	375.4	356.8	341.5
67.5°	368.6	380.4	385.6	388.9	385.6	380.4	368.6	353.8	334.8	315.5	298.2
70°	339.3	348.9	354.5	357.3	354.5	348.9	339.3	323.5	307.8	288.0	269.4
72.5°	305.9	315.9	322.5	323.1	322.5	315.9	305.9	292.4	275.7	257.4	241.0
75°	254.8	263.7	267.2	267.2	267.2	263.7	254.8	241.8	228.3	213.6	197.3
77.5°	201.6	206.3	210.6	211.5	210.6	206.3	201.6	192.3	181.2	166.5	154.2
80°	167.4	170.2	173.6	173.6	173.6	170.2	167.4	158.9	148.2	135.8	126.3
82.5°	132.2	134.6	137.9	137.5	137.9	134.6	132.2	125.6	116.7	108.4	99.6
85°	80.1	85.1	84.5	83.4	84.5	85.1	80.1	81.1	72.7	67.1	59.2
87.5°	38.0	38.6	39.9	40.8	39.9	38.6	38.0	36.6	32.5	30.2	28.3
90°	9.8	10.2	9.8	9.8	9.8	10.2	9.8	9.3	9.3	8.8	8.4
92.5°	39.9	37.4	35.8	35.8	35.8	37.4	39.9	45.4	54.7	68.7	91.3
95°	142.4	127.9	119.5	113.5	119.5	127.9	142.4	165.1	210.2	272.6	344.6
97.5°	355.0	326.9	313.0	303.3	313.0	326.9	355.0	388.3	436.9	482.4	509.2
100°	472.5	444.2	430.2	426.5	430.2	444.2	472.5	513.0	547.4	570.2	560.9
102.5°	571.9	551.3	536.6	533.6	536.6	551.3	571.9	596.7	611.1	604.5	558.3
105°	667.4	663.7	657.1	654.4	657.1	663.7	667.4	666.5	647.4	601.4	520.9
107.5°	682.7	693.3	698.0	699.2	698.0	693.3	682.7	659.7	618.3	553.4	467.8
110°	667.9	687.4	695.8	699.9	695.8	687.4	667.9	634.9	583.7	516.2	435.8



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	635.9	659.5	671.2	678.0	671.2	659.5	635.9	598.3	547.2	483.5	412.4
115°	581.8	609.8	624.6	628.4	624.6	609.8	581.8	545.1	500.4	446.1	388.8
117.5°	536.6	560.0	575.1	578.0	575.1	560.0	536.6	505.2	467.4	424.6	377.2
120°	512.1	532.6	544.6	549.8	544.6	532.6	512.1	485.5	452.5	415.3	372.1
122.5°	494.6	512.1	522.3	527.4	522.3	512.1	494.6	472.1	443.2	409.4	367.6
125°	476.2	489.8	498.6	501.3	498.6	489.8	476.2	457.6	432.0	400.0	360.0
127.5°	463.9	475.9	483.3	486.1	483.3	475.9	463.9	445.2	420.9	388.9	350.7
130°	455.3	466.9	474.4	477.2	474.4	466.9	455.3	436.3	411.6	380.0	343.2
132.5°	444.2	457.3	464.3	467.2	464.3	457.3	444.2	425.4	400.8	369.9	335.4
135°	425.1	438.1	445.6	448.3	445.6	438.1	425.1	406.5	383.2	354.9	324.7
137.5°	402.8	415.6	421.8	425.1	421.8	415.6	402.8	385.4	364.4	340.5	314.9
140°	387.9	398.1	404.6	408.4	404.6	398.1	387.9	371.6	352.0	331.2	309.2
142.5°	372.6	382.1	387.9	390.4	387.9	382.1	372.6	358.2	341.3	323.3	304.1
145°	351.1	359.1	363.7	366.0	363.7	359.1	351.1	339.5	326.5	312.5	296.7
147.5°	333.2	340.0	343.5	344.4	343.5	340.0	333.2	324.7	314.4	303.2	290.7
150°	322.8	328.8	331.6	332.1	331.6	328.8	322.8	315.4	307.0	297.7	287.0
152.5°	313.8	318.8	320.4	320.9	320.4	318.8	313.8	307.5	300.6	292.0	282.8
155°	301.4	305.1	306.5	306.5	306.5	305.1	301.4	296.7	291.1	284.1	276.7
157.5°	290.2	293.0	293.8	293.8	293.8	293.0	290.2	286.7	282.2	276.4	270.1
160°	282.7	285.6	286.0	286.0	286.0	285.6	282.7	280.0	276.2	271.2	266.0
162.5°	275.7	278.5	279.0	278.6	279.0	278.5	275.7	273.7	270.3	266.3	262.0
165°	266.5	268.3	267.9	267.4	267.9	268.3	266.5	264.6	262.3	259.0	256.2
167.5°	257.9	259.0	258.9	258.6	258.9	259.0	257.9	256.9	255.5	252.9	250.8
170°	253.0	253.5	253.0	253.0	253.0	253.5	253.0	252.1	250.7	248.8	247.4
172.5°	248.2	248.7	248.2	247.4	248.2	248.7	248.2	247.6	246.6	245.5	244.4
175°	241.8	242.8	241.8	240.9	241.8	242.8	241.8	241.8	241.8	240.9	240.4
177.5°	238.2	238.6	237.8	237.1	237.8	238.6	238.2	238.6	238.2	238.2	237.8
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332636-930
 CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1300.6	1302.4	1309.6	1316.4	1324.5	1330.4	1334.4	1339.0	1348.4	1356.1	1363.3
5°	1218.5	1221.4	1236.0	1246.2	1263.6	1278.9	1290.7	1303.7	1318.9	1339.7	1358.9
7.5°	1146.3	1156.7	1172.8	1189.3	1207.1	1227.0	1244.4	1263.9	1290.1	1318.7	1348.3
10°	1105.3	1117.1	1134.0	1153.2	1170.1	1193.2	1214.6	1237.7	1267.5	1302.5	1337.5
12.5°	1064.2	1083.7	1096.6	1119.3	1137.6	1156.7	1179.4	1209.7	1244.6	1281.3	1323.5
15°	1012.8	1023.5	1048.3	1060.7	1086.6	1116.0	1138.5	1169.0	1202.7	1251.2	1298.6
17.5°	953.6	967.6	987.3	1011.1	1040.8	1063.6	1091.8	1123.1	1165.7	1213.8	1273.1
20°	914.8	926.6	950.8	976.7	1008.3	1032.6	1062.4	1092.8	1136.9	1188.1	1250.1
22.5°	880.0	891.4	917.0	941.1	971.8	1001.4	1032.7	1068.0	1110.2	1164.2	1227.6
25°	826.3	841.5	864.1	888.8	918.1	951.9	985.8	1017.3	1062.4	1119.3	1187.0
27.5°	778.6	790.8	807.1	835.3	868.5	901.2	934.8	974.5	1017.8	1078.0	1148.2
30°	748.0	759.2	775.5	801.4	832.5	867.4	902.4	940.7	985.8	1045.5	1117.1
32.5°	723.6	732.1	746.7	769.9	798.2	834.9	869.4	909.1	956.4	1015.3	1085.1
35°	687.6	695.0	700.6	722.6	748.0	781.7	816.7	859.0	904.6	960.4	1030.3
37.5°	652.3	654.8	663.1	677.4	702.1	733.2	765.6	807.2	854.0	910.7	973.7
40°	630.7	631.9	636.9	650.4	671.8	701.2	732.7	773.9	818.4	872.0	934.5
42.5°	609.5	608.8	613.4	622.9	642.9	669.6	700.7	738.3	782.8	832.3	891.2
45°	576.0	576.0	574.9	582.8	599.2	625.1	651.0	687.1	724.2	772.7	822.3
47.5°	541.1	537.9	538.9	543.0	556.8	578.0	604.2	633.7	666.5	707.6	751.1
50°	518.5	514.0	512.3	516.8	529.2	547.8	572.7	598.6	629.6	665.6	702.9
52.5°	493.7	489.3	486.2	489.3	500.8	518.0	540.6	563.4	591.3	620.5	652.8
55°	455.4	450.4	448.7	449.8	458.2	471.7	490.9	511.8	532.6	556.8	579.4
57.5°	417.7	409.3	407.7	407.2	413.0	425.4	441.4	459.5	474.7	489.3	513.3
60°	392.8	382.7	379.3	378.8	383.3	393.4	408.1	426.1	436.8	446.9	467.8
62.5°	366.2	356.5	349.1	349.9	353.9	363.6	376.5	389.6	396.6	407.7	421.8
65°	325.2	312.8	307.2	305.5	307.8	315.6	325.8	334.2	342.1	346.7	360.1
67.5°	284.2	273.8	265.5	263.4	262.4	267.8	276.1	281.3	286.9	290.8	298.8
70°	255.4	246.3	236.2	232.8	232.2	236.7	244.6	245.2	253.1	254.8	263.2
72.5°	226.9	215.6	208.6	205.3	202.9	206.9	212.1	213.6	217.9	220.9	225.3
75°	182.6	174.1	167.4	162.3	160.6	162.9	162.9	165.7	168.5	170.2	175.3
77.5°	143.7	134.0	126.0	123.1	121.1	119.6	120.8	122.5	121.2	124.1	125.2
80°	116.7	106.6	100.4	99.2	95.8	93.0	92.5	94.1	91.9	93.0	96.4
82.5°	90.1	83.6	76.9	75.7	71.5	70.0	69.5	68.4	68.4	68.2	68.9
85°	53.6	49.6	45.1	42.2	40.6	37.7	37.7	36.6	35.5	34.4	35.0
87.5°	23.2	22.4	20.0	18.4	17.5	15.2	15.2	13.7	13.2	12.5	11.8
90°	7.9	8.4	7.4	6.5	6.5	3.8	3.8	3.3	2.8	1.4	0.5
92.5°	122.9	147.5	129.1	93.9	57.9	34.2	24.5	17.8	12.1	7.7	5.3
95°	389.7	379.0	286.0	174.9	98.6	58.1	38.6	27.5	21.4	16.7	15.3
97.5°	489.7	399.3	267.7	157.2	94.2	63.1	46.7	37.1	31.6	27.6	27.6
100°	493.0	373.9	242.8	147.9	95.3	67.9	53.0	44.2	38.6	35.4	35.4
102.5°	465.0	342.3	226.0	145.3	99.1	74.2	60.1	51.6	46.4	43.5	42.8
105°	414.4	305.1	211.7	146.5	107.9	85.6	72.1	63.8	58.1	55.8	54.4
107.5°	373.5	284.3	209.0	153.4	118.2	97.8	84.5	76.5	70.5	68.2	67.3
110°	353.0	277.2	209.8	158.6	126.0	105.6	93.0	84.6	79.1	76.7	75.8



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	341.4	273.9	212.0	164.2	133.5	113.7	101.2	92.9	87.6	85.0	84.0
115°	330.7	272.1	216.3	173.0	145.1	126.5	114.0	105.1	100.4	97.2	95.8
117.5°	325.9	271.6	220.8	182.1	156.4	138.7	125.6	117.4	112.3	109.4	108.1
120°	323.3	271.6	224.2	188.3	164.2	146.5	133.5	125.6	120.4	117.2	116.3
122.5°	320.2	271.3	227.6	194.3	171.6	153.9	141.3	132.6	127.9	124.7	123.7
125°	315.4	270.7	232.5	203.3	181.8	165.1	152.1	143.2	138.1	135.3	133.5
127.5°	308.8	269.6	236.5	211.0	191.4	175.1	162.0	152.8	147.0	143.7	142.1
130°	304.6	269.3	239.5	215.8	197.6	181.8	168.4	159.6	152.5	148.8	147.0
132.5°	300.9	268.9	242.1	220.6	202.8	187.0	174.3	164.8	158.2	153.3	151.8
135°	295.3	268.3	246.1	227.0	210.2	194.9	182.8	173.0	165.1	160.5	158.6
137.5°	290.5	268.2	248.3	231.5	215.8	201.5	190.0	179.8	172.3	167.1	165.4
140°	287.9	267.9	250.2	234.4	219.6	205.5	194.4	184.7	176.8	171.6	170.2
142.5°	285.7	267.9	251.7	236.6	222.9	209.3	198.5	189.1	181.6	176.8	175.5
145°	281.8	266.9	252.6	239.0	226.5	214.4	204.2	195.3	188.8	184.2	182.8
147.5°	278.4	265.3	253.0	241.2	230.2	218.9	209.7	202.3	195.6	191.5	191.0
150°	275.8	264.2	253.0	242.3	232.1	221.8	213.0	206.0	200.5	196.7	196.2
152.5°	272.8	262.3	252.3	243.0	233.6	224.5	216.4	210.1	204.9	201.2	201.1
155°	268.3	259.5	251.1	243.7	235.8	227.9	220.9	215.8	211.2	208.4	207.9
157.5°	263.8	256.7	250.0	243.7	237.4	230.6	225.2	220.7	217.1	214.5	214.5
160°	260.5	254.4	248.8	243.7	238.1	232.5	227.4	223.7	220.5	218.6	218.6
162.5°	257.5	252.2	247.7	243.7	238.9	233.7	229.7	226.3	223.4	221.9	222.3
165°	252.6	248.8	245.6	242.8	239.0	234.9	232.1	229.8	227.4	226.5	226.5
167.5°	248.1	245.5	243.4	241.7	239.0	235.9	233.7	232.4	230.6	230.2	230.6
170°	245.1	243.2	241.8	240.9	238.6	236.3	234.9	233.9	232.5	232.1	232.5
172.5°	242.5	241.0	240.4	240.2	238.2	236.6	235.6	235.1	234.0	233.9	234.4
175°	239.5	238.6	238.6	239.0	237.7	236.8	236.8	236.3	235.8	235.8	236.3
177.5°	237.5	237.1	237.1	237.8	237.1	236.8	236.8	236.8	236.4	236.8	237.1
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1369.6	1374.1	1380.0	1389.9	1393.5	1398.0	1404.4	1403.9	1405.7	1412.4	1426.9
5°	1374.7	1392.1	1409.1	1429.4	1450.7	1464.8	1484.0	1495.8	1507.7	1522.9	1548.8
7.5°	1376.7	1404.4	1435.4	1471.0	1502.8	1539.3	1567.7	1594.6	1618.9	1651.0	1681.9
10°	1373.5	1410.7	1450.7	1495.8	1543.8	1584.4	1621.0	1662.7	1698.2	1737.1	1772.1
12.5°	1367.7	1412.6	1466.1	1516.6	1572.6	1632.6	1678.2	1720.4	1767.7	1812.4	1866.3
15°	1354.4	1415.8	1478.4	1544.9	1619.8	1689.1	1755.1	1809.8	1860.5	1927.6	1998.1
17.5°	1337.5	1403.8	1482.6	1563.2	1641.5	1720.8	1802.4	1884.6	1948.6	2031.9	2087.0
20°	1321.7	1398.3	1479.5	1575.3	1653.7	1752.3	1833.4	1912.9	2000.8	2083.7	2149.6
22.5°	1299.6	1383.5	1469.6	1565.0	1668.1	1766.8	1860.5	1946.8	2034.7	2124.8	2204.7
25°	1271.5	1347.6	1449.6	1557.9	1660.4	1767.5	1875.2	1983.4	2078.0	2173.3	2247.7
27.5°	1223.8	1319.8	1414.8	1526.5	1640.5	1761.6	1876.7	1990.1	2089.2	2167.6	2213.7
30°	1199.4	1282.8	1385.9	1498.1	1621.5	1751.8	1871.8	1982.8	2075.3	2137.8	2156.4
32.5°	1163.4	1249.4	1350.3	1466.6	1597.2	1731.0	1856.0	1960.7	2037.8	2070.6	2048.2
35°	1109.8	1187.6	1289.6	1408.5	1544.3	1686.9	1810.4	1898.8	1938.3	1907.3	1830.1
37.5°	1045.5	1122.6	1225.1	1341.9	1482.5	1627.4	1739.0	1802.7	1789.6	1712.5	1597.4
40°	1000.5	1072.6	1170.1	1296.3	1433.3	1578.7	1676.7	1711.2	1675.1	1564.6	1442.3
42.5°	950.4	1020.8	1118.7	1240.4	1385.5	1519.6	1605.1	1607.9	1547.4	1415.4	1292.6
45°	874.2	941.3	1033.7	1160.5	1294.6	1420.9	1477.2	1449.6	1338.1	1210.6	1087.2
47.5°	799.0	857.1	948.3	1068.6	1196.0	1302.3	1330.2	1280.5	1161.6	1038.0	923.6
50°	744.0	802.6	888.3	1003.2	1126.1	1218.0	1231.5	1165.6	1048.9	924.3	834.7
52.5°	691.2	749.4	831.9	938.3	1050.8	1133.7	1134.1	1057.8	941.6	830.5	747.2
55°	613.8	666.2	740.6	835.8	936.2	1001.0	985.2	906.3	805.4	709.1	636.3
57.5°	539.2	584.8	653.4	732.8	821.2	874.7	848.5	772.5	682.4	600.7	545.6
60°	490.9	534.3	593.0	667.9	742.3	784.0	759.2	690.4	607.6	541.6	493.7
62.5°	444.0	480.6	537.0	602.1	671.1	702.0	679.9	612.0	540.4	480.8	441.9
65°	377.6	407.5	452.6	508.4	558.6	585.1	566.5	503.3	448.7	405.8	374.8
67.5°	315.6	339.0	373.1	417.8	460.5	474.8	457.9	413.9	367.6	333.3	311.4
70°	272.8	294.8	323.5	357.9	395.1	410.3	393.4	358.5	320.7	289.1	267.7
72.5°	235.4	252.4	276.6	306.1	335.2	350.3	338.8	305.2	273.4	249.9	231.6
75°	179.2	193.9	210.8	231.6	254.2	264.3	254.2	231.1	209.1	191.6	178.6
77.5°	130.3	138.2	151.2	166.8	180.9	188.7	179.9	164.2	150.8	138.8	132.5
80°	99.2	104.8	113.8	126.3	135.8	143.2	137.5	124.6	113.8	106.0	103.1
82.5°	72.2	76.0	81.9	91.1	97.5	101.3	98.7	89.4	85.0	78.0	75.2
85°	35.5	37.7	41.7	44.5	50.1	50.7	51.3	47.4	43.4	41.7	39.5
87.5°	12.5	13.2	14.6	16.1	17.9	18.9	18.4	18.6	17.0	16.5	14.8
90°	1.4	2.8	3.3	3.8	3.8	6.5	6.5	7.4	8.4	7.9	8.4
92.5°	7.7	12.1	17.8	24.5	34.2	57.9	93.9	129.1	147.5	122.9	91.3
95°	16.7	21.4	27.5	38.6	58.1	98.6	174.9	286.0	379.0	389.7	344.6
97.5°	27.6	31.6	37.1	46.7	63.1	94.2	157.2	267.7	399.3	489.7	509.2
100°	35.4	38.6	44.2	53.0	67.9	95.3	147.9	242.8	373.9	493.0	560.9
102.5°	43.5	46.4	51.6	60.1	74.2	99.1	145.3	226.0	342.3	465.0	558.3
105°	55.8	58.1	63.8	72.1	85.6	107.9	146.5	211.7	305.1	414.4	520.9
107.5°	68.2	70.5	76.5	84.5	97.8	118.2	153.4	209.0	284.3	373.5	467.8
110°	76.7	79.1	84.6	93.0	105.6	126.0	158.6	209.8	277.2	353.0	435.8



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	85.0	87.6	92.9	101.2	113.7	133.5	164.2	212.0	273.9	341.4	412.4
115°	97.2	100.4	105.1	114.0	126.5	145.1	173.0	216.3	272.1	330.7	388.8
117.5°	109.4	112.3	117.4	125.6	138.7	156.4	182.1	220.8	271.6	325.9	377.2
120°	117.2	120.4	125.6	133.5	146.5	164.2	188.3	224.2	271.6	323.3	372.1
122.5°	124.7	127.9	132.6	141.3	153.9	171.6	194.3	227.6	271.3	320.2	367.6
125°	135.3	138.1	143.2	152.1	165.1	181.8	203.3	232.5	270.7	315.4	360.0
127.5°	143.7	147.0	152.8	162.0	175.1	191.4	211.0	236.5	269.6	308.8	350.7
130°	148.8	152.5	159.6	168.4	181.8	197.6	215.8	239.5	269.3	304.6	343.2
132.5°	153.3	158.2	164.8	174.3	187.0	202.8	220.6	242.1	268.9	300.9	335.4
135°	160.5	165.1	173.0	182.8	194.9	210.2	227.0	246.1	268.3	295.3	324.7
137.5°	167.1	172.3	179.8	190.0	201.5	215.8	231.5	248.3	268.2	290.5	314.9
140°	171.6	176.8	184.7	194.4	205.5	219.6	234.4	250.2	267.9	287.9	309.2
142.5°	176.8	181.6	189.1	198.5	209.3	222.9	236.6	251.7	267.9	285.7	304.1
145°	184.2	188.8	195.3	204.2	214.4	226.5	239.0	252.6	266.9	281.8	296.7
147.5°	191.5	195.6	202.3	209.7	218.9	230.2	241.2	253.0	265.3	278.4	290.7
150°	196.7	200.5	206.0	213.0	221.8	232.1	242.3	253.0	264.2	275.8	287.0
152.5°	201.2	204.9	210.1	216.4	224.5	233.6	243.0	252.3	262.3	272.8	282.8
155°	208.4	211.2	215.8	220.9	227.9	235.8	243.7	251.1	259.5	268.3	276.7
157.5°	214.5	217.1	220.7	225.2	230.6	237.4	243.7	250.0	256.7	263.8	270.1
160°	218.6	220.5	223.7	227.4	232.5	238.1	243.7	248.8	254.4	260.5	266.0
162.5°	221.9	223.4	226.3	229.7	233.7	238.9	243.7	247.7	252.2	257.5	262.0
165°	226.5	227.4	229.8	232.1	234.9	239.0	242.8	245.6	248.8	252.6	256.2
167.5°	230.2	230.6	232.4	233.7	235.9	239.0	241.7	243.4	245.5	248.1	250.8
170°	232.1	232.5	233.9	234.9	236.3	238.6	240.9	241.8	243.2	245.1	247.4
172.5°	233.9	234.0	235.1	235.6	236.6	238.2	240.2	240.4	241.0	242.5	244.4
175°	235.8	235.8	236.3	236.8	236.8	237.7	239.0	238.6	238.6	239.5	240.4
177.5°	236.8	236.4	236.8	236.8	236.8	237.1	237.8	237.1	237.1	237.5	237.8
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1434.1	1435.0	1439.0	1442.2	1443.1	1447.6	1448.1
5°	1560.1	1569.7	1588.3	1590.0	1592.8	1607.4	1596.2
7.5°	1707.8	1732.1	1748.3	1762.7	1767.9	1774.3	1772.9
10°	1802.5	1838.5	1856.6	1885.3	1886.4	1893.8	1889.3
12.5°	1897.6	1939.5	1972.5	1977.8	2001.9	2005.6	2011.9
15°	2032.4	2077.0	2122.6	2138.9	2172.2	2180.1	2192.5
17.5°	2159.2	2204.7	2236.7	2278.9	2292.6	2310.9	2298.4
20°	2228.5	2278.2	2318.7	2352.0	2366.1	2376.2	2375.1
22.5°	2270.5	2320.5	2353.4	2378.6	2391.8	2396.1	2395.8
25°	2296.8	2325.5	2335.7	2345.2	2330.6	2325.5	2327.8
27.5°	2223.7	2216.3	2189.8	2155.1	2119.0	2090.3	2074.8
30°	2123.2	2079.2	2039.1	1969.3	1933.2	1911.8	1892.6
32.5°	1980.7	1911.0	1834.0	1770.0	1729.0	1697.2	1692.5
35°	1736.5	1631.7	1537.6	1459.2	1418.6	1384.2	1376.4
37.5°	1476.3	1367.4	1282.7	1213.7	1170.1	1145.8	1123.2
40°	1303.7	1210.1	1126.7	1068.0	1034.8	1017.3	1003.2
42.5°	1170.6	1085.2	1002.2	957.6	927.5	916.8	908.6
45°	986.9	907.4	849.9	816.1	798.7	780.6	772.2
47.5°	839.8	775.1	737.2	708.5	689.7	679.1	673.6
50°	756.4	703.4	669.6	647.6	630.7	622.2	617.8
52.5°	682.4	639.0	610.5	593.0	581.6	575.4	573.6
55°	587.8	554.6	536.5	521.4	512.9	507.3	505.0
57.5°	510.9	485.4	470.8	458.2	454.9	450.2	448.7
60°	460.5	440.8	428.4	419.9	417.1	411.5	412.5
62.5°	415.8	399.7	389.1	384.3	380.6	375.9	377.4
65°	351.7	339.9	334.2	329.7	325.2	322.4	324.7
67.5°	295.1	287.0	279.3	276.7	274.5	274.0	271.7
70°	258.1	251.4	244.6	243.0	243.0	240.7	240.1
72.5°	222.5	217.5	213.0	211.8	210.0	210.9	208.6
75°	171.9	168.0	166.2	164.6	164.0	164.0	162.3
77.5°	127.0	124.1	121.4	121.4	119.4	118.6	118.4
80°	96.4	95.2	93.0	93.0	91.9	92.5	91.3
82.5°	72.5	70.9	70.4	69.5	68.0	68.1	66.9
85°	38.9	37.2	36.6	35.0	33.8	35.0	33.8
87.5°	15.3	14.9	14.5	13.7	13.3	13.2	11.9
90°	8.8	9.3	9.3	9.8	10.2	9.8	9.8
92.5°	68.7	54.7	45.4	39.9	37.4	35.8	35.8
95°	272.6	210.2	165.1	142.4	127.9	119.5	113.5
97.5°	482.4	436.9	388.3	355.0	326.9	313.0	303.3
100°	570.2	547.4	513.0	472.5	444.2	430.2	426.5
102.5°	604.5	611.1	596.7	571.9	551.3	536.6	533.6
105°	601.4	647.4	666.5	667.4	663.7	657.1	654.4
107.5°	553.4	618.3	659.7	682.7	693.3	698.0	699.2
110°	516.2	583.7	634.9	667.9	687.4	695.8	699.9



TEST NUMBER: P332636-930

CATALOG NUMBER: SA4XXDIP-C1020D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	483.5	547.2	598.3	635.9	659.5	671.2	678.0
115°	446.1	500.4	545.1	581.8	609.8	624.6	628.4
117.5°	424.6	467.4	505.2	536.6	560.0	575.1	578.0
120°	415.3	452.5	485.5	512.1	532.6	544.6	549.8
122.5°	409.4	443.2	472.1	494.6	512.1	522.3	527.4
125°	400.0	432.0	457.6	476.2	489.8	498.6	501.3
127.5°	388.9	420.9	445.2	463.9	475.9	483.3	486.1
130°	380.0	411.6	436.3	455.3	466.9	474.4	477.2
132.5°	369.9	400.8	425.4	444.2	457.3	464.3	467.2
135°	354.9	383.2	406.5	425.1	438.1	445.6	448.3
137.5°	340.5	364.4	385.4	402.8	415.6	421.8	425.1
140°	331.2	352.0	371.6	387.9	398.1	404.6	408.4
142.5°	323.3	341.3	358.2	372.6	382.1	387.9	390.4
145°	312.5	326.5	339.5	351.1	359.1	363.7	366.0
147.5°	303.2	314.4	324.7	333.2	340.0	343.5	344.4
150°	297.7	307.0	315.4	322.8	328.8	331.6	332.1
152.5°	292.0	300.6	307.5	313.8	318.8	320.4	320.9
155°	284.1	291.1	296.7	301.4	305.1	306.5	306.5
157.5°	276.4	282.2	286.7	290.2	293.0	293.8	293.8
160°	271.2	276.2	280.0	282.7	285.6	286.0	286.0
162.5°	266.3	270.3	273.7	275.7	278.5	279.0	278.6
165°	259.0	262.3	264.6	266.5	268.3	267.9	267.4
167.5°	252.9	255.5	256.9	257.9	259.0	258.9	258.6
170°	248.8	250.7	252.1	253.0	253.5	253.0	253.0
172.5°	245.5	246.6	247.6	248.2	248.7	248.2	247.4
175°	240.9	241.8	241.8	241.8	242.8	241.8	240.9
177.5°	238.2	238.2	238.6	238.2	238.6	237.8	237.1
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8

(END OF REPORT)