

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331285-940

Luminaire Tested: **SA2XXDIP-C485D330U940-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331285-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D330U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3080.4 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331285-940
CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62				
1	101	97	93	90	95	91	88	85	80	77	75	70	68	66	60	59	58	53				
2	93	85	79	74	87	80	75	71	71	67	63	62	59	56	54	52	50	46				
3	85	76	68	63	79	71	65	60	63	58	54	55	52	48	48	45	43	39				
4	78	67	60	54	73	64	57	51	56	51	47	50	45	42	44	40	38	34				
5	72	60	52	46	67	57	50	45	51	45	41	45	40	37	40	36	33	30				
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	30	27				
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	27	24				
8	57	45	37	32	54	43	36	31	39	33	29	34	30	26	31	27	24	22				
9	54	41	34	29	50	39	33	28	35	30	26	32	27	24	28	25	22	20				
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	26	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13990	13990	13990	13990
5°	15686	14083	12478	14083
10°	17974	13967	10799	13967
15°	19883	13710	9541	13710
20°	19581	13435	8698	13435
25°	17655	13069	8165	13069
30°	14590	12486	7774	12486
35°	10634	11874	7496	11874
40°	8494	11152	7341	11152
45°	7421	10319	7133	10319
50°	6978	9510	6993	9510
55°	6432	8690	6804	8690
60°	5893	7818	6516	7818
65°	5368	7033	6235	7033
70°	4877	6274	5816	6274
75°	4323	5421	5153	5421
80°	3710	4491	4147	4491
85°	3335	3335	2464	3335



TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.5	2.7
10°-20°	239.9	7.8
20°-30°	348.2	11.3
30°-40°	367.4	11.9
40°-50°	325.3	10.6
50°-60°	259.6	8.4
60°-70°	176.5	5.7
70°-80°	90.5	2.9
80°-90°	22.8	0.7
90°-100°	13.3	0.4
100°-110°	48.7	1.6
110°-120°	130.3	4.2
120°-130°	215.1	7.0
130°-140°	228.7	7.4
140°-150°	212.6	6.9
150°-160°	170.9	5.5
160°-170°	110.1	3.6
170°-180°	37.9	1.2
0°-30°	670.6	21.8
0°-40°	1038.0	33.7
0°-60°	1623.0	52.7
0°-90°	1912.7	62.1
90°-120°	192.3	6.2
90°-150°	848.7	27.6
90°-180°	1168.0	37.9
0°-180°	3080.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	866	866	866	866	866	
5°	968	869	770	869	968	97
15°	1190	820	571	820	1190	328
25°	991	734	458	734	991	448
35°	540	602	380	602	540	351
45°	325	452	312	452	325	256
55°	228	309	242	309	228	205
65°	140	184	163	184	140	140
75°	69	87	83	87	69	74
85°	18	18	13	18	18	20
90°	8	0	8	0	8	4
95°	12	19	12	19	12	12
105°	22	88	22	88	22	23
115°	24	166	24	166	24	59
125°	246	234	246	234	246	213
135°	300	290	300	290	300	231
145°	342	336	342	336	342	214
155°	371	370	371	370	371	171
165°	390	390	390	390	390	110
175°	397	399	397	399	397	38
180°	398	398	398	398	398	



TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	906.5	906.8	907.2	903.0	902.5	902.5	898.8	895.5	891.8	886.7	887.3
5°	967.8	971.4	972.8	968.8	962.8	962.1	956.4	947.1	938.4	931.5	926.5
7.5°	1040.9	1042.3	1039.1	1033.8	1029.4	1021.4	1010.8	1000.5	986.1	972.8	963.0
10°	1096.3	1098.3	1092.6	1084.9	1078.6	1069.3	1054.0	1038.3	1019.4	1001.0	986.4
12.5°	1138.4	1143.4	1136.0	1135.1	1124.2	1111.4	1093.1	1085.2	1058.5	1033.0	1017.3
15°	1189.5	1189.2	1189.9	1183.6	1175.5	1173.6	1154.2	1133.3	1095.6	1080.7	1054.6
17.5°	1174.7	1179.8	1182.1	1182.1	1181.9	1180.6	1174.4	1161.2	1142.3	1118.0	1088.1
20°	1139.6	1146.2	1147.3	1154.9	1159.2	1164.9	1167.2	1163.6	1151.9	1131.6	1105.6
22.5°	1085.2	1087.1	1090.2	1102.2	1111.5	1125.7	1133.1	1145.4	1140.9	1131.0	1109.4
25°	991.0	987.7	999.3	1005.4	1027.0	1049.6	1066.0	1084.0	1099.9	1109.6	1103.3
27.5°	878.0	873.0	890.5	906.3	923.9	948.4	973.8	1003.9	1028.9	1060.2	1070.9
30°	782.6	785.6	802.3	819.2	845.9	880.5	909.1	942.1	977.8	1012.7	1037.0
32.5°	679.8	691.3	701.8	727.8	751.3	789.9	831.9	873.1	917.6	957.3	994.9
35°	539.5	552.8	567.5	586.5	619.4	657.7	698.7	754.3	814.9	869.2	913.8
37.5°	454.1	452.0	460.4	474.1	500.8	531.7	578.8	633.8	705.2	768.9	831.9
40°	403.0	401.6	407.6	420.3	440.6	463.2	504.5	552.8	619.1	697.0	772.0
42.5°	367.7	368.5	371.9	380.8	394.8	413.4	444.3	485.4	546.1	619.5	700.0
45°	325.0	327.3	331.0	335.4	343.3	358.6	375.9	405.3	453.3	514.5	593.8
47.5°	294.3	294.4	298.0	301.8	306.6	315.2	329.4	347.8	381.6	431.5	499.6
50°	277.8	275.4	278.0	281.1	286.1	292.0	301.4	318.7	341.3	381.7	438.5
52.5°	257.5	257.5	259.9	261.1	265.6	271.5	280.1	292.0	312.5	344.1	390.9
55°	228.5	230.2	231.5	233.4	237.5	241.7	248.4	256.5	272.4	296.0	330.6
57.5°	201.2	201.7	203.0	206.8	209.4	213.3	219.6	226.9	237.3	254.9	280.9
60°	182.5	182.5	185.1	186.8	190.1	194.1	199.1	206.2	215.4	229.8	250.7
62.5°	165.4	165.1	166.2	169.0	171.5	175.2	180.2	186.2	194.9	207.7	224.9
65°	140.5	139.9	141.9	142.5	145.2	148.8	152.8	159.2	166.2	175.5	190.8
67.5°	116.5	117.3	118.4	119.7	121.2	125.0	127.7	132.2	138.0	145.8	156.2
70°	103.3	103.3	103.3	104.2	106.2	108.3	110.9	114.6	120.2	126.9	136.2
72.5°	88.3	89.3	90.4	89.9	92.4	93.5	96.8	98.8	104.2	108.5	116.7
75°	69.3	69.3	69.3	70.9	72.0	72.9	74.9	77.0	79.6	84.9	89.3
77.5°	51.7	51.5	51.9	52.3	53.3	54.6	55.1	57.0	59.4	61.9	65.5
80°	39.9	40.7	40.9	41.6	41.6	42.3	42.6	44.9	46.6	48.3	50.6
82.5°	30.9	31.0	31.1	31.2	31.5	31.9	32.7	33.5	34.1	35.5	37.3
85°	18.0	17.7	17.7	18.3	18.0	18.0	18.6	19.4	19.4	19.6	20.7
87.5°	8.5	8.5	8.7	8.4	8.4	8.6	8.6	8.2	8.4	8.6	8.7
90°	7.8	7.7	7.5	7.4	7.3	7.0	6.7	6.4	6.1	5.8	5.3
92.5°	7.8	7.7	7.7	7.6	7.5	7.3	7.2	7.0	6.9	6.7	6.4
95°	12.4	12.5	12.5	12.6	12.7	12.5	12.2	11.9	11.6	11.2	10.8
97.5°	16.6	16.5	16.4	16.3	16.2	16.1	15.8	15.6	15.3	15.1	14.0
100°	19.4	19.2	19.1	18.9	18.8	18.5	18.0	17.5	16.9	16.4	15.3
102.5°	20.7	20.5	20.3	20.2	20.0	19.5	18.9	18.2	17.6	16.9	26.0
105°	21.9	21.7	21.4	21.1	20.9	20.4	19.7	19.0	18.3	17.6	35.0
107.5°	22.6	22.3	22.0	21.8	21.5	21.8	22.5	23.2	23.9	24.6	45.6
110°	22.7	22.6	22.3	22.0	21.8	24.8	31.2	37.6	44.1	50.5	68.9



TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	23.0	22.8	22.6	22.4	22.2	33.8	57.2	80.5	103.9	127.2	131.8
115°	23.6	28.3	32.9	37.5	42.1	59.2	88.9	118.6	148.2	177.9	176.3
117.5°	96.6	111.7	126.9	142.0	157.2	168.4	175.5	182.7	189.8	197.1	195.9
120°	175.8	184.5	193.1	201.8	210.4	214.4	213.7	212.9	212.1	211.3	210.2
122.5°	219.5	221.1	222.8	224.5	226.1	226.8	226.3	225.9	225.4	225.0	223.7
125°	246.5	246.3	246.1	245.9	245.8	245.4	245.0	244.5	244.1	243.6	242.4
127.5°	263.6	263.5	263.5	263.5	263.4	263.1	262.4	261.8	261.1	260.5	259.6
130°	274.2	274.3	274.3	274.4	274.5	274.1	273.4	272.7	272.0	271.3	270.6
132.5°	284.5	284.6	284.7	284.7	284.8	284.5	283.9	283.4	282.8	282.1	281.4
135°	299.5	299.7	299.8	300.0	300.1	299.8	299.2	298.5	297.9	297.3	296.7
137.5°	313.3	313.4	313.7	313.9	314.1	313.9	313.3	312.6	312.0	311.4	310.8
140°	321.7	322.1	322.4	322.7	323.1	322.9	322.4	321.7	321.2	320.6	319.9
142.5°	330.0	330.4	330.7	331.0	331.4	331.3	330.7	330.2	329.7	329.1	328.3
145°	341.6	342.0	342.3	342.6	343.0	342.9	342.4	342.0	341.5	341.1	340.0
147.5°	351.9	352.1	352.4	352.7	352.9	352.9	352.6	352.2	351.9	351.6	350.5
150°	358.1	358.4	358.7	359.1	359.4	359.4	358.9	358.6	358.2	357.8	356.8
152.5°	363.4	363.8	364.3	364.6	365.1	365.1	364.7	364.4	363.9	363.6	362.6
155°	370.8	371.3	371.8	372.3	372.8	372.9	372.5	372.1	371.8	371.3	370.6
157.5°	377.6	378.0	378.5	379.0	379.5	379.5	379.2	378.7	378.3	377.8	377.3
160°	381.5	381.9	382.4	382.8	383.3	383.3	382.9	382.5	382.1	381.7	381.4
162.5°	384.7	385.2	385.8	386.3	386.9	386.9	386.5	386.0	385.7	385.2	384.9
165°	389.5	389.9	390.4	390.8	391.3	391.3	390.8	390.4	389.9	389.5	389.3
167.5°	392.5	393.2	393.7	394.3	394.8	394.9	394.5	394.0	393.6	393.2	393.0
170°	394.4	395.0	395.6	396.2	396.7	396.8	396.4	395.9	395.5	395.0	394.8
172.5°	395.8	396.4	397.0	397.5	398.1	398.1	397.7	397.3	396.8	396.4	396.3
175°	397.0	397.6	398.3	399.0	399.6	399.7	399.2	398.8	398.3	397.9	397.8
177.5°	397.8	398.2	398.7	399.1	399.6	399.7	399.3	399.0	398.6	398.2	398.1
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331285-940
 CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	889.1	887.0	885.6	880.9	876.6	872.4	871.0	871.6	865.7	860.1	857.7
5°	923.8	917.1	910.8	901.8	891.2	879.5	873.5	868.9	857.2	844.5	837.2
7.5°	954.8	945.3	933.1	916.2	900.7	882.3	870.7	860.4	843.3	825.5	814.6
10°	973.7	960.7	945.1	924.4	905.4	883.2	867.5	851.9	831.9	810.6	797.3
12.5°	990.0	972.5	957.1	930.6	908.1	880.2	861.7	839.6	818.6	793.3	780.2
15°	1028.7	996.4	967.1	937.1	909.5	870.5	849.9	820.2	792.6	761.3	746.3
17.5°	1058.5	1022.3	976.2	938.1	905.8	862.6	832.3	796.8	764.1	728.3	708.0
20°	1075.7	1034.0	984.4	939.1	900.4	851.2	818.2	781.9	743.6	703.3	681.4
22.5°	1085.7	1042.1	992.9	935.1	889.8	841.9	800.4	760.6	721.8	678.3	655.2
25°	1089.0	1049.0	997.0	931.7	876.5	822.2	772.2	733.6	686.7	646.0	612.4
27.5°	1073.1	1044.5	994.5	925.5	861.1	797.6	742.0	698.2	648.6	604.6	570.7
30°	1053.6	1037.0	988.4	919.1	848.8	780.6	719.3	669.7	620.5	575.8	541.2
32.5°	1023.6	1019.9	977.2	910.1	835.8	759.0	695.6	645.4	590.8	547.0	514.0
35°	964.4	980.4	953.4	889.8	811.2	728.3	659.7	602.4	545.8	503.8	472.9
37.5°	885.2	924.9	917.8	860.1	778.0	694.9	619.1	559.3	505.3	463.0	432.6
40°	830.5	881.2	888.5	837.5	754.7	669.1	588.8	529.1	476.5	437.9	407.2
42.5°	772.0	831.1	851.2	810.4	729.1	641.9	561.6	499.9	447.8	410.2	383.1
45°	673.7	752.0	788.3	764.9	686.3	597.1	514.5	451.9	404.7	369.3	348.3
47.5°	581.8	667.4	716.2	707.9	638.8	550.5	468.9	408.8	362.7	334.6	315.8
50°	516.8	604.8	663.7	666.4	604.8	517.2	435.2	378.6	336.4	310.0	294.7
52.5°	460.4	544.3	608.6	622.7	566.7	482.5	405.1	348.8	311.6	287.4	273.7
55°	386.6	457.5	528.9	554.8	509.9	429.9	358.3	308.7	273.8	257.1	245.1
57.5°	321.5	380.6	446.4	475.1	447.4	379.0	311.8	268.8	240.4	225.8	216.6
60°	287.0	333.7	392.3	426.6	402.6	341.7	283.0	242.1	218.8	205.8	197.2
62.5°	255.1	296.4	345.9	377.3	364.3	306.7	254.3	218.1	198.0	185.8	179.6
65°	210.4	243.1	281.4	310.4	301.8	258.1	215.2	184.1	168.2	158.5	153.6
67.5°	173.3	196.9	223.5	248.8	241.8	210.9	176.5	152.3	140.4	132.1	129.1
70°	149.9	167.8	191.5	211.8	206.2	180.8	153.6	132.9	122.5	115.6	112.5
72.5°	127.5	142.2	160.3	176.9	173.1	152.0	129.3	113.7	105.8	99.3	96.8
75°	96.2	107.5	118.6	129.6	128.6	112.3	98.9	86.9	80.6	75.6	74.6
77.5°	71.1	77.4	84.9	91.4	89.6	80.3	69.8	63.0	58.3	54.9	54.4
80°	54.3	58.0	63.3	67.9	65.6	61.6	53.3	48.3	44.9	41.6	40.3
82.5°	39.3	43.1	46.2	48.8	47.0	43.2	38.1	34.7	32.7	30.4	29.9
85°	20.7	22.6	24.0	24.6	24.0	21.7	19.4	18.0	16.3	15.3	15.0
87.5°	8.9	8.8	8.7	9.2	8.2	8.0	6.9	5.9	5.8	5.7	5.3
90°	4.7	4.2	3.7	3.1	2.4	1.7	1.0	0.3	1.0	1.7	2.4
92.5°	6.2	5.9	5.7	5.5	5.6	5.7	5.8	5.8	5.8	5.7	5.6
95°	10.3	9.9	9.5	10.3	12.4	14.5	16.6	18.7	16.6	14.5	12.4
97.5°	12.9	11.9	10.9	13.4	19.4	25.2	31.2	37.2	31.2	25.2	19.4
100°	14.3	13.2	12.0	16.0	24.7	33.4	42.3	51.0	42.3	33.4	24.7
102.5°	35.1	44.2	53.3	58.9	60.7	62.5	64.4	66.3	64.4	62.5	60.7
105°	52.6	70.1	87.6	95.3	93.5	91.5	89.5	87.7	89.5	91.5	93.5
107.5°	66.6	87.6	108.5	118.2	116.7	115.1	113.6	112.0	113.6	115.1	116.7
110°	87.5	106.0	124.5	133.1	131.8	130.5	129.0	127.7	129.0	130.5	131.8



TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	136.4	141.0	145.5	147.2	146.1	144.9	143.7	142.5	143.7	144.9	146.1
115°	174.7	173.1	171.5	170.1	169.1	168.0	166.8	165.8	166.8	168.0	169.1
117.5°	194.8	193.8	192.6	191.5	190.3	189.0	187.8	186.6	187.8	189.0	190.3
120°	209.0	207.9	206.7	205.6	204.7	203.8	202.8	201.8	202.8	203.8	204.7
122.5°	222.4	221.1	219.9	218.8	217.8	216.8	215.8	214.7	215.8	216.8	217.8
125°	241.2	240.0	238.8	237.7	236.9	236.0	235.2	234.4	235.2	236.0	236.9
127.5°	258.7	257.7	256.8	255.9	255.0	254.0	253.2	252.2	253.2	254.0	255.0
130°	269.9	269.2	268.5	267.6	266.6	265.6	264.6	263.5	264.6	265.6	266.6
132.5°	280.7	280.0	279.3	278.6	277.7	276.8	275.9	275.1	275.9	276.8	277.7
135°	296.1	295.5	295.0	294.2	293.1	292.1	291.1	290.1	291.1	292.1	293.1
137.5°	310.0	309.4	308.8	308.1	307.4	306.7	305.9	305.2	305.9	306.7	307.4
140°	319.2	318.5	317.8	317.2	316.6	316.1	315.7	315.1	315.7	316.1	316.6
142.5°	327.5	326.7	325.9	325.3	324.9	324.3	323.9	323.4	323.9	324.3	324.9
145°	338.9	337.8	336.7	336.2	336.3	336.4	336.4	336.4	336.4	336.4	336.3
147.5°	349.5	348.3	347.2	346.9	347.1	347.3	347.6	347.9	347.6	347.3	347.1
150°	355.8	354.7	353.7	353.4	353.8	354.3	354.7	355.2	354.7	354.3	353.8
152.5°	361.6	360.6	359.6	359.4	359.9	360.4	361.0	361.4	361.0	360.4	359.9
155°	369.8	369.1	368.3	368.2	368.7	369.3	369.9	370.5	369.9	369.3	368.7
157.5°	376.7	376.2	375.7	375.6	376.1	376.6	377.1	377.6	377.1	376.6	376.1
160°	380.9	380.6	380.2	380.2	380.6	380.9	381.4	381.7	381.4	380.9	380.6
162.5°	384.5	384.1	383.9	383.9	384.2	384.7	385.0	385.4	385.0	384.7	384.2
165°	389.1	389.0	388.8	388.9	389.2	389.6	390.0	390.4	390.0	389.6	389.2
167.5°	392.8	392.6	392.4	392.5	392.9	393.3	393.7	394.0	393.7	393.3	392.9
170°	394.8	394.6	394.5	394.6	395.0	395.4	395.7	396.2	395.7	395.4	395.0
172.5°	396.1	396.0	395.8	396.0	396.4	396.7	397.2	397.5	397.2	396.7	396.4
175°	397.6	397.5	397.3	397.5	398.0	398.4	398.9	399.3	398.9	398.4	398.0
177.5°	398.1	398.1	398.1	398.1	398.5	398.9	399.2	399.6	399.2	398.9	398.5
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	855.1	853.5	847.8	844.9	840.2	835.6	832.7	834.0	835.1	834.6	833.7
5°	830.5	824.2	814.6	806.2	800.2	789.3	784.6	782.3	780.2	777.9	775.6
7.5°	801.4	791.4	777.6	765.7	754.5	740.8	733.1	728.3	723.5	718.3	713.6
10°	780.6	766.6	752.0	735.3	722.0	709.6	698.7	691.3	684.7	678.3	673.7
12.5°	758.8	742.6	724.5	701.8	687.1	669.4	667.8	654.9	644.4	640.5	635.1
15°	724.0	701.3	678.3	651.4	639.7	623.8	613.8	603.8	594.8	588.4	586.7
17.5°	684.5	655.1	632.3	613.0	593.9	577.5	568.3	560.3	552.9	544.4	543.3
20°	654.3	629.1	604.1	587.1	567.5	550.8	539.5	531.5	525.1	520.1	515.9
22.5°	625.9	598.2	575.3	556.7	537.3	523.9	515.0	507.3	502.0	496.5	492.4
25°	580.1	558.5	533.5	512.6	496.5	487.9	480.5	473.9	470.6	466.9	462.3
27.5°	540.1	516.0	492.7	476.4	462.4	454.7	449.5	445.0	441.8	439.7	437.0
30°	511.8	487.5	469.2	453.3	441.6	433.9	430.6	427.9	424.3	422.9	421.6
32.5°	484.6	462.8	447.1	433.3	422.1	417.1	414.1	411.7	408.8	407.5	404.8
35°	446.2	427.9	412.6	404.9	395.9	391.6	389.3	385.9	383.3	382.0	381.7
37.5°	410.1	394.1	384.1	374.3	370.4	367.7	364.6	362.3	361.5	361.3	361.0
40°	386.6	373.6	364.6	356.7	355.0	351.0	348.3	346.3	346.3	346.7	346.3
42.5°	365.3	353.7	345.7	338.9	336.9	334.5	331.8	331.7	332.3	333.3	332.3
45°	333.1	324.7	319.1	315.7	312.0	309.7	309.3	310.4	310.7	311.0	312.0
47.5°	303.3	297.7	292.7	289.0	287.4	287.0	286.6	288.3	289.9	290.5	292.0
50°	285.7	279.4	275.1	272.8	271.4	270.7	271.4	273.4	274.7	276.4	277.4
52.5°	266.0	261.5	258.6	256.7	256.2	256.6	256.7	259.0	261.2	261.7	262.3
55°	238.8	235.4	234.8	231.8	233.1	232.7	234.4	235.8	237.7	239.8	240.1
57.5°	211.6	208.9	207.1	207.4	207.8	209.3	210.6	213.0	215.2	217.2	217.5
60°	193.5	192.2	191.2	191.2	191.8	193.9	195.5	197.8	199.1	200.5	201.4
62.5°	177.0	175.7	174.6	175.1	176.9	178.1	180.0	181.3	182.6	184.0	184.4
65°	150.9	150.2	151.2	151.9	152.2	153.8	156.2	157.2	158.5	159.2	161.5
67.5°	126.8	127.0	126.8	127.8	129.7	130.1	132.2	134.6	134.9	136.2	137.7
70°	110.6	111.2	111.9	112.5	114.2	114.9	116.5	117.5	118.9	119.8	120.9
72.5°	95.7	95.8	96.5	96.3	97.7	99.2	100.6	101.6	102.9	104.2	105.1
75°	73.6	73.6	74.3	74.6	76.2	77.9	77.6	78.3	79.6	81.0	81.6
77.5°	53.8	53.1	53.8	54.0	54.6	56.0	56.3	57.2	58.8	58.3	59.0
80°	40.9	39.9	40.9	41.3	41.3	43.0	43.0	43.6	44.6	43.6	44.6
82.5°	29.2	28.8	29.5	29.6	30.1	30.1	30.7	30.9	31.8	31.4	31.8
85°	14.6	14.4	14.6	14.4	14.6	15.0	15.0	14.6	14.6	15.3	14.4
87.5°	5.2	5.0	4.8	4.9	4.8	4.6	4.5	4.5	4.5	4.1	4.1
90°	3.1	3.7	4.2	4.7	5.3	5.8	6.1	6.4	6.7	7.0	7.3
92.5°	5.5	5.7	5.9	6.2	6.4	6.7	6.9	7.0	7.2	7.3	7.5
95°	10.3	9.5	9.9	10.3	10.8	11.2	11.6	11.9	12.2	12.5	12.7
97.5°	13.4	10.9	11.9	12.9	14.0	15.1	15.3	15.6	15.8	16.1	16.2
100°	16.0	12.0	13.2	14.3	15.3	16.4	16.9	17.5	18.0	18.5	18.8
102.5°	58.9	53.3	44.2	35.1	26.0	16.9	17.6	18.2	18.9	19.5	20.0
105°	95.3	87.6	70.1	52.6	35.0	17.6	18.3	19.0	19.7	20.4	20.9
107.5°	118.2	108.5	87.6	66.6	45.6	24.6	23.9	23.2	22.5	21.8	21.5
110°	133.1	124.5	106.0	87.5	68.9	50.5	44.1	37.6	31.2	24.8	21.8



TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	147.2	145.5	141.0	136.4	131.8	127.2	103.9	80.5	57.2	33.8	22.2
115°	170.1	171.5	173.1	174.7	176.3	177.9	148.2	118.6	88.9	59.2	42.1
117.5°	191.5	192.6	193.8	194.8	195.9	197.1	189.8	182.7	175.5	168.4	157.2
120°	205.6	206.7	207.9	209.0	210.2	211.3	212.1	212.9	213.7	214.4	210.4
122.5°	218.8	219.9	221.1	222.4	223.7	225.0	225.4	225.9	226.3	226.8	226.1
125°	237.7	238.8	240.0	241.2	242.4	243.6	244.1	244.5	245.0	245.4	245.8
127.5°	255.9	256.8	257.7	258.7	259.6	260.5	261.1	261.8	262.4	263.1	263.4
130°	267.6	268.5	269.2	269.9	270.6	271.3	272.0	272.7	273.4	274.1	274.5
132.5°	278.6	279.3	280.0	280.7	281.4	282.1	282.8	283.4	283.9	284.5	284.8
135°	294.2	295.0	295.5	296.1	296.7	297.3	297.9	298.5	299.2	299.8	300.1
137.5°	308.1	308.8	309.4	310.0	310.8	311.4	312.0	312.6	313.3	313.9	314.1
140°	317.2	317.8	318.5	319.2	319.9	320.6	321.2	321.7	322.4	322.9	323.1
142.5°	325.3	325.9	326.7	327.5	328.3	329.1	329.7	330.2	330.7	331.3	331.4
145°	336.2	336.7	337.8	338.9	340.0	341.1	341.5	342.0	342.4	342.9	343.0
147.5°	346.9	347.2	348.3	349.5	350.5	351.6	351.9	352.2	352.6	352.9	352.9
150°	353.4	353.7	354.7	355.8	356.8	357.8	358.2	358.6	358.9	359.4	359.4
152.5°	359.4	359.6	360.6	361.6	362.6	363.6	363.9	364.4	364.7	365.1	365.1
155°	368.2	368.3	369.1	369.8	370.6	371.3	371.8	372.1	372.5	372.9	372.8
157.5°	375.6	375.7	376.2	376.7	377.3	377.8	378.3	378.7	379.2	379.5	379.5
160°	380.2	380.2	380.6	380.9	381.4	381.7	382.1	382.5	382.9	383.3	383.3
162.5°	383.9	383.9	384.1	384.5	384.9	385.2	385.7	386.0	386.5	386.9	386.9
165°	388.9	388.8	389.0	389.1	389.3	389.5	389.9	390.4	390.8	391.3	391.3
167.5°	392.5	392.4	392.6	392.8	393.0	393.2	393.6	394.0	394.5	394.9	394.8
170°	394.6	394.5	394.6	394.8	394.8	395.0	395.5	395.9	396.4	396.8	396.7
172.5°	396.0	395.8	396.0	396.1	396.3	396.4	396.8	397.3	397.7	398.1	398.1
175°	397.5	397.3	397.5	397.6	397.8	397.9	398.3	398.8	399.2	399.7	399.6
177.5°	398.1	398.1	398.1	398.1	398.1	398.2	398.6	399.0	399.3	399.7	399.6
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	831.1	830.5	830.5	828.1	830.5	830.5	831.1	833.7	834.6	835.1	834.0
5°	771.0	769.9	768.3	769.9	768.3	769.9	771.0	775.6	777.9	780.2	782.3
7.5°	711.5	707.5	706.9	702.9	706.9	707.5	711.5	713.6	718.3	723.5	728.3
10°	668.1	665.4	665.0	658.7	665.0	665.4	668.1	673.7	678.3	684.7	691.3
12.5°	635.0	628.6	629.9	626.2	629.9	628.6	635.0	635.1	640.5	644.4	654.9
15°	577.7	577.7	576.5	570.8	576.5	577.7	577.7	586.7	588.4	594.8	603.8
17.5°	536.7	536.0	532.8	534.4	532.8	536.0	536.7	543.3	544.4	552.9	560.3
20°	512.2	510.1	506.2	506.2	506.2	510.1	512.2	515.9	520.1	525.1	531.5
22.5°	489.0	488.8	484.6	486.0	484.6	488.8	489.0	492.4	496.5	502.0	507.3
25°	461.9	459.2	457.3	458.3	457.3	459.2	461.9	462.3	466.9	470.6	473.9
27.5°	436.2	434.7	434.6	431.9	434.6	434.7	436.2	437.0	439.7	441.8	445.0
30°	421.2	417.9	418.6	417.0	418.6	417.9	421.2	421.6	422.9	424.3	427.9
32.5°	404.2	403.1	402.3	400.9	402.3	403.1	404.2	404.8	407.5	408.8	411.7
35°	380.9	381.3	379.6	380.3	379.6	381.3	380.9	381.7	382.0	383.3	385.9
37.5°	360.7	361.8	361.0	361.1	361.0	361.8	360.7	361.0	361.3	361.5	362.3
40°	347.3	347.3	347.3	348.3	347.3	347.3	347.3	346.3	346.7	346.3	346.3
42.5°	334.6	334.0	333.5	333.4	333.5	334.0	334.6	332.3	333.3	332.3	331.7
45°	312.7	313.7	314.1	312.4	314.1	313.7	312.7	312.0	311.0	310.7	310.4
47.5°	292.9	293.0	292.9	294.4	292.9	293.0	292.9	292.0	290.5	289.9	288.3
50°	279.1	278.4	279.1	278.4	279.1	278.4	279.1	277.4	276.4	274.7	273.4
52.5°	264.4	264.6	264.1	264.0	264.1	264.6	264.4	262.3	261.7	261.2	259.0
55°	241.5	242.1	241.7	241.7	241.7	242.1	241.5	240.1	239.8	237.7	235.8
57.5°	217.7	218.3	218.7	217.2	218.7	218.3	217.7	217.5	217.2	215.2	213.0
60°	201.2	202.8	202.5	201.8	202.5	202.8	201.2	201.4	200.5	199.1	197.8
62.5°	185.9	186.5	186.5	186.4	186.5	186.5	185.9	184.4	184.0	182.6	181.3
65°	162.5	163.2	162.2	163.2	162.2	163.2	162.5	161.5	159.2	158.5	157.2
67.5°	137.2	137.5	138.2	138.7	138.2	137.5	137.2	137.7	136.2	134.9	134.6
70°	121.5	121.2	122.3	123.2	122.3	121.2	121.5	120.9	119.8	118.9	117.5
72.5°	105.0	105.8	105.4	106.2	105.4	105.8	105.0	105.1	104.2	102.9	101.6
75°	81.0	81.9	81.6	82.6	81.6	81.9	81.0	81.6	81.0	79.6	78.3
77.5°	58.5	58.6	58.5	59.0	58.5	58.6	58.5	59.0	58.3	58.8	57.2
80°	44.6	44.0	43.2	44.6	43.2	44.0	44.6	44.6	43.6	44.6	43.6
82.5°	31.0	31.5	30.8	30.8	30.8	31.5	31.0	31.8	31.4	31.8	30.9
85°	14.4	14.0	13.3	13.3	13.3	14.0	14.4	14.4	15.3	14.6	14.6
87.5°	4.1	3.9	3.9	3.7	3.9	3.9	4.1	4.1	4.1	4.5	4.5
90°	7.4	7.5	7.7	7.8	7.7	7.5	7.4	7.3	7.0	6.7	6.4
92.5°	7.6	7.7	7.7	7.8	7.7	7.7	7.6	7.5	7.3	7.2	7.0
95°	12.6	12.5	12.5	12.4	12.5	12.5	12.6	12.7	12.5	12.2	11.9
97.5°	16.3	16.4	16.5	16.6	16.5	16.4	16.3	16.2	16.1	15.8	15.6
100°	18.9	19.1	19.2	19.4	19.2	19.1	18.9	18.8	18.5	18.0	17.5
102.5°	20.2	20.3	20.5	20.7	20.5	20.3	20.2	20.0	19.5	18.9	18.2
105°	21.1	21.4	21.7	21.9	21.7	21.4	21.1	20.9	20.4	19.7	19.0
107.5°	21.8	22.0	22.3	22.6	22.3	22.0	21.8	21.5	21.8	22.5	23.2
110°	22.0	22.3	22.6	22.7	22.6	22.3	22.0	21.8	24.8	31.2	37.6



TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	22.4	22.6	22.8	23.0	22.8	22.6	22.4	22.2	33.8	57.2	80.5
115°	37.5	32.9	28.3	23.6	28.3	32.9	37.5	42.1	59.2	88.9	118.6
117.5°	142.0	126.9	111.7	96.6	111.7	126.9	142.0	157.2	168.4	175.5	182.7
120°	201.8	193.1	184.5	175.8	184.5	193.1	201.8	210.4	214.4	213.7	212.9
122.5°	224.5	222.8	221.1	219.5	221.1	222.8	224.5	226.1	226.8	226.3	225.9
125°	245.9	246.1	246.3	246.5	246.3	246.1	245.9	245.8	245.4	245.0	244.5
127.5°	263.5	263.5	263.5	263.6	263.5	263.5	263.5	263.4	263.1	262.4	261.8
130°	274.4	274.3	274.3	274.2	274.3	274.3	274.4	274.5	274.1	273.4	272.7
132.5°	284.7	284.7	284.6	284.5	284.6	284.7	284.7	284.8	284.5	283.9	283.4
135°	300.0	299.8	299.7	299.5	299.7	299.8	300.0	300.1	299.8	299.2	298.5
137.5°	313.9	313.7	313.4	313.3	313.4	313.7	313.9	314.1	313.9	313.3	312.6
140°	322.7	322.4	322.1	321.7	322.1	322.4	322.7	323.1	322.9	322.4	321.7
142.5°	331.0	330.7	330.4	330.0	330.4	330.7	331.0	331.4	331.3	330.7	330.2
145°	342.6	342.3	342.0	341.6	342.0	342.3	342.6	343.0	342.9	342.4	342.0
147.5°	352.7	352.4	352.1	351.9	352.1	352.4	352.7	352.9	352.9	352.6	352.2
150°	359.1	358.7	358.4	358.1	358.4	358.7	359.1	359.4	359.4	358.9	358.6
152.5°	364.6	364.3	363.8	363.4	363.8	364.3	364.6	365.1	365.1	364.7	364.4
155°	372.3	371.8	371.3	370.8	371.3	371.8	372.3	372.8	372.9	372.5	372.1
157.5°	379.0	378.5	378.0	377.6	378.0	378.5	379.0	379.5	379.5	379.2	378.7
160°	382.8	382.4	381.9	381.5	381.9	382.4	382.8	383.3	383.3	382.9	382.5
162.5°	386.3	385.8	385.2	384.7	385.2	385.8	386.3	386.9	386.9	386.5	386.0
165°	390.8	390.4	389.9	389.5	389.9	390.4	390.8	391.3	391.3	390.8	390.4
167.5°	394.3	393.7	393.2	392.5	393.2	393.7	394.3	394.8	394.9	394.5	394.0
170°	396.2	395.6	395.0	394.4	395.0	395.6	396.2	396.7	396.8	396.4	395.9
172.5°	397.5	397.0	396.4	395.8	396.4	397.0	397.5	398.1	398.1	397.7	397.3
175°	399.0	398.3	397.6	397.0	397.6	398.3	399.0	399.6	399.7	399.2	398.8
177.5°	399.1	398.7	398.2	397.8	398.2	398.7	399.1	399.6	399.7	399.3	399.0
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	832.7	835.6	840.2	844.9	847.8	853.5	855.1	857.7	860.1	865.7	871.6
5°	784.6	789.3	800.2	806.2	814.6	824.2	830.5	837.2	844.5	857.2	868.9
7.5°	733.1	740.8	754.5	765.7	777.6	791.4	801.4	814.6	825.5	843.3	860.4
10°	698.7	709.6	722.0	735.3	752.0	766.6	780.6	797.3	810.6	831.9	851.9
12.5°	667.8	669.4	687.1	701.8	724.5	742.6	758.8	780.2	793.3	818.6	839.6
15°	613.8	623.8	639.7	651.4	678.3	701.3	724.0	746.3	761.3	792.6	820.2
17.5°	568.3	577.5	593.9	613.0	632.3	655.1	684.5	708.0	728.3	764.1	796.8
20°	539.5	550.8	567.5	587.1	604.1	629.1	654.3	681.4	703.3	743.6	781.9
22.5°	515.0	523.9	537.3	556.7	575.3	598.2	625.9	655.2	678.3	721.8	760.6
25°	480.5	487.9	496.5	512.6	533.5	558.5	580.1	612.4	646.0	686.7	733.6
27.5°	449.5	454.7	462.4	476.4	492.7	516.0	540.1	570.7	604.6	648.6	698.2
30°	430.6	433.9	441.6	453.3	469.2	487.5	511.8	541.2	575.8	620.5	669.7
32.5°	414.1	417.1	422.1	433.3	447.1	462.8	484.6	514.0	547.0	590.8	645.4
35°	389.3	391.6	395.9	404.9	412.6	427.9	446.2	472.9	503.8	545.8	602.4
37.5°	364.6	367.7	370.4	374.3	384.1	394.1	410.1	432.6	463.0	505.3	559.3
40°	348.3	351.0	355.0	356.7	364.6	373.6	386.6	407.2	437.9	476.5	529.1
42.5°	331.8	334.5	336.9	338.9	345.7	353.7	365.3	383.1	410.2	447.8	499.9
45°	309.3	309.7	312.0	315.7	319.1	324.7	333.1	348.3	369.3	404.7	451.9
47.5°	286.6	287.0	287.4	289.0	292.7	297.7	303.3	315.8	334.6	362.7	408.8
50°	271.4	270.7	271.4	272.8	275.1	279.4	285.7	294.7	310.0	336.4	378.6
52.5°	256.7	256.6	256.2	256.7	258.6	261.5	266.0	273.7	287.4	311.6	348.8
55°	234.4	232.7	233.1	231.8	234.8	235.4	238.8	245.1	257.1	273.8	308.7
57.5°	210.6	209.3	207.8	207.4	207.1	208.9	211.6	216.6	225.8	240.4	268.8
60°	195.5	193.9	191.8	191.2	191.2	192.2	193.5	197.2	205.8	218.8	242.1
62.5°	180.0	178.1	176.9	175.1	174.6	175.7	177.0	179.6	185.8	198.0	218.1
65°	156.2	153.8	152.2	151.9	151.2	150.2	150.9	153.6	158.5	168.2	184.1
67.5°	132.2	130.1	129.7	127.8	126.8	127.0	126.8	129.1	132.1	140.4	152.3
70°	116.5	114.9	114.2	112.5	111.9	111.2	110.6	112.5	115.6	122.5	132.9
72.5°	100.6	99.2	97.7	96.3	96.5	95.8	95.7	96.8	99.3	105.8	113.7
75°	77.6	77.9	76.2	74.6	74.3	73.6	73.6	74.6	75.6	80.6	86.9
77.5°	56.3	56.0	54.6	54.0	53.8	53.1	53.8	54.4	54.9	58.3	63.0
80°	43.0	43.0	41.3	41.3	40.9	39.9	40.9	40.3	41.6	44.9	48.3
82.5°	30.7	30.1	30.1	29.6	29.5	28.8	29.2	29.9	30.4	32.7	34.7
85°	15.0	15.0	14.6	14.4	14.6	14.4	14.6	15.0	15.3	16.3	18.0
87.5°	4.5	4.6	4.8	4.9	4.8	5.0	5.2	5.3	5.7	5.8	5.9
90°	6.1	5.8	5.3	4.7	4.2	3.7	3.1	2.4	1.7	1.0	0.3
92.5°	6.9	6.7	6.4	6.2	5.9	5.7	5.5	5.6	5.7	5.8	5.8
95°	11.6	11.2	10.8	10.3	9.9	9.5	10.3	12.4	14.5	16.6	18.7
97.5°	15.3	15.1	14.0	12.9	11.9	10.9	13.4	19.4	25.2	31.2	37.2
100°	16.9	16.4	15.3	14.3	13.2	12.0	16.0	24.7	33.4	42.3	51.0
102.5°	17.6	16.9	26.0	35.1	44.2	53.3	58.9	60.7	62.5	64.4	66.3
105°	18.3	17.6	35.0	52.6	70.1	87.6	95.3	93.5	91.5	89.5	87.7
107.5°	23.9	24.6	45.6	66.6	87.6	108.5	118.2	116.7	115.1	113.6	112.0
110°	44.1	50.5	68.9	87.5	106.0	124.5	133.1	131.8	130.5	129.0	127.7



TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	103.9	127.2	131.8	136.4	141.0	145.5	147.2	146.1	144.9	143.7	142.5
115°	148.2	177.9	176.3	174.7	173.1	171.5	170.1	169.1	168.0	166.8	165.8
117.5°	189.8	197.1	195.9	194.8	193.8	192.6	191.5	190.3	189.0	187.8	186.6
120°	212.1	211.3	210.2	209.0	207.9	206.7	205.6	204.7	203.8	202.8	201.8
122.5°	225.4	225.0	223.7	222.4	221.1	219.9	218.8	217.8	216.8	215.8	214.7
125°	244.1	243.6	242.4	241.2	240.0	238.8	237.7	236.9	236.0	235.2	234.4
127.5°	261.1	260.5	259.6	258.7	257.7	256.8	255.9	255.0	254.0	253.2	252.2
130°	272.0	271.3	270.6	269.9	269.2	268.5	267.6	266.6	265.6	264.6	263.5
132.5°	282.8	282.1	281.4	280.7	280.0	279.3	278.6	277.7	276.8	275.9	275.1
135°	297.9	297.3	296.7	296.1	295.5	295.0	294.2	293.1	292.1	291.1	290.1
137.5°	312.0	311.4	310.8	310.0	309.4	308.8	308.1	307.4	306.7	305.9	305.2
140°	321.2	320.6	319.9	319.2	318.5	317.8	317.2	316.6	316.1	315.7	315.1
142.5°	329.7	329.1	328.3	327.5	326.7	325.9	325.3	324.9	324.3	323.9	323.4
145°	341.5	341.1	340.0	338.9	337.8	336.7	336.2	336.3	336.4	336.4	336.4
147.5°	351.9	351.6	350.5	349.5	348.3	347.2	346.9	347.1	347.3	347.6	347.9
150°	358.2	357.8	356.8	355.8	354.7	353.7	353.4	353.8	354.3	354.7	355.2
152.5°	363.9	363.6	362.6	361.6	360.6	359.6	359.4	359.9	360.4	361.0	361.4
155°	371.8	371.3	370.6	369.8	369.1	368.3	368.2	368.7	369.3	369.9	370.5
157.5°	378.3	377.8	377.3	376.7	376.2	375.7	375.6	376.1	376.6	377.1	377.6
160°	382.1	381.7	381.4	380.9	380.6	380.2	380.2	380.6	380.9	381.4	381.7
162.5°	385.7	385.2	384.9	384.5	384.1	383.9	383.9	384.2	384.7	385.0	385.4
165°	389.9	389.5	389.3	389.1	389.0	388.8	388.9	389.2	389.6	390.0	390.4
167.5°	393.6	393.2	393.0	392.8	392.6	392.4	392.5	392.9	393.3	393.7	394.0
170°	395.5	395.0	394.8	394.8	394.6	394.5	394.6	395.0	395.4	395.7	396.2
172.5°	396.8	396.4	396.3	396.1	396.0	395.8	396.0	396.4	396.7	397.2	397.5
175°	398.3	397.9	397.8	397.6	397.5	397.3	397.5	398.0	398.4	398.9	399.3
177.5°	398.6	398.2	398.1	398.1	398.1	398.1	398.1	398.5	398.9	399.2	399.6
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	871.0	872.4	876.6	880.9	885.6	887.0	889.1	887.3	886.7	891.8	895.5
5°	873.5	879.5	891.2	901.8	910.8	917.1	923.8	926.5	931.5	938.4	947.1
7.5°	870.7	882.3	900.7	916.2	933.1	945.3	954.8	963.0	972.8	986.1	1000.5
10°	867.5	883.2	905.4	924.4	945.1	960.7	973.7	986.4	1001.0	1019.4	1038.3
12.5°	861.7	880.2	908.1	930.6	957.1	972.5	990.0	1017.3	1033.0	1058.5	1085.2
15°	849.9	870.5	909.5	937.1	967.1	996.4	1028.7	1054.6	1080.7	1095.6	1133.3
17.5°	832.3	862.6	905.8	938.1	976.2	1022.3	1058.5	1088.1	1118.0	1142.3	1161.2
20°	818.2	851.2	900.4	939.1	984.4	1034.0	1075.7	1105.6	1131.6	1151.9	1163.6
22.5°	800.4	841.9	889.8	935.1	992.9	1042.1	1085.7	1109.4	1131.0	1140.9	1145.4
25°	772.2	822.2	876.5	931.7	997.0	1049.0	1089.0	1103.3	1109.6	1099.9	1084.0
27.5°	742.0	797.6	861.1	925.5	994.5	1044.5	1073.1	1070.9	1060.2	1028.9	1003.9
30°	719.3	780.6	848.8	919.1	988.4	1037.0	1053.6	1037.0	1012.7	977.8	942.1
32.5°	695.6	759.0	835.8	910.1	977.2	1019.9	1023.6	994.9	957.3	917.6	873.1
35°	659.7	728.3	811.2	889.8	953.4	980.4	964.4	913.8	869.2	814.9	754.3
37.5°	619.1	694.9	778.0	860.1	917.8	924.9	885.2	831.9	768.9	705.2	633.8
40°	588.8	669.1	754.7	837.5	888.5	881.2	830.5	772.0	697.0	619.1	552.8
42.5°	561.6	641.9	729.1	810.4	851.2	831.1	772.0	700.0	619.5	546.1	485.4
45°	514.5	597.1	686.3	764.9	788.3	752.0	673.7	593.8	514.5	453.3	405.3
47.5°	468.9	550.5	638.8	707.9	716.2	667.4	581.8	499.6	431.5	381.6	347.8
50°	435.2	517.2	604.8	666.4	663.7	604.8	516.8	438.5	381.7	341.3	318.7
52.5°	405.1	482.5	566.7	622.7	608.6	544.3	460.4	390.9	344.1	312.5	292.0
55°	358.3	429.9	509.9	554.8	528.9	457.5	386.6	330.6	296.0	272.4	256.5
57.5°	311.8	379.0	447.4	475.1	446.4	380.6	321.5	280.9	254.9	237.3	226.9
60°	283.0	341.7	402.6	426.6	392.3	333.7	287.0	250.7	229.8	215.4	206.2
62.5°	254.3	306.7	364.3	377.3	345.9	296.4	255.1	224.9	207.7	194.9	186.2
65°	215.2	258.1	301.8	310.4	281.4	243.1	210.4	190.8	175.5	166.2	159.2
67.5°	176.5	210.9	241.8	248.8	223.5	196.9	173.3	156.2	145.8	138.0	132.2
70°	153.6	180.8	206.2	211.8	191.5	167.8	149.9	136.2	126.9	120.2	114.6
72.5°	129.3	152.0	173.1	176.9	160.3	142.2	127.5	116.7	108.5	104.2	98.8
75°	98.9	112.3	128.6	129.6	118.6	107.5	96.2	89.3	84.9	79.6	77.0
77.5°	69.8	80.3	89.6	91.4	84.9	77.4	71.1	65.5	61.9	59.4	57.0
80°	53.3	61.6	65.6	67.9	63.3	58.0	54.3	50.6	48.3	46.6	44.9
82.5°	38.1	43.2	47.0	48.8	46.2	43.1	39.3	37.3	35.5	34.1	33.5
85°	19.4	21.7	24.0	24.6	24.0	22.6	20.7	20.7	19.6	19.4	19.4
87.5°	6.9	8.0	8.2	9.2	8.7	8.8	8.9	8.7	8.6	8.4	8.2
90°	1.0	1.7	2.4	3.1	3.7	4.2	4.7	5.3	5.8	6.1	6.4
92.5°	5.8	5.7	5.6	5.5	5.7	5.9	6.2	6.4	6.7	6.9	7.0
95°	16.6	14.5	12.4	10.3	9.5	9.9	10.3	10.8	11.2	11.6	11.9
97.5°	31.2	25.2	19.4	13.4	10.9	11.9	12.9	14.0	15.1	15.3	15.6
100°	42.3	33.4	24.7	16.0	12.0	13.2	14.3	15.3	16.4	16.9	17.5
102.5°	64.4	62.5	60.7	58.9	53.3	44.2	35.1	26.0	16.9	17.6	18.2
105°	89.5	91.5	93.5	95.3	87.6	70.1	52.6	35.0	17.6	18.3	19.0
107.5°	113.6	115.1	116.7	118.2	108.5	87.6	66.6	45.6	24.6	23.9	23.2
110°	129.0	130.5	131.8	133.1	124.5	106.0	87.5	68.9	50.5	44.1	37.6



TEST NUMBER: P331285-940
 CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	143.7	144.9	146.1	147.2	145.5	141.0	136.4	131.8	127.2	103.9	80.5
115°	166.8	168.0	169.1	170.1	171.5	173.1	174.7	176.3	177.9	148.2	118.6
117.5°	187.8	189.0	190.3	191.5	192.6	193.8	194.8	195.9	197.1	189.8	182.7
120°	202.8	203.8	204.7	205.6	206.7	207.9	209.0	210.2	211.3	212.1	212.9
122.5°	215.8	216.8	217.8	218.8	219.9	221.1	222.4	223.7	225.0	225.4	225.9
125°	235.2	236.0	236.9	237.7	238.8	240.0	241.2	242.4	243.6	244.1	244.5
127.5°	253.2	254.0	255.0	255.9	256.8	257.7	258.7	259.6	260.5	261.1	261.8
130°	264.6	265.6	266.6	267.6	268.5	269.2	269.9	270.6	271.3	272.0	272.7
132.5°	275.9	276.8	277.7	278.6	279.3	280.0	280.7	281.4	282.1	282.8	283.4
135°	291.1	292.1	293.1	294.2	295.0	295.5	296.1	296.7	297.3	297.9	298.5
137.5°	305.9	306.7	307.4	308.1	308.8	309.4	310.0	310.8	311.4	312.0	312.6
140°	315.7	316.1	316.6	317.2	317.8	318.5	319.2	319.9	320.6	321.2	321.7
142.5°	323.9	324.3	324.9	325.3	325.9	326.7	327.5	328.3	329.1	329.7	330.2
145°	336.4	336.4	336.3	336.2	336.7	337.8	338.9	340.0	341.1	341.5	342.0
147.5°	347.6	347.3	347.1	346.9	347.2	348.3	349.5	350.5	351.6	351.9	352.2
150°	354.7	354.3	353.8	353.4	353.7	354.7	355.8	356.8	357.8	358.2	358.6
152.5°	361.0	360.4	359.9	359.4	359.6	360.6	361.6	362.6	363.6	363.9	364.4
155°	369.9	369.3	368.7	368.2	368.3	369.1	369.8	370.6	371.3	371.8	372.1
157.5°	377.1	376.6	376.1	375.6	375.7	376.2	376.7	377.3	377.8	378.3	378.7
160°	381.4	380.9	380.6	380.2	380.2	380.6	380.9	381.4	381.7	382.1	382.5
162.5°	385.0	384.7	384.2	383.9	383.9	384.1	384.5	384.9	385.2	385.7	386.0
165°	390.0	389.6	389.2	388.9	388.8	389.0	389.1	389.3	389.5	389.9	390.4
167.5°	393.7	393.3	392.9	392.5	392.4	392.6	392.8	393.0	393.2	393.6	394.0
170°	395.7	395.4	395.0	394.6	394.5	394.6	394.8	394.8	395.0	395.5	395.9
172.5°	397.2	396.7	396.4	396.0	395.8	396.0	396.1	396.3	396.4	396.8	397.3
175°	398.9	398.4	398.0	397.5	397.3	397.5	397.6	397.8	397.9	398.3	398.8
177.5°	399.2	398.9	398.5	398.1	398.1	398.1	398.1	398.1	398.2	398.6	399.0
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	898.8	902.5	902.5	903.0	907.2	906.8	906.5
5°	956.4	962.1	962.8	968.8	972.8	971.4	967.8
7.5°	1010.8	1021.4	1029.4	1033.8	1039.1	1042.3	1040.9
10°	1054.0	1069.3	1078.6	1084.9	1092.6	1098.3	1096.3
12.5°	1093.1	1111.4	1124.2	1135.1	1136.0	1143.4	1138.4
15°	1154.2	1173.6	1175.5	1183.6	1189.9	1189.2	1189.5
17.5°	1174.4	1180.6	1181.9	1182.1	1182.1	1179.8	1174.7
20°	1167.2	1164.9	1159.2	1154.9	1147.3	1146.2	1139.6
22.5°	1133.1	1125.7	1111.5	1102.2	1090.2	1087.1	1085.2
25°	1066.0	1049.6	1027.0	1005.4	999.3	987.7	991.0
27.5°	973.8	948.4	923.9	906.3	890.5	873.0	878.0
30°	909.1	880.5	845.9	819.2	802.3	785.6	782.6
32.5°	831.9	789.9	751.3	727.8	701.8	691.3	679.8
35°	698.7	657.7	619.4	586.5	567.5	552.8	539.5
37.5°	578.8	531.7	500.8	474.1	460.4	452.0	454.1
40°	504.5	463.2	440.6	420.3	407.6	401.6	403.0
42.5°	444.3	413.4	394.8	380.8	371.9	368.5	367.7
45°	375.9	358.6	343.3	335.4	331.0	327.3	325.0
47.5°	329.4	315.2	306.6	301.8	298.0	294.4	294.3
50°	301.4	292.0	286.1	281.1	278.0	275.4	277.8
52.5°	280.1	271.5	265.6	261.1	259.9	257.5	257.5
55°	248.4	241.7	237.5	233.4	231.5	230.2	228.5
57.5°	219.6	213.3	209.4	206.8	203.0	201.7	201.2
60°	199.1	194.1	190.1	186.8	185.1	182.5	182.5
62.5°	180.2	175.2	171.5	169.0	166.2	165.1	165.4
65°	152.8	148.8	145.2	142.5	141.9	139.9	140.5
67.5°	127.7	125.0	121.2	119.7	118.4	117.3	116.5
70°	110.9	108.3	106.2	104.2	103.3	103.3	103.3
72.5°	96.8	93.5	92.4	89.9	90.4	89.3	88.3
75°	74.9	72.9	72.0	70.9	69.3	69.3	69.3
77.5°	55.1	54.6	53.3	52.3	51.9	51.5	51.7
80°	42.6	42.3	41.6	41.6	40.9	40.7	39.9
82.5°	32.7	31.9	31.5	31.2	31.1	31.0	30.9
85°	18.6	18.0	18.0	18.3	17.7	17.7	18.0
87.5°	8.6	8.6	8.4	8.4	8.7	8.5	8.5
90°	6.7	7.0	7.3	7.4	7.5	7.7	7.8
92.5°	7.2	7.3	7.5	7.6	7.7	7.7	7.8
95°	12.2	12.5	12.7	12.6	12.5	12.5	12.4
97.5°	15.8	16.1	16.2	16.3	16.4	16.5	16.6
100°	18.0	18.5	18.8	18.9	19.1	19.2	19.4
102.5°	18.9	19.5	20.0	20.2	20.3	20.5	20.7
105°	19.7	20.4	20.9	21.1	21.4	21.7	21.9
107.5°	22.5	21.8	21.5	21.8	22.0	22.3	22.6
110°	31.2	24.8	21.8	22.0	22.3	22.6	22.7



TEST NUMBER: P331285-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	57.2	33.8	22.2	22.4	22.6	22.8	23.0
115°	88.9	59.2	42.1	37.5	32.9	28.3	23.6
117.5°	175.5	168.4	157.2	142.0	126.9	111.7	96.6
120°	213.7	214.4	210.4	201.8	193.1	184.5	175.8
122.5°	226.3	226.8	226.1	224.5	222.8	221.1	219.5
125°	245.0	245.4	245.8	245.9	246.1	246.3	246.5
127.5°	262.4	263.1	263.4	263.5	263.5	263.5	263.6
130°	273.4	274.1	274.5	274.4	274.3	274.3	274.2
132.5°	283.9	284.5	284.8	284.7	284.7	284.6	284.5
135°	299.2	299.8	300.1	300.0	299.8	299.7	299.5
137.5°	313.3	313.9	314.1	313.9	313.7	313.4	313.3
140°	322.4	322.9	323.1	322.7	322.4	322.1	321.7
142.5°	330.7	331.3	331.4	331.0	330.7	330.4	330.0
145°	342.4	342.9	343.0	342.6	342.3	342.0	341.6
147.5°	352.6	352.9	352.9	352.7	352.4	352.1	351.9
150°	358.9	359.4	359.4	359.1	358.7	358.4	358.1
152.5°	364.7	365.1	365.1	364.6	364.3	363.8	363.4
155°	372.5	372.9	372.8	372.3	371.8	371.3	370.8
157.5°	379.2	379.5	379.5	379.0	378.5	378.0	377.6
160°	382.9	383.3	383.3	382.8	382.4	381.9	381.5
162.5°	386.5	386.9	386.9	386.3	385.8	385.2	384.7
165°	390.8	391.3	391.3	390.8	390.4	389.9	389.5
167.5°	394.5	394.9	394.8	394.3	393.7	393.2	392.5
170°	396.4	396.8	396.7	396.2	395.6	395.0	394.4
172.5°	397.7	398.1	398.1	397.5	397.0	396.4	395.8
175°	399.2	399.7	399.6	399.0	398.3	397.6	397.0
177.5°	399.3	399.7	399.6	399.1	398.7	398.2	397.8
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4

(END OF REPORT)