

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331303-940

Luminaire Tested: **SA2XXDIP-C485D725U940-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331303-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D725U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4497.3 lumens
Efficiency: N/A
Efficacy: 117.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331303-940
CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331303-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43				
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	44	43	42	37				
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31				
3	81	72	65	59	74	66	60	55	55	50	47	45	42	39	35	33	31	27				
4	74	64	56	50	67	59	52	47	49	44	40	40	37	34	32	29	27	24				
5	68	57	49	43	62	52	46	40	44	39	35	36	32	29	29	26	24	21				
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	21	18				
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17				
8	54	42	35	29	49	39	32	28	33	28	24	27	24	21	22	19	17	15				
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	21	18	16	14				
10	47	35	28	24	43	33	26	22	28	23	20	23	20	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13990	13990	13990	13990
5°	15686	14083	12478	14083
10°	17974	13967	10799	13967
15°	19883	13710	9541	13710
20°	19581	13435	8698	13435
25°	17655	13069	8165	13069
30°	14590	12486	7774	12486
35°	10634	11874	7496	11874
40°	8494	11152	7341	11152
45°	7421	10319	7133	10319
50°	6978	9510	6993	9510
55°	6432	8690	6804	8690
60°	5893	7818	6516	7818
65°	5368	7033	6235	7033
70°	4877	6274	5816	6274
75°	4323	5421	5153	5421
80°	3710	4491	4147	4491
85°	3335	3335	2464	3335



TEST NUMBER: P331303-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.5	1.8
10°-20°	239.9	5.3
20°-30°	348.2	7.7
30°-40°	367.4	8.2
40°-50°	325.3	7.2
50°-60°	259.6	5.8
60°-70°	176.5	3.9
70°-80°	90.5	2.0
80°-90°	24.0	0.5
90°-100°	29.4	0.7
100°-110°	107.8	2.4
110°-120°	288.3	6.4
120°-130°	475.8	10.6
130°-140°	506.0	11.3
140°-150°	470.3	10.5
150°-160°	378.1	8.4
160°-170°	243.7	5.4
170°-180°	83.9	1.9
0°-30°	670.6	14.9
0°-40°	1038.0	23.1
0°-60°	1623.0	36.1
0°-90°	1913.9	42.6
90°-120°	425.5	9.5
90°-150°	1877.7	41.8
90°-180°	2583.0	57.4
0°-180°	4497.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	866	866	866	866	866	
5°	968	869	770	869	968	97
15°	1190	820	571	820	1190	328
25°	991	734	458	734	991	448
35°	540	602	380	602	540	351
45°	325	452	312	452	325	256
55°	228	309	242	309	228	205
65°	140	184	163	184	140	140
75°	69	87	83	87	69	74
85°	18	18	13	18	18	20
90°	17	1	17	1	17	8
95°	28	42	28	42	28	26
105°	48	194	48	194	48	50
115°	52	367	52	367	52	131
125°	545	519	545	519	545	472
135°	663	642	663	642	663	511
145°	756	744	756	744	756	473
155°	820	820	820	820	820	379
165°	862	864	862	864	862	243
175°	878	883	878	883	878	84
180°	882	882	882	882	882	



TEST NUMBER: P331303-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	906.5	906.8	907.2	903.0	902.5	902.5	898.8	895.5	891.8	886.7	887.3
5°	967.8	971.4	972.8	968.8	962.8	962.1	956.4	947.1	938.4	931.5	926.5
7.5°	1040.9	1042.3	1039.1	1033.8	1029.4	1021.4	1010.8	1000.5	986.1	972.8	963.0
10°	1096.3	1098.3	1092.6	1084.9	1078.6	1069.3	1054.0	1038.3	1019.4	1001.0	986.4
12.5°	1138.4	1143.4	1136.0	1135.1	1124.2	1111.4	1093.1	1085.2	1058.5	1033.0	1017.3
15°	1189.5	1189.2	1189.9	1183.6	1175.5	1173.6	1154.2	1133.3	1095.6	1080.7	1054.6
17.5°	1174.7	1179.8	1182.1	1182.1	1181.9	1180.6	1174.4	1161.2	1142.3	1118.0	1088.1
20°	1139.6	1146.2	1147.3	1154.9	1159.2	1164.9	1167.2	1163.6	1151.9	1131.6	1105.6
22.5°	1085.2	1087.1	1090.2	1102.2	1111.5	1125.7	1133.1	1145.4	1140.9	1131.0	1109.4
25°	991.0	987.7	999.3	1005.4	1027.0	1049.6	1066.0	1084.0	1099.9	1109.6	1103.3
27.5°	878.0	873.0	890.5	906.3	923.9	948.4	973.8	1003.9	1028.9	1060.2	1070.9
30°	782.6	785.6	802.3	819.2	845.9	880.5	909.1	942.1	977.8	1012.7	1037.0
32.5°	679.8	691.3	701.8	727.8	751.3	789.9	831.9	873.1	917.6	957.3	994.9
35°	539.5	552.8	567.5	586.5	619.4	657.7	698.7	754.3	814.9	869.2	913.8
37.5°	454.1	452.0	460.4	474.1	500.8	531.7	578.8	633.8	705.2	768.9	831.9
40°	403.0	401.6	407.6	420.3	440.6	463.2	504.5	552.8	619.1	697.0	772.0
42.5°	367.7	368.5	371.9	380.8	394.8	413.4	444.3	485.4	546.1	619.5	700.0
45°	325.0	327.3	331.0	335.4	343.3	358.6	375.9	405.3	453.3	514.5	593.8
47.5°	294.3	294.4	298.0	301.8	306.6	315.2	329.4	347.8	381.6	431.5	499.6
50°	277.8	275.4	278.0	281.1	286.1	292.0	301.4	318.7	341.3	381.7	438.5
52.5°	257.5	257.5	259.9	261.1	265.6	271.5	280.1	292.0	312.5	344.1	390.9
55°	228.5	230.2	231.5	233.4	237.5	241.7	248.4	256.5	272.4	296.0	330.6
57.5°	201.2	201.7	203.0	206.8	209.4	213.3	219.6	226.9	237.3	254.9	280.9
60°	182.5	182.5	185.1	186.8	190.1	194.1	199.1	206.2	215.4	229.8	250.7
62.5°	165.4	165.1	166.2	169.0	171.5	175.2	180.2	186.2	194.9	207.7	224.9
65°	140.5	139.9	141.9	142.5	145.2	148.8	152.8	159.2	166.2	175.5	190.8
67.5°	116.5	117.3	118.4	119.7	121.2	125.0	127.7	132.2	138.0	145.8	156.2
70°	103.3	103.3	103.3	104.2	106.2	108.3	110.9	114.6	120.2	126.9	136.2
72.5°	88.3	89.3	90.4	89.9	92.4	93.5	96.8	98.8	104.2	108.5	116.7
75°	69.3	69.3	69.3	70.9	72.0	72.9	74.9	77.0	79.6	84.9	89.3
77.5°	51.7	51.5	51.9	52.3	53.3	54.6	55.1	57.0	59.4	61.9	65.5
80°	39.9	40.7	40.9	41.6	41.6	42.3	42.6	44.9	46.6	48.3	50.6
82.5°	30.9	31.0	31.1	31.2	31.5	31.9	32.7	33.5	34.1	35.5	37.3
85°	18.0	17.7	17.7	18.3	18.0	18.0	18.6	19.4	19.4	19.6	20.7
87.5°	10.3	10.3	10.5	10.2	10.2	10.3	10.2	9.7	9.9	10.0	10.1
90°	17.2	16.9	16.7	16.4	16.1	15.6	14.9	14.2	13.5	12.8	11.6
92.5°	17.2	17.0	16.9	16.7	16.6	16.2	15.9	15.5	15.2	14.8	14.3
95°	27.5	27.6	27.7	27.8	28.0	27.7	27.0	26.3	25.6	24.9	23.9
97.5°	36.6	36.5	36.3	36.1	35.9	35.6	35.0	34.4	33.9	33.3	31.0
100°	42.7	42.4	42.2	41.9	41.6	40.9	39.8	38.6	37.5	36.4	34.0
102.5°	45.8	45.4	45.0	44.6	44.2	43.2	41.8	40.3	38.9	37.4	35.5
105°	48.5	47.9	47.3	46.8	46.2	45.1	43.6	42.0	40.5	38.9	37.6
107.5°	49.8	49.3	48.8	48.2	47.6	48.2	49.7	51.3	52.9	54.5	100.9
110°	50.4	49.8	49.2	48.7	48.2	54.9	69.1	83.3	97.5	111.6	152.6



TEST NUMBER: P331303-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	50.9	50.5	50.0	49.6	49.0	74.7	126.4	178.2	229.9	281.5	291.7
115°	52.3	62.5	72.7	82.9	93.1	131.1	196.7	262.3	328.0	393.6	390.0
117.5°	213.6	247.1	280.6	314.1	347.7	372.4	388.3	404.2	420.1	436.0	433.5
120°	389.1	408.2	427.4	446.5	465.7	474.4	472.7	471.0	469.2	467.5	465.0
122.5°	485.5	489.3	492.9	496.7	500.4	501.8	500.7	499.7	498.6	497.7	494.9
125°	545.4	544.9	544.6	544.1	543.7	543.0	542.0	541.0	540.0	539.0	536.3
127.5°	583.2	583.1	583.0	582.9	582.8	582.0	580.6	579.2	577.7	576.2	574.3
130°	606.6	606.7	606.9	607.1	607.2	606.5	604.9	603.3	601.8	600.2	598.7
132.5°	629.5	629.7	629.9	630.0	630.2	629.5	628.2	626.9	625.5	624.2	622.7
135°	662.7	663.0	663.3	663.6	663.9	663.3	661.9	660.5	659.1	657.6	656.4
137.5°	692.9	693.5	693.9	694.5	694.9	694.5	693.0	691.7	690.3	688.9	687.4
140°	711.9	712.6	713.3	714.0	714.7	714.4	713.1	711.9	710.6	709.4	707.8
142.5°	730.2	730.9	731.6	732.4	733.1	732.8	731.6	730.5	729.3	728.2	726.4
145°	755.9	756.6	757.3	758.0	758.7	758.6	757.6	756.6	755.6	754.6	752.2
147.5°	778.5	779.1	779.6	780.2	780.9	780.8	780.1	779.3	778.6	777.8	775.4
150°	792.2	792.9	793.6	794.3	795.0	795.0	794.2	793.3	792.5	791.6	789.3
152.5°	804.0	804.9	805.8	806.8	807.7	807.8	806.9	806.0	805.2	804.3	802.2
155°	820.3	821.4	822.6	823.7	824.8	825.0	824.1	823.3	822.4	821.5	819.8
157.5°	835.3	836.3	837.4	838.6	839.6	839.7	838.7	837.8	836.9	835.9	834.6
160°	843.9	844.9	845.9	846.9	847.8	847.9	847.1	846.2	845.4	844.5	843.6
162.5°	851.0	852.3	853.5	854.7	856.0	856.0	855.1	854.1	853.2	852.2	851.5
165°	861.7	862.7	863.7	864.8	865.8	865.8	864.8	863.7	862.7	861.7	861.3
167.5°	868.5	869.8	871.1	872.4	873.6	873.8	872.8	871.8	870.8	869.8	869.4
170°	872.6	873.9	875.1	876.5	877.7	877.9	876.8	875.8	874.9	873.9	873.6
172.5°	875.7	876.9	878.2	879.5	880.7	880.9	879.9	879.0	878.0	876.9	876.6
175°	878.3	879.8	881.2	882.6	884.0	884.2	883.2	882.3	881.3	880.3	879.9
177.5°	880.0	881.0	882.1	883.1	884.1	884.2	883.4	882.6	881.8	881.0	880.9
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331303-940
 CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	889.1	887.0	885.6	880.9	876.6	872.4	871.0	871.6	865.7	860.1	857.7
5°	923.8	917.1	910.8	901.8	891.2	879.5	873.5	868.9	857.2	844.5	837.2
7.5°	954.8	945.3	933.1	916.2	900.7	882.3	870.7	860.4	843.3	825.5	814.6
10°	973.7	960.7	945.1	924.4	905.4	883.2	867.5	851.9	831.9	810.6	797.3
12.5°	990.0	972.5	957.1	930.6	908.1	880.2	861.7	839.6	818.6	793.3	780.2
15°	1028.7	996.4	967.1	937.1	909.5	870.5	849.9	820.2	792.6	761.3	746.3
17.5°	1058.5	1022.3	976.2	938.1	905.8	862.6	832.3	796.8	764.1	728.3	708.0
20°	1075.7	1034.0	984.4	939.1	900.4	851.2	818.2	781.9	743.6	703.3	681.4
22.5°	1085.7	1042.1	992.9	935.1	889.8	841.9	800.4	760.6	721.8	678.3	655.2
25°	1089.0	1049.0	997.0	931.7	876.5	822.2	772.2	733.6	686.7	646.0	612.4
27.5°	1073.1	1044.5	994.5	925.5	861.1	797.6	742.0	698.2	648.6	604.6	570.7
30°	1053.6	1037.0	988.4	919.1	848.8	780.6	719.3	669.7	620.5	575.8	541.2
32.5°	1023.6	1019.9	977.2	910.1	835.8	759.0	695.6	645.4	590.8	547.0	514.0
35°	964.4	980.4	953.4	889.8	811.2	728.3	659.7	602.4	545.8	503.8	472.9
37.5°	885.2	924.9	917.8	860.1	778.0	694.9	619.1	559.3	505.3	463.0	432.6
40°	830.5	881.2	888.5	837.5	754.7	669.1	588.8	529.1	476.5	437.9	407.2
42.5°	772.0	831.1	851.2	810.4	729.1	641.9	561.6	499.9	447.8	410.2	383.1
45°	673.7	752.0	788.3	764.9	686.3	597.1	514.5	451.9	404.7	369.3	348.3
47.5°	581.8	667.4	716.2	707.9	638.8	550.5	468.9	408.8	362.7	334.6	315.8
50°	516.8	604.8	663.7	666.4	604.8	517.2	435.2	378.6	336.4	310.0	294.7
52.5°	460.4	544.3	608.6	622.7	566.7	482.5	405.1	348.8	311.6	287.4	273.7
55°	386.6	457.5	528.9	554.8	509.9	429.9	358.3	308.7	273.8	257.1	245.1
57.5°	321.5	380.6	446.4	475.1	447.4	379.0	311.8	268.8	240.4	225.8	216.6
60°	287.0	333.7	392.3	426.6	402.6	341.7	283.0	242.1	218.8	205.8	197.2
62.5°	255.1	296.4	345.9	377.3	364.3	306.7	254.3	218.1	198.0	185.8	179.6
65°	210.4	243.1	281.4	310.4	301.8	258.1	215.2	184.1	168.2	158.5	153.6
67.5°	173.3	196.9	223.5	248.8	241.8	210.9	176.5	152.3	140.4	132.1	129.1
70°	149.9	167.8	191.5	211.8	206.2	180.8	153.6	132.9	122.5	115.6	112.5
72.5°	127.5	142.2	160.3	176.9	173.1	152.0	129.3	113.7	105.8	99.3	96.8
75°	96.2	107.5	118.6	129.6	128.6	112.3	98.9	86.9	80.6	75.6	74.6
77.5°	71.1	77.4	84.9	91.4	89.6	80.3	69.8	63.0	58.3	54.9	54.4
80°	54.3	58.0	63.3	67.9	65.6	61.6	53.3	48.3	44.9	41.6	40.3
82.5°	39.3	43.1	46.2	48.8	47.0	43.2	38.1	34.7	32.7	30.4	29.9
85°	20.7	22.6	24.0	24.6	24.0	21.7	19.4	18.0	16.3	15.3	15.0
87.5°	10.1	9.9	9.6	9.9	8.8	8.5	7.1	6.0	6.1	6.1	5.9
90°	10.5	9.4	8.2	6.9	5.4	3.7	2.2	0.6	2.2	3.7	5.4
92.5°	13.6	13.1	12.6	12.3	12.5	12.6	12.8	12.8	12.8	12.6	12.5
95°	22.9	21.9	20.9	22.7	27.5	32.1	36.8	41.5	36.8	32.1	27.5
97.5°	28.7	26.4	24.1	29.5	42.7	55.9	69.1	82.3	69.1	55.9	42.7
100°	31.6	29.2	26.8	35.2	54.7	74.1	93.5	112.9	93.5	74.1	54.7
102.5°	77.7	97.8	118.0	130.1	134.3	138.4	142.5	146.6	142.5	138.4	134.3
105°	116.3	155.0	193.7	210.9	206.7	202.4	198.1	193.9	198.1	202.4	206.7
107.5°	147.3	193.7	240.1	261.6	258.2	254.8	251.3	247.9	251.3	254.8	258.2
110°	193.6	234.5	275.4	294.4	291.5	288.6	285.5	282.6	285.5	288.6	291.5



TEST NUMBER: P331303-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	301.8	311.9	322.0	325.7	323.2	320.5	317.9	315.2	317.9	320.5	323.2
115°	386.5	382.9	379.4	376.4	374.0	371.6	369.2	366.8	369.2	371.6	374.0
117.5°	431.1	428.6	426.1	423.6	420.9	418.2	415.5	412.9	415.5	418.2	420.9
120°	462.4	459.9	457.4	455.0	452.9	450.8	448.6	446.5	448.6	450.8	452.9
122.5°	492.1	489.4	486.5	484.0	481.8	479.6	477.3	475.1	477.3	479.6	481.8
125°	533.6	530.9	528.2	525.9	524.1	522.3	520.4	518.6	520.4	522.3	524.1
127.5°	572.2	570.2	568.2	566.1	564.1	562.1	560.1	558.0	560.1	562.1	564.1
130°	597.1	595.6	594.0	592.1	589.8	587.5	585.3	583.0	585.3	587.5	589.8
132.5°	621.1	619.6	618.0	616.3	614.3	612.4	610.5	608.5	610.5	612.4	614.3
135°	655.1	653.8	652.6	650.8	648.5	646.2	644.0	641.7	644.0	646.2	648.5
137.5°	686.0	684.6	683.1	681.6	680.0	678.4	676.8	675.3	676.8	678.4	680.0
140°	706.2	704.6	703.1	701.7	700.6	699.5	698.3	697.2	698.3	699.5	700.6
142.5°	724.6	722.8	721.0	719.6	718.6	717.6	716.6	715.6	716.6	717.6	718.6
145°	749.8	747.3	744.9	743.9	744.0	744.1	744.2	744.4	744.2	744.1	744.0
147.5°	773.0	770.7	768.3	767.4	767.9	768.5	769.0	769.5	769.0	768.5	767.9
150°	787.0	784.8	782.6	781.9	782.9	783.9	784.9	785.9	784.9	783.9	782.9
152.5°	800.0	797.9	795.8	795.2	796.3	797.5	798.5	799.6	798.5	797.5	796.3
155°	818.1	816.5	814.8	814.6	815.8	817.1	818.4	819.7	818.4	817.1	815.8
157.5°	833.5	832.3	831.1	831.1	832.1	833.2	834.3	835.4	834.3	833.2	832.1
160°	842.8	842.0	841.2	841.2	842.0	842.8	843.6	844.5	843.6	842.8	842.0
162.5°	850.7	850.0	849.3	849.3	850.2	851.0	851.9	852.7	851.9	851.0	850.2
165°	860.9	860.5	860.1	860.2	861.1	862.0	862.8	863.7	862.8	862.0	861.1
167.5°	869.0	868.6	868.2	868.4	869.3	870.1	871.0	871.8	871.0	870.1	869.3
170°	873.3	873.1	872.7	873.1	873.9	874.8	875.6	876.5	875.6	874.8	873.9
172.5°	876.4	876.1	875.8	876.1	876.9	877.8	878.6	879.5	878.6	877.8	876.9
175°	879.7	879.4	879.1	879.5	880.5	881.5	882.4	883.4	882.4	881.5	880.5
177.5°	880.8	880.7	880.6	880.9	881.7	882.5	883.3	884.1	883.3	882.5	881.7
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331303-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	855.1	853.5	847.8	844.9	840.2	835.6	832.7	834.0	835.1	834.6	833.7
5°	830.5	824.2	814.6	806.2	800.2	789.3	784.6	782.3	780.2	777.9	775.6
7.5°	801.4	791.4	777.6	765.7	754.5	740.8	733.1	728.3	723.5	718.3	713.6
10°	780.6	766.6	752.0	735.3	722.0	709.6	698.7	691.3	684.7	678.3	673.7
12.5°	758.8	742.6	724.5	701.8	687.1	669.4	667.8	654.9	644.4	640.5	635.1
15°	724.0	701.3	678.3	651.4	639.7	623.8	613.8	603.8	594.8	588.4	586.7
17.5°	684.5	655.1	632.3	613.0	593.9	577.5	568.3	560.3	552.9	544.4	543.3
20°	654.3	629.1	604.1	587.1	567.5	550.8	539.5	531.5	525.1	520.1	515.9
22.5°	625.9	598.2	575.3	556.7	537.3	523.9	515.0	507.3	502.0	496.5	492.4
25°	580.1	558.5	533.5	512.6	496.5	487.9	480.5	473.9	470.6	466.9	462.3
27.5°	540.1	516.0	492.7	476.4	462.4	454.7	449.5	445.0	441.8	439.7	437.0
30°	511.8	487.5	469.2	453.3	441.6	433.9	430.6	427.9	424.3	422.9	421.6
32.5°	484.6	462.8	447.1	433.3	422.1	417.1	414.1	411.7	408.8	407.5	404.8
35°	446.2	427.9	412.6	404.9	395.9	391.6	389.3	385.9	383.3	382.0	381.7
37.5°	410.1	394.1	384.1	374.3	370.4	367.7	364.6	362.3	361.5	361.3	361.0
40°	386.6	373.6	364.6	356.7	355.0	351.0	348.3	346.3	346.3	346.7	346.3
42.5°	365.3	353.7	345.7	338.9	336.9	334.5	331.8	331.7	332.3	333.3	332.3
45°	333.1	324.7	319.1	315.7	312.0	309.7	309.3	310.4	310.7	311.0	312.0
47.5°	303.3	297.7	292.7	289.0	287.4	287.0	286.6	288.3	289.9	290.5	292.0
50°	285.7	279.4	275.1	272.8	271.4	270.7	271.4	273.4	274.7	276.4	277.4
52.5°	266.0	261.5	258.6	256.7	256.2	256.6	256.7	259.0	261.2	261.7	262.3
55°	238.8	235.4	234.8	231.8	233.1	232.7	234.4	235.8	237.7	239.8	240.1
57.5°	211.6	208.9	207.1	207.4	207.8	209.3	210.6	213.0	215.2	217.2	217.5
60°	193.5	192.2	191.2	191.2	191.8	193.9	195.5	197.8	199.1	200.5	201.4
62.5°	177.0	175.7	174.6	175.1	176.9	178.1	180.0	181.3	182.6	184.0	184.4
65°	150.9	150.2	151.2	151.9	152.2	153.8	156.2	157.2	158.5	159.2	161.5
67.5°	126.8	127.0	126.8	127.8	129.7	130.1	132.2	134.6	134.9	136.2	137.7
70°	110.6	111.2	111.9	112.5	114.2	114.9	116.5	117.5	118.9	119.8	120.9
72.5°	95.7	95.8	96.5	96.3	97.7	99.2	100.6	101.6	102.9	104.2	105.1
75°	73.6	73.6	74.3	74.6	76.2	77.9	77.6	78.3	79.6	81.0	81.6
77.5°	53.8	53.1	53.8	54.0	54.6	56.0	56.3	57.2	58.8	58.3	59.0
80°	40.9	39.9	40.9	41.3	41.3	43.0	43.0	43.6	44.6	43.6	44.6
82.5°	29.2	28.8	29.5	29.6	30.1	30.1	30.7	30.9	31.8	31.4	31.8
85°	14.6	14.4	14.6	14.4	14.6	15.0	15.0	14.6	14.6	15.3	14.4
87.5°	5.9	5.9	5.9	6.1	6.1	6.0	5.9	6.1	6.2	5.8	5.9
90°	6.9	8.2	9.4	10.5	11.6	12.8	13.5	14.2	14.9	15.6	16.1
92.5°	12.3	12.6	13.1	13.6	14.3	14.8	15.2	15.5	15.9	16.2	16.6
95°	22.7	20.9	21.9	22.9	23.9	24.9	25.6	26.3	27.0	27.7	28.0
97.5°	29.5	24.1	26.4	28.7	31.0	33.3	33.9	34.4	35.0	35.6	35.9
100°	35.2	26.8	29.2	31.6	34.0	36.4	37.5	38.6	39.8	40.9	41.6
102.5°	130.1	118.0	97.8	77.7	57.5	37.4	38.9	40.3	41.8	43.2	44.2
105°	210.9	193.7	155.0	116.3	77.6	38.9	40.5	42.0	43.6	45.1	46.2
107.5°	261.6	240.1	193.7	147.3	100.9	54.5	52.9	51.3	49.7	48.2	47.6
110°	294.4	275.4	234.5	193.6	152.6	111.6	97.5	83.3	69.1	54.9	48.2



TEST NUMBER: P331303-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	325.7	322.0	311.9	301.8	291.7	281.5	229.9	178.2	126.4	74.7	49.0
115°	376.4	379.4	382.9	386.5	390.0	393.6	328.0	262.3	196.7	131.1	93.1
117.5°	423.6	426.1	428.6	431.1	433.5	436.0	420.1	404.2	388.3	372.4	347.7
120°	455.0	457.4	459.9	462.4	465.0	467.5	469.2	471.0	472.7	474.4	465.7
122.5°	484.0	486.5	489.4	492.1	494.9	497.7	498.6	499.7	500.7	501.8	500.4
125°	525.9	528.2	530.9	533.6	536.3	539.0	540.0	541.0	542.0	543.0	543.7
127.5°	566.1	568.2	570.2	572.2	574.3	576.2	577.7	579.2	580.6	582.0	582.8
130°	592.1	594.0	595.6	597.1	598.7	600.2	601.8	603.3	604.9	606.5	607.2
132.5°	616.3	618.0	619.6	621.1	622.7	624.2	625.5	626.9	628.2	629.5	630.2
135°	650.8	652.6	653.8	655.1	656.4	657.6	659.1	660.5	661.9	663.3	663.9
137.5°	681.6	683.1	684.6	686.0	687.4	688.9	690.3	691.7	693.0	694.5	694.9
140°	701.7	703.1	704.6	706.2	707.8	709.4	710.6	711.9	713.1	714.4	714.7
142.5°	719.6	721.0	722.8	724.6	726.4	728.2	729.3	730.5	731.6	732.8	733.1
145°	743.9	744.9	747.3	749.8	752.2	754.6	755.6	756.6	757.6	758.6	758.7
147.5°	767.4	768.3	770.7	773.0	775.4	777.8	778.6	779.3	780.1	780.8	780.9
150°	781.9	782.6	784.8	787.0	789.3	791.6	792.5	793.3	794.2	795.0	795.0
152.5°	795.2	795.8	797.9	800.0	802.2	804.3	805.2	806.0	806.9	807.8	807.7
155°	814.6	814.8	816.5	818.1	819.8	821.5	822.4	823.3	824.1	825.0	824.8
157.5°	831.1	831.1	832.3	833.5	834.6	835.9	836.9	837.8	838.7	839.7	839.6
160°	841.2	841.2	842.0	842.8	843.6	844.5	845.4	846.2	847.1	847.9	847.8
162.5°	849.3	849.3	850.0	850.7	851.5	852.2	853.2	854.1	855.1	856.0	856.0
165°	860.2	860.1	860.5	860.9	861.3	861.7	862.7	863.7	864.8	865.8	865.8
167.5°	868.4	868.2	868.6	869.0	869.4	869.8	870.8	871.8	872.8	873.8	873.6
170°	873.1	872.7	873.1	873.3	873.6	873.9	874.9	875.8	876.8	877.9	877.7
172.5°	876.1	875.8	876.1	876.4	876.6	876.9	878.0	879.0	879.9	880.9	880.7
175°	879.5	879.1	879.4	879.7	879.9	880.3	881.3	882.3	883.2	884.2	884.0
177.5°	880.9	880.6	880.7	880.8	880.9	881.0	881.8	882.6	883.4	884.2	884.1
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331303-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	831.1	830.5	830.5	828.1	830.5	830.5	831.1	833.7	834.6	835.1	834.0
5°	771.0	769.9	768.3	769.9	768.3	769.9	771.0	775.6	777.9	780.2	782.3
7.5°	711.5	707.5	706.9	702.9	706.9	707.5	711.5	713.6	718.3	723.5	728.3
10°	668.1	665.4	665.0	658.7	665.0	665.4	668.1	673.7	678.3	684.7	691.3
12.5°	635.0	628.6	629.9	626.2	629.9	628.6	635.0	635.1	640.5	644.4	654.9
15°	577.7	577.7	576.5	570.8	576.5	577.7	577.7	586.7	588.4	594.8	603.8
17.5°	536.7	536.0	532.8	534.4	532.8	536.0	536.7	543.3	544.4	552.9	560.3
20°	512.2	510.1	506.2	506.2	506.2	510.1	512.2	515.9	520.1	525.1	531.5
22.5°	489.0	488.8	484.6	486.0	484.6	488.8	489.0	492.4	496.5	502.0	507.3
25°	461.9	459.2	457.3	458.3	457.3	459.2	461.9	462.3	466.9	470.6	473.9
27.5°	436.2	434.7	434.6	431.9	434.6	434.7	436.2	437.0	439.7	441.8	445.0
30°	421.2	417.9	418.6	417.0	418.6	417.9	421.2	421.6	422.9	424.3	427.9
32.5°	404.2	403.1	402.3	400.9	402.3	403.1	404.2	404.8	407.5	408.8	411.7
35°	380.9	381.3	379.6	380.3	379.6	381.3	380.9	381.7	382.0	383.3	385.9
37.5°	360.7	361.8	361.0	361.1	361.0	361.8	360.7	361.0	361.3	361.5	362.3
40°	347.3	347.3	347.3	348.3	347.3	347.3	347.3	346.3	346.7	346.3	346.3
42.5°	334.6	334.0	333.5	333.4	333.5	334.0	334.6	332.3	333.3	332.3	331.7
45°	312.7	313.7	314.1	312.4	314.1	313.7	312.7	312.0	311.0	310.7	310.4
47.5°	292.9	293.0	292.9	294.4	292.9	293.0	292.9	292.0	290.5	289.9	288.3
50°	279.1	278.4	279.1	278.4	279.1	278.4	279.1	277.4	276.4	274.7	273.4
52.5°	264.4	264.6	264.1	264.0	264.1	264.6	264.4	262.3	261.7	261.2	259.0
55°	241.5	242.1	241.7	241.7	241.7	242.1	241.5	240.1	239.8	237.7	235.8
57.5°	217.7	218.3	218.7	217.2	218.7	218.3	217.7	217.5	217.2	215.2	213.0
60°	201.2	202.8	202.5	201.8	202.5	202.8	201.2	201.4	200.5	199.1	197.8
62.5°	185.9	186.5	186.5	186.4	186.5	186.5	185.9	184.4	184.0	182.6	181.3
65°	162.5	163.2	162.2	163.2	162.2	163.2	162.5	161.5	159.2	158.5	157.2
67.5°	137.2	137.5	138.2	138.7	138.2	137.5	137.2	137.7	136.2	134.9	134.6
70°	121.5	121.2	122.3	123.2	122.3	121.2	121.5	120.9	119.8	118.9	117.5
72.5°	105.0	105.8	105.4	106.2	105.4	105.8	105.0	105.1	104.2	102.9	101.6
75°	81.0	81.9	81.6	82.6	81.6	81.9	81.0	81.6	81.0	79.6	78.3
77.5°	58.5	58.6	58.5	59.0	58.5	58.6	58.5	59.0	58.3	58.8	57.2
80°	44.6	44.0	43.2	44.6	43.2	44.0	44.6	44.6	43.6	44.6	43.6
82.5°	31.0	31.5	30.8	30.8	30.8	31.5	31.0	31.8	31.4	31.8	30.9
85°	14.4	14.0	13.3	13.3	13.3	14.0	14.4	14.4	15.3	14.6	14.6
87.5°	6.0	5.7	5.8	5.6	5.8	5.7	6.0	5.9	5.8	6.2	6.1
90°	16.4	16.7	16.9	17.2	16.9	16.7	16.4	16.1	15.6	14.9	14.2
92.5°	16.7	16.9	17.0	17.2	17.0	16.9	16.7	16.6	16.2	15.9	15.5
95°	27.8	27.7	27.6	27.5	27.6	27.7	27.8	28.0	27.7	27.0	26.3
97.5°	36.1	36.3	36.5	36.6	36.5	36.3	36.1	35.9	35.6	35.0	34.4
100°	41.9	42.2	42.4	42.7	42.4	42.2	41.9	41.6	40.9	39.8	38.6
102.5°	44.6	45.0	45.4	45.8	45.4	45.0	44.6	44.2	43.2	41.8	40.3
105°	46.8	47.3	47.9	48.5	47.9	47.3	46.8	46.2	45.1	43.6	42.0
107.5°	48.2	48.8	49.3	49.8	49.3	48.8	48.2	47.6	48.2	49.7	51.3
110°	48.7	49.2	49.8	50.4	49.8	49.2	48.7	48.2	54.9	69.1	83.3



TEST NUMBER: P331303-940
 CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	49.6	50.0	50.5	50.9	50.5	50.0	49.6	49.0	74.7	126.4	178.2
115°	82.9	72.7	62.5	52.3	62.5	72.7	82.9	93.1	131.1	196.7	262.3
117.5°	314.1	280.6	247.1	213.6	247.1	280.6	314.1	347.7	372.4	388.3	404.2
120°	446.5	427.4	408.2	389.1	408.2	427.4	446.5	465.7	474.4	472.7	471.0
122.5°	496.7	492.9	489.3	485.5	489.3	492.9	496.7	500.4	501.8	500.7	499.7
125°	544.1	544.6	544.9	545.4	544.9	544.6	544.1	543.7	543.0	542.0	541.0
127.5°	582.9	583.0	583.1	583.2	583.1	583.0	582.9	582.8	582.0	580.6	579.2
130°	607.1	606.9	606.7	606.6	606.7	606.9	607.1	607.2	606.5	604.9	603.3
132.5°	630.0	629.9	629.7	629.5	629.7	629.9	630.0	630.2	629.5	628.2	626.9
135°	663.6	663.3	663.0	662.7	663.0	663.3	663.6	663.9	663.3	661.9	660.5
137.5°	694.5	693.9	693.5	692.9	693.5	693.9	694.5	694.9	694.5	693.0	691.7
140°	714.0	713.3	712.6	711.9	712.6	713.3	714.0	714.7	714.4	713.1	711.9
142.5°	732.4	731.6	730.9	730.2	730.9	731.6	732.4	733.1	732.8	731.6	730.5
145°	758.0	757.3	756.6	755.9	756.6	757.3	758.0	758.7	758.6	757.6	756.6
147.5°	780.2	779.6	779.1	778.5	779.1	779.6	780.2	780.9	780.8	780.1	779.3
150°	794.3	793.6	792.9	792.2	792.9	793.6	794.3	795.0	795.0	794.2	793.3
152.5°	806.8	805.8	804.9	804.0	804.9	805.8	806.8	807.7	807.8	806.9	806.0
155°	823.7	822.6	821.4	820.3	821.4	822.6	823.7	824.8	825.0	824.1	823.3
157.5°	838.6	837.4	836.3	835.3	836.3	837.4	838.6	839.6	839.7	838.7	837.8
160°	846.9	845.9	844.9	843.9	844.9	845.9	846.9	847.8	847.9	847.1	846.2
162.5°	854.7	853.5	852.3	851.0	852.3	853.5	854.7	856.0	856.0	855.1	854.1
165°	864.8	863.7	862.7	861.7	862.7	863.7	864.8	865.8	865.8	864.8	863.7
167.5°	872.4	871.1	869.8	868.5	869.8	871.1	872.4	873.6	873.8	872.8	871.8
170°	876.5	875.1	873.9	872.6	873.9	875.1	876.5	877.7	877.9	876.8	875.8
172.5°	879.5	878.2	876.9	875.7	876.9	878.2	879.5	880.7	880.9	879.9	879.0
175°	882.6	881.2	879.8	878.3	879.8	881.2	882.6	884.0	884.2	883.2	882.3
177.5°	883.1	882.1	881.0	880.0	881.0	882.1	883.1	884.1	884.2	883.4	882.6
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331303-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	832.7	835.6	840.2	844.9	847.8	853.5	855.1	857.7	860.1	865.7	871.6
5°	784.6	789.3	800.2	806.2	814.6	824.2	830.5	837.2	844.5	857.2	868.9
7.5°	733.1	740.8	754.5	765.7	777.6	791.4	801.4	814.6	825.5	843.3	860.4
10°	698.7	709.6	722.0	735.3	752.0	766.6	780.6	797.3	810.6	831.9	851.9
12.5°	667.8	669.4	687.1	701.8	724.5	742.6	758.8	780.2	793.3	818.6	839.6
15°	613.8	623.8	639.7	651.4	678.3	701.3	724.0	746.3	761.3	792.6	820.2
17.5°	568.3	577.5	593.9	613.0	632.3	655.1	684.5	708.0	728.3	764.1	796.8
20°	539.5	550.8	567.5	587.1	604.1	629.1	654.3	681.4	703.3	743.6	781.9
22.5°	515.0	523.9	537.3	556.7	575.3	598.2	625.9	655.2	678.3	721.8	760.6
25°	480.5	487.9	496.5	512.6	533.5	558.5	580.1	612.4	646.0	686.7	733.6
27.5°	449.5	454.7	462.4	476.4	492.7	516.0	540.1	570.7	604.6	648.6	698.2
30°	430.6	433.9	441.6	453.3	469.2	487.5	511.8	541.2	575.8	620.5	669.7
32.5°	414.1	417.1	422.1	433.3	447.1	462.8	484.6	514.0	547.0	590.8	645.4
35°	389.3	391.6	395.9	404.9	412.6	427.9	446.2	472.9	503.8	545.8	602.4
37.5°	364.6	367.7	370.4	374.3	384.1	394.1	410.1	432.6	463.0	505.3	559.3
40°	348.3	351.0	355.0	356.7	364.6	373.6	386.6	407.2	437.9	476.5	529.1
42.5°	331.8	334.5	336.9	338.9	345.7	353.7	365.3	383.1	410.2	447.8	499.9
45°	309.3	309.7	312.0	315.7	319.1	324.7	333.1	348.3	369.3	404.7	451.9
47.5°	286.6	287.0	287.4	289.0	292.7	297.7	303.3	315.8	334.6	362.7	408.8
50°	271.4	270.7	271.4	272.8	275.1	279.4	285.7	294.7	310.0	336.4	378.6
52.5°	256.7	256.6	256.2	256.7	258.6	261.5	266.0	273.7	287.4	311.6	348.8
55°	234.4	232.7	233.1	231.8	234.8	235.4	238.8	245.1	257.1	273.8	308.7
57.5°	210.6	209.3	207.8	207.4	207.1	208.9	211.6	216.6	225.8	240.4	268.8
60°	195.5	193.9	191.8	191.2	191.2	192.2	193.5	197.2	205.8	218.8	242.1
62.5°	180.0	178.1	176.9	175.1	174.6	175.7	177.0	179.6	185.8	198.0	218.1
65°	156.2	153.8	152.2	151.9	151.2	150.2	150.9	153.6	158.5	168.2	184.1
67.5°	132.2	130.1	129.7	127.8	126.8	127.0	126.8	129.1	132.1	140.4	152.3
70°	116.5	114.9	114.2	112.5	111.9	111.2	110.6	112.5	115.6	122.5	132.9
72.5°	100.6	99.2	97.7	96.3	96.5	95.8	95.7	96.8	99.3	105.8	113.7
75°	77.6	77.9	76.2	74.6	74.3	73.6	73.6	74.6	75.6	80.6	86.9
77.5°	56.3	56.0	54.6	54.0	53.8	53.1	53.8	54.4	54.9	58.3	63.0
80°	43.0	43.0	41.3	41.3	40.9	39.9	40.9	40.3	41.6	44.9	48.3
82.5°	30.7	30.1	30.1	29.6	29.5	28.8	29.2	29.9	30.4	32.7	34.7
85°	15.0	15.0	14.6	14.4	14.6	14.4	14.6	15.0	15.3	16.3	18.0
87.5°	5.9	6.0	6.1	6.1	5.9	5.9	5.9	5.9	6.1	6.1	6.0
90°	13.5	12.8	11.6	10.5	9.4	8.2	6.9	5.4	3.7	2.2	0.6
92.5°	15.2	14.8	14.3	13.6	13.1	12.6	12.3	12.5	12.6	12.8	12.8
95°	25.6	24.9	23.9	22.9	21.9	20.9	22.7	27.5	32.1	36.8	41.5
97.5°	33.9	33.3	31.0	28.7	26.4	24.1	29.5	42.7	55.9	69.1	82.3
100°	37.5	36.4	34.0	31.6	29.2	26.8	35.2	54.7	74.1	93.5	112.9
102.5°	38.9	37.4	57.5	77.7	97.8	118.0	130.1	134.3	138.4	142.5	146.6
105°	40.5	38.9	77.6	116.3	155.0	193.7	210.9	206.7	202.4	198.1	193.9
107.5°	52.9	54.5	100.9	147.3	193.7	240.1	261.6	258.2	254.8	251.3	247.9
110°	97.5	111.6	152.6	193.6	234.5	275.4	294.4	291.5	288.6	285.5	282.6



TEST NUMBER: P331303-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	229.9	281.5	291.7	301.8	311.9	322.0	325.7	323.2	320.5	317.9	315.2
115°	328.0	393.6	390.0	386.5	382.9	379.4	376.4	374.0	371.6	369.2	366.8
117.5°	420.1	436.0	433.5	431.1	428.6	426.1	423.6	420.9	418.2	415.5	412.9
120°	469.2	467.5	465.0	462.4	459.9	457.4	455.0	452.9	450.8	448.6	446.5
122.5°	498.6	497.7	494.9	492.1	489.4	486.5	484.0	481.8	479.6	477.3	475.1
125°	540.0	539.0	536.3	533.6	530.9	528.2	525.9	524.1	522.3	520.4	518.6
127.5°	577.7	576.2	574.3	572.2	570.2	568.2	566.1	564.1	562.1	560.1	558.0
130°	601.8	600.2	598.7	597.1	595.6	594.0	592.1	589.8	587.5	585.3	583.0
132.5°	625.5	624.2	622.7	621.1	619.6	618.0	616.3	614.3	612.4	610.5	608.5
135°	659.1	657.6	656.4	655.1	653.8	652.6	650.8	648.5	646.2	644.0	641.7
137.5°	690.3	688.9	687.4	686.0	684.6	683.1	681.6	680.0	678.4	676.8	675.3
140°	710.6	709.4	707.8	706.2	704.6	703.1	701.7	700.6	699.5	698.3	697.2
142.5°	729.3	728.2	726.4	724.6	722.8	721.0	719.6	718.6	717.6	716.6	715.6
145°	755.6	754.6	752.2	749.8	747.3	744.9	743.9	744.0	744.1	744.2	744.4
147.5°	778.6	777.8	775.4	773.0	770.7	768.3	767.4	767.9	768.5	769.0	769.5
150°	792.5	791.6	789.3	787.0	784.8	782.6	781.9	782.9	783.9	784.9	785.9
152.5°	805.2	804.3	802.2	800.0	797.9	795.8	795.2	796.3	797.5	798.5	799.6
155°	822.4	821.5	819.8	818.1	816.5	814.8	814.6	815.8	817.1	818.4	819.7
157.5°	836.9	835.9	834.6	833.5	832.3	831.1	831.1	832.1	833.2	834.3	835.4
160°	845.4	844.5	843.6	842.8	842.0	841.2	841.2	842.0	842.8	843.6	844.5
162.5°	853.2	852.2	851.5	850.7	850.0	849.3	849.3	850.2	851.0	851.9	852.7
165°	862.7	861.7	861.3	860.9	860.5	860.1	860.2	861.1	862.0	862.8	863.7
167.5°	870.8	869.8	869.4	869.0	868.6	868.2	868.4	869.3	870.1	871.0	871.8
170°	874.9	873.9	873.6	873.3	873.1	872.7	873.1	873.9	874.8	875.6	876.5
172.5°	878.0	876.9	876.6	876.4	876.1	875.8	876.1	876.9	877.8	878.6	879.5
175°	881.3	880.3	879.9	879.7	879.4	879.1	879.5	880.5	881.5	882.4	883.4
177.5°	881.8	881.0	880.9	880.8	880.7	880.6	880.9	881.7	882.5	883.3	884.1
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331303-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	871.0	872.4	876.6	880.9	885.6	887.0	889.1	887.3	886.7	891.8	895.5
5°	873.5	879.5	891.2	901.8	910.8	917.1	923.8	926.5	931.5	938.4	947.1
7.5°	870.7	882.3	900.7	916.2	933.1	945.3	954.8	963.0	972.8	986.1	1000.5
10°	867.5	883.2	905.4	924.4	945.1	960.7	973.7	986.4	1001.0	1019.4	1038.3
12.5°	861.7	880.2	908.1	930.6	957.1	972.5	990.0	1017.3	1033.0	1058.5	1085.2
15°	849.9	870.5	909.5	937.1	967.1	996.4	1028.7	1054.6	1080.7	1095.6	1133.3
17.5°	832.3	862.6	905.8	938.1	976.2	1022.3	1058.5	1088.1	1118.0	1142.3	1161.2
20°	818.2	851.2	900.4	939.1	984.4	1034.0	1075.7	1105.6	1131.6	1151.9	1163.6
22.5°	800.4	841.9	889.8	935.1	992.9	1042.1	1085.7	1109.4	1131.0	1140.9	1145.4
25°	772.2	822.2	876.5	931.7	997.0	1049.0	1089.0	1103.3	1109.6	1099.9	1084.0
27.5°	742.0	797.6	861.1	925.5	994.5	1044.5	1073.1	1070.9	1060.2	1028.9	1003.9
30°	719.3	780.6	848.8	919.1	988.4	1037.0	1053.6	1037.0	1012.7	977.8	942.1
32.5°	695.6	759.0	835.8	910.1	977.2	1019.9	1023.6	994.9	957.3	917.6	873.1
35°	659.7	728.3	811.2	889.8	953.4	980.4	964.4	913.8	869.2	814.9	754.3
37.5°	619.1	694.9	778.0	860.1	917.8	924.9	885.2	831.9	768.9	705.2	633.8
40°	588.8	669.1	754.7	837.5	888.5	881.2	830.5	772.0	697.0	619.1	552.8
42.5°	561.6	641.9	729.1	810.4	851.2	831.1	772.0	700.0	619.5	546.1	485.4
45°	514.5	597.1	686.3	764.9	788.3	752.0	673.7	593.8	514.5	453.3	405.3
47.5°	468.9	550.5	638.8	707.9	716.2	667.4	581.8	499.6	431.5	381.6	347.8
50°	435.2	517.2	604.8	666.4	663.7	604.8	516.8	438.5	381.7	341.3	318.7
52.5°	405.1	482.5	566.7	622.7	608.6	544.3	460.4	390.9	344.1	312.5	292.0
55°	358.3	429.9	509.9	554.8	528.9	457.5	386.6	330.6	296.0	272.4	256.5
57.5°	311.8	379.0	447.4	475.1	446.4	380.6	321.5	280.9	254.9	237.3	226.9
60°	283.0	341.7	402.6	426.6	392.3	333.7	287.0	250.7	229.8	215.4	206.2
62.5°	254.3	306.7	364.3	377.3	345.9	296.4	255.1	224.9	207.7	194.9	186.2
65°	215.2	258.1	301.8	310.4	281.4	243.1	210.4	190.8	175.5	166.2	159.2
67.5°	176.5	210.9	241.8	248.8	223.5	196.9	173.3	156.2	145.8	138.0	132.2
70°	153.6	180.8	206.2	211.8	191.5	167.8	149.9	136.2	126.9	120.2	114.6
72.5°	129.3	152.0	173.1	176.9	160.3	142.2	127.5	116.7	108.5	104.2	98.8
75°	98.9	112.3	128.6	129.6	118.6	107.5	96.2	89.3	84.9	79.6	77.0
77.5°	69.8	80.3	89.6	91.4	84.9	77.4	71.1	65.5	61.9	59.4	57.0
80°	53.3	61.6	65.6	67.9	63.3	58.0	54.3	50.6	48.3	46.6	44.9
82.5°	38.1	43.2	47.0	48.8	46.2	43.1	39.3	37.3	35.5	34.1	33.5
85°	19.4	21.7	24.0	24.6	24.0	22.6	20.7	20.7	19.6	19.4	19.4
87.5°	7.1	8.5	8.8	9.9	9.6	9.9	10.1	10.1	10.0	9.9	9.7
90°	2.2	3.7	5.4	6.9	8.2	9.4	10.5	11.6	12.8	13.5	14.2
92.5°	12.8	12.6	12.5	12.3	12.6	13.1	13.6	14.3	14.8	15.2	15.5
95°	36.8	32.1	27.5	22.7	20.9	21.9	22.9	23.9	24.9	25.6	26.3
97.5°	69.1	55.9	42.7	29.5	24.1	26.4	28.7	31.0	33.3	33.9	34.4
100°	93.5	74.1	54.7	35.2	26.8	29.2	31.6	34.0	36.4	37.5	38.6
102.5°	142.5	138.4	134.3	130.1	118.0	97.8	77.7	57.5	37.4	38.9	40.3
105°	198.1	202.4	206.7	210.9	193.7	155.0	116.3	77.6	38.9	40.5	42.0
107.5°	251.3	254.8	258.2	261.6	240.1	193.7	147.3	100.9	54.5	52.9	51.3
110°	285.5	288.6	291.5	294.4	275.4	234.5	193.6	152.6	111.6	97.5	83.3



TEST NUMBER: P331303-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	317.9	320.5	323.2	325.7	322.0	311.9	301.8	291.7	281.5	229.9	178.2
115°	369.2	371.6	374.0	376.4	379.4	382.9	386.5	390.0	393.6	328.0	262.3
117.5°	415.5	418.2	420.9	423.6	426.1	428.6	431.1	433.5	436.0	420.1	404.2
120°	448.6	450.8	452.9	455.0	457.4	459.9	462.4	465.0	467.5	469.2	471.0
122.5°	477.3	479.6	481.8	484.0	486.5	489.4	492.1	494.9	497.7	498.6	499.7
125°	520.4	522.3	524.1	525.9	528.2	530.9	533.6	536.3	539.0	540.0	541.0
127.5°	560.1	562.1	564.1	566.1	568.2	570.2	572.2	574.3	576.2	577.7	579.2
130°	585.3	587.5	589.8	592.1	594.0	595.6	597.1	598.7	600.2	601.8	603.3
132.5°	610.5	612.4	614.3	616.3	618.0	619.6	621.1	622.7	624.2	625.5	626.9
135°	644.0	646.2	648.5	650.8	652.6	653.8	655.1	656.4	657.6	659.1	660.5
137.5°	676.8	678.4	680.0	681.6	683.1	684.6	686.0	687.4	688.9	690.3	691.7
140°	698.3	699.5	700.6	701.7	703.1	704.6	706.2	707.8	709.4	710.6	711.9
142.5°	716.6	717.6	718.6	719.6	721.0	722.8	724.6	726.4	728.2	729.3	730.5
145°	744.2	744.1	744.0	743.9	744.9	747.3	749.8	752.2	754.6	755.6	756.6
147.5°	769.0	768.5	767.9	767.4	768.3	770.7	773.0	775.4	777.8	778.6	779.3
150°	784.9	783.9	782.9	781.9	782.6	784.8	787.0	789.3	791.6	792.5	793.3
152.5°	798.5	797.5	796.3	795.2	795.8	797.9	800.0	802.2	804.3	805.2	806.0
155°	818.4	817.1	815.8	814.6	814.8	816.5	818.1	819.8	821.5	822.4	823.3
157.5°	834.3	833.2	832.1	831.1	831.1	832.3	833.5	834.6	835.9	836.9	837.8
160°	843.6	842.8	842.0	841.2	841.2	842.0	842.8	843.6	844.5	845.4	846.2
162.5°	851.9	851.0	850.2	849.3	849.3	850.0	850.7	851.5	852.2	853.2	854.1
165°	862.8	862.0	861.1	860.2	860.1	860.5	860.9	861.3	861.7	862.7	863.7
167.5°	871.0	870.1	869.3	868.4	868.2	868.6	869.0	869.4	869.8	870.8	871.8
170°	875.6	874.8	873.9	873.1	872.7	873.1	873.3	873.6	873.9	874.9	875.8
172.5°	878.6	877.8	876.9	876.1	875.8	876.1	876.4	876.6	876.9	878.0	879.0
175°	882.4	881.5	880.5	879.5	879.1	879.4	879.7	879.9	880.3	881.3	882.3
177.5°	883.3	882.5	881.7	880.9	880.6	880.7	880.8	880.9	881.0	881.8	882.6
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331303-940
 CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	898.8	902.5	902.5	903.0	907.2	906.8	906.5
5°	956.4	962.1	962.8	968.8	972.8	971.4	967.8
7.5°	1010.8	1021.4	1029.4	1033.8	1039.1	1042.3	1040.9
10°	1054.0	1069.3	1078.6	1084.9	1092.6	1098.3	1096.3
12.5°	1093.1	1111.4	1124.2	1135.1	1136.0	1143.4	1138.4
15°	1154.2	1173.6	1175.5	1183.6	1189.9	1189.2	1189.5
17.5°	1174.4	1180.6	1181.9	1182.1	1182.1	1179.8	1174.7
20°	1167.2	1164.9	1159.2	1154.9	1147.3	1146.2	1139.6
22.5°	1133.1	1125.7	1111.5	1102.2	1090.2	1087.1	1085.2
25°	1066.0	1049.6	1027.0	1005.4	999.3	987.7	991.0
27.5°	973.8	948.4	923.9	906.3	890.5	873.0	878.0
30°	909.1	880.5	845.9	819.2	802.3	785.6	782.6
32.5°	831.9	789.9	751.3	727.8	701.8	691.3	679.8
35°	698.7	657.7	619.4	586.5	567.5	552.8	539.5
37.5°	578.8	531.7	500.8	474.1	460.4	452.0	454.1
40°	504.5	463.2	440.6	420.3	407.6	401.6	403.0
42.5°	444.3	413.4	394.8	380.8	371.9	368.5	367.7
45°	375.9	358.6	343.3	335.4	331.0	327.3	325.0
47.5°	329.4	315.2	306.6	301.8	298.0	294.4	294.3
50°	301.4	292.0	286.1	281.1	278.0	275.4	277.8
52.5°	280.1	271.5	265.6	261.1	259.9	257.5	257.5
55°	248.4	241.7	237.5	233.4	231.5	230.2	228.5
57.5°	219.6	213.3	209.4	206.8	203.0	201.7	201.2
60°	199.1	194.1	190.1	186.8	185.1	182.5	182.5
62.5°	180.2	175.2	171.5	169.0	166.2	165.1	165.4
65°	152.8	148.8	145.2	142.5	141.9	139.9	140.5
67.5°	127.7	125.0	121.2	119.7	118.4	117.3	116.5
70°	110.9	108.3	106.2	104.2	103.3	103.3	103.3
72.5°	96.8	93.5	92.4	89.9	90.4	89.3	88.3
75°	74.9	72.9	72.0	70.9	69.3	69.3	69.3
77.5°	55.1	54.6	53.3	52.3	51.9	51.5	51.7
80°	42.6	42.3	41.6	41.6	40.9	40.7	39.9
82.5°	32.7	31.9	31.5	31.2	31.1	31.0	30.9
85°	18.6	18.0	18.0	18.3	17.7	17.7	18.0
87.5°	10.2	10.3	10.2	10.2	10.5	10.3	10.3
90°	14.9	15.6	16.1	16.4	16.7	16.9	17.2
92.5°	15.9	16.2	16.6	16.7	16.9	17.0	17.2
95°	27.0	27.7	28.0	27.8	27.7	27.6	27.5
97.5°	35.0	35.6	35.9	36.1	36.3	36.5	36.6
100°	39.8	40.9	41.6	41.9	42.2	42.4	42.7
102.5°	41.8	43.2	44.2	44.6	45.0	45.4	45.8
105°	43.6	45.1	46.2	46.8	47.3	47.9	48.5
107.5°	49.7	48.2	47.6	48.2	48.8	49.3	49.8
110°	69.1	54.9	48.2	48.7	49.2	49.8	50.4



TEST NUMBER: P331303-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	126.4	74.7	49.0	49.6	50.0	50.5	50.9
115°	196.7	131.1	93.1	82.9	72.7	62.5	52.3
117.5°	388.3	372.4	347.7	314.1	280.6	247.1	213.6
120°	472.7	474.4	465.7	446.5	427.4	408.2	389.1
122.5°	500.7	501.8	500.4	496.7	492.9	489.3	485.5
125°	542.0	543.0	543.7	544.1	544.6	544.9	545.4
127.5°	580.6	582.0	582.8	582.9	583.0	583.1	583.2
130°	604.9	606.5	607.2	607.1	606.9	606.7	606.6
132.5°	628.2	629.5	630.2	630.0	629.9	629.7	629.5
135°	661.9	663.3	663.9	663.6	663.3	663.0	662.7
137.5°	693.0	694.5	694.9	694.5	693.9	693.5	692.9
140°	713.1	714.4	714.7	714.0	713.3	712.6	711.9
142.5°	731.6	732.8	733.1	732.4	731.6	730.9	730.2
145°	757.6	758.6	758.7	758.0	757.3	756.6	755.9
147.5°	780.1	780.8	780.9	780.2	779.6	779.1	778.5
150°	794.2	795.0	795.0	794.3	793.6	792.9	792.2
152.5°	806.9	807.8	807.7	806.8	805.8	804.9	804.0
155°	824.1	825.0	824.8	823.7	822.6	821.4	820.3
157.5°	838.7	839.7	839.6	838.6	837.4	836.3	835.3
160°	847.1	847.9	847.8	846.9	845.9	844.9	843.9
162.5°	855.1	856.0	856.0	854.7	853.5	852.3	851.0
165°	864.8	865.8	865.8	864.8	863.7	862.7	861.7
167.5°	872.8	873.8	873.6	872.4	871.1	869.8	868.5
170°	876.8	877.9	877.7	876.5	875.1	873.9	872.6
172.5°	879.9	880.9	880.7	879.5	878.2	876.9	875.7
175°	883.2	884.2	884.0	882.6	881.2	879.8	878.3
177.5°	883.4	884.2	884.1	883.1	882.1	881.0	880.0
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5

(END OF REPORT)