

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332703-930

Luminaire Tested: **SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332703-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7538.5 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332703-930
CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332703-930

CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	95	91	87	92	88	85	81	76	73	71	64	63	61	54	53	51	47				
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39				
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33				
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	38	34	32	28				
5	69	57	49	43	64	54	46	41	47	41	36	40	35	32	34	30	28	25				
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24	22				
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22	19				
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	19	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13116	13116	13116
5°	13156	12998	13092
10°	13073	12892	12956
15°	12915	12709	12741
20°	12706	12482	12493
25°	12466	12222	12188
30°	12172	11918	11808
35°	11869	11599	11445
40°	11552	11236	11031
45°	11222	10880	10671
50°	10857	10562	10236
55°	10463	10151	9821
60°	10069	9689	9397
65°	9626	9251	8879
70°	9128	8665	8327
75°	8366	7960	7757
80°	7443	7141	6960
85°	6512	6271	6150



TEST NUMBER: P332703-930

CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.0	2.0
10°-20°	431.1	5.7
20°-30°	634.5	8.4
30°-40°	737.7	9.8
40°-50°	737.7	9.8
50°-60°	645.3	8.6
60°-70°	479.2	6.4
70°-80°	272.3	3.6
80°-90°	81.7	1.1
90°-100°	37.2	0.5
100°-110°	237.3	3.1
110°-120°	453.9	6.0
120°-130°	576.3	7.6
130°-140°	616.6	8.2
140°-150°	576.6	7.6
150°-160°	464.9	6.2
160°-170°	299.9	4.0
170°-180°	103.4	1.4
0°-30°	1218.6	16.2
0°-40°	1956.3	26.0
0°-60°	3339.3	44.3
0°-90°	4172.5	55.3
90°-120°	728.5	9.7
90°-150°	2497.9	33.1
90°-180°	3366.0	44.7
0°-180°	7538.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1625	1625	1625	1625	1625	
5°	1623	1618	1604	1617	1616	154
15°	1545	1539	1521	1528	1524	435
25°	1400	1390	1372	1373	1368	644
35°	1204	1195	1177	1168	1161	753
45°	983	973	953	939	935	757
55°	743	739	721	706	698	666
65°	504	497	484	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	2	11	18	23	24	6
95°	45	19	18	23	24	58
105°	245	250	254	259	232	256
115°	457	460	459	461	461	450
125°	643	646	645	647	648	574
135°	798	797	800	802	803	614
145°	920	922	922	923	924	574
155°	1008	1009	1007	1010	1008	465
165°	1064	1060	1060	1065	1059	300
175°	1088	1084	1084	1090	1082	104
180°	1088	1088	1088	1088	1088	



TEST NUMBER: P332703-930

CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1628.9	1628.2	1627.5	1626.8	1626.1	1624.5	1622.0	1619.4	1616.9	1614.4	1616.7
5°	1623.4	1622.3	1621.1	1620.0	1618.9	1616.7	1613.5	1610.3	1607.1	1603.9	1607.1
7.5°	1608.3	1607.2	1606.1	1604.8	1603.7	1601.4	1597.8	1594.3	1590.8	1587.2	1589.8
10°	1594.8	1593.7	1592.5	1591.3	1590.2	1587.7	1584.0	1580.2	1576.5	1572.7	1575.0
12.5°	1577.1	1576.0	1574.8	1573.6	1572.5	1569.9	1565.9	1562.0	1558.0	1554.0	1556.5
15°	1545.3	1544.2	1543.0	1541.9	1540.7	1538.0	1533.6	1529.3	1524.9	1520.6	1522.3
17.5°	1507.1	1505.6	1504.1	1502.8	1501.3	1498.5	1494.4	1490.3	1486.2	1482.1	1483.2
20°	1479.0	1477.5	1476.0	1474.6	1473.2	1470.2	1465.9	1461.6	1457.3	1452.9	1453.8
22.5°	1448.7	1446.8	1445.0	1443.0	1441.1	1437.9	1433.6	1429.3	1425.0	1420.6	1422.2
25°	1399.5	1397.5	1395.5	1393.4	1391.4	1388.4	1384.3	1380.3	1376.2	1372.1	1372.5
27.5°	1343.3	1341.2	1339.1	1337.0	1335.0	1332.0	1328.3	1324.5	1320.8	1317.0	1316.3
30°	1305.8	1303.5	1301.1	1298.9	1296.6	1293.5	1289.7	1286.0	1282.2	1278.5	1277.3
32.5°	1266.2	1264.1	1262.1	1260.0	1257.8	1254.8	1250.8	1246.8	1242.8	1238.8	1237.5
35°	1204.3	1202.2	1200.2	1198.2	1196.1	1193.1	1189.0	1185.0	1181.0	1176.9	1174.8
37.5°	1138.9	1137.0	1135.2	1133.3	1131.5	1128.4	1124.1	1119.7	1115.3	1111.0	1108.8
40°	1096.2	1093.9	1091.5	1089.2	1087.0	1083.6	1079.3	1074.9	1070.6	1066.2	1063.3
42.5°	1050.4	1049.0	1047.6	1046.2	1044.8	1041.7	1036.9	1032.1	1027.3	1022.5	1019.1
45°	982.9	980.9	978.8	976.8	974.9	971.5	966.9	962.2	957.6	953.0	949.8
47.5°	912.3	910.9	909.5	908.2	906.8	904.0	899.7	895.4	891.1	886.9	883.3
50°	864.5	863.3	862.1	861.0	859.8	857.2	853.1	849.1	845.1	841.0	837.0
52.5°	817.6	816.2	814.8	813.4	812.0	809.2	804.9	800.6	796.4	792.1	788.5
55°	743.4	742.5	741.7	740.8	739.9	737.4	733.4	729.4	725.3	721.2	717.8
57.5°	672.5	671.6	670.6	669.6	668.6	666.1	662.1	658.1	654.1	650.1	646.9
60°	623.6	622.2	620.7	619.3	617.8	615.2	611.5	607.7	603.9	600.1	597.5
62.5°	575.7	574.5	573.2	572.0	570.9	568.3	564.3	560.3	556.3	552.3	549.9
65°	503.9	502.4	500.9	499.5	498.1	495.9	493.0	490.1	487.2	484.3	481.4
67.5°	431.5	430.2	428.8	427.5	426.2	424.0	421.3	418.5	415.7	412.9	410.2
70°	386.7	384.7	382.6	380.6	378.5	376.4	374.1	371.8	369.4	367.1	364.8
72.5°	338.8	336.7	334.7	332.6	330.7	328.7	326.9	325.0	323.2	321.3	319.4
75°	268.2	266.8	265.3	263.8	262.4	261.0	259.5	258.0	256.7	255.2	254.0
77.5°	200.7	200.1	199.5	198.9	198.2	197.2	196.0	194.7	193.5	192.2	191.8
80°	160.1	159.2	158.4	157.5	156.7	156.0	155.4	154.7	154.2	153.6	153.0
82.5°	120.6	120.2	119.8	119.4	119.0	118.7	118.5	118.5	118.3	118.2	117.9
85°	70.3	70.3	70.3	70.3	70.3	70.0	69.5	68.9	68.2	67.7	67.7
87.5°	27.6	27.7	27.9	28.0	28.2	28.4	28.4	28.5	28.5	28.6	28.8
90°	2.4	4.4	6.4	8.4	10.4	12.1	13.5	15.0	16.5	17.9	19.0
92.5°	10.3	10.4	10.4	10.6	10.7	11.5	12.9	14.3	15.8	17.3	18.3
95°	44.8	38.6	32.4	26.3	20.1	17.2	17.4	17.5	17.7	17.9	19.0
97.5°	95.1	98.9	102.7	106.6	110.4	102.2	82.0	61.9	41.7	21.5	21.6
100°	133.5	136.7	140.0	143.2	146.5	135.7	110.7	85.8	60.7	35.8	32.8
102.5°	176.4	178.9	181.2	183.6	186.0	185.6	182.3	179.0	175.8	172.5	139.3
105°	245.0	246.1	247.1	248.3	249.3	250.3	251.2	252.1	253.1	254.0	255.6
107.5°	308.6	309.2	309.7	310.2	310.8	311.7	312.9	314.1	315.4	316.6	317.4
110°	351.6	352.1	352.7	353.2	353.8	354.6	355.6	356.8	357.8	358.9	359.3



TEST NUMBER: P332703-930

CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.3	394.3	395.3	396.2	397.2	397.9	398.4	398.9	399.4	399.9	399.9
115°	457.4	458.0	458.5	459.0	459.6	459.7	459.6	459.4	459.2	459.0	459.4
117.5°	515.2	515.9	516.7	517.4	518.1	518.6	519.0	519.4	519.8	520.2	520.2
120°	554.2	555.0	555.7	556.4	557.2	557.4	557.3	557.1	556.8	556.7	557.1
122.5°	590.7	591.2	591.6	592.0	592.5	592.8	593.0	593.3	593.5	593.8	594.0
125°	642.9	643.7	644.4	645.1	645.9	646.0	645.7	645.3	645.0	644.6	645.1
127.5°	692.4	692.6	692.8	693.0	693.2	693.7	694.6	695.4	696.2	697.0	696.9
130°	724.4	724.6	724.7	724.9	725.0	725.5	726.0	726.5	727.1	727.7	727.8
132.5°	753.7	754.0	754.3	754.6	755.0	755.5	756.2	756.8	757.5	758.2	758.4
135°	797.6	797.4	797.3	797.0	796.9	797.1	797.9	798.6	799.3	800.1	800.4
137.5°	836.5	836.6	836.7	836.7	836.8	837.2	838.0	838.9	839.6	840.4	840.8
140°	861.9	862.3	862.7	863.0	863.3	863.7	864.1	864.5	864.8	865.2	865.7
142.5°	884.7	885.3	886.0	886.6	887.3	887.7	887.9	888.2	888.4	888.6	889.0
145°	919.7	920.2	920.8	921.3	921.9	922.1	922.1	922.1	922.1	922.1	922.3
147.5°	947.5	948.5	949.6	950.6	951.6	952.0	951.8	951.6	951.5	951.3	951.5
150°	967.7	968.4	969.1	969.9	970.6	970.9	970.7	970.5	970.4	970.1	970.1
152.5°	984.6	985.2	985.8	986.3	986.9	987.1	986.8	986.4	986.1	985.8	986.1
155°	1008.4	1008.6	1008.8	1008.9	1009.1	1008.9	1008.4	1007.9	1007.3	1006.8	1007.5
157.5°	1028.4	1028.3	1028.2	1028.1	1028.0	1027.6	1027.0	1026.4	1025.8	1025.2	1026.1
160°	1040.2	1039.6	1039.1	1038.5	1038.0	1037.6	1037.5	1037.2	1037.1	1036.9	1038.0
162.5°	1050.6	1049.9	1049.2	1048.5	1047.8	1047.4	1047.2	1047.0	1046.8	1046.7	1047.7
165°	1063.7	1062.8	1061.9	1061.0	1060.1	1059.6	1059.6	1059.6	1059.6	1059.6	1061.1
167.5°	1074.2	1073.3	1072.3	1071.4	1070.4	1069.9	1069.8	1069.7	1069.6	1069.4	1071.1
170°	1080.0	1079.0	1077.8	1076.8	1075.7	1075.2	1075.4	1075.6	1075.8	1076.0	1077.4
172.5°	1083.9	1082.9	1081.7	1080.7	1079.6	1079.1	1079.3	1079.5	1079.7	1079.9	1081.3
175°	1088.2	1087.1	1086.0	1084.9	1083.9	1083.4	1083.5	1083.8	1083.9	1084.1	1085.7
177.5°	1090.1	1089.1	1088.1	1087.1	1086.1	1085.7	1086.0	1086.3	1086.5	1086.9	1088.0
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2



TEST NUMBER: P332703-930

CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1618.9	1621.3	1623.6	1624.6	1624.4	1624.2	1623.9	1623.7
5°	1610.3	1613.5	1616.7	1618.0	1617.4	1616.8	1616.2	1615.6
7.5°	1592.4	1594.9	1597.4	1598.6	1598.2	1597.8	1597.5	1597.2
10°	1577.3	1579.6	1581.9	1582.8	1582.3	1581.7	1581.0	1580.5
12.5°	1559.0	1561.5	1564.2	1565.0	1564.2	1563.3	1562.5	1561.7
15°	1524.0	1525.8	1527.5	1528.0	1527.1	1526.2	1525.3	1524.5
17.5°	1484.3	1485.4	1486.5	1486.7	1486.1	1485.6	1485.0	1484.4
20°	1454.7	1455.5	1456.4	1456.5	1456.0	1455.4	1454.8	1454.2
22.5°	1423.8	1425.3	1426.9	1427.1	1426.1	1425.1	1424.0	1422.9
25°	1372.8	1373.0	1373.4	1372.9	1371.7	1370.6	1369.5	1368.3
27.5°	1315.6	1314.9	1314.2	1313.1	1311.7	1310.3	1308.8	1307.3
30°	1276.1	1275.0	1273.8	1272.5	1271.1	1269.7	1268.2	1266.7
32.5°	1236.1	1234.7	1233.3	1231.9	1230.4	1229.0	1227.6	1226.1
35°	1172.9	1170.9	1168.8	1167.1	1165.6	1164.2	1162.7	1161.3
37.5°	1106.6	1104.4	1102.2	1100.2	1098.3	1096.3	1094.5	1092.5
40°	1060.5	1057.5	1054.7	1052.5	1051.1	1049.6	1048.1	1046.7
42.5°	1015.8	1012.4	1009.1	1006.9	1005.9	1004.9	1004.0	1003.0
45°	946.6	943.5	940.3	938.2	937.3	936.5	935.6	934.7
47.5°	879.7	876.1	872.5	869.6	867.4	865.2	863.0	860.8
50°	832.9	828.8	824.8	821.9	820.2	818.5	816.7	815.0
52.5°	784.9	781.3	777.7	774.9	772.7	770.5	768.3	766.1
55°	714.3	710.9	707.4	704.7	703.0	701.3	699.5	697.8
57.5°	643.6	640.3	637.0	634.5	632.8	631.1	629.4	627.8
60°	594.9	592.4	589.8	587.7	586.3	584.8	583.4	582.0
62.5°	547.5	545.1	542.7	540.9	539.4	537.9	536.5	535.1
65°	478.5	475.6	472.7	470.6	469.1	467.7	466.2	464.8
67.5°	407.4	404.6	401.9	400.2	399.8	399.4	399.0	398.6
70°	362.5	360.2	357.8	356.3	355.4	354.6	353.7	352.8
72.5°	317.6	315.8	313.9	312.5	311.7	310.8	309.9	309.1
75°	252.8	251.7	250.5	249.8	249.6	249.2	248.9	248.7
77.5°	191.4	191.1	190.8	190.2	189.5	188.7	187.9	187.2
80°	152.5	151.9	151.3	150.9	150.6	150.3	150.0	149.7
82.5°	117.5	117.2	116.8	116.5	116.2	115.9	115.6	115.4
85°	67.7	67.7	67.7	67.6	67.3	66.9	66.7	66.4
87.5°	29.0	29.2	29.4	29.6	29.7	29.8	29.8	29.8
90°	20.1	21.2	22.3	23.0	23.3	23.7	24.1	24.4
92.5°	19.4	20.5	21.6	22.2	22.3	22.3	22.4	22.5
95°	20.1	21.2	22.3	22.9	23.1	23.2	23.4	23.6
97.5°	21.7	21.9	21.9	22.1	22.3	22.4	22.6	22.8
100°	29.7	26.6	23.5	22.1	22.3	22.4	22.6	22.8
102.5°	106.2	73.1	39.9	23.3	23.3	23.4	23.4	23.5
105°	257.2	258.8	260.4	258.0	251.5	245.0	238.5	232.0
107.5°	318.2	319.0	319.8	320.5	321.2	321.9	322.6	323.3
110°	359.6	360.0	360.4	360.9	361.3	361.9	362.5	363.0



TEST NUMBER: P332703-930

CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	399.8	399.7	399.7	400.0	400.6	401.4	402.0	402.7
115°	459.7	460.2	460.5	460.6	460.6	460.6	460.6	460.6
117.5°	520.1	520.0	519.9	519.9	519.8	519.8	519.7	519.6
120°	557.4	557.7	558.2	558.2	557.7	557.4	557.1	556.7
122.5°	594.3	594.4	594.7	594.6	594.3	593.9	593.5	593.1
125°	645.7	646.2	646.8	647.1	647.3	647.5	647.7	647.8
127.5°	696.8	696.7	696.6	696.4	696.3	696.2	696.0	695.9
130°	728.0	728.1	728.3	728.5	728.5	728.5	728.5	728.5
132.5°	758.6	758.8	759.0	759.0	758.8	758.6	758.6	758.4
135°	800.8	801.1	801.5	801.8	802.3	802.6	802.9	803.3
137.5°	841.2	841.6	842.0	842.1	842.0	842.0	841.8	841.7
140°	866.3	866.8	867.3	867.7	867.9	868.0	868.2	868.5
142.5°	889.4	889.8	890.2	890.4	890.5	890.5	890.6	890.6
145°	922.5	922.7	922.8	923.2	923.5	923.8	924.2	924.5
147.5°	951.5	951.7	951.9	952.0	952.2	952.4	952.6	952.8
150°	970.1	970.1	970.1	970.2	970.5	970.6	970.8	970.9
152.5°	986.3	986.7	986.9	987.0	986.9	986.8	986.7	986.6
155°	1008.2	1008.9	1009.7	1009.7	1009.3	1008.7	1008.1	1007.6
157.5°	1027.0	1028.0	1028.9	1028.9	1028.0	1027.0	1026.1	1025.2
160°	1039.1	1040.2	1041.2	1041.2	1040.2	1039.1	1038.0	1036.9
162.5°	1048.8	1049.9	1051.0	1050.9	1049.7	1048.5	1047.3	1046.0
165°	1062.6	1064.0	1065.4	1065.4	1063.7	1062.1	1060.5	1058.8
167.5°	1072.6	1074.2	1075.8	1075.7	1073.9	1072.1	1070.2	1068.4
170°	1078.9	1080.3	1081.7	1081.6	1079.8	1078.0	1076.1	1074.3
172.5°	1082.8	1084.2	1085.7	1085.4	1083.5	1081.5	1079.5	1077.6
175°	1087.4	1089.0	1090.6	1090.3	1088.2	1086.0	1083.9	1081.7
177.5°	1089.2	1090.3	1091.5	1091.2	1089.5	1087.8	1086.0	1084.3
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2

(END OF REPORT)