

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331310-940

Luminaire Tested: **SA2XXDIP-C485D725U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331310-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D725U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4074.9 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331310-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331310-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43				
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36				
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	35	31				
3	80	71	63	58	73	65	58	53	54	49	45	44	40	38	34	32	30	26				
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22				
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19				
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20	17				
7	57	45	37	32	52	41	34	30	35	29	26	29	25	22	23	20	18	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	17	14	12				
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11183	11183	11183
5°	11225	11063	11128
10°	11158	10952	11006
15°	11020	10810	10798
20°	10825	10596	10584
25°	10630	10334	10334
30°	10381	10094	10006
35°	10147	9806	9662
40°	9853	9518	9333
45°	9565	9229	9001
50°	9251	8932	8616
55°	8923	8586	8267
60°	8557	8173	7869
65°	8164	7759	7404
70°	7671	7260	6916
75°	6981	6687	6525
80°	6192	6007	5700
85°	5057	4798	4316



TEST NUMBER: P331310-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.1	1.6
10°-20°	183.3	4.5
20°-30°	269.4	6.6
30°-40°	312.9	7.7
40°-50°	312.5	7.7
50°-60°	272.6	6.7
60°-70°	201.5	4.9
70°-80°	114.1	2.8
80°-90°	34.0	0.8
90°-100°	52.3	1.3
100°-110°	162.5	4.0
110°-120°	277.9	6.8
120°-130°	365.4	9.0
130°-140°	410.1	10.1
140°-150°	402.1	9.9
150°-160°	337.3	8.3
160°-170°	223.7	5.5
170°-180°	78.2	1.9
0°-30°	517.7	12.7
0°-40°	830.6	20.4
0°-60°	1415.7	34.7
0°-90°	1765.4	43.3
90°-120°	492.7	12.1
90°-150°	1670.3	41.0
90°-180°	2309.0	56.7
0°-180°	4074.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	693	693	693	693	693	
5°	693	690	683	688	687	66
15°	659	655	647	649	646	186
25°	597	591	580	581	580	274
35°	515	508	498	494	490	321
45°	419	414	404	397	394	323
55°	317	313	305	297	294	283
65°	214	210	203	197	194	211
75°	112	110	107	104	105	120
85°	27	27	26	24	23	31
90°	1	9	24	23	24	3
95°	36	43	45	45	43	42
105°	150	152	153	155	155	158
115°	279	283	282	281	279	276
125°	406	412	410	408	407	362
135°	525	532	534	533	531	405
145°	637	642	646	647	644	398
155°	728	730	732	736	734	335
165°	792	792	792	796	793	223
175°	825	822	821	825	822	78
180°	826	826	826	826	826	



TEST NUMBER: P331310-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	695.8	695.2	694.6	694.0	693.4	692.5	691.2	689.9	688.6	687.2	688.5
5°	692.6	692.0	691.4	690.8	690.3	689.1	687.5	685.9	684.2	682.6	683.8
7.5°	686.4	685.5	684.7	683.7	682.8	681.5	679.8	678.2	676.5	674.8	676.1
10°	680.6	679.6	678.5	677.5	676.5	675.0	673.2	671.5	669.8	668.0	669.1
12.5°	672.6	671.7	670.7	669.9	669.0	667.6	665.8	664.1	662.3	660.5	661.3
15°	659.3	658.4	657.5	656.7	655.8	654.3	652.4	650.5	648.5	646.7	647.2
17.5°	642.2	641.4	640.5	639.6	638.7	637.3	635.3	633.4	631.4	629.5	630.2
20°	630.0	629.1	628.2	627.3	626.4	625.0	622.9	620.8	618.8	616.7	617.2
22.5°	617.8	616.5	615.3	614.0	612.8	611.2	609.2	607.3	605.3	603.3	603.4
25°	596.7	595.5	594.3	593.2	592.0	590.1	587.6	585.1	582.6	580.1	580.3
27.5°	572.7	571.7	570.6	569.5	568.5	566.9	565.0	562.9	561.0	559.0	558.6
30°	556.8	555.5	554.4	553.2	552.0	550.3	548.0	545.9	543.7	541.4	541.0
32.5°	539.7	538.8	537.8	536.8	535.9	534.2	531.9	529.6	527.3	525.0	524.1
35°	514.8	513.3	511.8	510.3	508.9	506.9	504.6	502.2	499.8	497.5	496.6
37.5°	486.7	485.4	484.1	482.8	481.4	479.7	477.2	474.9	472.5	470.2	469.0
40°	467.5	466.3	465.1	464.0	462.8	461.0	458.6	456.3	453.9	451.6	450.2
42.5°	448.9	447.6	446.5	445.3	444.2	442.4	440.0	437.7	435.2	432.8	431.4
45°	418.9	417.9	416.8	415.8	414.7	413.1	410.9	408.7	406.4	404.2	402.6
47.5°	389.1	388.1	387.1	386.1	385.1	383.5	381.2	378.9	376.6	374.3	372.6
50°	368.3	367.6	366.8	366.0	365.3	363.9	361.9	359.8	357.7	355.6	353.6
52.5°	348.0	347.1	346.1	345.1	344.1	342.7	340.7	338.8	336.8	334.8	333.1
55°	317.0	316.1	315.2	314.3	313.4	312.1	310.3	308.5	306.7	305.0	303.3
57.5°	285.8	285.1	284.4	283.7	283.0	281.7	279.7	277.8	275.8	273.8	272.1
60°	265.0	264.5	263.9	263.2	262.7	261.4	259.3	257.2	255.1	253.1	251.5
62.5°	244.8	243.9	242.9	241.9	241.0	239.8	238.2	236.6	235.0	233.4	231.8
65°	213.7	212.9	212.0	211.1	210.3	209.0	207.6	206.1	204.6	203.1	201.8
67.5°	182.2	181.5	180.7	180.0	179.3	178.3	177.0	175.7	174.3	173.0	172.0
70°	162.5	161.9	161.3	160.7	160.2	159.2	157.8	156.5	155.2	153.8	152.8
72.5°	142.2	141.7	141.1	140.4	139.9	139.2	138.3	137.4	136.6	135.7	134.6
75°	111.9	111.6	111.3	111.0	110.7	110.2	109.4	108.7	108.0	107.2	106.3
77.5°	84.7	84.2	83.7	83.2	82.7	82.3	82.0	81.7	81.4	81.1	80.7
80°	66.6	66.4	66.3	66.2	66.0	65.8	65.5	65.2	64.9	64.6	64.1
82.5°	49.6	49.5	49.5	49.5	49.4	49.3	49.1	49.0	48.8	48.6	48.1
85°	27.3	27.2	27.0	26.8	26.8	26.6	26.4	26.3	26.1	25.9	25.5
87.5°	9.7	9.9	10.0	10.2	10.3	10.5	11.0	11.4	11.9	12.3	11.9
90°	0.7	2.6	4.5	6.2	8.1	10.8	14.2	17.6	21.0	24.4	24.1
92.5°	12.4	13.7	15.2	16.5	17.8	18.9	19.7	20.5	21.4	22.2	22.2
95°	36.2	37.8	39.3	40.9	42.4	43.3	43.7	44.0	44.3	44.6	44.6
97.5°	66.3	67.6	68.9	70.3	71.7	72.7	73.2	73.8	74.4	75.0	75.0
100°	88.5	89.8	91.0	92.2	93.5	94.3	94.8	95.2	95.7	96.2	96.2
102.5°	111.9	112.9	114.0	114.9	115.9	116.7	117.3	117.9	118.4	119.0	119.1
105°	149.9	150.3	150.8	151.2	151.7	152.1	152.4	152.8	153.0	153.4	153.6
107.5°	188.1	188.8	189.4	190.1	190.7	191.1	191.1	191.1	191.1	191.1	191.3
110°	212.6	213.5	214.5	215.3	216.3	216.8	216.8	216.8	216.8	216.8	216.8



TEST NUMBER: P331310-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	239.3	240.3	241.2	242.1	243.1	243.4	243.3	243.3	243.1	243.0	242.6
115°	278.8	279.7	280.6	281.6	282.5	282.9	282.5	282.2	281.9	281.6	281.4
117.5°	318.1	319.3	320.6	321.8	323.1	323.2	322.4	321.6	320.7	319.8	319.4
120°	344.3	345.5	346.8	348.0	349.3	349.3	348.0	346.8	345.5	344.3	344.3
122.5°	368.3	369.8	371.3	372.7	374.3	374.5	373.7	372.8	371.9	371.0	370.7
125°	405.6	407.1	408.4	409.8	411.3	411.7	411.3	410.7	410.3	409.8	409.4
127.5°	442.0	443.8	445.6	447.4	449.1	449.7	449.2	448.6	448.0	447.5	446.9
130°	464.9	466.9	469.0	470.9	473.0	473.8	473.5	473.1	472.9	472.6	472.3
132.5°	490.5	492.2	493.8	495.4	497.1	497.9	498.0	498.1	498.1	498.2	497.6
135°	524.9	526.6	528.2	529.9	531.6	532.6	533.0	533.2	533.6	533.9	533.8
137.5°	561.0	562.3	563.7	565.2	566.5	567.4	567.8	568.2	568.6	569.0	568.9
140°	582.7	584.1	585.5	586.8	588.3	589.3	590.1	590.9	591.7	592.5	592.5
142.5°	605.0	606.4	607.8	609.2	610.6	611.5	612.1	612.6	613.1	613.7	613.8
145°	637.0	638.1	639.3	640.3	641.4	642.4	643.4	644.3	645.2	646.1	646.3
147.5°	665.7	666.9	668.2	669.5	670.8	671.8	672.4	673.1	673.7	674.3	674.6
150°	685.2	686.1	687.0	688.0	688.8	689.6	690.3	690.9	691.5	692.1	692.6
152.5°	702.4	703.4	704.3	705.3	706.1	706.9	707.8	708.5	709.2	710.0	710.5
155°	728.3	728.8	729.3	729.8	730.2	730.7	731.1	731.6	732.1	732.5	733.3
157.5°	750.6	750.8	751.2	751.4	751.8	752.1	752.3	752.6	752.9	753.1	754.2
160°	763.9	764.2	764.6	764.8	765.2	765.4	765.5	765.7	765.9	766.0	767.0
162.5°	776.1	776.2	776.3	776.3	776.4	776.5	776.7	776.9	777.0	777.1	778.2
165°	792.5	792.4	792.2	792.0	791.8	791.8	791.8	791.8	791.8	791.8	792.9
167.5°	806.1	805.7	805.2	804.8	804.3	804.1	804.1	804.0	804.0	803.9	805.0
170°	813.4	813.0	812.4	812.0	811.5	811.2	811.1	810.9	810.7	810.6	811.7
172.5°	818.4	818.0	817.5	817.0	816.5	816.3	816.1	815.9	815.8	815.6	816.7
175°	824.6	824.1	823.6	823.1	822.7	822.3	822.0	821.7	821.4	821.1	822.2
177.5°	827.1	826.7	826.3	825.9	825.5	825.3	825.0	824.7	824.5	824.3	825.0
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331310-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	689.6	690.8	692.0	692.5	692.2	692.0	691.8	691.5
5°	685.0	686.2	687.3	687.8	687.5	687.2	686.9	686.6
7.5°	677.3	678.4	679.7	680.0	679.8	679.4	679.0	678.8
10°	670.3	671.5	672.7	673.1	672.6	672.2	671.7	671.3
12.5°	662.2	663.0	663.8	664.1	663.7	663.4	663.1	662.7
15°	647.8	648.5	649.0	648.9	648.2	647.5	646.8	646.0
17.5°	630.8	631.5	632.2	632.1	631.4	630.8	630.1	629.4
20°	617.6	618.0	618.5	618.4	617.8	617.2	616.6	616.0
22.5°	603.5	603.6	603.7	603.6	603.2	602.9	602.5	602.2
25°	580.7	580.9	581.2	581.2	580.9	580.7	580.3	580.1
27.5°	558.1	557.7	557.2	556.7	556.0	555.3	554.6	553.8
30°	540.6	540.1	539.7	539.1	538.5	538.0	537.3	536.7
32.5°	523.3	522.5	521.7	521.0	520.4	519.9	519.2	518.6
35°	495.7	494.8	493.9	493.1	492.4	491.6	490.9	490.2
37.5°	468.0	466.9	465.8	464.8	464.1	463.4	462.7	462.1
40°	448.9	447.5	446.2	445.2	444.6	444.1	443.4	442.8
42.5°	430.0	428.6	427.0	426.0	425.1	424.3	423.5	422.6
45°	401.0	399.4	397.7	396.6	396.0	395.5	394.8	394.2
47.5°	370.9	369.1	367.4	366.1	365.2	364.4	363.6	362.7
50°	351.5	349.4	347.3	345.9	345.2	344.5	343.7	343.0
52.5°	331.4	329.7	328.0	326.6	325.7	324.7	323.7	322.7
55°	301.5	299.7	297.9	296.7	295.9	295.2	294.4	293.7
57.5°	270.4	268.6	266.9	265.7	265.1	264.6	264.0	263.4
60°	249.8	248.2	246.6	245.5	245.0	244.6	244.2	243.7
62.5°	230.3	228.8	227.3	226.3	225.7	225.2	224.6	224.0
65°	200.5	199.1	197.8	196.7	196.0	195.3	194.6	193.8
67.5°	170.9	169.9	168.9	168.1	167.5	166.8	166.3	165.7
70°	151.8	150.7	149.7	148.9	148.3	147.7	147.1	146.5
72.5°	133.7	132.6	131.6	130.8	130.4	129.8	129.4	128.9
75°	105.4	104.6	103.7	103.3	103.7	104.0	104.2	104.6
77.5°	80.3	79.8	79.4	78.9	78.5	78.1	77.7	77.2
80°	63.7	63.2	62.9	62.4	62.2	61.9	61.5	61.3
82.5°	47.5	46.9	46.4	46.0	46.0	45.9	45.8	45.8
85°	25.1	24.6	24.2	23.9	23.7	23.6	23.5	23.3
87.5°	11.5	11.1	10.7	10.4	10.3	10.3	10.2	10.1
90°	23.8	23.5	23.2	23.1	23.3	23.4	23.5	23.7
92.5°	22.3	22.4	22.4	22.5	22.5	22.6	22.6	22.6
95°	44.6	44.6	44.6	44.5	44.1	43.9	43.5	43.2
97.5°	75.0	75.0	75.0	75.0	75.0	74.9	74.9	74.8
100°	96.2	96.2	96.2	96.1	95.9	95.8	95.7	95.5
102.5°	119.3	119.4	119.6	119.5	119.4	119.2	119.0	118.9
105°	154.0	154.3	154.6	154.7	154.7	154.7	154.7	154.7
107.5°	191.4	191.5	191.6	191.4	190.6	189.9	189.2	188.5
110°	216.8	216.8	216.8	216.5	216.1	215.6	215.2	214.6



TEST NUMBER: P331310-940

CATALOG NUMBER: SA2XXDIP-C485D725U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	242.2	241.8	241.5	241.1	240.8	240.4	240.1	239.8
115°	281.2	281.2	281.0	280.6	280.2	279.7	279.3	278.8
117.5°	319.1	318.7	318.3	317.9	317.4	316.9	316.5	316.0
120°	344.3	344.3	344.3	344.1	343.6	343.1	342.7	342.2
122.5°	370.3	370.0	369.6	369.3	368.9	368.5	368.2	367.9
125°	408.9	408.4	408.0	407.7	407.5	407.3	407.2	407.1
127.5°	446.4	445.8	445.2	444.7	444.3	443.7	443.3	442.7
130°	472.0	471.6	471.4	470.8	470.2	469.7	469.0	468.4
132.5°	496.9	496.1	495.5	494.9	494.4	493.9	493.4	492.9
135°	533.6	533.4	533.2	533.0	532.5	532.1	531.5	531.1
137.5°	568.8	568.6	568.6	568.2	567.6	566.9	566.3	565.7
140°	592.5	592.5	592.5	592.1	591.6	590.9	590.3	589.7
142.5°	613.9	614.0	614.1	613.9	613.2	612.6	612.1	611.4
145°	646.4	646.6	646.8	646.5	645.9	645.2	644.6	644.0
147.5°	674.9	675.3	675.6	675.6	674.9	674.3	673.8	673.2
150°	693.0	693.5	694.0	694.0	693.5	693.0	692.6	692.1
152.5°	711.1	711.8	712.3	712.3	711.8	711.1	710.5	710.0
155°	734.1	734.9	735.7	735.8	735.3	734.9	734.4	734.0
157.5°	755.3	756.3	757.4	757.5	756.8	756.1	755.3	754.6
160°	767.9	768.8	769.7	769.9	769.3	768.7	768.0	767.4
162.5°	779.3	780.3	781.4	781.5	780.8	780.1	779.3	778.6
165°	794.0	795.0	796.1	796.3	795.5	794.7	794.0	793.2
167.5°	806.1	807.2	808.2	808.4	807.6	806.8	806.0	805.2
170°	812.8	813.9	814.9	815.0	814.1	813.2	812.3	811.3
172.5°	817.8	818.9	819.9	820.0	819.1	818.1	817.3	816.4
175°	823.2	824.3	825.4	825.5	824.6	823.6	822.7	821.8
177.5°	825.7	826.5	827.2	827.2	826.5	825.7	825.0	824.3
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9

(END OF REPORT)