

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332705-930

Luminaire Tested: **SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332705-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7184.7 lumens  
Efficiency: N/A  
Efficacy: 107.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332705-930  
CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332705-930

CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58	58	58	49	49	49	41	41	41	35	35	35																
	1	100	95	91	88	93	89	85	82	77	74	72	66	64	63	56	55	54	49	49	49	41	41	41	35	35	35	30	30	30																
	2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	47	45	41	41	41	35	35	35	30	30	30	26	26	26																
	3	83	73	66	60	77	68	62	56	60	54	50	51	47	44	44	41	38	35	35	35	30	30	30	26	26	26	23	23	23																
	4	76	65	57	50	70	61	53	48	53	47	43	46	41	38	39	36	33	30	30	30	26	26	26	23	23	23	20	20	20																
	5	70	58	49	43	65	54	47	41	47	41	37	41	36	33	35	32	29	26	26	26	23	23	23	20	20	20	18	18	18																
	6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25	23	23	23	20	20	20	18	18	18	16	16	16																
	7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	25	23	20	20	20	18	18	18	16	16	16	15	15	15																
	8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20	18	18	18	16	16	16	15	15	15	14	14	14																
	9	51	39	31	26	48	37	30	25	32	27	23	29	24	21	25	21	18	16	16	16	15	15	15	14	14	14	13	13	13																
	10	48	36	28	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15	15	15	14	14	14	13	13	13	12	12	12																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13116	13116	13116
5°	13156	12998	13092
10°	13073	12892	12956
15°	12915	12709	12741
20°	12706	12482	12493
25°	12466	12222	12188
30°	12172	11918	11808
35°	11869	11599	11445
40°	11552	11236	11031
45°	11222	10880	10671
50°	10857	10562	10236
55°	10463	10151	9821
60°	10069	9689	9397
65°	9626	9251	8879
70°	9128	8665	8327
75°	8366	7960	7757
80°	7443	7141	6960
85°	6512	6271	6150



TEST NUMBER: P332705-930

CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.0	2.1
10°-20°	431.1	6.0
20°-30°	634.5	8.8
30°-40°	737.7	10.3
40°-50°	737.7	10.3
50°-60°	645.3	9.0
60°-70°	479.2	6.7
70°-80°	272.3	3.8
80°-90°	80.9	1.1
90°-100°	299.2	4.2
100°-110°	622.8	8.7
110°-120°	557.8	7.8
120°-130°	469.2	6.5
130°-140°	391.2	5.4
140°-150°	298.9	4.2
150°-160°	210.1	2.9
160°-170°	123.6	1.7
170°-180°	40.2	0.6
0°-30°	1218.6	17.0
0°-40°	1956.3	27.2
0°-60°	3339.3	46.5
0°-90°	4171.7	58.1
90°-120°	1479.8	20.6
90°-150°	2639.2	36.7
90°-180°	3013.0	41.9
0°-180°	7184.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1625	1625	1625	1625	1625	
5°	1623	1618	1604	1617	1616	154
15°	1545	1539	1521	1528	1524	435
25°	1400	1390	1372	1373	1368	644
35°	1204	1195	1177	1168	1161	753
45°	983	973	953	939	935	757
55°	743	739	721	706	698	666
65°	504	497	484	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	1	6	15	16	17	5
95°	27	85	663	328	199	30
105°	95	138	534	1150	1145	102
115°	168	210	476	915	1100	166
125°	234	278	474	778	877	208
135°	278	330	470	691	785	214
145°	320	366	467	583	641	201
155°	364	393	454	514	536	168
165°	396	409	436	461	468	112
175°	413	414	418	423	422	39
180°	414	414	414	414	414	



TEST NUMBER: P332705-930

CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1628.9	1628.2	1627.5	1626.8	1626.1	1624.5	1622.0	1619.4	1616.9	1614.4	1616.7
5°	1623.4	1622.3	1621.1	1620.0	1618.9	1616.7	1613.5	1610.3	1607.1	1603.9	1607.1
7.5°	1608.3	1607.2	1606.1	1604.8	1603.7	1601.4	1597.8	1594.3	1590.8	1587.2	1589.8
10°	1594.8	1593.7	1592.5	1591.3	1590.2	1587.7	1584.0	1580.2	1576.5	1572.7	1575.0
12.5°	1577.1	1576.0	1574.8	1573.6	1572.5	1569.9	1565.9	1562.0	1558.0	1554.0	1556.5
15°	1545.3	1544.2	1543.0	1541.9	1540.7	1538.0	1533.6	1529.3	1524.9	1520.6	1522.3
17.5°	1507.1	1505.6	1504.1	1502.8	1501.3	1498.5	1494.4	1490.3	1486.2	1482.1	1483.2
20°	1479.0	1477.5	1476.0	1474.6	1473.2	1470.2	1465.9	1461.6	1457.3	1452.9	1453.8
22.5°	1448.7	1446.8	1445.0	1443.0	1441.1	1437.9	1433.6	1429.3	1425.0	1420.6	1422.2
25°	1399.5	1397.5	1395.5	1393.4	1391.4	1388.4	1384.3	1380.3	1376.2	1372.1	1372.5
27.5°	1343.3	1341.2	1339.1	1337.0	1335.0	1332.0	1328.3	1324.5	1320.8	1317.0	1316.3
30°	1305.8	1303.5	1301.1	1298.9	1296.6	1293.5	1289.7	1286.0	1282.2	1278.5	1277.3
32.5°	1266.2	1264.1	1262.1	1260.0	1257.8	1254.8	1250.8	1246.8	1242.8	1238.8	1237.5
35°	1204.3	1202.2	1200.2	1198.2	1196.1	1193.1	1189.0	1185.0	1181.0	1176.9	1174.8
37.5°	1138.9	1137.0	1135.2	1133.3	1131.5	1128.4	1124.1	1119.7	1115.3	1111.0	1108.8
40°	1096.2	1093.9	1091.5	1089.2	1087.0	1083.6	1079.3	1074.9	1070.6	1066.2	1063.3
42.5°	1050.4	1049.0	1047.6	1046.2	1044.8	1041.7	1036.9	1032.1	1027.3	1022.5	1019.1
45°	982.9	980.9	978.8	976.8	974.9	971.5	966.9	962.2	957.6	953.0	949.8
47.5°	912.3	910.9	909.5	908.2	906.8	904.0	899.7	895.4	891.1	886.9	883.3
50°	864.5	863.3	862.1	861.0	859.8	857.2	853.1	849.1	845.1	841.0	837.0
52.5°	817.6	816.2	814.8	813.4	812.0	809.2	804.9	800.6	796.4	792.1	788.5
55°	743.4	742.5	741.7	740.8	739.9	737.4	733.4	729.4	725.3	721.2	717.8
57.5°	672.5	671.6	670.6	669.6	668.6	666.1	662.1	658.1	654.1	650.1	646.9
60°	623.6	622.2	620.7	619.3	617.8	615.2	611.5	607.7	603.9	600.1	597.5
62.5°	575.7	574.5	573.2	572.0	570.9	568.3	564.3	560.3	556.3	552.3	549.9
65°	503.9	502.4	500.9	499.5	498.1	495.9	493.0	490.1	487.2	484.3	481.4
67.5°	431.5	430.2	428.8	427.5	426.2	424.0	421.3	418.5	415.7	412.9	410.2
70°	386.7	384.7	382.6	380.6	378.5	376.4	374.1	371.8	369.4	367.1	364.8
72.5°	338.8	336.7	334.7	332.6	330.7	328.7	326.9	325.0	323.2	321.3	319.4
75°	268.2	266.8	265.3	263.8	262.4	261.0	259.5	258.0	256.7	255.2	254.0
77.5°	200.7	200.1	199.5	198.9	198.2	197.2	196.0	194.7	193.5	192.2	191.8
80°	160.1	159.2	158.4	157.5	156.7	156.0	155.4	154.7	154.2	153.6	153.0
82.5°	120.6	120.2	119.8	119.4	119.0	118.7	118.5	118.5	118.3	118.2	117.9
85°	70.3	70.3	70.3	70.3	70.3	70.0	69.5	68.9	68.2	67.7	67.7
87.5°	27.2	27.3	27.6	27.6	27.5	27.2	28.0	27.7	27.8	28.0	27.8
90°	0.8	2.4	4.9	5.7	6.5	6.5	11.4	11.4	13.0	14.7	13.9
92.5°	9.3	13.5	21.2	31.1	43.0	59.9	101.3	164.4	225.9	258.2	215.1
95°	26.8	29.3	37.4	48.0	67.6	101.7	172.5	306.1	500.6	663.3	682.1
97.5°	48.2	48.2	55.2	65.0	81.7	110.4	164.9	275.1	468.5	698.6	856.9
100°	61.9	61.9	67.6	77.3	92.8	118.9	166.9	258.9	424.9	654.4	862.7
102.5°	74.8	76.1	81.2	90.3	105.2	129.9	173.3	254.3	395.6	599.1	813.9
105°	95.2	97.7	101.7	111.5	126.1	149.8	188.8	256.4	370.3	533.9	725.2
107.5°	117.7	119.4	123.4	133.8	147.8	171.0	206.9	268.4	365.7	497.5	653.5
110°	132.6	134.3	138.4	148.1	162.8	184.7	220.5	277.5	367.0	485.1	617.8



TEST NUMBER: P332705-930

CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.0	148.6	153.4	162.5	177.1	199.1	233.6	287.3	371.0	479.2	597.6
115°	167.7	170.1	175.8	183.9	199.4	221.4	254.0	302.8	378.5	476.1	578.7
117.5°	189.1	191.4	196.5	205.5	219.9	242.7	273.6	318.5	386.5	475.3	570.2
120°	203.5	205.1	210.8	219.7	233.6	256.4	287.3	329.6	392.3	475.3	565.7
122.5°	216.5	218.1	223.8	232.1	247.3	269.4	300.4	340.1	398.2	474.7	560.4
125°	233.6	236.8	241.7	250.7	266.1	288.9	318.2	355.7	407.0	473.7	551.9
127.5°	248.7	251.4	257.2	267.4	283.6	306.6	334.8	369.2	413.9	471.9	540.3
130°	257.2	260.5	266.9	279.2	294.6	318.2	345.9	377.6	419.1	471.2	533.1
132.5°	265.6	268.2	276.7	288.3	305.1	327.3	355.1	386.1	423.7	470.6	526.6
135°	277.5	280.8	288.9	302.8	319.8	341.0	367.9	397.2	430.6	469.6	516.8
137.5°	289.4	292.5	301.5	314.6	332.4	352.6	377.6	405.0	434.6	469.4	508.3
140°	297.9	300.4	309.3	323.1	340.2	359.8	384.2	410.2	437.9	468.8	503.9
142.5°	307.0	309.5	317.7	330.9	347.4	366.2	390.0	414.1	440.5	468.8	499.9
145°	319.8	322.3	330.4	341.9	357.3	375.2	396.4	418.3	442.0	467.2	493.3
147.5°	334.4	335.2	342.3	354.1	366.9	383.0	402.9	422.1	442.8	464.2	487.2
150°	343.5	344.3	350.8	360.6	372.8	388.2	406.2	424.0	442.8	462.3	482.7
152.5°	352.0	352.1	358.7	367.7	378.6	392.8	408.8	425.3	441.5	459.0	477.4
155°	363.8	364.6	369.5	377.6	386.6	398.8	412.6	426.5	439.5	454.2	469.6
157.5°	375.4	375.4	379.9	386.3	394.1	403.7	415.4	426.5	437.4	449.1	461.6
160°	382.5	382.5	385.8	391.5	398.0	407.0	416.7	426.5	435.5	445.2	455.8
162.5°	389.1	388.4	391.0	396.1	401.9	409.0	418.0	426.5	433.5	441.3	450.6
165°	396.4	396.4	398.0	402.1	406.2	411.0	418.3	424.9	429.7	435.5	442.0
167.5°	403.7	402.9	403.7	406.8	409.1	412.8	418.2	422.9	425.8	429.6	434.1
170°	407.0	406.2	407.0	409.4	411.0	413.4	417.5	421.6	423.2	425.7	428.9
172.5°	410.2	409.4	409.5	411.3	412.3	414.1	416.9	420.3	420.6	421.8	424.4
175°	413.4	412.6	412.6	413.4	414.3	414.3	415.9	418.3	417.5	417.5	419.1
177.5°	414.9	414.3	413.6	414.3	414.3	414.3	414.9	416.2	414.9	414.9	415.6
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332705-930

CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1618.9	1621.3	1623.6	1624.6	1624.4	1624.2	1623.9	1623.7
5°	1610.3	1613.5	1616.7	1618.0	1617.4	1616.8	1616.2	1615.6
7.5°	1592.4	1594.9	1597.4	1598.6	1598.2	1597.8	1597.5	1597.2
10°	1577.3	1579.6	1581.9	1582.8	1582.3	1581.7	1581.0	1580.5
12.5°	1559.0	1561.5	1564.2	1565.0	1564.2	1563.3	1562.5	1561.7
15°	1524.0	1525.8	1527.5	1528.0	1527.1	1526.2	1525.3	1524.5
17.5°	1484.3	1485.4	1486.5	1486.7	1486.1	1485.6	1485.0	1484.4
20°	1454.7	1455.5	1456.4	1456.5	1456.0	1455.4	1454.8	1454.2
22.5°	1423.8	1425.3	1426.9	1427.1	1426.1	1425.1	1424.0	1422.9
25°	1372.8	1373.0	1373.4	1372.9	1371.7	1370.6	1369.5	1368.3
27.5°	1315.6	1314.9	1314.2	1313.1	1311.7	1310.3	1308.8	1307.3
30°	1276.1	1275.0	1273.8	1272.5	1271.1	1269.7	1268.2	1266.7
32.5°	1236.1	1234.7	1233.3	1231.9	1230.4	1229.0	1227.6	1226.1
35°	1172.9	1170.9	1168.8	1167.1	1165.6	1164.2	1162.7	1161.3
37.5°	1106.6	1104.4	1102.2	1100.2	1098.3	1096.3	1094.5	1092.5
40°	1060.5	1057.5	1054.7	1052.5	1051.1	1049.6	1048.1	1046.7
42.5°	1015.8	1012.4	1009.1	1006.9	1005.9	1004.9	1004.0	1003.0
45°	946.6	943.5	940.3	938.2	937.3	936.5	935.6	934.7
47.5°	879.7	876.1	872.5	869.6	867.4	865.2	863.0	860.8
50°	832.9	828.8	824.8	821.9	820.2	818.5	816.7	815.0
52.5°	784.9	781.3	777.7	774.9	772.7	770.5	768.3	766.1
55°	714.3	710.9	707.4	704.7	703.0	701.3	699.5	697.8
57.5°	643.6	640.3	637.0	634.5	632.8	631.1	629.4	627.8
60°	594.9	592.4	589.8	587.7	586.3	584.8	583.4	582.0
62.5°	547.5	545.1	542.7	540.9	539.4	537.9	536.5	535.1
65°	478.5	475.6	472.7	470.6	469.1	467.7	466.2	464.8
67.5°	407.4	404.6	401.9	400.2	399.8	399.4	399.0	398.6
70°	362.5	360.2	357.8	356.3	355.4	354.6	353.7	352.8
72.5°	317.6	315.8	313.9	312.5	311.7	310.8	309.9	309.1
75°	252.8	251.7	250.5	249.8	249.6	249.2	248.9	248.7
77.5°	191.4	191.1	190.8	190.2	189.5	188.7	187.9	187.2
80°	152.5	151.9	151.3	150.9	150.6	150.3	150.0	149.7
82.5°	117.5	117.2	116.8	116.5	116.2	115.9	115.6	115.4
85°	67.7	67.7	67.7	67.6	67.3	66.9	66.7	66.4
87.5°	28.0	28.1	28.3	28.3	28.5	28.6	28.5	28.5
90°	14.7	15.5	16.3	16.3	17.1	17.9	17.1	17.1
92.5°	159.9	120.3	95.7	79.4	69.9	65.5	62.7	62.7
95°	603.1	477.0	367.9	288.9	249.1	223.8	209.2	198.6
97.5°	891.1	844.2	764.6	679.6	621.2	572.2	547.8	530.8
100°	981.6	997.8	958.0	897.7	827.0	777.3	752.8	746.4
102.5°	977.1	1057.8	1069.3	1044.2	1000.8	964.8	939.1	933.9
105°	911.6	1052.4	1132.9	1166.4	1168.0	1161.5	1150.1	1145.2
107.5°	818.6	968.6	1082.1	1154.6	1194.8	1213.4	1221.6	1223.7
110°	762.6	903.4	1021.5	1111.0	1168.8	1203.0	1217.6	1225.0





TEST NUMBER: P332705-930

CATALOG NUMBER: SA4XXDIP-C1195D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	721.6	846.1	957.7	1047.2	1112.8	1154.1	1174.7	1186.5
115°	680.4	780.6	875.8	953.9	1018.2	1067.1	1093.1	1099.6
117.5°	660.2	743.1	818.0	884.3	939.1	980.2	1006.5	1011.5
120°	651.1	726.8	792.0	849.7	896.1	932.0	953.1	962.1
122.5°	643.4	716.4	775.7	826.3	865.5	896.1	914.0	923.0
125°	630.0	699.9	756.1	800.9	833.5	857.0	872.5	877.4
127.5°	613.7	680.6	736.6	779.1	811.8	832.8	845.8	850.7
130°	600.7	665.0	720.3	763.4	796.8	817.2	830.2	835.1
132.5°	587.0	647.4	701.4	744.6	777.3	800.2	812.6	817.5
135°	568.1	621.0	670.7	711.3	744.0	766.7	779.8	784.6
137.5°	551.1	595.8	637.6	674.4	704.8	727.3	738.1	744.0
140°	541.3	579.5	616.1	650.3	678.8	696.8	708.1	714.6
142.5°	532.1	565.8	597.3	626.9	652.1	668.7	678.8	683.4
145°	519.3	547.0	571.4	594.2	614.5	628.4	636.5	640.6
147.5°	508.7	530.7	550.2	568.1	583.1	595.0	601.2	602.6
150°	502.2	520.9	537.2	551.9	564.8	575.4	580.3	581.1
152.5°	495.0	511.1	526.1	538.2	549.3	557.8	560.8	561.6
155°	484.3	497.3	509.5	519.3	527.4	533.9	536.4	536.4
157.5°	472.7	483.6	493.9	501.7	507.8	512.7	514.2	514.2
160°	465.5	474.5	483.5	490.0	494.9	499.8	500.6	500.6
162.5°	458.4	466.0	473.0	478.9	482.5	487.4	488.2	487.5
165°	448.5	453.4	459.0	463.1	466.4	469.6	468.8	468.0
167.5°	438.9	442.6	447.2	449.6	451.3	453.4	453.2	452.6
170°	433.0	435.5	438.7	441.2	442.8	443.6	442.8	442.8
172.5°	427.8	429.6	431.5	433.3	434.3	435.1	434.3	433.0
175°	420.8	421.6	423.2	423.2	423.2	424.9	423.2	421.6
177.5°	416.2	416.9	416.9	417.5	416.9	417.5	416.2	414.9
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3

(END OF REPORT)