

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331317-940

Luminaire Tested: **SA2XXDIP-C485D925U940-4F0-1E-UDD-D4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331317-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D925U940-4F0-1E-UDD-D4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4977.5 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331317-940

CATALOG NUMBER: SA2XXDIP-C485D925U940-4F0-1E-UDD-D4

Luminous Intensity Polar Plot





TEST NUMBER: P331317-940

CATALOG NUMBER: SA2XXDIP-C485D925U940-4F0-1E-UDD-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31	31	31	20	
1	93	88	84	80	83	79	76	72	62	60	58	47	45	44	33	32	31	24	24	24	24	
2	84	76	70	65	75	69	63	59	54	50	47	41	38	36	28	27	25	20	20	20	20	
3	76	67	59	53	68	60	54	48	47	43	39	36	33	30	25	23	21	16	16	16	16	
4	70	59	51	45	62	53	46	41	42	37	33	32	28	25	22	20	18	14	14	14	14	
5	64	52	44	38	57	47	40	35	37	32	28	28	25	22	20	17	15	12	12	12	12	
6	58	46	38	33	52	42	35	30	33	28	24	25	22	19	18	15	13	10	10	10	10	
7	54	42	34	28	48	38	31	26	30	25	21	23	19	16	16	14	12	9	9	9	9	
8	50	38	30	25	45	34	27	23	27	22	19	21	17	15	15	12	11	8	8	8	8	
9	46	34	27	22	42	31	25	20	25	20	16	19	16	13	14	11	9	7	7	7	7	
10	43	31	24	19	39	28	22	18	23	18	15	18	14	12	13	10	9	6	6	6	6	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7419	7419	7419
5°	7455	7143	7115
10°	7408	6931	6854
15°	7306	6708	6577
20°	7177	6468	6312
25°	7050	6237	6072
30°	6870	5999	5829
35°	6689	5771	5659
40°	6498	5576	5488
45°	6317	5402	5343
50°	6123	5242	5199
55°	5916	5073	5052
60°	5666	4897	4897
65°	5405	4692	4714
70°	5117	4470	4516
75°	4741	4251	4334
80°	4149	4028	4148
85°	3591	3837	4006



TEST NUMBER: P331317-940

CATALOG NUMBER: SA2XXDIP-C485D925U940-4F0-1E-UDD-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.5	0.9
10°-20°	124.9	2.5
20°-30°	189.2	3.8
30°-40°	230.5	4.6
40°-50°	247.9	5.0
50°-60°	240.8	4.8
60°-70°	210.2	4.2
70°-80°	161.8	3.3
80°-90°	112.8	2.3
90°-100°	259.9	5.2
100°-110°	682.6	13.7
110°-120°	703.2	14.1
120°-130°	569.3	11.4
130°-140°	449.4	9.0
140°-150°	334.7	6.7
150°-160°	234.2	4.7
160°-170°	137.9	2.8
170°-180°	44.9	0.9
0°-30°	357.6	7.2
0°-40°	588.1	11.8
0°-60°	1076.8	21.6
0°-90°	1561.6	31.4
90°-120°	1645.6	33.1
90°-150°	2999.0	60.3
90°-180°	3416.0	68.6
0°-180°	4977.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	460	460	460	460	460	
5°	461	459	455	459	458	44
15°	440	441	441	446	446	124
25°	400	404	410	418	420	184
35°	344	356	368	382	388	215
45°	282	301	324	344	351	218
55°	216	241	275	298	308	193
65°	148	181	220	246	256	147
75°	82	119	162	189	199	87
85°	24	65	108	135	145	26
90°	8	58	118	142	152	6
95°	36	114	425	233	211	37
105°	112	187	717	1258	1091	119
115°	194	253	592	1198	1387	192
125°	268	318	553	962	1117	238
135°	314	375	532	796	914	243
145°	358	411	522	651	716	225
155°	407	439	506	573	595	187
165°	443	457	485	514	522	125
175°	462	462	466	472	471	44
180°	463	463	463	463	463	



TEST NUMBER: P331317-940

CATALOG NUMBER: SA2XXDIP-C485D925U940-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5
2.5°	462.2	461.8	461.5	461.1	460.7	460.1	459.3	458.5	457.7	456.8	457.4
5°	460.8	460.4	459.9	459.5	459.1	458.4	457.5	456.6	455.8	454.9	455.8
7.5°	456.7	456.4	456.1	455.8	455.6	455.0	454.3	453.7	453.0	452.3	453.3
10°	453.5	453.3	452.9	452.6	452.4	452.0	451.6	451.1	450.7	450.2	451.4
12.5°	448.2	448.3	448.4	448.4	448.4	448.3	448.0	447.6	447.3	447.0	448.2
15°	439.5	439.8	440.1	440.4	440.7	440.9	440.9	440.9	440.9	440.9	442.2
17.5°	428.4	429.0	429.6	430.3	430.9	431.4	431.9	432.3	432.8	433.3	434.6
20°	420.9	421.6	422.4	423.1	423.8	424.5	425.1	425.7	426.3	426.9	428.5
22.5°	412.9	413.8	414.6	415.4	416.3	417.1	418.0	418.8	419.6	420.5	422.1
25°	399.6	400.6	401.6	402.7	403.7	404.9	406.3	407.6	408.9	410.2	412.0
27.5°	383.6	385.3	387.0	388.7	390.3	392.0	393.5	395.1	396.6	398.2	400.5
30°	372.9	374.9	376.7	378.7	380.7	382.5	384.5	386.4	388.3	390.2	392.6
32.5°	361.2	363.4	365.5	367.7	369.9	372.1	374.3	376.7	378.9	381.2	383.9
35°	344.3	346.8	349.4	351.9	354.4	357.0	359.8	362.7	365.4	368.3	371.5
37.5°	325.9	328.9	331.7	334.7	337.5	340.8	344.5	348.0	351.7	355.3	359.0
40°	313.7	316.9	320.2	323.4	326.7	330.3	334.3	338.3	342.3	346.3	350.2
42.5°	301.9	305.2	308.4	311.7	315.0	318.9	323.5	328.1	332.7	337.2	341.4
45°	282.4	286.3	290.3	294.4	298.4	302.9	308.1	313.3	318.5	323.7	328.2
47.5°	263.1	267.4	271.8	276.1	280.4	285.7	291.8	297.8	303.9	310.0	314.8
50°	249.8	254.3	259.0	263.5	268.0	273.7	280.4	287.0	293.7	300.3	305.4
52.5°	236.9	241.7	246.6	251.5	256.3	262.2	269.2	276.2	283.2	290.3	295.3
55°	216.4	221.8	227.1	232.4	237.7	244.2	252.0	259.7	267.3	275.0	280.4
57.5°	196.2	202.2	208.2	214.2	220.3	227.1	235.0	242.8	250.7	258.5	264.3
60°	181.8	188.2	194.6	200.9	207.2	214.6	223.1	231.5	240.0	248.4	254.0
62.5°	169.0	175.6	182.3	188.9	195.5	203.0	211.3	219.8	228.3	236.7	242.6
65°	147.8	155.1	162.4	169.6	176.8	184.9	193.6	202.3	211.1	219.8	225.9
67.5°	128.4	136.0	143.6	151.1	158.7	166.9	175.9	184.9	193.8	202.7	208.8
70°	114.6	122.3	129.9	137.6	145.3	153.7	162.9	172.1	181.3	190.5	196.8
72.5°	101.7	109.7	117.6	125.6	133.5	142.1	151.4	160.7	170.0	179.2	185.6
75°	81.9	90.2	98.4	106.7	115.0	123.9	133.4	142.9	152.4	161.8	168.2
77.5°	62.8	71.4	80.1	88.7	97.5	106.6	116.2	125.8	135.5	145.1	151.4
80°	49.9	58.9	68.0	77.0	86.1	95.4	105.0	114.6	124.2	133.8	140.1
82.5°	39.3	48.2	57.1	66.0	74.9	84.3	94.0	103.7	113.4	123.2	129.4
85°	24.0	33.2	42.4	51.5	60.6	70.0	79.5	88.9	98.4	107.9	114.1
87.5°	13.2	22.6	32.1	41.3	50.5	60.2	70.5	81.2	91.8	101.4	107.3
90°	7.6	18.8	30.9	41.3	51.6	63.4	77.3	93.0	107.8	118.2	123.2
92.5°	16.9	29.8	44.1	56.1	70.1	87.0	116.3	153.7	188.1	198.8	186.6
95°	36.5	47.0	62.9	77.8	99.0	128.3	178.1	264.4	376.5	425.4	387.4
97.5°	55.4	66.3	82.0	100.3	122.9	154.4	214.4	330.7	510.9	666.4	701.1
100°	73.2	81.3	94.8	114.5	137.8	169.6	225.1	341.9	542.4	769.6	903.3
102.5°	89.0	95.9	109.0	128.2	151.8	183.2	234.9	339.4	525.4	769.5	976.3
105°	111.9	119.8	130.3	147.9	171.8	202.7	252.3	339.1	493.7	716.8	958.7
107.5°	137.4	143.7	153.2	168.9	191.7	222.2	270.2	346.6	475.4	660.8	874.9
110°	154.0	160.5	168.8	183.3	204.9	235.9	282.3	353.6	469.4	633.3	822.2



TEST NUMBER: P331317-940

CATALOG NUMBER: SA2XXDIP-C485D925U940-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.6	175.7	184.2	197.5	218.0	249.2	293.8	361.2	466.8	613.9	784.3
115°	194.0	200.1	207.1	219.4	238.8	267.0	311.9	372.8	465.8	591.7	736.8
117.5°	218.6	223.2	229.6	240.1	258.3	286.9	328.4	385.5	467.3	577.9	704.5
120°	234.3	238.4	244.3	253.0	271.3	299.5	340.2	394.1	468.6	569.7	686.9
122.5°	249.2	252.4	257.9	266.9	284.9	313.4	351.5	401.6	470.7	563.7	671.5
125°	268.3	271.0	276.3	287.0	304.8	332.1	368.9	413.7	473.6	553.0	648.7
127.5°	284.0	287.4	294.7	306.3	323.2	350.7	385.7	425.4	477.3	545.2	627.6
130°	293.2	296.7	305.4	317.7	335.4	361.8	396.0	432.9	480.5	540.6	613.6
132.5°	301.8	305.9	315.4	328.4	346.8	372.8	404.9	440.4	483.8	536.7	601.7
135°	314.0	317.4	328.1	341.5	361.9	387.6	417.6	450.2	487.3	531.5	585.3
137.5°	326.0	330.3	340.9	355.2	375.4	398.9	427.6	457.3	490.4	527.4	572.7
140°	335.3	338.7	349.2	363.3	382.7	406.0	432.9	460.8	491.4	524.6	565.3
142.5°	344.6	347.2	357.0	371.1	389.9	411.5	437.6	464.5	492.7	523.5	558.7
145°	357.8	361.3	370.2	383.6	401.4	421.0	445.0	469.9	494.8	521.5	550.9
147.5°	372.7	375.4	383.9	396.2	411.0	428.5	451.0	473.0	495.5	518.4	543.3
150°	382.7	385.3	392.4	404.0	417.4	433.4	453.9	474.3	494.8	516.2	537.5
152.5°	392.6	393.9	401.0	411.2	423.8	438.4	456.7	475.0	493.4	512.6	532.5
155°	406.7	407.6	413.0	422.8	432.5	445.9	461.0	476.1	491.2	506.4	523.3
157.5°	418.5	419.4	423.7	432.1	440.0	451.2	464.0	476.1	487.1	500.0	514.6
160°	426.3	427.2	430.7	437.8	445.0	454.8	465.5	476.1	485.0	495.7	508.2
162.5°	434.1	433.5	437.1	442.8	449.2	456.9	466.2	475.4	482.9	492.1	502.5
165°	443.2	442.3	444.1	449.4	453.9	459.2	467.3	473.5	478.8	485.0	493.0
167.5°	450.7	449.6	451.2	454.6	457.8	461.2	467.1	472.3	474.7	478.8	483.8
170°	455.7	453.9	454.8	457.4	459.2	461.9	466.4	470.8	472.6	475.2	478.8
172.5°	458.5	457.4	456.9	459.6	460.7	462.6	465.7	468.7	469.8	471.0	473.9
175°	461.9	461.0	460.1	461.9	461.9	462.8	464.6	466.4	465.5	466.4	467.3
177.5°	463.5	462.1	461.4	462.8	462.8	462.8	463.5	464.9	463.5	462.8	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331317-940

CATALOG NUMBER: SA2XXDIP-C485D925U940-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5
2.5°	458.1	458.6	459.2	459.4	459.1	459.0	458.7	458.4
5°	456.6	457.5	458.4	458.8	458.6	458.5	458.3	458.2
7.5°	454.4	455.5	456.6	457.0	456.9	456.7	456.6	456.5
10°	452.5	453.7	455.0	455.5	455.3	455.1	455.0	454.9
12.5°	449.3	450.6	451.7	452.3	452.1	451.9	451.8	451.7
15°	443.5	444.9	446.2	446.7	446.7	446.5	446.3	446.2
17.5°	436.0	437.5	438.8	439.5	439.5	439.5	439.5	439.5
20°	430.2	431.8	433.4	434.2	434.2	434.2	434.2	434.2
22.5°	423.7	425.3	427.0	427.9	428.2	428.4	428.6	428.9
25°	413.8	415.5	417.3	418.5	418.9	419.4	419.8	420.3
27.5°	402.8	405.0	407.2	408.5	408.8	409.2	409.5	409.8
30°	395.0	397.3	399.8	401.1	401.5	402.0	402.4	402.9
32.5°	386.6	389.3	392.1	393.9	394.7	395.5	396.3	397.1
35°	374.8	378.1	381.3	383.4	384.5	385.5	386.6	387.6
37.5°	362.6	366.2	369.8	372.1	373.3	374.3	375.4	376.6
40°	354.0	357.8	361.7	364.3	365.6	366.9	368.3	369.6
42.5°	345.6	349.8	354.0	356.9	358.1	359.4	360.8	362.1
45°	332.9	337.4	342.0	345.0	346.5	348.0	349.5	351.0
47.5°	319.5	324.3	329.1	332.3	333.9	335.6	337.2	338.9
50°	310.4	315.4	320.5	323.8	325.5	327.1	328.7	330.3
52.5°	300.5	305.7	310.9	314.2	316.0	317.8	319.5	321.3
55°	285.7	291.1	296.3	300.0	301.9	303.8	305.8	307.6
57.5°	270.0	275.7	281.5	285.3	287.3	289.3	291.2	293.2
60°	259.7	265.3	270.9	274.7	276.8	278.9	281.0	283.0
62.5°	248.6	254.6	260.6	264.6	266.5	268.5	270.5	272.4
65°	231.9	238.0	244.1	248.1	249.9	251.9	253.8	255.7
67.5°	215.0	221.1	227.2	231.3	233.3	235.3	237.4	239.3
70°	203.2	209.6	215.9	220.0	221.8	223.6	225.3	227.1
72.5°	191.8	198.0	204.3	208.5	210.5	212.7	214.8	217.0
75°	174.6	180.9	187.3	191.5	193.3	195.3	197.2	199.1
77.5°	157.7	164.1	170.4	174.6	176.6	178.7	180.8	182.9
80°	146.3	152.5	158.7	162.8	165.0	167.0	169.1	171.1
82.5°	135.6	141.9	148.0	152.1	154.1	156.0	158.0	160.0
85°	120.3	126.5	132.8	136.9	138.9	141.1	143.1	145.2
87.5°	113.2	118.8	125.2	129.4	131.3	133.1	135.0	137.0
90°	128.2	132.3	140.1	144.8	146.6	148.4	150.2	151.9
92.5°	172.3	167.1	165.4	163.7	164.8	163.6	166.1	166.5
95°	321.0	272.3	240.6	224.7	214.9	209.6	208.7	211.3
97.5°	625.9	532.4	441.7	380.9	340.2	320.0	308.8	303.1
100°	890.1	785.2	668.8	564.6	492.4	455.8	431.6	417.1
102.5°	1061.9	1042.4	958.6	848.0	769.4	705.6	675.0	655.0
105°	1148.9	1254.6	1271.4	1245.5	1191.9	1138.4	1101.7	1090.9
107.5°	1076.1	1232.5	1330.1	1376.4	1385.0	1383.7	1377.6	1362.7
110°	1014.8	1178.8	1297.4	1373.6	1413.5	1432.1	1441.7	1442.4



TEST NUMBER: P331317-940

CATALOG NUMBER: SA2XXDIP-C485D925U940-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	958.4	1116.0	1242.5	1329.4	1384.2	1414.1	1430.8	1437.3
115°	888.1	1029.6	1150.6	1245.3	1310.1	1352.6	1377.4	1387.1
117.5°	833.7	958.4	1068.5	1157.4	1223.3	1268.1	1294.1	1302.3
120°	805.8	920.3	1018.8	1102.7	1166.6	1210.1	1237.5	1248.0
122.5°	783.2	888.3	981.7	1057.6	1114.8	1157.4	1181.7	1190.5
125°	749.8	845.3	927.6	997.1	1050.1	1085.2	1108.8	1117.2
127.5°	716.7	803.3	880.8	944.9	991.2	1024.2	1044.7	1051.8
130°	695.4	775.5	849.4	910.5	955.3	986.8	1005.7	1014.1
132.5°	674.9	749.2	817.3	874.8	918.8	950.3	967.8	975.4
135°	646.3	708.1	770.0	822.0	861.4	892.0	909.2	913.9
137.5°	622.6	674.5	723.8	769.1	805.0	831.3	846.3	852.7
140°	607.7	652.7	696.1	736.8	766.2	790.2	804.5	810.7
142.5°	595.7	633.9	671.0	705.1	733.0	754.7	767.4	769.3
145°	579.3	609.6	638.1	664.7	686.8	702.7	712.3	715.7
147.5°	566.9	590.2	611.9	631.0	649.0	661.4	667.8	669.8
150°	558.9	578.5	597.2	613.1	626.5	637.2	642.6	643.5
152.5°	551.1	569.2	585.1	599.0	609.4	618.7	622.6	622.8
155°	540.2	554.5	567.8	577.6	587.4	593.6	597.2	595.4
157.5°	527.5	539.5	550.7	558.4	565.3	570.4	572.0	572.0
160°	519.7	529.5	539.3	545.5	551.8	556.2	557.1	557.1
162.5°	511.9	520.2	528.6	533.4	539.7	542.7	543.6	542.9
165°	500.2	506.4	512.6	516.2	519.7	523.3	523.3	522.4
167.5°	488.9	493.7	498.0	501.2	502.8	504.8	504.6	503.5
170°	483.2	485.9	489.5	491.2	492.1	494.8	493.9	492.1
172.5°	476.8	478.8	481.6	482.7	483.6	484.8	483.9	482.9
175°	469.9	470.8	471.7	472.6	472.6	473.5	472.6	470.8
177.5°	464.9	464.9	465.7	465.7	465.7	465.7	464.9	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8

(END OF REPORT)