

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331367-940

Luminaire Tested: **SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331367-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6050.1 lumens  
Efficiency: N/A  
Efficacy: 106.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331367-940  
CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331367-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	81	75	70	65	62	58	55	51	48	46	40	38	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	27	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	23	20	18	15
9	50	39	31	26	46	36	29	25	30	25	22	26	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	19125	19125	19125	19125
5°	21441	19248	17057	19248
10°	24568	19090	14762	19090
15°	27178	18740	13041	18740
20°	26764	18364	11888	18364
25°	24134	17865	11158	17865
30°	19943	17066	10625	17066
35°	14534	16232	10247	16232
40°	11609	15247	10037	15247
45°	10145	14104	9750	14104
50°	9535	12999	9560	12999
55°	8791	11879	9303	11879
60°	8054	10685	8909	10685
65°	7339	9616	8520	9616
70°	6661	8573	7950	8573
75°	5908	7411	7043	7411
80°	5086	6137	5672	6137
85°	4557	4557	3372	4557



TEST NUMBER: P331367-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.8	1.9
10°-20°	327.9	5.4
20°-30°	475.9	7.9
30°-40°	502.2	8.3
40°-50°	444.7	7.3
50°-60°	354.9	5.9
60°-70°	241.2	4.0
70°-80°	123.7	2.0
80°-90°	34.7	0.6
90°-100°	77.8	1.3
100°-110°	241.6	4.0
110°-120°	412.9	6.8
120°-130°	543.0	9.0
130°-140°	609.4	10.1
140°-150°	597.6	9.9
150°-160°	501.2	8.3
160°-170°	332.4	5.5
170°-180°	116.2	1.9
0°-30°	916.7	15.2
0°-40°	1418.9	23.5
0°-60°	2218.4	36.7
0°-90°	2618.0	43.3
90°-120°	732.3	12.1
90°-150°	2482.3	41.0
90°-180°	3432.0	56.7
0°-180°	6050.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1184	1184	1184	1184	1184	
5°	1323	1188	1052	1188	1323	132
15°	1626	1121	780	1121	1626	449
25°	1355	1003	626	1003	1355	612
35°	737	824	520	824	737	480
45°	444	618	427	618	444	349
55°	312	422	330	422	312	280
65°	192	252	223	252	192	191
75°	95	119	113	119	95	101
85°	25	25	18	25	25	28
90°	35	1	35	1	35	16
95°	64	54	64	54	64	72
105°	230	223	230	223	230	242
115°	414	414	414	414	414	409
125°	605	603	605	603	605	539
135°	789	780	789	780	789	608
145°	957	947	957	947	957	598
155°	1091	1082	1091	1082	1091	502
165°	1179	1178	1179	1178	1179	332
175°	1221	1225	1221	1225	1221	116
180°	1227	1227	1227	1227	1227	



TEST NUMBER: P331367-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1239.0	1239.4	1240.2	1234.3	1233.6	1233.6	1228.5	1224.1	1219.1	1212.1	1212.8
5°	1322.9	1327.8	1329.6	1324.2	1316.0	1315.1	1307.3	1294.6	1282.7	1273.2	1266.4
7.5°	1422.8	1424.8	1420.3	1413.1	1407.0	1396.2	1381.7	1367.6	1347.8	1329.7	1316.3
10°	1498.5	1501.3	1493.5	1483.1	1474.4	1461.7	1440.7	1419.3	1393.4	1368.3	1348.3
12.5°	1556.0	1562.8	1552.9	1551.5	1536.7	1519.2	1494.2	1483.5	1446.9	1412.0	1390.5
15°	1625.9	1625.5	1626.5	1617.8	1606.9	1604.1	1577.7	1549.1	1497.6	1477.1	1441.6
17.5°	1605.8	1612.7	1615.9	1615.8	1615.5	1613.8	1605.3	1587.2	1561.5	1528.2	1487.2
20°	1557.7	1566.8	1568.2	1578.7	1584.6	1592.3	1595.4	1590.5	1574.6	1546.8	1511.3
22.5°	1483.5	1485.9	1490.2	1506.5	1519.4	1538.7	1548.9	1565.8	1559.6	1546.0	1516.4
25°	1354.7	1350.1	1366.1	1374.2	1403.8	1434.8	1457.1	1481.7	1503.5	1516.7	1508.1
27.5°	1200.1	1193.3	1217.1	1238.9	1262.9	1296.5	1331.2	1372.3	1406.4	1449.1	1463.7
30°	1069.7	1073.8	1096.6	1119.8	1156.2	1203.5	1242.7	1287.8	1336.5	1384.3	1417.5
32.5°	929.2	944.9	959.3	994.9	1026.9	1079.8	1137.1	1193.5	1254.2	1308.5	1359.9
35°	737.4	755.6	775.7	801.6	846.7	899.0	955.0	1031.0	1113.9	1188.1	1249.1
37.5°	620.7	617.8	629.3	648.0	684.6	726.7	791.2	866.4	963.9	1051.1	1137.1
40°	550.8	548.9	557.1	574.4	602.3	633.2	689.6	755.6	846.2	952.7	1055.2
42.5°	502.7	503.8	508.4	520.6	539.6	565.1	607.3	663.5	746.5	846.8	956.8
45°	444.3	447.5	452.5	458.4	469.3	490.3	513.9	554.0	619.6	703.3	811.6
47.5°	402.3	402.3	407.4	412.6	419.1	430.9	450.2	475.3	521.6	589.8	682.9
50°	379.6	376.5	380.1	384.1	391.0	399.2	412.0	435.6	466.5	521.7	599.5
52.5°	352.0	352.0	355.3	356.9	363.0	371.1	382.8	399.2	427.2	470.3	534.3
55°	312.3	314.5	316.4	319.1	324.6	330.5	339.6	350.5	372.4	404.7	452.0
57.5°	274.9	275.6	277.5	282.7	286.1	291.6	300.2	310.1	324.4	348.3	383.9
60°	249.4	249.4	253.1	255.4	259.9	265.4	272.2	281.8	294.5	314.1	342.8
62.5°	226.1	225.8	227.2	231.0	234.4	239.5	246.4	254.5	266.4	283.8	307.5
65°	192.1	191.2	193.9	194.8	198.5	203.5	208.9	217.6	227.1	239.9	260.8
67.5°	159.3	160.4	161.8	163.6	165.6	170.9	174.5	180.7	188.7	199.3	213.5
70°	141.1	141.1	141.1	142.5	145.2	147.9	151.6	156.6	164.3	173.4	186.2
72.5°	120.7	122.2	123.6	122.8	126.3	127.9	132.2	135.1	142.5	148.3	159.6
75°	94.7	94.7	94.7	96.9	98.4	99.7	102.5	105.1	108.8	116.1	122.0
77.5°	70.6	70.4	70.9	71.4	72.9	74.5	75.3	77.8	81.2	84.5	89.6
80°	54.7	55.6	56.0	56.9	56.9	57.8	58.2	61.4	63.8	66.0	69.2
82.5°	42.3	42.4	42.5	42.7	43.1	43.6	44.8	45.8	46.6	48.5	51.0
85°	24.6	24.2	24.2	25.1	24.6	24.6	25.5	26.4	26.4	26.8	28.2
87.5°	16.5	16.5	16.8	16.4	16.3	16.7	16.8	16.5	17.0	17.5	16.8
90°	35.2	35.0	34.8	34.5	34.3	34.4	34.9	35.3	35.8	36.3	31.2
92.5°	33.5	33.5	33.4	33.4	33.3	33.3	33.2	33.1	33.0	32.9	31.7
95°	64.2	64.6	65.2	65.6	66.1	66.3	66.3	66.3	66.3	66.3	65.8
97.5°	111.3	111.3	111.4	111.4	111.5	111.5	111.5	111.5	111.5	111.5	110.6
100°	141.9	142.1	142.4	142.6	142.9	142.9	142.9	142.9	142.9	142.9	142.2
102.5°	176.7	176.9	177.2	177.4	177.6	177.6	177.5	177.3	177.1	176.9	176.0
105°	230.0	230.0	230.0	230.0	230.0	229.7	229.3	228.8	228.4	227.8	227.4
107.5°	280.1	281.2	282.2	283.3	284.3	284.7	284.5	284.4	284.2	284.0	284.0
110°	319.1	319.7	320.4	321.1	321.8	322.2	322.2	322.2	322.2	322.2	322.2



TEST NUMBER: P331367-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.3	356.9	357.3	357.8	358.4	358.9	359.4	360.0	360.5	361.1	361.2
115°	414.3	415.0	415.7	416.4	417.1	417.5	417.8	418.0	418.2	418.5	418.9
117.5°	469.7	470.3	471.0	471.7	472.4	473.1	473.6	474.1	474.7	475.2	476.5
120°	508.5	509.3	510.0	510.7	511.3	511.7	511.7	511.7	511.7	511.7	513.5
122.5°	546.7	547.2	547.7	548.2	548.8	549.2	549.8	550.4	550.9	551.4	552.8
125°	604.9	605.1	605.4	605.6	605.8	606.3	607.0	607.7	608.3	609.0	609.8
127.5°	657.9	658.7	659.4	660.1	660.8	661.6	662.5	663.3	664.1	664.9	665.8
130°	696.1	697.0	697.9	698.8	699.7	700.4	700.9	701.3	701.8	702.3	702.8
132.5°	732.5	733.3	734.0	734.8	735.5	736.4	737.4	738.3	739.4	740.4	740.3
135°	789.3	790.0	790.7	791.3	792.0	792.5	792.7	793.0	793.2	793.4	793.0
137.5°	840.6	841.6	842.5	843.4	844.4	844.9	845.1	845.3	845.4	845.6	845.0
140°	876.3	877.2	878.2	879.0	879.9	880.4	880.4	880.4	880.4	880.4	879.3
142.5°	908.6	909.5	910.4	911.3	912.3	912.7	912.5	912.3	912.1	912.0	911.2
145°	957.1	958.0	958.9	959.8	960.7	961.1	960.9	960.6	960.4	960.2	958.8
147.5°	1000.4	1001.2	1002.1	1003.0	1003.9	1004.1	1003.5	1003.1	1002.6	1002.0	1001.1
150°	1028.6	1029.2	1029.9	1030.6	1031.4	1031.4	1030.6	1029.9	1029.2	1028.6	1027.6
152.5°	1055.1	1056.0	1056.9	1057.7	1058.5	1058.5	1057.7	1056.9	1056.0	1055.1	1054.0
155°	1090.7	1091.4	1092.1	1092.8	1093.4	1093.2	1092.1	1090.9	1089.8	1088.6	1088.0
157.5°	1121.3	1122.5	1123.6	1124.6	1125.8	1125.5	1124.0	1122.4	1120.9	1119.3	1118.8
160°	1140.4	1141.3	1142.3	1143.2	1144.1	1143.9	1142.5	1141.1	1139.7	1138.4	1138.1
162.5°	1157.0	1158.1	1159.2	1160.3	1161.4	1161.2	1159.6	1158.1	1156.5	1154.9	1154.7
165°	1178.8	1179.9	1181.1	1182.2	1183.3	1183.1	1181.5	1179.9	1178.3	1176.7	1176.7
167.5°	1196.6	1197.7	1198.9	1200.2	1201.3	1201.1	1199.5	1197.9	1196.3	1194.7	1194.7
170°	1205.7	1207.0	1208.4	1209.8	1211.2	1211.0	1209.4	1207.8	1206.2	1204.6	1204.9
172.5°	1213.1	1214.5	1215.8	1217.3	1218.6	1218.5	1216.9	1215.3	1213.7	1212.1	1212.3
175°	1221.2	1222.6	1224.0	1225.4	1226.7	1226.6	1225.0	1223.4	1221.8	1220.1	1220.7
177.5°	1224.9	1226.0	1227.2	1228.2	1229.3	1229.3	1228.2	1227.2	1226.0	1224.9	1225.3
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331367-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1215.4	1212.5	1210.7	1204.1	1198.3	1192.5	1190.6	1191.3	1183.4	1175.7	1172.4
5°	1262.8	1253.7	1245.0	1232.7	1218.2	1202.2	1194.0	1187.6	1171.7	1154.4	1144.4
7.5°	1305.2	1292.2	1275.5	1252.3	1231.2	1206.1	1190.2	1176.1	1152.7	1128.4	1113.4
10°	1331.1	1313.2	1291.8	1263.6	1237.7	1207.2	1185.8	1164.4	1137.1	1108.0	1089.8
12.5°	1353.3	1329.3	1308.2	1272.0	1241.4	1203.2	1177.8	1147.6	1118.9	1084.3	1066.5
15°	1406.1	1362.0	1321.9	1280.9	1243.1	1189.9	1161.7	1121.1	1083.3	1040.6	1020.1
17.5°	1447.0	1397.4	1334.3	1282.2	1238.1	1179.2	1137.7	1089.2	1044.6	995.6	967.8
20°	1470.3	1413.4	1345.6	1283.7	1230.8	1163.5	1118.5	1068.8	1016.5	961.4	931.3
22.5°	1484.2	1424.3	1357.3	1278.2	1216.3	1150.8	1094.0	1039.6	986.6	927.2	895.6
25°	1488.5	1433.9	1362.9	1273.6	1198.1	1123.9	1055.6	1002.8	938.6	883.1	837.1
27.5°	1466.9	1427.7	1359.4	1265.1	1177.1	1090.3	1014.2	954.4	886.6	826.3	780.2
30°	1440.3	1417.5	1351.0	1256.3	1160.3	1067.0	983.2	915.4	848.0	787.0	739.7
32.5°	1399.1	1394.2	1335.8	1243.9	1142.5	1037.5	950.8	882.3	807.6	747.7	702.6
35°	1318.3	1340.2	1303.2	1216.3	1108.8	995.5	901.8	823.5	746.1	688.8	646.4
37.5°	1210.0	1264.2	1254.5	1175.8	1063.5	949.9	846.3	764.5	690.7	632.8	591.3
40°	1135.2	1204.4	1214.5	1144.9	1031.5	914.5	804.8	723.4	651.4	598.6	556.7
42.5°	1055.2	1136.0	1163.5	1107.7	996.5	877.4	767.7	683.2	612.1	560.7	523.6
45°	920.9	1027.9	1077.5	1045.6	938.2	816.2	703.3	617.7	553.0	504.8	476.2
47.5°	795.3	912.2	978.9	967.7	873.3	752.4	640.9	558.7	495.8	457.3	431.6
50°	706.5	826.6	907.2	910.9	826.6	706.9	594.9	517.5	459.8	423.8	402.9
52.5°	629.3	744.0	831.9	851.1	774.5	659.6	553.8	476.8	425.9	392.8	374.1
55°	528.5	625.4	722.8	758.4	696.9	587.6	489.8	422.0	374.2	351.4	335.0
57.5°	439.3	520.2	610.2	649.4	611.5	518.0	426.2	367.4	328.6	308.6	296.0
60°	392.4	456.1	536.2	583.1	550.4	467.1	386.9	330.9	299.1	281.3	269.5
62.5°	348.7	405.1	472.9	515.8	497.9	419.4	347.6	298.2	270.6	254.0	245.5
65°	287.7	332.3	384.7	424.3	412.4	352.8	294.1	251.7	229.9	216.7	209.8
67.5°	236.9	269.1	305.4	340.1	330.6	288.3	241.2	208.2	191.9	180.6	176.5
70°	204.8	229.4	261.7	289.5	281.8	247.2	209.8	181.6	167.6	157.9	153.8
72.5°	174.2	194.5	219.1	241.8	236.6	207.9	176.7	155.4	144.5	135.7	132.3
75°	131.5	147.0	162.0	177.1	175.7	153.4	135.2	118.8	110.1	103.3	101.9
77.5°	97.1	105.8	116.0	124.9	122.4	109.7	95.4	86.1	79.6	75.1	74.4
80°	74.2	79.2	86.5	92.8	89.7	84.2	72.9	66.0	61.4	56.9	55.1
82.5°	53.8	58.9	63.2	66.6	64.2	59.1	52.1	47.4	44.7	41.6	40.8
85°	28.2	30.9	32.8	33.7	32.8	29.6	26.4	24.6	22.3	21.0	20.5
87.5°	16.1	15.2	14.1	14.1	12.4	11.9	9.9	8.2	8.4	8.6	8.4
90°	26.1	21.0	16.0	12.1	9.4	6.6	3.8	1.1	3.8	6.6	9.4
92.5°	30.6	29.3	28.2	26.6	24.5	22.5	20.4	18.5	20.4	22.5	24.5
95°	65.4	64.9	64.5	63.0	60.7	58.5	56.2	53.9	56.2	58.5	60.7
97.5°	109.7	108.8	108.0	106.5	104.5	102.5	100.4	98.4	100.4	102.5	104.5
100°	141.5	140.9	140.2	138.9	137.1	135.3	133.4	131.5	133.4	135.3	137.1
102.5°	175.1	174.3	173.4	172.3	170.8	169.3	167.8	166.4	167.8	169.3	170.8
105°	226.9	226.5	226.0	225.4	224.8	224.1	223.4	222.7	223.4	224.1	224.8
107.5°	284.0	284.0	284.0	283.5	282.5	281.5	280.4	279.5	280.4	281.5	282.5
110°	322.2	322.2	322.2	321.5	320.0	318.7	317.3	315.9	317.3	318.7	320.0





TEST NUMBER: P331367-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	361.4	361.6	361.9	361.2	359.8	358.5	357.0	355.7	357.0	358.5	359.8
115°	419.4	419.8	420.3	419.8	418.5	417.1	415.7	414.3	415.7	417.1	418.5
117.5°	477.8	479.1	480.4	480.1	478.2	476.4	474.6	472.7	474.6	476.4	478.2
120°	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7	513.5	515.4	517.2
122.5°	554.0	555.4	556.6	556.2	553.9	551.7	549.6	547.3	549.6	551.7	553.9
125°	610.5	611.1	611.8	611.1	609.0	607.0	604.9	602.8	604.9	607.0	609.0
127.5°	666.6	667.4	668.3	667.4	664.8	662.2	659.5	656.9	659.5	662.2	664.8
130°	703.2	703.6	704.1	702.8	699.8	696.9	693.8	690.9	693.8	696.9	699.8
132.5°	740.2	740.1	740.0	738.8	736.3	733.9	731.5	729.0	731.5	733.9	736.3
135°	792.5	792.0	791.6	790.1	787.6	785.1	782.5	780.0	782.5	785.1	787.6
137.5°	844.5	843.8	843.2	841.9	839.8	837.8	835.7	833.6	835.7	837.8	839.8
140°	878.2	877.0	875.8	874.2	872.2	870.0	868.0	865.9	868.0	870.0	872.2
142.5°	910.3	909.5	908.7	907.3	905.3	903.2	901.2	899.1	901.2	903.2	905.3
145°	957.4	956.0	954.7	953.1	951.5	949.9	948.3	946.7	948.3	949.9	951.5
147.5°	1000.2	999.3	998.4	996.9	995.0	993.0	991.1	989.2	991.1	993.0	995.0
150°	1026.7	1025.8	1024.8	1023.7	1022.3	1020.9	1019.6	1018.2	1019.6	1020.9	1022.3
152.5°	1052.8	1051.8	1050.6	1049.4	1048.0	1046.6	1045.3	1043.8	1045.3	1046.6	1048.0
155°	1087.3	1086.5	1085.8	1085.2	1084.5	1083.8	1083.1	1082.4	1083.1	1083.8	1084.5
157.5°	1118.5	1118.0	1117.6	1117.2	1116.7	1116.2	1115.8	1115.4	1115.8	1116.2	1116.7
160°	1137.9	1137.6	1137.4	1137.1	1136.6	1136.1	1135.7	1135.2	1135.7	1136.1	1136.6
162.5°	1154.4	1154.2	1154.0	1153.9	1153.7	1153.6	1153.5	1153.4	1153.5	1153.6	1153.7
165°	1176.7	1176.7	1176.7	1176.8	1177.0	1177.2	1177.5	1177.7	1177.5	1177.2	1177.0
167.5°	1194.8	1194.8	1194.9	1195.2	1196.0	1196.6	1197.3	1198.0	1197.3	1196.6	1196.0
170°	1205.1	1205.3	1205.6	1206.0	1206.7	1207.4	1208.1	1208.8	1208.1	1207.4	1206.7
172.5°	1212.5	1212.8	1213.0	1213.4	1214.2	1214.9	1215.6	1216.2	1215.6	1214.9	1214.2
175°	1221.1	1221.6	1222.0	1222.6	1223.2	1224.0	1224.7	1225.4	1224.7	1224.0	1223.2
177.5°	1225.7	1226.0	1226.4	1226.9	1227.4	1228.0	1228.5	1229.0	1228.5	1228.0	1227.4
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331367-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1168.8	1166.6	1159.0	1154.9	1148.3	1142.2	1138.2	1140.1	1141.5	1140.8	1139.6
5°	1135.2	1126.6	1113.4	1102.1	1093.9	1078.8	1072.5	1069.3	1066.6	1063.4	1060.2
7.5°	1095.4	1081.7	1062.8	1046.6	1031.3	1012.6	1002.0	995.6	989.1	981.9	975.5
10°	1067.0	1047.8	1027.9	1005.0	986.9	970.0	955.0	945.0	935.9	927.3	920.9
12.5°	1037.1	1015.1	990.3	959.2	939.1	915.1	912.8	895.1	880.9	875.6	868.1
15°	989.6	958.7	927.3	890.4	874.4	852.6	838.9	825.3	813.0	804.3	802.1
17.5°	935.6	895.5	864.3	837.9	811.7	789.3	776.8	765.8	755.7	744.1	742.6
20°	894.5	859.9	825.7	802.5	775.7	752.9	737.4	726.5	717.8	711.1	705.1
22.5°	855.5	817.6	786.4	761.0	734.5	716.1	703.9	693.4	686.2	678.6	673.1
25°	793.0	763.4	729.2	700.5	678.7	666.9	656.8	647.7	643.2	638.2	631.9
27.5°	738.2	705.3	673.4	651.2	632.0	621.5	614.4	608.2	604.0	601.0	597.4
30°	699.6	666.4	641.4	619.6	603.6	593.2	588.6	585.0	580.0	578.1	576.3
32.5°	662.5	632.6	611.2	592.2	577.0	570.2	566.0	562.8	558.8	557.0	553.3
35°	609.9	585.0	564.0	553.5	541.3	535.3	532.2	527.5	524.0	522.1	521.7
37.5°	560.5	538.8	525.0	511.6	506.4	502.7	498.4	495.3	494.2	493.9	493.5
40°	528.5	510.8	498.5	487.5	485.3	479.7	476.2	473.4	473.4	473.9	473.4
42.5°	499.4	483.4	472.6	463.2	460.5	457.2	453.5	453.3	454.1	455.7	454.1
45°	455.2	443.8	436.0	431.5	426.5	423.3	422.8	424.3	424.7	425.2	426.5
47.5°	414.6	407.1	400.0	395.0	392.8	392.3	391.7	394.1	396.3	397.1	399.2
50°	390.6	381.9	376.0	372.8	371.0	370.1	371.0	373.7	375.5	377.8	379.2
52.5°	363.6	357.5	353.4	351.0	350.3	350.8	351.0	354.1	357.0	357.8	358.5
55°	326.4	321.8	320.9	316.8	318.6	318.2	320.5	322.3	325.0	327.7	328.2
57.5°	289.3	285.6	283.1	283.5	284.0	286.1	287.9	291.1	294.1	296.9	297.2
60°	264.5	262.6	261.3	261.3	262.2	264.9	267.2	270.4	272.2	274.0	275.4
62.5°	241.9	240.0	238.7	239.4	241.8	243.4	246.1	247.8	249.6	251.5	252.1
65°	206.2	205.3	206.7	207.6	208.0	210.3	213.5	214.8	216.7	217.6	220.8
67.5°	173.3	173.5	173.3	174.6	177.3	177.8	180.8	184.0	184.3	186.1	188.2
70°	151.1	152.0	152.9	153.8	156.1	157.0	159.3	160.7	162.5	163.9	165.2
72.5°	130.7	130.9	131.8	131.6	133.6	135.5	137.5	138.8	140.6	142.4	143.7
75°	100.6	100.6	101.5	101.9	104.2	106.6	106.0	107.0	108.8	110.6	111.6
77.5°	73.5	72.5	73.5	73.9	74.6	76.6	77.0	78.2	80.3	79.6	80.7
80°	56.0	54.7	56.0	56.4	56.4	58.8	58.8	59.7	61.0	59.7	61.0
82.5°	39.9	39.3	40.3	40.4	41.1	41.2	42.0	42.2	43.5	42.9	43.5
85°	20.1	19.6	20.1	19.6	20.1	20.5	20.5	20.1	20.1	21.0	19.6
87.5°	8.6	9.0	9.6	10.7	11.3	11.9	11.5	11.4	11.3	10.5	10.5
90°	12.1	16.0	21.0	26.1	31.2	36.3	35.8	35.3	34.9	34.4	34.3
92.5°	26.6	28.2	29.3	30.6	31.7	32.9	33.0	33.1	33.2	33.3	33.3
95°	63.0	64.5	64.9	65.4	65.8	66.3	66.3	66.3	66.3	66.3	66.1
97.5°	106.5	108.0	108.8	109.7	110.6	111.5	111.5	111.5	111.5	111.5	111.5
100°	138.9	140.2	140.9	141.5	142.2	142.9	142.9	142.9	142.9	142.9	142.9
102.5°	172.3	173.4	174.3	175.1	176.0	176.9	177.1	177.3	177.5	177.6	177.6
105°	225.4	226.0	226.5	226.9	227.4	227.8	228.4	228.8	229.3	229.7	230.0
107.5°	283.5	284.0	284.0	284.0	284.0	284.0	284.2	284.4	284.5	284.7	284.3
110°	321.5	322.2	322.2	322.2	322.2	322.2	322.2	322.2	322.2	322.2	321.8



TEST NUMBER: P331367-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	361.2	361.9	361.6	361.4	361.2	361.1	360.5	360.0	359.4	358.9	358.4
115°	419.8	420.3	419.8	419.4	418.9	418.5	418.2	418.0	417.8	417.5	417.1
117.5°	480.1	480.4	479.1	477.8	476.5	475.2	474.7	474.1	473.6	473.1	472.4
120°	519.1	519.1	517.2	515.4	513.5	511.7	511.7	511.7	511.7	511.7	511.3
122.5°	556.2	556.6	555.4	554.0	552.8	551.4	550.9	550.4	549.8	549.2	548.8
125°	611.1	611.8	611.1	610.5	609.8	609.0	608.3	607.7	607.0	606.3	605.8
127.5°	667.4	668.3	667.4	666.6	665.8	664.9	664.1	663.3	662.5	661.6	660.8
130°	702.8	704.1	703.6	703.2	702.8	702.3	701.8	701.3	700.9	700.4	699.7
132.5°	738.8	740.0	740.1	740.2	740.3	740.4	739.4	738.3	737.4	736.4	735.5
135°	790.1	791.6	792.0	792.5	793.0	793.4	793.2	793.0	792.7	792.5	792.0
137.5°	841.9	843.2	843.8	844.5	845.0	845.6	845.4	845.3	845.1	844.9	844.4
140°	874.2	875.8	877.0	878.2	879.3	880.4	880.4	880.4	880.4	880.4	879.9
142.5°	907.3	908.7	909.5	910.3	911.2	912.0	912.1	912.3	912.5	912.7	912.3
145°	953.1	954.7	956.0	957.4	958.8	960.2	960.4	960.6	960.9	961.1	960.7
147.5°	996.9	998.4	999.3	1000.2	1001.1	1002.0	1002.6	1003.1	1003.5	1004.1	1003.9
150°	1023.7	1024.8	1025.8	1026.7	1027.6	1028.6	1029.2	1029.9	1030.6	1031.4	1031.4
152.5°	1049.4	1050.6	1051.8	1052.8	1054.0	1055.1	1056.0	1056.9	1057.7	1058.5	1058.5
155°	1085.2	1085.8	1086.5	1087.3	1088.0	1088.6	1089.8	1090.9	1092.1	1093.2	1093.4
157.5°	1117.2	1117.6	1118.0	1118.5	1118.8	1119.3	1120.9	1122.4	1124.0	1125.5	1125.8
160°	1137.1	1137.4	1137.6	1137.9	1138.1	1138.4	1139.7	1141.1	1142.5	1143.9	1144.1
162.5°	1153.9	1154.0	1154.2	1154.4	1154.7	1154.9	1156.5	1158.1	1159.6	1161.2	1161.4
165°	1176.8	1176.7	1176.7	1176.7	1176.7	1176.7	1178.3	1179.9	1181.5	1183.1	1183.3
167.5°	1195.2	1194.9	1194.8	1194.8	1194.7	1194.7	1196.3	1197.9	1199.5	1201.1	1201.3
170°	1206.0	1205.6	1205.3	1205.1	1204.9	1204.6	1206.2	1207.8	1209.4	1211.0	1211.2
172.5°	1213.4	1213.0	1212.8	1212.5	1212.3	1212.1	1213.7	1215.3	1216.9	1218.5	1218.6
175°	1222.6	1222.0	1221.6	1221.1	1220.7	1220.1	1221.8	1223.4	1225.0	1226.6	1226.7
177.5°	1226.9	1226.4	1226.0	1225.7	1225.3	1224.9	1226.0	1227.2	1228.2	1229.3	1229.3
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331367-940  
 CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1136.0	1135.2	1135.2	1132.0	1135.2	1135.2	1136.0	1139.6	1140.8	1141.5	1140.1
5°	1053.8	1052.4	1050.2	1052.4	1050.2	1052.4	1053.8	1060.2	1063.4	1066.6	1069.3
7.5°	972.5	967.1	966.3	960.8	966.3	967.1	972.5	975.5	981.9	989.1	995.6
10°	913.1	909.5	909.0	900.4	909.0	909.5	913.1	920.9	927.3	935.9	945.0
12.5°	868.0	859.3	860.9	856.0	860.9	859.3	868.0	868.1	875.6	880.9	895.1
15°	789.8	789.8	787.9	780.2	787.9	789.8	789.8	802.1	804.3	813.0	825.3
17.5°	733.6	732.7	728.3	730.5	728.3	732.7	733.6	742.6	744.1	755.7	765.8
20°	700.1	697.4	691.9	691.9	691.9	697.4	700.1	705.1	711.1	717.8	726.5
22.5°	668.4	668.2	662.5	664.2	662.5	668.2	668.4	673.1	678.6	686.2	693.4
25°	631.3	627.8	625.0	626.3	625.0	627.8	631.3	631.9	638.2	643.2	647.7
27.5°	596.2	594.2	594.1	590.3	594.1	594.2	596.2	597.4	601.0	604.0	608.2
30°	575.9	571.3	572.2	569.9	572.2	571.3	575.9	576.3	578.1	580.0	585.0
32.5°	552.5	550.9	550.0	548.0	550.0	550.9	552.5	553.3	557.0	558.8	562.8
35°	520.8	521.2	519.0	519.9	519.0	521.2	520.8	521.7	522.1	524.0	527.5
37.5°	493.0	494.5	493.4	493.7	493.4	494.5	493.0	493.5	493.9	494.2	495.3
40°	474.7	474.7	474.7	476.2	474.7	474.7	474.7	473.4	473.9	473.4	473.4
42.5°	457.3	456.6	455.8	455.8	455.8	456.6	457.3	454.1	455.7	454.1	453.3
45°	427.4	428.8	429.3	427.0	429.3	428.8	427.4	426.5	425.2	424.7	424.3
47.5°	400.4	400.6	400.4	402.4	400.4	400.6	400.4	399.2	397.1	396.3	394.1
50°	381.5	380.6	381.5	380.6	381.5	380.6	381.5	379.2	377.8	375.5	373.7
52.5°	361.4	361.6	361.1	360.9	361.1	361.6	361.4	358.5	357.8	357.0	354.1
55°	330.0	330.9	330.5	330.5	330.5	330.9	330.0	328.2	327.7	325.0	322.3
57.5°	297.6	298.4	299.0	296.9	299.0	298.4	297.6	297.2	296.9	294.1	291.1
60°	274.9	277.2	276.8	275.9	276.8	277.2	274.9	275.4	274.0	272.2	270.4
62.5°	254.2	255.0	254.9	254.8	254.9	255.0	254.2	252.1	251.5	249.6	247.8
65°	222.1	223.0	221.7	223.0	221.7	223.0	222.1	220.8	217.6	216.7	214.8
67.5°	187.6	187.9	189.0	189.6	189.0	187.9	187.6	188.2	186.1	184.3	184.0
70°	166.1	165.7	167.0	168.4	167.0	165.7	166.1	165.2	163.9	162.5	160.7
72.5°	143.6	144.5	144.1	145.1	144.1	144.5	143.6	143.7	142.4	140.6	138.8
75°	110.6	112.0	111.6	112.9	111.6	112.0	110.6	111.6	110.6	108.8	107.0
77.5°	79.9	80.1	79.9	80.7	79.9	80.1	79.9	80.7	79.6	80.3	78.2
80°	61.0	60.1	59.2	61.0	59.2	60.1	61.0	61.0	59.7	61.0	59.7
82.5°	42.4	43.0	42.1	42.1	42.1	43.0	42.4	43.5	42.9	43.5	42.2
85°	19.6	19.1	18.2	18.2	18.2	19.1	19.6	19.6	21.0	20.1	20.1
87.5°	10.5	10.3	10.3	10.0	10.3	10.3	10.5	10.5	10.5	11.3	11.4
90°	34.5	34.8	35.0	35.2	35.0	34.8	34.5	34.3	34.4	34.9	35.3
92.5°	33.4	33.4	33.5	33.5	33.5	33.4	33.4	33.3	33.3	33.2	33.1
95°	65.6	65.2	64.6	64.2	64.6	65.2	65.6	66.1	66.3	66.3	66.3
97.5°	111.4	111.4	111.3	111.3	111.3	111.4	111.4	111.5	111.5	111.5	111.5
100°	142.6	142.4	142.1	141.9	142.1	142.4	142.6	142.9	142.9	142.9	142.9
102.5°	177.4	177.2	176.9	176.7	176.9	177.2	177.4	177.6	177.6	177.5	177.3
105°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	229.7	229.3	228.8
107.5°	283.3	282.2	281.2	280.1	281.2	282.2	283.3	284.3	284.7	284.5	284.4
110°	321.1	320.4	319.7	319.1	319.7	320.4	321.1	321.8	322.2	322.2	322.2



TEST NUMBER: P331367-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	357.8	357.3	356.9	356.3	356.9	357.3	357.8	358.4	358.9	359.4	360.0
115°	416.4	415.7	415.0	414.3	415.0	415.7	416.4	417.1	417.5	417.8	418.0
117.5°	471.7	471.0	470.3	469.7	470.3	471.0	471.7	472.4	473.1	473.6	474.1
120°	510.7	510.0	509.3	508.5	509.3	510.0	510.7	511.3	511.7	511.7	511.7
122.5°	548.2	547.7	547.2	546.7	547.2	547.7	548.2	548.8	549.2	549.8	550.4
125°	605.6	605.4	605.1	604.9	605.1	605.4	605.6	605.8	606.3	607.0	607.7
127.5°	660.1	659.4	658.7	657.9	658.7	659.4	660.1	660.8	661.6	662.5	663.3
130°	698.8	697.9	697.0	696.1	697.0	697.9	698.8	699.7	700.4	700.9	701.3
132.5°	734.8	734.0	733.3	732.5	733.3	734.0	734.8	735.5	736.4	737.4	738.3
135°	791.3	790.7	790.0	789.3	790.0	790.7	791.3	792.0	792.5	792.7	793.0
137.5°	843.4	842.5	841.6	840.6	841.6	842.5	843.4	844.4	844.9	845.1	845.3
140°	879.0	878.2	877.2	876.3	877.2	878.2	879.0	879.9	880.4	880.4	880.4
142.5°	911.3	910.4	909.5	908.6	909.5	910.4	911.3	912.3	912.7	912.5	912.3
145°	959.8	958.9	958.0	957.1	958.0	958.9	959.8	960.7	961.1	960.9	960.6
147.5°	1003.0	1002.1	1001.2	1000.4	1001.2	1002.1	1003.0	1003.9	1004.1	1003.5	1003.1
150°	1030.6	1029.9	1029.2	1028.6	1029.2	1029.9	1030.6	1031.4	1031.4	1030.6	1029.9
152.5°	1057.7	1056.9	1056.0	1055.1	1056.0	1056.9	1057.7	1058.5	1058.5	1057.7	1056.9
155°	1092.8	1092.1	1091.4	1090.7	1091.4	1092.1	1092.8	1093.4	1093.2	1092.1	1090.9
157.5°	1124.6	1123.6	1122.5	1121.3	1122.5	1123.6	1124.6	1125.8	1125.5	1124.0	1122.4
160°	1143.2	1142.3	1141.3	1140.4	1141.3	1142.3	1143.2	1144.1	1143.9	1142.5	1141.1
162.5°	1160.3	1159.2	1158.1	1157.0	1158.1	1159.2	1160.3	1161.4	1161.2	1159.6	1158.1
165°	1182.2	1181.1	1179.9	1178.8	1179.9	1181.1	1182.2	1183.3	1183.1	1181.5	1179.9
167.5°	1200.2	1198.9	1197.7	1196.6	1197.7	1198.9	1200.2	1201.3	1201.1	1199.5	1197.9
170°	1209.8	1208.4	1207.0	1205.7	1207.0	1208.4	1209.8	1211.2	1211.0	1209.4	1207.8
172.5°	1217.3	1215.8	1214.5	1213.1	1214.5	1215.8	1217.3	1218.6	1218.5	1216.9	1215.3
175°	1225.4	1224.0	1222.6	1221.2	1222.6	1224.0	1225.4	1226.7	1226.6	1225.0	1223.4
177.5°	1228.2	1227.2	1226.0	1224.9	1226.0	1227.2	1228.2	1229.3	1229.3	1228.2	1227.2
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331367-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1138.2	1142.2	1148.3	1154.9	1159.0	1166.6	1168.8	1172.4	1175.7	1183.4	1191.3
5°	1072.5	1078.8	1093.9	1102.1	1113.4	1126.6	1135.2	1144.4	1154.4	1171.7	1187.6
7.5°	1002.0	1012.6	1031.3	1046.6	1062.8	1081.7	1095.4	1113.4	1128.4	1152.7	1176.1
10°	955.0	970.0	986.9	1005.0	1027.9	1047.8	1067.0	1089.8	1108.0	1137.1	1164.4
12.5°	912.8	915.1	939.1	959.2	990.3	1015.1	1037.1	1066.5	1084.3	1118.9	1147.6
15°	838.9	852.6	874.4	890.4	927.3	958.7	989.6	1020.1	1040.6	1083.3	1121.1
17.5°	776.8	789.3	811.7	837.9	864.3	895.5	935.6	967.8	995.6	1044.6	1089.2
20°	737.4	752.9	775.7	802.5	825.7	859.9	894.5	931.3	961.4	1016.5	1068.8
22.5°	703.9	716.1	734.5	761.0	786.4	817.6	855.5	895.6	927.2	986.6	1039.6
25°	656.8	666.9	678.7	700.5	729.2	763.4	793.0	837.1	883.1	938.6	1002.8
27.5°	614.4	621.5	632.0	651.2	673.4	705.3	738.2	780.2	826.3	886.6	954.4
30°	588.6	593.2	603.6	619.6	641.4	666.4	699.6	739.7	787.0	848.0	915.4
32.5°	566.0	570.2	577.0	592.2	611.2	632.6	662.5	702.6	747.7	807.6	882.3
35°	532.2	535.3	541.3	553.5	564.0	585.0	609.9	646.4	688.8	746.1	823.5
37.5°	498.4	502.7	506.4	511.6	525.0	538.8	560.5	591.3	632.8	690.7	764.5
40°	476.2	479.7	485.3	487.5	498.5	510.8	528.5	556.7	598.6	651.4	723.4
42.5°	453.5	457.2	460.5	463.2	472.6	483.4	499.4	523.6	560.7	612.1	683.2
45°	422.8	423.3	426.5	431.5	436.0	443.8	455.2	476.2	504.8	553.0	617.7
47.5°	391.7	392.3	392.8	395.0	400.0	407.1	414.6	431.6	457.3	495.8	558.7
50°	371.0	370.1	371.0	372.8	376.0	381.9	390.6	402.9	423.8	459.8	517.5
52.5°	351.0	350.8	350.3	351.0	353.4	357.5	363.6	374.1	392.8	425.9	476.8
55°	320.5	318.2	318.6	316.8	320.9	321.8	326.4	335.0	351.4	374.2	422.0
57.5°	287.9	286.1	284.0	283.5	283.1	285.6	289.3	296.0	308.6	328.6	367.4
60°	267.2	264.9	262.2	261.3	261.3	262.6	264.5	269.5	281.3	299.1	330.9
62.5°	246.1	243.4	241.8	239.4	238.7	240.0	241.9	245.5	254.0	270.6	298.2
65°	213.5	210.3	208.0	207.6	206.7	205.3	206.2	209.8	216.7	229.9	251.7
67.5°	180.8	177.8	177.3	174.6	173.3	173.5	173.3	176.5	180.6	191.9	208.2
70°	159.3	157.0	156.1	153.8	152.9	152.0	151.1	153.8	157.9	167.6	181.6
72.5°	137.5	135.5	133.6	131.6	131.8	130.9	130.7	132.3	135.7	144.5	155.4
75°	106.0	106.6	104.2	101.9	101.5	100.6	100.6	101.9	103.3	110.1	118.8
77.5°	77.0	76.6	74.6	73.9	73.5	72.5	73.5	74.4	75.1	79.6	86.1
80°	58.8	58.8	56.4	56.4	56.0	54.7	56.0	55.1	56.9	61.4	66.0
82.5°	42.0	41.2	41.1	40.4	40.3	39.3	39.9	40.8	41.6	44.7	47.4
85°	20.5	20.5	20.1	19.6	20.1	19.6	20.1	20.5	21.0	22.3	24.6
87.5°	11.5	11.9	11.3	10.7	9.6	9.0	8.6	8.4	8.6	8.4	8.2
90°	35.8	36.3	31.2	26.1	21.0	16.0	12.1	9.4	6.6	3.8	1.1
92.5°	33.0	32.9	31.7	30.6	29.3	28.2	26.6	24.5	22.5	20.4	18.5
95°	66.3	66.3	65.8	65.4	64.9	64.5	63.0	60.7	58.5	56.2	53.9
97.5°	111.5	111.5	110.6	109.7	108.8	108.0	106.5	104.5	102.5	100.4	98.4
100°	142.9	142.9	142.2	141.5	140.9	140.2	138.9	137.1	135.3	133.4	131.5
102.5°	177.1	176.9	176.0	175.1	174.3	173.4	172.3	170.8	169.3	167.8	166.4
105°	228.4	227.8	227.4	226.9	226.5	226.0	225.4	224.8	224.1	223.4	222.7
107.5°	284.2	284.0	284.0	284.0	284.0	284.0	283.5	282.5	281.5	280.4	279.5
110°	322.2	322.2	322.2	322.2	322.2	322.2	321.5	320.0	318.7	317.3	315.9



TEST NUMBER: P331367-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	360.5	361.1	361.2	361.4	361.6	361.9	361.2	359.8	358.5	357.0	355.7
115°	418.2	418.5	418.9	419.4	419.8	420.3	419.8	418.5	417.1	415.7	414.3
117.5°	474.7	475.2	476.5	477.8	479.1	480.4	480.1	478.2	476.4	474.6	472.7
120°	511.7	511.7	513.5	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7
122.5°	550.9	551.4	552.8	554.0	555.4	556.6	556.2	553.9	551.7	549.6	547.3
125°	608.3	609.0	609.8	610.5	611.1	611.8	611.1	609.0	607.0	604.9	602.8
127.5°	664.1	664.9	665.8	666.6	667.4	668.3	667.4	664.8	662.2	659.5	656.9
130°	701.8	702.3	702.8	703.2	703.6	704.1	702.8	699.8	696.9	693.8	690.9
132.5°	739.4	740.4	740.3	740.2	740.1	740.0	738.8	736.3	733.9	731.5	729.0
135°	793.2	793.4	793.0	792.5	792.0	791.6	790.1	787.6	785.1	782.5	780.0
137.5°	845.4	845.6	845.0	844.5	843.8	843.2	841.9	839.8	837.8	835.7	833.6
140°	880.4	880.4	879.3	878.2	877.0	875.8	874.2	872.2	870.0	868.0	865.9
142.5°	912.1	912.0	911.2	910.3	909.5	908.7	907.3	905.3	903.2	901.2	899.1
145°	960.4	960.2	958.8	957.4	956.0	954.7	953.1	951.5	949.9	948.3	946.7
147.5°	1002.6	1002.0	1001.1	1000.2	999.3	998.4	996.9	995.0	993.0	991.1	989.2
150°	1029.2	1028.6	1027.6	1026.7	1025.8	1024.8	1023.7	1022.3	1020.9	1019.6	1018.2
152.5°	1056.0	1055.1	1054.0	1052.8	1051.8	1050.6	1049.4	1048.0	1046.6	1045.3	1043.8
155°	1089.8	1088.6	1088.0	1087.3	1086.5	1085.8	1085.2	1084.5	1083.8	1083.1	1082.4
157.5°	1120.9	1119.3	1118.8	1118.5	1118.0	1117.6	1117.2	1116.7	1116.2	1115.8	1115.4
160°	1139.7	1138.4	1138.1	1137.9	1137.6	1137.4	1137.1	1136.6	1136.1	1135.7	1135.2
162.5°	1156.5	1154.9	1154.7	1154.4	1154.2	1154.0	1153.9	1153.7	1153.6	1153.5	1153.4
165°	1178.3	1176.7	1176.7	1176.7	1176.7	1176.7	1176.8	1177.0	1177.2	1177.5	1177.7
167.5°	1196.3	1194.7	1194.7	1194.8	1194.8	1194.9	1195.2	1196.0	1196.6	1197.3	1198.0
170°	1206.2	1204.6	1204.9	1205.1	1205.3	1205.6	1206.0	1206.7	1207.4	1208.1	1208.8
172.5°	1213.7	1212.1	1212.3	1212.5	1212.8	1213.0	1213.4	1214.2	1214.9	1215.6	1216.2
175°	1221.8	1220.1	1220.7	1221.1	1221.6	1222.0	1222.6	1223.2	1224.0	1224.7	1225.4
177.5°	1226.0	1224.9	1225.3	1225.7	1226.0	1226.4	1226.9	1227.4	1228.0	1228.5	1229.0
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331367-940  
 CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1190.6	1192.5	1198.3	1204.1	1210.7	1212.5	1215.4	1212.8	1212.1	1219.1	1224.1
5°	1194.0	1202.2	1218.2	1232.7	1245.0	1253.7	1262.8	1266.4	1273.2	1282.7	1294.6
7.5°	1190.2	1206.1	1231.2	1252.3	1275.5	1292.2	1305.2	1316.3	1329.7	1347.8	1367.6
10°	1185.8	1207.2	1237.7	1263.6	1291.8	1313.2	1331.1	1348.3	1368.3	1393.4	1419.3
12.5°	1177.8	1203.2	1241.4	1272.0	1308.2	1329.3	1353.3	1390.5	1412.0	1446.9	1483.5
15°	1161.7	1189.9	1243.1	1280.9	1321.9	1362.0	1406.1	1441.6	1477.1	1497.6	1549.1
17.5°	1137.7	1179.2	1238.1	1282.2	1334.3	1397.4	1447.0	1487.2	1528.2	1561.5	1587.2
20°	1118.5	1163.5	1230.8	1283.7	1345.6	1413.4	1470.3	1511.3	1546.8	1574.6	1590.5
22.5°	1094.0	1150.8	1216.3	1278.2	1357.3	1424.3	1484.2	1516.4	1546.0	1559.6	1565.8
25°	1055.6	1123.9	1198.1	1273.6	1362.9	1433.9	1488.5	1508.1	1516.7	1503.5	1481.7
27.5°	1014.2	1090.3	1177.1	1265.1	1359.4	1427.7	1466.9	1463.7	1449.1	1406.4	1372.3
30°	983.2	1067.0	1160.3	1256.3	1351.0	1417.5	1440.3	1417.5	1384.3	1336.5	1287.8
32.5°	950.8	1037.5	1142.5	1243.9	1335.8	1394.2	1399.1	1359.9	1308.5	1254.2	1193.5
35°	901.8	995.5	1108.8	1216.3	1303.2	1340.2	1318.3	1249.1	1188.1	1113.9	1031.0
37.5°	846.3	949.9	1063.5	1175.8	1254.5	1264.2	1210.0	1137.1	1051.1	963.9	866.4
40°	804.8	914.5	1031.5	1144.9	1214.5	1204.4	1135.2	1055.2	952.7	846.2	755.6
42.5°	767.7	877.4	996.5	1107.7	1163.5	1136.0	1055.2	956.8	846.8	746.5	663.5
45°	703.3	816.2	938.2	1045.6	1077.5	1027.9	920.9	811.6	703.3	619.6	554.0
47.5°	640.9	752.4	873.3	967.7	978.9	912.2	795.3	682.9	589.8	521.6	475.3
50°	594.9	706.9	826.6	910.9	907.2	826.6	706.5	599.5	521.7	466.5	435.6
52.5°	553.8	659.6	774.5	851.1	831.9	744.0	629.3	534.3	470.3	427.2	399.2
55°	489.8	587.6	696.9	758.4	722.8	625.4	528.5	452.0	404.7	372.4	350.5
57.5°	426.2	518.0	611.5	649.4	610.2	520.2	439.3	383.9	348.3	324.4	310.1
60°	386.9	467.1	550.4	583.1	536.2	456.1	392.4	342.8	314.1	294.5	281.8
62.5°	347.6	419.4	497.9	515.8	472.9	405.1	348.7	307.5	283.8	266.4	254.5
65°	294.1	352.8	412.4	424.3	384.7	332.3	287.7	260.8	239.9	227.1	217.6
67.5°	241.2	288.3	330.6	340.1	305.4	269.1	236.9	213.5	199.3	188.7	180.7
70°	209.8	247.2	281.8	289.5	261.7	229.4	204.8	186.2	173.4	164.3	156.6
72.5°	176.7	207.9	236.6	241.8	219.1	194.5	174.2	159.6	148.3	142.5	135.1
75°	135.2	153.4	175.7	177.1	162.0	147.0	131.5	122.0	116.1	108.8	105.1
77.5°	95.4	109.7	122.4	124.9	116.0	105.8	97.1	89.6	84.5	81.2	77.8
80°	72.9	84.2	89.7	92.8	86.5	79.2	74.2	69.2	66.0	63.8	61.4
82.5°	52.1	59.1	64.2	66.6	63.2	58.9	53.8	51.0	48.5	46.6	45.8
85°	26.4	29.6	32.8	33.7	32.8	30.9	28.2	28.2	26.8	26.4	26.4
87.5°	9.9	11.9	12.4	14.1	14.1	15.2	16.1	16.8	17.5	17.0	16.5
90°	3.8	6.6	9.4	12.1	16.0	21.0	26.1	31.2	36.3	35.8	35.3
92.5°	20.4	22.5	24.5	26.6	28.2	29.3	30.6	31.7	32.9	33.0	33.1
95°	56.2	58.5	60.7	63.0	64.5	64.9	65.4	65.8	66.3	66.3	66.3
97.5°	100.4	102.5	104.5	106.5	108.0	108.8	109.7	110.6	111.5	111.5	111.5
100°	133.4	135.3	137.1	138.9	140.2	140.9	141.5	142.2	142.9	142.9	142.9
102.5°	167.8	169.3	170.8	172.3	173.4	174.3	175.1	176.0	176.9	177.1	177.3
105°	223.4	224.1	224.8	225.4	226.0	226.5	226.9	227.4	227.8	228.4	228.8
107.5°	280.4	281.5	282.5	283.5	284.0	284.0	284.0	284.0	284.0	284.2	284.4
110°	317.3	318.7	320.0	321.5	322.2	322.2	322.2	322.2	322.2	322.2	322.2





TEST NUMBER: P331367-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	357.0	358.5	359.8	361.2	361.9	361.6	361.4	361.2	361.1	360.5	360.0
115°	415.7	417.1	418.5	419.8	420.3	419.8	419.4	418.9	418.5	418.2	418.0
117.5°	474.6	476.4	478.2	480.1	480.4	479.1	477.8	476.5	475.2	474.7	474.1
120°	513.5	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7	511.7	511.7
122.5°	549.6	551.7	553.9	556.2	556.6	555.4	554.0	552.8	551.4	550.9	550.4
125°	604.9	607.0	609.0	611.1	611.8	611.1	610.5	609.8	609.0	608.3	607.7
127.5°	659.5	662.2	664.8	667.4	668.3	667.4	666.6	665.8	664.9	664.1	663.3
130°	693.8	696.9	699.8	702.8	704.1	703.6	703.2	702.8	702.3	701.8	701.3
132.5°	731.5	733.9	736.3	738.8	740.0	740.1	740.2	740.3	740.4	739.4	738.3
135°	782.5	785.1	787.6	790.1	791.6	792.0	792.5	793.0	793.4	793.2	793.0
137.5°	835.7	837.8	839.8	841.9	843.2	843.8	844.5	845.0	845.6	845.4	845.3
140°	868.0	870.0	872.2	874.2	875.8	877.0	878.2	879.3	880.4	880.4	880.4
142.5°	901.2	903.2	905.3	907.3	908.7	909.5	910.3	911.2	912.0	912.1	912.3
145°	948.3	949.9	951.5	953.1	954.7	956.0	957.4	958.8	960.2	960.4	960.6
147.5°	991.1	993.0	995.0	996.9	998.4	999.3	1000.2	1001.1	1002.0	1002.6	1003.1
150°	1019.6	1020.9	1022.3	1023.7	1024.8	1025.8	1026.7	1027.6	1028.6	1029.2	1029.9
152.5°	1045.3	1046.6	1048.0	1049.4	1050.6	1051.8	1052.8	1054.0	1055.1	1056.0	1056.9
155°	1083.1	1083.8	1084.5	1085.2	1085.8	1086.5	1087.3	1088.0	1088.6	1089.8	1090.9
157.5°	1115.8	1116.2	1116.7	1117.2	1117.6	1118.0	1118.5	1118.8	1119.3	1120.9	1122.4
160°	1135.7	1136.1	1136.6	1137.1	1137.4	1137.6	1137.9	1138.1	1138.4	1139.7	1141.1
162.5°	1153.5	1153.6	1153.7	1153.9	1154.0	1154.2	1154.4	1154.7	1154.9	1156.5	1158.1
165°	1177.5	1177.2	1177.0	1176.8	1176.7	1176.7	1176.7	1176.7	1176.7	1178.3	1179.9
167.5°	1197.3	1196.6	1196.0	1195.2	1194.9	1194.8	1194.8	1194.7	1194.7	1196.3	1197.9
170°	1208.1	1207.4	1206.7	1206.0	1205.6	1205.3	1205.1	1204.9	1204.6	1206.2	1207.8
172.5°	1215.6	1214.9	1214.2	1213.4	1213.0	1212.8	1212.5	1212.3	1212.1	1213.7	1215.3
175°	1224.7	1224.0	1223.2	1222.6	1222.0	1221.6	1221.1	1220.7	1220.1	1221.8	1223.4
177.5°	1228.5	1228.0	1227.4	1226.9	1226.4	1226.0	1225.7	1225.3	1224.9	1226.0	1227.2
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331367-940  
 CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1228.5	1233.6	1233.6	1234.3	1240.2	1239.4	1239.0
5°	1307.3	1315.1	1316.0	1324.2	1329.6	1327.8	1322.9
7.5°	1381.7	1396.2	1407.0	1413.1	1420.3	1424.8	1422.8
10°	1440.7	1461.7	1474.4	1483.1	1493.5	1501.3	1498.5
12.5°	1494.2	1519.2	1536.7	1551.5	1552.9	1562.8	1556.0
15°	1577.7	1604.1	1606.9	1617.8	1626.5	1625.5	1625.9
17.5°	1605.3	1613.8	1615.5	1615.8	1615.9	1612.7	1605.8
20°	1595.4	1592.3	1584.6	1578.7	1568.2	1566.8	1557.7
22.5°	1548.9	1538.7	1519.4	1506.5	1490.2	1485.9	1483.5
25°	1457.1	1434.8	1403.8	1374.2	1366.1	1350.1	1354.7
27.5°	1331.2	1296.5	1262.9	1238.9	1217.1	1193.3	1200.1
30°	1242.7	1203.5	1156.2	1119.8	1096.6	1073.8	1069.7
32.5°	1137.1	1079.8	1026.9	994.9	959.3	944.9	929.2
35°	955.0	899.0	846.7	801.6	775.7	755.6	737.4
37.5°	791.2	726.7	684.6	648.0	629.3	617.8	620.7
40°	689.6	633.2	602.3	574.4	557.1	548.9	550.8
42.5°	607.3	565.1	539.6	520.6	508.4	503.8	502.7
45°	513.9	490.3	469.3	458.4	452.5	447.5	444.3
47.5°	450.2	430.9	419.1	412.6	407.4	402.3	402.3
50°	412.0	399.2	391.0	384.1	380.1	376.5	379.6
52.5°	382.8	371.1	363.0	356.9	355.3	352.0	352.0
55°	339.6	330.5	324.6	319.1	316.4	314.5	312.3
57.5°	300.2	291.6	286.1	282.7	277.5	275.6	274.9
60°	272.2	265.4	259.9	255.4	253.1	249.4	249.4
62.5°	246.4	239.5	234.4	231.0	227.2	225.8	226.1
65°	208.9	203.5	198.5	194.8	193.9	191.2	192.1
67.5°	174.5	170.9	165.6	163.6	161.8	160.4	159.3
70°	151.6	147.9	145.2	142.5	141.1	141.1	141.1
72.5°	132.2	127.9	126.3	122.8	123.6	122.2	120.7
75°	102.5	99.7	98.4	96.9	94.7	94.7	94.7
77.5°	75.3	74.5	72.9	71.4	70.9	70.4	70.6
80°	58.2	57.8	56.9	56.9	56.0	55.6	54.7
82.5°	44.8	43.6	43.1	42.7	42.5	42.4	42.3
85°	25.5	24.6	24.6	25.1	24.2	24.2	24.6
87.5°	16.8	16.7	16.3	16.4	16.8	16.5	16.5
90°	34.9	34.4	34.3	34.5	34.8	35.0	35.2
92.5°	33.2	33.3	33.3	33.4	33.4	33.5	33.5
95°	66.3	66.3	66.1	65.6	65.2	64.6	64.2
97.5°	111.5	111.5	111.5	111.4	111.4	111.3	111.3
100°	142.9	142.9	142.9	142.6	142.4	142.1	141.9
102.5°	177.5	177.6	177.6	177.4	177.2	176.9	176.7
105°	229.3	229.7	230.0	230.0	230.0	230.0	230.0
107.5°	284.5	284.7	284.3	283.3	282.2	281.2	280.1
110°	322.2	322.2	321.8	321.1	320.4	319.7	319.1



TEST NUMBER: P331367-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	359.4	358.9	358.4	357.8	357.3	356.9	356.3
115°	417.8	417.5	417.1	416.4	415.7	415.0	414.3
117.5°	473.6	473.1	472.4	471.7	471.0	470.3	469.7
120°	511.7	511.7	511.3	510.7	510.0	509.3	508.5
122.5°	549.8	549.2	548.8	548.2	547.7	547.2	546.7
125°	607.0	606.3	605.8	605.6	605.4	605.1	604.9
127.5°	662.5	661.6	660.8	660.1	659.4	658.7	657.9
130°	700.9	700.4	699.7	698.8	697.9	697.0	696.1
132.5°	737.4	736.4	735.5	734.8	734.0	733.3	732.5
135°	792.7	792.5	792.0	791.3	790.7	790.0	789.3
137.5°	845.1	844.9	844.4	843.4	842.5	841.6	840.6
140°	880.4	880.4	879.9	879.0	878.2	877.2	876.3
142.5°	912.5	912.7	912.3	911.3	910.4	909.5	908.6
145°	960.9	961.1	960.7	959.8	958.9	958.0	957.1
147.5°	1003.5	1004.1	1003.9	1003.0	1002.1	1001.2	1000.4
150°	1030.6	1031.4	1031.4	1030.6	1029.9	1029.2	1028.6
152.5°	1057.7	1058.5	1058.5	1057.7	1056.9	1056.0	1055.1
155°	1092.1	1093.2	1093.4	1092.8	1092.1	1091.4	1090.7
157.5°	1124.0	1125.5	1125.8	1124.6	1123.6	1122.5	1121.3
160°	1142.5	1143.9	1144.1	1143.2	1142.3	1141.3	1140.4
162.5°	1159.6	1161.2	1161.4	1160.3	1159.2	1158.1	1157.0
165°	1181.5	1183.1	1183.3	1182.2	1181.1	1179.9	1178.8
167.5°	1199.5	1201.1	1201.3	1200.2	1198.9	1197.7	1196.6
170°	1209.4	1211.0	1211.2	1209.8	1208.4	1207.0	1205.7
172.5°	1216.9	1218.5	1218.6	1217.3	1215.8	1214.5	1213.1
175°	1225.0	1226.6	1226.7	1225.4	1224.0	1222.6	1221.2
177.5°	1228.2	1229.3	1229.3	1228.2	1227.2	1226.0	1224.9
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4

(END OF REPORT)