

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331368-940

Luminaire Tested: **SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331368-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6366.3 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331368-940
CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41				41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41				35	
2	88	81	75	70	80	74	69	65	61	58	54	49	47	45	38	37	35				30	
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	30				26	
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27				23	
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23				20	
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21				18	
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19				16	
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17				14	
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15				13	
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19125	19125	19125	19125
5°	21441	19248	17057	19248
10°	24568	19090	14762	19090
15°	27178	18740	13041	18740
20°	26764	18364	11888	18364
25°	24134	17865	11158	17865
30°	19943	17066	10625	17066
35°	14534	16232	10247	16232
40°	11609	15247	10037	15247
45°	10145	14104	9750	14104
50°	9535	12999	9560	12999
55°	8791	11879	9303	11879
60°	8054	10685	8909	10685
65°	7339	9616	8520	9616
70°	6661	8573	7950	8573
75°	5908	7411	7043	7411
80°	5086	6137	5672	6137
85°	4557	4557	3372	4557



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	1.8
10°-20°	327.9	5.2
20°-30°	475.9	7.5
30°-40°	502.2	7.9
40°-50°	444.7	7.0
50°-60°	354.9	5.6
60°-70°	241.2	3.8
70°-80°	123.7	1.9
80°-90°	34.7	0.5
90°-100°	215.4	3.4
100°-110°	730.9	11.5
110°-120°	776.4	12.2
120°-130°	639.2	10.0
130°-140°	513.3	8.1
140°-150°	387.9	6.1
150°-160°	272.6	4.3
160°-170°	160.5	2.5
170°-180°	52.2	0.8
0°-30°	916.7	14.4
0°-40°	1418.9	22.3
0°-60°	2218.4	34.8
0°-90°	2617.9	41.1
90°-120°	1722.7	27.1
90°-150°	3263.0	51.3
90°-180°	3748.0	58.9
0°-180°	6366.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1184	1184	1184	1184	1184	
5°	1323	1188	1052	1188	1323	132
15°	1626	1121	780	1121	1626	449
25°	1355	1003	626	1003	1355	612
35°	737	824	520	824	737	480
45°	444	618	427	618	444	349
55°	312	422	330	422	312	280
65°	192	252	223	252	192	191
75°	95	119	113	119	95	101
85°	25	25	18	25	25	28
90°	34	1	34	1	34	19
95°	118	36	118	36	118	154
105°	1167	126	1167	126	1167	1130
115°	1536	223	1536	223	1536	1504
125°	1246	311	1246	311	1246	1126
135°	1033	365	1033	365	1033	802
145°	825	416	825	416	825	524
155°	693	473	693	473	693	323
165°	608	516	608	516	608	174
175°	548	538	548	538	548	53
180°	539	539	539	539	539	



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1239.0	1239.4	1240.2	1234.3	1233.6	1233.6	1228.5	1224.1	1219.1	1212.1	1212.8
5°	1322.9	1327.8	1329.6	1324.2	1316.0	1315.1	1307.3	1294.6	1282.7	1273.2	1266.4
7.5°	1422.8	1424.8	1420.3	1413.1	1407.0	1396.2	1381.7	1367.6	1347.8	1329.7	1316.3
10°	1498.5	1501.3	1493.5	1483.1	1474.4	1461.7	1440.7	1419.3	1393.4	1368.3	1348.3
12.5°	1556.0	1562.8	1552.9	1551.5	1536.7	1519.2	1494.2	1483.5	1446.9	1412.0	1390.5
15°	1625.9	1625.5	1626.5	1617.8	1606.9	1604.1	1577.7	1549.1	1497.6	1477.1	1441.6
17.5°	1605.8	1612.7	1615.9	1615.8	1615.5	1613.8	1605.3	1587.2	1561.5	1528.2	1487.2
20°	1557.7	1566.8	1568.2	1578.7	1584.6	1592.3	1595.4	1590.5	1574.6	1546.8	1511.3
22.5°	1483.5	1485.9	1490.2	1506.5	1519.4	1538.7	1548.9	1565.8	1559.6	1546.0	1516.4
25°	1354.7	1350.1	1366.1	1374.2	1403.8	1434.8	1457.1	1481.7	1503.5	1516.7	1508.1
27.5°	1200.1	1193.3	1217.1	1238.9	1262.9	1296.5	1331.2	1372.3	1406.4	1449.1	1463.7
30°	1069.7	1073.8	1096.6	1119.8	1156.2	1203.5	1242.7	1287.8	1336.5	1384.3	1417.5
32.5°	929.2	944.9	959.3	994.9	1026.9	1079.8	1137.1	1193.5	1254.2	1308.5	1359.9
35°	737.4	755.6	775.7	801.6	846.7	899.0	955.0	1031.0	1113.9	1188.1	1249.1
37.5°	620.7	617.8	629.3	648.0	684.6	726.7	791.2	866.4	963.9	1051.1	1137.1
40°	550.8	548.9	557.1	574.4	602.3	633.2	689.6	755.6	846.2	952.7	1055.2
42.5°	502.7	503.8	508.4	520.6	539.6	565.1	607.3	663.5	746.5	846.8	956.8
45°	444.3	447.5	452.5	458.4	469.3	490.3	513.9	554.0	619.6	703.3	811.6
47.5°	402.3	402.3	407.4	412.6	419.1	430.9	450.2	475.3	521.6	589.8	682.9
50°	379.6	376.5	380.1	384.1	391.0	399.2	412.0	435.6	466.5	521.7	599.5
52.5°	352.0	352.0	355.3	356.9	363.0	371.1	382.8	399.2	427.2	470.3	534.3
55°	312.3	314.5	316.4	319.1	324.6	330.5	339.6	350.5	372.4	404.7	452.0
57.5°	274.9	275.6	277.5	282.7	286.1	291.6	300.2	310.1	324.4	348.3	383.9
60°	249.4	249.4	253.1	255.4	259.9	265.4	272.2	281.8	294.5	314.1	342.8
62.5°	226.1	225.8	227.2	231.0	234.4	239.5	246.4	254.5	266.4	283.8	307.5
65°	192.1	191.2	193.9	194.8	198.5	203.5	208.9	217.6	227.1	239.9	260.8
67.5°	159.3	160.4	161.8	163.6	165.6	170.9	174.5	180.7	188.7	199.3	213.5
70°	141.1	141.1	141.1	142.5	145.2	147.9	151.6	156.6	164.3	173.4	186.2
72.5°	120.7	122.2	123.6	122.8	126.3	127.9	132.2	135.1	142.5	148.3	159.6
75°	94.7	94.7	94.7	96.9	98.4	99.7	102.5	105.1	108.8	116.1	122.0
77.5°	70.6	70.4	70.9	71.4	72.9	74.5	75.3	77.8	81.2	84.5	89.6
80°	54.7	55.6	56.0	56.9	56.9	57.8	58.2	61.4	63.8	66.0	69.2
82.5°	42.3	42.4	42.5	42.7	43.1	43.6	44.8	45.8	46.6	48.5	51.0
85°	24.6	24.2	24.2	25.1	24.6	24.6	25.5	26.4	26.4	26.8	28.2
87.5°	16.3	16.3	16.7	16.3	16.3	16.5	16.1	16.1	16.7	17.2	17.4
90°	34.2	34.2	34.2	34.2	34.2	33.2	31.1	33.2	34.2	35.2	34.2
92.5°	57.4	59.0	58.2	61.5	62.3	68.8	77.5	90.3	113.8	134.6	132.8
95°	118.1	117.1	120.2	128.4	141.9	164.7	208.2	271.4	355.3	406.1	359.4
97.5°	232.5	241.1	256.3	281.8	331.3	406.1	518.2	633.3	727.2	693.2	522.1
100°	370.9	389.5	419.5	464.0	550.0	675.4	817.3	945.7	967.5	818.3	563.5
102.5°	652.6	677.9	715.4	791.4	884.8	1017.6	1121.4	1150.5	1057.0	822.5	547.8
105°	1167.4	1182.0	1226.5	1290.7	1355.0	1389.1	1375.6	1258.6	1043.1	767.6	516.9
107.5°	1491.2	1510.5	1519.4	1523.0	1514.8	1464.7	1357.0	1180.7	952.2	708.7	501.6
110°	1589.0	1590.1	1580.7	1561.0	1516.5	1431.6	1299.0	1113.6	895.0	680.6	498.3



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1587.3	1581.8	1564.1	1531.2	1469.3	1371.9	1230.2	1052.2	855.2	662.4	499.1
115°	1536.2	1526.9	1499.9	1452.3	1378.8	1272.0	1136.4	976.9	805.9	642.2	503.5
117.5°	1444.8	1437.0	1408.5	1358.3	1283.3	1183.2	1060.2	920.1	774.8	632.5	510.9
120°	1386.0	1375.6	1345.6	1296.9	1224.4	1130.2	1020.3	891.9	758.2	626.7	515.9
122.5°	1324.6	1316.0	1289.2	1241.4	1176.3	1091.2	987.2	869.5	744.1	623.4	521.7
125°	1246.2	1237.9	1212.0	1172.6	1112.5	1034.8	943.7	837.0	724.1	617.4	530.4
127.5°	1177.4	1170.7	1148.3	1111.5	1059.1	987.4	901.4	804.9	705.4	613.9	539.3
130°	1138.4	1130.2	1109.5	1074.2	1023.4	955.1	873.3	784.2	693.0	612.2	545.9
132.5°	1097.8	1090.4	1071.3	1036.1	986.1	921.9	846.8	764.3	683.1	611.4	552.5
135°	1032.8	1028.6	1010.0	975.8	931.2	873.3	804.9	736.5	669.1	610.1	560.4
137.5°	968.9	962.8	946.4	916.9	876.4	825.8	771.5	714.3	659.4	609.9	567.5
140°	925.1	918.8	903.3	876.4	843.2	797.6	750.0	700.3	653.6	609.1	570.8
142.5°	881.1	879.9	866.0	841.5	810.0	772.0	730.9	688.7	647.8	609.1	573.3
145°	824.6	821.4	811.1	793.4	768.7	738.6	706.5	672.3	640.2	607.0	576.0
147.5°	777.1	775.3	768.2	754.1	733.6	711.7	686.6	659.7	632.3	603.3	576.8
150°	748.9	747.9	741.7	729.2	713.7	695.1	673.3	650.5	625.6	600.8	576.0
152.5°	724.9	724.7	720.1	709.4	697.1	681.0	662.5	641.4	619.8	596.6	574.3
155°	693.0	695.1	690.9	683.7	672.3	660.8	645.3	628.7	609.1	589.4	571.8
157.5°	665.8	665.8	664.0	658.0	649.9	641.0	627.9	614.0	599.0	581.9	567.0
160°	648.5	648.5	647.4	642.2	635.0	627.8	616.4	604.9	591.5	577.0	564.5
162.5°	631.9	632.7	631.7	628.1	620.9	615.3	605.6	595.8	584.9	572.8	562.0
165°	608.1	609.1	609.1	604.9	600.8	596.6	589.4	582.2	573.9	564.5	557.3
167.5°	586.1	587.4	587.5	585.2	583.4	579.7	574.7	569.1	563.1	557.3	552.5
170°	572.8	574.9	576.0	572.8	571.8	569.7	565.6	562.5	557.3	553.1	550.0
172.5°	562.0	563.3	564.4	562.9	561.9	560.6	557.3	555.0	551.5	548.2	546.7
175°	548.0	550.0	551.1	550.0	550.0	549.0	548.0	547.0	543.9	542.8	541.8
177.5°	539.5	541.2	542.0	542.0	542.0	542.0	541.2	541.2	539.5	538.7	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1215.4	1212.5	1210.7	1204.1	1198.3	1192.5	1190.6	1191.3	1183.4	1175.7	1172.4
5°	1262.8	1253.7	1245.0	1232.7	1218.2	1202.2	1194.0	1187.6	1171.7	1154.4	1144.4
7.5°	1305.2	1292.2	1275.5	1252.3	1231.2	1206.1	1190.2	1176.1	1152.7	1128.4	1113.4
10°	1331.1	1313.2	1291.8	1263.6	1237.7	1207.2	1185.8	1164.4	1137.1	1108.0	1089.8
12.5°	1353.3	1329.3	1308.2	1272.0	1241.4	1203.2	1177.8	1147.6	1118.9	1084.3	1066.5
15°	1406.1	1362.0	1321.9	1280.9	1243.1	1189.9	1161.7	1121.1	1083.3	1040.6	1020.1
17.5°	1447.0	1397.4	1334.3	1282.2	1238.1	1179.2	1137.7	1089.2	1044.6	995.6	967.8
20°	1470.3	1413.4	1345.6	1283.7	1230.8	1163.5	1118.5	1068.8	1016.5	961.4	931.3
22.5°	1484.2	1424.3	1357.3	1278.2	1216.3	1150.8	1094.0	1039.6	986.6	927.2	895.6
25°	1488.5	1433.9	1362.9	1273.6	1198.1	1123.9	1055.6	1002.8	938.6	883.1	837.1
27.5°	1466.9	1427.7	1359.4	1265.1	1177.1	1090.3	1014.2	954.4	886.6	826.3	780.2
30°	1440.3	1417.5	1351.0	1256.3	1160.3	1067.0	983.2	915.4	848.0	787.0	739.7
32.5°	1399.1	1394.2	1335.8	1243.9	1142.5	1037.5	950.8	882.3	807.6	747.7	702.6
35°	1318.3	1340.2	1303.2	1216.3	1108.8	995.5	901.8	823.5	746.1	688.8	646.4
37.5°	1210.0	1264.2	1254.5	1175.8	1063.5	949.9	846.3	764.5	690.7	632.8	591.3
40°	1135.2	1204.4	1214.5	1144.9	1031.5	914.5	804.8	723.4	651.4	598.6	556.7
42.5°	1055.2	1136.0	1163.5	1107.7	996.5	877.4	767.7	683.2	612.1	560.7	523.6
45°	920.9	1027.9	1077.5	1045.6	938.2	816.2	703.3	617.7	553.0	504.8	476.2
47.5°	795.3	912.2	978.9	967.7	873.3	752.4	640.9	558.7	495.8	457.3	431.6
50°	706.5	826.6	907.2	910.9	826.6	706.9	594.9	517.5	459.8	423.8	402.9
52.5°	629.3	744.0	831.9	851.1	774.5	659.6	553.8	476.8	425.9	392.8	374.1
55°	528.5	625.4	722.8	758.4	696.9	587.6	489.8	422.0	374.2	351.4	335.0
57.5°	439.3	520.2	610.2	649.4	611.5	518.0	426.2	367.4	328.6	308.6	296.0
60°	392.4	456.1	536.2	583.1	550.4	467.1	386.9	330.9	299.1	281.3	269.5
62.5°	348.7	405.1	472.9	515.8	497.9	419.4	347.6	298.2	270.6	254.0	245.5
65°	287.7	332.3	384.7	424.3	412.4	352.8	294.1	251.7	229.9	216.7	209.8
67.5°	236.9	269.1	305.4	340.1	330.6	288.3	241.2	208.2	191.9	180.6	176.5
70°	204.8	229.4	261.7	289.5	281.8	247.2	209.8	181.6	167.6	157.9	153.8
72.5°	174.2	194.5	219.1	241.8	236.6	207.9	176.7	155.4	144.5	135.7	132.3
75°	131.5	147.0	162.0	177.1	175.7	153.4	135.2	118.8	110.1	103.3	101.9
77.5°	97.1	105.8	116.0	124.9	122.4	109.7	95.4	86.1	79.6	75.1	74.4
80°	74.2	79.2	86.5	92.8	89.7	84.2	72.9	66.0	61.4	56.9	55.1
82.5°	53.8	58.9	63.2	66.6	64.2	59.1	52.1	47.4	44.7	41.6	40.8
85°	28.2	30.9	32.8	33.7	32.8	29.6	26.4	24.6	22.3	21.0	20.5
87.5°	16.5	15.1	14.0	14.2	12.7	12.2	9.9	8.2	8.5	8.9	8.6
90°	28.0	20.7	15.5	12.4	10.3	8.3	4.1	1.1	4.1	8.3	10.3
92.5°	103.3	70.4	47.0	37.3	30.2	25.7	18.2	12.7	18.2	25.7	30.2
95°	239.2	149.2	101.5	76.7	60.1	50.7	40.4	36.3	40.4	50.7	60.1
97.5°	322.4	196.8	137.0	108.8	89.7	75.6	64.6	59.0	64.6	75.6	89.7
100°	339.7	213.4	158.5	129.5	108.8	92.2	82.8	79.7	82.8	92.2	108.8
102.5°	340.6	228.3	177.5	148.6	127.0	110.4	101.1	98.8	101.1	110.4	127.0
105°	346.0	253.8	205.1	176.1	153.3	137.8	130.5	126.4	130.5	137.8	153.3
107.5°	360.3	279.9	232.6	203.5	180.8	166.6	159.5	156.2	159.5	166.6	180.8
110°	371.8	297.3	251.7	221.7	199.9	186.5	180.2	176.1	180.2	186.5	199.9



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	384.3	313.9	269.9	239.1	218.1	205.5	198.5	194.3	198.5	205.5	218.1
115°	403.0	339.7	295.2	267.2	246.6	234.1	227.9	222.7	227.9	234.1	246.6
117.5°	422.8	363.6	322.4	293.4	273.5	262.5	256.3	252.2	256.3	262.5	273.5
120°	436.1	380.1	339.7	310.8	290.1	280.7	274.5	270.4	274.5	280.7	290.1
122.5°	447.7	395.9	358.0	328.1	307.5	297.3	291.1	287.8	291.1	297.3	307.5
125°	466.2	419.5	382.3	353.2	332.5	320.1	313.9	310.8	313.9	320.1	332.5
127.5°	483.3	441.5	405.2	375.4	355.5	341.9	333.1	329.0	333.1	341.9	355.5
130°	494.1	454.8	418.5	389.5	368.8	354.3	343.9	339.7	343.9	354.3	368.8
132.5°	504.9	466.4	431.8	402.8	381.2	365.9	354.7	349.7	354.7	365.9	381.2
135°	519.0	482.7	449.6	420.5	396.7	381.2	368.8	364.6	368.8	381.2	396.7
137.5°	529.8	496.0	463.2	436.3	412.7	396.1	383.7	378.7	383.7	396.1	412.7
140°	535.6	503.5	472.3	445.4	422.7	406.1	393.6	389.5	393.6	406.1	422.7
142.5°	540.6	509.3	479.0	453.7	431.8	415.2	403.6	400.3	403.6	415.2	431.8
145°	547.0	517.9	490.0	467.2	446.5	431.0	420.5	416.4	420.5	431.0	446.5
147.5°	550.5	525.0	498.6	478.4	461.2	446.8	436.9	433.8	436.9	446.8	461.2
150°	552.1	528.3	504.4	485.8	470.3	456.8	448.5	445.4	448.5	456.8	470.3
152.5°	552.9	531.6	510.2	493.3	478.6	466.7	458.5	457.0	458.5	466.7	478.6
155°	554.2	536.5	519.0	503.5	492.0	480.6	474.4	473.4	474.4	480.6	492.0
157.5°	554.2	540.1	525.2	512.1	503.0	493.1	488.1	487.1	488.1	493.1	503.0
160°	554.2	541.8	529.3	517.9	509.6	501.3	497.2	496.1	497.2	501.3	509.6
162.5°	553.4	542.6	531.8	522.9	515.4	508.8	504.7	505.3	504.7	508.8	515.4
165°	551.1	543.9	534.5	528.3	523.1	516.9	514.9	515.9	514.9	516.9	523.1
167.5°	549.7	543.6	536.8	532.9	529.1	525.2	523.3	524.6	523.3	525.2	529.1
170°	548.0	542.8	537.6	534.5	532.4	529.3	528.3	530.4	528.3	529.3	532.4
172.5°	545.5	542.0	538.4	536.2	534.9	531.8	532.4	533.7	532.4	531.8	534.9
175°	542.8	540.7	538.7	537.6	537.6	535.6	536.5	537.6	536.5	535.6	537.6
177.5°	541.2	539.5	538.7	538.7	538.7	537.0	537.8	539.5	537.8	537.0	538.7
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1168.8	1166.6	1159.0	1154.9	1148.3	1142.2	1138.2	1140.1	1141.5	1140.8	1139.6
5°	1135.2	1126.6	1113.4	1102.1	1093.9	1078.8	1072.5	1069.3	1066.6	1063.4	1060.2
7.5°	1095.4	1081.7	1062.8	1046.6	1031.3	1012.6	1002.0	995.6	989.1	981.9	975.5
10°	1067.0	1047.8	1027.9	1005.0	986.9	970.0	955.0	945.0	935.9	927.3	920.9
12.5°	1037.1	1015.1	990.3	959.2	939.1	915.1	912.8	895.1	880.9	875.6	868.1
15°	989.6	958.7	927.3	890.4	874.4	852.6	838.9	825.3	813.0	804.3	802.1
17.5°	935.6	895.5	864.3	837.9	811.7	789.3	776.8	765.8	755.7	744.1	742.6
20°	894.5	859.9	825.7	802.5	775.7	752.9	737.4	726.5	717.8	711.1	705.1
22.5°	855.5	817.6	786.4	761.0	734.5	716.1	703.9	693.4	686.2	678.6	673.1
25°	793.0	763.4	729.2	700.5	678.7	666.9	656.8	647.7	643.2	638.2	631.9
27.5°	738.2	705.3	673.4	651.2	632.0	621.5	614.4	608.2	604.0	601.0	597.4
30°	699.6	666.4	641.4	619.6	603.6	593.2	588.6	585.0	580.0	578.1	576.3
32.5°	662.5	632.6	611.2	592.2	577.0	570.2	566.0	562.8	558.8	557.0	553.3
35°	609.9	585.0	564.0	553.5	541.3	535.3	532.2	527.5	524.0	522.1	521.7
37.5°	560.5	538.8	525.0	511.6	506.4	502.7	498.4	495.3	494.2	493.9	493.5
40°	528.5	510.8	498.5	487.5	485.3	479.7	476.2	473.4	473.4	473.9	473.4
42.5°	499.4	483.4	472.6	463.2	460.5	457.2	453.5	453.3	454.1	455.7	454.1
45°	455.2	443.8	436.0	431.5	426.5	423.3	422.8	424.3	424.7	425.2	426.5
47.5°	414.6	407.1	400.0	395.0	392.8	392.3	391.7	394.1	396.3	397.1	399.2
50°	390.6	381.9	376.0	372.8	371.0	370.1	371.0	373.7	375.5	377.8	379.2
52.5°	363.6	357.5	353.4	351.0	350.3	350.8	351.0	354.1	357.0	357.8	358.5
55°	326.4	321.8	320.9	316.8	318.6	318.2	320.5	322.3	325.0	327.7	328.2
57.5°	289.3	285.6	283.1	283.5	284.0	286.1	287.9	291.1	294.1	296.9	297.2
60°	264.5	262.6	261.3	261.3	262.2	264.9	267.2	270.4	272.2	274.0	275.4
62.5°	241.9	240.0	238.7	239.4	241.8	243.4	246.1	247.8	249.6	251.5	252.1
65°	206.2	205.3	206.7	207.6	208.0	210.3	213.5	214.8	216.7	217.6	220.8
67.5°	173.3	173.5	173.3	174.6	177.3	177.8	180.8	184.0	184.3	186.1	188.2
70°	151.1	152.0	152.9	153.8	156.1	157.0	159.3	160.7	162.5	163.9	165.2
72.5°	130.7	130.9	131.8	131.6	133.6	135.5	137.5	138.8	140.6	142.4	143.7
75°	100.6	100.6	101.5	101.9	104.2	106.6	106.0	107.0	108.8	110.6	111.6
77.5°	73.5	72.5	73.5	73.9	74.6	76.6	77.0	78.2	80.3	79.6	80.7
80°	56.0	54.7	56.0	56.4	56.4	58.8	58.8	59.7	61.0	59.7	61.0
82.5°	39.9	39.3	40.3	40.4	41.1	41.2	42.0	42.2	43.5	42.9	43.5
85°	20.1	19.6	20.1	19.6	20.1	20.5	20.5	20.1	20.1	21.0	19.6
87.5°	8.6	8.9	9.6	11.1	11.9	11.8	11.2	11.0	10.6	10.3	10.5
90°	12.4	15.5	20.7	28.0	34.2	35.2	34.2	33.2	31.1	33.2	34.2
92.5°	37.3	47.0	70.4	103.3	132.8	134.6	113.8	90.3	77.5	68.8	62.3
95°	76.7	101.5	149.2	239.2	359.4	406.1	355.3	271.4	208.2	164.7	141.9
97.5°	108.8	137.0	196.8	322.4	522.1	693.2	727.2	633.3	518.2	406.1	331.3
100°	129.5	158.5	213.4	339.7	563.5	818.3	967.5	945.7	817.3	675.4	550.0
102.5°	148.6	177.5	228.3	340.6	547.8	822.5	1057.0	1150.5	1121.4	1017.6	884.8
105°	176.1	205.1	253.8	346.0	516.9	767.6	1043.1	1258.6	1375.6	1389.1	1355.0
107.5°	203.5	232.6	279.9	360.3	501.6	708.7	952.2	1180.7	1357.0	1464.7	1514.8
110°	221.7	251.7	297.3	371.8	498.3	680.6	895.0	1113.6	1299.0	1431.6	1516.5



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	239.1	269.9	313.9	384.3	499.1	662.4	855.2	1052.2	1230.2	1371.9	1469.3
115°	267.2	295.2	339.7	403.0	503.5	642.2	805.9	976.9	1136.4	1272.0	1378.8
117.5°	293.4	322.4	363.6	422.8	510.9	632.5	774.8	920.1	1060.2	1183.2	1283.3
120°	310.8	339.7	380.1	436.1	515.9	626.7	758.2	891.9	1020.3	1130.2	1224.4
122.5°	328.1	358.0	395.9	447.7	521.7	623.4	744.1	869.5	987.2	1091.2	1176.3
125°	353.2	382.3	419.5	466.2	530.4	617.4	724.1	837.0	943.7	1034.8	1112.5
127.5°	375.4	405.2	441.5	483.3	539.3	613.9	705.4	804.9	901.4	987.4	1059.1
130°	389.5	418.5	454.8	494.1	545.9	612.2	693.0	784.2	873.3	955.1	1023.4
132.5°	402.8	431.8	466.4	504.9	552.5	611.4	683.1	764.3	846.8	921.9	986.1
135°	420.5	449.6	482.7	519.0	560.4	610.1	669.1	736.5	804.9	873.3	931.2
137.5°	436.3	463.2	496.0	529.8	567.5	609.9	659.4	714.3	771.5	825.8	876.4
140°	445.4	472.3	503.5	535.6	570.8	609.1	653.6	700.3	750.0	797.6	843.2
142.5°	453.7	479.0	509.3	540.6	573.3	609.1	647.8	688.7	730.9	772.0	810.0
145°	467.2	490.0	517.9	547.0	576.0	607.0	640.2	672.3	706.5	738.6	768.7
147.5°	478.4	498.6	525.0	550.5	576.8	603.3	632.3	659.7	686.6	711.7	733.6
150°	485.8	504.4	528.3	552.1	576.0	600.8	625.6	650.5	673.3	695.1	713.7
152.5°	493.3	510.2	531.6	552.9	574.3	596.6	619.8	641.4	662.5	681.0	697.1
155°	503.5	519.0	536.5	554.2	571.8	589.4	609.1	628.7	645.3	660.8	672.3
157.5°	512.1	525.2	540.1	554.2	567.0	581.9	599.0	614.0	627.9	641.0	649.9
160°	517.9	529.3	541.8	554.2	564.5	577.0	591.5	604.9	616.4	627.8	635.0
162.5°	522.9	531.8	542.6	553.4	562.0	572.8	584.9	595.8	605.6	615.3	620.9
165°	528.3	534.5	543.9	551.1	557.3	564.5	573.9	582.2	589.4	596.6	600.8
167.5°	532.9	536.8	543.6	549.7	552.5	557.3	563.1	569.1	574.7	579.7	583.4
170°	534.5	537.6	542.8	548.0	550.0	553.1	557.3	562.5	565.6	569.7	571.8
172.5°	536.2	538.4	542.0	545.5	546.7	548.2	551.5	555.0	557.3	560.6	561.9
175°	537.6	538.7	540.7	542.8	541.8	542.8	543.9	547.0	548.0	549.0	550.0
177.5°	538.7	538.7	539.5	541.2	539.5	538.7	539.5	541.2	541.2	542.0	542.0
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331368-940
 CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1136.0	1135.2	1135.2	1132.0	1135.2	1135.2	1136.0	1139.6	1140.8	1141.5	1140.1
5°	1053.8	1052.4	1050.2	1052.4	1050.2	1052.4	1053.8	1060.2	1063.4	1066.6	1069.3
7.5°	972.5	967.1	966.3	960.8	966.3	967.1	972.5	975.5	981.9	989.1	995.6
10°	913.1	909.5	909.0	900.4	909.0	909.5	913.1	920.9	927.3	935.9	945.0
12.5°	868.0	859.3	860.9	856.0	860.9	859.3	868.0	868.1	875.6	880.9	895.1
15°	789.8	789.8	787.9	780.2	787.9	789.8	789.8	802.1	804.3	813.0	825.3
17.5°	733.6	732.7	728.3	730.5	728.3	732.7	733.6	742.6	744.1	755.7	765.8
20°	700.1	697.4	691.9	691.9	691.9	697.4	700.1	705.1	711.1	717.8	726.5
22.5°	668.4	668.2	662.5	664.2	662.5	668.2	668.4	673.1	678.6	686.2	693.4
25°	631.3	627.8	625.0	626.3	625.0	627.8	631.3	631.9	638.2	643.2	647.7
27.5°	596.2	594.2	594.1	590.3	594.1	594.2	596.2	597.4	601.0	604.0	608.2
30°	575.9	571.3	572.2	569.9	572.2	571.3	575.9	576.3	578.1	580.0	585.0
32.5°	552.5	550.9	550.0	548.0	550.0	550.9	552.5	553.3	557.0	558.8	562.8
35°	520.8	521.2	519.0	519.9	519.0	521.2	520.8	521.7	522.1	524.0	527.5
37.5°	493.0	494.5	493.4	493.7	493.4	494.5	493.0	493.5	493.9	494.2	495.3
40°	474.7	474.7	474.7	476.2	474.7	474.7	474.7	473.4	473.9	473.4	473.4
42.5°	457.3	456.6	455.8	455.8	455.8	456.6	457.3	454.1	455.7	454.1	453.3
45°	427.4	428.8	429.3	427.0	429.3	428.8	427.4	426.5	425.2	424.7	424.3
47.5°	400.4	400.6	400.4	402.4	400.4	400.6	400.4	399.2	397.1	396.3	394.1
50°	381.5	380.6	381.5	380.6	381.5	380.6	381.5	379.2	377.8	375.5	373.7
52.5°	361.4	361.6	361.1	360.9	361.1	361.6	361.4	358.5	357.8	357.0	354.1
55°	330.0	330.9	330.5	330.5	330.5	330.9	330.0	328.2	327.7	325.0	322.3
57.5°	297.6	298.4	299.0	296.9	299.0	298.4	297.6	297.2	296.9	294.1	291.1
60°	274.9	277.2	276.8	275.9	276.8	277.2	274.9	275.4	274.0	272.2	270.4
62.5°	254.2	255.0	254.9	254.8	254.9	255.0	254.2	252.1	251.5	249.6	247.8
65°	222.1	223.0	221.7	223.0	221.7	223.0	222.1	220.8	217.6	216.7	214.8
67.5°	187.6	187.9	189.0	189.6	189.0	187.9	187.6	188.2	186.1	184.3	184.0
70°	166.1	165.7	167.0	168.4	167.0	165.7	166.1	165.2	163.9	162.5	160.7
72.5°	143.6	144.5	144.1	145.1	144.1	144.5	143.6	143.7	142.4	140.6	138.8
75°	110.6	112.0	111.6	112.9	111.6	112.0	110.6	111.6	110.6	108.8	107.0
77.5°	79.9	80.1	79.9	80.7	79.9	80.1	79.9	80.7	79.6	80.3	78.2
80°	61.0	60.1	59.2	61.0	59.2	60.1	61.0	61.0	59.7	61.0	59.7
82.5°	42.4	43.0	42.1	42.1	42.1	43.0	42.4	43.5	42.9	43.5	42.2
85°	19.6	19.1	18.2	18.2	18.2	19.1	19.6	19.6	21.0	20.1	20.1
87.5°	10.5	10.1	10.1	9.7	10.1	10.1	10.5	10.5	10.3	10.6	11.0
90°	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	33.2	31.1	33.2
92.5°	61.5	58.2	59.0	57.4	59.0	58.2	61.5	62.3	68.8	77.5	90.3
95°	128.4	120.2	117.1	118.1	117.1	120.2	128.4	141.9	164.7	208.2	271.4
97.5°	281.8	256.3	241.1	232.5	241.1	256.3	281.8	331.3	406.1	518.2	633.3
100°	464.0	419.5	389.5	370.9	389.5	419.5	464.0	550.0	675.4	817.3	945.7
102.5°	791.4	715.4	677.9	652.6	677.9	715.4	791.4	884.8	1017.6	1121.4	1150.5
105°	1290.7	1226.5	1182.0	1167.4	1182.0	1226.5	1290.7	1355.0	1389.1	1375.6	1258.6
107.5°	1523.0	1519.4	1510.5	1491.2	1510.5	1519.4	1523.0	1514.8	1464.7	1357.0	1180.7
110°	1561.0	1580.7	1590.1	1589.0	1590.1	1580.7	1561.0	1516.5	1431.6	1299.0	1113.6



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1531.2	1564.1	1581.8	1587.3	1581.8	1564.1	1531.2	1469.3	1371.9	1230.2	1052.2
115°	1452.3	1499.9	1526.9	1536.2	1526.9	1499.9	1452.3	1378.8	1272.0	1136.4	976.9
117.5°	1358.3	1408.5	1437.0	1444.8	1437.0	1408.5	1358.3	1283.3	1183.2	1060.2	920.1
120°	1296.9	1345.6	1375.6	1386.0	1375.6	1345.6	1296.9	1224.4	1130.2	1020.3	891.9
122.5°	1241.4	1289.2	1316.0	1324.6	1316.0	1289.2	1241.4	1176.3	1091.2	987.2	869.5
125°	1172.6	1212.0	1237.9	1246.2	1237.9	1212.0	1172.6	1112.5	1034.8	943.7	837.0
127.5°	1111.5	1148.3	1170.7	1177.4	1170.7	1148.3	1111.5	1059.1	987.4	901.4	804.9
130°	1074.2	1109.5	1130.2	1138.4	1130.2	1109.5	1074.2	1023.4	955.1	873.3	784.2
132.5°	1036.1	1071.3	1090.4	1097.8	1090.4	1071.3	1036.1	986.1	921.9	846.8	764.3
135°	975.8	1010.0	1028.6	1032.8	1028.6	1010.0	975.8	931.2	873.3	804.9	736.5
137.5°	916.9	946.4	962.8	968.9	962.8	946.4	916.9	876.4	825.8	771.5	714.3
140°	876.4	903.3	918.8	925.1	918.8	903.3	876.4	843.2	797.6	750.0	700.3
142.5°	841.5	866.0	879.9	881.1	879.9	866.0	841.5	810.0	772.0	730.9	688.7
145°	793.4	811.1	821.4	824.6	821.4	811.1	793.4	768.7	738.6	706.5	672.3
147.5°	754.1	768.2	775.3	777.1	775.3	768.2	754.1	733.6	711.7	686.6	659.7
150°	729.2	741.7	747.9	748.9	747.9	741.7	729.2	713.7	695.1	673.3	650.5
152.5°	709.4	720.1	724.7	724.9	724.7	720.1	709.4	697.1	681.0	662.5	641.4
155°	683.7	690.9	695.1	693.0	695.1	690.9	683.7	672.3	660.8	645.3	628.7
157.5°	658.0	664.0	665.8	665.8	665.8	664.0	658.0	649.9	641.0	627.9	614.0
160°	642.2	647.4	648.5	648.5	648.5	647.4	642.2	635.0	627.8	616.4	604.9
162.5°	628.1	631.7	632.7	631.9	632.7	631.7	628.1	620.9	615.3	605.6	595.8
165°	604.9	609.1	609.1	608.1	609.1	609.1	604.9	600.8	596.6	589.4	582.2
167.5°	585.2	587.5	587.4	586.1	587.4	587.5	585.2	583.4	579.7	574.7	569.1
170°	572.8	576.0	574.9	572.8	574.9	576.0	572.8	571.8	569.7	565.6	562.5
172.5°	562.9	564.4	563.3	562.0	563.3	564.4	562.9	561.9	560.6	557.3	555.0
175°	550.0	551.1	550.0	548.0	550.0	551.1	550.0	550.0	549.0	548.0	547.0
177.5°	542.0	542.0	541.2	539.5	541.2	542.0	542.0	542.0	542.0	541.2	541.2
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1138.2	1142.2	1148.3	1154.9	1159.0	1166.6	1168.8	1172.4	1175.7	1183.4	1191.3
5°	1072.5	1078.8	1093.9	1102.1	1113.4	1126.6	1135.2	1144.4	1154.4	1171.7	1187.6
7.5°	1002.0	1012.6	1031.3	1046.6	1062.8	1081.7	1095.4	1113.4	1128.4	1152.7	1176.1
10°	955.0	970.0	986.9	1005.0	1027.9	1047.8	1067.0	1089.8	1108.0	1137.1	1164.4
12.5°	912.8	915.1	939.1	959.2	990.3	1015.1	1037.1	1066.5	1084.3	1118.9	1147.6
15°	838.9	852.6	874.4	890.4	927.3	958.7	989.6	1020.1	1040.6	1083.3	1121.1
17.5°	776.8	789.3	811.7	837.9	864.3	895.5	935.6	967.8	995.6	1044.6	1089.2
20°	737.4	752.9	775.7	802.5	825.7	859.9	894.5	931.3	961.4	1016.5	1068.8
22.5°	703.9	716.1	734.5	761.0	786.4	817.6	855.5	895.6	927.2	986.6	1039.6
25°	656.8	666.9	678.7	700.5	729.2	763.4	793.0	837.1	883.1	938.6	1002.8
27.5°	614.4	621.5	632.0	651.2	673.4	705.3	738.2	780.2	826.3	886.6	954.4
30°	588.6	593.2	603.6	619.6	641.4	666.4	699.6	739.7	787.0	848.0	915.4
32.5°	566.0	570.2	577.0	592.2	611.2	632.6	662.5	702.6	747.7	807.6	882.3
35°	532.2	535.3	541.3	553.5	564.0	585.0	609.9	646.4	688.8	746.1	823.5
37.5°	498.4	502.7	506.4	511.6	525.0	538.8	560.5	591.3	632.8	690.7	764.5
40°	476.2	479.7	485.3	487.5	498.5	510.8	528.5	556.7	598.6	651.4	723.4
42.5°	453.5	457.2	460.5	463.2	472.6	483.4	499.4	523.6	560.7	612.1	683.2
45°	422.8	423.3	426.5	431.5	436.0	443.8	455.2	476.2	504.8	553.0	617.7
47.5°	391.7	392.3	392.8	395.0	400.0	407.1	414.6	431.6	457.3	495.8	558.7
50°	371.0	370.1	371.0	372.8	376.0	381.9	390.6	402.9	423.8	459.8	517.5
52.5°	351.0	350.8	350.3	351.0	353.4	357.5	363.6	374.1	392.8	425.9	476.8
55°	320.5	318.2	318.6	316.8	320.9	321.8	326.4	335.0	351.4	374.2	422.0
57.5°	287.9	286.1	284.0	283.5	283.1	285.6	289.3	296.0	308.6	328.6	367.4
60°	267.2	264.9	262.2	261.3	261.3	262.6	264.5	269.5	281.3	299.1	330.9
62.5°	246.1	243.4	241.8	239.4	238.7	240.0	241.9	245.5	254.0	270.6	298.2
65°	213.5	210.3	208.0	207.6	206.7	205.3	206.2	209.8	216.7	229.9	251.7
67.5°	180.8	177.8	177.3	174.6	173.3	173.5	173.3	176.5	180.6	191.9	208.2
70°	159.3	157.0	156.1	153.8	152.9	152.0	151.1	153.8	157.9	167.6	181.6
72.5°	137.5	135.5	133.6	131.6	131.8	130.9	130.7	132.3	135.7	144.5	155.4
75°	106.0	106.6	104.2	101.9	101.5	100.6	100.6	101.9	103.3	110.1	118.8
77.5°	77.0	76.6	74.6	73.9	73.5	72.5	73.5	74.4	75.1	79.6	86.1
80°	58.8	58.8	56.4	56.4	56.0	54.7	56.0	55.1	56.9	61.4	66.0
82.5°	42.0	41.2	41.1	40.4	40.3	39.3	39.9	40.8	41.6	44.7	47.4
85°	20.5	20.5	20.1	19.6	20.1	19.6	20.1	20.5	21.0	22.3	24.6
87.5°	11.2	11.8	11.9	11.1	9.6	8.9	8.6	8.6	8.9	8.5	8.2
90°	34.2	35.2	34.2	28.0	20.7	15.5	12.4	10.3	8.3	4.1	1.1
92.5°	113.8	134.6	132.8	103.3	70.4	47.0	37.3	30.2	25.7	18.2	12.7
95°	355.3	406.1	359.4	239.2	149.2	101.5	76.7	60.1	50.7	40.4	36.3
97.5°	727.2	693.2	522.1	322.4	196.8	137.0	108.8	89.7	75.6	64.6	59.0
100°	967.5	818.3	563.5	339.7	213.4	158.5	129.5	108.8	92.2	82.8	79.7
102.5°	1057.0	822.5	547.8	340.6	228.3	177.5	148.6	127.0	110.4	101.1	98.8
105°	1043.1	767.6	516.9	346.0	253.8	205.1	176.1	153.3	137.8	130.5	126.4
107.5°	952.2	708.7	501.6	360.3	279.9	232.6	203.5	180.8	166.6	159.5	156.2
110°	895.0	680.6	498.3	371.8	297.3	251.7	221.7	199.9	186.5	180.2	176.1



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	855.2	662.4	499.1	384.3	313.9	269.9	239.1	218.1	205.5	198.5	194.3
115°	805.9	642.2	503.5	403.0	339.7	295.2	267.2	246.6	234.1	227.9	222.7
117.5°	774.8	632.5	510.9	422.8	363.6	322.4	293.4	273.5	262.5	256.3	252.2
120°	758.2	626.7	515.9	436.1	380.1	339.7	310.8	290.1	280.7	274.5	270.4
122.5°	744.1	623.4	521.7	447.7	395.9	358.0	328.1	307.5	297.3	291.1	287.8
125°	724.1	617.4	530.4	466.2	419.5	382.3	353.2	332.5	320.1	313.9	310.8
127.5°	705.4	613.9	539.3	483.3	441.5	405.2	375.4	355.5	341.9	333.1	329.0
130°	693.0	612.2	545.9	494.1	454.8	418.5	389.5	368.8	354.3	343.9	339.7
132.5°	683.1	611.4	552.5	504.9	466.4	431.8	402.8	381.2	365.9	354.7	349.7
135°	669.1	610.1	560.4	519.0	482.7	449.6	420.5	396.7	381.2	368.8	364.6
137.5°	659.4	609.9	567.5	529.8	496.0	463.2	436.3	412.7	396.1	383.7	378.7
140°	653.6	609.1	570.8	535.6	503.5	472.3	445.4	422.7	406.1	393.6	389.5
142.5°	647.8	609.1	573.3	540.6	509.3	479.0	453.7	431.8	415.2	403.6	400.3
145°	640.2	607.0	576.0	547.0	517.9	490.0	467.2	446.5	431.0	420.5	416.4
147.5°	632.3	603.3	576.8	550.5	525.0	498.6	478.4	461.2	446.8	436.9	433.8
150°	625.6	600.8	576.0	552.1	528.3	504.4	485.8	470.3	456.8	448.5	445.4
152.5°	619.8	596.6	574.3	552.9	531.6	510.2	493.3	478.6	466.7	458.5	457.0
155°	609.1	589.4	571.8	554.2	536.5	519.0	503.5	492.0	480.6	474.4	473.4
157.5°	599.0	581.9	567.0	554.2	540.1	525.2	512.1	503.0	493.1	488.1	487.1
160°	591.5	577.0	564.5	554.2	541.8	529.3	517.9	509.6	501.3	497.2	496.1
162.5°	584.9	572.8	562.0	553.4	542.6	531.8	522.9	515.4	508.8	504.7	505.3
165°	573.9	564.5	557.3	551.1	543.9	534.5	528.3	523.1	516.9	514.9	515.9
167.5°	563.1	557.3	552.5	549.7	543.6	536.8	532.9	529.1	525.2	523.3	524.6
170°	557.3	553.1	550.0	548.0	542.8	537.6	534.5	532.4	529.3	528.3	530.4
172.5°	551.5	548.2	546.7	545.5	542.0	538.4	536.2	534.9	531.8	532.4	533.7
175°	543.9	542.8	541.8	542.8	540.7	538.7	537.6	537.6	535.6	536.5	537.6
177.5°	539.5	538.7	539.5	541.2	539.5	538.7	538.7	538.7	537.0	537.8	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1190.6	1192.5	1198.3	1204.1	1210.7	1212.5	1215.4	1212.8	1212.1	1219.1	1224.1
5°	1194.0	1202.2	1218.2	1232.7	1245.0	1253.7	1262.8	1266.4	1273.2	1282.7	1294.6
7.5°	1190.2	1206.1	1231.2	1252.3	1275.5	1292.2	1305.2	1316.3	1329.7	1347.8	1367.6
10°	1185.8	1207.2	1237.7	1263.6	1291.8	1313.2	1331.1	1348.3	1368.3	1393.4	1419.3
12.5°	1177.8	1203.2	1241.4	1272.0	1308.2	1329.3	1353.3	1390.5	1412.0	1446.9	1483.5
15°	1161.7	1189.9	1243.1	1280.9	1321.9	1362.0	1406.1	1441.6	1477.1	1497.6	1549.1
17.5°	1137.7	1179.2	1238.1	1282.2	1334.3	1397.4	1447.0	1487.2	1528.2	1561.5	1587.2
20°	1118.5	1163.5	1230.8	1283.7	1345.6	1413.4	1470.3	1511.3	1546.8	1574.6	1590.5
22.5°	1094.0	1150.8	1216.3	1278.2	1357.3	1424.3	1484.2	1516.4	1546.0	1559.6	1565.8
25°	1055.6	1123.9	1198.1	1273.6	1362.9	1433.9	1488.5	1508.1	1516.7	1503.5	1481.7
27.5°	1014.2	1090.3	1177.1	1265.1	1359.4	1427.7	1466.9	1463.7	1449.1	1406.4	1372.3
30°	983.2	1067.0	1160.3	1256.3	1351.0	1417.5	1440.3	1417.5	1384.3	1336.5	1287.8
32.5°	950.8	1037.5	1142.5	1243.9	1335.8	1394.2	1399.1	1359.9	1308.5	1254.2	1193.5
35°	901.8	995.5	1108.8	1216.3	1303.2	1340.2	1318.3	1249.1	1188.1	1113.9	1031.0
37.5°	846.3	949.9	1063.5	1175.8	1254.5	1264.2	1210.0	1137.1	1051.1	963.9	866.4
40°	804.8	914.5	1031.5	1144.9	1214.5	1204.4	1135.2	1055.2	952.7	846.2	755.6
42.5°	767.7	877.4	996.5	1107.7	1163.5	1136.0	1055.2	956.8	846.8	746.5	663.5
45°	703.3	816.2	938.2	1045.6	1077.5	1027.9	920.9	811.6	703.3	619.6	554.0
47.5°	640.9	752.4	873.3	967.7	978.9	912.2	795.3	682.9	589.8	521.6	475.3
50°	594.9	706.9	826.6	910.9	907.2	826.6	706.5	599.5	521.7	466.5	435.6
52.5°	553.8	659.6	774.5	851.1	831.9	744.0	629.3	534.3	470.3	427.2	399.2
55°	489.8	587.6	696.9	758.4	722.8	625.4	528.5	452.0	404.7	372.4	350.5
57.5°	426.2	518.0	611.5	649.4	610.2	520.2	439.3	383.9	348.3	324.4	310.1
60°	386.9	467.1	550.4	583.1	536.2	456.1	392.4	342.8	314.1	294.5	281.8
62.5°	347.6	419.4	497.9	515.8	472.9	405.1	348.7	307.5	283.8	266.4	254.5
65°	294.1	352.8	412.4	424.3	384.7	332.3	287.7	260.8	239.9	227.1	217.6
67.5°	241.2	288.3	330.6	340.1	305.4	269.1	236.9	213.5	199.3	188.7	180.7
70°	209.8	247.2	281.8	289.5	261.7	229.4	204.8	186.2	173.4	164.3	156.6
72.5°	176.7	207.9	236.6	241.8	219.1	194.5	174.2	159.6	148.3	142.5	135.1
75°	135.2	153.4	175.7	177.1	162.0	147.0	131.5	122.0	116.1	108.8	105.1
77.5°	95.4	109.7	122.4	124.9	116.0	105.8	97.1	89.6	84.5	81.2	77.8
80°	72.9	84.2	89.7	92.8	86.5	79.2	74.2	69.2	66.0	63.8	61.4
82.5°	52.1	59.1	64.2	66.6	63.2	58.9	53.8	51.0	48.5	46.6	45.8
85°	26.4	29.6	32.8	33.7	32.8	30.9	28.2	28.2	26.8	26.4	26.4
87.5°	9.9	12.2	12.7	14.2	14.0	15.1	16.5	17.4	17.2	16.7	16.1
90°	4.1	8.3	10.3	12.4	15.5	20.7	28.0	34.2	35.2	34.2	33.2
92.5°	18.2	25.7	30.2	37.3	47.0	70.4	103.3	132.8	134.6	113.8	90.3
95°	40.4	50.7	60.1	76.7	101.5	149.2	239.2	359.4	406.1	355.3	271.4
97.5°	64.6	75.6	89.7	108.8	137.0	196.8	322.4	522.1	693.2	727.2	633.3
100°	82.8	92.2	108.8	129.5	158.5	213.4	339.7	563.5	818.3	967.5	945.7
102.5°	101.1	110.4	127.0	148.6	177.5	228.3	340.6	547.8	822.5	1057.0	1150.5
105°	130.5	137.8	153.3	176.1	205.1	253.8	346.0	516.9	767.6	1043.1	1258.6
107.5°	159.5	166.6	180.8	203.5	232.6	279.9	360.3	501.6	708.7	952.2	1180.7
110°	180.2	186.5	199.9	221.7	251.7	297.3	371.8	498.3	680.6	895.0	1113.6



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	198.5	205.5	218.1	239.1	269.9	313.9	384.3	499.1	662.4	855.2	1052.2
115°	227.9	234.1	246.6	267.2	295.2	339.7	403.0	503.5	642.2	805.9	976.9
117.5°	256.3	262.5	273.5	293.4	322.4	363.6	422.8	510.9	632.5	774.8	920.1
120°	274.5	280.7	290.1	310.8	339.7	380.1	436.1	515.9	626.7	758.2	891.9
122.5°	291.1	297.3	307.5	328.1	358.0	395.9	447.7	521.7	623.4	744.1	869.5
125°	313.9	320.1	332.5	353.2	382.3	419.5	466.2	530.4	617.4	724.1	837.0
127.5°	333.1	341.9	355.5	375.4	405.2	441.5	483.3	539.3	613.9	705.4	804.9
130°	343.9	354.3	368.8	389.5	418.5	454.8	494.1	545.9	612.2	693.0	784.2
132.5°	354.7	365.9	381.2	402.8	431.8	466.4	504.9	552.5	611.4	683.1	764.3
135°	368.8	381.2	396.7	420.5	449.6	482.7	519.0	560.4	610.1	669.1	736.5
137.5°	383.7	396.1	412.7	436.3	463.2	496.0	529.8	567.5	609.9	659.4	714.3
140°	393.6	406.1	422.7	445.4	472.3	503.5	535.6	570.8	609.1	653.6	700.3
142.5°	403.6	415.2	431.8	453.7	479.0	509.3	540.6	573.3	609.1	647.8	688.7
145°	420.5	431.0	446.5	467.2	490.0	517.9	547.0	576.0	607.0	640.2	672.3
147.5°	436.9	446.8	461.2	478.4	498.6	525.0	550.5	576.8	603.3	632.3	659.7
150°	448.5	456.8	470.3	485.8	504.4	528.3	552.1	576.0	600.8	625.6	650.5
152.5°	458.5	466.7	478.6	493.3	510.2	531.6	552.9	574.3	596.6	619.8	641.4
155°	474.4	480.6	492.0	503.5	519.0	536.5	554.2	571.8	589.4	609.1	628.7
157.5°	488.1	493.1	503.0	512.1	525.2	540.1	554.2	567.0	581.9	599.0	614.0
160°	497.2	501.3	509.6	517.9	529.3	541.8	554.2	564.5	577.0	591.5	604.9
162.5°	504.7	508.8	515.4	522.9	531.8	542.6	553.4	562.0	572.8	584.9	595.8
165°	514.9	516.9	523.1	528.3	534.5	543.9	551.1	557.3	564.5	573.9	582.2
167.5°	523.3	525.2	529.1	532.9	536.8	543.6	549.7	552.5	557.3	563.1	569.1
170°	528.3	529.3	532.4	534.5	537.6	542.8	548.0	550.0	553.1	557.3	562.5
172.5°	532.4	531.8	534.9	536.2	538.4	542.0	545.5	546.7	548.2	551.5	555.0
175°	536.5	535.6	537.6	537.6	538.7	540.7	542.8	541.8	542.8	543.9	547.0
177.5°	537.8	537.0	538.7	538.7	538.7	539.5	541.2	539.5	538.7	539.5	541.2
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1228.5	1233.6	1233.6	1234.3	1240.2	1239.4	1239.0
5°	1307.3	1315.1	1316.0	1324.2	1329.6	1327.8	1322.9
7.5°	1381.7	1396.2	1407.0	1413.1	1420.3	1424.8	1422.8
10°	1440.7	1461.7	1474.4	1483.1	1493.5	1501.3	1498.5
12.5°	1494.2	1519.2	1536.7	1551.5	1552.9	1562.8	1556.0
15°	1577.7	1604.1	1606.9	1617.8	1626.5	1625.5	1625.9
17.5°	1605.3	1613.8	1615.5	1615.8	1615.9	1612.7	1605.8
20°	1595.4	1592.3	1584.6	1578.7	1568.2	1566.8	1557.7
22.5°	1548.9	1538.7	1519.4	1506.5	1490.2	1485.9	1483.5
25°	1457.1	1434.8	1403.8	1374.2	1366.1	1350.1	1354.7
27.5°	1331.2	1296.5	1262.9	1238.9	1217.1	1193.3	1200.1
30°	1242.7	1203.5	1156.2	1119.8	1096.6	1073.8	1069.7
32.5°	1137.1	1079.8	1026.9	994.9	959.3	944.9	929.2
35°	955.0	899.0	846.7	801.6	775.7	755.6	737.4
37.5°	791.2	726.7	684.6	648.0	629.3	617.8	620.7
40°	689.6	633.2	602.3	574.4	557.1	548.9	550.8
42.5°	607.3	565.1	539.6	520.6	508.4	503.8	502.7
45°	513.9	490.3	469.3	458.4	452.5	447.5	444.3
47.5°	450.2	430.9	419.1	412.6	407.4	402.3	402.3
50°	412.0	399.2	391.0	384.1	380.1	376.5	379.6
52.5°	382.8	371.1	363.0	356.9	355.3	352.0	352.0
55°	339.6	330.5	324.6	319.1	316.4	314.5	312.3
57.5°	300.2	291.6	286.1	282.7	277.5	275.6	274.9
60°	272.2	265.4	259.9	255.4	253.1	249.4	249.4
62.5°	246.4	239.5	234.4	231.0	227.2	225.8	226.1
65°	208.9	203.5	198.5	194.8	193.9	191.2	192.1
67.5°	174.5	170.9	165.6	163.6	161.8	160.4	159.3
70°	151.6	147.9	145.2	142.5	141.1	141.1	141.1
72.5°	132.2	127.9	126.3	122.8	123.6	122.2	120.7
75°	102.5	99.7	98.4	96.9	94.7	94.7	94.7
77.5°	75.3	74.5	72.9	71.4	70.9	70.4	70.6
80°	58.2	57.8	56.9	56.9	56.0	55.6	54.7
82.5°	44.8	43.6	43.1	42.7	42.5	42.4	42.3
85°	25.5	24.6	24.6	25.1	24.2	24.2	24.6
87.5°	16.1	16.5	16.3	16.3	16.7	16.3	16.3
90°	31.1	33.2	34.2	34.2	34.2	34.2	34.2
92.5°	77.5	68.8	62.3	61.5	58.2	59.0	57.4
95°	208.2	164.7	141.9	128.4	120.2	117.1	118.1
97.5°	518.2	406.1	331.3	281.8	256.3	241.1	232.5
100°	817.3	675.4	550.0	464.0	419.5	389.5	370.9
102.5°	1121.4	1017.6	884.8	791.4	715.4	677.9	652.6
105°	1375.6	1389.1	1355.0	1290.7	1226.5	1182.0	1167.4
107.5°	1357.0	1464.7	1514.8	1523.0	1519.4	1510.5	1491.2
110°	1299.0	1431.6	1516.5	1561.0	1580.7	1590.1	1589.0



TEST NUMBER: P331368-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1230.2	1371.9	1469.3	1531.2	1564.1	1581.8	1587.3
115°	1136.4	1272.0	1378.8	1452.3	1499.9	1526.9	1536.2
117.5°	1060.2	1183.2	1283.3	1358.3	1408.5	1437.0	1444.8
120°	1020.3	1130.2	1224.4	1296.9	1345.6	1375.6	1386.0
122.5°	987.2	1091.2	1176.3	1241.4	1289.2	1316.0	1324.6
125°	943.7	1034.8	1112.5	1172.6	1212.0	1237.9	1246.2
127.5°	901.4	987.4	1059.1	1111.5	1148.3	1170.7	1177.4
130°	873.3	955.1	1023.4	1074.2	1109.5	1130.2	1138.4
132.5°	846.8	921.9	986.1	1036.1	1071.3	1090.4	1097.8
135°	804.9	873.3	931.2	975.8	1010.0	1028.6	1032.8
137.5°	771.5	825.8	876.4	916.9	946.4	962.8	968.9
140°	750.0	797.6	843.2	876.4	903.3	918.8	925.1
142.5°	730.9	772.0	810.0	841.5	866.0	879.9	881.1
145°	706.5	738.6	768.7	793.4	811.1	821.4	824.6
147.5°	686.6	711.7	733.6	754.1	768.2	775.3	777.1
150°	673.3	695.1	713.7	729.2	741.7	747.9	748.9
152.5°	662.5	681.0	697.1	709.4	720.1	724.7	724.9
155°	645.3	660.8	672.3	683.7	690.9	695.1	693.0
157.5°	627.9	641.0	649.9	658.0	664.0	665.8	665.8
160°	616.4	627.8	635.0	642.2	647.4	648.5	648.5
162.5°	605.6	615.3	620.9	628.1	631.7	632.7	631.9
165°	589.4	596.6	600.8	604.9	609.1	609.1	608.1
167.5°	574.7	579.7	583.4	585.2	587.5	587.4	586.1
170°	565.6	569.7	571.8	572.8	576.0	574.9	572.8
172.5°	557.3	560.6	561.9	562.9	564.4	563.3	562.0
175°	548.0	549.0	550.0	550.0	551.1	550.0	548.0
177.5°	541.2	542.0	542.0	542.0	542.0	541.2	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7

(END OF REPORT)