

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332575-930

Luminaire Tested: **SA4XXDIP-C575D1205U930-4F0-1E-UDD-D1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332575-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D1205U930-4F0-1E-UDD-D1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5332.9 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332575-930

CATALOG NUMBER: SA4XXDIP-C575D1205U930-4F0-1E-UDD-D1

Luminous Intensity Polar Plot





TEST NUMBER: P332575-930

CATALOG NUMBER: SA4XXDIP-C575D1205U930-4F0-1E-UDD-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	93	89	85	81	84	80	77	74	64	61	59	49	47	46	35	34	33	27
2	85	77	71	66	76	70	64	60	56	52	48	43	40	38	30	29	27	22
3	77	68	60	54	69	61	55	50	49	44	40	37	34	32	27	25	23	18
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	21	20	15
5	64	53	45	39	58	48	41	36	38	33	29	30	26	23	21	19	17	13
6	59	47	39	33	53	43	36	31	34	29	25	27	23	20	19	17	15	12
7	55	42	35	29	49	38	32	27	31	26	22	24	20	17	17	15	13	10
8	51	38	31	25	45	35	28	23	28	23	19	22	18	15	16	13	12	9
9	47	35	27	22	42	32	25	21	26	21	17	20	16	14	15	12	10	8
10	44	32	25	20	39	29	23	18	24	19	15	18	15	12	14	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4574	4574	4574
5°	4588	4470	4482
10°	4560	4397	4393
15°	4519	4312	4289
20°	4458	4219	4187
25°	4388	4114	4074
30°	4313	4011	3959
35°	4227	3903	3858
40°	4160	3802	3753
45°	4059	3708	3663
50°	3973	3600	3567
55°	3884	3499	3454
60°	3746	3369	3353
65°	3597	3231	3227
70°	3414	3072	3080
75°	3157	2896	2948
80°	2873	2730	2819
85°	2514	2579	2742



TEST NUMBER: P332575-930

CATALOG NUMBER: SA4XXDIP-C575D1205U930-4F0-1E-UDD-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.6	1.0
10°-20°	153.7	2.9
20°-30°	232.4	4.4
30°-40°	281.2	5.3
40°-50°	297.3	5.6
50°-60°	279.8	5.2
60°-70°	232.1	4.4
70°-80°	163.1	3.1
80°-90°	95.8	1.8
90°-100°	135.5	2.5
100°-110°	279.8	5.2
110°-120°	433.4	8.1
120°-130°	550.9	10.3
130°-140°	608.1	11.4
140°-150°	592.4	11.1
150°-160°	497.1	9.3
160°-170°	330.7	6.2
170°-180°	115.8	2.2
0°-30°	439.8	8.2
0°-40°	721.0	13.5
0°-60°	1298.1	24.3
0°-90°	1789.2	33.5
90°-120°	848.7	15.9
90°-150°	2600.1	48.8
90°-180°	3544.0	66.5
0°-180°	5332.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	567	567	567	567	567	
5°	567	565	561	566	565	54
15°	544	544	542	548	548	153
25°	497	501	503	510	511	229
35°	435	443	449	458	460	272
45°	363	375	387	397	401	280
55°	284	298	317	329	333	253
65°	197	217	239	254	260	195
75°	109	133	159	176	183	116
85°	34	60	89	107	114	36
90°	13	49	84	107	115	10
95°	65	95	127	146	153	70
105°	226	241	267	285	294	241
115°	417	423	441	453	457	411
125°	604	604	618	628	630	538
135°	777	783	787	795	796	601
145°	943	946	947	950	950	590
155°	1080	1080	1079	1082	1079	497
165°	1176	1173	1171	1176	1173	331
175°	1223	1218	1217	1223	1217	116
180°	1225	1225	1225	1225	1225	



TEST NUMBER: P332575-930

CATALOG NUMBER: SA4XXDIP-C575D1205U930-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	566.6	566.6	566.6	566.6	566.6	566.6	566.6	566.6	566.6	566.6	566.6
2.5°	568.6	568.3	567.9	567.5	567.2	566.6	565.7	564.8	563.9	563.0	563.8
5°	567.2	566.8	566.3	565.9	565.5	564.8	563.8	562.8	561.8	560.8	562.0
7.5°	562.4	562.1	561.8	561.6	561.3	560.8	560.0	559.2	558.3	557.5	558.8
10°	558.3	558.2	558.0	557.9	557.7	557.3	556.6	555.9	555.2	554.5	555.8
12.5°	552.7	552.7	552.7	552.6	552.6	552.4	551.9	551.4	550.9	550.4	551.5
15°	543.7	543.9	544.0	544.1	544.3	544.1	543.7	543.3	542.8	542.4	543.7
17.5°	531.4	531.8	532.2	532.6	533.1	533.3	533.2	533.1	533.0	533.0	534.2
20°	522.8	523.2	523.6	524.1	524.5	524.7	524.9	525.1	525.1	525.3	526.7
22.5°	513.1	513.6	514.2	514.7	515.3	515.7	515.9	516.2	516.4	516.7	518.1
25°	497.4	498.2	499.1	499.9	500.8	501.4	501.8	502.2	502.7	503.1	504.7
27.5°	479.9	481.1	482.3	483.6	484.9	485.8	486.4	487.1	487.7	488.4	489.8
30°	468.2	469.4	470.4	471.6	472.7	473.8	474.7	475.7	476.7	477.8	479.3
32.5°	455.5	456.9	458.2	459.6	461.0	462.2	463.3	464.4	465.5	466.6	468.3
35°	435.2	436.9	438.6	440.3	442.0	443.5	444.9	446.4	447.8	449.1	451.2
37.5°	414.8	416.7	418.7	420.6	422.6	424.4	426.2	428.0	429.7	431.4	433.4
40°	401.6	403.4	405.3	407.1	409.0	410.8	412.8	414.7	416.8	418.7	420.9
42.5°	386.4	388.4	390.4	392.6	394.6	396.8	399.1	401.4	403.7	406.0	408.4
45°	362.9	365.6	368.3	371.0	373.6	376.3	379.0	381.6	384.3	387.0	389.4
47.5°	340.5	343.2	345.9	348.7	351.5	354.4	357.5	360.6	363.7	366.8	369.3
50°	324.2	327.3	330.4	333.5	336.6	339.7	342.8	345.9	349.0	352.1	354.9
52.5°	307.9	311.0	314.1	317.2	320.3	323.7	327.3	330.8	334.4	337.9	340.7
55°	284.2	287.1	290.2	293.1	296.0	299.6	303.9	308.1	312.3	316.6	319.4
57.5°	257.7	261.4	265.1	268.7	272.4	276.3	280.5	284.7	288.9	293.1	296.4
60°	240.4	244.1	247.8	251.4	255.1	259.3	263.9	268.6	273.2	277.9	281.1
62.5°	223.7	227.7	231.7	235.7	239.7	244.0	248.7	253.3	258.0	262.7	265.9
65°	196.7	201.2	205.7	210.2	214.7	219.4	224.1	228.9	233.7	238.6	242.1
67.5°	170.6	175.5	180.3	185.1	189.8	194.8	199.9	205.0	210.2	215.3	218.9
70°	152.9	157.7	162.5	167.3	172.1	177.2	182.5	187.8	193.2	198.6	202.4
72.5°	135.7	140.6	145.4	150.3	155.2	160.5	166.2	171.9	177.7	183.4	187.0
75°	109.1	114.3	119.5	124.7	130.0	135.6	141.5	147.4	153.4	159.2	163.2
77.5°	84.4	89.9	95.5	100.9	106.5	112.3	118.5	124.7	130.9	137.1	141.1
80°	69.1	74.8	80.5	86.1	91.7	97.6	103.9	110.1	116.3	122.5	126.7
82.5°	53.9	59.8	65.6	71.5	77.4	83.4	89.6	95.8	102.0	108.3	112.6
85°	33.6	39.5	45.5	51.4	57.3	63.4	69.8	76.1	82.5	88.8	93.0
87.5°	19.3	25.6	31.8	38.0	44.2	50.5	57.1	63.6	70.1	76.6	81.0
90°	13.0	21.0	28.9	36.9	44.8	52.7	60.4	68.2	75.9	83.6	89.0
92.5°	29.9	37.7	45.3	53.1	60.8	68.3	75.6	82.8	90.0	97.3	102.0
95°	65.1	71.7	78.2	84.7	91.2	98.2	105.4	112.7	119.9	127.2	131.6
97.5°	106.7	112.3	117.8	123.3	128.8	135.3	142.8	150.2	157.7	165.1	169.6
100°	139.6	144.1	148.6	153.1	157.6	163.5	171.0	178.4	185.7	193.1	197.4
102.5°	174.5	178.0	181.6	185.1	188.7	194.0	201.1	208.2	215.3	222.4	226.7
105°	226.4	229.4	232.4	235.5	238.6	243.0	249.2	255.2	261.2	267.3	271.5
107.5°	282.2	284.7	287.3	289.8	292.4	296.3	301.3	306.4	311.4	316.5	320.6
110°	319.5	322.0	324.3	326.8	329.1	332.7	337.5	342.1	346.8	351.6	354.4



TEST NUMBER: P332575-930

CATALOG NUMBER: SA4XXDIP-C575D1205U930-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	358.5	360.3	362.1	363.9	365.7	368.8	373.2	377.5	381.9	386.2	389.2
115°	416.8	418.1	419.3	420.6	421.8	424.5	428.6	432.8	436.8	440.9	443.8
117.5°	472.4	473.3	474.3	475.2	476.1	478.5	482.4	486.3	490.2	494.2	496.4
120°	509.0	510.2	511.5	512.7	514.0	516.4	519.8	523.3	526.8	530.3	532.0
122.5°	547.6	548.0	548.5	548.9	549.3	551.3	554.9	558.5	562.0	565.6	567.7
125°	604.1	603.9	603.7	603.6	603.5	605.0	608.4	611.6	615.0	618.3	620.5
127.5°	655.6	656.1	656.6	657.0	657.5	659.0	661.4	663.7	666.1	668.5	670.6
130°	691.5	691.9	692.4	692.9	693.4	694.8	697.1	699.3	701.6	703.8	706.0
132.5°	728.6	729.0	729.3	729.6	729.9	730.8	732.5	734.2	735.8	737.4	739.4
135°	777.1	778.3	779.6	780.8	782.1	783.2	784.2	785.2	786.2	787.2	789.0
137.5°	830.5	830.9	831.4	831.8	832.3	832.9	833.7	834.5	835.4	836.2	837.6
140°	866.1	866.3	866.7	866.9	867.2	867.4	867.6	867.7	867.8	868.0	869.6
142.5°	898.1	898.5	898.9	899.4	899.7	899.8	899.5	899.3	899.0	898.8	900.3
145°	943.1	943.8	944.5	945.2	945.9	946.4	946.6	946.8	947.0	947.2	947.9
147.5°	987.8	988.7	989.5	990.4	991.3	991.6	991.5	991.3	991.2	991.0	990.9
150°	1015.1	1015.8	1016.5	1017.2	1017.9	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2
152.5°	1040.3	1040.8	1041.3	1041.8	1042.3	1042.6	1042.8	1042.9	1043.1	1043.3	1043.7
155°	1079.8	1079.8	1079.8	1079.8	1079.8	1079.7	1079.5	1079.3	1079.0	1078.9	1079.7
157.5°	1113.1	1112.8	1112.4	1112.1	1111.7	1111.4	1111.4	1111.3	1111.3	1111.3	1111.9
160°	1132.9	1132.7	1132.5	1132.2	1132.0	1131.8	1131.6	1131.4	1131.1	1131.0	1131.6
162.5°	1151.0	1150.5	1150.0	1149.4	1148.8	1148.5	1148.3	1148.1	1147.9	1147.6	1148.8
165°	1175.5	1174.8	1174.2	1173.6	1173.0	1172.4	1172.0	1171.6	1171.2	1170.8	1172.0
167.5°	1194.3	1193.4	1192.5	1191.6	1190.7	1190.3	1190.3	1190.3	1190.4	1190.4	1191.7
170°	1204.8	1203.8	1202.7	1201.7	1200.6	1200.2	1200.4	1200.6	1200.9	1201.1	1202.3
172.5°	1212.4	1211.5	1210.6	1209.7	1208.9	1208.4	1208.5	1208.6	1208.6	1208.7	1210.1
175°	1222.9	1221.8	1220.7	1219.7	1218.6	1218.0	1217.8	1217.6	1217.4	1217.2	1218.6
177.5°	1226.3	1225.4	1224.6	1223.8	1222.9	1222.5	1222.5	1222.5	1222.5	1222.5	1223.7
180°	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7



TEST NUMBER: P332575-930

CATALOG NUMBER: SA4XXDIP-C575D1205U930-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	566.6	566.6	566.6	566.6	566.6	566.6	566.6	566.6
2.5°	564.6	565.3	566.1	566.5	566.4	566.2	566.1	566.1
5°	563.1	564.2	565.3	565.8	565.7	565.6	565.4	565.2
7.5°	560.1	561.3	562.6	563.2	563.0	562.9	562.7	562.6
10°	557.0	558.3	559.5	560.1	560.0	559.9	559.7	559.5
12.5°	552.8	553.9	555.1	555.6	555.6	555.5	555.5	555.5
15°	544.9	546.3	547.5	548.0	548.0	547.8	547.6	547.5
17.5°	535.5	536.8	538.1	538.7	538.6	538.5	538.3	538.3
20°	528.2	529.5	530.9	531.7	531.7	531.7	531.7	531.7
22.5°	519.5	520.9	522.3	523.2	523.3	523.6	523.8	524.1
25°	506.2	507.8	509.3	510.1	510.3	510.5	510.5	510.7
27.5°	491.3	492.7	494.2	495.0	495.1	495.3	495.5	495.6
30°	480.9	482.4	484.0	484.9	485.1	485.4	485.7	486.0
32.5°	470.1	471.9	473.7	474.7	475.0	475.2	475.6	475.8
35°	453.1	455.1	457.1	458.3	458.7	459.1	459.5	460.0
37.5°	435.5	437.4	439.4	440.7	441.1	441.6	442.0	442.5
40°	423.0	425.1	427.2	428.5	429.1	429.7	430.2	430.8
42.5°	410.7	413.0	415.4	416.8	417.3	417.7	418.2	418.6
45°	391.8	394.2	396.6	398.1	398.8	399.6	400.2	401.0
47.5°	371.8	374.3	376.7	378.4	379.3	380.1	381.0	381.8
50°	357.8	360.6	363.4	365.3	366.1	366.9	367.8	368.6
52.5°	343.6	346.3	349.2	351.0	351.9	352.7	353.5	354.4
55°	322.2	325.1	327.8	329.7	330.5	331.4	332.2	333.0
57.5°	299.8	303.2	306.6	308.6	309.4	310.1	311.0	311.8
60°	284.4	287.6	290.8	293.0	294.2	295.3	296.4	297.6
62.5°	269.1	272.4	275.7	277.8	278.9	280.1	281.2	282.3
65°	245.6	249.2	252.7	254.9	256.1	257.2	258.4	259.5
67.5°	222.5	226.1	229.7	232.0	233.1	234.2	235.3	236.4
70°	206.2	210.0	213.8	216.2	217.2	218.2	219.2	220.1
72.5°	190.7	194.4	198.1	200.5	201.6	202.7	203.8	204.9
75°	167.1	171.0	175.0	177.7	178.9	180.2	181.5	182.7
77.5°	145.2	149.2	153.2	155.9	157.2	158.6	159.9	161.3
80°	130.9	135.1	139.3	142.0	143.2	144.3	145.4	146.6
82.5°	116.9	121.2	125.6	128.4	129.6	130.9	132.1	133.4
85°	97.3	101.5	105.7	108.6	110.0	111.4	112.8	114.2
87.5°	85.3	89.7	94.0	96.9	98.2	99.5	100.8	102.2
90°	94.3	99.7	105.1	108.5	110.1	111.6	113.2	114.7
92.5°	106.7	111.5	116.2	119.3	120.7	122.1	123.4	124.8
95°	136.1	140.5	145.0	147.8	149.0	150.3	151.6	152.9
97.5°	174.0	178.5	183.0	185.7	186.9	188.2	189.4	190.6
100°	201.6	205.9	210.0	212.6	213.6	214.7	215.6	216.6
102.5°	231.0	235.3	239.5	242.3	243.6	244.8	246.1	247.4
105°	275.7	279.8	284.0	286.9	288.6	290.4	292.2	293.9
107.5°	324.6	328.6	332.7	335.3	336.2	337.2	338.2	339.1
110°	357.3	360.0	362.9	365.2	366.9	368.7	370.5	372.2



TEST NUMBER: P332575-930

CATALOG NUMBER: SA4XXDIP-C575D1205U930-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	392.2	395.3	398.4	400.5	401.8	403.0	404.3	405.5
115°	446.7	449.6	452.5	454.3	455.1	455.8	456.6	457.4
117.5°	498.6	500.8	503.0	504.4	505.2	505.9	506.5	507.3
120°	533.8	535.6	537.3	539.0	540.5	542.1	543.6	545.2
122.5°	569.8	571.9	574.0	575.2	575.4	575.7	575.9	576.2
125°	622.8	625.1	627.3	628.7	629.1	629.5	630.0	630.4
127.5°	672.7	674.8	676.9	678.3	678.9	679.6	680.2	680.8
130°	708.1	710.2	712.3	713.4	713.4	713.4	713.4	713.4
132.5°	741.4	743.4	745.4	746.7	747.2	747.7	748.2	748.7
135°	790.8	792.6	794.5	795.5	795.7	796.0	796.1	796.4
137.5°	839.2	840.7	842.2	843.3	844.2	845.1	845.9	846.7
140°	871.2	872.9	874.5	875.5	876.0	876.5	877.0	877.5
142.5°	901.9	903.5	905.1	906.1	906.6	907.2	907.8	908.3
145°	948.5	949.1	949.7	950.1	950.0	949.9	949.8	949.7
147.5°	990.8	990.8	990.8	990.8	991.1	991.3	991.6	991.8
150°	1018.2	1018.2	1018.2	1018.1	1017.9	1017.7	1017.5	1017.3
152.5°	1044.2	1044.8	1045.3	1045.3	1044.7	1044.2	1043.6	1043.1
155°	1080.6	1081.4	1082.2	1082.2	1081.4	1080.6	1079.7	1078.9
157.5°	1112.6	1113.1	1113.8	1113.8	1113.0	1112.3	1111.6	1110.9
160°	1132.2	1132.9	1133.5	1133.3	1132.2	1131.1	1130.2	1129.1
162.5°	1149.9	1151.0	1152.2	1152.3	1151.2	1150.1	1149.1	1148.0
165°	1173.3	1174.5	1175.8	1176.0	1175.2	1174.4	1173.5	1172.6
167.5°	1192.9	1194.3	1195.5	1195.5	1194.2	1192.9	1191.6	1190.3
170°	1203.6	1204.8	1206.2	1206.0	1204.5	1203.1	1201.6	1200.1
172.5°	1211.5	1212.9	1214.4	1214.4	1212.8	1211.4	1209.9	1208.4
175°	1220.1	1221.6	1223.0	1223.0	1221.6	1220.1	1218.6	1217.2
177.5°	1224.8	1226.0	1227.2	1227.1	1225.7	1224.4	1223.0	1221.7
180°	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7

(END OF REPORT)