

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331374-940

Luminaire Tested: **SA2XXDIP-C675D1080U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331374-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D1080U940-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6161.8 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331374-940
CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331374-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	80	73	68	79	72	67	63	59	56	52	47	45	42	36	34	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	66	56	50	44	46	41	37	37	34	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	27	26	23	21	17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	18	15
7	56	44	37	31	51	41	34	29	34	29	25	27	23	20	21	18	16	14
8	52	40	33	27	47	37	30	26	31	26	22	25	21	18	19	17	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15285	15285	15285
5°	15344	15123	15211
10°	15252	14969	15044
15°	15064	14775	14760
20°	14795	14483	14467
25°	14530	14125	14125
30°	14188	13798	13679
35°	13868	13403	13204
40°	13468	13009	12760
45°	13075	12618	12305
50°	12645	12210	11776
55°	12197	11738	11299
60°	11699	11170	10756
65°	11163	10609	10120
70°	10485	9928	9456
75°	9538	9145	8914
80°	8461	8210	7782
85°	6928	6576	5891



TEST NUMBER: P331374-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.0	1.4
10°-20°	250.5	4.1
20°-30°	368.2	6.0
30°-40°	427.7	6.9
40°-50°	427.2	6.9
50°-60°	372.6	6.0
60°-70°	275.5	4.5
70°-80°	156.0	2.5
80°-90°	46.8	0.8
90°-100°	215.4	3.5
100°-110°	730.9	11.9
110°-120°	776.4	12.6
120°-130°	639.2	10.4
130°-140°	513.3	8.3
140°-150°	387.9	6.3
150°-160°	272.6	4.4
160°-170°	160.5	2.6
170°-180°	52.2	0.8
0°-30°	707.7	11.5
0°-40°	1135.4	18.4
0°-60°	1935.1	31.4
0°-90°	2413.4	39.2
90°-120°	1722.7	28.0
90°-150°	3263.0	53.0
90°-180°	3748.0	60.8
0°-180°	6161.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	947	943	933	940	938	90
15°	901	895	884	887	883	254
25°	816	808	793	794	793	375
35°	704	694	680	675	670	439
45°	573	566	553	543	539	442
55°	433	428	417	406	401	387
65°	292	286	278	270	265	289
75°	153	151	147	142	143	163
85°	37	36	36	33	32	43
90°	1	14	35	34	34	4
95°	36	89	406	153	118	38
105°	126	191	768	1372	1167	134
115°	223	281	642	1325	1536	221
125°	311	368	617	1074	1246	276
135°	365	435	610	902	1033	282
145°	416	479	607	754	825	261
155°	473	511	589	667	693	218
165°	516	531	564	599	608	145
175°	538	538	543	550	548	51
180°	539	539	539	539	539	



TEST NUMBER: P331374-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	951.1	950.3	949.5	948.7	947.9	946.6	944.8	943.0	941.2	939.4	941.0
5°	946.7	945.9	945.1	944.3	943.5	942.0	939.8	937.5	935.3	933.1	934.7
7.5°	938.3	937.1	935.9	934.6	933.4	931.6	929.3	927.0	924.8	922.5	924.1
10°	930.3	928.9	927.5	926.0	924.7	922.7	920.3	917.9	915.4	913.0	914.6
12.5°	919.4	918.2	916.9	915.6	914.4	912.6	910.1	907.7	905.3	902.9	904.0
15°	901.2	900.0	898.8	897.6	896.3	894.4	891.8	889.1	886.5	883.9	884.8
17.5°	877.9	876.6	875.5	874.2	873.1	871.1	868.4	865.8	863.1	860.4	861.4
20°	861.1	860.0	858.7	857.5	856.3	854.3	851.4	848.6	845.8	842.9	843.6
22.5°	844.4	842.7	841.0	839.3	837.6	835.4	832.8	830.1	827.4	824.7	824.8
25°	815.6	814.0	812.4	810.7	809.1	806.6	803.2	799.8	796.3	792.9	793.3
27.5°	782.8	781.4	780.0	778.5	777.0	775.0	772.2	769.5	766.8	764.1	763.5
30°	761.0	759.4	757.8	756.2	754.6	752.2	749.2	746.2	743.2	740.1	739.5
32.5°	737.7	736.4	735.1	733.8	732.5	730.3	727.1	723.9	720.7	717.5	716.4
35°	703.6	701.7	699.6	697.6	695.5	692.9	689.7	686.4	683.2	680.0	678.8
37.5°	665.2	663.4	661.6	659.9	658.2	655.6	652.4	649.2	646.0	642.7	641.1
40°	639.0	637.4	635.8	634.2	632.6	630.2	626.9	623.7	620.5	617.2	615.4
42.5°	613.6	611.9	610.3	608.7	607.1	604.7	601.4	598.2	594.9	591.7	589.7
45°	572.6	571.1	569.7	568.4	566.9	564.7	561.7	558.7	555.6	552.6	550.4
47.5°	531.8	530.5	529.1	527.8	526.5	524.2	521.0	517.9	514.8	511.6	509.3
50°	503.4	502.4	501.4	500.3	499.4	497.4	494.6	491.8	488.9	486.1	483.3
52.5°	475.7	474.4	473.1	471.7	470.4	468.4	465.7	463.1	460.4	457.7	455.4
55°	433.3	432.1	430.9	429.6	428.5	426.6	424.2	421.8	419.4	417.0	414.5
57.5°	390.7	389.8	388.8	387.8	386.8	385.0	382.4	379.7	377.0	374.3	371.9
60°	362.3	361.5	360.7	359.9	359.1	357.2	354.5	351.6	348.7	345.9	343.7
62.5°	334.7	333.3	332.1	330.7	329.5	327.7	325.6	323.3	321.2	319.0	316.9
65°	292.2	291.0	289.8	288.6	287.3	285.7	283.7	281.7	279.6	277.7	275.8
67.5°	249.1	248.1	247.1	246.1	245.1	243.8	241.9	240.1	238.4	236.5	235.1
70°	222.1	221.3	220.5	219.7	218.9	217.6	215.7	213.9	212.1	210.3	208.8
72.5°	194.5	193.6	192.8	192.0	191.2	190.2	189.0	187.9	186.7	185.5	184.1
75°	152.9	152.5	152.1	151.7	151.3	150.6	149.6	148.6	147.6	146.6	145.3
77.5°	115.8	115.1	114.4	113.7	113.1	112.5	112.1	111.6	111.3	110.8	110.3
80°	91.0	90.9	90.6	90.4	90.2	89.9	89.5	89.1	88.7	88.3	87.7
82.5°	67.8	67.7	67.7	67.6	67.6	67.4	67.1	67.0	66.7	66.4	65.7
85°	37.4	37.1	36.9	36.7	36.5	36.3	36.1	35.9	35.7	35.5	34.9
87.5°	13.3	13.6	14.1	14.2	14.3	14.6	15.3	16.4	17.4	17.2	16.6
90°	1.1	4.1	8.3	10.3	12.4	15.5	20.7	28.0	34.2	35.2	34.2
92.5°	12.7	18.2	25.7	30.2	37.3	47.0	70.4	103.3	132.8	134.6	113.8
95°	36.3	40.4	50.7	60.1	76.7	101.5	149.2	239.2	359.4	406.1	355.3
97.5°	59.0	64.6	75.6	89.7	108.8	137.0	196.8	322.4	522.1	693.2	727.2
100°	79.7	82.8	92.2	108.8	129.5	158.5	213.4	339.7	563.5	818.3	967.5
102.5°	98.8	101.1	110.4	127.0	148.6	177.5	228.3	340.6	547.8	822.5	1057.0
105°	126.4	130.5	137.8	153.3	176.1	205.1	253.8	346.0	516.9	767.6	1043.1
107.5°	156.2	159.5	166.6	180.8	203.5	232.6	279.9	360.3	501.6	708.7	952.2
110°	176.1	180.2	186.5	199.9	221.7	251.7	297.3	371.8	498.3	680.6	895.0



TEST NUMBER: P331374-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	194.3	198.5	205.5	218.1	239.1	269.9	313.9	384.3	499.1	662.4	855.2
115°	222.7	227.9	234.1	246.6	267.2	295.2	339.7	403.0	503.5	642.2	805.9
117.5°	252.2	256.3	262.5	273.5	293.4	322.4	363.6	422.8	510.9	632.5	774.8
120°	270.4	274.5	280.7	290.1	310.8	339.7	380.1	436.1	515.9	626.7	758.2
122.5°	287.8	291.1	297.3	307.5	328.1	358.0	395.9	447.7	521.7	623.4	744.1
125°	310.8	313.9	320.1	332.5	353.2	382.3	419.5	466.2	530.4	617.4	724.1
127.5°	329.0	333.1	341.9	355.5	375.4	405.2	441.5	483.3	539.3	613.9	705.4
130°	339.7	343.9	354.3	368.8	389.5	418.5	454.8	494.1	545.9	612.2	693.0
132.5°	349.7	354.7	365.9	381.2	402.8	431.8	466.4	504.9	552.5	611.4	683.1
135°	364.6	368.8	381.2	396.7	420.5	449.6	482.7	519.0	560.4	610.1	669.1
137.5°	378.7	383.7	396.1	412.7	436.3	463.2	496.0	529.8	567.5	609.9	659.4
140°	389.5	393.6	406.1	422.7	445.4	472.3	503.5	535.6	570.8	609.1	653.6
142.5°	400.3	403.6	415.2	431.8	453.7	479.0	509.3	540.6	573.3	609.1	647.8
145°	416.4	420.5	431.0	446.5	467.2	490.0	517.9	547.0	576.0	607.0	640.2
147.5°	433.8	436.9	446.8	461.2	478.4	498.6	525.0	550.5	576.8	603.3	632.3
150°	445.4	448.5	456.8	470.3	485.8	504.4	528.3	552.1	576.0	600.8	625.6
152.5°	457.0	458.5	466.7	478.6	493.3	510.2	531.6	552.9	574.3	596.6	619.8
155°	473.4	474.4	480.6	492.0	503.5	519.0	536.5	554.2	571.8	589.4	609.1
157.5°	487.1	488.1	493.1	503.0	512.1	525.2	540.1	554.2	567.0	581.9	599.0
160°	496.1	497.2	501.3	509.6	517.9	529.3	541.8	554.2	564.5	577.0	591.5
162.5°	505.3	504.7	508.8	515.4	522.9	531.8	542.6	553.4	562.0	572.8	584.9
165°	515.9	514.9	516.9	523.1	528.3	534.5	543.9	551.1	557.3	564.5	573.9
167.5°	524.6	523.3	525.2	529.1	532.9	536.8	543.6	549.7	552.5	557.3	563.1
170°	530.4	528.3	529.3	532.4	534.5	537.6	542.8	548.0	550.0	553.1	557.3
172.5°	533.7	532.4	531.8	534.9	536.2	538.4	542.0	545.5	546.7	548.2	551.5
175°	537.6	536.5	535.6	537.6	537.6	538.7	540.7	542.8	541.8	542.8	543.9
177.5°	539.5	537.8	537.0	538.7	538.7	538.7	539.5	541.2	539.5	538.7	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331374-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	942.6	944.3	945.9	946.6	946.2	945.9	945.6	945.3
5°	936.3	937.9	939.5	940.1	939.8	939.3	939.0	938.5
7.5°	925.8	927.4	929.0	929.5	929.1	928.7	928.3	927.8
10°	916.2	917.9	919.5	920.0	919.4	918.8	918.2	917.6
12.5°	905.1	906.2	907.4	907.7	907.2	906.9	906.4	906.0
15°	885.6	886.4	887.2	887.1	886.0	885.0	884.0	883.0
17.5°	862.3	863.2	864.2	864.2	863.2	862.2	861.2	860.2
20°	844.2	844.8	845.3	845.3	844.5	843.6	842.8	842.0
22.5°	825.0	825.1	825.2	825.0	824.6	824.0	823.6	823.1
25°	793.7	794.1	794.5	794.5	794.1	793.7	793.3	792.9
27.5°	762.9	762.3	761.7	760.9	759.9	758.9	758.0	757.0
30°	738.9	738.2	737.6	736.9	736.1	735.3	734.5	733.7
32.5°	715.3	714.3	713.1	712.2	711.4	710.6	709.7	708.9
35°	677.6	676.4	675.1	674.0	673.1	672.0	671.0	669.9
37.5°	639.7	638.2	636.7	635.4	634.5	633.5	632.6	631.6
40°	613.6	611.7	609.9	608.6	607.8	607.0	606.2	605.4
42.5°	587.7	585.8	583.8	582.2	581.0	580.0	578.8	577.7
45°	548.1	545.9	543.7	542.2	541.4	540.6	539.8	538.9
47.5°	506.9	504.5	502.2	500.4	499.3	498.1	497.0	495.8
50°	480.5	477.6	474.7	472.9	471.8	470.8	469.8	468.8
52.5°	453.0	450.7	448.4	446.5	445.1	443.8	442.5	441.1
55°	412.1	409.7	407.2	405.5	404.5	403.5	402.4	401.4
57.5°	369.5	367.1	364.8	363.2	362.4	361.7	360.9	360.1
60°	341.4	339.2	337.0	335.6	335.0	334.4	333.8	333.1
62.5°	314.9	312.8	310.8	309.3	308.5	307.7	307.0	306.2
65°	274.0	272.2	270.4	268.9	268.0	266.9	265.9	264.9
67.5°	233.6	232.3	230.9	229.7	228.9	228.1	227.3	226.5
70°	207.4	206.1	204.6	203.5	202.7	201.9	201.1	200.3
72.5°	182.7	181.3	179.9	178.8	178.2	177.5	176.9	176.2
75°	144.1	142.9	141.7	141.3	141.7	142.1	142.5	142.9
77.5°	109.7	109.1	108.4	107.9	107.3	106.7	106.2	105.6
80°	87.1	86.5	85.9	85.3	85.0	84.5	84.2	83.7
82.5°	64.9	64.1	63.4	63.0	62.9	62.8	62.7	62.6
85°	34.3	33.7	33.1	32.6	32.5	32.3	32.1	31.8
87.5°	15.9	15.0	14.9	14.8	14.6	14.4	14.3	14.1
90°	33.2	31.1	33.2	34.2	34.2	34.2	34.2	34.2
92.5°	90.3	77.5	68.8	62.3	61.5	58.2	59.0	57.4
95°	271.4	208.2	164.7	141.9	128.4	120.2	117.1	118.1
97.5°	633.3	518.2	406.1	331.3	281.8	256.3	241.1	232.5
100°	945.7	817.3	675.4	550.0	464.0	419.5	389.5	370.9
102.5°	1150.5	1121.4	1017.6	884.8	791.4	715.4	677.9	652.6
105°	1258.6	1375.6	1389.1	1355.0	1290.7	1226.5	1182.0	1167.4
107.5°	1180.7	1357.0	1464.7	1514.8	1523.0	1519.4	1510.5	1491.2
110°	1113.6	1299.0	1431.6	1516.5	1561.0	1580.7	1590.1	1589.0



TEST NUMBER: P331374-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1052.2	1230.2	1371.9	1469.3	1531.2	1564.1	1581.8	1587.3
115°	976.9	1136.4	1272.0	1378.8	1452.3	1499.9	1526.9	1536.2
117.5°	920.1	1060.2	1183.2	1283.3	1358.3	1408.5	1437.0	1444.8
120°	891.9	1020.3	1130.2	1224.4	1296.9	1345.6	1375.6	1386.0
122.5°	869.5	987.2	1091.2	1176.3	1241.4	1289.2	1316.0	1324.6
125°	837.0	943.7	1034.8	1112.5	1172.6	1212.0	1237.9	1246.2
127.5°	804.9	901.4	987.4	1059.1	1111.5	1148.3	1170.7	1177.4
130°	784.2	873.3	955.1	1023.4	1074.2	1109.5	1130.2	1138.4
132.5°	764.3	846.8	921.9	986.1	1036.1	1071.3	1090.4	1097.8
135°	736.5	804.9	873.3	931.2	975.8	1010.0	1028.6	1032.8
137.5°	714.3	771.5	825.8	876.4	916.9	946.4	962.8	968.9
140°	700.3	750.0	797.6	843.2	876.4	903.3	918.8	925.1
142.5°	688.7	730.9	772.0	810.0	841.5	866.0	879.9	881.1
145°	672.3	706.5	738.6	768.7	793.4	811.1	821.4	824.6
147.5°	659.7	686.6	711.7	733.6	754.1	768.2	775.3	777.1
150°	650.5	673.3	695.1	713.7	729.2	741.7	747.9	748.9
152.5°	641.4	662.5	681.0	697.1	709.4	720.1	724.7	724.9
155°	628.7	645.3	660.8	672.3	683.7	690.9	695.1	693.0
157.5°	614.0	627.9	641.0	649.9	658.0	664.0	665.8	665.8
160°	604.9	616.4	627.8	635.0	642.2	647.4	648.5	648.5
162.5°	595.8	605.6	615.3	620.9	628.1	631.7	632.7	631.9
165°	582.2	589.4	596.6	600.8	604.9	609.1	609.1	608.1
167.5°	569.1	574.7	579.7	583.4	585.2	587.5	587.4	586.1
170°	562.5	565.6	569.7	571.8	572.8	576.0	574.9	572.8
172.5°	555.0	557.3	560.6	561.9	562.9	564.4	563.3	562.0
175°	547.0	548.0	549.0	550.0	550.0	551.1	550.0	548.0
177.5°	541.2	541.2	542.0	542.0	542.0	542.0	541.2	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7

(END OF REPORT)