

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332541-930

Luminaire Tested: **SA4XXDIP-C575D365U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332541-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C575D365U930-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3224.6 lumens  
Efficiency: N/A  
Efficacy: 117.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332541-930  
CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332541-930

CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63				
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	53				
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	51	48	44				
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41	38				
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	32				
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28				
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	25				
7	60	47	39	34	56	45	37	32	40	34	30	36	31	27	31	27	24	22				
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20				
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	18				
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6391	6391	6391
5°	6412	6334	6380
10°	6370	6283	6314
15°	6294	6193	6209
20°	6192	6082	6088
25°	6075	5956	5940
30°	5931	5808	5754
35°	5784	5653	5577
40°	5630	5476	5376
45°	5469	5302	5200
50°	5291	5148	4987
55°	5098	4947	4787
60°	4907	4721	4579
65°	4690	4508	4327
70°	4447	4223	4057
75°	4077	3877	3780
80°	3626	3477	3394
85°	3168	3057	3001



TEST NUMBER: P332541-930

CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.6	2.3
10°-20°	210.1	6.5
20°-30°	309.2	9.6
30°-40°	359.5	11.1
40°-50°	359.5	11.1
50°-60°	314.5	9.8
60°-70°	233.5	7.2
70°-80°	132.7	4.1
80°-90°	39.4	1.2
90°-100°	13.2	0.4
100°-110°	84.0	2.6
110°-120°	160.7	5.0
120°-130°	204.0	6.3
130°-140°	218.3	6.8
140°-150°	204.1	6.3
150°-160°	164.6	5.1
160°-170°	106.2	3.3
170°-180°	36.6	1.1
0°-30°	593.9	18.4
0°-40°	953.4	29.6
0°-60°	1627.3	50.5
0°-90°	2032.9	63.0
90°-120°	257.9	8.0
90°-150°	884.3	27.4
90°-180°	1192.0	37.0
0°-180°	3224.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	792	792	792	792	792	
5°	791	788	782	788	787	75
15°	753	750	741	744	743	212
25°	682	677	669	669	667	314
35°	587	582	574	569	566	367
45°	479	474	464	458	456	369
55°	362	360	352	344	340	324
65°	246	242	236	230	226	243
75°	131	128	124	122	121	139
85°	34	34	33	33	32	38
90°	1	4	6	8	9	3
95°	16	7	6	8	8	20
105°	87	88	90	92	82	91
115°	162	163	162	163	163	159
125°	228	229	228	229	229	203
135°	282	282	283	284	284	217
145°	326	326	326	327	327	203
155°	357	357	356	357	357	165
165°	377	375	375	377	375	106
175°	385	384	384	386	383	37
180°	385	385	385	385	385	



TEST NUMBER: P332541-930

CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	793.8	793.4	793.1	792.8	792.5	791.7	790.4	789.2	787.9	786.7	787.8
5°	791.2	790.6	790.0	789.5	788.9	787.8	786.3	784.7	783.2	781.6	783.2
7.5°	783.7	783.2	782.7	782.1	781.5	780.4	778.7	777.0	775.2	773.5	774.8
10°	777.1	776.7	776.1	775.5	774.9	773.7	771.9	770.1	768.3	766.4	767.5
12.5°	768.6	768.0	767.4	766.9	766.3	765.1	763.1	761.2	759.2	757.2	758.5
15°	753.1	752.5	752.0	751.4	750.8	749.5	747.4	745.3	743.1	741.0	741.8
17.5°	734.4	733.7	733.0	732.3	731.6	730.3	728.2	726.3	724.2	722.3	722.8
20°	720.7	720.0	719.3	718.6	717.9	716.5	714.4	712.2	710.1	708.0	708.4
22.5°	706.0	705.1	704.2	703.2	702.3	700.7	698.6	696.5	694.4	692.3	693.1
25°	682.0	681.0	680.0	679.1	678.1	676.6	674.6	672.6	670.7	668.7	668.9
27.5°	654.6	653.6	652.6	651.6	650.5	649.1	647.3	645.5	643.6	641.8	641.5
30°	636.3	635.2	634.1	632.9	631.9	630.3	628.5	626.6	624.8	623.1	622.5
32.5°	617.0	616.0	615.0	614.0	613.0	611.5	609.6	607.6	605.7	603.7	603.1
35°	586.9	585.9	584.9	583.9	582.9	581.4	579.4	577.5	575.5	573.6	572.5
37.5°	555.0	554.1	553.2	552.3	551.4	549.9	547.8	545.7	543.6	541.4	540.4
40°	534.2	533.0	531.9	530.8	529.7	528.1	525.9	523.8	521.7	519.6	518.2
42.5°	511.8	511.2	510.5	509.8	509.2	507.6	505.3	503.0	500.6	498.3	496.7
45°	479.0	478.0	477.0	476.1	475.1	473.4	471.2	468.9	466.7	464.4	462.8
47.5°	444.6	443.9	443.3	442.5	441.9	440.5	438.5	436.3	434.2	432.2	430.4
50°	421.3	420.7	420.1	419.6	419.0	417.8	415.8	413.8	411.8	409.9	407.9
52.5°	398.4	397.8	397.1	396.4	395.7	394.4	392.2	390.2	388.1	386.0	384.3
55°	362.2	361.8	361.4	361.0	360.6	359.4	357.4	355.4	353.4	351.5	349.8
57.5°	327.8	327.3	326.8	326.3	325.8	324.7	322.7	320.7	318.8	316.8	315.2
60°	303.9	303.2	302.5	301.7	301.1	299.8	298.0	296.1	294.3	292.4	291.2
62.5°	280.5	280.0	279.3	278.8	278.2	276.9	275.0	273.0	271.1	269.1	268.0
65°	245.5	244.8	244.1	243.4	242.7	241.7	240.3	238.8	237.4	236.0	234.6
67.5°	210.3	209.6	209.0	208.3	207.7	206.7	205.3	204.0	202.6	201.2	199.9
70°	188.4	187.4	186.5	185.5	184.5	183.4	182.3	181.2	180.0	178.9	177.8
72.5°	165.1	164.1	163.1	162.1	161.1	160.2	159.3	158.4	157.5	156.5	155.6
75°	130.7	130.0	129.3	128.6	127.8	127.2	126.5	125.7	125.1	124.3	123.8
77.5°	97.8	97.5	97.2	96.9	96.6	96.1	95.5	94.9	94.2	93.7	93.4
80°	78.0	77.6	77.2	76.8	76.3	76.0	75.7	75.4	75.2	74.8	74.6
82.5°	58.8	58.5	58.4	58.1	58.0	57.8	57.8	57.7	57.6	57.6	57.4
85°	34.2	34.2	34.2	34.2	34.2	34.1	33.8	33.6	33.3	33.0	33.0
87.5°	13.4	13.4	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5
90°	0.9	1.5	2.3	3.0	3.7	4.3	4.8	5.3	5.8	6.4	6.7
92.5°	3.7	3.7	3.7	3.8	3.8	4.1	4.6	5.1	5.6	6.1	6.5
95°	15.8	13.7	11.5	9.3	7.2	6.1	6.1	6.2	6.3	6.4	6.7
97.5°	33.7	35.0	36.4	37.7	39.1	36.2	29.0	21.9	14.8	7.6	7.7
100°	47.3	48.4	49.6	50.7	51.9	48.0	39.2	30.3	21.5	12.7	11.6
102.5°	62.5	63.3	64.2	65.0	65.9	65.7	64.6	63.4	62.2	61.1	49.3
105°	86.7	87.1	87.5	87.9	88.3	88.6	88.9	89.3	89.6	89.9	90.5
107.5°	109.3	109.4	109.7	109.8	110.1	110.3	110.8	111.2	111.6	112.1	112.3
110°	124.5	124.7	124.8	125.1	125.2	125.6	125.9	126.3	126.7	127.1	127.2



TEST NUMBER: P332541-930

CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	139.3	139.6	139.9	140.2	140.6	140.9	141.0	141.2	141.4	141.6	141.5
115°	161.9	162.2	162.3	162.5	162.7	162.7	162.7	162.7	162.6	162.5	162.7
117.5°	182.4	182.6	182.9	183.2	183.4	183.6	183.8	183.9	184.0	184.2	184.2
120°	196.2	196.5	196.7	197.0	197.2	197.3	197.3	197.2	197.1	197.1	197.2
122.5°	209.1	209.3	209.5	209.6	209.8	209.9	209.9	210.0	210.1	210.3	210.3
125°	227.6	227.9	228.1	228.4	228.7	228.7	228.6	228.4	228.4	228.2	228.4
127.5°	245.2	245.2	245.2	245.3	245.4	245.6	245.9	246.1	246.5	246.8	246.7
130°	256.4	256.5	256.6	256.7	256.7	256.8	257.0	257.2	257.4	257.6	257.6
132.5°	266.8	266.9	267.0	267.2	267.3	267.4	267.7	267.9	268.2	268.4	268.5
135°	282.3	282.3	282.3	282.2	282.1	282.2	282.5	282.7	283.0	283.2	283.4
137.5°	296.1	296.2	296.2	296.2	296.3	296.4	296.7	296.9	297.3	297.5	297.7
140°	305.2	305.2	305.4	305.5	305.7	305.7	305.9	306.1	306.1	306.3	306.5
142.5°	313.2	313.4	313.6	313.9	314.1	314.3	314.4	314.5	314.5	314.6	314.7
145°	325.6	325.8	326.0	326.2	326.4	326.4	326.4	326.4	326.4	326.4	326.5
147.5°	335.4	335.8	336.1	336.6	336.9	337.0	337.0	336.9	336.8	336.8	336.8
150°	342.6	342.8	343.1	343.4	343.6	343.7	343.6	343.6	343.5	343.5	343.5
152.5°	348.6	348.8	349.0	349.2	349.4	349.4	349.4	349.2	349.1	349.0	349.1
155°	357.0	357.1	357.1	357.2	357.3	357.2	357.0	356.8	356.6	356.4	356.7
157.5°	364.1	364.0	364.0	363.9	363.9	363.8	363.6	363.4	363.1	363.0	363.3
160°	368.3	368.0	367.9	367.7	367.5	367.4	367.3	367.2	367.1	367.0	367.5
162.5°	371.9	371.7	371.5	371.2	371.0	370.8	370.7	370.6	370.6	370.6	371.0
165°	376.6	376.3	375.9	375.6	375.3	375.1	375.1	375.1	375.1	375.1	375.7
167.5°	380.3	379.9	379.6	379.3	379.0	378.8	378.7	378.7	378.6	378.6	379.2
170°	382.4	382.0	381.6	381.2	380.8	380.7	380.7	380.8	380.8	380.9	381.4
172.5°	383.8	383.4	382.9	382.6	382.2	382.0	382.1	382.2	382.2	382.3	382.8
175°	385.2	384.8	384.5	384.1	383.7	383.5	383.6	383.7	383.8	383.8	384.4
177.5°	386.0	385.6	385.2	384.8	384.5	384.3	384.5	384.6	384.7	384.7	385.2
180°	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2



TEST NUMBER: P332541-930

CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	789.0	790.1	791.2	791.7	791.6	791.5	791.4	791.2
5°	784.7	786.3	787.8	788.5	788.1	787.9	787.6	787.3
7.5°	776.0	777.2	778.4	779.0	778.9	778.7	778.5	778.3
10°	768.7	769.8	770.9	771.4	771.0	770.8	770.5	770.2
12.5°	759.8	761.0	762.2	762.6	762.2	761.8	761.5	761.1
15°	742.7	743.6	744.4	744.6	744.2	743.8	743.3	742.9
17.5°	723.3	723.8	724.4	724.5	724.2	723.9	723.7	723.4
20°	708.9	709.3	709.7	709.8	709.5	709.2	709.0	708.7
22.5°	693.8	694.6	695.4	695.5	695.0	694.5	694.0	693.4
25°	669.0	669.1	669.3	669.0	668.5	667.9	667.3	666.8
27.5°	641.2	640.7	640.4	639.9	639.2	638.5	637.8	637.1
30°	621.9	621.3	620.8	620.1	619.4	618.7	618.0	617.3
32.5°	602.3	601.7	601.0	600.3	599.7	598.9	598.2	597.5
35°	571.5	570.5	569.6	568.8	568.0	567.3	566.6	565.9
37.5°	539.3	538.2	537.1	536.1	535.2	534.3	533.4	532.4
40°	516.8	515.4	514.0	512.9	512.2	511.5	510.8	510.1
42.5°	495.0	493.3	491.7	490.6	490.2	489.8	489.3	488.8
45°	461.3	459.7	458.2	457.2	456.8	456.4	455.9	455.5
47.5°	428.7	426.9	425.2	423.8	422.7	421.6	420.5	419.5
50°	405.9	403.9	401.9	400.6	399.7	398.8	398.0	397.1
52.5°	382.5	380.7	379.0	377.6	376.5	375.4	374.4	373.3
55°	348.1	346.4	344.7	343.4	342.6	341.8	340.9	340.1
57.5°	313.6	312.0	310.4	309.2	308.3	307.5	306.7	305.9
60°	289.9	288.7	287.4	286.4	285.7	285.0	284.3	283.6
62.5°	266.8	265.6	264.5	263.6	262.9	262.2	261.5	260.7
65°	233.2	231.8	230.4	229.3	228.6	227.9	227.2	226.5
67.5°	198.5	197.2	195.8	195.0	194.9	194.7	194.4	194.3
70°	176.7	175.5	174.4	173.7	173.2	172.8	172.4	171.9
72.5°	154.7	153.8	153.0	152.3	151.9	151.5	151.1	150.6
75°	123.2	122.6	122.1	121.7	121.6	121.5	121.3	121.2
77.5°	93.3	93.1	92.9	92.7	92.3	92.0	91.6	91.2
80°	74.3	74.0	73.7	73.5	73.4	73.2	73.1	73.0
82.5°	57.2	57.1	56.9	56.7	56.7	56.5	56.3	56.2
85°	33.0	33.0	33.0	32.9	32.8	32.6	32.5	32.4
87.5°	13.6	13.7	13.8	13.8	13.9	13.9	13.9	13.9
90°	7.1	7.5	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	6.8	7.3	7.7	7.8	7.9	7.9	7.9	8.0
95°	7.1	7.5	7.9	8.1	8.2	8.2	8.3	8.3
97.5°	7.7	7.7	7.7	7.8	7.9	7.9	8.0	8.1
100°	10.5	9.4	8.3	7.8	7.9	7.9	8.0	8.1
102.5°	37.6	25.8	14.1	8.2	8.2	8.2	8.3	8.3
105°	91.1	91.6	92.2	91.3	89.0	86.7	84.4	82.1
107.5°	112.7	112.9	113.2	113.5	113.7	114.0	114.2	114.5
110°	127.3	127.4	127.6	127.8	127.9	128.2	128.3	128.5





TEST NUMBER: P332541-930

CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	141.5	141.5	141.5	141.6	141.9	142.1	142.4	142.6
115°	162.7	162.9	163.1	163.1	163.1	163.1	163.1	163.1
117.5°	184.1	184.1	184.1	184.0	184.0	184.0	184.0	183.9
120°	197.3	197.5	197.6	197.6	197.5	197.3	197.2	197.1
122.5°	210.3	210.4	210.5	210.5	210.3	210.3	210.1	210.0
125°	228.6	228.8	228.9	229.1	229.2	229.3	229.3	229.3
127.5°	246.7	246.6	246.6	246.5	246.5	246.5	246.4	246.4
130°	257.7	257.8	257.9	257.9	257.9	257.9	257.9	257.9
132.5°	268.6	268.6	268.7	268.7	268.6	268.6	268.6	268.5
135°	283.5	283.6	283.7	283.9	284.0	284.1	284.3	284.4
137.5°	297.8	298.0	298.1	298.2	298.1	298.1	298.0	298.0
140°	306.6	306.9	307.0	307.2	307.3	307.3	307.4	307.4
142.5°	314.9	315.0	315.1	315.2	315.3	315.3	315.3	315.3
145°	326.6	326.7	326.7	326.8	326.9	327.1	327.2	327.3
147.5°	336.9	337.0	337.0	337.0	337.1	337.1	337.2	337.3
150°	343.5	343.5	343.5	343.5	343.6	343.6	343.6	343.7
152.5°	349.2	349.3	349.4	349.4	349.4	349.4	349.4	349.3
155°	356.9	357.2	357.4	357.5	357.3	357.1	356.9	356.7
157.5°	363.6	363.9	364.3	364.3	363.9	363.6	363.3	363.0
160°	367.9	368.3	368.6	368.6	368.3	367.9	367.5	367.0
162.5°	371.3	371.7	372.1	372.0	371.6	371.2	370.7	370.3
165°	376.2	376.7	377.2	377.2	376.6	376.0	375.4	374.9
167.5°	379.8	380.3	380.8	380.8	380.2	379.5	378.9	378.3
170°	382.0	382.5	382.9	382.9	382.3	381.6	381.0	380.3
172.5°	383.4	383.8	384.3	384.3	383.6	382.9	382.2	381.5
175°	385.0	385.6	386.1	386.0	385.2	384.5	383.7	382.9
177.5°	385.6	386.0	386.5	386.3	385.7	385.1	384.5	383.8
180°	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2

(END OF REPORT)