

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332543-930

Luminaire Tested: **SA4XXDIP-C575D365U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332543-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C575D365U930-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3099.3 lumens  
Efficiency: N/A  
Efficacy: 112.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332543-930  
CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332543-930

CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66				
1	101	97	93	89	95	91	88	84	81	78	76	71	69	67	62	61	59	55				
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50	46				
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43	39				
4	77	66	58	51	72	62	55	49	56	50	45	49	45	41	43	40	37	34				
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29				
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28	26				
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	23				
8	56	43	36	30	53	41	34	29	37	31	27	33	28	25	30	26	23	20				
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18				
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	21	19	17				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6391	6391	6391
5°	6412	6334	6380
10°	6370	6283	6314
15°	6294	6193	6209
20°	6192	6082	6088
25°	6075	5956	5940
30°	5931	5808	5754
35°	5784	5653	5577
40°	5630	5476	5376
45°	5469	5302	5200
50°	5291	5148	4987
55°	5098	4947	4787
60°	4907	4721	4579
65°	4690	4508	4327
70°	4447	4223	4057
75°	4077	3877	3780
80°	3626	3477	3394
85°	3168	3057	3001



TEST NUMBER: P332543-930

CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.6	2.4
10°-20°	210.1	6.8
20°-30°	309.2	10.0
30°-40°	359.5	11.6
40°-50°	359.5	11.6
50°-60°	314.5	10.1
60°-70°	233.5	7.5
70°-80°	132.7	4.3
80°-90°	39.1	1.3
90°-100°	105.9	3.4
100°-110°	220.5	7.1
110°-120°	197.5	6.4
120°-130°	166.1	5.4
130°-140°	138.5	4.5
140°-150°	105.8	3.4
150°-160°	74.4	2.4
160°-170°	43.7	1.4
170°-180°	14.2	0.5
0°-30°	593.9	19.2
0°-40°	953.4	30.8
0°-60°	1627.3	52.5
0°-90°	2032.6	65.6
90°-120°	523.9	16.9
90°-150°	934.3	30.1
90°-180°	1067.0	34.4
0°-180°	3099.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	792	792	792	792	792	
5°	791	788	782	788	787	75
15°	753	750	741	744	743	212
25°	682	677	669	669	667	314
35°	587	582	574	569	566	367
45°	479	474	464	458	456	369
55°	362	360	352	344	340	324
65°	246	242	236	230	226	243
75°	131	128	124	122	121	139
85°	34	34	33	33	32	38
90°	0	2	5	6	6	2
95°	10	30	235	116	70	11
105°	34	49	189	407	405	36
115°	59	74	169	324	389	59
125°	83	98	168	276	311	74
135°	98	117	166	245	278	76
145°	113	130	165	206	227	71
155°	129	139	161	182	190	59
165°	140	145	154	163	166	40
175°	146	147	148	150	149	14
180°	147	147	147	147	147	



TEST NUMBER: P332543-930

CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	793.8	793.4	793.1	792.8	792.5	791.7	790.4	789.2	787.9	786.7	787.8
5°	791.2	790.6	790.0	789.5	788.9	787.8	786.3	784.7	783.2	781.6	783.2
7.5°	783.7	783.2	782.7	782.1	781.5	780.4	778.7	777.0	775.2	773.5	774.8
10°	777.1	776.7	776.1	775.5	774.9	773.7	771.9	770.1	768.3	766.4	767.5
12.5°	768.6	768.0	767.4	766.9	766.3	765.1	763.1	761.2	759.2	757.2	758.5
15°	753.1	752.5	752.0	751.4	750.8	749.5	747.4	745.3	743.1	741.0	741.8
17.5°	734.4	733.7	733.0	732.3	731.6	730.3	728.2	726.3	724.2	722.3	722.8
20°	720.7	720.0	719.3	718.6	717.9	716.5	714.4	712.2	710.1	708.0	708.4
22.5°	706.0	705.1	704.2	703.2	702.3	700.7	698.6	696.5	694.4	692.3	693.1
25°	682.0	681.0	680.0	679.1	678.1	676.6	674.6	672.6	670.7	668.7	668.9
27.5°	654.6	653.6	652.6	651.6	650.5	649.1	647.3	645.5	643.6	641.8	641.5
30°	636.3	635.2	634.1	632.9	631.9	630.3	628.5	626.6	624.8	623.1	622.5
32.5°	617.0	616.0	615.0	614.0	613.0	611.5	609.6	607.6	605.7	603.7	603.1
35°	586.9	585.9	584.9	583.9	582.9	581.4	579.4	577.5	575.5	573.6	572.5
37.5°	555.0	554.1	553.2	552.3	551.4	549.9	547.8	545.7	543.6	541.4	540.4
40°	534.2	533.0	531.9	530.8	529.7	528.1	525.9	523.8	521.7	519.6	518.2
42.5°	511.8	511.2	510.5	509.8	509.2	507.6	505.3	503.0	500.6	498.3	496.7
45°	479.0	478.0	477.0	476.1	475.1	473.4	471.2	468.9	466.7	464.4	462.8
47.5°	444.6	443.9	443.3	442.5	441.9	440.5	438.5	436.3	434.2	432.2	430.4
50°	421.3	420.7	420.1	419.6	419.0	417.8	415.8	413.8	411.8	409.9	407.9
52.5°	398.4	397.8	397.1	396.4	395.7	394.4	392.2	390.2	388.1	386.0	384.3
55°	362.2	361.8	361.4	361.0	360.6	359.4	357.4	355.4	353.4	351.5	349.8
57.5°	327.8	327.3	326.8	326.3	325.8	324.7	322.7	320.7	318.8	316.8	315.2
60°	303.9	303.2	302.5	301.7	301.1	299.8	298.0	296.1	294.3	292.4	291.2
62.5°	280.5	280.0	279.3	278.8	278.2	276.9	275.0	273.0	271.1	269.1	268.0
65°	245.5	244.8	244.1	243.4	242.7	241.7	240.3	238.8	237.4	236.0	234.6
67.5°	210.3	209.6	209.0	208.3	207.7	206.7	205.3	204.0	202.6	201.2	199.9
70°	188.4	187.4	186.5	185.5	184.5	183.4	182.3	181.2	180.0	178.9	177.8
72.5°	165.1	164.1	163.1	162.1	161.1	160.2	159.3	158.4	157.5	156.5	155.6
75°	130.7	130.0	129.3	128.6	127.8	127.2	126.5	125.7	125.1	124.3	123.8
77.5°	97.8	97.5	97.2	96.9	96.6	96.1	95.5	94.9	94.2	93.7	93.4
80°	78.0	77.6	77.2	76.8	76.3	76.0	75.7	75.4	75.2	74.8	74.6
82.5°	58.8	58.5	58.4	58.1	58.0	57.8	57.8	57.7	57.6	57.6	57.4
85°	34.2	34.2	34.2	34.2	34.2	34.1	33.8	33.6	33.3	33.0	33.0
87.5°	13.3	13.3	13.3	13.3	13.2	13.1	13.3	13.2	13.2	13.2	13.1
90°	0.3	0.9	1.7	2.0	2.3	2.3	4.0	4.0	4.6	5.2	4.9
92.5°	3.3	4.8	7.5	11.0	15.2	21.2	35.9	58.2	80.0	91.4	76.1
95°	9.5	10.4	13.3	17.0	23.9	36.0	61.1	108.4	177.2	234.8	241.5
97.5°	17.0	17.0	19.6	23.0	28.9	39.1	58.4	97.4	165.8	247.4	303.4
100°	21.9	21.9	23.9	27.4	32.9	42.1	59.1	91.6	150.4	231.7	305.4
102.5°	26.5	27.0	28.8	32.0	37.3	46.0	61.4	90.0	140.1	212.1	288.1
105°	33.8	34.6	36.0	39.5	44.7	53.0	66.9	90.7	131.1	189.0	256.7
107.5°	41.7	42.2	43.7	47.4	52.3	60.6	73.2	95.1	129.5	176.1	231.4
110°	47.0	47.5	49.0	52.4	57.6	65.4	78.1	98.2	130.0	171.7	218.7



TEST NUMBER: P332543-930

CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	52.0	52.6	54.3	57.5	62.7	70.4	82.7	101.7	131.3	169.7	211.6
115°	59.4	60.3	62.2	65.1	70.6	78.4	89.9	107.2	134.0	168.6	204.9
117.5°	66.9	67.8	69.5	72.7	77.9	85.9	96.9	112.8	136.8	168.3	201.9
120°	72.1	72.6	74.6	77.8	82.7	90.7	101.7	116.7	138.9	168.3	200.2
122.5°	76.6	77.2	79.2	82.2	87.6	95.4	106.3	120.4	141.0	168.0	198.4
125°	82.7	83.8	85.6	88.8	94.2	102.3	112.7	125.9	144.1	167.7	195.3
127.5°	88.1	88.9	91.1	94.7	100.4	108.5	118.5	130.7	146.6	167.1	191.3
130°	91.1	92.2	94.5	98.8	104.3	112.7	122.5	133.7	148.4	166.8	188.7
132.5°	94.1	95.0	98.0	102.1	108.0	115.9	125.7	136.7	150.0	166.6	186.5
135°	98.2	99.4	102.3	107.2	113.2	120.7	130.2	140.6	152.5	166.2	183.0
137.5°	102.5	103.5	106.7	111.4	117.6	124.8	133.7	143.4	153.8	166.2	180.0
140°	105.5	106.3	109.5	114.4	120.4	127.3	136.0	145.2	155.0	166.0	178.4
142.5°	108.7	109.6	112.5	117.2	122.9	129.6	138.1	146.6	156.0	166.0	177.0
145°	113.2	114.1	117.0	121.0	126.5	132.8	140.3	148.1	156.5	165.4	174.6
147.5°	118.4	118.6	121.2	125.3	129.9	135.6	142.6	149.4	156.8	164.4	172.5
150°	121.6	121.9	124.2	127.7	132.0	137.5	143.8	150.1	156.8	163.6	170.9
152.5°	124.6	124.7	126.9	130.2	134.0	139.1	144.7	150.6	156.3	162.5	169.0
155°	128.8	129.1	130.9	133.7	136.9	141.2	146.1	151.0	155.6	160.8	166.2
157.5°	132.9	132.9	134.5	136.7	139.5	142.9	147.1	151.0	154.8	159.0	163.5
160°	135.4	135.4	136.6	138.6	140.9	144.1	147.6	151.0	154.2	157.6	161.3
162.5°	137.7	137.5	138.4	140.2	142.3	144.8	148.0	151.0	153.4	156.2	159.6
165°	140.3	140.3	140.9	142.4	143.8	145.5	148.1	150.4	152.1	154.2	156.5
167.5°	142.9	142.6	142.9	144.0	144.8	146.2	148.1	149.7	150.7	152.1	153.7
170°	144.1	143.8	144.1	145.0	145.5	146.3	147.8	149.3	149.9	150.7	151.9
172.5°	145.2	145.0	145.0	145.6	145.9	146.6	147.6	148.8	149.0	149.3	150.3
175°	146.3	146.1	146.1	146.3	146.7	146.7	147.2	148.1	147.8	147.8	148.4
177.5°	146.9	146.7	146.4	146.7	146.7	146.7	146.9	147.3	146.9	146.9	147.2
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332543-930

CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	789.0	790.1	791.2	791.7	791.6	791.5	791.4	791.2
5°	784.7	786.3	787.8	788.5	788.1	787.9	787.6	787.3
7.5°	776.0	777.2	778.4	779.0	778.9	778.7	778.5	778.3
10°	768.7	769.8	770.9	771.4	771.0	770.8	770.5	770.2
12.5°	759.8	761.0	762.2	762.6	762.2	761.8	761.5	761.1
15°	742.7	743.6	744.4	744.6	744.2	743.8	743.3	742.9
17.5°	723.3	723.8	724.4	724.5	724.2	723.9	723.7	723.4
20°	708.9	709.3	709.7	709.8	709.5	709.2	709.0	708.7
22.5°	693.8	694.6	695.4	695.5	695.0	694.5	694.0	693.4
25°	669.0	669.1	669.3	669.0	668.5	667.9	667.3	666.8
27.5°	641.2	640.7	640.4	639.9	639.2	638.5	637.8	637.1
30°	621.9	621.3	620.8	620.1	619.4	618.7	618.0	617.3
32.5°	602.3	601.7	601.0	600.3	599.7	598.9	598.2	597.5
35°	571.5	570.5	569.6	568.8	568.0	567.3	566.6	565.9
37.5°	539.3	538.2	537.1	536.1	535.2	534.3	533.4	532.4
40°	516.8	515.4	514.0	512.9	512.2	511.5	510.8	510.1
42.5°	495.0	493.3	491.7	490.6	490.2	489.8	489.3	488.8
45°	461.3	459.7	458.2	457.2	456.8	456.4	455.9	455.5
47.5°	428.7	426.9	425.2	423.8	422.7	421.6	420.5	419.5
50°	405.9	403.9	401.9	400.6	399.7	398.8	398.0	397.1
52.5°	382.5	380.7	379.0	377.6	376.5	375.4	374.4	373.3
55°	348.1	346.4	344.7	343.4	342.6	341.8	340.9	340.1
57.5°	313.6	312.0	310.4	309.2	308.3	307.5	306.7	305.9
60°	289.9	288.7	287.4	286.4	285.7	285.0	284.3	283.6
62.5°	266.8	265.6	264.5	263.6	262.9	262.2	261.5	260.7
65°	233.2	231.8	230.4	229.3	228.6	227.9	227.2	226.5
67.5°	198.5	197.2	195.8	195.0	194.9	194.7	194.4	194.3
70°	176.7	175.5	174.4	173.7	173.2	172.8	172.4	171.9
72.5°	154.7	153.8	153.0	152.3	151.9	151.5	151.1	150.6
75°	123.2	122.6	122.1	121.7	121.6	121.5	121.3	121.2
77.5°	93.3	93.1	92.9	92.7	92.3	92.0	91.6	91.2
80°	74.3	74.0	73.7	73.5	73.4	73.2	73.1	73.0
82.5°	57.2	57.1	56.9	56.7	56.7	56.5	56.3	56.2
85°	33.0	33.0	33.0	32.9	32.8	32.6	32.5	32.4
87.5°	13.2	13.3	13.4	13.4	13.4	13.5	13.4	13.4
90°	5.2	5.5	5.8	5.8	6.0	6.4	6.0	6.0
92.5°	56.6	42.6	33.9	28.1	24.7	23.2	22.2	22.2
95°	213.5	168.8	130.2	102.3	88.1	79.2	74.0	70.3
97.5°	315.4	298.9	270.7	240.6	219.9	202.6	194.0	187.9
100°	347.5	353.3	339.2	317.8	292.8	275.2	266.5	264.2
102.5°	345.9	374.5	378.5	369.7	354.3	341.6	332.5	330.6
105°	322.7	372.6	401.1	412.9	413.5	411.2	407.2	405.4
107.5°	289.8	342.9	383.0	408.8	423.0	429.6	432.4	433.2
110°	270.0	319.8	361.7	393.3	413.8	425.9	431.0	433.7





TEST NUMBER: P332543-930

CATALOG NUMBER: SA4XXDIP-C575D365U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	255.4	299.5	339.0	370.7	394.0	408.6	415.9	420.0
115°	240.9	276.3	310.1	337.7	360.4	377.7	387.0	389.3
117.5°	233.7	263.1	289.6	313.1	332.5	347.0	356.3	358.1
120°	230.5	257.3	280.4	300.8	317.2	330.0	337.5	340.6
122.5°	227.7	253.6	274.6	292.5	306.4	317.2	323.6	326.8
125°	223.1	247.8	267.7	283.6	295.1	303.5	308.9	310.6
127.5°	217.3	240.9	260.8	275.8	287.4	294.8	299.5	301.2
130°	212.6	235.5	255.0	270.3	282.1	289.3	293.9	295.6
132.5°	207.8	229.2	248.3	263.6	275.2	283.3	287.7	289.4
135°	201.1	219.9	237.4	251.8	263.3	271.4	276.1	277.8
137.5°	195.1	210.9	225.8	238.7	249.6	257.5	261.3	263.3
140°	191.6	205.1	218.1	230.2	240.4	246.6	250.7	253.0
142.5°	188.4	200.3	211.4	221.9	230.9	236.8	240.4	241.9
145°	183.8	193.6	202.3	210.3	217.5	222.4	225.3	226.7
147.5°	180.1	187.8	194.8	201.1	206.4	210.7	212.8	213.4
150°	177.8	184.4	190.2	195.3	200.0	203.7	205.5	205.7
152.5°	175.3	181.0	186.3	190.5	194.4	197.5	198.5	198.9
155°	171.5	176.0	180.3	183.8	186.7	189.0	189.9	189.9
157.5°	167.4	171.2	174.9	177.7	179.8	181.6	182.1	182.1
160°	164.9	168.0	171.1	173.5	175.2	176.9	177.2	177.2
162.5°	162.3	165.0	167.5	169.6	170.8	172.5	172.8	172.6
165°	158.7	160.5	162.5	164.0	165.1	166.2	166.0	165.7
167.5°	155.4	156.7	158.3	159.1	159.7	160.5	160.5	160.2
170°	153.3	154.2	155.3	156.2	156.8	157.0	156.8	156.8
172.5°	151.5	152.1	152.8	153.4	153.8	154.0	153.8	153.3
175°	149.0	149.3	149.9	149.9	149.9	150.4	149.9	149.3
177.5°	147.3	147.6	147.6	147.8	147.6	147.8	147.3	146.9
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7

(END OF REPORT)