

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331355-940

Luminaire Tested: **SA2XXDIP-C675D725U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331355-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D725U940-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4721.4 lumens  
Efficiency: N/A  
Efficacy: 102.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331355-940  
CATALOG NUMBER: SA2XXDIP-C675D725U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331355-940

CATALOG NUMBER: SA2XXDIP-C675D725U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	50	49	48	43				
2	89	82	76	70	82	76	70	66	64	60	57	54	51	49	44	42	41	36				
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31				
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23				
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20				
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15285	15285	15285
5°	15344	15123	15211
10°	15252	14969	15044
15°	15064	14775	14760
20°	14795	14483	14467
25°	14530	14125	14125
30°	14188	13798	13679
35°	13868	13403	13204
40°	13468	13009	12760
45°	13075	12618	12305
50°	12645	12210	11776
55°	12197	11738	11299
60°	11699	11170	10756
65°	11163	10609	10120
70°	10485	9928	9456
75°	9538	9145	8914
80°	8461	8210	7782
85°	6928	6576	5891



TEST NUMBER: P331355-940

CATALOG NUMBER: SA2XXDIP-C675D725U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.0	1.9
10°-20°	250.5	5.3
20°-30°	368.2	7.8
30°-40°	427.7	9.1
40°-50°	427.2	9.0
50°-60°	372.6	7.9
60°-70°	275.5	5.8
70°-80°	156.0	3.3
80°-90°	45.3	1.0
90°-100°	52.3	1.1
100°-110°	162.5	3.4
110°-120°	277.9	5.9
120°-130°	365.4	7.7
130°-140°	410.1	8.7
140°-150°	402.1	8.5
150°-160°	337.3	7.1
160°-170°	223.7	4.7
170°-180°	78.2	1.7
0°-30°	707.7	15.0
0°-40°	1135.4	24.0
0°-60°	1935.1	41.0
0°-90°	2411.9	51.1
90°-120°	492.7	10.4
90°-150°	1670.3	35.4
90°-180°	2309.0	48.9
0°-180°	4721.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	947	943	933	940	938	90
15°	901	895	884	887	883	254
25°	816	808	793	794	793	375
35°	704	694	680	675	670	439
45°	573	566	553	543	539	442
55°	433	428	417	406	401	387
65°	292	286	278	270	265	289
75°	153	151	147	142	143	163
85°	37	36	36	33	32	43
90°	1	9	24	23	24	4
95°	36	43	45	45	43	42
105°	150	152	153	155	155	158
115°	279	283	282	281	279	276
125°	406	412	410	408	407	362
135°	525	532	534	533	531	405
145°	637	642	646	647	644	398
155°	728	730	732	736	734	335
165°	792	792	792	796	793	223
175°	825	822	821	825	822	78
180°	826	826	826	826	826	



TEST NUMBER: P331355-940

CATALOG NUMBER: SA2XXDIP-C675D725U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	951.1	950.3	949.5	948.7	947.9	946.6	944.8	943.0	941.2	939.4	941.0
5°	946.7	945.9	945.1	944.3	943.5	942.0	939.8	937.5	935.3	933.1	934.7
7.5°	938.3	937.1	935.9	934.6	933.4	931.6	929.3	927.0	924.8	922.5	924.1
10°	930.3	928.9	927.5	926.0	924.7	922.7	920.3	917.9	915.4	913.0	914.6
12.5°	919.4	918.2	916.9	915.6	914.4	912.6	910.1	907.7	905.3	902.9	904.0
15°	901.2	900.0	898.8	897.6	896.3	894.4	891.8	889.1	886.5	883.9	884.8
17.5°	877.9	876.6	875.5	874.2	873.1	871.1	868.4	865.8	863.1	860.4	861.4
20°	861.1	860.0	858.7	857.5	856.3	854.3	851.4	848.6	845.8	842.9	843.6
22.5°	844.4	842.7	841.0	839.3	837.6	835.4	832.8	830.1	827.4	824.7	824.8
25°	815.6	814.0	812.4	810.7	809.1	806.6	803.2	799.8	796.3	792.9	793.3
27.5°	782.8	781.4	780.0	778.5	777.0	775.0	772.2	769.5	766.8	764.1	763.5
30°	761.0	759.4	757.8	756.2	754.6	752.2	749.2	746.2	743.2	740.1	739.5
32.5°	737.7	736.4	735.1	733.8	732.5	730.3	727.1	723.9	720.7	717.5	716.4
35°	703.6	701.7	699.6	697.6	695.5	692.9	689.7	686.4	683.2	680.0	678.8
37.5°	665.2	663.4	661.6	659.9	658.2	655.6	652.4	649.2	646.0	642.7	641.1
40°	639.0	637.4	635.8	634.2	632.6	630.2	626.9	623.7	620.5	617.2	615.4
42.5°	613.6	611.9	610.3	608.7	607.1	604.7	601.4	598.2	594.9	591.7	589.7
45°	572.6	571.1	569.7	568.4	566.9	564.7	561.7	558.7	555.6	552.6	550.4
47.5°	531.8	530.5	529.1	527.8	526.5	524.2	521.0	517.9	514.8	511.6	509.3
50°	503.4	502.4	501.4	500.3	499.4	497.4	494.6	491.8	488.9	486.1	483.3
52.5°	475.7	474.4	473.1	471.7	470.4	468.4	465.7	463.1	460.4	457.7	455.4
55°	433.3	432.1	430.9	429.6	428.5	426.6	424.2	421.8	419.4	417.0	414.5
57.5°	390.7	389.8	388.8	387.8	386.8	385.0	382.4	379.7	377.0	374.3	371.9
60°	362.3	361.5	360.7	359.9	359.1	357.2	354.5	351.6	348.7	345.9	343.7
62.5°	334.7	333.3	332.1	330.7	329.5	327.7	325.6	323.3	321.2	319.0	316.9
65°	292.2	291.0	289.8	288.6	287.3	285.7	283.7	281.7	279.6	277.7	275.8
67.5°	249.1	248.1	247.1	246.1	245.1	243.8	241.9	240.1	238.4	236.5	235.1
70°	222.1	221.3	220.5	219.7	218.9	217.6	215.7	213.9	212.1	210.3	208.8
72.5°	194.5	193.6	192.8	192.0	191.2	190.2	189.0	187.9	186.7	185.5	184.1
75°	152.9	152.5	152.1	151.7	151.3	150.6	149.6	148.6	147.6	146.6	145.3
77.5°	115.8	115.1	114.4	113.7	113.1	112.5	112.1	111.6	111.3	110.8	110.3
80°	91.0	90.9	90.6	90.4	90.2	89.9	89.5	89.1	88.7	88.3	87.7
82.5°	67.8	67.7	67.7	67.6	67.6	67.4	67.1	67.0	66.7	66.4	65.7
85°	37.4	37.1	36.9	36.7	36.5	36.3	36.1	35.9	35.7	35.5	34.9
87.5°	13.3	13.3	13.4	13.4	13.5	13.6	14.0	14.4	14.7	15.1	14.5
90°	0.7	2.6	4.5	6.2	8.1	10.8	14.2	17.6	21.0	24.4	24.1
92.5°	12.4	13.7	15.2	16.5	17.8	18.9	19.7	20.5	21.4	22.2	22.2
95°	36.2	37.8	39.3	40.9	42.4	43.3	43.7	44.0	44.3	44.6	44.6
97.5°	66.3	67.6	68.9	70.3	71.7	72.7	73.2	73.8	74.4	75.0	75.0
100°	88.5	89.8	91.0	92.2	93.5	94.3	94.8	95.2	95.7	96.2	96.2
102.5°	111.9	112.9	114.0	114.9	115.9	116.7	117.3	117.9	118.4	119.0	119.1
105°	149.9	150.3	150.8	151.2	151.7	152.1	152.4	152.8	153.0	153.4	153.6
107.5°	188.1	188.8	189.4	190.1	190.7	191.1	191.1	191.1	191.1	191.1	191.3
110°	212.6	213.5	214.5	215.3	216.3	216.8	216.8	216.8	216.8	216.8	216.8



TEST NUMBER: P331355-940

CATALOG NUMBER: SA2XXDIP-C675D725U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	239.3	240.3	241.2	242.1	243.1	243.4	243.3	243.3	243.1	243.0	242.6
115°	278.8	279.7	280.6	281.6	282.5	282.9	282.5	282.2	281.9	281.6	281.4
117.5°	318.1	319.3	320.6	321.8	323.1	323.2	322.4	321.6	320.7	319.8	319.4
120°	344.3	345.5	346.8	348.0	349.3	349.3	348.0	346.8	345.5	344.3	344.3
122.5°	368.3	369.8	371.3	372.7	374.3	374.5	373.7	372.8	371.9	371.0	370.7
125°	405.6	407.1	408.4	409.8	411.3	411.7	411.3	410.7	410.3	409.8	409.4
127.5°	442.0	443.8	445.6	447.4	449.1	449.7	449.2	448.6	448.0	447.5	446.9
130°	464.9	466.9	469.0	470.9	473.0	473.8	473.5	473.1	472.9	472.6	472.3
132.5°	490.5	492.2	493.8	495.4	497.1	497.9	498.0	498.1	498.1	498.2	497.6
135°	524.9	526.6	528.2	529.9	531.6	532.6	533.0	533.2	533.6	533.9	533.8
137.5°	561.0	562.3	563.7	565.2	566.5	567.4	567.8	568.2	568.6	569.0	568.9
140°	582.7	584.1	585.5	586.8	588.3	589.3	590.1	590.9	591.7	592.5	592.5
142.5°	605.0	606.4	607.8	609.2	610.6	611.5	612.1	612.6	613.1	613.7	613.8
145°	637.0	638.1	639.3	640.3	641.4	642.4	643.4	644.3	645.2	646.1	646.3
147.5°	665.7	666.9	668.2	669.5	670.8	671.8	672.4	673.1	673.7	674.3	674.6
150°	685.2	686.1	687.0	688.0	688.8	689.6	690.3	690.9	691.5	692.1	692.6
152.5°	702.4	703.4	704.3	705.3	706.1	706.9	707.8	708.5	709.2	710.0	710.5
155°	728.3	728.8	729.3	729.8	730.2	730.7	731.1	731.6	732.1	732.5	733.3
157.5°	750.6	750.8	751.2	751.4	751.8	752.1	752.3	752.6	752.9	753.1	754.2
160°	763.9	764.2	764.6	764.8	765.2	765.4	765.5	765.7	765.9	766.0	767.0
162.5°	776.1	776.2	776.3	776.3	776.4	776.5	776.7	776.9	777.0	777.1	778.2
165°	792.5	792.4	792.2	792.0	791.8	791.8	791.8	791.8	791.8	791.8	792.9
167.5°	806.1	805.7	805.2	804.8	804.3	804.1	804.1	804.0	804.0	803.9	805.0
170°	813.4	813.0	812.4	812.0	811.5	811.2	811.1	810.9	810.7	810.6	811.7
172.5°	818.4	818.0	817.5	817.0	816.5	816.3	816.1	815.9	815.8	815.6	816.7
175°	824.6	824.1	823.6	823.1	822.7	822.3	822.0	821.7	821.4	821.1	822.2
177.5°	827.1	826.7	826.3	825.9	825.5	825.3	825.0	824.7	824.5	824.3	825.0
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331355-940

CATALOG NUMBER: SA2XXDIP-C675D725U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	942.6	944.3	945.9	946.6	946.2	945.9	945.6	945.3
5°	936.3	937.9	939.5	940.1	939.8	939.3	939.0	938.5
7.5°	925.8	927.4	929.0	929.5	929.1	928.7	928.3	927.8
10°	916.2	917.9	919.5	920.0	919.4	918.8	918.2	917.6
12.5°	905.1	906.2	907.4	907.7	907.2	906.9	906.4	906.0
15°	885.6	886.4	887.2	887.1	886.0	885.0	884.0	883.0
17.5°	862.3	863.2	864.2	864.2	863.2	862.2	861.2	860.2
20°	844.2	844.8	845.3	845.3	844.5	843.6	842.8	842.0
22.5°	825.0	825.1	825.2	825.0	824.6	824.0	823.6	823.1
25°	793.7	794.1	794.5	794.5	794.1	793.7	793.3	792.9
27.5°	762.9	762.3	761.7	760.9	759.9	758.9	758.0	757.0
30°	738.9	738.2	737.6	736.9	736.1	735.3	734.5	733.7
32.5°	715.3	714.3	713.1	712.2	711.4	710.6	709.7	708.9
35°	677.6	676.4	675.1	674.0	673.1	672.0	671.0	669.9
37.5°	639.7	638.2	636.7	635.4	634.5	633.5	632.6	631.6
40°	613.6	611.7	609.9	608.6	607.8	607.0	606.2	605.4
42.5°	587.7	585.8	583.8	582.2	581.0	580.0	578.8	577.7
45°	548.1	545.9	543.7	542.2	541.4	540.6	539.8	538.9
47.5°	506.9	504.5	502.2	500.4	499.3	498.1	497.0	495.8
50°	480.5	477.6	474.7	472.9	471.8	470.8	469.8	468.8
52.5°	453.0	450.7	448.4	446.5	445.1	443.8	442.5	441.1
55°	412.1	409.7	407.2	405.5	404.5	403.5	402.4	401.4
57.5°	369.5	367.1	364.8	363.2	362.4	361.7	360.9	360.1
60°	341.4	339.2	337.0	335.6	335.0	334.4	333.8	333.1
62.5°	314.9	312.8	310.8	309.3	308.5	307.7	307.0	306.2
65°	274.0	272.2	270.4	268.9	268.0	266.9	265.9	264.9
67.5°	233.6	232.3	230.9	229.7	228.9	228.1	227.3	226.5
70°	207.4	206.1	204.6	203.5	202.7	201.9	201.1	200.3
72.5°	182.7	181.3	179.9	178.8	178.2	177.5	176.9	176.2
75°	144.1	142.9	141.7	141.3	141.7	142.1	142.5	142.9
77.5°	109.7	109.1	108.4	107.9	107.3	106.7	106.2	105.6
80°	87.1	86.5	85.9	85.3	85.0	84.5	84.2	83.7
82.5°	64.9	64.1	63.4	63.0	62.9	62.8	62.7	62.6
85°	34.3	33.7	33.1	32.6	32.5	32.3	32.1	31.8
87.5°	14.0	13.5	12.8	12.6	12.4	12.3	12.1	12.0
90°	23.8	23.5	23.2	23.1	23.3	23.4	23.5	23.7
92.5°	22.3	22.4	22.4	22.5	22.5	22.6	22.6	22.6
95°	44.6	44.6	44.6	44.5	44.1	43.9	43.5	43.2
97.5°	75.0	75.0	75.0	75.0	75.0	74.9	74.9	74.8
100°	96.2	96.2	96.2	96.1	95.9	95.8	95.7	95.5
102.5°	119.3	119.4	119.6	119.5	119.4	119.2	119.0	118.9
105°	154.0	154.3	154.6	154.7	154.7	154.7	154.7	154.7
107.5°	191.4	191.5	191.6	191.4	190.6	189.9	189.2	188.5
110°	216.8	216.8	216.8	216.5	216.1	215.6	215.2	214.6





TEST NUMBER: P331355-940

CATALOG NUMBER: SA2XXDIP-C675D725U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	242.2	241.8	241.5	241.1	240.8	240.4	240.1	239.8
115°	281.2	281.2	281.0	280.6	280.2	279.7	279.3	278.8
117.5°	319.1	318.7	318.3	317.9	317.4	316.9	316.5	316.0
120°	344.3	344.3	344.3	344.1	343.6	343.1	342.7	342.2
122.5°	370.3	370.0	369.6	369.3	368.9	368.5	368.2	367.9
125°	408.9	408.4	408.0	407.7	407.5	407.3	407.2	407.1
127.5°	446.4	445.8	445.2	444.7	444.3	443.7	443.3	442.7
130°	472.0	471.6	471.4	470.8	470.2	469.7	469.0	468.4
132.5°	496.9	496.1	495.5	494.9	494.4	493.9	493.4	492.9
135°	533.6	533.4	533.2	533.0	532.5	532.1	531.5	531.1
137.5°	568.8	568.6	568.6	568.2	567.6	566.9	566.3	565.7
140°	592.5	592.5	592.5	592.1	591.6	590.9	590.3	589.7
142.5°	613.9	614.0	614.1	613.9	613.2	612.6	612.1	611.4
145°	646.4	646.6	646.8	646.5	645.9	645.2	644.6	644.0
147.5°	674.9	675.3	675.6	675.6	674.9	674.3	673.8	673.2
150°	693.0	693.5	694.0	694.0	693.5	693.0	692.6	692.1
152.5°	711.1	711.8	712.3	712.3	711.8	711.1	710.5	710.0
155°	734.1	734.9	735.7	735.8	735.3	734.9	734.4	734.0
157.5°	755.3	756.3	757.4	757.5	756.8	756.1	755.3	754.6
160°	767.9	768.8	769.7	769.9	769.3	768.7	768.0	767.4
162.5°	779.3	780.3	781.4	781.5	780.8	780.1	779.3	778.6
165°	794.0	795.0	796.1	796.3	795.5	794.7	794.0	793.2
167.5°	806.1	807.2	808.2	808.4	807.6	806.8	806.0	805.2
170°	812.8	813.9	814.9	815.0	814.1	813.2	812.3	811.3
172.5°	817.8	818.9	819.9	820.0	819.1	818.1	817.3	816.4
175°	823.2	824.3	825.4	825.5	824.6	823.6	822.7	821.8
177.5°	825.7	826.5	827.2	827.2	826.5	825.7	825.0	824.3
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9

(END OF REPORT)